

# L6219R

### Stepper motor driver

#### Features

- Able to drive both windings of bipolar stepper motor
- Output current up to 500 mA each winding
- Wide voltage range 4.5 V to 10 V
- Half-step, full-step and microstepping mode
- Built-in protection diodes
- Internal pwm current control
- Low output saturation voltage
- Designed for unstabilized motor supply voltage
- Internal thermal shutdown

#### Description

The L6219R is a bipolar monolithic integrated circuits intended to control and drive both winding of a bipolar stepper motor or bidirectionally control two DC motors. The L6219R with a few external components form a complete control and drive circuit for LS-TTL or microprocessor controlled stepper motor system. The power stage is a dual full bridge capable of sustaining 10 V and including four diodes for current recirculation.



A cross conduction protection is provided to avoid simultaneous cross conduction during switching current direction.

An internal pulse-width-modulation (PWM) controls the output current to 500mA with peak start-up current up to 1 A. Wide range of current control from 500 mA (each bridge) is permitted by means of two logic inputs and an external voltage reference. A phase input to each bridge determines the load current direction. A thermal protection circuitry disables the outputs if the chip temperature exceeds safe operating limits.

#### Table 1. Device summary

Part number	Package	Packing
L6219R	SO-24	Tube
L6219R013TR	SO-24	Tape & reel
E-L6219R <sup>(1)</sup>	SO-24	Tube
E-L6219R013TR <sup>(1)</sup>	SO-24	Tape & reel

1. Lead free package (ECOPACK®) see Chapter 5.

## **Table of contents**

1	Bloc	k diagram and pins description5
2	Elec	trical specifications7
	2.1	Absolute maximum ratings 7
	2.2	Thermal data
	2.3	Electrical characteristics 8
3	Fund	ctional description
	3.1	Input logic (I0 and I1) 10
	3.2	Phase
	3.3	Current sensor
	3.4	Single-pulse generator 11
	3.5	Output stage
	3.6	VS, VSS, VRef
4	Арр	lication informations
	4.1	Electrical characteristics curves 13
5	Pack	age informations
6	Revi	sion history



## List of tables

	Device summary
Table 2.	Pin description
Table 3.	Absolute maximum ratings
Table 4.	Thermal data
Table 5.	Electrical characteristics
Table 6.	Input logic current level
Table 7.	Document revision history



## List of figures

Figure 1.	Block diagram	5
Figure 2.	Pin connection (top view)	5
	Windings of a bipolar stepper motor	
Figure 4.	Principle operating sequence 1	1
Figure 5.	Typical application circuit	2
Figure 6.	Maximum output current vs. supply voltage (DAC=100%)1	3
Figure 7.	Maximum reference voltages vs. supply voltage 1	3
Figure 8.	Maximum output current vs. reference voltage (DAC=100%)1	3
Figure 9.	SO-24 mechanical data and package dimensions 1	4



1

### Block diagram and pins description









Table 2.	Pin description		
Pin #	Name	Description	
1,2	Output A	See pins 5,21	
3,23	Sense resistor	Connection to lower emitters of output stage for insertion of current sense resistor	
4,22	Comparator input	Input connected to the comparators. The voltage across the sense resistor is feedback to this input throught the low pass filter RC CC. The higher power transistors are disabled when the sense voltage exceeds the reference voltage of the selected comparator. When this occurs the current decays for a time set by RT CT (toff = 1.1 RT CT). See <i>Figure 4</i>	
5,21	Output B	Output connection. The output stage is a H bridge formed by four transistors and four diodes suitable for switching applications	
6,19	Ground	See pins 7,18	
7,18	Ground	Ground connection. With pins 6 and 19 also conducts heat from die to printed circuit copper	
8,20	Input 0	See input 1 (pins 9,17)	
9,17	Input 1	These pins and pins 8,20 (input 0) are logic inputs which select the outputs of the comparators to set the current level. Current also depends on the sensing resistor and reference voltage. See funcional description	
10,16	Phase	This TTL-compatible logic inputs sets the direction of current flow through the load. a high level causes current to flow from output a (source) to output B (sink). A schmitt trigger on this input provides good noise immunity and a delay circuit prevents output stage short circuits during switching	
11,15	Reference voltage	A voltage applied to this pin sets the reference voltage of the comparators, this determining the output current (also thus depending on Rs and the two inputs input 0 and input 1)	
12,14	RC	A parallel RC network connected to this pin sets the OFF time of the higher power transistors. The pulse generator is a monostable triggered by the output of the comparators (toff = $1.1 \text{ RT CT}$ )	
13	Vss - Logic supply	Supply voltage input for logic circuitry	
24	Vs - Load supply	Supply voltage input for the output stages	

Table 2.Pin description

Note: ESD on GND, Vs, Vss, OUT 1 A and OUT 2 A is guaranteed up to 1.5 KV (human body model, 1500 W, 100 pF).



## 2 Electrical specifications

### 2.1 Absolute maximum ratings

#### Table 3. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V <sub>S</sub>	Supply voltage	30	V
Ι <sub>ο</sub>	Output current (peak)	±1	А
Ι <sub>ο</sub>	Output current (continuous)	±0.5	А
V <sub>SS</sub>	Logic supply voltage	7	V
V <sub>IN</sub>	Logic input voltage range	-0.3 to V <sub>SS</sub>	V
V <sub>sense</sub>	Sense output voltage	1.5	V
Τ <sub>J</sub>	Junction temperature	+150	°C
Т <sub>ор</sub>	Operating temperature range	-20 to +85	°C
T <sub>stg</sub>	Storage temperature range	-55 to +150	°C

### 2.2 Thermal data

#### Table 4. Thermal data

Symbol	Description		Value	Unit
R <sub>thj-case</sub>	Thermal resistance junction-case Ma	<b>K</b> .	18	°C/W
R <sub>thj-amb</sub>	Thermal resistance junction-ambient Ma	<b>k</b> .	75 <sup>(1)</sup>	°C/W

1. With minimized copper area.

57

#### 2.3 Electrical characteristics

#### Table 5. Electrical characteristics

(T<sub>j</sub> = 25 °C, V<sub>S</sub> = 4.5 V, V<sub>SS</sub> = 4.75 V to 5.25 V, V<sub>REF</sub> = 2 V, unless otherwise specified) See *Figure 5*.

Symbol	Parameter	Test Condition	Min.	Тур.	Max.	Unit
OUTPUT DRIVERS (OUT <sub>A</sub> or OUT <sub>B</sub> )						
Vs	Motor supply range		4.5		10	V
I <sub>CEX</sub>	Output leakage current	$V_{s} = 30 \text{ V}, V_{OUT} = V_{s},$ $V_{s} = 30 \text{ V}, V_{OUT} = 0$	- -50	<1 <-1	50	μΑ μΑ
V <sub>CE(sat)</sub>	Output saturation voltage	Sink driver, I <sub>OUT</sub> = +300 mA Sink driver, I <sub>OUT</sub> = +500 mA Source driver, I <sub>OUT</sub> = -300 mA Source driver, I <sub>OUT</sub> = -500 mA		0.3 0.7 1.1 1.3	0.6 1 1.4 1.6	V V V V
$V_{F}$	Clamp diode forward voltage	Sink diode Source diode I <sub>F</sub> = 500 mA		1 1	1.5 1.5	V V
I <sub>S(on)</sub>	Driver supply current	Both bridges ON, no load $V_s = 10 V$	-	8	15	mA
I <sub>S(off)</sub>	Driver supply current	Both bridges OFF, V <sub>s</sub> = 10 V	-	6	10	mA
CONTRO	LLOGIC					
V <sub>IN(H)</sub>	Input voltage	All inputs	2.4	-	-	V
V <sub>IN(L)</sub>	Input voltage	All inputs	-	-	0.8	V
I <sub>IN(H)</sub>	Input current	V <sub>IN</sub> = 2.4 V	-	<1	20	μA
I <sub>IN(L)</sub>	Input current	V <sub>IN</sub> = 0.84 V	-	-3	-200	μA
V <sub>REF</sub>	Reference voltage	Operating <sup>(1) (2)</sup>	1.5	-	2	V
I <sub>SS(ON)</sub>	Total logic supply current	$I_0 = I_1 = 0.8 \text{ V}$ , no load	-	44	60	mA
I <sub>SS(OFF)</sub>	Total logic supply current	I <sub>o</sub> = I <sub>1</sub> = 2.4 V, no load	-	10	14	mA
COMPAR	ATORS			•	•	
		I <sub>o</sub> = I <sub>1</sub> = 0.8 V	9.5	10	10.5	-
V <sub>REF</sub> /	Current limit threshold (at trip	I <sub>o</sub> = 2.4 V, I <sub>1</sub> = 0.8 V	13.5	15	16.5	-
V <sub>sense</sub>	point)	l <sub>o</sub> = 0.8 V, l <sub>1</sub> = 2.4 V	25.5	30	34.5	-
t <sub>off</sub>	Cutoff time	$R_{t} = 56 \text{ K}\Omega \text{ C}_{t} = 820 \text{ pF}$	-	50		μs
t <sub>d</sub>	Turn off delay	see Figure 1	-	1		μs
PROTEC	ΓΙΟΝ					
Tj	Thermal shutdown temperature		-	170	-	°C
-	1		I		L	I

1. The maximum reference voltage accepted by the device depends from the supply voltage Vs (see Figure 7).

 To reduce the switching losses the base bias of the bridge's low side NPN transistor is proportional to the DAC output, then the output current driving capability is also proportional to the DAC output voltage (see *Figure 6* and *Figure 8* for DAC=100%, it is proportional for lower percentages).







### 3 Functional description

The circuit is intended to drive both windings of a bipolar stepper motor.

The peak current control is generated through switch mode regulation. There is a choice of three different current levels with the two logic inputs  $I_{01} - I_{11}$  for winding 1 and  $I_{02} - I_{12}$  for winding 2.

The current can also be switched off completely

### 3.1 Input logic ( $I_0$ and $I_1$ )

The current level in the motor winding is selected with these inputs. (See Figure 4)

If any of the logic inputs is left open, the circuit will treat it has a high level input.

I <sub>0</sub>	I <sub>1</sub>	Current level
Н	Н	No current
L	Н	Low current 1/3 I <sub>O</sub> max
Н	L	Medium current 2/3 I <sub>O</sub> max
L	L	Maximum current I <sub>O</sub> max

Table 6.Input logic current level

#### 3.2 Phase

This input determines the direction of current flow in the windings, depending on the motor connections. The signal is fed through a schmidt-trigger for noise immunity, and through a time delay in order to guarantee that no short-circuit occurs in the output stage during phase-shift. High level on the phase input causes the motor current flow from out A through the winding to out B

#### 3.3 Current sensor

This part contains a current sensing resistor (R<sub>S</sub>), a low pass filter (R<sub>C</sub>, C<sub>C</sub>) and three comparators. Only one comparator is active at a time. It is activated by the input logic according to the current level chosen with signals I<sub>o</sub> and I<sub>1</sub>. The motor current flows through the sensing resistor RS. When the current has increased so that the voltage across R<sub>S</sub> becomes higher than the reference voltage on the other comparator input, the comparator goes high, which triggers the pulse generator.

The max peak current Imax can be defined by:

$$I_{max} = \frac{V_{ref}}{10R_s}$$

See figures Figure 3, 4 and 5 for maximum allowable output current and reference voltage versus  $V_s$  supply.

#### 3.4 Single-pulse generator

The pulse generator is a monostable triggered on the positive going edge of the comparator output. The monostable output is high during the pulse time, toff , which is determined by the time components  $R_t$  and  $C_t$ .

$$t_{off} = 1.1 \cdot R_t C_t$$

The single pulse switches off the power feed to the motor winding, causing the winding current to decrease during toff. If a new trigger signal should occur during toff, it is ignored.

#### 3.5 Output stage

The output stage contains four darlington transistors (source drivers) four saturated transistors (sink drivers) and eight diodes, connected in two H bridge.

#### Figure 4. Principle operating sequence



The source transistors are used to switch the power supplied to the motor winding, thus driving a constant current through the winding. It should be noted however, that is not permitted to short circuit the outputs.

Internal circuitry is added in order to increase the accuracy of the motor current particularly with low current levels.

### 3.6 $V_S, V_{SS}, V_{Ref}$

The circuit will stand any order of turn-on or turn-off the supply voltages  $\rm V_S$  and  $\rm V_{SS}.$  Normal dV/dt values are then assumed.

Preferably,  $V_{Ref}$  should be tracking  $V_{SS}$  during power-on and power-off if  $V_S$  is established.

### 4 Application informations

Some stepper motors are not designed for contin-uous operation at maximum current. As the circuit drives a constant current through the motor, its temperature might increase exceedingly both at low and high speed operation. Also, some stepper motors have such high core losses that they are not suited for switch mode current regulation.

Unused inputs should be connected to proper voltage levels in order to get the highest noise immunity. As the circuit operates with switch mode current regulation, interference generation problems might arise in some applications. A good measure might then be to decouple the circuit with a 100 nF capacitor, located near the package between power line and ground. The ground lead between Rs, and circuit GND should be kept as short as possible. A typical application circuit is shown in *Figure 5*. Note that Ct must be NPO type or similar else. To sense the winding current, paralleled metal film resistors are recommended ( $R_s$ )



Figure 5. Typical application circuit.



### 4.1 Electrical characteristics curves

# Figure 6.Maximum output current vs. supply Figure 7.<br/>voltage (DAC=100%)Maximum reference voltages vs.<br/>supply voltage



Figure 8. Maximum output current vs. reference voltage (DAC=100%)



57

### 5 Package informations

In order to meet environmental requirements, ST offers these devices in ECOPACK® packages. These packages have a Lead-free second level interconnect. The category of second Level Interconnect is marked on the package and on the inner box label, in compliance with JEDEC Standard JESD97. The maximum ratings related to soldering conditions are also marked on the inner box label. ECOPACK is an ST trademark.

ECOPACK specifications are available at: www.st.com.



Figure 9. SO-24 mechanical data and package dimensions

## 6 Revision history

#### Table 7.Document revision history

Date	Revision	Changes
09-Jan-2003	1	First Issue
06-May-2005	2	Modified Table 2 on page 6.
22-Jun-2006	3	Changed look anf fill. Changed value of the Output Current (continuous) in <i>Table 3</i> . Changed the curve diagrams of the <i>Figure 6</i> and <i>7</i> .
05-Sep-2008	4	Added note 1 and 2 in Table 5 on page 8.



#### Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZE REPRESENTATIVE OF ST, ST PRODUCTS ARE NOT DESIGNED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS, WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2008 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan -Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com

