16-Channel, High-Voltage Analog Switch without High-Voltage Supply Requirement

General Description

The MAX14866 is a 16-channel, high-voltage (HV), analog SPST switch primarily intended for HV multiplexing in ultrasound applications.

The MAX14866 operates from one only low-voltage supply (+5V) and does not require dedicated HV supplies, resulting in cost-saving and system simplification. Moreover, for in-probe applications, HV supplies do not need to be associated with the MAX14866 in the probe/ transducer head, resulting in greater safety and easier compliance with safety regulations.

The MAX14866 features best-in-class performance in terms of bandwidth (up to 50MHz), charge injection (<100pC), and linear transmit input range (up to 210V_{PKPK}). The low-signal switch R_{DSON} is typically about 7 Ω around 0V and remains flat in the entire input range ensuring extremely good linearity.

The latchup-free SOI (Silicon-on-Insulator) technology and the wide analog range results in extremely high robustness during undershoots and overshoots that occur in ultrasound systems due to the resonant nature of the load.

The status of the switches can be individually controlled through a high-speed SPI interface (up to 30MHz). Daisy-chain architecture is supported.

Alternatively, switches can also be controlled with global control signal (SET and CLR) for bank selections or relay replacement applications.

The MAX14866 is offered in two different packages: wafer-level packages (WLPs) and TQFNs. The 110bump WLP size is only 5.53 x 5.47mm, resulting in less than 1.9mm²/channel footprint and allowing for very high levels of integration, which is especially beneficial for in-probe applications.

The size of the TQFN package is an industry standard 48-pin, 7mm x 7mm package.

Applications

- Medical Ultrasound Imaging
- Relays replacements
- NDT
- Printers

Benefits and Features

- Flexibility and Ease-of-Design
 - HV Switches Operate From +5V Supply Only–Eliminating Dedicated High-Voltage Supplies Eases Probe Compliance To Industry Safety Standards
 - SOI Technology–Latchup Free
 - Large Analog Input range (up to 210VPKPK)
 - 16 Independent SPST Ensure Flexibility Supporting All Possible MUX Combinations
 - Switches Can Be Controlled Either Individually or Globally (Bank Selection)
 - 30MHz SPI Interface for Individually Programming the Status of the Switches
 - SET and CLR CMOS for global control of the switches (Bank Selection or Relay Replacements Applications)
 - Extended Digital Logic Input Range From 1.8V to 5V
- High Level Of Integration and Density for Space-Saving Applications
 - 16 Channels Linear SPST switches
 - < 1.9mm²/channel footprint (WLP)
- High Performance:
 - Low R_{ON} (7Ω typ) Ensures Low Insertion Loss
 - R_{ON} Flatness in the Entire Input Range Ensures Excellent Performances In Harmonic Imaging
 - Low Charge Injection <100pC.
 - Wide Bandwidth of Operation (Up to 50MHz)
 - Low On Input Capacitance (33pF) Low Off Input Capacitance (7.7pF)
 - Excellent Off Isolation (-75dB at 5MHz)
 Excellent Crosstalk Performances (-62dB at 5MHz)

Ordering Information appears at end of data sheet.



16-Channel, High-Voltage Analog Switch without High-Voltage Supply Requirement

Absolute Maximum Ratings

V _{CC} to GND	0.3V to 5.6V
V _{DD} to GND	0.3V to 5.6V
COMx to GND, x = 015	
NOx to GND, x = 015	
COMx to NOx, x = 015	
SDIN to GND	0.3V to 5.6V
SDOUT to GND	0.3V to V _{DD} + 0.3V
LE to GND	0.3V to 5.6V
CLK to GND	0.3V to 5.6V
CLR to GND	0.3V to 5.6V
SET to GND	0.3V to 5.6V

Package Thermal Characteristics (Note 1)

110-Bump WLP	
Junction-to-Ambient Thermal Resistance (θ_{JA}) .	26.93°C/W
Junction-to-Case Thermal Resistance (0JC)	N/A

QFN Continuous Power Dissipation (Single Layer Board, T _A = +70°C,
derate 27.8mW/°C above +70°C.)0mW to 2222mW
QFN Continuous Power Dissipation
(Multilayer Board, T _A = +70°C,
derate 40 mW/°C above +70°C.)0mW to 3200mW
VLP Continuous Power Dissipation
(Multilayer Board, T _A = +70°C,
derate 37mW/°C above +70°C.)0mW to 2960mW
Dperating Temperature Range0°C to 85°C
lunction Temperature +150°C
Storage Temperature Range
Soldering Temperature (reflow)

48-Pin TQFN

Junction-to-Ambient Thermal Resistance (θ_{JA})	.25°C/W
Junction-to-Case Thermal Resistance (θ_{JC})	1°C/W

Note 1: Package thermal resistances were obtained using the method described in JEDEC specification JESD51-7, using a four-layer board. For detailed information on package thermal considerations, refer to www.maximintegrated.com/thermal-tutorial.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

Electrical Characteristics

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
POWER SUPPLIES			·			
V _{DD} Logic Supply Voltage	V _{DD}		1.7		5.5	V
V _{DD} Static Current	I _{DDS}			1	5	μA
V _{DD} Dynamic Current	IDD	V _{DD} = +5V, f _{CLK} = 5MHz, f _{DIN} = 2.5MHz, CDOUT = 15pF		300		μA
V _{CC} Supply Static Current	Iccs	All switches remain on or off, COM_= NO_= GND		240	425	μA
V _{CC} Supply Dynamic Current	Icc	All Channel Switching, f = 50kHz		5.2	8.5	mA
V _{CC} Supply Voltage Range	V _{CC}		4.75	5	5.25	V
LOGIC LEVELS						
Logic-Input Low Voltage	V _{IL}				0.33 x V _{DD}	V
Logic-Input High Voltage	VIH		0.66 x V _D	D		V
Logic-Output Low Voltage	V _{OL}	I _{SINK} = 1mA			0.2	V
Logic-Output High Voltage	V _{OH}	I _{SOURCE} = 1mA	V _{DD} -0.2			V
Logic-Input Capacitance	C _{IN}			5		pF

16-Channel, High-Voltage Analog Switch without High-Voltage Supply Requirement

Electrical Characteristics (continued)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
Logic-Input Leakage	I _{IN}	CLK, DIN pins	-1		+1	μA
LEB Pullup Resitor	R _{PU}		70	100		ΚΩ
CLR, SET Pulldown Resistor	R _{PDW}		70	100		ΚΩ
SWITCH CHARACTERISTICS		-				<u>.</u>
Analog Dynamic Signal Range	V _{SW} _	AC operation only, f > 500kHz	-105		+105	V
Small Signal On-Resistance	R _{ONS}	V(NO) = 0V, I(COM) = 5mA		7	13	Ω
Small Signal On-Resistance Matching	DRONS	3 std, VNO_ = 0V, ICOM_ = 5mA		3		%
Switch Symmetry	Symm	AC measured, 100Ω Resistive load NO and GND. Transmit bipolar low frequency pulse $\pm 80V$, f = 0.5MHz Compare positive and negative output level on NO Symmetry = $[V_{OP} - V_{ON}]/[0.5 x (V_{OP} + V_{ON})]$		±1		%
Analog Switch Peak Current	I _{PEAK}	V(NO) = GND, V(COM) HV pulse 100ns duration		2.7		А
COM to GND Leakage Current Switch OFF	ICOMOFF	V(COM) = ±100mV	-1		+1	uA
COM to GND Equivalent Resistor. Switch ON	R _{COMON}	V(COM) = 100mV	60	82	104	ΚΩ
NO to GND Equivalent Resistor. Switch OFF	R _{NOOFF}	V(NO) = 100mV	35	52	65	ΚΩ
NO to GND Equivalent Resistor Switch ON	R _{NOON}	V(NO) = 100mV	60	82	104	ΚΩ
Switch-Off DC Offset COM Pin	V _{OFF1}	Ref. Test Circuit R = 100KΩ	-5		+6	mV
Switch-Off DC Offset NO Pin	V _{OFF2}	Ref. Test Circuit R = 100KΩ	-5		+6	mV
Switch-On DC Offset	V _{OFF3}	Ref. Test Circuit R = 100KΩ	-5		+9	mV
SWITCH DYNAMIC CHARACTE	RISITICS	·				
Turn-On Time	ton	Ref. Test Circuit. VCOM_ = +1V, R _L = 50Ω , from switch ON digital command to 90% of the transition completed			4	μs
Turn-Off Time	t _{OFF}	Ref. Test Circuit VCOM_ = +1V, R _L = 50Ω from switch OFF digital command to 90% of the transition completed			4	μs
Off-Isolation in Transmission (TX)	V _{ISOTX}	Ref. Test Circuit		-75		dB

16-Channel, High-Voltage Analog Switch without High-Voltage Supply Requirement

Electrical Characteristics (continued)

PARAMETER	SYMBOL	CONDITIONS	MIN TYP	MAX	UNITS
		Ref. Test Circuit. ZL = 50Ω	-80		
Off-Isolation in Reception (RX)	VISORX	Ref. Test Circuit. ZL = 1kΩ//15pF	-60	dB	
Crosstalk	V _{CT}	Ref Test Circuit. RX and TX with switches open or closed	-62		dB
SW_ Off-Capacitance Small-Signal - NO Pin	C _{SW_(OFF)}	f = 5MHz, 100mV _{PK} on NO pin	7.7		pF
SW_ On-Capacitance Small-Signal	C _{SW_(ON)}	f = 5MHz, 100mV _{PK}	33		pF
SW_Off-Capacitance Small-Signal - COM Pin	C _{SW_(OFF)}	f = 5MHz, 100mV _{PK} on COM pin	11		pF
SW_ Off-Capacitance Large-Signal - COM Pin	C _{SW_(OFF)}	f = 5MHz, 100V _{PK} on COM pin	11		pF
SW_ On-Capacitance Large-Signal	C _{SW_(ON)}	f = 5MHz, 100V _{PK}	16		pF
Charge Injection	QCH	Ref. Test Circuit	<100		рС
Output Voltage Spike	V _{SPK}	Ref. Test Circuit	65		mVpkpk
Large-signal Analog Bandwidth (-3dB)	f _{BW_L}	CLOAD = 200pF, 60V amplitude sinusoidal burst, 1% duty cycle	>50		MHz
Small-signal Analog Bandwidth (-3dB)	f _{BW_S}	CLOAD = 200pF, 100mV amplitude sinusoidal signal	80	MHz	
TIMING CHARACTERISTICS			L		
2nd Harmonic Distortion HV	THD2	f _{OUT} = 5MHz, Transmit amplitude 200V _{PKPK} square wave (20 cycles), NO Load: 100Ω // 100pF	-45	dBc	
Pulse Cancellation 1 Fundamental	PC1	$f_{OUT_}$ = 1MHz - 5MHz, Transmit amplitude 200V _{PKPK} , 2 cycles. Strength ratio of the strongest spurious signal of the sum function in the f0 ± f0/2 bandwidth to the fundamental signal. NO Load: 100Ω // 100pF		dBc	
Pulse Cancellation 2 Second Harmonic	PC2	$f_{OUT_}$ = 1MHz - 5MHz, Transmit Amplitude 200V _{PKPK} , 2 cycles. Strength ratio of the strongest spurious signal of the sum function in the 2 x f0 ± f0/2 bandwidth to the fundamental signal. NO Load: 100Ω // 100pF	-40		dBc

16-Channel, High-Voltage Analog Switch without High-Voltage Supply Requirement

Electrical Characteristics (continued)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS						
TIMING CHARACTERISTICS/SPI TIMINGS												
CLK Frequency	fCLK				30	MHz						
DIN to CLK Setup Time	t _{DS}		3			ns						
DIN to CLK Hold Time	t _{DH}		3			ns						
CLK to $\overline{\text{LE}}$ Setup Time	t _{CS}		3			ns						
LE Low Pulse Width	t _{WL}		5			ns						
CLR High Pulse Width	t _{WC}		115			ns						
SET High Pulse Width	t _{WS}		115			ns						
CLK Rise and Fall Times	t _R , t _F				50	ns						
CLK to DOUT Delay	t	V _{DD} from 2.5V - 5% to 5V + 5%, CDOUT = 15pF	5		20	20						
	t _{DO}	V _{DD} = +1.8V ± 5%, CDOUT = 15pF	5		30	ns						

16-Channel, High-Voltage Analog Switch without High-Voltage Supply Requirement

Typical Operating Characteristics

 V_{DD} = 3V, V_{CC} = 5V, T_A = 25°C, unless otherwise noted.



16-Channel, High-Voltage Analog Switch without High-Voltage Supply Requirement

Typical Operating Characteristics (continued) $V_{DD} = 3V$, $V_{CC} = 5V$, $T_A = 25^{\circ}C$, unless otherwise noted.













16-Channel, High-Voltage Analog Switch without High-Voltage Supply Requirement

Pin Configurations



16-Channel, High-Voltage Analog Switch without High-Voltage Supply Requirement

Pin Description

F	PIN		
MAX14866 WLP	MAX14866 TQFN	NAME	FUNCTION
B2	1	COM0	Analog Switch 0 - Terminal
C3	2	NO0	Analog Switch 0 - Terminal
A3	3	COM1	Analog Switch 1 - Terminal
B4	4	NO1	Analog Switch 1 - Terminal
C5	5	COM2	Analog Switch 2 - Terminal
A5	6	NO2	Analog Switch 2 - Terminal
B6	7	COM3	Analog Switch 3 - Terminal
A7	8	NO3	Analog Switch 3 - Terminal
E4–E7	9	GND	Ground
F1–F7	10	GND	Ground
C7	11	COM4	Analog Switch 4 - Terminal
A9	12	NO4	Analog Switch 4 - Terminal
B8	13	COM5	Analog Switch 5 - Terminal
B10	14	NO5	Analog Switch 5 - Terminal
C11	15	COM6	Analog Switch 6 - Terminal
C9	16	NO6	Analog Switch 6 - Terminal
D10	17	COM7	Analog Switch 7 - Terminal
E11	18	NO7	Analog Switch 7 - Terminal
F9	19	NO8	Analog Switch 8 - Terminal
G10	20	COM8	Analog Switch 8 - Terminal
H9	21	NO9	Analog Switch 9 - Terminal
H11	22	COM9	Analog Switch 9 - Terminal
J10	23	NO10	Analog Switch 10 - Terminal
J8	24	COM10	Analog Switch 10 - Terminal
K9	25	NO11	Analog Switch 11 - Terminal
H7	26	COM11	Analog Switch 11 - Terminal
	27	GND	Ground
	28	GND	Ground
K7	29	NO12	Analog Switch 12 - Terminal
J6	30	COM12	Analog Switch 12 - Terminal
K5	31	NO13	Analog Switch 13 - Terminal
H5	32	COM13	Analog Switch 13 - Terminal
J4	33	NO14	Analog Switch 14 - Terminal

16-Channel, High-Voltage Analog Switch without High-Voltage Supply Requirement

Pin Description (continued)

Р	IN		FUNCTION					
MAX14866 WLP	MAX14866 TQFN	NAME	FUNCTION					
К3	34	COM14	Analog Switch 14 - Terminal					
H3	35	NO15	Analog Switch 15 - Terminal					
J2	36	COM15	Analog Switch 15 - Terminal					
	37	GND	Ground					
G2	38	LE	CMOS Digital Logic Input. Active-Low Latch Enable Input					
H1	39	DOUT	CMOS Digital Logic Output - SPI Data Output					
G1	40	VDD	Positive LV supply input for digital I/O (from 1.7V to 5.5V). Bypass VDD to GND with a 0.1μ F or greater ceramic capacitor					
	41	GND	Ground					
	42	GND	Ground					
E1, E2	43	VCC	Positive LV Supply Input (+5V). Bypass VCC to GND with a $0.1\mu F$ or greater ceramic capacitor					
E3	44	DIN	CMOS Digital Logic Input - SPI Data Input					
D1	45	CLK	CMOS Digital Logic Input - SPI Clock Input					
C1	46	SET	CMOS Digital Logic Input - Asynchrounous Set Input					
D2	47	CLR	CMOS Digital Logic Input - Asynchronous Clear Input					
	48	GND	Ground					
_	EP		Exposed PAD (Thermal PAD). Connet EP to GND					
A1, A2, A4, A6, A8, A10, A11, B1, B3, B5, B7,B9,B11, C2, C4, C6, C8, C10, D3-D9, D11, E8-E10, F8, F10, F11, G3-G9, G11, H2, H4, H6, H8, H10, J1, J3, J5, J7, J9, J11, K1, K2, K4, K6, K8, K10, K11	_	N.C.	Not internally connected					

16-Channel, High-Voltage Analog Switch without High-Voltage Supply Requirement

Functional (or Block) Diagram



16-Channel, High-Voltage Analog Switch without High-Voltage Supply Requirement

Detailed Description

The MAX14866 is a 16-channel, high-voltage (HV), Analog SPST switch primarily intended for HV multiplexing in ultrasound applications.

The MAX14866 operates from one only low voltage supply (+5V) and does not require dedicated HV supplies resulting in cost saving and system simplification. Moreover, for in-probe applications, HV supplies do not need to be associated with the MAX14866 in the probe/transducer head, resulting in greater safety and easier compliance to safety regulations.

The MAX14866 features best-in-class performances in terms of bandwidth (up to 50MHz), charge injection (<100pC) and linear transmit input range (up to $210V_{PKPK}$). The low signal switch R_{DSON} is typically about 7 Ω around 0V and remains flat in the entire input range ensuring extremely good linearity.

The latch-up free SOI (Silicon-on-Insulator) technology and the wide analog range results in extremely high robustness during undershoots and overshoots which occur in ultrasound systems due to the resonant nature of the load.

The status of the switches can be individually controlled through a high speed SPI interface (up to 30MHz). Daisy-chain architecture is supported.

Alternatively, switches can also be controlled with global control signal (SET and CLR) for bank selections or relay replacement applications.

The MAX14866 is offered in two different packages: wafer-level package (WLP) and Thin-QFN (TQFN). The 110-Bump WLP size is only 5.53 x 5.47mm, resulting in less than 1.9mm²/channel footprint and allowing for very high levels of integration which is beneficial especially for in-probe applications.

The size of the TQFN package is an industry standard 48-pin 7mm x 7mm package.

Analog Switches

The MAX14866 can transmit undistorted analog signals up to $210V_{P-P}$. For reliable operation, the maximum drop between input and output of the switch (pins COM and NO) must be less than 110V (refer to the absolute maximum rating in the <u>Electrical Characteristics</u> table)

It is required that the input signal is set at GND prior to HV transmission. The minimum guaranteed transmit frequency is 500KHz. The switch is not symmetrical. Transducer elements must be connected to pin named NOx (x = 0..15) while the transmit/receive front end circuits must be connected to the pin named COMx (x = 0..15). Refer to the Typical Application Circuit for further details.

Voltage Supply

The MAX14866 operates from a low voltage supply V_{CC} = +5V ±5%, and a logic supply V_{DD} (from +1.7V to +5.5V). In particular, if the logic high level of the control input signals (SPI, CLR, SET) is +5V, the two supply voltage inputs V_{DD} and V_{CC} can be connected together and the part can operate from one single +5V supply.

Local bypassing on supply voltage inputs is required (C > 100nF).

Bleed Resistors

The MAX14866 features integrated bleed resistors. Bleed resistors are intended to fully discharge the transducers and eliminate any voltage built up. The bleed resistor values depends on the status of the switch. Refer to the *Electrical Characteristics* table and to Figure 1 for further details.

Heading RST

The MAX14866 Equivalent Electrical Circuit is shown in <u>Figure 1</u> under different conditions depending on the status of the switch (on/off) and on the level of the signal (small-signal/large-signal).

16-Channel, High-Voltage Analog Switch without High-Voltage Supply Requirement



Figure 1. Electrical Equivalent Circuit

- Note 3: The large-signal NO equivalent input impedance (30Ω typical) is shown for completeness only. It is intended that the High Voltage excitation signals are applied to terminal COM only so that no any HV transmit burst will hit terminal NO whenever the switch is programmed off.
- Note 4: Resistances and capacitances values are typical.

Transmit Operations: High-Voltage Bursts (Voltage Amplitude Greater Than 20V_{PK})

The MAX14866 is capable of transmitting long High Voltage Bipolar Bursts (from $40V_{PKPK}$ to $210V_{PKPK}$) with excellent linearity and stability. When transmitting Bipolar HV bursts (amplitude greater than $20V_{PK}$) the device is not sensitive to the DC content of the signal.

In particular, the MAX14866 supports long burst excitation modes like the ones commonly used in Elastography. The user must ensure that the total dissipated power can be handled by the package.

Unipolar transmission is supported up to 100Vpk-to-pk only.

For reliability reasons, it is requested that both the switch input and output (COM and NO pins) are set at ground before the transmission is initiated.

Transmit Operations: Continuous Wave

Bipolar Continuous Wave Operation (CW) is supported for transmit voltages less than $20V_{PKPK}$ (amplitude less than 10V). It is required that the DC content (offset) of the CW transmit waveform is less than ±1V. Larger DC offsets during CW operation results in signal degradation and can affect the device reliability. In particular, unipolar CW operation is not supported.

Serial Interface

The MAX14866 is controlled by a serial interface with a 16-bit serial shift register and transparent latch. Each of the 16 data bits controls a single analog switch (see Table 1). Data on DIN is clocked with the most significant bit (MSB) first into the shift register on the rising edge of CLK. Data is clocked out of the shift register onto DOUT on the rising edge of CLK. DOUT reflects the status of DIN, delayed by 16 clock cycles (see Figure 2 and Figure 3).

Changing the switch status (from on to off or viceversa) during the transmission of the analog signal is not permitted and can result in reliability issues. The user must ensure that the analog input is kept quiet at GND before any SPI programming session and during the entire settling time of the switches (T_{ON} , T_{OFF}). Similarly the user must ensure that the analog input is quiet at GND before asserting either the CLR or the SET signal and during the entire settling time of the switches (T_{ON} , T_{OFF}).

16-Channel, High-Voltage Analog Switch without High-Voltage Supply Requirement

			DATA	BITS	5						CONT	ROL B	ITS				FUNCTIO	N
D0 (LSB)	D1	D2	D3	D4	D5	D6	D7	ĪĒ	CLR	SET	SW0	SW1	SW2	SW3	SW4	SW5	SW6	SW7
L								L	L	L	OFF							
н								L	L	L	ON							
	L							L	L	L		OFF						
	Н							L	L	L		ON						
		L						L	L	L			OFF					
		н						L	L	L			ON					
			L					L	L	L				OFF				
			Н					L	L	L				ON				
				L				L	L	L					OFF			
				н				L	L	L					ON			
					L			L	L	L						OFF		
					Н			L	L	L						ON		
						L		L	L	L							OFF	
						н		L	L	L							ON	
							L	L	L	L								OFF
							Н	L	L	L								ON
Х	Х	Х	Х	Х	Х	Х	Х	Н	L	L								
Х	Х	Х	Х	Х	Х	Х	Х	Х	н	Х	OFF	OFF	OFF	OFF	OFF	OFF	OFF	OFF
Х	Х	Х	Х	Х	Х	Х	Х	Х	L	н	ON	ON	ON	ON	ON	ON	ON	ON
			DATA	BITS	3						CONT	ROL B	ITS			I	FUNCTIO	N
D8	D9	D10	D11	D12	D13	D14	D15 (MSB)	ĪĒ	CLR	SET	SW8	SW9	SW10	SW11	SW12	SW13	SW14	SW15
L								L	L	L	OFF							
Н								L	L	L	ON							
	L							L	L	L		OFF						
	Н							L	L	L		ON						
		L						L	L	L			OFF					
		Н						L	L	L			ON					
			L					L	L	L				OFF				
			Н					L	L	L				ON				
				L				L	L	L					OFF			
				н				L	L	L					ON			
					L			L	L	L						OFF		
					н			L	L	L						ON		

Table 1. SPI Programming and Logic Table

16-Channel, High-Voltage Analog Switch without High-Voltage Supply Requirement

			DATA		5			CONTROL BITS								FUNCTION			
D8	D9	D10	D11	D12	D13	D14	D15 (MSB)	ĪĒ	CLR	SET	SW8	SW9	SW10	SW11	SW12	SW13	SW14	SW15	
						L		L	L	L							OFF		
						н		L	L	L							ON		
							L	L	L	L								OFF	
							Н	L	L	L								ON	
х	Х	х	Х	Х	Х	х	Х	н	L	L	HOLD PREVIOUS STATE								
Х	Х	Х	Х	Х	Х	Х	Х	Х	н	Х	OFF	OFF	OFF	OFF	OFF	OFF	OFF	OFF	
Х	X	Х	Х	Х	Х	Х	Х	Х	L	Н	ON	ON	ON	ON	ON	ON	ON	ON	

Table 1. SPI Programming and Logic Table (continued)

Note 5: TNote 5: The 16 switches operate independently.

Note 6: Serial data is clocked in on the rising edge of CLK.

Note 7: The switches go to a state retaining their present condition on the rising edge of $\overline{\text{LE}}$. When $\overline{\text{LE}}$ is low, the shift register data flows through the latch.

Note 8: DOUT is the data output pin of the 16 bits shift register. It always reflects the status of DIN delayed by 16 clock cycles.

Note 9: Shift register clocking has no effect on the switch states if \overline{LE} is high.

Note 10: The CLR input overrides all other inputs.

SPI Programming Inhibition During Transmit

The MAX14866 cannot be programmed during the transmission of HV bursts. The device features a transmit detector circuit. If a transmit input signal greater than $\pm 2V$ is detected, any SPI programming is inhibited for 4.5µs max. During such an interval any attempts of programming the part via the SPI is ignored and the previous device status is hold. This function prevents faults caused by false programming of the logic due to the large switching noise occurring during HV transmit.

LE description

Drive \overline{LE} logic-low to change the contents of the latch and update the state of the high-voltage switches (Figure 3). Drive \overline{LE} logic-high to freeze the contents of the latch and prevent changes to the switch states. To reduce noise due to clock feedthrough, drive \overline{LE} logic-high while data is clocked into the shift register. After the data shift register is loaded with valid data, pulse \overline{LE} logic-low to load the contents of the shift register into the latch.

CLR description

The MAX14866 features a latch clear input. Drive CLR logic-high to reset the contents of the latch to zero and open all switches. CLR does not affect the contents of the data shift register. Pulse $\overline{\text{LE}}$ logic-low to reload the contents of the shift register into the latch.

SET description

The MAX14866 features a latch set input. Drive SET logic-high to set the contents of the latch to logic-high and close all switches. SET does not affect the contents of the data shift register. Pulse $\overline{\text{LE}}$ logic-low to reload the contents of the shift register into the latch. CLR is dominant with respect to SET.

Power-On reset

The MAX14866 features a power-on-reset circuit to ensure all switches are open at power-on. The internal 16-bit serial shift register and latch are set to zero on power-up.

16-Channel, High-Voltage Analog Switch without High-Voltage Supply Requirement



Figure 2. Timings

16-Channel, High-Voltage Analog Switch without High-Voltage Supply Requirement



Figure 3. SPI Programming

16-Channel, High-Voltage Analog Switch without High-Voltage Supply Requirement

Test Circuits 1



16-Channel, High-Voltage Analog Switch without High-Voltage Supply Requirement

Test Circuits 2



16-Channel, High-Voltage Analog Switch without High-Voltage Supply Requirement

Applications Information

Power Supply

The MAX14866 does not require dedicated high-voltage supplies; at a minimum, the device operates from a single LV supply only ($V_{CC} = V_{DD} = +5V$).

 V_{DD} (supply voltage input for CMOS logic input) can be set at a lower voltage than V_{CC} and can vary from +1.8V to +5V depending on the voltage level of CMOS logic signals.

Logic Inputs

The MAX14866 digital interface inputs CLK, DIN, \overline{LE} , CLR, SET operate on the V_{DD} logic supply voltage.

Daisy Chain

Digital output DOUT is provided to allow the programming of multiple MAX14866 devices in daisy-chain configuration (Figure 4). Connect each DOUT to the DIN of the subsequent device in the chain. Connect CLK, \overline{LE} , CLR, and SET inputs of all devices, and drive \overline{LE} logic-low to update all devices simultaneously. Drive CLR high to open all the switches simultaneously.

Banks-Switching Applications

For relay replacement applications or any application in which the user needs to control the status of all the switches simultaneously so that independent control is not needed (bank selection, bi-plane or triplane probes, multidimensional array etc ..), CLR and SET command can be used to control the status of all the switches simultaneously. Notice that the CLR logic input is dominant with respect to the SET logic input so that CLR = SET = High corresponds to a Clear command (see <u>Table 1</u>). Therefore, in these applications, one only control signal is required since the the user can toggle the CLR signal only while the SET input can be tied to V_{DD}. Whenever the SPI is not used, connect DIN and CLK to GND and $\overline{\text{LE}}$ to V_{DD} and leave D_{OUT} unconnected.

Power Sequencing and Bypassing

The MAX14866 does not require special sequencing of the V_{DD}, V_{CC} supply voltages. Bypass V_{DD}, V_{CC} to GND with greater than 0.1μ F ceramic capacitor as close as possible to the device.



Figure 4. Daisy-Chain Connection

16-Channel, High-Voltage Analog Switch without High-Voltage Supply Requirement

Typical Application Circuit



Figure 5. Application Diagram

16-Channel, High-Voltage Analog Switch without High-Voltage Supply Requirement

Ordering Information

PART	TEMP RANGE	PIN-PACKAGE	
MAX14866UWZ+	0°C to 85°C	110 WLP (5.47mm x 5.53mm)	
MAX14866UTM+	0°C to 85°C	48 TQFN (7mm x 7mm)	

+Denotes a lead (Pb)-free package/RoHS-compliant package

Chip Information

PROCESS: DICMOS

Package Information

For the latest package outline information and land patterns (footprints), go to <u>www.maximintegrated.com/packages</u>. Note that a "+", "#", or "-" in the package code indicates RoHS status only. Package drawings may show a different suffix character, but the drawing pertains to the package regardless of RoHS status.

PACKAGE TYPE	PACKAGE CODE	OUTLINE NO.	LAND PATTERN NO.
110 Bump WLP	W1105C5+1	<u>21-11001051</u>	Refer to Application Note 1891
48 Pin TQFN	T4877+6	<u>90-0130</u>	Refer to Application Note 1891

16-Channel, High-Voltage Analog Switch without High-Voltage Supply Requirement

Revision History

REVISION NUMBER	REVISION DATE	DESCRIPTION	PAGES CHANGED
0	7/17	Initial release	—
1	4/18	Updated Pin Description table	10

For pricing, delivery, and ordering information, please contact Maxim Direct at 1-888-629-4642, or visit Maxim Integrated's website at www.maximintegrated.com.

Maxim Integrated cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim Integrated product. No circuit patent licenses are implied. Maxim Integrated reserves the right to change the circuitry and specifications without notice at any time. The parametric values (min and max limits) shown in the Electrical Characteristics table are guaranteed. Other parametric values quoted in this data sheet are provided for guidance.