

Ceramic transient voltage suppressors

SMD multilayer transient voltage suppressors for automotive applications

The following products presented in this data sheet are being withdrawn.

| Ordering Code | Substitute Product | Date of Withdrawal | Deadline Last Orders | Last Shipments |
|-----------------|--------------------|--------------------|----------------------|----------------|
| B72510T5250K062 | | 2012-11-09 | 2013-03-01 | 2013-06-01 |

For further information please contact your nearest EPCOS sales office, which will also support you in selecting a suitable substitute. The addresses of our worldwide sales network are presented at www.epcos.com/sales.

© EPCOS AG 2015. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

EPCOS AG is a TDK Group Company.

Multilayer varistors (MLVs)

Automotive series

SMD

EPCOS type designation system for automotive series

| CN | 2220 | S | 14 | B | AUTO | E2 | G2 | K2 |
|---|------|---|----|---|------|----|----|----|
| <p>Construction: CT \triangleq Single chip with nickel barrier termination (AgNiSn) CN \triangleq Single chip with silver-palladium termination (AgPd) CN...K2 \triangleq Single chip with silver-platinum termination (AgPt)</p> | | | | | | | | |
| <p>EAI case sizes: 0603 0805 1206 1210 1812 2220</p> | | | | | | | | |
| <p>Varistor voltage tolerance: K \triangleq $\pm 10\%$, standard S \triangleq Special tolerance</p> | | | | | | | | |
| <p>Maximum RMS operating voltage (V_{RMS}): 14 \triangleq 14 V $V_{RMS} < 25$ V are suitable for 12 V DC supply systems $V_{RMS} \geq 25$ V are suitable for 24 V DC supply systems</p> | | | | | | | | |
| <p>Special tolerance for the varistor voltage: – \triangleq Standard tolerance B \triangleq Special tolerance</p> | | | | | | | | |
| <p>Automotive series</p> | | | | | | | | |
| <p>Special features: – \triangleq Standard energy handling capability E2 \triangleq Increased energy handling capability HT \triangleq High temperature version LC \triangleq Low capacitance version CC \triangleq Controlled capacitance version</p> | | | | | | | | |
| <p>Taping mode: G \triangleq Taped, 180-mm reel, 7" G2 \triangleq Taped, 330-mm reel, 13"</p> | | | | | | | | |
| <p>AgPt termination</p> | | | | | | | | |

Multilayer varistors (MLVs)

Automotive series

SMD

Features

- ESD protection up to 25 kV, ISO 10605 level IV, acc. to IEC 61000-4-2 level 4 (8 kV contact, 15 kV air)
- High energy absorption capability
- Low leakage current
- High temperature versions
- Stable protection level
- Bidirectional clamping
- No temperature derating up to 125 °C
- RoHS-compatible
- Nickel barrier and AgPt series suitable for lead-free soldering
- Nickel barrier and AgPt series qualified based on AEC-Q200 rev. C
- PSpice simulation models available

Applications

- Transient overvoltage protection in automotive applications: engine management, airbag, control units, electrohydraulic brake, ABS/ESP, sunroof
- Load dump protection
- Jump start protection

Design


- Multilayer technology
- Lack of plastic or epoxy encapsulation for flammability rating better than UL 94 V-0
- Termination (see “Soldering directions”):
 - CT types with nickel barrier terminations (AgNiSn), recommended for lead-free reflow and wave soldering, and compatible with tin/lead solder.
 - CN types with silver-palladium terminations (AgPd) only suitable for reflow and wave soldering with solder on tin/lead basis and for adhesive glueing.
 - CN...K2 types with silver-platinum terminations (AgPt) suitable for reflow lead-free soldering.

V/I characteristics and derating curves

V/I and derating curves are attached to the data sheet. The curves are sorted by V_{RMS} and then by case size, which is included in the type designation.

Single chip

Internal circuit



MLV0006-H

Available case sizes:

| EIA | Metric |
|------|--------|
| 0603 | 1608 |
| 0805 | 2012 |
| 1206 | 3216 |
| 1210 | 3225 |
| 1812 | 4532 |
| 2220 | 5750 |

Multilayer varistors (MLVs)
Automotive series
SMD
General technical data

| | | | | |
|-------------------------------|---------------------------|-----------------|-------------|----|
| Maximum RMS operating voltage | | $V_{RMS,max}$ | 14 ... 30 | V |
| Maximum DC operating voltage | | $V_{DC,max}$ | 16 ... 38 | V |
| Maximum surge current | (8/20 μ s) | $I_{surge,max}$ | 5 ... 1200 | A |
| Maximum load dump energy | (10 pulses) | W_{LD} | 1 ... 25 | J |
| Maximum jump start voltage | (5 min) | V_{jump} | 24.5 ... 45 | V |
| Maximum clamping voltage | (8/20 μ s) | $V_{clamp,max}$ | 40 ... 120 | V |
| Operating temperature | AUTO types | T_{op} | -55/+125 | °C |
| Operating temperature | HT types | T_{op} | -55/+150 | °C |
| Operating temperature | special capacitance types | T_{op} | -55/+125 | °C |
| Operating temperature | standard types | T_{op} | -55/+125 | °C |
| Storage temperature | all types | LCT/UCT | -55/+150 | °C |


Multilayer varistors (MLVs)

Automotive series

SMD


Temperature derating

Climatic category: $-55/+125\text{ }^{\circ}\text{C}$



For automotive, special capacitance and standard range.

Climatic category: $-55/+150\text{ }^{\circ}\text{C}$



For high temperature (HT) range.

Multilayer varistors (MLVs)
Automotive series
SMD
Electrical specifications and ordering codes
Maximum ratings ($T_{op,max} = 125\text{ }^{\circ}\text{C}$, for HT types $T_{op,max} = 150\text{ }^{\circ}\text{C}$)

| Type | Ordering code | $V_{RMS,max}$ | $V_{DC,max}$ | $I_{surge,max}$ (8/20 μs) | W_{max} (2 ms) | W_{LD} (10 pulses) | $P_{diss,max}$ |
|--|-----------------|---------------|--------------|---|---------------------|----------------------------|----------------|
| | | V | V | A | mJ | J | mW |
| AUTO range, CN types | | | | | | | |
| CN1812S14BAUTOE2G2 | B72580V3140S272 | 14 | 16 | 800 | 2400 | 12 | 15 |
| CN1812S14BAUTOE2G2K2 | B72582V3140S272 | 14 | 16 | 800 | 2400 | 12 | 15 |
| CN1812S14BAUTOG | B72580V1140S262 | 14 | 16 | 800 | 2400 | 6 | 15 |
| CN1812S14BAUTOGK2 | B72582V1140S262 | 14 | 16 | 800 | 2400 | 6 | 15 |
| CN2220S14BAUTOE2G2 | B72540V3140S272 | 14 | 16 | 1200 | 5800 | 25 | 30 |
| CN2220S14BAUTOE2G2K2 | B72542V3140S272 | 14 | 16 | 1200 | 5800 | 25 | 30 |
| CN2220S14BAUTOG | B72540V1140S262 | 14 | 16 | 1200 | 5800 | 12 | 30 |
| CN2220S14BAUTOGK2 | B72542V1140S262 | 14 | 16 | 1200 | 5800 | 12 | 30 |
| CN2220S14EAUTOE2G2K2 | B72542V3140S572 | 14 | 16 | 1200 | 5800 | 25 | 30 |
| CN2220K30AUTOE2G2 | B72540V3300K072 | 30 | 34 | 1200 | 12000 | 25 | 30 |
| CN2220K30AUTOE2G2K2 | B72542V3300K072 | 30 | 34 | 1200 | 12000 | 25 | 30 |
| CN2220K30AUTOG | B72540V1300K062 | 30 | 34 | 1200 | 12000 | 12 | 30 |
| CN2220K30AUTOGK2 | B72542V1300K062 | 30 | 34 | 1200 | 12000 | 12 | 30 |
| AUTO range, CT types | | | | | | | |
| CT0603S14BAUTOG | B72500T1140S260 | 14 | 16 | 30 | 200 | - | 3 |
| CT0805S14BAUTOG | B72510T1140S262 | 14 | 16 | 120 | 300 | 1 | 8 |
| CT1206S14BAUTOG | B72520T1140S262 | 14 | 16 | 200 | 600 | 1.5 | 8 |
| CT1210S14BAUTOG | B72530T1140S262 | 14 | 16 | 400 | 1600 | 3 | 10 |
| CT1210K17AUTOG | B72530T1170K062 | 17 | 22 | 400 | 1700 | 3 | 10 |
| CT1206K20AUTOG | B72520T1200K062 | 20 | 26 | 200 | 700 | 1.5 | 8 |
| CT1210K20AUTOG | B72530T1200K062 | 20 | 26 | 400 | 1900 | 3 | 10 |
| CT0805K25AUTOG | B72510T1250K062 | 25 | 31 | 80 | 300 | 1 | 5 |
| CT1206K25AUTOG | B72520T1250K062 | 25 | 31 | 200 | 1000 | 1.5 | 8 |
| CT1210K25AUTOG | B72530T1250K062 | 25 | 31 | 300 | 1700 | 3 | 10 |
| High temperature (HT) range | | | | | | | |
| CN0603S14BHTG2 | B72500H0140S270 | 14 | 18 | 30 | 200 | - | 3 |
| CN0603S17BHTG | B72500H0170S260 | 17 | 22 | 30 | 75 | - | 3 |
| CN1210K17AUTOHTG | B72530H1170K062 | 17 | 22 | 400 | 1700 | 3 | 10 |
| CN0603K25HTG5 | B72500H0250K062 | 25 | 31 | 30 | 300 | - | 3 |
| Special capacitance range, CT types | | | | | | | |
| CT0603S14AHSG | B72500T8140S160 | 14 | 16 | 5 | 30 | - | 3 |
| CT0603K17CCG | B72500T5170K060 | 17 | 22 | 30 | 200 | - | 3 |
| CT0603K17LCG | B72500T2170K060 | 17 | 22 | 10 | 100 | - | 1 |
| CT0603S17ALCG | B72500T2170S160 | 17 | 22 | 30 | 75 | - | 3 |
| CT0603S17BCCG | B72500T5170S260 | 17 | 22 | 30 | 75 | - | 3 |

Multilayer varistors (MLVs)
Automotive series
SMD
Characteristics (T_A = 25 °C)

| Type | V _V (1 mA) | ΔV _V | V _{jump} (5 min) | V _{clamp,max} | I _{clamp} (8/20 μs) | C _{typ} (1 kHz) | C _{min} (1 kHz) | C _{max} (1 kHz) |
|--|--------------------------|-----------------|------------------------------|------------------------|------------------------------------|-----------------------------|-----------------------------|-----------------------------|
| | V | % | V | V | A | pF | pF | pF |
| AUTO range, CN types | | | | | | | | |
| CN1812S14BAUTOE2G2 | 22 | +23/-0 | 24.5 | 40 | 5 | 7000 | - | - |
| CN1812S14BAUTOE2G2K2 | 22 | +23/-0 | 24.5 | 40 | 5 | 7000 | - | - |
| CN1812S14BAUTOG | 22 | +23/-0 | 24.5 | 40 | 5 | 5600 | - | - |
| CN1812S14BAUTOGK2 | 22 | +23/-0 | 24.5 | 40 | 5 | 5600 | - | - |
| CN2220S14BAUTOE2G2 | 22 | +23/-0 | 24.5 | 40 | 10 | 15000 | - | - |
| CN2220S14BAUTOE2G2K2 | 22 | +23/-0 | 24.5 | 40 | 10 | 15000 | - | - |
| CN2220S14BAUTOG | 22 | +23/-0 | 24.5 | 40 | 10 | 9500 | - | - |
| CN2220S14BAUTOGK2 | 22 | +23/-0 | 24.5 | 40 | 10 | 9500 | - | - |
| CN2220S14EAUTOE2G2K2 | 25 | ±10 | 24.5 | 40 | 10 | 15000 | - | - |
| CN2220K30AUTOE2G2 | 47 | ±10 | 45 | 77 | 10 | 10000 | - | - |
| CN2220K30AUTOE2G2K2 | 47 | ±10 | 45 | 77 | 10 | 10000 | - | - |
| CN2220K30AUTOG | 47 | ±10 | 45 | 77 | 10 | 4000 | - | - |
| CN2220K30AUTOGK2 | 47 | ±10 | 45 | 77 | 10 | 4000 | - | - |
| AUTO range, CT types | | | | | | | | |
| CT0603S14BAUTOG | 22 | +23/-0 | 24.5 | 42 | 1 | 120 | - | - |
| CT0805S14BAUTOG | 22 | +23/-0 | 24.5 | 42 | 1 | 400 | - | - |
| CT1206S14BAUTOG | 22 | +23/-0 | 24.5 | 40 | 1 | 800 | - | - |
| CT1210S14BAUTOG | 22 | +23/-0 | 24.5 | 40 | 2.5 | 1700 | - | - |
| CT1210K17AUTOG | 27 | ±10 | 26.5 | 44 | 2.5 | 1800 | - | - |
| CT1206K20AUTOG | 33 | ±10 | 27 | 54 | 1 | 600 | - | - |
| CT1210K20AUTOG | 33 | ±10 | 27 | 54 | 2.5 | 1500 | - | - |
| CT0805K25AUTOG | 39 | ±10 | 29 | 67 | 1 | 250 | - | - |
| CT1206K25AUTOG | 39 | ±10 | 29 | 65 | 1 | 550 | - | - |
| CT1210K25AUTOG | 39 | ±10 | 29 | 65 | 2.5 | 1200 | - | - |
| High temperature (HT) range | | | | | | | | |
| CN0603S14BHTG2 | 22 | +23/-0 | - | 42 | 1 | 120 | - | - |
| CN0603S17BHTG | 25 | +60/-0 | - | 50 | 1 | - | 32 ¹⁾ | 74 ¹⁾ |
| CN1210K17AUTOHTG | 27 | ±10 | 26.5 | 44 | 2.5 | 1800 | - | - |
| CN0603K25HTG5 | 39 | ±10 | - | 67 | 1 | 90 ¹⁾ | - | - |
| Special capacitance range, CT types | | | | | | | | |
| CT0603S14AHSG | 23 | +44/-0 | - | 66 | 1 | 15 ¹⁾ | - | 30 ¹⁾ |
| CT0603K17CCG | 27 | ±10 | - | 46 | 1 | - | 128 | 192 |
| CT0603K17LCG | 27 | ±10 | - | 50 | 1 | - | - | 50 ¹⁾ |
| CT0603S17ALCG | 25 | +60/-0 | - | 50 | 1 | - | - | 75 ¹⁾ |
| CT0603S17BCCG | 25 | +60/-0 | - | 50 | 1 | - | 31.8 ¹⁾ | 74.2 ¹⁾ |

1) Measured @ 1 MHz, 1 V

Multilayer varistors (MLVs)
Automotive series
SMD
Electrical specifications and ordering codes
Maximum ratings ($T_{op,max} = 125\text{ }^{\circ}\text{C}$, for HT types $T_{op,max} = 150\text{ }^{\circ}\text{C}$)

| Type | Ordering code | $V_{RMS,max}$ | $V_{DC,max}$ | $I_{surge,max}$ (8/20 μs) | W_{max} (2 ms) | W_{LD} (10 pulses) | $P_{diss,max}$ |
|--|-----------------|---------------|--------------|---|---------------------|----------------------------|----------------|
| | | V | V | A | mJ | J | mW |
| Special capacitance range, CT types | | | | | | | |
| CT0805K17AUTOLCG | B72510S2170K062 | 17 | 22 | 30 | 100 | - | 4 |
| CT0805K17LCG | B72510T2170K062 | 17 | 22 | 30 | 100 | - | 4 |
| CT0603S20ACCG | B72500T5200S160 | 20 | 26 | 30 | 300 | - | 3 |
| CT0805S20ACC2G2 | B72510T9200S172 | 20 | 26 | 80 | 400 | - | 5 |
| CT0603L25HSG | B72500T8250L060 | 25 | 32 | 5 | - | - | - |
| CT0805K25CCG | B72510T5250K062 | 25 | 31 | 80 | 300 | - | 5 |
| Standard range, CN types | | | | | | | |
| CN1812K14G | B72580V0140K062 | 14 | 18 | 800 | 2300 | - | 15 |
| CN1812K14GK2 | B72582V0140K062 | 14 | 18 | 800 | 2300 | - | 15 |
| CN2220K14G | B72540V0140K062 | 14 | 18 | 1200 | 5800 | - | 20 |
| CN1812K17G | B72580V0170K062 | 17 | 22 | 800 | 2700 | - | 15 |
| CN2220K17G | B72540V0170K062 | 17 | 22 | 1200 | 7200 | - | 20 |
| CN1812K20G | B72580V0200K062 | 20 | 26 | 800 | 3000 | - | 15 |
| CN2220K20G | B72540V0200K062 | 20 | 26 | 1200 | 7800 | - | 20 |
| CN2220K20GK2 | B72542V0200K062 | 20 | 26 | 1200 | 7800 | - | 20 |
| CN1812K25G | B72580V0250K062 | 25 | 31 | 800 | 3700 | - | 15 |
| CN2220K25G | B72540V0250K062 | 25 | 31 | 1200 | 9600 | - | 20 |
| CN2220K25GK2 | B72542V0250K062 | 25 | 31 | 1200 | 9600 | - | 20 |
| CN1812K30G | B72580V0300K062 | 30 | 38 | 800 | 4200 | - | 15 |
| CN1812K30GK2 | B72582V0300K062 | 30 | 38 | 800 | 4200 | - | 15 |
| CN2220K30G | B72540V0300K062 | 30 | 38 | 1200 | 12000 | - | 20 |
| CN2220K30GK2 | B72542V0300K062 | 30 | 38 | 1200 | 12000 | - | 20 |
| Standard range, CT types | | | | | | | |
| CT0603K14G | B72500T0140K060 | 14 | 18 | 30 | 200 | - | 3 |
| CT0603S14BG | B72500T0140S160 | 14 | 18 | 30 | 200 | - | 3 |
| CT0805K14G | B72510T0140K062 | 14 | 18 | 120 | 300 | - | 5 |
| CT1206K14G | B72520T0140K062 | 14 | 18 | 200 | 500 | - | 8 |
| CT1210K14G | B72530T0140K062 | 14 | 18 | 400 | 1500 | - | 10 |
| CT0603K17G | B72500T0170K060 | 17 | 22 | 30 | 200 | - | 3 |
| CT0805K17G | B72510T0170K062 | 17 | 22 | 120 | 300 | - | 5 |
| CT1206K17G | B72520T0170K062 | 17 | 22 | 200 | 600 | - | 8 |
| CT1210K17G | B72530T0170K062 | 17 | 22 | 400 | 1700 | - | 10 |
| CT0603K20G | B72500T0200K060 | 20 | 26 | 30 | 200 | - | 3 |
| CT0805K20G | B72510T0200K062 | 20 | 26 | 80 | 300 | - | 5 |

Multilayer varistors (MLVs)
Automotive series
SMD
Characteristics (T_A = 25 °C)

| Type | V _V (1 mA) | ΔV _V | V _{jump} (5 min) | V _{clamp,max} | I _{clamp} (8/20 μs) | C _{typ} (1 kHz) | C _{min} (1 kHz) | C _{max} (1 kHz) |
|--|--------------------------|-----------------|------------------------------|------------------------|------------------------------------|-----------------------------|-----------------------------|-----------------------------|
| | V | % | V | V | A | pF | pF | pF |
| Special capacitance range, CT types | | | | | | | | |
| CT0805K17AUTOLCG | 25 | +32/-0 | - | 50 | 1 | - | - | 100 ¹⁾ |
| CT0805K17LCG | 25 | +32/-0 | - | 50 | 1 | - | - | 100 ¹⁾ |
| CT0603S20ACCG | 30 | +40/-0 | - | 67 | 1 | - | 64 ¹⁾ | 96 ¹⁾ |
| CT0805S20ACCG2G2 | 29.7 | +34/-0 | - | 64 | 1 | - | 170 | 270 |
| CT0603L25HSG | 51.9 | +35/-0 | - | 120 | 1 | 10 ¹⁾ | - | 15 ¹⁾ |
| CT0805K25CCG | 39 | ±10 | - | 67 | 1 | - | 162.5 | 337.5 |
| Standard range, CN types | | | | | | | | |
| CN1812K14G | 22 | ±10 | - | 38 | 5 | 4500 | - | - |
| CN1812K14GK2 | 22 | ±10 | - | 38 | 5 | 4500 | - | - |
| CN2220K14G | 22 | ±10 | - | 38 | 10 | 10000 | - | - |
| CN1812K17G | 27 | ±10 | - | 44 | 5 | 4000 | - | - |
| CN2220K17G | 27 | ±10 | - | 44 | 10 | 9000 | - | - |
| CN1812K20G | 33 | ±10 | - | 54 | 5 | 3000 | - | - |
| CN2220K20G | 33 | ±10 | - | 54 | 10 | 7000 | - | - |
| CN2220K20GK2 | 33 | ±10 | - | 54 | 10 | 7000 | - | - |
| CN1812K25G | 39 | ±10 | - | 65 | 5 | 2500 | - | - |
| CN2220K25G | 39 | ±10 | - | 65 | 10 | 5000 | - | - |
| CN2220K25GK2 | 39 | ±10 | - | 65 | 10 | 5000 | - | - |
| CN1812K30G | 47 | ±10 | - | 77 | 5 | 2000 | - | - |
| CN1812K30GK2 | 47 | ±10 | - | 77 | 5 | 2000 | - | - |
| CN2220K30G | 47 | ±10 | - | 77 | 10 | 4000 | - | - |
| CN2220K30GK2 | 47 | ±10 | - | 77 | 10 | 4000 | - | - |
| Standard range, CT types | | | | | | | | |
| CT0603K14G | 22 | ±10 | - | 40 | 1 | 100 | - | - |
| CT0603S14BG | 22 | +23/-0 | - | 42 | 1 | 120 | - | - |
| CT0805K14G | 22 | ±10 | - | 40 | 1 | 350 | - | - |
| CT1206K14G | 22 | ±10 | - | 38 | 1 | 700 | - | - |
| CT1210K14G | 22 | ±10 | - | 38 | 2.5 | 2000 | - | - |
| CT0603K17G | 27 | ±10 | - | 46 | 1 | 100 | - | - |
| CT0805K17G | 27 | ±10 | - | 46 | 1 | 400 | - | - |
| CT1206K17G | 27 | ±10 | - | 44 | 1 | 650 | - | - |
| CT1210K17G | 27 | ±10 | - | 44 | 2.5 | 1800 | - | - |
| CT0603K20G | 33 | ±10 | - | 56 | 1 | 90 | - | - |
| CT0805K20G | 33 | ±10 | - | 56 | 1 | 300 | - | - |

Multilayer varistors (MLVs)
Automotive series
SMD
Electrical specifications and ordering codes
Maximum ratings ($T_{op,max} = 125\text{ °C}$, for HT types $T_{op,max} = 150\text{ °C}$)

| Type | Ordering code | $V_{RMS,max}$ | $V_{DC,max}$ | $I_{surge,max}$ (8/20 μ s) | W_{max} (2 ms) | W_{LD} (10 pulses) | $P_{diss,max}$ |
|---------------------------------|-----------------|---------------|--------------|--------------------------------------|---------------------|----------------------------|----------------|
| | | V | V | A | mJ | J | mW |
| Standard range, CT types | | | | | | | |
| CT1206K20G | B72520T0200K062 | 20 | 26 | 200 | 700 | - | 8 |
| CT1210K20G | B72530T0200K062 | 20 | 26 | 400 | 1900 | - | 10 |
| CT0603K25G | B72500T0250K060 | 25 | 31 | 30 | 300 | - | 3 |
| CT0805K25G | B72510T0250K062 | 25 | 31 | 80 | 300 | - | 5 |
| CT1206K25G | B72520T0250K062 | 25 | 31 | 200 | 1000 | - | 8 |
| CT1210K25G | B72530T0250K062 | 25 | 31 | 300 | 1700 | - | 10 |
| CT0805K30G | B72510T0300K062 | 30 | 38 | 80 | 300 | - | 5 |
| CT1206K30G | B72520T0300K062 | 30 | 38 | 200 | 1100 | - | 8 |
| CT1210K30G | B72530T0300K062 | 30 | 38 | 300 | 2000 | - | 10 |

Characteristics ($T_A = 25\text{ °C}$)


| Type | V_V (1 mA) | ΔV_V | V_{jump} (5 min) | $V_{clamp,max}$ | I_{clamp} (8/20 μ s) | C_{typ} (1 kHz) | C_{min} (1 kHz) | C_{max} (1 kHz) |
|---------------------------------|-----------------|--------------|-----------------------|-----------------|----------------------------------|----------------------|----------------------|----------------------|
| | V | % | V | V | A | pF | pF | pF |
| Standard range, CT types | | | | | | | | |
| CT1206K20G | 33 | ± 10 | - | 54 | 1 | 600 | - | - |
| CT1210K20G | 33 | ± 10 | - | 54 | 2.5 | 1500 | - | - |
| CT0603K25G | 39 | ± 10 | - | 67 | 1 | 90 | - | - |
| CT0805K25G | 39 | ± 10 | - | 67 | 1 | 250 | - | - |
| CT1206K25G | 39 | ± 10 | - | 65 | 1 | 550 | - | - |
| CT1210K25G | 39 | ± 10 | - | 65 | 2.5 | 1200 | - | - |
| CT0805K30G | 47 | ± 10 | - | 77 | 1 | 200 | - | - |
| CT1206K30G | 47 | ± 10 | - | 77 | 1 | 500 | - | - |
| CT1210K30G | 47 | ± 10 | - | 77 | 2.5 | 1000 | - | - |

Multilayer varistors (MLVs)

Automotive series

SMD


Dimensional drawing



Dimensions in mm

| Case size EIA / mm | l | w | h | k |
|-----------------------|-----------|------------|----------|---------------|
| 0603 / 1608 | 1.6 ±0.15 | 0.80 ±0.10 | 0.9 max. | 0.10 ... 0.40 |
| 0805 / 2012 | 2.0 ±0.20 | 1.25 ±0.15 | 1.4 max. | 0.13 ... 0.75 |
| 1206 / 3216 | 3.2 ±0.30 | 1.60 ±0.20 | 1.7 max. | 0.25 ... 0.75 |
| 1210 / 3225 | 3.2 ±0.30 | 2.50 ±0.25 | 1.7 max. | 0.25 ... 0.75 |
| 1812 / 4532 | 4.5 ±0.40 | 3.20 ±0.30 | 2.5 max. | 0.25 ... 1.00 |
| 2220 / 5750 | 5.7 ±0.40 | 5.00 ±0.40 | 2.5 max. | 0.25 ... 1.00 |

Recommended solder pad layout



Dimensions in mm

| Case size EIA / mm | A | B | C |
|-----------------------|------|------|------|
| 0603 / 1608 | 1.00 | 1.00 | 1.00 |
| 0805 / 2012 | 1.40 | 1.20 | 1.00 |
| 1206 / 3216 | 1.80 | 1.20 | 2.10 |
| 1210 / 3225 | 2.80 | 1.20 | 2.10 |
| 1812 / 4532 | 3.60 | 1.50 | 3.00 |
| 2220 / 5750 | 5.50 | 1.50 | 4.20 |

Multilayer varistors (MLVs)
Automotive series
SMD
Delivery mode

| EIA case size | Taping | Reel size mm | Packing unit pcs. | Type | Ordering code |
|---------------|-----------|-----------------|----------------------|----------------------|-----------------|
| 0603 | Blister | 180 | 4000 | CN0603K25HTG5 | B72500H0250K062 |
| 0603 | Cardboard | 330 | 16000 | CN0603S14BHTG2 | B72500H0140S270 |
| 0603 | Cardboard | 180 | 4000 | CN0603S17BHTG | B72500H0170S260 |
| 1210 | Blister | 180 | 3000 | CN1210K17AUTOHTG | B72530H1170K062 |
| 1812 | Blister | 180 | 1500 | CN1812K14G | B72580V0140K062 |
| 1812 | Blister | 180 | 1500 | CN1812K14GK2 | B72582V0140K062 |
| 1812 | Blister | 180 | 1500 | CN1812K17G | B72580V0170K062 |
| 1812 | Blister | 180 | 1500 | CN1812K20G | B72580V0200K062 |
| 1812 | Blister | 180 | 1000 | CN1812K25G | B72580V0250K062 |
| 1812 | Blister | 180 | 1000 | CN1812K30G | B72580V0300K062 |
| 1812 | Blister | 180 | 1000 | CN1812K30GK2 | B72582V0300K062 |
| 1812 | Blister | 330 | 3000 | CN1812S14BAUTOE2G2 | B72580V3140S272 |
| 1812 | Blister | 330 | 3000 | CN1812S14BAUTOE2G2K2 | B72582V3140S272 |
| 1812 | Blister | 180 | 1500 | CN1812S14BAUTOG | B72580V1140S262 |
| 1812 | Blister | 180 | 1500 | CN1812S14BAUTOGK2 | B72582V1140S262 |
| 2220 | Blister | 180 | 1500 | CN2220K14G | B72540V0140K062 |
| 2220 | Blister | 180 | 1500 | CN2220K17G | B72540V0170K062 |
| 2220 | Blister | 180 | 1500 | CN2220K20G | B72540V0200K062 |
| 2220 | Blister | 180 | 1500 | CN2220K20GK2 | B72542V0200K062 |
| 2220 | Blister | 180 | 1000 | CN2220K25G | B72540V0250K062 |
| 2220 | Blister | 180 | 1000 | CN2220K25GK2 | B72542V0250K062 |
| 2220 | Blister | 330 | 3000 | CN2220K30AUTOE2G2 | B72540V3300K072 |
| 2220 | Blister | 330 | 3000 | CN2220K30AUTOE2G2K2 | B72542V3300K072 |
| 2220 | Blister | 180 | 1000 | CN2220K30AUTOG | B72540V1300K062 |
| 2220 | Blister | 180 | 1000 | CN2220K30AUTOGK2 | B72542V1300K062 |
| 2220 | Blister | 180 | 1000 | CN2220K30G | B72540V0300K062 |
| 2220 | Blister | 180 | 1000 | CN2220K30GK2 | B72542V0300K062 |
| 2220 | Blister | 330 | 3000 | CN2220S14BAUTOE2G2 | B72540V3140S272 |
| 2220 | Blister | 330 | 3000 | CN2220S14BAUTOE2G2K2 | B72542V3140S272 |
| 2220 | Blister | 180 | 1500 | CN2220S14BAUTOG | B72540V1140S262 |
| 2220 | Blister | 180 | 1500 | CN2220S14BAUTOGK2 | B72542V1140S262 |
| 2220 | Blister | 330 | 3000 | CN2220S14EAUTOE2G2K2 | B72542V3140S572 |
| 0603 | Cardboard | 180 | 4000 | CT0603K14G | B72500T0140K060 |
| 0603 | Cardboard | 180 | 4000 | CT0603K17CCG | B72500T5170K060 |
| 0603 | Cardboard | 180 | 4000 | CT0603K17G | B72500T0170K060 |
| 0603 | Cardboard | 180 | 4000 | CT0603K17LCG | B72500T2170K060 |
| 0603 | Cardboard | 180 | 4000 | CT0603K20G | B72500T0200K060 |
| 0603 | Cardboard | 180 | 4000 | CT0603K25G | B72500T0250K060 |
| 0603 | Cardboard | 180 | 4000 | CT0603L25HSG | B72500T8250L060 |
| 0603 | Cardboard | 180 | 4000 | CT0603S14AHSG | B72500T8140S160 |
| 0603 | Cardboard | 180 | 4000 | CT0603S14BAUTOG | B72500T1140S260 |
| 0603 | Cardboard | 180 | 4000 | CT0603S14BG | B72500T0140S160 |

Multilayer varistors (MLVs)
Automotive series
SMD


| EIA case size | Taping | Reel size mm | Packing unit pcs. | Type | Ordering code |
|---------------|-----------|-----------------|----------------------|------------------|-----------------|
| 0603 | Cardboard | 180 | 4000 | CT0603S17ALCG | B72500T2170S160 |
| 0603 | Cardboard | 180 | 4000 | CT0603S17BCCG | B72500T5170S260 |
| 0603 | Cardboard | 180 | 4000 | CT0603S20ACCG | B72500T5200S160 |
| 0805 | Blister | 180 | 3000 | CT0805K14G | B72510T0140K062 |
| 0805 | Blister | 180 | 3000 | CT0805K17AUTOLCG | B72510S2170K062 |
| 0805 | Blister | 180 | 3000 | CT0805K17G | B72510T0170K062 |
| 0805 | Blister | 180 | 3000 | CT0805K17LCG | B72510T2170K062 |
| 0805 | Blister | 180 | 3000 | CT0805K20G | B72510T0200K062 |
| 0805 | Blister | 180 | 3000 | CT0805K25AUTOG | B72510T1250K062 |
| 0805 | Blister | 180 | 3000 | CT0805K25CCG | B72510T5250K062 |
| 0805 | Blister | 180 | 3000 | CT0805K25G | B72510T0250K062 |
| 0805 | Blister | 180 | 3000 | CT0805K30G | B72510T0300K062 |
| 0805 | Blister | 180 | 3000 | CT0805S14BAUTOG | B72510T1140S262 |
| 0805 | Blister | 330 | 12000 | CT0805S20ACC2G2 | B72510T9200S172 |
| 1206 | Blister | 180 | 3000 | CT1206K14G | B72520T0140K062 |
| 1206 | Blister | 180 | 3000 | CT1206K17G | B72520T0170K062 |
| 1206 | Blister | 180 | 3000 | CT1206K20AUTOG | B72520T1200K062 |
| 1206 | Blister | 180 | 3000 | CT1206K20G | B72520T0200K062 |
| 1206 | Blister | 180 | 2000 | CT1206K25AUTOG | B72520T1250K062 |
| 1206 | Blister | 180 | 2000 | CT1206K25G | B72520T0250K062 |
| 1206 | Blister | 180 | 2000 | CT1206K30G | B72520T0300K062 |
| 1206 | Blister | 180 | 3000 | CT1206S14BAUTOG | B72520T1140S262 |
| 1210 | Blister | 180 | 3000 | CT1210K14G | B72530T0140K062 |
| 1210 | Blister | 180 | 3000 | CT1210K17AUTOG | B72530T1170K062 |
| 1210 | Blister | 180 | 2000 | CT1210K17G | B72530T0170K062 |
| 1210 | Blister | 180 | 3000 | CT1210K20AUTOG | B72530T1200K062 |
| 1210 | Blister | 180 | 3000 | CT1210K20G | B72530T0200K062 |
| 1210 | Blister | 180 | 2000 | CT1210K25AUTOG | B72530T1250K062 |
| 1210 | Blister | 180 | 2000 | CT1210K25G | B72530T0250K062 |
| 1210 | Blister | 180 | 2000 | CT1210K30G | B72530T0300K062 |
| 1210 | Blister | 180 | 3000 | CT1210S14BAUTOG | B72530T1140S262 |

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for automotive range, CN types



CN1812S14BAUTOE2G2(K2)




CN1812S14BAUTOG(K2)

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for automotive range, CN types



CN2220S14BAUTOE2G2(K2)




CN2220S14BAUTOG(K2)

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for automotive range, CN types



CN2220K30AUTOE2G2(K2)




CN2220K30AUTOG(K2)

Multilayer varistors (MLVs)

Automotive series

SMD

V/I characteristics for automotive range, CN types




CN2220S14EAUTOE2G2K2

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for automotive range, CT types



CT0603S14BAUTOG




CT0805S14BAUTOG

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for automotive range, CT types



CT0805K25AUTOG




CT1206S14BAUTOG

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for automotive range, CT types



CT1206K20AUTOG




CT1206K25AUTOG

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for automotive range, CT types



CT1210S14BAUTOG




CT1210K17AUTOG

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for automotive range, CT types



CT1210K20AUTOG




CT1210K25AUTOG

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for high temperature (HT) range



CN0603S14BHTG2




CN0603S17BHTG

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for high temperature (HT) range



CN0603K25HTG




CN1210K17AUTOHTG

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for special capacitance range



CT0603S14AHSG




CT0603K17CCG

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for special capacitance range



CT0603K17LCG




CT0603S17ALCG
CT0603S17BCCG

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for special capacitance range



CT0603S20ACCG




CT0603L25HSG

Multilayer varistors (MLVs)

Automotive series


SMD

V/I characteristics for special capacitance range



CT0805K17LCG

CT0805K17AUTLCG




CT0805S20ACC2G2

Multilayer varistors (MLVs)

Automotive series

SMD

V/I characteristics for special capacitance range




CT0805K25CCG

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for standard range, CN types



CN1812K14G(K2)




CN1812K17G

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for standard range, CN types



CN1812K20G




CN1812K25G

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for standard range, CN types



CN1812K30G(K2)




CN2220K14G

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for standard range, CN types



CN2220K17G




CN2220K20G(K2)

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for standard range, CN types



CN2220K25G(K2)




CN2220K30G(K2)

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for standard range, CT types



CT0603K14G




CT0603S14BG

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for standard range, CT types



CT0603K17G




CT0603K20G

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for standard range, CT types



CT0603K25G




CT0805K14G

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for standard range, CT types



CT0805K17G




CT0805K20G

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for standard range, CT types



CT0805K25G




CT0805K30G

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for standard range, CT types



CT1206K14G




CT1206K17G

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for standard range, CT types



CT1206K20G




CT1206K25G

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for standard range, CT types



CT1206K30G




CT1210K14G

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for standard range, CT types



CT1210K17G




CT1210K20G

Multilayer varistors (MLVs)


Automotive series

SMD

V/I characteristics for standard range, CT types



CT1210K25G



CT1210K30G

Multilayer varistors (MLVs)


Automotive series

SMD


Derating curves

Maximum surge current $I_{\text{surge,max}} = f(t_r, \text{pulse train})$

For explanation of the derating curves refer to "General technical information", chapter 2.7.2



CN0603 ... HTG (G2, G5), CT0603K14 ... K25G, CT0603S14B(AUTO)G, CT0603K17CCG, CT0603S17ALCG, CT0603S17BCCG, CT0603S20ACCG, CT0805K17(AUTO)LCG



CT0603K17LCG

Multilayer varistors (MLVs)


Automotive series

SMD


Derating curves

Maximum surge current $I_{\text{surge,max}} = f(t_r, \text{pulse train})$

For explanation of the derating curves refer to "General technical information", chapter 2.7.2



CT0805K20 ... K30G, CT0805S20ACC2G2, CT0805K25AUTOG, CT0805K25CCG



CT0805S14BAUTOG, CT0805K14 ... K17G

Multilayer varistors (MLVs)


Automotive series

SMD


Derating curves

Maximum surge current $I_{\text{surge,max}} = f(t_r, \text{pulse train})$

For explanation of the derating curves refer to "General technical information", chapter 2.7.2



CT1206 ... (AUTO)G



CT1210K25(AUTO)G, CT1210K30G

Multilayer varistors (MLVs)


Automotive series

SMD


Derating curves

Maximum surge current $I_{\text{surge,max}} = f(t_r, \text{pulse train})$

For explanation of the derating curves refer to "General technical information", chapter 2.7.2



CT1210K14 ... K20G, CT1210S14BAUTOG, CT1210K17AUTOG, CN1210K17AUTOHTG, CT1210K20AUTOG, CT1210K25AUTOG



CN1812K14 ... K30G(K2),
CN1812S14BAUTO(E2)G(2)(K2)

Multilayer varistors (MLVs)


Automotive series

SMD


Derating curves

Maximum surge current $I_{\text{surge,max}} = f(t_r, \text{pulse train})$

For explanation of the derating curves refer to "General technical information", chapter 2.7.2



CN2220K14 ... K30G(K2), CN2220 ... AUTO(E2)G(2)(K2)



CN2220S14EAUTOE2G2K2

Multilayer varistors (MLVs)


Automotive series

SMD

Taping and packing

1 Taping and packing for SMD components

1.1 Blister tape (the taping to IEC 60286-3)



KKE0063-C-E

Dimensions in mm

| | 8-mm tape | | | | | 12-mm tape | | 16-mm tape | | Tolerance |
|----------------|---------------------|---------------|---------------|---------------|---------------|---------------------|---------------|---------------------|-------|---------------------|
| | Case size (inch/mm) | | | | | Case size (inch/mm) | | Case size (inch/mm) | | |
| | | | 0508/ 1220 | 0612/ 1632 | 1012/ 2532 | | | | | |
| | 0603/ 1608 | 0506/ 1216 | 0805/ 2012 | 1206/ 3216 | 1210/ 3225 | 1812/ 4532 | 2220/ 5750 | 3225 | 4032 | |
| A ₀ | 0.9 ±0.10 | 1.50 | 1.60 | 1.90 | 2.80 | 3.50 | 5.10 | 7.00 | 8.60 | ±0.20 |
| B ₀ | 1.75 ±0.10 | 1.80 | 2.40 | 3.50 | 3.50 | 4.80 | 6.00 | 8.70 | 10.60 | ±0.20 |
| K ₀ | 1.0 | 0.80 | 1.80 | | | 2.60 | | 5.00 | | max. |
| T | 0.30 | | | | | 0.30 | | 0.30 | | max. |
| T ₂ | 1.3 | 1.20 | 2.50 | | | 3.50 | | 5.50 | | max. |
| D ₀ | 1.50 | | | | | 1.50 | | 1.50 | | +0.10/-0 |
| D ₁ | 1.00 | | | | | 1.50 | | 1.50 | | min. |
| P ₀ | 4.00 | | | | | 4.00 | | 4.00 | | ±0.10 ¹⁾ |
| P ₂ | 2.00 | | | | | 2.00 | | 2.00 | | ±0.05 |
| P ₁ | 4.00 | | | | | 8.00 | | 12.00 | | ±0.10 |
| W | 8.00 | | | | | 12.00 | | 16.00 | | ±0.30 |
| E | 1.75 | | | | | 1.75 | | 1.75 | | ±0.10 |
| F | 3.50 | | | | | 5.50 | | 7.50 | | ±0.05 |
| G | 0.75 | | | | | 0.75 | | 0.75 | | min. |

1) ≤±0.2 mm over 10 sprocket holes.


Multilayer varistors (MLVs)

Automotive series


SMD

Part orientation in tape pocket for blister tape


For discrete chip, case sizes 0603, 0805, 1206, 1210, 1812 and 2220




For array, case sizes 0612



For arrays 0506 and 1012



For filter array, case size 0508



Additional taping information


| | |
|---------------------------|---|
| Reel material | Polystyrol (PS) |
| Tape material | Polystyrol (PS) or Polycarbonat (PC) or PVC |
| Tape break force | min. 10 N |
| Top cover tape strength | min. 10 N |
| Top cover tape peel force | 0.2 to 0.6 N for 8-mm tape and 0.2 to 0.8 N for 12-mm tape at a peel speed of 300 mm/min |
| Tape peel angle | Angle between top cover tape and the direction of feed during peel off: 165° to 180° |
| Cavity play | Each part rests in the cavity so that the angle between the part and cavity center line is no more than 20° |

Multilayer varistors (MLVs)

Automotive series

SMD

1.2 Cardboard tape (taping to IEC 60286-3)



Dimensions in mm

| | 8-mm tape | | | | | | Tolerance |
|----------------|---------------------|-----------|-----------|-----------|-----------|---------------------|---------------------|
| | Case size (inch/mm) | | | | | Case size (inch/mm) | |
| | 0201/0603 | 0402/1005 | 0405/1012 | 0603/1608 | 1003/2508 | 0508/1220 | |
| A ₀ | 0.38 ±0.05 | 0.60 | 1.05 | 0.95 | 1.00 | 1.60 | ±0.20 |
| B ₀ | 0.68 ±0.05 | 1.15 | 1.60 | 1.80 | 2.85 | 2.40 | ±0.20 |
| T | 0.35 ±0.02 | 0.60 | 0.75 | 0.95 | 1.00 | 0.95 | max. |
| T ₂ | 0.4 min. | 0.70 | 0.90 | 1.10 | 1.10 | 1.12 | max. |
| D ₀ | 1.50 ±0.1 | 1.50 | | | | 1.50 | +0.10/-0 |
| P ₀ | 4.00 | | | | | | ±0.10 ²⁾ |
| P ₂ | 2.00 | | | | | | ±0.05 |
| P ₁ | 2.00 ±0.05 | 2.00 | 4.00 | 4.00 | 4.00 | 4.00 | ±0.10 |
| W | 8.00 | | | | | | ±0.30 |
| E | 1.75 | | | | | | ±0.10 |
| F | 3.50 | | | | | | ±0.05 |
| G | 1.35 | 0.75 | | | | | min. |

2) ≤0.2 mm over 10 sprocket holes.

Multilayer varistors (MLVs)



Automotive series

SMD

Part orientation in tape pocket for cardboard tape



For discrete chip case sizes 0201, 0402, 0603 and 1003

For array case size 0405



For array case size 0508

For filter array, case size 0405



Additional taping information


| | |
|---------------------------|---|
| Reel material | Polystyrol (PS) |
| Tape material | Cardboard |
| Tape break force | min. 10 N |
| Top cover tape strength | min. 10 N |
| Top cover tape peel force | 0.1 to 0.65 N at a peel speed of 300 mm/min |
| Tape peel angle | Angle between top cover tape and the direction of feed during peel off: 165° to 180° |
| Cavity play | Each part rests in the cavity so that the angle between the part and cavity center line is no more than 20° |

Multilayer varistors (MLVs)

Automotive series

SMD

1.3 Reel packing




Dimensions in mm


| | 8-mm tape | | 12-mm tape | | 16-mm tape |
|----------------|-------------|-------------|--------------|--------------|--------------|
| | 180-mm reel | 330-mm reel | 180-mm reel | 330-mm reel | 330-mm reel |
| A | 180 -3/+0 | 330 -2.0 | 180 -3/+0 | 330 -2.0 | 330 -2.0 |
| W ₁ | 8.4 +1.5/-0 | 8.4 +1.5/-0 | 12.4 +1.5/-0 | 12.4 +1.5/-0 | 16.4 +1.5/-0 |
| W ₂ | 14.4 max. | 14.4 max. | 18.4 max. | 18.4 max. | 22.4 max. |

Leader, trailer

Tape end (Trailer)







Leader part



KKE0289-Q-E

Multilayer varistors (MLVs)
Automotive series
SMD
1.4 Packing units for discrete chip and array chip

| |  |  | |  |  |
|----------------------|---|---|-------------------|---|--|
| Case size inch/mm | Chip thickness th | Cardboard tape W | Blister tape W | ∅ 180-mm reel pcs. | ∅ 330-mm reel pcs. |
| 0201/0603 | 0.33 mm | 8 mm | – | 15000 | – |
| 0402/1005 | 0.6 mm | 8 mm | – | 10000 | – |
| 0405/1012 | 0.7 mm | 8 mm | – | 5000 | – |
| 0506/1216 | 0.5 mm | – | 8 mm | 4000 | – |
| 0508/1220 | 0.9 mm | 8 mm | 8 mm | 4000 | – |
| 0603/1608 | 0.9 mm | 8 mm | 8 mm | 4000 | 16000 |
| 0612/1632 | 0.9 mm | – | 8 mm | 3000 | – |
| 0805/2012 | 0.7 mm | – | 8 mm | 3000 | – |
| | 0.9 mm | – | 8 mm | 3000 | 12000 |
| | 1.3 mm | – | 8 mm | 3000 | – |
| 1003/2508 | 0.9 mm | 8 mm | – | 4000 | – |
| 1012/2532 | 1.0 mm | – | 8 mm | 2000 | – |
| 1206/3216 | 0.9 mm | – | 8 mm | 3000 | – |
| | 1.3 mm | – | 8 mm | 3000 | – |
| | 1.4 mm | – | 8 mm | 2000 | – |
| | 1.6 mm | – | 8 mm | 2000 | – |
| 1210/3225 | 0.9 mm | – | 8 mm | 3000 | – |
| | 1.3 mm | – | 8 mm | 3000 | – |
| | 1.4 mm | – | 8 mm | 2000 | – |
| | 1.6 mm | – | 8 mm | 2000 | – |
| 1812/4532 | 1.3 mm | – | 12 mm | 1500 | – |
| | 1.4 mm | – | 12 mm | 1000 | – |
| | 1.6 mm | – | 12 mm | – | 4000 |
| | 2.3 mm | – | 12 mm | – | 3000 |
| 2220/5750 | 1.3 mm | – | 12 mm | 1500 | – |
| | 1.4 mm | – | 12 mm | 1000 | – |
| | 2.0 mm | – | 12 mm | – | 3000 |
| | 2.3 mm | – | 12 mm | – | 3000 |
| 3225 | 3.2 mm | – | 16 mm | – | 1000 |
| | 4.5 mm | – | 16 mm | – | 1000 |
| 4032 | 3.2 mm | – | 16 mm | – | 1000 |
| | 4.5 mm | – | 16 mm | – | 1000 |

Multilayer varistors (MLVs)**Automotive series****SMD****2 Delivery mode for leaded SHCV varistors**

Standard delivery mode for SHCV types is bulk. Alternative taping modes (AMMO pack or taped on reel) are available upon request.

Packing units for:

| Type | Pieces |
|-----------|--------|
| SR6 | 2000 |
| SR1 / SR2 | 1000 |

For types not listed in this data book please contact EPCOS.

Multilayer varistors (MLVs)

Automotive series


SMD

Soldering directions

1 Terminations

1.1 Nickel barrier termination

The nickel barrier layer of the silver/nickel/tin termination prevents leaching of the silver base metallization layer. This allows great flexibility in the selection of soldering parameters. The tin prevents the nickel layer from oxidizing and thus ensures better wetting by the solder. The nickel barrier termination is suitable for all commonly-used soldering methods.




Multilayer CTVS: Structure of nickel barrier termination

1.2 Silver-palladium termination

Silver-palladium terminations are used for the large case sizes 1812 and 2220 and for chips intended for conductive adhesion. This metallization improves the resistance of large chips to thermal shock.

In case of conductive adhesion, the silver-palladium metallization reduces susceptibility to corrosion. Silver-palladium termination can be used for smaller case sizes (only chip) for hybrid applications as well. The silver-palladium termination is not approved for lead-free soldering.



Multilayer varistor: Structure of silver-palladium termination


Multilayer varistors (MLVs)

Automotive series

SMD

1.3 Silver-platinum termination

Silver-platinum terminations are mainly used for the large case sizes 1812 and 2220. The silver-platinum termination is approved for reflow soldering, SnPb soldering and lead-free soldering with a silver containing solder paste. In case of SnPb soldering, a solder paste Sn62Pb36Ag2 is recommended. For lead-free reflow soldering, a solder paste SAC, e.g. Sn95.5Ag3.8Cu0.7, is recommended.




Multilayer varistor: Structure of silver-platinum termination

2 Recommended soldering temperature profiles

2.1 Reflow soldering temperature profile

Recommended temperature characteristic for reflow soldering following JEDEC J-STD-020D



Multilayer varistors (MLVs)

Automotive series

SMD

| Profile feature | | Sn-Pb eutectic assembly | Pb-free assembly |
|--|--------------------------|---------------------------------|---------------------------------|
| Preheat and soak | | | |
| - Temperature min | T_{smin} | 100 °C | 150 °C |
| - Temperature max | T_{smax} | 150 °C | 200 °C |
| - Time | t_{smin} to t_{smax} | 60 ... 120 s | 60 ... 180 s |
| Average ramp-up rate | T_{smax} to T_p | 3 °C/ s max. | 3 °C/ s max. |
| Liquidous temperature | T_L | 183 °C | 217 °C |
| Time at liquidous | t_L | 60 ... 150 s | 60 ... 150 s |
| Peak package body temperature | T_p ¹⁾ | 220 °C ... 235 °C ²⁾ | 245 °C ... 260 °C ²⁾ |
| Time (t_p) ³⁾ within 5 °C of specified classification temperature (T_c) | | 20 s ³⁾ | 30 s ³⁾ |
| Average ramp-down rate | T_p to T_{smax} | 6 °C/ s max. | 6 °C/ s max. |
| Time 25 °C to peak temperature | | maximum 6 min | maximum 8 min |

1) Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.


2) Depending on package thickness. For details please refer to JEDEC J-STD-020D.

3) Tolerance for time at peak profile temperature (t_p) is defined as a supplier minimum and a user maximum.

Note: All temperatures refer to topside of the package, measured on the package body surface.
Number of reflow cycles: 3

2.2 Wave soldering temperature profile

Temperature characteristics at component terminal with dual-wave soldering



Multilayer varistors (MLVs)

Automotive series

SMD

2.3 Lead-free soldering processes

EPCOS multilayer CTVS with AgNiSn termination are designed for the requirements of lead-free soldering processes only.

Soldering temperature profiles to JEDEC J-STD-020D, IEC 60068-2-58 and ZVEI recommendations.

3 Recommended soldering methods - type-specific releases by EPCOS

3.1 Overview

| Type | Case size | Reflow soldering | | Wave soldering | |
|-----------------|---------------|------------------|-----------|----------------|-----------|
| | | SnPb | Lead-free | SnPb | Lead-free |
| CT... / CD... | 0201/ 0402 | Approved | Approved | No | No |
| CT... / CD... | 0603 ... 2220 | Approved | Approved | Approved | Approved |
| CN... | 0603 ... 2220 | Approved | No | Approved | No |
| CN...K2 | 1812, 2220 | Approved | Approved | No | No |
| Arrays | 0405 ... 1012 | Approved | Approved | No | No |
| ESD/EMI filters | 0405, 0508 | Approved | Approved | No | No |
| CU | 3225, 4032 | Approved | Approved | Approved | Approved |
| SHCV | - | No | No | Approved | Approved |

3.2 Nickel barrier and AgPt terminated multilayer CTVS

All EPCOS MLVs with nickel barrier and AgPt termination are suitable and fully qualified for lead-free soldering. The nickel barrier layer is 100% matte tin-plated.

3.3 Silver-palladium terminated MLVs

AgPd-terminated MLVs are mainly designed for conductive adhesion technology on hybrid material. Additionally MLVs with AgPd termination are suitable for reflow and wave soldering with SnPb solder.

Note:

Lead-free soldering is not approved for MLVs with AgPd termination.

3.4 Silver-platinum terminated MLVs

The silver-platinum termination is approved for reflow soldering, SnPb soldering and lead-free with a silver containing solder paste. In case of SnPb soldering, a solder paste Sn62Pb36Ag2 is recommended. For lead-free reflow soldering, a solder paste SAC, e.g. Sn95.5Ag3.8Cu0.7, is recommended.

Multilayer varistors (MLVs)

Automotive series

SMD

3.5 Tinned copper alloy

All EPCOS CU types with tinned termination are approved for lead-free and SnPb soldering.

3.6 Tinned iron wire

All EPCOS SHCV types with tinned termination are approved for lead-free and SnPb soldering.

4 Solder joint profiles / solder quantity


4.1 Nickel barrier termination

If the meniscus height is too low, that means the solder quantity is too low, the solder joint may break, i.e. the component becomes detached from the joint. This problem is sometimes interpreted as leaching of the external terminations.

If the solder meniscus is too high, i.e. the solder quantity is too large, the vise effect may occur. As the solder cools down, the solder contracts in the direction of the component. If there is too much solder on the component, it has no leeway to evade the stress and may break, as in a vise.


The figures below show good and poor solder joints for dual-wave and infrared soldering.

4.1.1 Solder joint profiles for nickel barrier termination - dual-wave soldering



Good and poor solder joints caused by amount of solder in dual-wave soldering.


4.1.2 Solder joint profiles for nickel barrier termination / silver-palladium / silver-platinum termination - reflow soldering



Multilayer varistors (MLVs)


Automotive series

SMD



Good and poor solder joints caused by amount of solder in reflow soldering.

5 Conductive adhesion



Attaching surface-mounted devices (SMDs) with electrically conductive adhesives is a commercially attractive method of component connection to supplement or even replace conventional soldering methods.

Electrically conductive adhesives consist of a non-conductive plastic (epoxy resin, polyimide or silicon) in which electrically conductive metal particles (gold, silver, palladium, nickel, etc) are embedded. Electrical conduction is effected by contact between the metal particles.

Adhesion is particularly suitable for meeting the demands of hybrid technology. The adhesives can be deposited ready for production requirements by screen printing, stamping or by dispensers. As shown in the following table, conductive adhesion involves two work operations fewer than soldering.

| Reflow soldering | Wave soldering | Conductive adhesion |
|---------------------------|----------------|----------------------------------|
| Screen-print solder paste | Apply glue dot | Screen-print conductive adhesive |
| Mount SMD | Mount SMD | Mount SMD |
| Predry solder paste | Cure glue | Cure adhesive |
| Reflow soldering | Wave soldering | Inspect |
| Wash | Wash | |
| Inspect | Inspect | |

Multilayer varistors (MLVs)

Automotive series

SMD

A further advantage of adhesion is that the components are subjected to virtually no temperature shock at all. The curing temperatures of the adhesives are between 120 °C and 180 °C, typical curing times are between 30 minutes and one hour.

The bending strength of glued chips is, in comparison with that of soldered chips, higher by a factor of at least 2, as is to be expected due to the elasticity of the glued joints.

The lower conductivity of conductive adhesive may lead to higher contact resistance and thus result in electrical data different to those of soldered components. Users must pay special attention to this in RF applications.

6 Solderability tests

| Test | Standard | Test conditions Sn-Pb soldering | Test conditions Pb-free soldering | Criteria/ test results |
|---|-------------------|--|---|---|
| Wettability | IEC 60068-2-58 | Immersion in 60/40 SnPb solder using non-activated flux at 215 ± 3 °C for 3 ± 0.3 s | Immersion in Sn96.5Ag3.0Cu0.5 solder using non- or low activated flux at 245 ± 5 °C for 3 ± 0.3 s | Covering of 95% of end termination, checked by visual inspection |
| Leaching resistance | IEC 60068-2-58 | Immersion in 60/40 SnPb solder using mildly activated flux without preheating at 260 ± 5 °C for 10 ± 1 s | Immersion in Sn96.5Ag3.0Cu0.5 solder using non- or low activated flux without preheating at 255 ± 5 °C for 10 ± 1 s | No leaching of contacts |
| Thermal shock (solder shock) | | Dip soldering at 300 °C/5 s | Dip soldering at 300 °C/5 s | No deterioration of electrical parameters. Capacitance change: $\leq \pm 15\%$ |
| Tests of resistance to soldering heat for SMDs | IEC 60068-2-58 | Immersion in 60/40 SnPb for 10 s at 260 °C | Immersion in Sn96.5Ag3.0Cu0.5 for 10 s at 260 °C | Change of varistor voltage: $\leq \pm 5\%$ |
| Tests of resistance to soldering heat for radial leaded components (SHCV) | IEC 60068-2-20 | Immersion of leads in 60/40 SnPb for 10 s at 260 °C | Immersion of leads in Sn96.5Ag3.0Cu0.5 for 10 s at 260 °C | Change of varistor voltage: $\leq \pm 5\%$ Change of capacitance X7R: $\leq -5/+10\%$ |

Multilayer varistors (MLVs)


Automotive series

SMD


Note:

Leaching of the termination

Effective area at the termination might be lost if the soldering temperature and/or immersion time are not kept within the recommended conditions. Leaching of the outer electrode should not exceed 25% of the chip end area (full length of the edge A-B-C-D) and 25% of the length A-B, shown below as mounted on substrate.



As a single chip



As mounted on substrate

7 Notes for proper soldering

7.1 Preheating and cooling

- According to JEDEC J-STD-020D. Please refer to chapter 2.

7.2 Repair / rework

Manual soldering with a soldering iron must be avoided, hot-air methods are recommended for rework purposes.

7.3 Cleaning

All environmentally compatible agents are suitable for cleaning. Select the appropriate cleaning solution according to the type of flux used. The temperature difference between the components and cleaning liquid must not be greater than 100 °C. Ultrasonic cleaning should be carried out with the utmost caution. Too high ultrasonic power can impair the adhesive strength of the metalized surfaces.

7.4 Solder paste printing (reflow soldering)

An excessive application of solder paste results in too high a solder fillet, thus making the chip more susceptible to mechanical and thermal stress. Too little solder paste reduces the adhesive strength on the outer electrodes and thus weakens the bonding to the PCB. The solder should be applied smoothly to the end surface.

Multilayer varistors (MLVs)

Automotive series

SMD

7.5 Adhesive application

Thin or insufficient adhesive causes chips to loosen or become disconnected during curing. Low viscosity of the adhesive causes chips to slip after mounting. It is advised to consult the manufacturer of the adhesive on proper usage and amounts of adhesive to use.

7.6 Selection of flux

Used flux should have less than or equal to 0.1 wt % of halogenated content, since flux residue after soldering could lead to corrosion of the termination and/or increased leakage current on the surface of the component. Strong acidic flux must not be used. The amount of flux applied should be carefully controlled, since an excess may generate flux gas, which in turn is detrimental to solderability.

7.7 Storage of CTVs

Solderability is guaranteed for one year from date of delivery for multilayer varistors, CeraDiodes and ESD/EMI filters (half a year for chips with AgPd and AgPt terminations) and two years for SHCV and CU components, provided that components are stored in their original packages.

Storage temperature: $-25\text{ }^{\circ}\text{C}$ to $+45\text{ }^{\circ}\text{C}$

Relative humidity: $\leq 75\%$ annual average, $\leq 95\%$ on 30 days a year

The solderability of the external electrodes may deteriorate if SMDs and leaded components are stored where they are exposed to high humidity, dust or harmful gas (hydrogen chloride, sulfurous acid gas or hydrogen sulfide).

Do not store SMDs and leaded components where they are exposed to heat or direct sunlight. Otherwise the packing material may be deformed or SMDs/ leaded components may stick together, causing problems during mounting.

After opening the factory seals, such as polyvinyl-sealed packages, it is recommended to use the SMDs or leaded components as soon as possible.

7.8 Placement of components on circuit board

Especially in the case of dual-wave soldering, it is of advantage to place the components on the board before soldering in that way that their two terminals do not enter the solder bath at different times.

Ideally, both terminals should be wetted simultaneously.

7.9 Soldering cautions

- An excessively long soldering time or high soldering temperature results in leaching of the outer electrodes, causing poor adhesion and a change of electrical properties of the varistor due to the loss of contact between electrodes and termination.
- Wave soldering must not be applied for MLVs designated for reflow soldering only.
- Keep the recommended down-cooling rate.

Multilayer varistors (MLVs)

Automotive series

SMD

7.10 Standards

CECC 00802

IEC 60068-2-58

IEC 60068-2-20

JEDEC J-STD-020D

Multilayer varistors (MLVs)

Automotive series

SMD

Symbols and terms

| Symbol | Term |
|-------------------|--|
| $C_{line,typ}$ | Typical capacitance per line |
| C_{max} | Maximum capacitance |
| C_{min} | Minimum capacitance |
| C_{nom} | Nominal capacitance |
| ΔC_{nom} | Tolerance of nominal capacitance |
| C_{typ} | Typical capacitance |
| $f_{cut-off,min}$ | Minimum cut-off frequency |
| I | Current |
| I_{clamp} | Clamping current |
| I_{leak} | Leakage current |
| $I_{leak,typ}$ | Typical leakage current |
| I_{PP} | Peak pulse current |
| $I_{surge,max}$ | Maximum surge current (also termed peak current) |
| LCT | Lower category temperature |
| L_{typ} | Typical inductance |
| $P_{diss,max}$ | Maximum power dissipation |
| P_{PP} | Peak pulse power |
| R_{ins} | Insulation resistance |
| R_{min} | Minimum resistance |
| R_S | Resistance per line |
| T_A | Ambient temperature |
| T_{op} | Operating temperature |
| T_{stg} | Storage temperature |
| t_r | Duration of equivalent rectangular wave |
| t_{resp} | Response time |
| UCT | Upper category temperature |
| V | Voltage |
| $V_{BR,min}$ | Minimum breakdown voltage |
| $V_{clamp,max}$ | Maximum clamping voltage |
| $V_{DC,max}$ | Maximum DC operating voltage (also termed working voltage) |
| $V_{ESD,air}$ | Air discharge ESD capability |
| $V_{ESD,contact}$ | Contact discharge ESD capability |
| V_{jump} | Maximum jump start voltage |

Multilayer varistors (MLVs)

Automotive series

SMD

| | |
|-----------------------|--|
| $V_{\text{RMS,max}}$ | Maximum AC operating voltage, root-mean-square value |
| V_V | Varistor voltage (also termed breakdown voltage) |
| $V_{V,\text{min}}$ | Minimum varistor voltage |
| $V_{V,\text{max}}$ | Maximum varistor voltage |
| ΔV_V | Tolerance of varistor voltage |
| W_{LD} | Maximum load dump |
| W_{max} | Maximum energy absorption (also termed transient energy) |
| α_{typ} | Typical insertion loss |
| e | Lead spacing |
| $\ll * \gg$ | Maximum possible application conditions |

All dimensions are given in mm.

The commas used in numerical values denote decimal points.

Multilayer varistors (MLVs)

Automotive series

SMD

Cautions and warnings

General

Some parts of this publication contain statements about the suitability of our ceramic transient voltage suppressor (CTVS) components (multilayer varistors (MLVs), CeraDiodes, ESD/EMI filters, SMD disk varistors (CU types), leaded transient voltage/ RFI suppressors (SHCV types)) for certain areas of application, including recommendations about incorporation/design-in of these products into customer applications. The statements are based on our knowledge of typical requirements often made of our CTVS devices in the particular areas. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our CTVS components for a particular customer application. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always incumbent on the customer to check and decide whether the CTVS devices with the properties described in the product specification are suitable for use in a particular customer application.

- Do not use EPCOS CTVS components for purposes not identified in our specifications, application notes and data books.
- Ensure the suitability of a CTVS in particular by testing it for reliability during design-in. Always evaluate a CTVS component under worst-case conditions.
- Pay special attention to the reliability of CTVS devices intended for use in safety-critical applications (e.g. medical equipment, automotive, spacecraft, nuclear power plant).

Design notes

- Always connect a CTVS in parallel with the electronic circuit to be protected.
- Consider maximum rated power dissipation if a CTVS has insufficient time to cool down between a number of pulses occurring within a specified isolated time period. Ensure that electrical characteristics do not degrade.
- Consider derating at higher operating temperatures. Choose the highest voltage class compatible with derating at higher temperatures.
- Surge currents beyond specified values will puncture a CTVS. In extreme cases a CTVS will burst.
- If steep surge current edges are to be expected, make sure your design is as low-inductance as possible.
- In some cases the malfunctioning of passive electronic components or failure before the end of their service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In applications requiring a very high level of operational safety and especially when the malfunction or failure of a passive electronic component could endanger human life or health (e.g. in accident prevention, life-saving systems, or automotive battery line applications such as clamp 30), ensure by suitable design of the application or other measures (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of such a malfunction or failure. Only use CTVS components from the automotive series in safety-relevant applications.

Multilayer varistors (MLVs)

Automotive series

SMD

- Specified values only apply to CTVS components that have not been subject to prior electrical, mechanical or thermal damage. The use of CTVS devices in line-to-ground applications is therefore not advisable, and it is only allowed together with safety countermeasures like thermal fuses.

Storage

- Only store CTVS in their original packaging. Do not open the package before storage.
- Storage conditions in original packaging: temperature -25 to $+45^{\circ}\text{C}$, relative humidity $\leq 75\%$ annual average, maximum 95% , dew precipitation is inadmissible.
- Do not store CTVS devices where they are exposed to heat or direct sunlight. Otherwise the packaging material may be deformed or CTVS may stick together, causing problems during mounting.
- Avoid contamination of the CTVS surface during storage, handling and processing.
- Avoid storing CTVS devices in harmful environments where they are exposed to corrosive gases for example (SO_x , Cl).
- Use CTVS as soon as possible after opening factory seals such as polyvinyl-sealed packages.
- Solder CTVS components after shipment from EPCOS within the time specified:
 - CTVS with Ni barrier termination, 12 months
 - CTVS with AgPd and AgPt termination, 6 months
 - SHCV and CU series, 24 months

Handling

- Do not drop CTVS components and allow them to be chipped.
- Do not touch CTVS with your bare hands - gloves are recommended.
- Avoid contamination of the CTVS surface during handling.

Mounting

- When CTVS devices are encapsulated with sealing material or overmolded with plastic material, electrical characteristics might be degraded and the life time reduced.
- Make sure an electrode is not scratched before, during or after the mounting process.
- Make sure contacts and housings used for assembly with CTVS components are clean before mounting.
- The surface temperature of an operating CTVS can be higher. Ensure that adjacent components are placed at a sufficient distance from a CTVS to allow proper cooling.
- Avoid contamination of the CTVS surface during processing.
- Multilayer varistors (MLVs) with AgPd termination are not approved for lead-free soldering.

Soldering

- Complete removal of flux is recommended to avoid surface contamination that can result in an instable and/or high leakage current.
- Use resin-type or non-activated flux.
- Bear in mind that insufficient preheating may cause ceramic cracks.
- Rapid cooling by dipping in solvent is not recommended, otherwise a component may crack.

Multilayer varistors (MLVs)

Automotive series

SMD

Conductive adhesive gluing

- Only multilayer varistors (MLVs) with an AgPd termination are approved for conductive adhesive gluing.

Operation

- Use CTVS only within the specified operating temperature range.
- Use CTVS only within specified voltage and current ranges.
- Environmental conditions must not harm a CTVS. Only use them in normal atmospheric conditions. Reducing the atmosphere (e.g. hydrogen or nitrogen atmosphere) is prohibited.
- Prevent a CTVS from contacting liquids and solvents. Make sure that no water enters a CTVS (e.g. through plug terminals).
- Avoid dewing and condensation.
- EPCOS CTVS components are mainly designed for encased applications. Under all circumstances avoid exposure to:
 - direct sunlight
 - rain or condensation
 - steam, saline spray
 - corrosive gases
 - atmosphere with reduced oxygen content
- EPCOS CTVS devices are not suitable for switching applications or voltage stabilization where static power dissipation is required.
- Multilayer varistors (MLVs) are designed for ESD protection and transient suppression. CeraDiodes are designed for ESD protection only, ESD/EMI filters are designed for ESD and EMI protection only.

This listing does not claim to be complete, but merely reflects the experience of EPCOS AG.

Important notes

The following applies to all products named in this publication:

1. Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out **that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application**. As a rule we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
2. We also point out that **in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
3. **The warnings, cautions and product-specific notes must be observed.**
4. In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous)**. Useful information on this will be found in our Material Data Sheets on the Internet (www.tdk-electronics.tdk.com/material). Should you have any more detailed questions, please contact our sales offices.
5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order.

We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
6. Unless otherwise agreed in individual contracts, **all orders are subject to our General Terms and Conditions of Supply**.
7. **Our manufacturing sites serving the automotive business apply the IATF 16949 standard**. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that **only requirements mutually agreed upon can and will be implemented in our Quality Management System**. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.
8. The trade names EPCOS, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at www.tdk-electronics.tdk.com/trademarks.