


HVCW-3433EQXA



3433 PLCC6 系列产品 / Products Series

具有高发光效率、高一致性、高稳定性、高可靠性，主要用于汽车应用

High luminous efficiency, consistency, stability and reliability, it is mainly used in automobile applications.

特征

- 外观：白色PPA塑料，荧光硅胶封装
- 50% I_v 视角：120°
- 颜色：Cx=0.33,Cy=0.33 (CIE1931)
- 资格：通过了AEC-Q102 & IEC 60810可靠性测试
- 潮湿敏感等级-2

Features

- Package: Colored diffused silicone in white PPA cup
- Viewing angle at 50% I_v : 120°
- Color: Cx=0.33,Cy=0.33 (acc.to CIE1931)
- Qualifications: Passed reliability test per AEC-Q102 & IEC 60810 requirement
- MSL-2

应用

- 信号灯
- 汽车内外部照明应用

Applications

- Signaling
- Interior and exterior lighting for automotive

订购信息 / Ordering Information

型号 Type	发光强度 Luminous Intensity I _v @ I _f =140mA	订单编号 Ordering Code
HVCW-3433EQXA-XXXX-XXXX-XX 亮度档 Brightness 色度坐标 Chromaticity Coordinate 电压档 Forward Voltage	7.10 - 22.40 cd	XXXXXX

备注

■ 亮度档

单个最小包装只装有同一个亮度档次的产品，具体分档信息请见第4页

例如：HVCW-3433EQXA-EAGA-XXXX-XX，单个卷盘中的产品只有EA、EB、FA、FB、GA中的某一档

■ 色度坐标档

单个最小包装只装有同一个色度坐标档次的产品，具体分档信息请见第5页

例如：HVCW-3433EQXA-XXXX-JKQL-XX，单个卷盘中的产品只有JK、JL...QK、QL或FK0、FL0、GK0、GL0、HK0、HL0……PN0中的某一档

■ 正向电压档

单个最小包装只装有同一个正向电压档次的产品，具体分档信息请见第4页

例如：HVCW-3433EQXA-XXXX-XXXX-47，单个卷盘中的产品只有4、5、6、7中的某一档

Note

■ Brightness Grouping

Only one brightness group will be packed in each reel. Please refer to page #4 for details.

E.g.: HVCW-3433EQXA-EAGA-XXXX-XX, means only one bin of EA、EB、FA、FB or GA is in each reel.

■ Chromaticity Coordinate Groups

Only one Chromaticity Coordinate group will be packed in each reel. Please refer to page #5 for details.

E.g.: HVCW-3433EQXA-XXXX-JKQL-XX, means only one bin of JK、JL...QK、QL or FK0、FL0、GK0、GL0、HK0、HL0……PN0 is in each reel.

■ Forward Voltage Groups

Only one forward voltage group will be packed in each reel. Please refer to page #4 for details.

E.g.: HVCW-3433EQXA-XXXX-XXXX-47, means only one bin of 4, 5, 6 or 7 is in each

极限参数 / Maximum Ratings

参数 Parameters	符号 Symbol	数值 Rating	单位 Unit
结温 / Junction Temperature	T_j	125	°C
正向电流 / Forward Current ($T_s=25^{\circ}\text{C}$)	I_f	240	mA
峰值正向电流 Peak Forward Current ($t \leq 10\mu\text{s}$; $D=0.005$; $T_s=25^{\circ}\text{C}$)	I_{fp}	750	mA
反向电压 / Reverse Voltage ($T_s=25^{\circ}\text{C}$)	V_r	不可施加反向电压 / not designed for reverse operation	V
抗静电能力 Electrostatic Discharge (HBM)	V_{ESD}	2000	V
操作温度 / Operating Temperature	T_{opr}	-40 ~ +110	°C
储存温度 / Storage Temperature	T_{stg}	-40 ~ +110	°C

特性 / Characteristics ($T_s = 25^{\circ}\text{C}$; $I_f = 140\text{ mA}$)


参数 Parameters		符号 Symbol	数值 Rating	单位 Unit
色坐标 / Chromaticity coordinates acc. to CIE 1931	typ.	C_x C_y	0.33 0.33	nm
50 % I_v 下的视角 / Viewing Angle at 50 % I_v	typ.	2ϕ	120	°
正向电压 / Forward Voltage	min. typ. max	V_f V_f V_f	2.90 3.30 4.10	V V V
反向电流 / Reverse Current ($V_R=12\text{V}$)	typ. max.	I_r I_r	不可施加反向 电压 / not designed for reverse operation	μA μA
实际热阻值 (PN结-环境) / Real Thermal Resistance (Junction / Ambient)	max.	$R_{th JA_{real}}$	40	K/W
实际热阻值 (PN结-焊点) / Real Thermal Resistance (Junction / Solder Point)	max.	$R_{th JS_{real}}$	34	K/W

亮度分档 / Brightness Grouping ($T_s = 25\text{ }^{\circ}\text{C}$; $I_f = 140\text{ mA}$)


档次 Grouping	发光强度 Luminous Intensity I_v (min.)	发光强度 Luminous Intensity I_v (max.)	光通量 Luminous Flux Φ_v (typ.)
EA	7.10 cd	9.00 cd	24.20 lm
EB	9.00 cd	11.20 cd	30.30 lm
FA	11.20 cd	14.00 cd	37.80 lm
FB	14.00 cd	18.00 cd	45.80 lm
GA	18.00 cd	22.40 cd	54.20 lm

正向电压分档 / Forward Voltage Grouping ($T_s = 25\text{ }^{\circ}\text{C}$; $I_f = 140\text{ mA}$)

档次 Grouping	正向电压 Forward Voltage V_f (min.)	正向电压 Forward Voltage V_f (max.)
4	2.90 V	3.20 V
5	3.20 V	3.50 V
6	3.50 V	3.80 V
7	3.80 V	4.10 V

颜色色度分档/Colour Chromaticity Groups 1 ($T_s = 25\text{ }^{\circ}\text{C}$; $I_f = 140\text{ mA}$)

	X	Y		X	Y		X	Y		X	Y
JK	0.2910	0.2680	LK	0.3100	0.2970	NK	0.3288	0.3081	PK	0.3484	0.3388
	0.2960	0.2590		0.3130	0.2840		0.3288	0.3282		0.3484	0.3571
	0.3005	0.2825		0.3197	0.3131		0.3386	0.3235		0.3582	0.3542
	0.3045	0.2715		0.3205	0.2956		0.3386	0.3426		0.3582	0.3715
JL	0.2850	0.2790	LL	0.3070	0.3120	NL	0.3288	0.3282	PL	0.3484	0.3571
	0.2910	0.2680		0.3100	0.2970		0.3288	0.3453		0.3484	0.3730
	0.2960	0.2955		0.3189	0.3302		0.3386	0.3426		0.3582	0.3715
	0.3005	0.2825		0.3197	0.3131		0.3386	0.3591		0.3582	0.3792
KK	0.3005	0.2825	MK	0.3197	0.3131	OK	0.3386	0.3235	QK	0.3582	0.3542
	0.3045	0.2715		0.3205	0.2956		0.3386	0.3426		0.3582	0.3715
	0.3100	0.2970		0.3288	0.3081		0.3484	0.3388		0.3680	0.3695
	0.3130	0.2840		0.3288	0.3282		0.3484	0.3571		0.3680	0.3859
KL	0.2960	0.2955	ML	0.3189	0.3302	OL	0.3386	0.3426	QL	0.3582	0.3715
	0.3005	0.2825		0.3197	0.3131		0.3386	0.3591		0.3582	0.3792
	0.3070	0.3120		0.3288	0.3282		0.3484	0.3571		0.3680	0.3859
	0.3100	0.2970		0.3288	0.3452		0.3484	0.3730			

颜色色度分档/Colour Chromaticity Groups 2 ($T_s = 25\text{ }^{\circ}\text{C}$; $I_f = 140\text{ mA}$)

	X	Y		X	Y		X	Y
FK0	0.2498	0.2053	HK0	0.2700	0.2361	JK0	0.2898	0.2664
	0.2597	0.2204		0.2797	0.2509		0.3007	0.2830
	0.2682	0.2146		0.2861	0.2427		0.3045	0.2717
	0.2589	0.2000		0.2775	0.2292		0.2950	0.2568
FL0	0.2402	0.2108	HL0	0.2624	0.2431	JL0	0.2848	0.2757
	0.2509	0.2264		0.2733	0.2590		0.2971	0.2935
	0.2597	0.2204		0.2797	0.2509		0.3007	0.2830
	0.2498	0.2053		0.2700	0.2361		0.2898	0.2664
FM0	0.2269	0.2185	HM0	0.2520	0.2527	JM0	0.2780	0.2883
	0.2388	0.2348		0.2646	0.2700		0.2922	0.3077
	0.2509	0.2264		0.2733	0.2590		0.2971	0.2935
	0.2402	0.2108		0.2624	0.2431		0.2848	0.2757
FN0	0.2136	0.2262	HN0	0.2416	0.2623	JN0	0.2712	0.3009
	0.2267	0.2432		0.2559	0.2810		0.2873	0.3219
	0.2388	0.2348		0.2646	0.2700		0.2922	0.3077
	0.2269	0.2185		0.2520	0.2527		0.2780	0.2883

GK0	0.2597	0.2204	IK0	0.2797	0.2509	KK0	0.3007	0.2830
	0.2700	0.2361		0.2898	0.2664		0.3113	0.2992
	0.2775	0.2292		0.2950	0.2568		0.3138	0.2862
	0.2682	0.2146		0.2861	0.2427		0.3045	0.2717
GL0	0.2509	0.2264	ILO	0.2733	0.2590	KL0	0.2971	0.2935
	0.2624	0.2431		0.2848	0.2757		0.3090	0.3108
	0.2700	0.2361		0.2898	0.2664		0.3113	0.2992
	0.2597	0.2204		0.2797	0.2509		0.3007	0.2830
GM0	0.2388	0.2348	IMO	0.2464	0.2700	KM0	0.2922	0.3077
	0.2520	0.2527		0.2780	0.2883		0.3060	0.3266
	0.2624	0.2431		0.2848	0.2757		0.3090	0.3108
	0.2509	0.2264		0.2733	0.2590		0.2971	0.2935
GN0	0.2267	0.2432	INO	0.2559	0.2810	KN0	0.2873	0.3219
	0.2416	0.2623		0.2712	0.3009		0.3030	0.3424
	0.2520	0.2527		0.2780	0.2883		0.3060	0.3266
	0.2388	0.2348		0.2464	0.2700		0.2922	0.3077
LK0	0.3113	0.2992	MM0	0.3196	0.3451	PK0	0.3465	0.3530
	0.3219	0.3154		0.3345	0.3654		0.3599	0.3735
	0.3231	0.3008		0.3341	0.3472		0.3567	0.3535
	0.3138	0.2862		0.3209	0.3281		0.3447	0.3347
LL0	0.3090	0.3108	MN0	0.3183	0.3621	PL0	0.3479	0.3673
	0.3209	0.3281		0.3349	0.3830		0.3623	0.3882
	0.3219	0.3154		0.3345	0.3654		0.3599	0.3735
	0.3113	0.2992		0.3196	0.3451		0.3465	0.3530
LM0	0.3060	0.3266	NK0	0.3339	0.3336	PM0	0.3498	0.3863
	0.3196	0.3451		0.3465	0.3530		0.3655	0.4079
	0.3209	0.3281		0.3447	0.3347		0.3623	0.3882
	0.3090	0.3108		0.3335	0.3172		0.3479	0.3673
LN0	0.3030	0.3424	NL0	0.3341	0.3472	PN0	0.3517	0.4053
	0.3183	0.3621		0.3479	0.3673		0.3687	0.4276
	0.3196	0.3451		0.3465	0.3530		0.3655	0.4079
	0.3060	0.3266		0.3339	0.3336		0.3498	0.3863
MK0	0.3219	0.3154	NM0	0.3345	0.3654			
	0.3339	0.3336		0.3498	0.3863			
	0.3335	0.3172		0.3479	0.3673			
	0.3231	0.3008		0.3341	0.3472			
ML0	0.3209	0.3281	NN0	0.3349	0.3830			
	0.3341	0.3472		0.3517	0.4053			
	0.3339	0.3336		0.3498	0.3863			
	0.3219	0.3154		0.3345	0.3654			

标签信息 / Information on Label


例 / E.g.: EB-JK-4

亮度档 / Brightness	颜色 / Color	正向电压 / Forward Voltage
EB	JK	4

相对发射光谱 - $V(\lambda)$ = 标准人眼视觉曲线


Relative Spectral Emission - $V(\lambda)$ = Standard Eye Response Curve

$I_{rel} = f(\lambda)$; $T_s = 25\text{ }^{\circ}\text{C}$; $I_f = 140\text{ mA}$




辐射特性 / Radiation Characteristics

$$I_{\text{rel}} = f(\phi); T_s = 25^\circ\text{C}$$




正向电流 / Forward Current

$$I_f = f(V_f); T_a = 25^\circ\text{C}$$




相对亮度特性曲线 / Relative Luminous Intensity


$$I_v/I_v(140\text{ mA}) = f(I_f); T_a = 25^\circ\text{C}$$




色坐标数据表/Chromaticity coordinate shift

 $\Delta C_x, \Delta C_y = f(I_f); T_s = 25^\circ\text{C}$ 


相对正向电压 / Relative Forward Voltage

 $\Delta V_f = V_f - V_f(25^\circ\text{C}) = f(T_j); I_f = 140\text{ mA}$ 


相对发光强度 / Relative Luminous Intensity

 $I_v/I_v(25^\circ\text{C}) = f(T_j); I_f = 140\text{ mA}$ 


色坐标数据表/Chromaticity coordinate shift

 $\Delta C_x, \Delta C_y = f(I_f); I_f = 140\text{mA}$ 

焊点温度与正向电流 / Solder Point Temperature vs. Forward Current

 $I_f = f(T_s)$ 

产品尺寸 / Package Outline



备注

■ 统计质量: 40mg

■ 标 记: 阳极

■ 腐蚀试验: 等级 3B

测试条件: 1) H_2S 测试: $40^\circ C$ / 90%R.H, 15ppm, 336小时 (标准IEC 60068-2-43)

2) 流动混合气体测试: $25^\circ C$ / 75 %R.H, 500小时

(标准IEC 60068-2-60 方法 4: 10ppb H_2S , 200ppb SO_2 , 200ppb NO_2 , 10ppb Cl_2)

NOTE

■ Approximate Weight: 30mg

■ Mark: Anode

■ Corrosion test: Class 3B


Test conditions: 1) H_2S test: $40^\circ C$ / 90%R.H, 15ppm, 336hours

(Standards IEC 60068-2-43)

2) Flowing mixed gas test: $25^\circ C$ / 75 %R.H, 500hours

(Standards IEC 60068-2-60 test method 4: 10ppb H_2S , 200ppb SO_2 , 200ppb NO_2 , 10ppb Cl_2)

推荐焊盘 / Recommended Solder Pad




注释

■ 不适合超声波清洗的封装

NOTE



■ Package not suitable for ultrasonic cleaning

回流焊要求 / Reflow Soldering Profile



主要特性 Profile Feature	符号 Symbol	无铅焊接 Pb-Free (SnAgCu) Assembly			单位 Unit
		min.	rec.	max.	
预热升温速率 Ramp-up Rate to Preheat 25°C–150°C	–	–	2	3	°C/s
时间 / Time (T_{smin} to T_{smax})	T_s	60	100	120	s
峰值升温速率 Ramp-up Rate to Peak (T_{smax} to T_p)	–	–	2	3	°C/s
熔点温度 Liquidus Temperature	T_l		217		°C
高于熔点温度的时间 Time above Liquidus Temperature	t_l	–	80	100	s
峰值温度 / Peak Temperature	T_p	–	255	260	°C
规定的峰值温度 $\pm 5^\circ\text{C}$ 以内的时间 Time within 5°C of the Specified Peak Temperature	t_p	10	20	30	s
降温速率 / Ramp-down Rate (T_p to 100°C)	–	–	3	6	°C/s
时间 / Time (25°C to T_p)	–	–	–	480	s

卷带与卷盘 / Tape and Reel



前端空带: 最小400 mm; 尾端空带: 最小160 mm; 尺寸符合: IEC 60286-3, EIA 481-D标准

Leader: min. 400 mm; Trailer: min. 160 mm; Requirement acc. to IEC 60286-3, EIA 481-D

卷带尺寸 / Tape Dimensions (mm)

W	P0	P1	P2	D0	E	F
12±0.3	4±0.1	4±0.1	2±0.1	1.5+0.1/-0	1.75±0.1	5.5±0.1

卷盘尺寸 / Reel Dimensions (mm)

A	W1	W2	N	R
177.8±0.1	12.7+2/-0.5	14.8+2/-0.5	58.5±0.2	13.5±0.2

数量 (颗/卷) / Quantity (pcs/reel)

1000

条形码标签 / Barcode-Product-Label (BPL)



HONGLI TRONIC
鸿利光电



Device No: HVXX-XXXXXXX



Lot No: XXXX-XXXXXXXX



Product No: XXXXXXXXXXXXX



Qty: XXXXPCS **D/C:** XXXX



BIN: XX-XX-XX

IV: XXXX-XXXX mcd

X/Y: XX


VF: XXX-XXX V



MSL:2



包装材料及过程 / Dry Packing Process and Materials




备注

产品包装在一个干燥的铝箔袋里，同时内附有干燥剂和湿度卡。
对于干燥包装，您可以从网络或JEDEC标准里获取。

NOTE

Moisture-sensitive product is packed in a dry bag containing desiccant and HIC (humidity indicator card).
Regarding dry pack you may find further information in the internet or JEDEC.

出货包装及材料 / Transportation Packing and Materials



出货箱尺寸 / Dimensions of Transportation Box (mm)

宽度 / Width	长度 / Length	高度 / Height
256 ± 5	223 ± 5	62 ± 5
256 ± 5	223 ± 5	124 ± 5

注释

典型值: 每个产品的实际值可能与这些统计出的典型值不同。

公差: 除非图纸中有说明, 公差默认为 $\pm 0.1 \text{ mm}$ 。

正向电压: 正向电压是在8ms脉冲电流并且内部在线性为 $\pm 0.05\text{V}$ 和一个 $\pm 0.1\text{V}$ 的外在不确定性 (按照GUM K=3因子) 来进行测试的。

色度坐标: 色度坐标是在25ms脉冲电流并且内部在线性为 ± 0.005 和一个 ± 0.01 的外在不确定性 (按照GUM K=3因子) 来进行测试的。

亮度: 亮度是在25ms脉冲电流并且内部在线性为 $\pm 8\%$ 和一个 $\pm 11\%$ 的外在不确定性 (按照GUM K=3因子) 来进行测试的。

特殊声明: 本版本最终解释权归属鸿利智汇, 当中英文意思发生歧义时, 以中文为准。

Glossary

Typical Values: Actual values of each product may differ from these statistical values .

Tolerance of Measure: Unless otherwise noted in drawing, tolerances are specified with $\pm 0.1\text{mm}$.

Forward Voltage: The forward voltage is measured during a current pulse of typically 8 ms, with an internal reproducibility of $\pm 0.05 \text{ V}$ and an expanded uncertainty of $\pm 0.1 \text{ V}$ (acc. to GUM with a coverage factor of $k = 3$).

Chromaticity coordinate groups: Chromaticity coordinate groups is measured at a current pulse of typically 25 ms, with an internal reproducibility of ± 0.005 and an expanded uncertainty of ± 0.01 (acc. to GUM with a coverage factor of $k = 3$).

Brightness: Brightness values are measured during a current pulse of typically 25 ms, with an internal reproducibility of $\pm 8\%$ and an expanded uncertainty of $\pm 11\%$ (acc. to GUM with a coverage factor of $k = 3$).

Special Statement: The final interpretation of this specification shall be vested in Honglitrionic, in the case of ambiguity, the Chinese version shall prevail.