



📕 Order

Now





DCPA10505, DCPA10505D DCPA10512, DCPA10512D DCPA10515, DCPA10515D

ZHCSG81-APRIL 2017

# DCPA1 系列 1W、隔离式非稳压直流/直流转换器模块

## 1 特性

**TEXAS** 

• 2.0kV 直流隔离(运行)

INSTRUMENTS

- 具有软启动,可减小浪涌电流
- 频率同步
- EN55022 B 类 EMC 性能
- UL1950 认证组件
- 7 引脚 PDIP 和 7 引脚 SOP 封装
- 2 应用
- 信号路径隔离
- 消除接地环路
- 数据采集
- 工业控制和仪器
- 测试设备

## 3 说明

DCPA1 系列是一系列 1W、隔离式非稳压直流/直流转 换器模块。DCPA1 系列器件需要至少两个外部组件, 其包含片上器件保护装置,且能够同步至外部时钟。

**DCPA1** 系列器件集 这些特性 和小型尺寸于一体,适 合各种 应用且在需要信号路径隔离的 应用中 是一种易 于使用的解决方案。

警告:此产品具有运行隔离功能,仅可用于信号隔离。 不可作为需要增强型隔离的安全隔离电路的一部分使 用。请参见*功能描述*部分中的定义。

#### 器件信息 <sup>(1)</sup>

部件号	封装	封装尺寸 (标称值)
	PDIP (7)	10.18mm + 10.60mm
DCPA1xxxx	SOP (7)	19.18mm × 10.60mm

(1) 要了解所有可用封装,请参见数据表末尾的可订购产品附录。







An IMPORTANT NOTICE at the end of this data sheet addresses availability, warranty, changes, use in safety-critical applications, intellectual property matters and other important disclaimers. PRODUCTION DATA.



#### DCPA10505, DCPA10505D DCPA10512, DCPA10512D DCPA10515, DCPA10515D

ZHCSG81-APRIL 2017

1	特性	
2	应用	
3	说明	
4	修订	历史记录
5	Pin (	Configuration and Functions 3
6	Spee	cifications 4
	6.1	Absolute Maximum Ratings 4
	6.2	ESD Ratings 4
	6.3	Recommended Operating Conditions 4
	6.4	Electrical Characteristics 4
	6.5	Switching Characteristics 6
	6.6	Typical Characteristics (DCPA10505)7
	6.7	Typical Characteristics (DCPA10512) 8
	6.8	Typical Characteristics (DCPA10515) 9
	6.9	Typical Characteristics (DCPA10505D) 10
	6.10	Typical Characteristics (DCPA10512D) 11
	6.11	Typical Characteristics (DCPA10515D) 12
7	Deta	iled Description 13
	7.1	Overview

## 目录

	7.2	Functional Block Diagrams	13
	7.3	Feature Description	14
8		ication and Implementation	
	8.1	Application Information	17
	8.2	Typical Application	18
9	Powe	er Supply Recommendations	19
10	Layo	out	20
	10.1	Layout Guidelines	20
	10.2	Layout Example	20
11	器件	和文档支持	21
	11.1	器件支持	21
	11.2	文档支持	21
	11.3	社区资源	21
	11.4	相关链接	21
	11.5	商标	21
	11.6	静电放电警告	22
	11.7	Glossary	22
12	机械	、封装和可订购信息	22

## 4 修订历史记录

注: 之前版本的页码可能与当前版本有所不同。

日期	修订版本	注释
2017 年 4 月	*	首次发布。



www.ti.com.cn



## 5 Pin Configuration and Functions



#### **Pin Functions**

	PIN NUMBER			
PIN NAME	SINGLE- OUTPUT	DUAL- OUTPUT	I/O <sup>(1)</sup>	Description
СОМ	_	5	0	Output side common
NC	7	—		No connection
SYNCIN	14	14	Ι	Synchronization. This pin is used to synchronize to an external clock. Internally it is pulled to GND. If valid clock is not detected on this pin, the SN6505 shifts automatically to internal clock.
SW <sub>OUT</sub>	8	8	0	Unrectified transformer output.
+V <sub>OUT</sub>	6	6	0	Positive output voltage
+V <sub>S</sub>	1	1	Ι	Input voltage
-V <sub>OUT</sub>	5	7	0	Negative output voltage
-V <sub>S</sub>	2	2	Ι	Input side common

(1) I = Input, O = Output

## 6 Specifications

## 6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted) <sup>(1)</sup>

			MIN	MAX	UNIT
Input voltage			-0.5	6	V
	+V <sub>S</sub>	50ns transient	-1.0	7	V
	SYNCIN		-0.5	+V <sub>S</sub>	V
		50ns transient	-1.0	6	V
ead temperature (soldering, 10 s)				260	°C
Storage temperature,	torage temperature, T <sub>stg</sub>				°C

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

#### 6.2 ESD Ratings

			VALUE	UNIT
	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>		N/	
V <sub>(ESD)</sub>	discharge	Charged-device model (CDM), per JEDEC specification JESD22-C101 <sup>(2)</sup>	±250	V

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

## 6.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

	MIN	NOM	MAX	UNIT
Input voltage	4.5	5	5.5	V
Output power	0.05		1	W
Operating ambient temperature range	-40		100	°C

#### 6.4 Electrical Characteristics

 $T_A = 25^{\circ}C$ , +V<sub>S</sub> = nominal,  $C_{IN} = 2.2 \ \mu\text{F}$ ,  $C_{OUT} = 1.0 \ \mu\text{F}$ , (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
OUTPU	т	·				
P <sub>OUT</sub>	Output power	Over +V <sub>S</sub> range, I <sub>OUT</sub> = 100% (full load)			1	W
		DCPA10505			200	mA
	Output current	DCPA10505D			200 <sup>(1)</sup>	mA
		DCPA10512			83	mA
IOUT		DCPA10512D			83 <sup>(1)</sup>	mA
		DCPA10515			66	mA
		DCPA10515D			66 <sup>(1)</sup>	mA



## **Electrical Characteristics (continued)**

$T_{1} = 25^{\circ}C_{1} + V_{2}$	= nominal Court	22 UF Court =	= 1 0 uF (unles	s otherwise noted)
$I_A = 200, \pm v_S$	$_{\rm S}$ – normal, $O_{\rm IN}$ –	- z.z µi , o <sub>out</sub> -	- 1.0 µr, (urnes	so otherwise noted)

	PARAMETER	TEST CO	NDITIONS	MIN	TYP	MAX	UNIT
			DCPA10505		5.0		V
$V_{OUT} \qquad \qquad$	DCPA10505D		±5.0		V		
	Output voltage	$= 100\% \text{ load}^{(2)}$	DCPA10512		5.0       ±5.0       12.0       ±12.0       ±15.0       ±15.0       ±15.0       ±0.02       10%       5%       20       4.5     5.5		V
	Oulput voltage	$I_{OUT} = 100\%$ load ( )	DCPA10512D				V
V			DCPA10515		15.0		V
VOUT			DCPA10515D		±15.0		V
	Temperature variation	$-40^{\circ}C \le T_A \le 100^{\circ}C, I_{OI}$	<sub>JT</sub> = 100% load		0.02		%/°C
		+V <sub>S</sub> (MIN) to +V <sub>S</sub> (TYP),	I <sub>OUT</sub> = 10% load		10%		
V <sub>RIPPLE</sub>	Line regulation	+V <sub>S</sub> (TYP) to +V <sub>S</sub> (MAX), $I_{OUT}$ = 10% load			10%		
	Load regulation <sup>(3)</sup>	10% to 100% load			5%		
V <sub>RIPPLE</sub>	Output voltage ripple <sup>(4)</sup>	$C_{OUT} = 1 \ \mu F, \ I_{OUT} = 50\%$	C <sub>OUT</sub> = 1 μF, I <sub>OUT</sub> = 50%		20		$mV_{PP}$
INPUT							
+V <sub>S</sub>	Input voltage range			4.5		5.5	V
	W Undervoltage lookout	+V <sub>S</sub> increasing threshole	b			2.25	V
0100	+vs ondervoltage lockout	+V <sub>S</sub> decreasing thresho	ld	1.7	5.0 $\pm 5.0$ 12.0 $\pm 12.0$ 15.0 $\pm 15.0$ 0.02 10% 10% 20 5% 20 5.5 2.25 2.25 35 25 29 36 31	V	
			DCPA10505		35		mA
			DCPA10505D		25		mA
	Quiessiant aurrent	I = 0% lood	DCPA10512		29		mA
<b>I</b> Q		$i_{OUT} = 0\%$ 1080	DCPA10512D		36		mA
			DCPA10515		31		mA
			DCPA10515D		38		mA

See Load Regulation graphs in the Typical Characterization section for typical voltage at all load conditions. Load regulation = ( $V_{OUT}$  at 10% load –  $V_{OUT}$  at 100%)/ $V_{OUT}$  at 75% load Guaranteed by design. Not production tested. (2)

(2) (3) (4)



## **Electrical Characteristics (continued)**

 $T_A = 25^{\circ}C$ , +V<sub>S</sub> = nominal,  $C_{IN} = 2.2 \ \mu$ F,  $C_{OUT} = 1.0 \ \mu$ F, (unless otherwise noted)

	PARAMETER	TEST COM	TEST CONDITIONS		TYP	MAX	UNIT
ISOLAT	TION						
		1-second flash test,	DC	2.0 <sup>(5)(4)</sup>			kVDC
		voltage	AC	1.5 <sup>(5)</sup>			kVrms
	DN DC $2.0^{(5)(4)}$ Isolation 1-second flash test, voltage DC $2.0^{(5)(4)}$ Isolation 1-second flash test, leakage current Isolation DC   Continuous working voltage across isolation barrier DC AC 4   MANCE AC 4   Isolation DC AC 4   MANCE VISO = 750 Vrms 28   Isolation DCPA10505 85%   DCPA10505 85%   DCPA10505 85%   DCPA10512 87%   DCPA10515 86%   DCPA10515 86%   DCPA10515 86%   DCPA10515 86%   DCPA10515 2.0%   DCPA10515 2.0%	30	μA				
V <sub>ISO</sub>	Isolation	Continuous working	DC			60	VDC
		voltage across isolation	AC			42.5	VAC
		barrier	dV/dt			50	V/ms
C <sub>ISO</sub>	Barrier capacitance	V <sub>ISO</sub> = 750 Vrms			28		pF
PERFO	RMANCE						
			DCPA10505		85%		
		DC	DCPA10505D		85%		
	<b>F</b> #isianay		DCPA10512		87%		
Efficiency	100T = 100 %	DCPA10512D		88%			
		DCPA10515		86%			
			DCPA10515D		86%		
			DCPA10505		3.0%		
		50% to 100% load step	DCPA10512		1.9%		
	Transient response (4)		DCPA10515		2.0%		
	Transient response (*)		DCPA10505D		2.7%		
		50% to 100% load step	DCPA10512D		2.0%		
		per output	DCPA10515D		1.6%		
RELIAB	BILITY						
	Demonstrated	T <sub>A</sub> = 55°C			55		FITS
CAPAC	ITANCE					·	
C <sub>IN</sub>	External input capacitance	Ceramic		2.2			μF
C <sub>OUT</sub>	External output capacitance	Ceramic		0.1	1.0	200	μF
THERM	AL SHUTDOWN						
T <sub>SD</sub>	Die temperature at shutdown				168		°C
I <sub>SD</sub>	Shutdown current				3		mA

(5) See Isolation Voltage section for more information.

(6) Transient testing for dual output devices are tested with one output loaded with a 50% static load and the other output loaded with a 50% to 100% dynamic load step.

## 6.5 Switching Characteristics

at T<sub>A</sub> = +25°C, +V<sub>S</sub> = nominal, C<sub>IN</sub> = 2.2  $\mu$ F, C<sub>OUT</sub> = 1.0  $\mu$ F, (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
f <sub>OSC</sub>	Oscillator frequency	$f_{SW} = f_{OSC}/2$		850		kHz
f <sub>SYNC</sub>	Synchronization frequency range		750		1000	kHz
VIH	High-level input threshold, SYNCIN		0.7			V
V <sub>IL</sub>	Low-level input threshold, SYNCIN				0.3	V



DCPA10505, DCPA10505D DCPA10512, DCPA10512D DCPA10515, DCPA10515D ZHCSG81-APRIL 2017

## 6.6 Typical Characteristics (DCPA10505)



Texas Instruments

www.ti.com.cn

## 6.7 Typical Characteristics (DCPA10512)





DCPA10505, DCPA10505D DCPA10512, DCPA10512D DCPA10515, DCPA10515D ZHCSG81 – APRIL 2017

## 6.8 Typical Characteristics (DCPA10515)



ZHCSG81-APRIL 2017

## 6.9 Typical Characteristics (DCPA10505D)

At  $T_A = 25^{\circ}C$ ,  $+V_S =$  nominal, (unless otherwise noted)



www.ti.com.cn

10



## 6.10 Typical Characteristics (DCPA10512D)



Texas Instruments

www.ti.com.cn

## 6.11 Typical Characteristics (DCPA10515D)





## 7 Detailed Description

#### 7.1 Overview

The DCPA1 offers up to 1 W of isolated, unregulated output power from a 5-V input source with a typical efficiency of up to 87%. This efficiency is achieved through highly integrated packaging technology and the implementation of a custom power stage and control device. The DCPA1 devices are specified for operational isolation only. The circuit design uses an advanced BiCMOS and DMOS process.

## 7.2 Functional Block Diagrams



图 31. Single Output Device



图 32. Dual Output Device

#### 7.3.1 Isolation

Underwriters Laboratories, UL<sup>™</sup> defines several classes of isolation that are used in modern power supplies.

Safety extra low voltage (SELV) is defined by UL (UL1950 E199929) as a secondary circuit which is so designated and protected that under normal and single fault conditions the voltage between any two accessible parts, or between an accessible part and the equipment earthing terminal for operational isolation does not exceed steady state 42 V peak or 60  $V_{DC}$  for more than 1 second.

#### 7.3.1.1 Operation or Functional Isolation

Operational or functional isolation is defined by the use of a high-potential (hipot) test only. Typically, this isolation is defined as the use of insulated wire in the construction of the transformer as the primary isolation barrier. The hipot one-second duration test (dielectric voltage, withstand test) is a production test used to verify that the isolation barrier is functioning. Products with operational isolation should never be used as an element in a safety-isolation system.

#### 7.3.1.2 Basic or Enhanced Isolation

Basic or enhanced isolation is defined by specified creepage and clearance limits between the primary and secondary circuits of the power supply. Basic isolation is the use of an isolation barrier in addition to the insulated wire in the construction of the transformer. Input and output circuits must also be physically separated by specified distances.

#### 7.3.1.3 Continuous Voltage

For a device that has no specific safety agency approvals (operational isolation), the continuous voltage that can be applied across the part in normal operation is less than 42.4  $V_{RMS}$ , or 60  $V_{DC}$ . Ensure that both input and output voltages maintain normal SELV limits. The isolation test voltage represents a measure of immunity to transient voltages.

#### WARNING

Do not use the device as an element of a safety isolation system that exceeds the SELV limit.

If the device is expected to function correctly with more than 42.4  $V_{RMS}$  or 60  $V_{DC}$  applied continuously across the isolation barrier, then the circuitry on both sides of the barrier must be regarded as operating at an unsafe voltage, and further isolation or insulation systems must form a barrier between these circuits and any user-accessible circuitry according to safety standard requirements.

#### 7.3.1.4 Isolation Voltage

The terms *Hipot test, flash-tested, withstand voltage, proof voltage, dielectric withstand voltage,* and *isolation test voltage* all describe the same spec. The terms describe a test voltage applied for a specified time across a component designed to provide electrical isolation to verify the integrity of that isolation. TI's DCPA1 series of dc-dc converters are all 100% production tested at 1.5  $kV_{AC}$  for one second.

#### 7.3.1.5 Repeated High-Voltage Isolation Testing

Repeated high-voltage isolation testing of a barrier component can degrade the isolation capability, depending on materials, construction, and environment. The DCPA1 series of dc-dc converters have toroidal, enameled, wire isolation transformers with no additional insulation between the primary and secondary windings. While a device can be expected to withstand several times the stated test voltage, the isolation capability depends on the wire insulation. Any material, including this enamel (typically polyurethane), is susceptible to eventual chemical degradation when subject to very-high applied voltages. Therefore, strictly limit the number of high-voltage tests and repeated high-voltage isolation testing. However, if it is absolutely required, reduce the voltage by 20% from specified test voltage with a duration limit of one second per test.

**NSTRUMENTS** 

**EXAS** 



#### Feature Description (接下页)

#### 7.3.2 Power Stage

The DCPA1 series of devices uses a push-pull, center-tapped topology. The DCPA1 devices switch at 425 kHz (divide-by-2 from an 850-kHz oscillator).

#### 7.3.3 Input and Output Capacitors

For all DCPA1 designs, a minimum 2.2- $\mu$ F, low-ESR, ceramic input capacitor is required. Place the input capacitor as close as possible to the device input pins, +V<sub>S</sub> and -V<sub>S</sub>, to ensure good startup performance.

The recommended typical output capacitance for each output of any DCPA1 device is  $1.0-\mu$ F of low-ESR, ceramic capacitance. Adding additional output capacitance will aid in ripple reduction, however, any additional capacitance will also require additional input current at start-up.

#### 7.3.4 Oscillator And Watchdog Circuit

The onboard, 850-kHz oscillator generates the switching frequency via a divide-by-2 circuit. The oscillator can be synchronized to an external source, and is used to minimize system noise. A watchdog circuit checks the operation of the oscillator circuit.

#### 7.3.5 Synchronization

When more than one DC/DC converter is needed onboard, beat frequencies and other electrical interference can be generated. This interference occurs because of the small variations in switching frequencies between the DC/DC converters.

The DCPA1 series of devices overcomes this interference by allowing devices to synchronize to an external clock. The SYNC<sub>IN</sub> pin responds to the rising edge of the external clock. If the external clock is removed, the DCPA1 will return to the frequency of the internal oscillator. If unused, it is recommended to connect this pin to the input side common,  $-V_s$ .

#### 7.3.6 SW<sub>OUT</sub>

The SW<sub>OUT</sub> pin is directly connected to one winding of the transformer secondary prior to the output rectifier. It is not recommended to pull current from this pin. Do not connect capacitance directly to this pin as it will degrade performance. The SW<sub>OUT</sub> pin is not compatible with the SYNC<sub>IN</sub> pin, therefore these two pins should not be connected together.

#### 7.3.7 Soft Start

The DCPA1 series of devices includes a soft-start feature that prevents high in-rush current during power up. Once input power is applied, there is a delay of typically 10 ms before the output voltage begins to rise. Once the output voltage begins to rise, the soft start time is typically 5 ms.

#### 7.3.8 Load Regulation

The load regulation of the DCPA1 series of devices is specified at 10% to 100% load. Operation below 10% load may cause the output voltage to increase up to 40% higher than the typical output voltage. Placing a minimum 10% load will ensure the output voltage is within the range specified in the *Electrical Characteristics* table.

#### Feature Description (接下页)

#### 7.3.9 Thermal Performance

The DCPA1 family of devices have been characterized to operate over an ambient temperature range of  $-40^{\circ}$ C to  $+100^{\circ}$ C. The Safe Operating Area curve shown below in 33, represents the operating conditions of the DCPA1 devices where the maximum thermal ratings will not be exceeded. 33 shows that all DCPA1 devices can safely operate over the full ambient temperature range, without airflow, to the full current rating of the device.



图 33. Thermal Safe Operating Area

#### 7.3.9.1 Thermal Protection

The DCPA1 series of devices are protected by a thermal-shutdown circuit.

If the on-chip temperature rises above 150°C, the device shuts down. Normal operation resumes as soon as the temperature falls below 150°C. While the overtemperature condition continues, operation randomly cycles on and off. This cycling continues until the temperature is reduced.

#### 7.3.10 Current Limit

For protection against a short circuit on the output, the DCPA1 series of devices have a built in current limit protection threshold of 1.75A (typical). These devices are not intended to be used at output currents greater than the device's output current rating as shown in the *Electrical Characteristics* table. Operating at currents greater than the device's current rating, but less than current limit threshold will cause excessive stress to the internal components. For protection against a partial short circuit condition, an input fuse or output fuse is recommended.

#### 7.3.11 Construction

The basic construction of the DCPA1 series of devices is the same as standard integrated circuits. The molded package contains no substrate. The DCPA1 series of devices are constructed using an IC, rectifier diodes, and a wound magnetic toroid on a leadframe. Because the package contains no solder, the devices do not require any special printed circuit board (PCB) assembly processing. This architecture results in an isolated DC/DC converter with inherently high reliability.



## 8 Application and Implementation

#### 注

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

#### 8.1 Application Information

#### 8.1.1 Ripple Reduction

The high switching frequency of 425 kHz allows simple filtering. To reduce output voltage ripple, it is recommended that a minimum of  $1-\mu$ F capacitor be used on the  $+V_{OUT}$  pin. For dual output devices, decouple both of the outputs to the COM pin. The required 2.2- $\mu$ F, low ESR ceramic input capacitor also helps to reduce ripple and noise. See *DC-to-DC Converter Noise Reduction* (SBVA012).

#### 8.1.2 Connecting the DCPA1 in Series

Multiple DCPA1 isolated 1-W DC/DC converters can be connected in series to provide non-standard voltage rails. This configuration is possible by using the floating outputs provided by the galvanic isolation of the DCPA1 devices by connecting the  $+V_{OUT}$  from one DCPA1 to the  $-V_{OUT}$  of another as shown in B 34. The synchronization feature allows easy synchronization to prevent power-rail beat frequencies at no additional filtering cost.



图 34. Multiple DCPA1 Devices Connected in Series

The outputs of a dual-output DCPA1 device can also be connected in series to provide two times the magnitude of  $+V_{OUT}$ , as shown in  $\mathbb{R}$  35. For example, connect a dual-output, ±15-V, DCPA10515D device to provide a 30-V rail.



#### 8.1.3 Connecting the DCPA1 in Parallel

If the output power from one DCPA1 is not sufficient, it is possible to parallel the outputs of multiple DCPA1s, as shown in 🕅 36, (applies to single output devices only). The synchronization feature allows easy synchronization to prevent power-rail beat frequencies at no additional filtering cost.



图 36. Multiple DCPA1 Devices Connected in Parallel

## 8.2 Typical Application



图 37. Typical DCPA10505 Application

#### 8.2.1 Design Requirements

For this design example, use the parameters listed in 表 1 and follow the design procedures shown in *Detailed Design Procedure* section.

	PARAMETER	VALUE	UNIT
V <sub>(+VS)</sub>	Input voltage	5	V
V <sub>(+VOUT)</sub>	Output voltage	5	V
I <sub>OUT</sub>	Output current rating	200	mA
f <sub>SW</sub>	Operating frequency	425	kHz

#### 表 1. Design Example Parameters



#### 8.2.2 DCPA10505 Application Curves



#### 8.2.3 Detailed Design Procedure

#### 8.2.3.1 Input Capacitor

For all DCPA1, 5-V input voltage designs, select a 2.2-µF low-ESR ceramic input capacitor to ensure a good startup performance.

#### 8.2.3.2 Output Capacitor

For any DCPA1 design, select a 1.0-µF low-ESR ceramic output capacitor to reduce output ripple.

#### 8.2.3.3 SYNC<sub>IN</sub> Pin

In a stand-alone application, it is recommended to connect this pin to the input side common, -V<sub>S</sub>.

#### 8.2.4 PCB Design

The copper losses (resistance and inductance) can be minimized by the use of mutual ground and power planes where possible. If that is not possible, use wide traces to reduce the losses. If several devices are being powered from a common power source, a star-connected system for the traces must be deployed. Do not connect the devices in series, because that type of connection cascades the resistive losses. The position of the decoupling capacitors is important. They must be as close to the devices as possible in order to reduce losses. See the *PCB Layout* section for more details.

#### 9 Power Supply Recommendations

The DCPA1 is a switching power supply, and as such can place high peak current demands on the input supply. In order to avoid the supply falling momentarily during the fast switching pulses, ground and power planes should be used to connect the power to the input of DCPA1 device. If this connection is not possible, then the supplies must be connected in a star formation with the traces made as wide as possible.



## 10 Layout

#### 10.1 Layout Guidelines

Due to the high power density of these devices, provide ground planes on the input and output rails.

图 40 shows the schematic for a single output DCPA1 device. 图 40 illustrates a printed circuit board (PCB) layout for the schematics.

Including input power and ground planes provides a low-impedance path for the input power. For the output, the COM signal connects via a ground plane, while the connections for the positive and negative voltage outputs conduct via wide traces in order to minimize losses.

The output should be taken from the device using ground and power planes, thereby ensuring minimum losses.

The location of the decoupling capacitors in close proximity to their respective pins ensures low losses due to the effects of stray inductance, thus improving the ripple performance. This location is of particular importance to the input decoupling capacitor, because this capacitor supplies the transient current associated with the fast switching waveforms of the power drive circuits.

If the SYNC<sub>IN</sub> pin is unused, it is recommended to connect this pin to the input side common,  $-V_s$ . Allow the SW<sub>OUT</sub> pin, to remain configured as a floating pad.

#### **10.2 Layout Example**



图 40. Typical Layout



11 器件和文档支持

- 11.1 器件支持
- 11.1.1 器件命名规则

	DCPA1	05	05	(D)	(P)
Basic model number: 1-W product					
Voltage input:		i			- i
5 V					- i
Voltage output:			i		į
5 V, 12 V or 15 V					- i
Output type:				i	į
D (dual) or No Character (single)					
Package code:					i
P = 7-pin PDIP (NVA package)					
P-U = 7-pin SOP (DUA package)					

图 41. 补充订购信息

11.2 文档支持

11.2.1 相关文档

直流到直流转换器降噪 (SBVA012)

DCP01/02 系列直流/直流转换器的外部同步 (SBAA035)

优化 DCP01/02 系列直流/直流转换器的性能 (SBVA013)

#### 11.3 社区资源

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

# TI E2E<sup>™</sup> Online Community *TI's Engineer-to-Engineer (E2E) Community.* Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

**Design Support TI's Design Support** Quickly find helpful E2E forums along with design support tools and contact information for technical support.

#### 11.4 相关链接

以下表格列出了快速访问链接。范围包括技术文档、支持与社区资源、工具和软件,并且可以快速访问样片或购买 链接。

器件	器件 产品文件夹 样片与购买		技术文档	工具与软件	支持与社区	
DCPA10505	请单击此处	请单击此处	请单击此处	请单击此处	请单击此处	
DCPA10505D	请单击此处	请单击此处	请单击此处	请单击此处	请单击此处	
DCPA10512	请单击此处	请单击此处	请单击此处	请单击此处	请单击此处	
DCPA10512D	请单击此处	请单击此处	请单击此处	请单击此处	请单击此处	
DCPA10515	请单击此处	请单击此处	请单击此处	请单击此处	请单击此处	
DCPA10515D	请单击此处	请单击此处	请单击此处	请单击此处	请单击此处	

#### 表 2. 相关链接

## 11.5 商标

E2E is a trademark of Texas Instruments. Underwriters Laboratories, UL are trademarks of UL LLC. All other trademarks are the property of their respective owners.



## 11.6 静电放电警告



这些装置包含有限的内置 ESD 保护。 存储或装卸时,应将导线一起截短或将装置放置于导电泡棉中,以防止 MOS 门极遭受静电损伤。

## 11.7 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

## 12 机械、封装和可订购信息

以下页中包括机械、封装和可订购信息。这些信息是针对指定器件可提供的最新数据。这些数据会在无通知且不对 本文档进行修订的情况下发生改变。欲获得该数据表的浏览器版本,请查阅左侧的导航栏。



10-Dec-2020

## **PACKAGING INFORMATION**

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
DCPA10505DP	ACTIVE	PDIP	NVA	7	25	RoHS & Non-Green	NIPDAU	N / A for Pkg Type	-40 to 100	DCPA10505DP	Samples
DCPA10505DP-U/700	ACTIVE	SOP	DUA	7	700	RoHS & Non-Green	NIPDAU	Level-3-260C-168 HR	-40 to 100	DCPA10505DP-U	Samples
DCPA10505P	ACTIVE	PDIP	NVA	7	25	RoHS & Non-Green	NIPDAU	N / A for Pkg Type	-40 to 100	DCPA10505P	Samples
DCPA10505P-U/700	ACTIVE	SOP	DUA	7	700	RoHS & Non-Green	NIPDAU	Level-3-260C-168 HR	-40 to 100	DCPA10505P-U	Samples
DCPA10512DP	ACTIVE	PDIP	NVA	7	25	RoHS & Non-Green	NIPDAU	N / A for Pkg Type	-40 to 100	DCPA10512DP	Samples
DCPA10512DP-U/700	ACTIVE	SOP	DUA	7	700	RoHS & Non-Green	NIPDAU	Level-3-260C-168 HR	-40 to 100	DCPA10512DP-U	Samples
DCPA10512P	ACTIVE	PDIP	NVA	7	25	RoHS & Non-Green	NIPDAU	N / A for Pkg Type	-40 to 100	DCPA10512P	Samples
DCPA10512P-U/700	ACTIVE	SOP	DUA	7	700	RoHS & Non-Green	NIPDAU	Level-3-260C-168 HR	-40 to 100	DCPA10512P-U	Samples
DCPA10515DP	ACTIVE	PDIP	NVA	7	25	RoHS & Non-Green	NIPDAU	N / A for Pkg Type	-40 to 100	DCPA10515DP	Samples
DCPA10515DP-U/700	ACTIVE	SOP	DUA	7	700	RoHS & Non-Green	NIPDAU	Level-3-260C-168 HR	-40 to 100	DCPA10515DP-U	Samples
DCPA10515P	ACTIVE	PDIP	NVA	7	25	RoHS & Non-Green	NIPDAU	N / A for Pkg Type	-40 to 100	DCPA10515P	Samples
DCPA10515P-U/700	ACTIVE	SOP	DUA	7	700	RoHS & Non-Green	NIPDAU	Level-3-260C-168 HR	-40 to 100	DCPA10515P-U	Samples

<sup>(1)</sup> The marketing status values are defined as follows: **ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".



# PACKAGE OPTION ADDENDUM

10-Dec-2020

**RoHS Exempt:** TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption. **Green:** TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

<sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

<sup>(6)</sup> Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

# **MECHANICAL DATA**



- G. Pointed or rounded lead tips are preferred to ease insertion.
- L. Falls within JEDEC MS-001-AA.



## **MECHANICAL DATA**



- to be 0.005 (0,13) minimum.
- TEXAS INSTRUMENTS

www.ti.com

#### 重要声明和免责声明

Ⅱ 均以"原样"提供技术性及可靠性数据(包括数据表)、设计资源(包括参考设计)、应用或其他设计建议、网络工具、安全信息和其他资源,不保证其中不含任何瑕疵,且不做任何明示或暗示的担保,包括但不限于对适销性、适合某特定用途或不侵犯任何第三方知识产权的暗示担保。

所述资源可供专业开发人员应用TI产品进行设计使用。您将对以下行为独自承担全部责任:(1)针对您的应用选择合适的TI产品;(2)设计、 验证并测试您的应用;(3)确保您的应用满足相应标准以及任何其他安全、安保或其他要求。所述资源如有变更,恕不另行通知。TI对您使用 所述资源的授权仅限于开发资源所涉及TI产品的相关应用。除此之外不得复制或展示所述资源,也不提供其它TI或任何第三方的知识产权授权 许可。如因使用所述资源而产生任何索赔、赔偿、成本、损失及债务等,TI对此概不负责,并且您须赔偿由此对TI及其代表造成的损害。

TI所提供产品均受TI的销售条款 (http://www.ti.com.cn/zh-cn/legal/termsofsale.html) 以及ti.com.cn上或随附TI产品提供的其他可适用条款的约束。TI提供所述资源并不扩展或以其他方式更改TI 针对TI 产品所发布的可适用的担保范围或担保免责声明。

邮寄地址:上海市浦东新区世纪大道 1568 号中建大厦 32 楼,邮政编码: 200122 Copyright © 2020 德州仪器半导体技术(上海)有限公司