



### AL8862 60V 1A STEP-DOWN LED DRIVER

### Description

The DIODES<sup>™</sup> AL8862 is a step-down DC/DC converter designed to drive LEDs with a constant current. The AL8862 operates with an input supply voltage from 5V to 60V and provides an externally-adjustable output current up to 1A. Series connection of the LEDs provides identical LED currents, resulting in uniform brightness and eliminating the need for ballast resistors. The AL8862 switches at frequencies up to 1MHz. This allows the use of smaller-sized external components, hence minimizing the PCB size.

The AL8862 integrates the power switch and a high-side output current-sensing circuit. Maximum output current of the AL8862 is set via an external resistor connected between the VIN and SET input pins. Dimming is achieved by applying either a DC voltage or a PWM signal at the CTRL input pin. The soft-start time can be adjusted using an external capacitor from the CTRL pin to ground. An input voltage of 0.3V or lower at CTRL pin will shut down the power switch.

### **Pin Assignments**



### Features

- Wide Input Voltage Range: 5V to 60V
- Output Current up to 1A
- Internal 60V NDMOS Switch
- Typical 4% Output Current Accuracy
- Single Pin for On/Off and Brightness Control by DC Voltage or PWM Signal
- High-Efficiency (Up to 97%)
- LED Short-Circuit Protection
- Inherent Open-Circuit LED Protection
- Current-Sense Resistor Short-Circuit Protection
- Overtemperature Shutdown
- Up to 1MHz Switching Frequency
- SO-8EP and U-DFN3030-6 Packages Available in Green Molding Compound (No Br, Sb)
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen- and Antimony-Free. "Green" Device (Note 3)
- An Automotive-Compliant Part is Available Under Separate Datasheet (AL8862Q)

### Applications

- Commercial & industrial lightings
- Appliances interior lightings
- Architecture detail lightings
- External drivers with multiple channels and smart lightings

Notes: 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3).compliant.

2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.



### **Typical Applications Circuit**



### **Pin Descriptions**

Pin Number (SO-8EP)	Pin Number (U-DFN3030-6)	Pin Name	Function
1	4	SET	Set Nominal Output Current Pin. Connect resistor R <sub>SET</sub> from this pin to VIN to define nominal average output current.
2, 7	2, 5	GND	Ground of IC
3	—	NC	No connection
4	6	VIN	Input voltage (5V to 60V). Decouple to ground with $10\mu$ F or higher X7R ceramic capacitor close to device.
5,6	1	SW	Switch Pin. Connect inductor/freewheeling diode here, minimizing track length at this pin to reduce EMI.
8	3	CTRL	Multi-function On/Off and brightness control pin: Leave floating for normal operation. Drive to voltage below 0.3V to turn off output current Drive with DC voltage (0.4V < VSET< 2.5V) to adjust output current from 10% to 100% of IouT_NOM Drive with an analog voltage >2.6V output current will be 100% of IouT_NOM A PWM signal (Low level <0.3V, High level >2.6V, transition times less than 1µs) allows the output current to be adjusted over a wide range up to 100% Connect a capacitor from this pin to ground to increase soft-start time. (Default soft-start time = 0.1ms. Additional soft-start time is approx. 1.5ms/1nF)
EP	EP	EP	Exposed pad/TAB connects to GND and thermal mass for enhanced thermal impedance.



### **Functional Block Diagram**



### Absolute Maximum Ratings (Note 4)

Symbol	Parameter	Rating	Unit
Vin	Input Voltage	-0.3 to 65	V
Vsw, Vset	SW, SET Pin Voltage	-0.3 to 65	V
Vctrl	CTRL Pin Input Voltage	-0.3 to 6	V
T <sub>A</sub>	Operating Ambient Temperature	-40 to +105	°C
TJ	Operating Junction Temperature	-40 to +150	°C
Тѕтс	Storage Temperature Range	-65 to +150	°C
T <sub>LEAD</sub>	Lead Temperature (Soldering, 10sec)	+300	°C

Note: 4. Stresses greater than those listed under "Absolute Maximum Ratings" can cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "Recommended Operating Conditions" is not implied. Exposure to Absolute Maximum Ratings for extended periods can affect device reliability. Besides, if the voltage on CTRL Pin is higher than 5V, the device will enter the test mode for parameter test. Therefore, the voltage on CTRL Pin should keep below 5V for normal operation.



### **ESD** Ratings

Symbol	Parameter	Rating	Unit	
N	Human-Body Model (HBM)	2000		
Vesd	Charged-Device Model (CDM)	750	v	

### **Recommended Operating Conditions**

Symbol	Parameter	Min	Max	Unit
Vin	Input Voltage	5	60	V
fsw	Switching Frequency	_	1	MHz
Ιουτ	Continuous Output Current	_	1	А
VCTRL	Voltage Range for 10% to 100% DC Dimming Relative to GND	0.4	2.5	V
Vctrl_high	Voltage High for PWM Dimming Relative to GND	2.6	5	V
VCTRL_LOW	Voltage Low for PWM Dimming Relative to GND	0	0.3	V
TA	Operating Ambient Temperature	-40	+105	°C
TJ	Operating Junction Temperature	-40	+125	°C

### Thermal Information (Note 5)

Package	θ <sub>JC</sub> Thermal Resistance Junction-to-Case	θ <sub>JA</sub> Thermal Resistance Junction-to-Ambient
SO-8EP	6.4°C/W	58°C/W
U-DFN3030-6	16.5°C/W	72.7°C/W

Note: 5. Device mounted on 2"×2" FR-4 substrate PCB, 2oz copper, with minimum recommended pad layout.



## Electrical Characteristics (T<sub>A</sub> = +25°C, unless otherwise noted.)

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
SUPPLY VOL	TAGE		•			•
VIN	Input Voltage	_	5.0		60	V
lq	Quiescent Current	CTRL Pin Floating, VIN = 16V		450	_	μA
Vuvlo	Under Voltage Lockout	V <sub>IN</sub> Rising		4.8	_	V
VUVLO_HYS	UVLO Hysteresis	—	_	200	_	mV
HYSTERESTI	CCONTROL	•				
VSET	Mean Current Sense Threshold Voltage	Measured on SET Pin with Respect to V <sub>IN</sub>	96	100	104	mV
VSET_HYS	Sense Threshold Hysteresis	—	_	±13	_	%
ISET	ISET Pin Input Current	V <sub>SET</sub> = V <sub>IN</sub> -0.1	_	8	_	μA
ENABLE AND	DIMMING					
VCTRL	Voltage Range on CTRL Pin	For Analog Dimming	0.4	_	2.5	V
—	Analog Dimming Range	—	10	_	100	%
Vctrl_on	DC Voltage on CTRL Pin for Analog Dimming on	VCTRL Rising	—	0.45		V
Vctrl_off	DC Voltage on CTRL Pin for Analog Dimming off	VCTRL Falling	_	0.40		V
SWITCHING (	OPERATION					
Ron	SW Switch On Resistance	@ Isw = 100mA		0.4		Ω
ISW_LEAK	SW Switch Leakage Current	Vsw = 65V, Other Pins Floating	_	—	8	μA
tss	Soft-Start Time	$V_{IN} = 16V, C_{CTRL} = 1nF$	_	1.5	_	ms
fsw	Operating Frequency	V <sub>IN</sub> = 16V, V <sub>O</sub> = 9.6 V (3 LEDs) L = 47μH, ΔI = 0.25A (I <sub>LED</sub> = 1A)	_	250	_	kHz
f <sub>SW_MAX</sub>	Recommended Maximum Switch Frequency	_	_	_	1	MHz
ton_rec	Recommended Minimum Switch ON Time	For 4% Accuracy	_	500		ns
tPD	Internal Comparator Propagation Delay (Note 6)	Delay Time from Triggering of Current Sense Threshold to SW On/Off	_	100	_	ns
THERMAL SH	IUTDOWN					
TOTP	Over Temperature Protection	—	_	+150		°C
T <sub>OTP_HYS</sub>	Temperature Protection Hysteresis	—	_	+30	_	°C
ISW MAX	Current Limit	Peak Inductor Current	2.2	3	3.6	Α

Note: 6. Guaranteed by design.



### Typical Performance Characteristics (T<sub>A</sub> = +25°C, V<sub>IN</sub> = 16V, unless otherwise noted.)

#### Quiescent Current vs. Input Voltage



SET Threshold Voltage vs. Input Voltage







#### **Quiescent Current vs. Temperature**



SET Threshold Voltage vs. Temperature



Analog Dimming (V<sub>IN</sub> =16V, 3LEDs, 47µH, Rs=0.3Ω) LED Current vs. CTRL Pin Voltage





### **Typical Performance Characteristics** (continued) ( $T_A = +25^{\circ}C$ , $V_{IN} = 16V$ , unless otherwise noted.)



Efficiency vs. Input Voltage (Rs=0.1Ω, L=100µH)







# Efficiency vs. Input Voltage (Rs=0.15Ω, L=68µH)



LED Current vs. Input Voltage (Rs=0.3Ω, L=100µH)



#### LED Current vs. Input Voltage (Rs=0.1Ω, L=100μH)





### **Typical Performance Characteristics** (continued) ( $T_A = +25$ °C, $V_{IN} = 16V$ , unless otherwise noted.)



**Operating Frequency vs. Input Voltage** (Rs=0.1Ω, L=100µH)





**Operating Frequency vs. Input Voltage** (Rs=0.15Ω, L=68µH)



LED Current vs. Output Voltage (Rs=0.3Ω, L=100µH)







48 51 54 57 60



### Typical Performance Characteristics (continued) (T<sub>A</sub> = +25°C, V<sub>IN</sub> = 16V, unless otherwise noted.)





PWM Dimming (100Hz 50% Duty Cycle) ( $V_{LED} = 9V, R_S = 0.3\Omega, L = 47\mu H$ )









AL8862 Document number: DS40375 Rev. 5 - 2



### **Application Information**

#### AL8862 Operation

In normal operation, when normal input voltage is applied at V<sub>IN</sub>, the AL8862 internal switch will turn on. Current starts to flow through sense resistor R<sub>SET</sub>, inductor L1, and the LEDs. The current ramps up linearly, and the ramp-up rate is determined by the input voltage V<sub>IN</sub>, V<sub>OUT</sub> and the inductor L1.

This rising current produces a voltage ramp across R<sub>SET</sub>. The internal circuit of the AL8862 senses the voltage across R<sub>SET</sub> and applies a proportional voltage to the input of the internal comparator. When this voltage reaches an internally-set upper threshold, the internal switch is turned off. The inductor current continues to flow through R<sub>SET</sub>, L1, LEDs, and diode D1, and back to the supply rail; but it decays, with the rate determined by the forward voltage drop of LEDs and the diode D1.

This decaying current produces a falling voltage on R<sub>SET</sub>, which is sensed by the AL8862. A voltage proportional to the sense voltage across R<sub>SET</sub> will be applied at the input of internal comparator. When this voltage falls to the internally-set lower threshold, the internal switch is turned on again. This switch-on-and-off cycle continues to provide the average LED current set by the sense resistor R<sub>SET</sub>.

#### **LED Current Configuration**

The nominal average output current in the LED(s) is determined by the value of the external current sense resistor (R<sub>SET</sub>) connected between V<sub>IN</sub> and SET and is given by:

$$I_{OUT(NOM)} = \frac{0.1}{R_{SET}}$$

The table below gives values of nominal average output current for several preferred values of current setting resistor (R<sub>SET</sub>) in the typical application circuit shown on page 1.

Rset (Ω)	Nominal Average Output Current (mA)
0.1	1000
0.15	667
0.3	333

The above values assume that the CTRL pin is floating and at a nominal reference voltage for internal comparator. It is possible to use different values of R<sub>SET</sub> if the CTRL pin is driven by an external dimming signal.

#### Analog Dimming

Application of a DC voltage from 0.4V to 2.5V on the CTRL pin can adjust output current from 10% to 100% of I<sub>OUT\_NOM</sub> linearly, as shown in Figure 1. If the CTRL pin is brought higher than 2.5V, the LED current will clamp to 100% of I<sub>OUT\_NOM</sub>. If the CTRL voltage falls below 0.3V, the output switch will turn off.

#### **PWM Dimming**

LED current can be adjusted digitally, by applying a low frequency pulse-width-modulated (PWM) logic signal to the CTRL pin to turn the device on and off. This will produce an average output current proportional to the duty cycle of the control signal. To achieve a high resolution, the PWM frequency is recommended to be lower than 500Hz, however higher dimming frequencies can be used, at the expense of dimming dynamic range and accuracy. Typically, for a PWM frequency of 500Hz, the accuracy is better than 1% for PWM ranging from 1% to 100%.

The accuracy of the low duty cycle dimming is affected by both the PWM frequency and also the switching frequency of the AL8862. For best accuracy/resolution, the switching frequency should be increased while the PWM frequency should be reduced.

The CTRL pin is designed to be driven by both 3.3V and 5V logic levels directly from a logic output with either an open drain output or push pull output stage.



### Application Information (continued)



Figure 1. Analog Dimming Curve

#### Soft Start

The default soft-start time for the AL8862 is 0.1ms—this provides very fast turn on of the output, improving PWM dimming accuracy.

Nevertheless, adding an external capacitor from the CTRL pin to ground will provide a longer soft-start delay. This is achieved by increasing the time for the CTRL voltage rising to the turn-on threshold and by slowing down the rising rate of the control voltage at the input of hysteresis comparator. The additional soft-start time is related to the capacitance between CTRL and GND, the typical value will be 1.5ms/nF.

#### **Capacitor Selection**

A low ESR capacitor should be used for input decoupling, as the ESR of this capacitor appears in series with the supply source impedance and will lower overall efficiency. This capacitor has to supply the relatively high peak current to the coil and smooth the ripple on the input current.

The minimum capacitance needed is determined by the input power, cable's length, and peak current. 4.7~10µF is a commonly used value for most of cases. A higher value will improve performance at lower input voltages, especially when the source impedance is high. The input capacitor should be placed as close as possible to the IC.

For maximum stability overtemperature and voltage, capacitors with X7R, X5R, or better dielectrics are recommended. Capacitors with Y5V dielectrics are not suitable for decoupling in this application and should NOT be used.

#### **Diode Selection**

For maximum efficiency and performance, the freewheeling diode (D1) should be a fast, low capacitance Schottky diode with low reverse leakage current. It also provides better efficiency than silicon diodes, due to lower forward voltage and reduced recovery time.

It is important to select parts with a peak current rating above the peak coil current and a continuous current rating higher than the maximum output load current. It is very important to consider the reverse leakage current of the diode when operating above +85°C. Excess leakage current will increase power dissipation.

The higher forward voltage and overshoot due to reverse recovery time in silicon diodes will increase the peak voltage on the SW output. If a silicon diode is used, more care should be taken to ensure that the total voltage appearing on the SW pin, including supply ripple, won't exceed the specified maximum value.



### Application Information (continued)

#### Inductor Selection

Recommended inductor values for the AL8862 are in the ranges  $33\mu$ H to  $100\mu$ H. Higher inductance is recommended at higher supply voltages to minimize output current tolerance due to switching delays, which will result in increased ripple and lower efficiency. Higher inductance also results in a better line regulation. The inductor should be mounted as close to the device as possible with low resistance connections to SW pins.

The chosen coil should have saturation current higher than the peak output current and a continuous current rating above the required mean output current.

The inductor value should be chosen to maintain operating duty cycle and switch "on"/"off" times within the specified limits over the supply voltage and load current range. The following equations can be used as a guide.

SW Switch "On" time

$$t_{ON} = \frac{L\Delta I}{V_{IN} - V_{LED} - I_{LED}(R_{SET} + R_L + R_{sw})}$$

SW Switch "Off" time

$$t_{OFF} = \frac{L\Delta I}{V_{LED} + V_D + I_{LED}(R_{SET} + R_L)}$$

Where: L is the coil inductance;  $R_L$  is the coil resistance;  $R_{SET}$  is the current sense resistance;  $I_{LED}$  is the required LED current;  $\Delta I$  is the coil peakpeak ripple current (Internally set to 0.26 x  $I_{LED}$ );  $V_{IN}$  is the supply voltage;  $V_{LED}$  is the total LED forward voltage;  $R_{SW}$  is the switch resistance (0.55 $\Omega$  nominal);  $V_D$  is the diode forward voltage at the required load current.

#### **Thermal Protection**

The AL8862 includes Overtemperature Protection (OTP) circuitry that will turn off the device if its junction temperature gets too high. This is to protect the device from excessive heat damage. The OTP circuitry includes thermal hysteresis that will cause the device to restart normal operation once its junction temperature has cooled down by approximately +30°C.

#### **Open-Circuit LED Protection**

The AL8862 has, by default, open LED protection. If the LEDs should become open circuit, the AL8862 will stop oscillating; the SET pin will rise to  $V_{IN}$ , and the SW pin will then fall to GND. No excessive voltages will be seen by the AL8862.

#### **LED Short-Circuit Protection**

If the LED string becomes shorted together (the anode of the top LED becomes shorted to the cathode of the bottom LED), the AL8862 will continue to switch and the current through the AL8862's internal switch will still be at the expected current. Thus, no excessive heat will be generated within the AL8862. However, the duty cycle at which it operates will change dramatically and the switching frequency will most likely decrease. See Figure 2 for an example of this behavior at 24V input voltage driving 3 LEDs.

The on-time of the internal power MOSFET switch is significantly reduced because almost all of the input voltage is now developed across the inductor. The off-time is significantly increased because the reverse voltage across the inductor is now just the Schottky diode voltage (See Figure 2), causing a much slower decay in inductor current.



### Application Information (continued)



Figure 2. Switching Characteristics (Normal Operation to LED String Shorted)

#### **Current Sense Resistor Short-Circuit Protection**

The AL8862 has an internal current limit at about 3A. If the current-sense resistor RSET is shorted out, the AL8862 will operate at maximum duty cycle of 100%. See Figure 3, the inductor current keeps going up until the internal 3A current limit is reached, and then the AL8862 enters hiccup mode. When the current limit is reached, SW is turned off with inductor current going down, and SW is turned on again after 55us. Then inductor current goes up until 3A current limit is reached, and the cycle repeats. If the current limit is reached for accumulated 8 times, the AL8862 is latched off. Only a power cycle of VIN can reset the AL8862.



Figure 3. System Start up with Sense Resistor Short-circuit



### **Ordering Information**



Dert Number	Dart Number Deckare Code Deckare		Pac	king
Part Number	Package Code	Package	Qty.	Carrier
AL8862SP-13	SP	SO-8EP	2500	13" Tape & Reel
AL8862FF-7	FF	U-DFN3030-6	1500	7" Tape & Reel

### Marking Information

1) SO-8EP



2) U-DFN3030-6



Part Number	Package	Identification Code
AL8862FF-7	U-DFN3030-6	P5



### **Package Outline Dimensions**

Please see http://www.diodes.com/package-outlines.html for the latest version.

#### Package Type 1:



	SO-8	BEP	
Dim	Min	Max	Тур
Α	1.40	1.50	1.45
A1	0.00	0.13	1
b	0.30	0.50	0.40
с	0.15	0.25	0.20
D	4.85	4.95	4.90
ш	3.80	3.90	3.85
E0	3.85	3.95	3.90
E1	5.90	6.10	6.00
e	-	1	1.27
F	2.75	3.35	3.05
H	2.11	2.71	2.41
L	0.62	0.82	0.72
N	-	-	0.35
q	0.60	0.70	0.65
All Di	mensi	ons in	mm

#### Package Type 2:



	U-DFN3030-6				
Dim	Min	Max	Тур		
Α	0.57	0.63	0.60		
A1	0	0.05	0.02		
A3	-	-	0.15		
b	0.35	0.45	0.40		
D	2.95	3.05	3.00		
D2	2.25	2.45	2.35		
Ε	2.95	3.05	3.00		
E2	1.48	1.68	1.58		
е	-	-	0.95		
L	0.35	0.45	0.40		
Ζ	-	-	0.35		
All	Dimen	sions ir	n mm		

#### U-DFN3030-6



### **Suggested Pad Layout**

Please see http://www.diodes.com/package-outlines.html for the latest version.

#### Package Type 1:



SO-8EP

Dimensions	Value (in mm)
С	1.270
Х	0.802
X1	3.502
X2	4.612
Y	1.505
Y1	2.613
Y2	6.500

Package Type 2:



# U-DFN3030-6

Dimensions	Value (in mm)
С	0.950
Х	0.500
X1	2.400
X2	2.550
Y	0.600
Y1	1.780
Y2	3.300

### **Mechanical Data**

#### SO-8EP

- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Annealed over Copper Leadframe. Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.075 grams (Approximate)

#### U-DFN3030-6

- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish NiPdAu. Solderable per MIL-STD-202, Method 208 @
- Weight: 0.016 grams (Approximate)



#### IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

Diodes' products provided subject Diodes' Standard Terms and of are to Conditions Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at <a href="https://www.diodes.com/about/company/terms-and-conditions/important-notice">https://www.diodes.com/about/company/terms-and-conditions/important-notice</a>

DIODES is a trademark of Diodes Incorporated in the United States and other countries. The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. © 2022 Diodes Incorporated. All Rights Reserved.

#### www.diodes.com