

PT7M7803/7809-7812/7823-7825

µP Supervisor Circuits

PERICOM

Features

- ➔ Precision supply-voltage monitor
 - 4.63V (PT7M78xxL)
 - 4.38V (PT7M78xxM)
 - 3.08V (PT7M78xxT)
 - 2.93V (PT7M78xxS)
 - 2.63V (PT7M78xxR)
 - 2.32V (PT7M78xxZ)
 - 2.20V (PT7M78xxY)
 - 4.00V (PT7M78xxJ)
 - 2.25V (PT7M78xxK)
 - 2.80V (PT7M78xxG)
- ➔ 200ms reset pulse width
- Debounced CMOS-compatible manual-reset input (7811, 7812, 7823, 7825)
- ➔ Reset Output Signal for Watchdog and Power Abnormal, Manual Reset
- ➔ Reset Push-Pull output (PT7M7809,7811,7823, 7824,7825)
- → Reset Open-Drain output (PT7M7803)
- ➔ Voltage monitor for power-fail or low battery warning
- → Guaranteed $\overline{\text{RESET}}/\text{RESET}$ valid at V_{CC} =1.0V

Description

The PT7M78xx family microprocessor (μ P) supervisory circuits are targeted to improve reliability and accuracy of power-supply circuitry in μ P systems. These devices reduce the complexity and number of components required to monitor power-supply and battery functions.

The main functions are:

- 1. Asserting reset output during power-up, powerdown and brownout conditions for μP system.
- 2. Watchdog functions
- 3. Manual reset.

Applications

- → Power-supply circuitry in μ P systems
- ➔ Networking
- ➔ Security System
- ➔ Server/Storage
- ➔ Embedded System

Function Comparison Table

Part No.		RESE	T output	RESET output	Manual Reset	Watchdog
	i uit i to.	Push-Pull Open-Drain		(push-pull)	Input	Input
1	PT7M7803	-		-	-	-
2	PT7M7809	\checkmark	-	-	-	-
3	PT7M7810	-	-	\checkmark	-	-
4	PT7M7811	\checkmark	-	-	\checkmark	-
5	PT7M7812	-	-	\checkmark	\checkmark	-
6	PT7M7823	\checkmark	-	-	\checkmark	
7	PT7M7824		-		-	
8	PT7M7825	\checkmark	-			-





PT7M7803/7809-7812/7823-7825

Pin Configuration



Pin Description





Pin	Туре	Description
MR	Ι	Manual-Reset: (CMOS). Active low. Pull low to force a reset. Reset remains asserted for the duration of the Reset Timeout Period after MR transitions from low to high. Leave unconnected or connected to VCC if not used.
VCC	Power	Supply Voltage. Reset is asserted when V_{CC} drops below the Reset Threshold Voltage (V_{RST}). Reset remains asserted until V_{CC} rises above V_{RST} and keep asserted for the duration of the Reset Timeout Period (t_{RS}) once V_{CC} rises above V_{RST} .
GND	-	Ground Reference for all signals.
WDI	Ι	Watchdog Input (CMOS). If WDI remains high or low for the duration of the watchdog timeout period (t _{WD}), the internal watchdog timer trigger a reset output. Floating WDI or connecting WDI to a high-impedance three-state buffer disables the watchdog feature. The internal watchdog timer clears whenever reset is asserted or WDI occurs a rising or falling edge.
RESET	О	Active-Low Reset Output (Push-Pull or Open-Drain). It goes low when Vcc is below the reset threshold. It remains low for about 200ms after one of the following occurs: Vcc rises above the reset threshold (VRST), the watchdog triggers a reset, or MR goes from low to high.
RESET	0	The inverse of RESET , active high. Whenever RESET is high, RESET is low.
NC	-	No connection.

Block Diagram







PT7M7803/7809-7812/7823-7825



Maximum Ratings

Storage Temperature65°C to +150°C
Ambient Temperature with Power Applied40°C to +85°C
Supply Voltage to Ground Potential (Vcc to GND)0.3V to +7.0V
DC Input Voltage (All inputs except Vcc and GND)0.3V to V _{CC} +0.3V
Open-drain RESET0.3V to +7.0V
DC Output Current (All outputs)
Power Dissipation

Note:

Stresses greater than those listed under MAXIMUM RATINGS may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.

Recommended Operation Conditions

Sym	Description	Test Conditions	Min.	Тур.	Max.	Unit
	Supply Voltage for 78xxL/M/J	-	4.5	5.0	5.5	V
V _{CC}	Supply Voltage for 78xxT/S	-	3.0	3.3	5.5	V
	Supply Voltage for 78xxR/Z/Y/K/G	-	2.7	3.0	5.5	V
V _{IH}	Input High Voltage (WDI, MR)	-	0.7V _{CC}	-	V _{CC}	V
▼ IH	Input High Voltage for Open-drain RESET		0		5.5	V
V _{IL}	Input Low Voltage	-	-	-	0.3V _{CC}	V
T _A	Operating Temperature	-	-40	-	85	С

All trademarks are property of their respective owners. 2017-04-0010





PT7M7803/7809-7812/7823-7825

DC Electrical Characteristics

 $(V_{CC} = V_{RN} + 5\%$ to 5.5V, T_A = -40~85 °C, unless otherwise noted.)(Note 1)

Symbol Description		Test Conditions	Min.	Typ.	Max.	Unit		
V _{CC}	Operating Voltage Range	-		1.0	-	5.5	V	
I _{CC}	Supply Current	Vcc = 5V, No	7803/09/10/11/12	-	10	30	μΑ	
ICC		load	7823/24/25	-	13	36		
V _{IH}	Input High Voltage	Pin: MR, WDI		$0.7 V_{CC}$	-	V _{CC}	V	
V _{IL}	Input Low Voltage	Pin: MR, WDI		-	-	0.3V _{CC}	V	
	Threshold Voltage(Falling-	$\begin{array}{c} T_A = 25 \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $		V _{RN} - 1.5%	V _{RN}	V _{RN} +1.5%		
V _{RST}	edge)(Note 2)			V _{RN} - 2.5%	V _{RN}	V _{RN} + 2.5%	V	
		X7	7823/24/25L/M	-	12	-		
V _{RTH}	Reset Threshold Hysteresis (Note 2)	Vcc varies between	7823/24/25 T/S/R/K/Z/Y	-	4	-	mV	
		$V_{RN} \pm 5\%$	Others	-	50	-	1	
		$Vcc \ge 4.5V$ Isou	Vcc-1.5	-	-	V		
	Output High Voltage(Except 7823/24/25) Output High Voltage(7823/24/25)	$Vcc \ge 2.7V$ Isou	0.8×Vcc	-	-			
		$Vcc \ge 1.8V$ Iso	0.8×Vcc	-	-			
V _{OH}		$Vcc \ge 1.0V$ Iso	0.8×Vcc	-	-			
		7823/24/25L/M, Isource=120 μA	Vcc-1.5	-	-	V		
		7823/24/25T/S/F Isource=30µA	0.8×Vcc	-	-	V		
		$Vcc \ge 4.5V$ Isin	-	-	0.4	v		
V _{OL}	Output Low Voltage	$Vcc \ge 2.7V$ Isin	-	-	0.3			
		$Vcc \ge 1.0V$ Isin	-	-	0.3			
I _{LKG}	Open-Drain Output Leakage Current	$V_{CC} > V_{TH(MAX)}$	for 7803	-	-	1	μΑ	
т	Average WDI Input	WDI connected	to V _{CC} : 5.5V	-	120	160		
I _{WDI}	Current (Note 3)	WDI connected to GND		-20	-15	-	μA	
T	RESET Output Short- Circuit Current (only for	PT7M782xL/M, Vcc=5.5V	-	-	800			
I _{source}	PT7M7823/24/25)	PT7M782xT/S/F Vcc=3.6V	-	-	400	- μΑ		
	MR pull-up resistor	PT7M7811/7812	2	10	20	40	1.0	
r	(internal)	PT7M7823/7824	/7825	35	52	75	kΩ	
	1	1			1	·		

Note: 1. Parameters of room temperature guaranteed by production test and parameters of full-temperature guaranteed by design. 2. Valid for both RESET and RESET. V_{RST} (V_{RTH}-) is the Reset threshold voltage when V_{CC} from high to low level, and V_{RTH}+ is the Reset threshold

voltage when V_{CC} from low to high level. V_{RN} is nominal reset threshold voltage.

3. WDI is internally serviced within the watchdog period if WDI is left unconnected.





PT7M7803/7809-7812/7823-7825

AC Electrical Characteristics

Symbol	Description	Test Conditions	Min.	Тур.	Max.	Unit
t _{RS}	Reset Pulse Width	MR from low to High.	140	200	400	ms
t _{WD}	Watchdog Timeout Period	WDI, \overline{MR} tied to Vcc, Vcc>V _{RN} +5%.	1.12	1.6	2.25	s
t _{MR}	MR Pulse Width	-	200	-	-	ns
t _{MD}	MR to RESET Delay	Vcc=5V	-	-	250	ns
t _{WP}	WDI Pulse Width	-	150	-	-	ns

Watchdog Timing Diagram







PT7M7803/7809-7812/7823-7825

Functional Description

Reset Output

A microprocessor (μP) reset input starts the μP in a known state. Whenever the μP is in an unknown state, it should be held in reset. The supervisory circuits assert reset during power-up and prevent code execution errors during power-down or brownout conditions.

On power-up, once Vcc reaches about 1.0V, RESET is a guaranteed logic low of 0.4V or less. As Vcc rises, RESET stays low. When Vcc rises above the reset threshold, an internal timer releases RESET after about 200ms. RESET pulses low whenever Vcc drops below the reset threshold, i.e. brownout condition. If brownout occurs in the middle of a previously initiated reset pulse, the pulse continues for at least another 200ms. On power-down, once Vcc falls below the reset threshold, RESET stays low and is guaranteed to be 0.4V or less until Vcc drops below 1.0V. Watchdog Timing Diagram shows the timing relationship.

The active-high RESET output is simply the inverse of the $\overline{\text{RESET}}$ output, and is guaranteed to be valid with Vcc down to 1.0V.

Watchdog Timer

The PT7M78xx watchdog circuit monitors the μ P activity. If the μ P does not toggle the watch-dog input (WDI) within 1.6s, reset asserts. As long as reset is asserted or the WDI input is toggled, the watchdog timer will stay clear and will not count. As soon as reset is released, the timer will start counting. WDI input pulses as short as 150ns can be detected. Disable the watchdog function by leaving WDI unconnected or by three-stating driver connected to WDI. Do not apply voltage level on DCI over Vcc.

Manual Reset

The manual-reset input (\overline{MR}) allows reset to be triggered by a push button switch. \overline{MR} has an internal pullup resistor, so it can be left open when not used. Do not apply voltage level over Vcc.

Typical Application Circuit





All trademarks are property of their respective owners. 2017-04-0010





PT7M7803/7809-7812/7823-7825









All trademarks are property of their respective owners. 2017-04-0010





Mechanical Information

T (SOT23)







PT7M7803/7809-7812/7823-7825

C (SC70)







PT7M7803/7809-7812/7823-7825

TA (SOT23)







PT7M7803/7809-7812/7823-7825

TB (SOT143)







Note: For latest package info, please check: http://www.pericom.com/support/packaging/packaging-mechanicals-and-thermal-characteristics/

Ordering Information

Part Number	Package Code	Package
PT7M7803XTEX	Т	3-Pin, Small Outline Transistor Plastic (SOT23), Tape & Reel
PT7M7809XTEX	Т	3-Pin, Small Outline Transistor Plastic (SOT23), Tape & Reel
PT7M7810XTEX	Т	3-Pin, Small Outline Transistor Plastic (SOT23), Tape & Reel
PT7M7803XC3EX	C3	3-Pin, SOT323 (SC70), Tape & Reel
PT7M7809XC3EX	C3	3-Pin, SOT323 (SC70), Tape & Reel
PT7M7810XC3EX	C3	3-Pin, SOT323 (SC70), Tape & Reel
PT7M7811XTAEX	TA	5-Pin, Small Outline Transistor Plastic Package (SOT23), Tape & Reel
PT7M7812XTAEX	TA	5-Pin, Small Outline Transistor Plastic Package (SOT23), Tape & Reel
PT7M7823XTAEX	TA	5-Pin, Small Outline Transistor Plastic Package (SOT23), Tape & Reel
PT7M7824XTAEX	TA	5-Pin, Small Outline Transistor Plastic Package (SOT23), Tape & Reel
PT7M7825XTAEX	TA	5-Pin, Small Outline Transistor Plastic Package (SOT23), Tape & Reel
PT7M7811XTBEX	TB	4-Pin (SOT143), Tape & Reel
PT7M7812XTBEX	TB	4-Pin (SOT143), Tape & Reel
*PT7M7809XUWF	UWF	Wafer form

Note:

• Thermal characteristics can be found on the company web site at www.pericom.com/packaging/

• E = Pb-free and Green

• Adding X Suffix= Tape/Reel

• "*" for UWF package, please check the storage with related sales.

Suffix: X—Monitored Voltage

X	L	Μ	Т	S	R	Z	Y	J	K	G
Reset Threshold (V)	4.63	4.38	3.08	2.93	2.63	2.32	2.20	4.00	2.25	2.80





PT7M7803/7809-7812/7823-7825

Marking Information



Code	Description
12	Part Number
3	Year
4	Work Week
•	Only for PT7M7809M

Part Number Code

Code 1 2	Part No						
AA	PT7M7809L	AO	PT7M7811L	BC	PT7M7803L	BQ	PT7M7824L
AB	PT7M7809M	AP	PT7M7811M	BD	PT7M7803M	BR	PT7M7824M
AC	PT7M7809T	AQ	PT7M7811T	BE	PT7M7803T	BS	PT7M7824T
AD	PT7M7809S	AR	PT7M7811S	BF	PT7M7803S	BT	PT7M7824S
AE	PT7M7809R	AS	PT7M7811R	BG	PT7M7803R	BU	PT7M7824R
AF	PT7M7809Z	AT	PT7M7811Z	BH	PT7M7803Z	BV	PT7M7824Z
AG	PT7M7809Y	AU	PT7M7811Y	BI	PT7M7803Y	BW	PT7M7824Y
jm	PT7M7809J	sf	PT7M7811J	sc	PT7M7803J	si	PT7M7824J
pE	PT7M7809G					mQ	PT7M7824K
AH	PT7M7810L	AV	PT7M7812L	BJ	PT7M7823L	BX	PT7M7825L
AI	PT7M7810M	AW	PT7M7812M	BK	PT7M7823M	BY	PT7M7825M
AJ	PT7M7810T	AX	PT7M7812T	BL	PT7M7823T	BZ	PT7M7825T
AK	PT7M7810S	AY	PT7M7812S	BM	PT7M7823S	CA	PT7M7825S
AL	PT7M7810R	AZ	PT7M7812R	BN	PT7M7823R	CB	PT7M7825R
AM	PT7M7810Z	BA	PT7M7812Z	BO	PT7M7823Z	CC	PT7M7825Z
AN	PT7M7810Y	BB	PT7M7812Y	BP	PT7M7823Y	CD	PT7M7825Y
se	PT7M7810J	sg	PT7M7812J	sh	PT7M7823J	sj	PT7M7825J
				mP	PT7M7823K		



PERICOM

IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or

2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2016, Diodes Incorporated

www.diodes.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated:

 PT7M7812RTBEX
 PT7M7809MTEX
 PT7M7809TTEX-1507
 PT7M7809TTEX-1612
 PT7M7809ZTEX-1507

 PT7M7810MTEX
 PT7M7810STEX-1507
 PT7M7811TTBEX-1516
 PT7M7811TTBEX-1612
 PT7M7812LTBEX

 PT7M7812MTBEX
 PT7M7810STEX-1507
 PT7M7803SC3EX-2017
 PT7M7803STEX-2017
 PT7M7809JTEX-2017

 PT7M7809MTEX-2017
 PT7M7809RTEX-2017
 PT7M7809STEX-2017
 PT7M7823TTAEX-2017
 PT7M7825STAEX-2017

 PT7M7811RTBEX-2017
 PT7M7811STAEX-2017
 PT7M7810STEX-2017
 PT7M7810TTBEX-2017
 PT7M7810TTBEX-2017

 PT7M7823RTAEX-2017
 PT7M7810RTEX-2017
 PT7M7810RTEX-2017
 PT7M7810STEX-2017
 PT7M7810RTEX-2017

 2017
 PT7M7810MTEX-2017
 PT7M7810RTEX-2017
 PT7M7810STEX-2017
 PT7M7810RTEX-2017