

## 1A, 200 kHz Buck Regulator

### Features

- Fixed 200 kHz Operation
- 3.3V, 5V, and Adjustable Output Versions
- Voltage over Specified Line and Load Conditions:
  - Fixed Version:  $\pm 3\%$  Max. Output Voltage
  - Adjustable Version:  $\pm 2\%$  Max. Feedback Voltage
- Guaranteed 1A Switch Current
- Wide 4V to 24V Input Voltage Range
- Wide 1.23V to 20V Output Voltage Range
- Requires Minimum External Components
- <200  $\mu$ A Typical Shutdown Mode
- 75% Efficiency (Adjustable Version >75% typ.)
- Standard Inductors and Capacitors are 25% of Typical LM2575 Values
- Thermal Shutdown
- Overcurrent Protection
- 100% Electrical Thermal Limit Burn-In

### Applications

- Simple High-Efficiency Step-Down (Buck) Regulator
- Efficient Pre-Regulator for Linear Regulators
- On-Card Switching Regulators
- Positive-to-Negative Converter (Inverting Buck-Boost)
- Battery Charger
- Negative Boost Converter
- Step-Down 6V to 3.3V for Intel Pentium and Similar Microprocessors

### General Description

The MIC4575 is a series of easy to use fixed and adjustable BiCMOS step-down (buck) switch-mode voltage regulators. The 200 kHz MIC4575 duplicates the pinout and function of the 52 kHz LM2575. The higher switching frequency may allow up to a 2:1 reduction in output filter inductor size.

The MIC4575 is available in 3.3V and 5V fixed output versions or a 1.23V to 20V adjustable output version. Both versions are capable of driving a 1A load with excellent line and load regulation.


The feedback voltage is guaranteed to  $\pm 2\%$  tolerance for adjustable versions, and the output voltage is guaranteed to  $\pm 3\%$  for fixed versions, within specified voltages and load conditions. The oscillator frequency is guaranteed to  $\pm 10\%$ .

In shutdown mode, the regulator draws less than 200  $\mu$ A standby current. The regulator performs cycle-by-cycle current limiting and thermal shutdown for protection under fault conditions.

This series of simple switch-mode regulators requires a minimum number of external components and can operate using a standard series of inductors. Frequency compensation is provided internally.


The MIC4575 is available in TO-220 (T) and DDPAK (U) packages for the industrial temperature range.

### Package Types




# MIC4575

## Typical Application Circuits



## Functional Block Diagrams



## 1.0 ELECTRICAL CHARACTERISTICS

### Absolute Maximum Ratings †

Supply Voltage ( $V_{IN}$ , Note 1)	.....	+40V
Shutdown Voltage ( $V_{SHDN}$ )	.....	-0.3V to +36V
Output Switch ( $V_{SW}$ , Steady State)	.....	-1V
Storage Temperature	.....	-65°C to +150°C
ESD Rating	.....	Note 2

### Operating Ratings ‡‡

Supply Voltage ( $V_{IN}$ )	.....	+24V
Junction Temperature ( $T_J$ )	.....	+150°C
Package Thermal Resistance		
TO-220, DDPAK ( $\theta_{JA}$ )	.....	65°C/W
TO-220, DDPAK ( $\theta_{JC}$ )	.....	2°C/W

**† Notice:** Stresses above those listed under “Absolute Maximum Ratings” may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational sections of this specification is not intended. Exposure to maximum rating conditions for extended periods may affect device reliability.

**‡‡ Notice:** The device is not guaranteed to function outside its operating ratings.

**Note 1:** The MIC4575 is not guaranteed to survive a short-circuit to ground for input voltages above 24V.

**2:** Device is ESD sensitive. Handling precautions recommended.

# MIC4575

---

## ELECTRICAL CHARACTERISTICS

**Electrical Characteristics:**  $V_{IN} = 12V$ ;  $I_{LOAD} = 200\text{ mA}$ ;  $T_A = +25^\circ\text{C}$ , **bold** values indicate  $-40^\circ\text{C} \leq T_A \leq +85^\circ\text{C}$ ; unless noted. [Note 1](#)

Parameter	Sym.	Min.	Typ.	Max.	Units	Conditions
<b>MIC4575 (Adjustable)</b>						
Feedback Voltage	$V_{FB}$	1.217	1.230	1.243	V	—
Feedback Voltage	$V_{FB}$	1.193	1.230	1.267	V	$8V \leq V_{IN} \leq 24V, 0.2A \leq I_{LOAD} \leq 1A$
		<b>1.180</b>	—	<b>1.280</b>		
Efficiency		—	77	—	%	$I_{LOAD} = 1A, V_{OUT} = 5V$
Feedback Bias Current	$I_{BIAS}$	—	50	100	nA	—
		—	—	<b>500</b>		
<b>MIC4575-3.3</b>						
Output Voltage	$V_{OUT}$	3.234	3.3	3.366	V	—
Output Voltage	$V_{OUT}$	3.168	3.3	3.432	V	$6V \leq V_{IN} \leq 24V, 0.2A \leq I_{LOAD} \leq 1A$
		<b>3.135</b>	—	<b>3.465</b>		
Efficiency		—	72	—	%	$I_{LOAD} = 1A$
<b>MIC4575-5.0</b>						
Output Voltage	$V_{OUT}$	4.9	5.0	5.1	V	—
Output Voltage	$V_{OUT}$	4.8	5.0	5.2	V	$8V \leq V_{IN} \leq 24V, 0.1A \leq I_{LOAD} \leq 0.5A$
		<b>4.75</b>	—	<b>5.25</b>		
Efficiency		—	77	—	%	$I_{LOAD} = 1A$
<b>MIC4575/-3.3/-5.0</b>						
Oscillator Frequency	$f_O$	180	200	220	kHz	—
Saturation Voltage	$V_{SAT}$	—	1	1.3	V	$I_{OUT} = 1A$
		—	—	<b>1.5</b>		
Maximum Duty Cycle (On)	$D_{MAX}$	90	95	—	%	FB connected to 0V
Current Limit	$I_{LIM}$	1.7	2.2	3.0	A	Peak Current, $t_{ON} \leq 3\text{ }\mu\text{s}$
		<b>1.3</b>	—	<b>3.2</b>		
Output Leakage Current	$I_{OUT}$	—	0	2	mA	Output = 0V, $V_{IN} = 24V$ , FB connected to 0V
		—	7.5	35		Output = -1V, $V_{IN} = 24V$ , FB connected to 0V
Quiescent Current	$I_Q$	—	5	10	mA	—
Standby Quiescent Current	$I_{Q(STBY)}$	—	50	200	$\mu\text{A}$	SHDN = 5V (regulator off)
SHDN Input Logic Level		2.2	1.4	—	V	$V_{OUT} = 0V$ (regulator off)
		<b>2.4</b>	—	—		
		—	1.2	1.0	V	$V_{OUT} = 3.3V$ or $5V$ (regulator on)
		—	—	<b>0.8</b>		
SHDN Input Current		—	4	30	$\mu\text{A}$	SHDN = 5V (regulator off)
		-10	0.01	10		SHDN = 0V (regulator on)

**Note 1:** Specification for packaged product only.

**TEMPERATURE SPECIFICATIONS**

Parameters	Sym.	Min.	Typ.	Max.	Units	Conditions
<b>Temperature Ranges</b>						
Junction Temperature	T <sub>J</sub>	—	—	+150	°C	—
Storage Temperature Range	T <sub>S</sub>	-65	—	+150	°C	—
<b>Package Thermal Resistances</b>						
Thermal Resistance, TO-220, TO-263	θ <sub>JA</sub>	—	65	—	°C/W	—
Thermal Resistance, TO-220, TO-263	θ <sub>JC</sub>	—	2	—	°C/W	—

**Note 1:** The maximum allowable power dissipation is a function of ambient temperature, the maximum allowable junction temperature and the thermal resistance from junction to air (i.e., T<sub>A</sub>, T<sub>J</sub>, θ<sub>JA</sub>). Exceeding the maximum allowable power dissipation will cause the device operating junction temperature to exceed the maximum +125°C rating. Sustained junction temperatures above +125°C can impact the device reliability.

# MIC4575

---

---

## 2.0 PIN DESCRIPTIONS

The descriptions of the pins are listed in [Table 2-1](#).

**TABLE 2-1: PIN FUNCTION TABLE**

Pin Number	Pin Name	Description
1	IN	Supply Voltage (Input): Unregulated +4V to +40V supply voltage.
2	SW	Switch (Output): Emitter of NPN output switch. Connect to external storage inductor and Schottky diode.
3, TAB	GND	Ground.
4	FB	Feedback (Input): Output voltage feedback to regulator. Connect to output of supply for fixed versions. Connect to 1.23V tap of resistive divider for adjustable versions.
5	SHDN	Shutdown (Input): Logic low enables regulator. Logic high (> 2.4V) shuts down regulator.

## 3.0 FUNCTIONAL DESCRIPTION

The MIC4575 is a variable duty cycle switch-mode regulator with an internal power switch. Refer to the [Functional Block Diagrams](#).

### 3.1 Supply Voltage

The MIC4575 operates from a +4V to +24V unregulated input. Highest efficiency operation is from a supply voltage below +15V.

### 3.2 Enable/Shutdown

The shutdown (SHDN) input is TTL-compatible. Ground the input if unused. A logic low enables the regulator. A logic high shuts down the internal regulator, which reduces the current to typically 50  $\mu$ A.

### 3.3 Feedback

Fixed versions of the regulator have an internal resistive divider from the feedback (FB) pin. Connect FB directly to the output line.

Adjustable versions require an external resistive voltage divider from the output voltage to ground, connected from the 1.23V tap to FB.

### 3.4 Duty Cycle Control

A fixed-gain error amplifier compares the feedback signal with a 1.23V bandgap voltage reference. The resulting error amplifier output voltage is compared to a 200 kHz sawtooth waveform to produce a voltage controlled variable duty cycle output.

A higher feedback voltage increases the error amplifier output voltage. A higher error amplifier voltage (comparator inverting input) causes the comparator to detect only the peaks of the sawtooth, reducing the duty cycle of the comparator output. A lower feedback voltage increases the duty cycle.

### 3.5 Output Switching

When the internal switch is on, an increasing current flows from the supply  $V_{IN}$ , through external storage inductor L1, to output capacitor  $C_{OUT}$  and the load. Energy is stored in the inductor as the current increases with time.

When the internal switch is turned off, the collapse of the magnetic field in L1 forces current to flow through fast recovery diode D1, charging  $C_{OUT}$ .

### 3.6 Output Capacitor

External output capacitor  $C_{OUT}$  provides stabilization and reduces ripple.

### 3.7 Return Paths


During the on portion of the cycle, the output capacitor and load currents return to the supply ground. During the off portion of the cycle, current is being supplied to the output capacitor and load by storage inductor L1, which means that D1 is part of the high-current return path.

# MIC4575


## 4.0 APPLICATION INFORMATION

The applications circuits that follow have been constructed and tested. Refer to AN 15, *Practical Switching Regulator Circuits*, for additional information, including efficiency graphs and manufacturer's addresses and telephone numbers for most circuits.


For a mathematical approach to component selection and circuit design, refer to AN 14, 200 kHz MIC4574/5/6 Family Design Guide.




**FIGURE 4-1:** 16V<sub>IN</sub> - 24V<sub>IN</sub> to 12V/0.5A Buck Converter Through Hole.




**FIGURE 4-2:** 6V<sub>IN</sub> - 24V<sub>IN</sub> to 3.3V/1A Buck Converter Low-Profile Surface Mount.




**FIGURE 4-3:** 8V<sub>IN</sub> - 24V<sub>IN</sub> to 5V/1A Buck Converter Low-Profile Surface Mount.




**FIGURE 4-4:** 16V<sub>IN</sub> - 24V<sub>IN</sub> to 12V/1A Buck Converter Low-Profile Surface Mount.



**FIGURE 4-5:** 6V<sub>IN</sub> - 24V<sub>IN</sub> to 3.3V/1A Buck Converter Surface Mount.



**FIGURE 4-6:** 8V<sub>IN</sub> - 24V<sub>IN</sub> to 5V/1A Buck Converter Surface Mount.



**FIGURE 4-7:** 16V<sub>IN</sub> - 24V<sub>IN</sub> to 12V/1A Buck Converter Surface Mount.




FIGURE 4-8: Split ±5V Supply.


## 5.0 PACKAGING INFORMATION

### 5.1 Package Marking Information


5-Lead TO-220\*




Example



5-Lead DDPAK\*



Example




<b>Legend:</b>	XX...X Product code or customer-specific information Y Year code (last digit of calendar year) YY Year code (last 2 digits of calendar year) WW Week code (week of January 1 is week '01') NNN Alphanumeric traceability code  Pb-free JEDEC® designator for Matte Tin (Sn) * This package is Pb-free. The Pb-free JEDEC designator  can be found on the outer packaging for this package. •, ▲, ▼ Pin one index is identified by a dot, delta up, or delta down (triangle mark).
<b>Note:</b>	In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for customer-specific information. Package may or may not include the corporate logo. Underbar (_) and/or Overbar (˜) symbol may not be to scale.

## 5-Lead TO-220 Package Outline &amp; Recommended Land Pattern

**TITLE**

5 LEAD TO220 PACKAGE OUTLINE &amp; RECOMMENDED LAND PATTERN

DRAWING #	TO220-5LD-PL-1	UNIT	INCH
Lead Frame	Copper Alloy	Lead Finish	Matte Tin



POS	INCH	
	MIN	MAX
A	0.160	0.190
b	0.025	0.040
C1	0.012	0.022
D	0.351	0.361
E	0.385	0.420
e	0.062	0.072
F	0.045	0.055
H1	0.560	0.619
J1	0.080	0.120
$\phi P$	0.146	0.156
Q	0.103	0.113
L	0.500	0.580
$q_1$	$3^\circ$	$10^\circ$
$q_2$	$1^\circ$	$7^\circ$
U	0.256	Ref.
V	0.486	Ref.

Note : Foot Length using gauge plane  
method measurement 0.010".


Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>.

# MIC4575

## 5-Lead DDPAK Package Outline and Recommended Land Pattern

### 5-Lead Plastic (ET) [DDPAK]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



		Units	INCHES		
		Dimension Limits	MIN	NOM	MAX
Number of Pins	N		5		
Pitch	e		.067	BSC	
Overall Height	A	.160	—	.190	
Standoff §	A1	.000	—	.010	
Overall Width	E	.380	—	.420	
Exposed Pad Width	E1	.245	—	—	
Molded Package Length	D	.330	—	.380	
Overall Length	H	.549	—	.625	
Exposed Pad Length	D1	.270	—	—	
Lead Thickness	c	.014	—	.029	
Pad Thickness	C2	.045	—	.065	
Lead Width	b	.020	—	.039	
Foot Length	L	.068	—	.110	
Pad Length	L1	—	—	.067	
Foot Angle	ϕ	0°	—	8°	

#### Notes:


- § Significant Characteristic.
- Dimensions D and E do not include mold flash or protrusions. Mold flash or protrusions shall not exceed .005" per side.
- Dimensioning and tolerancing per ASME Y14.5M.

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing C04-012B

## 5-Lead Plastic (ET) [DDPAK]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



RECOMMENDED LAND PATTERN

Units		INCHES		
Dimension Limits		MIN	NOM	MAX
Contact Pitch	E		.067 BSC	
Optional Center Pad Width	X2			.423
Optional Center Pad Length	Y2			.327
Contact Pad Spacing	C1		.248	
Contact Pad Width (X5)	X1			.041
Contact Pad Length (X5)	Y1			.159

## Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2012A

# **MIC4575**

---

---

## **NOTES:**

## APPENDIX A: REVISION HISTORY

### Revision A (December 2020)

- Converted Micrel document MIC4575 to Microchip data sheet template DS20006464A.
- Minor grammatical text changes throughout.

# **MIC4575**

---

---

## **NOTES:**

## PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, contact your local Microchip representative or sales office.

Device Part No.	<u>-XX</u> Output Voltage	X Junction Temp. Range	<u>XX</u> Package	<u>-XX</u> Media Type	Examples:
<b>Device:</b>	MIC4575:	1A, 200 kHz Step-Down Regulator			a) MIC4575WT: MIC4575, Adjustable Output Voltage, -40°C to +85°C Temperature Range, 5-Lead TO-220, 50/Tube
<b>Output Voltage:</b>	3.3 = 3.3V Fixed 5.0 = 5.0V Fixed <blank> = Adjustable				b) MIC4575-3.3WU: MIC4575, 3.3V Fixed Output Voltage, -40°C to +85°C Temperature Range, 5-Lead DDPAK, 50/Tube
<b>Junction Temperature Range:</b>	W = -40°C to +85°C, RoHS-Compliant with High Melting Solder Exemption				c) MIC4575-3.3WU-TR: MIC4575, 3.3V Fixed Output Voltage, -40°C to +85°C Temperature Range, 5-Lead DDPAK, 750/Reel
<b>Package:</b>	T = 5-Lead TO-220 U = 5-Lead DDPAK				d) MIC4575-5.0WT: MIC4575, 5.0V Fixed Output Voltage, -40°C to +85°C Temperature Range, 5-Lead TO-220, 50/Tube
<b>Media Type:</b>	<blank> = 50/Tube (both package options) TR = 750/Reel (DDPAK package option only)				e) MIC4575-5.0WU-TR: MIC4575, 5.0V Fixed Output Voltage, -40°C to +85°C Temperature Range, 5-Lead DDPAK, 750/Reel
<b>Note 1:</b> Tape and Reel identifier only appears in the catalog part number description. This identifier is used for ordering purposes and is not printed on the device package. Check with your Microchip Sales Office for package availability with the Tape and Reel option.					

# **MIC4575**

---

---

## **NOTES:**

---

**Note the following details of the code protection feature on Microchip devices:**

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
  - Microchip believes that its family of products is secure when used in the intended manner and under normal conditions.
  - There are dishonest and possibly illegal methods being used in attempts to breach the code protection features of the Microchip devices. We believe that these methods require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Attempts to breach these code protection features, most likely, cannot be accomplished without violating Microchip's intellectual property rights.
  - Microchip is willing to work with any customer who is concerned about the integrity of its code.
  - Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not mean that we are guaranteeing the product is "unbreakable." Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.
- 

Information contained in this publication is provided for the sole purpose of designing with and using Microchip products. Information regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDIRECT, SPECIAL, PUNITIVE, INCIDENTAL OR CONSEQUENTIAL LOSS, DAMAGE, COST OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

**Trademarks**

The Microchip name and logo, the Microchip logo, Adaptec, AnyRate, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, chipKIT, chipKIT logo, CryptoMemory, CryptoRF, dsPIC, FlashFlex, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Kleer, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PackeTime, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AgileSwitch, APT, ClockWorks, The Embedded Control Solutions Company, EtherSynch, FlashTec, Hyper Speed Control, HyperLight Load, IntelliMOS, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, Temux, TimeCesium, TimeHub, TimePictra, TimeProvider, WinPath, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, Augmented Switching, BlueSky, BodyCom, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, Espresso T1S, EtherGREEN, IdealBridge, In-Circuit Serial Programming, ICSP, INICnet, Intelligent Paralleling, Inter-Chip Connectivity, JitterBlocker, maxCrypto, maxView, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, RTAX, RTG4, SAM-ICE, Serial Quad I/O, simpleMAP, SimpliPHY, SmartBuffer, SMART-I.S., storClad, SQL, SuperSwitcher, SuperSwitcher II, Switchtec, SynchroPHY, Total Endurance, TSHARC, USBCheck, VariSense, VectorBlox, VeriPHY, ViewSpan, WiperLock, XpressConnect, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, and Symmcom are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2020, Microchip Technology Incorporated, All Rights Reserved.

ISBN: 978-1-5224-7356-5

For information regarding Microchip's Quality Management Systems, please visit [www.microchip.com/quality](http://www.microchip.com/quality).



# MICROCHIP

## Worldwide Sales and Service

### AMERICAS

**Corporate Office**  
2355 West Chandler Blvd.  
Chandler, AZ 85224-6199  
Tel: 480-792-7200  
Fax: 480-792-7277  
Technical Support:  
<http://www.microchip.com/support>  
Web Address:  
[www.microchip.com](http://www.microchip.com)

**Atlanta**

Duluth, GA  
Tel: 678-957-9614  
Fax: 678-957-1455

**Austin, TX**

Tel: 512-257-3370

**Boston**

Westborough, MA  
Tel: 774-760-0087  
Fax: 774-760-0088

**Chicago**

Itasca, IL  
Tel: 630-285-0071  
Fax: 630-285-0075

**Dallas**

Addison, TX  
Tel: 972-818-7423  
Fax: 972-818-2924

**Detroit**

Novi, MI  
Tel: 248-848-4000

**Houston, TX**

Tel: 281-894-5983

**Indianapolis**

Noblesville, IN  
Tel: 317-773-8323  
Fax: 317-773-5453  
Tel: 317-536-2380

**Los Angeles**

Mission Viejo, CA  
Tel: 949-462-9523  
Fax: 949-462-9608  
Tel: 951-273-7800

**Raleigh, NC**

Tel: 919-844-7510

**New York, NY**

Tel: 631-435-6000

**San Jose, CA**

Tel: 408-735-9110  
Tel: 408-436-4270

**Canada - Toronto**

Tel: 905-695-1980  
Fax: 905-695-2078

### ASIA/PACIFIC

**Australia - Sydney**  
Tel: 61-2-9868-6733  
**China - Beijing**  
Tel: 86-10-8569-7000  
**China - Chengdu**  
Tel: 86-28-8665-5511  
**China - Chongqing**  
Tel: 86-23-8980-9588  
**China - Dongguan**  
Tel: 86-769-8702-9880  
**China - Guangzhou**  
Tel: 86-20-8755-8029  
**China - Hangzhou**  
Tel: 86-571-8792-8115  
**China - Hong Kong SAR**  
Tel: 852-2943-5100  
**China - Nanjing**  
Tel: 86-25-8473-2460  
**China - Qingdao**  
Tel: 86-532-8502-7355  
**China - Shanghai**  
Tel: 86-21-3326-8000  
**China - Shenyang**  
Tel: 86-24-2334-2829  
**China - Shenzhen**  
Tel: 86-755-8864-2200  
**China - Suzhou**  
Tel: 86-186-6233-1526  
**China - Wuhan**  
Tel: 86-27-5980-5300  
**China - Xian**  
Tel: 86-29-8833-7252  
**China - Xiamen**  
Tel: 86-592-2388138  
**China - Zhuhai**  
Tel: 86-756-3210040

### ASIA/PACIFIC

**India - Bangalore**  
Tel: 91-80-3090-4444  
**India - New Delhi**  
Tel: 91-11-4160-8631  
**India - Pune**  
Tel: 91-20-4121-0141  
**Japan - Osaka**  
Tel: 81-6-6152-7160  
**Japan - Tokyo**  
Tel: 81-3-6880- 3770  
**Korea - Daegu**  
Tel: 82-53-744-4301  
**Korea - Seoul**  
Tel: 82-2-554-7200  
**Malaysia - Kuala Lumpur**  
Tel: 60-3-7651-7906  
**Malaysia - Penang**  
Tel: 60-4-227-8870  
**Philippines - Manila**  
Tel: 63-2-634-9065  
**Singapore**  
Tel: 65-6334-8870  
**Taiwan - Hsin Chu**  
Tel: 886-3-577-8366  
**Taiwan - Kaohsiung**  
Tel: 886-7-213-7830  
**Taiwan - Taipei**  
Tel: 886-2-2508-8600  
**Thailand - Bangkok**  
Tel: 66-2-694-1351  
**Vietnam - Ho Chi Minh**  
Tel: 84-28-5448-2100

### EUROPE

**Austria - Wels**  
Tel: 43-7242-2244-39  
Fax: 43-7242-2244-393  
**Denmark - Copenhagen**  
Tel: 45-4485-5910  
Fax: 45-4485-2829  
**Finland - Espoo**  
Tel: 358-9-4520-820  
**France - Paris**  
Tel: 33-1-69-53-63-20  
Fax: 33-1-69-30-90-79  
**Germany - Garching**  
Tel: 49-8931-9700  
**Germany - Haan**  
Tel: 49-2129-3766400  
**Germany - Heilbronn**  
Tel: 49-7131-72400  
**Germany - Karlsruhe**  
Tel: 49-721-625370  
**Germany - Munich**  
Tel: 49-89-627-144-0  
Fax: 49-89-627-144-44  
**Germany - Rosenheim**  
Tel: 49-8031-354-560  
**Israel - Ra'anana**  
Tel: 972-9-744-7705  
**Italy - Milan**  
Tel: 39-0331-742611  
Fax: 39-0331-466781  
**Italy - Padova**  
Tel: 39-049-7625286  
**Netherlands - Drunen**  
Tel: 31-416-690399  
Fax: 31-416-690340  
**Norway - Trondheim**  
Tel: 47-7288-4388  
**Poland - Warsaw**  
Tel: 48-22-3325737  
**Romania - Bucharest**  
Tel: 40-21-407-87-50  
**Spain - Madrid**  
Tel: 34-91-708-08-90  
Fax: 34-91-708-08-91  
**Sweden - Gothenberg**  
Tel: 46-31-704-60-40  
**Sweden - Stockholm**  
Tel: 46-8-5090-4654  
**UK - Wokingham**  
Tel: 44-118-921-5800  
Fax: 44-118-921-5820