

#### Electronic fuse for 5 V line



TSOT23-8L

#### **Features**

- 5.7 V typical output overvoltage clamp
- Absolute maximum voltage of 25 V
- · Adjustable current limit
- Thermal protection
- Input undervoltage lockout
- · Low inrush current during startup
- Integrated 40 mΩ Power FET
- En/fault pin
- · Adjustable slew rate for output voltage
- TSOT23-8L package
- Latch (STEF05S) or auto-retry (STEF05SA) versions

### **Application**

- · Hard disk and SSD drives
- Hard disk array
- · Hot-swap board
- · Hot-plug protection

#### **Maturity status link**

STEF05S

#### **Description**

The STEF05S is an integrated electronic fuse optimized for monitoring the 5 V DC power lines.

When connected in series to the main power rail, it is able to precisely detect and react to overcurrent and overvoltage conditions.

When an overload condition occurs, the device limits the output current to a safe value defined by the user. If the anomalous overload condition persists, the device goes into an open state, disconnecting the load from the power supply.

In case of overvoltage on the input, the device regulates the output to a preset safe value.

Undervoltage lockout prevents the load from malfunction, keeping the device off if the rail voltage is too low.


The STEF05S features the adjustable turn-on slew rate, which is useful to keep the inrush current under control during startup and hot-swap operations.

The STEF12S is a companion chip for the 12 V rails, useful to implement a complete power rail control in data-storage applications.



# 1 Diagram

Figure 1. Block diagram




DS13054 - Rev 1 page 2/26



# Pin configuration

Figure 2. Pin connection (top view)



**Table 1. Pin description** 

Pin #	Symbol	Function
1	I <sub>Lim</sub> <sup>(1)</sup>	An $R_{\text{Lim}}$ resistor between this pin and the Source pin sets the overload and short-circuit current limit levels.
		The En/Fault pin is a tri-state, bi-directional interface. During normal operation the pin must be left floating, or it can be used to disable the output of the device by pulling it to ground using an open drain or open collector device.
2	En/Fault	If a thermal fault occurs, the voltage on this pin goes into an intermediate state to signal a monitor circuit that the device is in thermal shutdown. It can be connected to another device of this family to cause a simultaneous shutdown during thermal events.
3	dV/dt	The internal dv/dt circuit controls the slew rate of the output voltage at turn-on. The internal capacitor allows a ramp-up time of around 1.35 ms. An external capacitor can be added to this pin to increase the ramp time. If an additional capacitor is not required, this pin should be left open.
4	GND	Ground connection.
5 - 6	Source/V <sub>OUT</sub>	Connected to the source of the internal power MOSFET and to the output terminal of the fuse.
7 - 8	V <sub>CC</sub>	Positive input voltage of the eFuse.


<sup>1.</sup> Important: missing or shorted  $R_{Lim}$  causes current limit circuit malfunction and may lead to device damage.

DS13054 - Rev 1 page 3/26



# 3 Typical application

Figure 3. Typical application circuit



DS13054 - Rev 1 page 4/26



## 4 Maximum ratings

Table 2. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V <sub>CC</sub>	Positive power supply voltage	-0.3 to 25	V
V <sub>OUT</sub> /source	Output voltage	-0.3 to Vcc+0.3	V
l <sub>Lim</sub>	Current limit resistor pin voltage	-0.3 to 25	V
En/fault	En/Fault pin voltage	-0.3 to 7	V
dv/dt	dv/dt pin voltage	-0.3 to 7	V
T <sub>op</sub>	Operating junction temperature range	-40 to 125	°C
T <sub>STG</sub>	Storage temperature range	-65 to 150	°C
T <sub>LEAD</sub>	Lead temperature (soldering) 10 s	260	°C
НВМ	ESD protection - Human Body Model	2	kV
CDM	ESD protection - Charged device model (TSOT23-8L package)	500	V

<sup>1.</sup> The thermal limit is set above the maximum thermal rating. It is not recommended to operate the device at temperatures greater than the maximum ratings for extended periods of time.

Note:

Absolute maximum ratings are those values beyond which damage to the device may occur. Functional operation under these conditions is not implied. All values are referred to GND.

Table 3. Thermal data

Symbol	Parameter	Value	Unit
R <sub>thJA</sub>	Thermal resistance junction-ambient	140	°C/W
R <sub>thJC</sub>	Thermal resistance junction-case	35	°C/W

<sup>1.</sup> Based on JESD51-7, 4-layer PCB.

Table 4. Recommended operating condition

Symbol	Parameter	Value	Unit
V <sub>CC</sub>	Operating power supply voltage	3.5 to 5.5	V
I <sub>D</sub>	Maximum continuous current T <sub>A</sub> = 25 °C	3.5	А
C <sub>IN</sub>	Suggested input capacitor	1	μF
C <sub>OUT</sub>	Minimum output capacitor	1	μF

<sup>1.</sup> The maximum allowable power dissipation is a function of the maximum junction temperature  $T_{J(MAX)}$ , the junction-to-ambient thermal resistance  $\theta_{JA}$ , and the ambient temperature  $T_A$  and can be estimated by:  $P_{D(MAX)} = (T_{J(MAX)} - T_A) / \theta_{JA}$ . Exceeding the maximum allowable power dissipation produces overheating that may cause thermal shutdown.

DS13054 - Rev 1 page 5/26



## 5 Electrical characteristics

Table 5. Electrical characteristics  $V_{CC}$  = 5 V,  $V_{En/Fault}$  = 5 V,  $C_{I}$  = 10  $\mu$ F,  $C_{O}$  = 10  $\mu$ F,  $T_{J}$  = 25 °C (unless otherwise specified).

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit	
Under/Ove	rvoltage protection					,	
V <sub>Clamp</sub>	Output clamping voltage	V <sub>CC</sub> = 8 V	5.5	5.7	5.9	V	
V <sub>UVLO</sub>	Undervoltage lockout	Turn-on, voltage rising	2.85	2.9	2.95	V	
V <sub>Hyst</sub>	UVLO hysteresis			0.15		V	
Power MO	SFET						
t <sub>dly</sub>	Delay time	Enabling of chip to soft-start beginning (10% of V <sub>OUT</sub> ), no C <sub>dv/dt</sub>		350		μs	
		T <sub>J</sub> = 25 °C		40	50		
R <sub>DSon</sub>	On-resistance	T <sub>J</sub> = 85 °C		48		mΩ	
V <sub>OFF</sub>	Off state output voltage	V <sub>CC</sub> = 18 V, V <sub>GS</sub> = 0, R <sub>L</sub> = infinite		1	10	mV	
Current Lir	mit				ı		
I <sub>Short</sub>	Short-circuit current limit	R <sub>Lim</sub> = 22 Ω		2		А	
I <sub>Lim</sub>	Overload current limit	R <sub>Lim</sub> = 22 Ω		5.2		Α	
I <sub>Short</sub>	Short-circuit current limit	$R_{Lim}$ = 49.9 $\Omega$		1.1		Α	
I <sub>Lim</sub>	Overload current limit	$R_{Lim} = 49.9 \Omega$		3.2		А	
dv/dt circu	it				ı		
dv/dt	Output voltage ramp time	From 10% to 90% of V <sub>OUT</sub> , no Cdv/dt		1.35		ms	
En/Fault							
V <sub>IL</sub>	Low level input voltage	Output disabled			0.5	V	
V <sub>I(INT)</sub>	Intermediate level input voltage	Thermal fault, output disabled	1.2	1.3	1.45	V	
V <sub>IH</sub>	High level input voltage	Output enabled	2.55			V	
V <sub>I(MAX)</sub>	High state maximum voltage			4.9		V	
I <sub>IL</sub>	Low level input current (sink)	V <sub>En/Fault</sub> = 0 V		-20	-50	μA	
I <sub>I</sub>	High level leakage current for external switch	V <sub>En/Fault</sub> = 5 V			1	μA	
	Maximum fan-out for fault signal	Total numbers of chips that can be connected to this pin for simultaneous shutdown			3	Units	
Current co	nsumption						
		Device operational		0.37			
$I_{Bias}$	Bias current	Thermal shutdown		0.16		mA	
		Off mode, V <sub>En/Fault</sub> = 0 V		0.12			
Thermal pr	rotection						
T <sub>SHDN</sub>	Thermal shutdown			165		°C	
SHUN	Hysteresis			20		1	

<sup>1.</sup> Pulsed test.

DS13054 - Rev 1 page 6/26

<sup>2.</sup> Guaranteed by design and correlation but not tested in production.



### 6 Application information

#### 6.1 Turn-on and soft startup feature

When the input voltage is applied, the En/Fault pin goes up to the high state, and the internal control circuitry is enabled.

After an initial delay time of typically 350  $\mu$ s, the output voltage is ramped up with a slope defined by the internal dv/dt circuitry. If no additional capacitor is connected to the dv/dt pin, the ramp-up time ( $V_{OUT}$  from 10% to 90%) is around 1.35 ms

Connecting a capacitor between the  $C_{dv/dt}$  pin and GND allows the modification of the output voltage ramp-up time. Given the desired time interval  $\Delta t$  during which the output voltage goes from zero to its maximum value, the capacitance to be added on the  $C_{dv/dt}$  pin can be calculated using the following theoretical formula.

$$\Delta t \left( ms \right) = 1.35 + C_{dv/dt} (pF) \times 0.03 \tag{1}$$

Where C<sub>dv/dt</sub> is expressed in farads and the time in seconds.

Figure 4. Delay time and  $V_{\text{OUT}}$  ramp-up time




Table 6. Rise time vs. C<sub>dvdt</sub>

C <sub>dvdt</sub> (pF)	0	22	33	47	100	180	270	470	1000
Rise time (ms)	1.35	2	2.3	2.8	4.4	6.8	9.5	15.5	31.5

#### 6.2 Maximum load at startup

Depending on supply voltage and load, it is possible that during startup the power dissipation is such that the maximum power protection is triggered and the output is shut down before the startup is complete. The EN/Fault signal is set according to Figure 5. En/Fault pin status.

In case of strong capacitive loads, the total start-up time may be longer than the programmed start-up time, since it is dependent also on the limitation current, the output load and the output capacitance value. In such a situation, the foldback current limit could activate, so that the startup is longer or eventually interrupted by the intervention of thermal protection. To avoid this occurrence, a longer start-up time should be set by the appropriate selection of the  $C_{\text{dv/dt}}$  capacitor.

DS13054 - Rev 1 page 7/26



#### 6.3 Normal operating conditions

The STEF05S behaves like a mechanical fuse, supplying the circuitry on its output with the same voltage shown at its input, with a small voltage fall due to the internal N-channel MOSFET R<sub>DSOn</sub>.

#### 6.4 Output voltage clamp

This internal protection circuit clamps the output voltage to a maximum safe value, typically 5.7 V, if the input voltage exceeds the  $V_{CLAMP}$  threshold. In this condition the device regulates the output voltage, therefore power dissipation increases. Thermal shutdown can occur if the overvoltage persists.

#### 6.5 Current limiting

During operation, if the load current reaches the  $I_{LIM}$  overload threshold, an overload is detected. The current limiting circuit reduces the conductivity of the power MOSFET, in order to clamp the output current at the  $I_{SHORT}$  value. The overload threshold and current limit can be customized by means of the limiting resistor  $R_{Lim}$  Figure 3. Typical application circuit.

As shown in Figure 1. Block diagram, the device uses an internal N-channel sense FET with a fixed ratio, to monitor the output current and limit it at the level set by the user.

The  $R_{Lim}$  value for achieving the requested current limitation can be selected by using the following table, together with the graph in Figure 8.  $I_{Lim}$  and  $I_{Short}$  vs.  $R_{Lim}$  and Figure 9.  $I_{Lim}$  and  $I_{Short}$  vs.  $R_{Lim}$  (magnification). Higher resistor values can be used, but due to the current limit trend shown in the graphs previously mentioned, the minimum values of  $I_{LIM}$  and  $I_{SHORT}$  are asymptotically limited.

R<sub>Lim</sub> (Ω) 22 30 39 50 100 200 300 I<sub>Lim</sub> (A) 5.2 4.2 3.55 3.2 2.1 1.6 1.4 I<sub>Short</sub> (A) 2 1.6 1.3 0.55 0.3 0.2 11

Table 7. ILim / IShort vs. RLim

Note: Missing or shorted R<sub>Lim</sub> causes current limit circuit malfunction and may lead to device damage.

#### 6.6 Thermal shutdown

If the device temperature exceeds the thermal shutdown threshold (T<sub>SHDN</sub>), typically 165 °C, the power MOSFET is turned off and the load disconnected.

On the STEF05S latch version the EN/Fault pin of the device is automatically set to an intermediate voltage (typically 1.3 V), in order to signal the overtemperature event to the system controller.

The device can be reset from this condition either by cycling the supply voltage or by pulling down the EN pin below the  $V_{il}$  threshold and then releasing it.

On the auto-retry version (STEF05SA), the EN/Fault pin is set to a low logic level and the auto-retry circuit attempts to restart the device with soft-start once the die temperature is reduced to 145 °C typ. (165 °C minus the hysteresis value, 20 °C typ.).

DS13054 - Rev 1 page 8/26



#### 6.7 En/Fault pin

The EN/Fault pin has the dual function of controlling the output of the device and providing information about the device status to the application. A simplified diagram of this circuit is depicted in Figure 6.

When it is used as a standard Enable pin, it can be connected to an external open-drain or open-collector device. In this case, when it is pulled at low logic level, it turns the output of the eFuse off.

If this pin is left floating, since it has internal pull-up circuitry, the eFuse is turned ON.

On the STEF05S (latch version), in case of thermal fault, the pin is pulled to an intermediate state (Figure 5). This signal can be provided to a monitor circuit, informing it that a thermal shutdown has occurred, or it can be directly connected to the EN/Fault pins of other eFuse devices on the same application in order to achieve a simultaneous enable/disable feature.

When a thermal fault occurs, the device can be reset either by cycling the supply voltage or by pulling down the Enable pin below the  $V_{ii}$  threshold and then releasing it.

On the STEF05SA auto-retry version, once the thermal shutdown is triggered, the EN/Fault pin of the device is set to low state. It goes back to high level once the auto-retry occurs.




Figure 5. En/Fault pin status

DS13054 - Rev 1 page 9/26






Figure 6. EN/Fault driver circuit

### 6.8 Application suggestions and PCB layout guidelines

Input and output capacitors are mandatory to guarantee device control loop stability and reduce the transient effects of stray inductances which may be present on the input and output power paths. In fact, when the STEF05S interrupts the current flow, input inductance generates a positive voltage spike on the input, and output inductance generates a negative voltage spike on the output.

To reduce the effects of such transients, a  $C_{IN}$  capacitor of at least 1  $\mu F$  is recommended between the input pin and GND, and located as close as possible to the device.

For the same reason, a C<sub>OUT</sub> capacitor of at least 1 µF must be connected at the output port.

When the device is powered by a power line made up of very long wires, the input inductance is higher than few µH, so the input capacitor should be increased in order to guarantee the proper operation of the device.

It is suggested to provide for additional protections and methods for addressing these transients, such as:

- Minimizing inductance of the input and output tracks
- TVS diodes on the input to absorb inductive spikes
- Schottky diode on the output to absorb negative spikes
- · Combination of ceramic and electrolytic capacitors on the input and output


PCB layout is critical for a stable and reliable operation. Refer to the typical PCB layout example shown in Figure 7. PCB layout example and to the following guidelines:


- Define the high current input and output copper traces as short as possible and adequately sized to sustain at least the overload current.
- Locate the R<sub>Lim</sub> resistor close to the I<sub>Lim</sub> pin and connect the other terminal of the component to V<sub>OUT</sub> with
  the shortest possible trace. In fact, parasitic effects on the R<sub>Lim</sub> connection trace can affect the current limit
  accuracy.
- Locate the Cdv/dt capacitor close to the dv/dt pin and connect the other terminal to GND with the shortest possible trace. Use low-leakage components for C<sub>dvdt</sub>.
- The TSOT23-8L package dissipates thermal power mainly through the leads, so providing large enough copper areas around the PCB soldering pads is recommended.

DS13054 - Rev 1 page 10/26



Figure 7. PCB layout example





Top layer


Bottom layer


DS13054 - Rev 1 page 11/26





## 7 Typical characteristics

 $V_{CC}$  = 5 V,  $V_{En/Fault}$  = floating,  $R_{Lim}$  = 22  $\Omega$ ,  $C_{OUT}$  = 10  $\mu$ F,  $C_{dV/dt}$  = floating,  $T_A$  = 25 °C, unless otherwise specified.









DS13054 - Rev 1 page 12/26



Figure 12. R<sub>DS\_ON</sub> vs. temperature

Figure 13. Clamping voltage vs. temperature

V<sub>cc</sub>=8V

8.0

7.5

7.0

6.5

6.0

4.5

4.0

3.5

3.0

-50

-25

0

25

50


75


100


125


150

Temperature [°C]









DS13054 - Rev 1 page 13/26



Figure 18. En/Fault pin current vs. temperature (En/Fault to GND)




Figure 19. Soft-start time vs. temperature (no C<sub>dvdt</sub>)




Figure 20. Startup via input voltage (No load)





Figure 21. Startup via En/Fault pin (No load)









Figure 23. Startup via En/Fault ( $C_{OUT}$  = 470  $\mu$ F)





DS13054 - Rev 1 page 14/26

















DS13054 - Rev 1 page 15/26





## 8 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

### 8.1 TQFN 12 (2.00 x 1.70 mm) package information

Figure 30. TSOT23-8L package outline





DS13054 - Rev 1 page 16/26




Table 8. TSOT23-8L mechanical data

Dim.	mm					
DIM.	Min.	Тур.	Max.			
А			1			
A1	0.01	0.05	0.1			
A2	0.84	0.87	0.9			
b	0.22	-	0.36			
b1	0.22	0.26	0.3			
С	0.12	0.15	0.2			
c1	0.08	0.13	0.16			
D	-	2.90 BSC	-			
Е	-	2.80 BSC	-			
E1	-	1.60 BSC	-			
е	-	0.65 BSC	-			
e1	-	1.95 BSC	-			
L	0.3	0.4	0.5			
L1	-	0.60 BSC	-			
L2	-	0.25 BSC	-			
R	0.1	-	-			
R1	0.1	-	0.25			
Θ	0	4°	8°			
Θ1	4°	10°	12°			
	Tolerance of for	rm and position				
aaa		0.15				
bbb	0.25					
ccc	0.1					
ddd	0.13					
N	8					
ND	4					

DS13054 - Rev 1 page 17/26



Figure 31. TSOT23-8L recommended footprint




DS13054 - Rev 1 page 18/26



## 8.2 TSOT23-8L packing information


Figure 32. TSOT23-8L reel drawing outline



DS13054 - Rev 1 page 19/26



Figure 33. TSOT23-8L carrier tape



Ao	3.23 +/-0.10
Во	3.17 +/-0.10
Kο	1.37 +/-0.10
F	3.50 +/-0.05
P1	4.00 +/-0.10
187	800 +03/-01

- (I) Measured from centreline of sprocket hale to centreline of pocket.

  (II) Cumulative talerance of 10 sprocket hales is ± 0.20.


  (III) Measured from centreline of sprocket hale to centreline of pocket.

  (IV) Other material available.

- (V) Typical SR of form tape Max. 10<sup>9</sup> OHM/SR

ALL DIMENSIONS IN MILLIMETRES UNLESS OTHERWISE STATED.

Figure 34. TSOT23-8L device orientation in tape



DS13054 - Rev 1 page 20/26





# 9 Ordering information

#### Table 9. Order codes

Order code	Package	Packaging	Marking	Thermal protection
STEF05SGR	TSOT23-8	Tape and reel	05SL	Latch-off

DS13054 - Rev 1 page 21/26



## **Revision history**

Table 10. Document revision history

Date	Revision	Changes
27-Oct-2021	1	Initial release.

DS13054 - Rev 1 page 22/26



## **Contents**

1	Diag	gram	2
2		configuration	
3	Турі	ical application	4
4	Max	kimum ratings	5
5	Elec	ctrical characteristics	6
6	Арр	Dication information	7
	6.1	Turn-on and soft startup feature	7
	6.2	Maximum load at startup	
	6.3	Normal operating conditions	8
	6.4	Output voltage clamp	8
	6.5	Current limiting	8
	6.6	Thermal shutdown	8
	6.7	En/Fault pin	9
	6.8	Application suggestions and PCB layout guidelines	10
7	Турі	ical characteristics	12
8	Pac	kage information	16
	8.1	TSOT23-8L package information	16
	8.2	TSOT23-8L packing information	19
9	Ord	ering information	21
Re	vision	history	22



## **List of tables**

Table 1.	Pin description	3
	Absolute maximum ratings	
	Thermal data	
Table 4.	Recommended operating condition	5
Table 5.	Electrical characteristics $V_{CC}$ = 5 V, $V_{En/Fault}$ = 5 V, $C_{I}$ = 10 $\mu$ F, $C_{O}$ = 10 $\mu$ F, $T_{J}$ = 25 °C (unless otherwise specified).	.6
Table 6.	Rise time vs. C <sub>dvdt</sub>	7
Table 7.	I <sub>Lim</sub> / I <sub>Short</sub> vs. R <sub>Lim</sub>	8
Table 8.	TSOT23-8L mechanical data	17
Table 9.	Order codes	21
Table 10.	Document revision history	22

DS13054 - Rev 1



# **List of figures**

Figure 1.	Block diagram	. 2
Figure 2.	Pin connection (top view)	. 3
Figure 3.	Typical application circuit	. 4
Figure 4.	Delay time and V <sub>OUT</sub> ramp-up time	. 7
Figure 5.	En/Fault pin status	. 9
Figure 6.	EN/Fault driver circuit	10
Figure 7.	PCB layout example	11
Figure 8.	I <sub>Lim</sub> and I <sub>Short</sub> vs. R <sub>Lim</sub>	12
Figure 9.	I <sub>Lim</sub> and I <sub>Short</sub> vs. R <sub>Lim</sub> (magnification)	12
Figure 10.	Bias current vs. temperature.	12
Figure 11.	Bias current vs. temperature (thermal shutdown)	12
Figure 12.	R <sub>DS_ON</sub> vs. temperature	13
Figure 13.	Clamping voltage vs. temperature	13
Figure 14.	UVLO vs. temperature	13
Figure 15.	UVLO Hysteresis vs. temperature	13
Figure 16.	En/Fault pin thresholds vs. temperature	13
Figure 17.	En/Fault pull-up voltage vs. temperature	13
Figure 18.	En/Fault pin current vs. temperature (En/Fault to GND)	
Figure 19.	Soft-start time vs. temperature (no C <sub>dvdt</sub> )	14
Figure 20.	Startup via input voltage (No load)	14
Figure 21.	Startup via En/Fault pin (No load)	14
Figure 22.	Startup via input voltage (5 $\Omega$ load)	14
Figure 23.	Startup via En/Fault ( $C_{OUT}$ = 470 $\mu$ F)	14
Figure 24.	Startup into voltage clamp	15
Figure 25.	Voltage clamp during operation	15
Figure 26.	Startup into output short-circuit	15
Figure 27.	Hot-plug into overload	
Figure 28.	Overcurrent protection during operation	15
Figure 29.	Output short-circuit during operation	
Figure 30.	TSOT23-8L package outline	
Figure 31.	TSOT23-8L recommended footprint	
Figure 32.	TSOT23-8L reel drawing outline	
Figure 33.	TSOT23-8L carrier tape	
Figure 34.	TSOT23-8L device orientation in tape	20



#### **IMPORTANT NOTICE - PLEASE READ CAREFULLY**

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2021 STMicroelectronics - All rights reserved

DS13054 - Rev 1 page 26/26