

October 2005

General Description

Combining low-power CMOS logic with high-current, high-voltage power FET outputs, the Series SLA706xM translator/drivers provide complete control and drive for a two-phase unipolar stepper motor with internal fixed off time and pulse-width modulation (PWM) control of the output current in a power multi-chip module (PMCMTM).

There are no phase-sequence tables, high-frequency control lines, or complex interfaces to program. The CMOS logic section provides the sequencing logic, direction, control, synchronous/asynchronous PWM operation, and a "sleep"function. The minimum CLOCK input is an ideal fit for applications where a complex μ P is unavailable or overburdened. TTL or LSTTL may require the use of appropriate pull-up resistors to ensure a proper input-logic high. For PWM current control, the maximum output current is determined by the user's selection of a reference voltage and sensing resistor. The NMOS outputs are capable of sinking up to 1, 2, or 3 A (depending on device) and withstanding 46 V in the off state.

Clamp diodes provide protection against inductive transients. Special power-up sequencing is not required.

Half-, quarter-, eighth-, and sixteenth-step operation are externally selectable for the SLA7060/61/62M. Full-, Half-, quarter-, and eighth-step operation are externally selectable for the SLA7065/66/67M.

Half-step excitation alternates between the one-phase and two-phase modes (A-AB-B-AB-A-AB-BAB),providing an eight-step sequence.

■Applications

- •PPC
- •Printer
- •OA Equipment

■Features

- To 3 A Output Rating
- •Internal Sequencer for Microstepping Operation
- •PWM Constant-Current Motor Drive
- •Cost-Effective, Multi-Chip Solution
- •100 V, Avalanche-Rated NMOS Outputs
- •Low rDS(on) NMOS Outputs (150 milli-ohms typical)
- •Advanced, Improved Body Diodes
- •nputs Compatible with 3.3 V or 5 V Control Signals
- •Sleep Mode
- •Internal Clamp Diodes

■Package



■Key Specifications

- •Motor Supply Voltage (VM) : 44V max
- •Load Supply Voltage (Vs) : $10V \sim 44V$
- •Logic Supply Voltage (Vcc) : $3V \sim 5.5V$
- •Output Current (Io): 1A(SLA7060M,SLA7065M)
 - 2A(SLA7061M,SLA7066M)
 - 3A(SLA7062M,SLA7067M)
- $\bullet Output$ Maximum Voltage (V_{DSS}) : 100V min



Sanken Electric Co.,Ltd. http://www.sanken-ele.co.jp/en/



October 2005

Scope

The present specifications shall apply to a micro-stepping capable 2-phase unipolar stepper motor driver IC, SLA706xM Series. The present specifications shall apply to SLA706xM Series which is performed RoHS instructions. Lead part solder : Pb free Inner solder : Lead content >85%

Outline

Туре	Hybrid integrated circuit		
Structure	Plastic molded (transfer mold)		
Applications	To drive a 2-phase stepper motor. (Micro-Stepping Capable. PWM Constant-Current Control.)		

Absolute maximum ratings

8				
Characteristic	Symbol	Ratings	Unit	Remarks
Load Supply Voltage	V _M	46	V	
Main Power Supply Voltage	V _{BB}	46	V	
Logic Supply Voltage	Vdd	7	V	
		1.0		SLA7060M,SLA7065M
Output Current	Io**	2.0	А	SLA7061M,SLA7066M
		3.0		SLA7062M,SLA7067M
Logic Input Voltage	VIN	$-0.3 \sim V_{DD} + 0.3$	V	
REF Input Voltage	V_{REF}	$-0.3 \sim V_{DD} + 0.3$	V	
Sense Voltage	$V_{\rm RS}$	±2	V	Tw<1µS doesn't contain it.
Domos Dissingtion	PD	3.5	W	at Ta=25°C
Power Dissipation		16	W	at Tc=25°C
Junction Temperature	T_{j}	150	°C	
Operating Temperature Range	T_{a}	$-20{\sim}85$	°C	
Storage Temperature Range	$\mathrm{T}_{\mathrm{stg}}$	$-30 \sim 150$	°C	

*Output current rating may be limited by duty cycle, ambient temperature, and heat sinking.

Under any set of conditions, do not exceed the specified junction temperature(T_j).



October 2005

Electrical characteristics

Recommendable Operating Range

Characteristic	Symbol	Ratings			Remarks	
Characteristic	Symbol	MIN	MAX	Unit	Remarks	
Load Supply Voltage	VM		44	V		
Main Power Supply Voltage Range	V_{BB}	10	44	V		
Logic Supply Voltage Range	V_{DD}	3.0	5.5	V	Please adjust the Vcc surge voltage to 0.5V or less.	
REF Input Voltage Range	$V_{\rm REF}$	0.1	1.0	V	The control current accuracy decreases in 0.1V or less.	
Case Temperature	Tc		90	°C	11Pin temperature (at No Fin)	

Electrical Characteristic (T_a=25°C,V_{BB}=24V,V_{DD}=5V Unless Otherwise Noted.)

Oleanastaristia	Granhal		Limits		TL	That Care dition
Characteristic	Symbol	Min.	Тур.	Max.	Unit	Test Condition
Main Power Supply Current	IBB			15	mA	Regularity
Main Tower Supply Current	IBBS			100	μA	at SLEEP operates
Logic Supply Current	IDD			4	mA	
Drain-Source Breakdown	V(BR)DS	100			V	V _{BB} =44V I _D =1mA
Output On Resistance	$R_{DS(on)}$		0.25	0.4	Ω	ID=2A
Body Diode Forward Voltage	$V_{\rm F}$		0.95	1.2	V	I _F =2A
Maximum Clock Frequency	$\mathbf{f}_{\mathrm{clk}}$	250^{*}			kHz	duty=50%
Logic Input Voltage	VIL			$0.25\mathrm{V}_\mathrm{DD}$	V	
Logic Input voltage	VIH	$0.75 V_{DD}$			V	
	IIL		±1		μA	Clock, Reset,
Logic Input Current	$I_{\rm IH}$		±1		μA	CW/CCW, Sync
Logic Input Current	IILM	-75	-50	-25	μA	M1,M2
	I _{IHM}		± 1		μA	1011,1012
REF Input Voltage Range	VREF	0		1.5	V	Stationary current control
KEF input voltage Kange	VREFS	2.0		V_{DD}	V	at SLEEP operates
REF Input Current	IREF		±10		μA	V _{REF} =0~V _{DD}
Mo Output Voltage	VMOL			1.25	V	I _{MOL} =1.5mA
	V _{MOH}	V_{DD} -1.25			V	Iмон =-1.5mA
Mo Output Current	I _{MOL}			3	mA	
	Імон	-3			mA	

*Operation at a step frequency greater than the specified minimum value is possible but not warranted.

Note.

Negative current is defined as coming out of the specified pin.



October 2005

Electrical Characteristic(cont	(1_a)	=25°C, V _{BB}		5V Unless	otherv	wise Noted.)
Characteristic	Symbol		Limits	Unit		Test Condition
Characteristic	Gymbol	Min.	Тур.	Max.	OIIIt	
Sense Voltage	V _{SENSE}	0.95	1.00	1.05	v	$V_{REF}=1.0V$
Sense voltage	V SENSE	0.95	1.00	1.05	v	at Mode F
Sense pins Sink Current	Isense		±10		μΑ	
	Mode F		100		%	
	Mode E		98.1		%	
	Mode D*		95.7		%	
	Mode C		92.4		%	
	Mode B [*]		88.2		%	
	Mode A		83.1		%	
	Mode 9 [%]		77.3		%	1000/
Step Reference Current Ratio	Mode 8		70.7		%	V _{SENSE} =100% V _{REF} =0.1~1V
	Mode 7 ^{**}		63.4		%	
	Mode 6		55.5		%	
	Mode 5 ^{**}		47.1		%	
	Mode 4		38.2		%	
	Mode 3 ^{**}		29.0		%	
	Mode 2		19.5		%	
	Mode 1 ^{**}		9.8		%	
Wake-Up time	t_{SE}	100			μs	$V_{REF}: 2.0 \rightarrow 1.5V$
	t_{pdon}		2.0		μs	Clock→Out ON
Switching Time	,		1 6			$Clock \rightarrow Out$
	$t_{ m pdoff}$		1.5		μs	OFF
PWM Minimum On Time	ton(min)		1.8		μs	
	toff1		12		μs	Mode 8~F
PWM OFF Time	$t_{\rm OFF2}$		9		μs	Mode 4~7
	t _{OFF3}		7		μs	Mode 1~3

Electrical Characteristic(continued) $(T_a=25^{\circ}C, V_{BB}=24V, V_{DD}=5V \text{ Unless Otherwise Noted.})$

Note.

• Negative current is defined as coming out of the specified pin.

• SLA7065M, SLA7066M, and SLA7067M of the item of * sign of Step Reference Current Ratio are off the subject.



October 2005



Truth Table

• Input Pin

Pin Name	Low Level	High Level	Clock	
Reset	Run	Logic Reset	-	
CW/CCW	Forward (CW)	Reverse (CCW)	•	
M1 M2	Micro-Stepping Ope	Micro-Stepping Operation Mode Setting		
REF	Enable	Sleep Mode	-	
Sync	Asynchronous PWM operation	Synchronous PWM operation	-	



October 2005

Micro-Stepping Operation Mode Setting

SLA7060M, SLA7061M, SLA7062M]					
Operation Mode	Input Level				
Operation Mode	M1	M2			
4W 1-2phase (1/16 Step)	L	L			
2W 1-2phase (1/8 Step)	L	Н			
W 1-2phase (1/4 Step)	Н	L			
1-2phase (1/2 Step)	Н	Н			

[SLA7065M, SLA7066M, SLA7067M]

Operation Mode	Input Level		
Operation Mode	M1	M2	
2W 1-2phase (1/8 Step)	L	L	
W 1-2phase (1/4 Step)	L	Н	
1-2phase (1/2 Step)	Н	L	
2-2phase (Full Step)	Н	Н	

• Output Pin

ľ

Pin Name	High Level	Low Level
Mo	Half-Step Position (Mode 8)	-



Logic Input Timing Requirements

Sanken Electric Co.,Ltd.



October 2005





Sanken Electric Co.,Ltd.



October 2005





Sanken Electric Co.,Ltd.



October 2005





Sanken Electric Co.,Ltd.



October 2005



Sanken Electric Co.,Ltd.



October 2005

Internal functional block diagram



Pin Assignment (Terminal Functions)

Pin No.	Symbol	Function
1	OutA	Phase A Output
2	OutA	Phase A Output
3	OutA/	Phase A/ Output
4	OutA	r nase A/ Output
5	SenseA	Phase A Current Sense
6	V_{DD}	Logic Supply
7	REF	Control Current Set & OFF Output
8	Reset	Reset Input for Logic Circuit
9	CW/CC	Forward / Reverse Switch Input
	W	
10	Clock	Step Clock Input
11	GND	GND
12	M2	Micro-Stepping Operation Mode
13	M1	Setting Input
14	Mo	Position Monitoring Output
15	Sync	PWM Chopping Function Select
10	Bylic	Input
16	V_{BB}	Main Power Supply (For Motor)
17	SenseB	Phase B Current Sense
18	OutB/	Phase B/ Output
19	OutD/	Phase B/ Output
20	OutB	B相出力 Phase B Output
21	Outb	B 相出力 Phase B Output

Sanken Electric Co.,Ltd.



October 2005

Example application circuit



 $\stackrel{\scriptscriptstyle \wedge}{\succ} Precaution to avoid the noise on <math display="inline">V_{DD}$ line.

Switching noise from PCB traces, where high current flows, to the V_{DD} line should be minimized

because the noise level more than 0.5V on the V_{DD} line may cause malfunctioning operation. The tip for avoiding such problem is to separate the logic GND (S-GND) and the power GND (P-GND) on a PCB,

and then connect them together at IC GND pin (#11).

 ${\stackrel{{}_{\scriptstyle \sim}}{\rightarrowtail}} The \ loss \ of `Rs' \ resistance \ will \ occur.$



October 2005

Package information



Dimensions in millimeters Material of terminal : Cu Treatment of terminal : Ni planting + solder dip (Pb Free)

Appearance

The body shall be clean and shall not bear any stain, rust or flaw.

Marking

The type number and lot number shall be clearly marked in white.



October 2005





Sanken Electric Co.,Ltd.



October 2005

Cautions and warnings

The calculation of control current

SLA706xM Series control current Io (at Mode F) is calculated as follow.

 $I_O = \frac{V_{REF}}{R_S}$

REF voltage is recommended to be from 0.1 to 1.0V. %When the REF<0.1V, the accuracy of the current control becomes worst.

Moreover, setting the REF voltage more than 2V activates the sleep mode (all outputs is in OFF state).

However, the internal logic circuit is alive.

Logic inputs/output (RESET, CLOCK, CW/CCW, M1, M2, SYNC, Mo)

• Following timing should comply with the "Logic input timing".

-The rising edge timing of CW/CCW, M1, M2 and that of CLOCK input

-The RESET release timing(=the falling edge on RESET input) and the rising edge timing of CLOCK input

XIn case it does not comply with the "Logic input timing", it may operate at an unexpected sequence.

• Be sure to prevent the logic inputs(RESET, CLOCK, CW/CCW, M1, M2, SYNC) from being "OPEN".

If some of the logic inputs are not used, be sure to connect them to VDD or GND.

%In case some of the logic inputs stay "OPEN", a malfunction may occur due to external noises.

- When the logic output(Mo) is not used, be sure to keep it "OPEN".
 - %In case it is connected to VDD or GND, it may cause the device's deterioration or/and breakdown.

Installation to a heat sink

1) Recommended Clamping	Torque (to l	External Heat sink)	0.490~0.822N•m
2) Recommended Silicone	G746	{SHIN-ETSU CHE	MICAL}
	YG6260	{TOSHIBA SILICO	NE}
	SC102	{DOW CORNING 1	FORAY SILICONE}

Notice

This driver has C-MOS inputs. Please notice as following contents.

- When static electricity is a problem, care should be taken to properly control the room humidity. This is particularly true in the winter when static electricity is most troublesome.
- Care should be taken with device leads and with assembly sequencing to avoid applying static charges to IC leads. PC board pins should be shorted together to keep them at the same potential to avoid this kind of trouble.



October 2005

<Worldwide Contacts>

Asia Pacific

<u>China</u>

Sanken Electric Hong Kong Co., Ltd. Suite 1026 Ocean Centre, Canton Road, Tsimshatsui, Kowloon, Hong Kong Tel: 852-2735-5262 Fax: 852-2735-5494

Sanken Electric (Shanghai) Co., Ltd. Room3202, Maxdo Centre, Xingyi Road 8, Changning district, Shanghai, China Tel: 86-21-5208-1177 Fax: 86-21-5208-1757

Taiwan Sanken Electric Co., Ltd.

Room 1801, 18th Floor, 88 Jung Shiau East Road, Sec. 2, Taipei 100, Taiwan R.O.C. Tel: 886-2-2356-8161 Fax: 886-2-2356-8261

<u>India</u>

Saket Devices Pvt. Ltd.

Office No.13, First Floor, Bandal - Dhankude Plaza, Near PMT Depot, Paud Road, Kothrud, Pune - 411 038, India Tel: 91-20-5621-2340 91-20-2528-5449 Fax: 91-20-2528-5459

<u>Japan</u>

Sanken Electric Co., Ltd. Overseas Sales Headquaters Metropolitan Plaza Bldg. 1-11-1 Nishi-Ikebukuro, Toshima-ku, Tokyo 171-0021, Japan Tel: 81-3-3986-6164 Fax: 81-3-3986-8637

<u>Korea</u>

Sanken Electric Korea Co., Ltd. Mirae Asset Life Bldg. 6F, 168 Kongduk-dong, Mapo-ku, Seoul, 121-705, Korea Tel: 82-2-714-3700 Fax: 82-2-3272-2145

Singapore

Sanken Electric Singapore Pte. Ltd. 150 Beach Road, #14-03 The Gateway West, Singapore 189720 Tel: 65-6291-4755 Fax: 65-6297-1744



October 2005

Europe

United Kingdom

Sanken Power Systems (UK) Limited Pencoed Technology Park, Pencoed, Bridgend CF35 5HY. UK Tel: 44-1656-869-100 Fax: 44-1656-869-162

North America

United States

Allegro MicroSystems, Inc. 115 Northeast Cutoff, Worcester, Massachusetts 01606, U.S.A. Tel: 1-508-853-5000 Fax: 1-508-853-3353

Allegro MicroSystems, Inc. (Southern California)

14 Hughes Street, Suite B105, Irvine, CA 92618 Tel: 1-949-460-2003 Fax: 1-949-460-7837



October 2005

CAUTION / WARNING

- •The information in this publication has been carefully checked and is believed to be accurate; however, no responsibility is assumed for inaccuracies.
- Sanken reserves the right to make changes without further notice to any products herein in the interest of
 improvements in the performance, reliability, or manufacturability of its products.
 Before placing an order, Sanken advises its customers to obtain the latest version of the relevant information to verify
 that the information being relied upon is current.
- Application and operation examples described in this catalog are quoted for the sole purpose of reference for the use of the products herein and Sanken can assume no responsibility for any infringement of industrial property rights, intellectual property rights or any other rights of Sanken or any third party which may result from its use.
- When using the products herein, the applicability and suitability of such products for the intended purpose or object shall be reviewed at the users' responsibility.
- Although Sanken undertakes to enhance the quality and reliability of its products, the occurrence of failure nd defect of semiconductor products at a certain rate is inevitable. Users of Sanken products are requested to take, at their own risk, preventative measures including safety design of the equipment or systems against any possible injury, death, fires or damages to the society due to device failure or malfunction.
- Sanken products listed in this catalog are designed and intended for the use as components in general purpose electronic equipment or apparatus (home appliances, office equipment, telecommunication equipment, measuring equipment, etc.). Before placing an order, the user's written consent to the specifications is requested. When considering the use of Sanken products in the applications where higher reliability is required (transportation equipment and its control systems, traffic signal control systems or equipment, fire/crime alarm systems, various safety devices, etc.), please contact your nearest Sanken sales representative to discuss and obtain written confirmation of your specifications. The use of Sanken products without the written consent of Sanken in the applications where extremely high reliability is required (aerospace equipment, nuclear power control systems, life support systems, etc.) is strictly prohibited.
- Anti radioactive ray design is not considered for the products listed herein.
- This publication shall not be reproduced in whole or in part without prior written approval from Sanken.
- •This is notification that you, as purchaser of the products/technology, are not allowed to perform any of the following:
- 1. Resell or retransfer these products/technology to any party intending to disturb international peace and security.
- 2. Use these products/technology yourself for activities disturbing international peace and security.

3. Allow any other party to use these products/technology for activities disturbing international peace and security. Also, as purchaser of these products/technology, you agree to follow the procedures for the export or transfer of these products/technology under the Foreign Exchange and Foreign Trade Law, when you export or transfer the

products/technology, under the Foreign Exchange and Foreign Trade Law, when you export or transfer the products/technology abroad.