

# Si8941/46/47 Data Sheet

# Isolated Delta-Sigma Modulator for Current Shunt Measurement

The Si8941/46/47 is a galvanically isolated delta-sigma modulator which outputs a digital signal proportional to the voltage level at the input. The low-voltage differential input is ideal for measuring voltage across a current shunt resistor or for any place where a sensor must be isolated from the control system. Low noise, low error, and high precision ensure an accurate measurement of system current.

The output of the Si8941/46/47 comes from a 2nd order delta-sigma modulator. The modulator can be clocked either from an onboard oscillator (Si8946/47) or from an external clock (Si8941). The output is typically digitally filtered by an MCU or FPGA in the system.

The Si8941/46/47 isolated delta-sigma modulator utilizes Skyworks' proprietary isolation technology. It supports up to 5.0 kVrms withstand voltage per UL1577. This technology enables higher performance, reduced variation with temperature and age, tighter part-to-part matching, and longer lifetimes compared to other isolation technologies.

## Applications:


- · Industrial, HEV and renewable energy inverters
- · AC, Brushless, and DC motor controls and drives
- · Variable speed motor control in consumer white goods
- · Isolated switch mode and UPS power supplies
- · Automotive onboard chargers, battery management systems, and charging stations

# Safety Approvals:

- UL 1577 recognized
  - Up to 5000 Vrms for 1 minute
- CSA approval
  - 62368-1 (reinforced insulation)
- · VDE certification conformity
  - EN62368-1 (reinforced insulation)
  - Pending IEC60747-17 (basic/reinforced insulation)
- · CQC certification approval
  - GB4943.1-2011

#### **KEY FEATURES**

- · Low voltage differential input
  - ±62.5 mV and ±250 mV options
- · Modulator clock options
  - External clock up to 25 MHz (Si8941)
  - 10 MHz internal clock (Si8946)
  - · 20 MHz internal clock (Si8947)
- Typical input offset: ±50 μV
- Typical gain error: ±0.05%
- · Excellent drift specifications
  - ±0.5 μV/°C typical offset drift
  - ±4 ppm/°C typical gain drift
- Typical 14-bit (ENOB) precision
- High common-mode transient immunity: 75 kV/µs
- · Typical SNR: 90 dB
- Typical THD: -97 dB
- Typical nonlinearity: 0.001%
- · Auomotive-grade OPNs
  - AIAG-compliant PPAP documentation support
  - IMDS and CAMDS listing support
- · Compact packages
  - 8-pin wide body stretched SOIC
  - 8-pin narrow body SOIC
- –40 to 125 °C



# 1. Ordering Guide

Table 1.1. Si8941-46-47 Ordering Guide<sup>1, 2, 3</sup>

Ordering		Ordering Options					
Part Number (OPN)	Automotive OPN <sup>4</sup>	Specified Input Range	Isolation Rating	Clock	Package Type		
Si8941AD-IS4	Si8941AD-AS4	±62.5 mV	5.0 kVrms	Input	WB Stretched SOIC-8		
Si8941BD-IS4	Si8941BD-AS4	±250 mV	5.0 kVrms	Input	WB Stretched SOIC-8		
SI8946AD-IS4	SI8946AD-AS4	±62.5 mV	5.0 kVrms	10 MHz Output	WB Stretched SOIC-8		
SI8946BD-IS4	SI8946BD-AS4	±250 mV	5.0 kVrms	10 MHz Output	WB Stretched SOIC-8		
SI8947AD-IS4	SI8947AD-AS4	±62.5 mV	5.0 kVrms	20 MHz Output	WB Stretched SOIC-8		
SI8947BD-IS4	SI8947BD-AS4	±250 mV	5.0 kVrms	20 MHz Output	WB Stretched SOIC-8		
Si8941AB-IS	Si8941AB-AS	±62.5 mV	2.5 kVrms	Input	NB SOIC-8		
Si8941BB-IS	Si8941BB-AS	±250 mV	2.5 kVrms	Input	NB SOIC-8		
SI8946AB-IS	SI8946AB-AS	±62.5 mV	2.5 kVrms	10 MHz Output	NB SOIC-8		
SI8946BB-IS	SI8946BB-AS	±250 mV	2.5 kVrms	10 MHz Output	NB SOIC-8		
SI8947AB-IS	SI8947AB-AS	±62.5 mV	2.5 kVrms	20 MHz Output	NB SOIC-8		
SI8947BB-IS	SI8947BB-AS	±250 mV	2.5 kVrms	20 MHz Output	NB SOIC-8		

- 1. All packages are RoHS-compliant.
- 2. "Si" and "SI" are used interchangeably.
- 3. AEC-Q100 pending qualification.
- 4. Automotive-Grade devices ("-A" suffix) are identical in construction materials, topside marking, and electrical parameters to their Industrial-Grade ("-I" suffix) version counterparts. Automotive-Grade products are produced utilizing full automotive process flows and additional statistical process controls throughout the manufacturing flow. The Automotive-Grade part number is included on shipping labels.

# **Table of Contents**

1.	Ordering Guide	. 2
2.	System Overview	. 4
	2.1 Fail-Safe and Low-Power Modes	. 4
	2.2 Modulator	. 5
3.	Current Sense Application	. 6
4.	Electrical Specifications	. 8
	4.1 Regulatory Information	.14
	4.2 Typical Operating Characteristics	.16
5.	Pin Descriptions	22
6.	Packaging	23
	6.1 Package Outline: 8-Pin Wide Body Stretched SOIC	.23
	6.2 Package Outline: 8-Pin Narrow Body SOIC	.25
	6.3 Land Pattern: 8-Pin Wide Body Stretched SOIC	.27
	6.4 Land Pattern: 8-Pin Narrow Body SOIC	.28
	6.5 Top Marking: 8-Pin Wide Body Stretched SOIC	.29
	6.6 Top Marking: 8-Pin Narrow Body SOIC	.30
7	Revision History	31

## 2. System Overview

The input to the Si8941/46/47 is designed for low-voltage, differential signals. This is ideal for connection to low-resistance current shunt measurement resistors. The Si8941A/46A/47A has a specified full scale input range of  $\pm 62.5$  mV, and the Si8941B/46B/47B has a specified full scale input range of  $\pm 250$  mV. This allows the user to choose low-ohmic resistance value sense resistors to minimize system power loss.

The analog input stage of the Si8941/46/47 is a fully differential amplifier feeding the input of a second-order, delta-sigma ( $\Delta\Sigma$ ) modulator that digitizes the input signal into a 1-bit output stream. The isolated data output ADAT pin of the converter provides a stream of digital ones and zeros that is synchronous to the ACLK pin. The Si8946/47 clock is generated internally while the Si8941 clock is provided externally. The time average of this serial bit-stream output is proportional to the analog input voltage.




Figure 2.1. Functional Block Diagram

## 2.1 Fail-Safe and Low-Power Modes

The Si8941/46/47 implements a fail-safe output when the high-side supply voltage VDDA goes away. The fail-safe output is a steady state Logic 0 on ADAT for the externally clocked Si8941. The fail-safe output is a steady state logic 1 on ADAT for the internally clocked Si8946/47. The clock output ACLK of the Si8946/47 will stop after 256 cycles with a steady state Logic 1. When the supply comes back, the clock will be turned back on and the normal DSM data stream will be output in approximately 250 µs. To differentiate from the failsafe output, a maximum nominal input signal will generate a single one every 128 bits at ADAT.

In addition to the fail-safe output, when a loss of VDDA supply occurs, the part will automatically move into a lower power mode that reduces IDDB current to approximately 1 mA. Similarly, a loss of VDDB supply will reduce IDDA current to approximately 1 mA. When the supply voltage is returned, normal operation begins in approximately 250 µs.

## 2.2 Modulator

The output of the Si8941/46/47 comes from a 2nd order delta-sigma modulator (Figure 2.2 Typical 2nd Order Delta-Sigma Modulator Block Diagram on page 5). The modulator provides 1-bit datastream whose average represents the input analog voltage. 0 V across the inputs is represented at the output by a pulse train that has 50% ones density. Positive specified linear full-scale at the input (e.g., +250 mV for the Si8941B/46B/47B and +62.5 mV for the Si8941A/46A/47A) produces an output datastream that has 89.06% ones density, and negative specified full scale gives an output that has 10.94% ones density. Table Table 2.1 Modulator Output on page 5 shows the values for other input levels and for both full-scale input options of the device.




Figure 2.2. Typical 2nd Order Delta-Sigma Modulator Block Diagram

**Table 2.1. Modulator Output** 

Differen	Bitstream % Ones	
Si8941A/46A/47A	Si8941B/46B/47B	
+62.5 mV	+250 mV	89.06%
+31.25 mV	+125 mV	69.53%
0 mV	0 mV	50%
-31.25 mV	-125 mV	30.47%
-62.5 mV	-250 mV	10.94%

## 3. Current Sense Application

In the driver circuit presented below, the Si8941/46/47 is used to amplify the voltage across the sense resistor, RSENSE, where it is oversampled and converted into a 1-bit bitstream, then transmitted across the isolation barrier to be processed by the system controller/FPGA. Placing the sense resistor before the load is known as high-side sensing and isolation is needed because the voltage of RSENSE with respect to ground will swing between 0 V and the high voltage rail connected to the drain of Q1.




Figure 3.1. Current Sense Application

The load in this application can be a motor winding or a similar inductive winding. In a three-phase motor drive application, this circuit would be repeated three times, one for each phase. RSENSE should be a small resistor value to reduce power loss. However, an excessively low resistance will reduce the signal-to-noise ratio of the measurement. Si8941/46/47 offers two specified linear full-scale input options, ±62.5 mV (Si8941A/46A/47A) and ±250 mV (Si8941B/46B/47B), for optimizing the value of RSENSE. Further product ordering options include whether the CLK pin is an input (Si8941) or an output (Si8946/47).

AIP and AIN connections to the RSENSE resistor should be made as close as possible to each end of the RSENSE resistor as trace resistance will add error to the measurement. The input to the Si8941/46/47 is differential, and the PCB traces back to the input pins should run in parallel. This ensures that any large noise transients that occur on the high-voltage side are coupled equally to the AIP and AIN pins and will be rejected by the Si8941/46/47 as a common-mode signal.

The Si8941/46/47 has intrinsic low-pass filtering at approximately 800 kHz. If further input filtering is required, a passive, differential RC low-pass filter can be placed between RSENSE and the input pins. Values of R1 = R2 =  $20~\Omega$  and C1 = 10~nF provides a cutoff at approximately 400 kHz. For the lowest gain error, R1 and R2 should always be less than  $33~\Omega$  to keep the source impedance sufficiently low compared to the Si8941/46/47 input impedance.

The common-mode voltage of AIN and AIP must be greater than -0.2 V but less than 1 V with respect to GNDA. To meet this requirement, route a trace from the GNDA pin of the Si8941/46/47 to one side of the RSENSE resistor. In this circuit, GNDA, RSENSE, the source of Q1, and the drain of Q2 are connected. The ground of the gate driver (one half of the Skyworks' Si8234 in this example) is also commonly connected to the same node.

The Q1 gate driver has a floating supply of 24 V. Since the input and output of the Si8941/46/47 are galvanically isolated from each other, separate power supplies are necessary on each side. Q3, R3, C3, and D1 make a regulator circuit for powering the input side of the Si8941/46/47 from this floating supply. D1 establishes a voltage of 5.6 V at the base of Q3. R3 is selected to provide a Zener current of 10 mA for D1. C3 provides filtering at the base of Q3, and the emitter output of Q3 provides approximately 5 V to VDDA. C2 is a bypass capacitor for the supply and should be placed at the VDDA pin with its return trace connecting to the GNDA connection at RSENSE.

C4, the local bypass capacitor for the B-side of Si8941/46/47, should be placed closed to VDDB supply pin with its return close to GNDB. The output signal typically goes directly to a digital filter for additional processing. The digital filter may be implemented by a dedicated FPGA in the system or may be a peripheral in the main system controller. The Si8941 expects an external clock to provide

the clock signal for the modulator. That external clock can be provided by the same device that implements the digital filtering or another device that syncs both the modulator and the digital filter. The Si8946/47 generates an internal clock to the digital filter.

# 4. Electrical Specifications

**Table 4.1. Electrical Specifications** 

 $T_A = -40$  to +125 °C, AIN = GNDA, SINC3 filter with 256 oversampling ratio and 20 MHz clock; typical specs at 25 °C with VDDA = VDDB = 5 V unless specified differently under Test Condition

Parameter		Symbol	Test Condition	Min	Тур	Max	Units
Input Side S	Supply Voltage	VDDA		3.0		5.5	V
	Si8941	IDDA	VDDA = 3.3 V	5.3	6.9	8.2	mA
Input Supply Cur- rent	Si8946	IDDA	VDDA = 3.3 V	5.1	6.7	8.1	mA
	Si8947	IDDA	VDDA = 3.3 V	5.3	6.6	8.8	mA
Output Side	Supply Voltage	VDDB		3.0		5.5	V
	Si8941	IDDB	VDDB = 3.3 V	1.0	4	4.8	mA
Output Supply Current	Si8946	IDDB	VDDB = 3.3 V	1.7	8	6.6	mA
	Si8947	IDDB	VDDB = 3.3 V	4.0	7.2	9.7	mA
Amplifier Input							
Specified Linear	Si8941A/46A/47A	VAIP – VAIN		-62.5		62.5	mV
Input Range	Si8941B/46B/47B	VAIF - VAIN		-250		250	mV
Maximum Input	Si8941A/46A/47A	\/AID \/AIN			±80		mV
Voltage Before Clipping	Si8941B/46B/47B	VAIP – VAIN			±320		mV
Common-Mode	Operating Range	VCM	AIN ≠ GNDA	-0.2		1	V
Inpu	Input Offset		T <sub>A</sub> = 25 °C, AIP = AIN = 0	-0.18	±0.05	0.18	mV
Input C	Input Offset Drift			-2	±0.5	2	μV/°C
Gai	n Error	E <sub>G</sub>	T <sub>A</sub> = 25 °C	-0.18	±0.05	0.18	%
Gain I	Error Drift	E <sub>GT</sub>		-25	-4	25	ppm/°C
Differential Input	Si8941A/46A/47A	RIN			6.3		kΩ
Impedance	Si8941B/46B/47B	KIIN			21.4		kΩ
Differential Inp	ut Impedance Drift	RIN <sub>T</sub>			850		ppm/°C
Dynamic Charact	eristics						1
	Si8941A/46A/47A		F <sub>IN</sub> = 5 kHz	80	86		dB
SNR	Si8941B/46B/47B	SNR	BW = 40 kHz (Si8941/47) BW = 20 kHz (Si8946)	84	90		dB
M. P. W	Si8941A/46A/47A		T - 05 °C	-0.008	0.002	0.008	%
Nonlinearity	Si8941B/46B/47B		T <sub>A</sub> = 25 °C	-0.004	0.001	0.004	%
Nonlinearity Drift	Si8941/46/47		T <sub>A</sub> = 25 °C	-0.6		0.6	ppm/°C
	l .	l .	1		I .	1	1

Par	Parameter		Test Condition	Min	Тур	Max	Units
			F <sub>IN</sub> = 5 kHz				
	Si8941A/46A/47A	THD	BW = 40 kHz (Si8941/47)		-95	-81	dB
Total Harmonic			BW = 20 kHz (Si8946)				
Distortion			F <sub>IN</sub> = 5 kHz				
	Si8941B/46B/47B	THD	BW = 40 kHz (Si8941/47)		<b>–</b> 97	-81	dB
			BW = 20 kHz (Si8946)				
			VDDA at DC		-100		dB
Davis Count	. Deiesties Deti-	DODD	VDDA at 100 mV and 10 kHz ripple		-100		dB
Power-Supply	y Rejection Ratio	PSRR	VDDB at DC		-100		dB
			VDDB at 100 mV and 10 kHz ripple		-100		dB
Common-Mode	Transient Immunity	CMTI		50	75		kV/μs
Digital							
Logic high input	threshold (Si8941)	VIH		85% of VDDB			V
Logic low input	threshold (Si8941)	VIL				15% of VDDB	V
Input I	nysteresis	VIHYST			120		mV
Output loa	d capacitance	CLOAD			15		pF
External Clock (S	Si8941)						
Clock I	Frequency	FCLKIN		5		25	MHz
Dut	y Cycle	FDUTY		45	50	55	%
Delay to	Data Valid	TDELAY				23	ns
Data I	Hold Time	THOLD		6			ns
Internal Clock (S	i8946)						
Clock	Frequency	FCLKOUT	T <sub>A</sub> = 25 °C	9.9	10	10.1	MHz
CIOCK	requericy	TOLKOOT	$T_A = -40 ^{\circ}\text{C} \text{ to } 125 ^{\circ}\text{C}$	9.8	10	10.2	MHz
Dut	y Cycle	FDUTY		45	50	55	%
Delay to	Delay to Data Valid					60	ns
Data Hold Time		THOLD		40			ns
Internal Clock (Si	18947)						
Clock Frequency		FOLKOUT	T <sub>A</sub> = 25 °C	19.8	20	20.2	MHz
CIOCK	течиенсу	FCLKOUT	T <sub>A</sub> = -40 °C to 125 °C	19.6	20	20.4	MHz
Dut	y Cycle	FDUTY		45	50	55	%
Delay to	Data Valid	TDELAY				30	ns
Data I	Hold Time	THOLD		20			ns




Figure 4.1. Si8941 Clock Input




Figure 4.2. Si8946/47 Clock Output




Figure 4.3. Common-Mode Transient Immunity Characterization Circuit

Table 4.2. IEC 60747-17 Safety Limiting Values<sup>1</sup>

Parameter	Symbol	Test Condition	Characteristic	Unit
Safety Temperature	T <sub>S</sub>		150	°C
		θ <sub>JA</sub> = 90 °C/W		
		VDD = 5.5 V	050	
		T <sub>J</sub> = 150 °C	253	mA
0.51.1.1.0.101.0.10.00.00.00.00.00.00.00		T <sub>A</sub> = 25 °C		
Safety Input Current (WB Stretched SOIC-8)	Is	θ <sub>JA</sub> = 90 °C/W		
		VDD = 3.6 V		_
		T <sub>J</sub> = 150 °C	386	mA
		T <sub>A</sub> = 25 °C		
		θ <sub>JA</sub> = 112 °C/W	203	
		VDD = 5.5 V		
		T <sub>J</sub> = 150 °C		mA
		T <sub>A</sub> = 25 °C		
Safety Input Current (NB SOIC-8)	I <sub>S</sub>	θ <sub>JA</sub> = 112 °C/W		
		VDD = 3.6 V	- 1-	
		T <sub>J</sub> = 150 °C	310	mA
		T <sub>A</sub> = 25 °C		
		θ <sub>JA</sub> = 90 °C/W		
Safety Input Power (WB Stretched SOIC-8)	P <sub>S</sub>	T <sub>J</sub> = 150 °C	1389	mW
		T <sub>A</sub> = 25 °C		
		θ <sub>JA</sub> = 112 °C/W		
Safety Input Power (NB SOIC-8)	P <sub>S</sub>	T <sub>J</sub> = 150 °C	1116	mW
•		T <sub>A</sub> = 25 °C		

# Note:

1. Maximum value allowed in the event of a failure. Refer to the thermal derating curves below.

**Table 4.3. Thermal Characteristics** 

Parameter	Symbol	WB Stretched SOIC-8	NB SOIC-8	Unit
IC Junction-to-Air Thermal Resistance	$\theta_{JA}$	90	112	°C/W




Figure 4.4. WB Stretched SOIC-8 Thermal Derating Curve for Safety Limiting Current




Figure 4.5. NB SOIC-8 Thermal Derating Curve for Safety Limiting Current

Table 4.4. Absolute Maximum Ratings<sup>1</sup>

Parameter	Symbol	Min	Max	Unit
Storage Temperature	T <sub>STG</sub>	-65	150	°C
Ambient Temperature Under Bias	T <sub>A</sub>	<b>–</b> 40	125	°C
Junction Temperature	TJ	_	150	°C
Supply Voltage	VDDA, VDDB	-0.5	6.0	V
Input Voltage respect to GNDA	VAIP, VAIN	-0.5	VDDA+ 0.5	V
Output Sink or Source Current	I <sub>O</sub>	_	5	mA
Total Power Dissipation	P <sub>T</sub>	_	212	mW
Lead Solder Termperature (10 s)		_	260	°C
Human Body Model ESD Rating		6000	_	V
Capacitive Discharge Model ESD Rating		2000	_	V

<sup>1.</sup> Permanent device damage may occur if the absolute maximum ratings are exceeded. Functional operation should be restricted to conditions as specified in the operational sections of the data sheet.

## 4.1 Regulatory Information

# Table 4.5. Regulatory Information<sup>1, 2</sup>

## **CSA**

The Si8941/46/47 is certified under CSA. For more details, see Master Contract Number 232873.

62368-1: Up to 600 V<sub>RMS</sub> reinforced insulation working voltage; up to 1000 V<sub>RMS</sub> basic insulation working voltage.

## **VDE**

The Si8941/46/47 is pending certification under VDE. For more details, see File 5028467.

IEC60747-17: Up to 2121 V<sub>peak</sub> for reinforced insulation working voltage.

EN62368-1: Up to 600 V<sub>RMS</sub> reinforced insulation working voltage; up to 1000 V<sub>RMS</sub> basic insulation working voltage.

## UL

The Si8941/46/47 is certified under UL1577 component recognition program. For more details, see File E257455.

Rated up to 5000 V<sub>RMS</sub> isolation voltage for basic protection.

#### CQC

The Si8941/46/47 is certified under GB4943.1-2011.

Rated up to 250  $V_{RMS}$  reinforced insulation working voltage at 5000 meters.

## Note:

- 1. Regulatory Certifications apply to 5 kV<sub>RMS</sub> rated devices which are production tested to 6.0 kV<sub>RMS</sub> for 1 sec.
- 2. Regulatory Certifications apply to 2.5 kV<sub>RMS</sub> rated devices which are production tested to 3.0 kV<sub>RMS</sub> for 1 sec.

Table 4.6. Insulation and Safety-Related Specifications

			Value		Unit	
Parameter	Symbol Test Condition		WB Stretched SOIC-8	NB SOIC-8		
Nominal External Air Gap (Clearance)	CLR		8.0	4.0	mm	
Nominal External Tracking (Creepage)	CRP		8.0	4.0	mm	
Minimum Internal Gap (Internal Clearance)	DTI		36	36	μm	
Tracking Resistance	PTI or CTI	IEC60112	600	600	V	
Erosion Depth	ED		0.04	0.04	mm	
Resistance (Input-Output)	R <sub>IO</sub>		10 <sup>12</sup>	10 <sup>12</sup>	Ω	
Capacitance (Input-Output)	C <sub>IO</sub>	f = 1 MHz	1	1	pF	

#### Note:

1. To determine resistance and capacitance, the Si8941/46/47 is converted into a 2-terminal device. Pins 1–4 are shorted together to form the first terminal, and pins 5–8 are shorted together to form the second terminal. The parameters are then measured between these two terminals.

Table 4.7. IEC 60664-1 Ratings

		Specif	ication
Parameter	Test Conditions	WB Stretched SOIC-8	NB SOIC-8
Basic Isolation Group	Material Group	I	I
Installation	Rated Mains Voltages ≤ 150 V <sub>RMS</sub>	I-IV	I-IV
Installation  Classification	Rated Mains Voltages ≤ 300 V <sub>RMS</sub>	I-IV	I-IV
	Rated Mains Voltages ≤ 600 V <sub>RMS</sub>	I-IV	I-III

Table 4.8. IEC 60747-17 Insulation Characteristics<sup>1</sup>

			Characteri		
Parameter	Symbol	Test Condition	WB Stretched SOIC-8	NB SOIC8	Unit
Maximum Working Insulation Voltage	V <sub>IORM</sub>		1500	1500	V <sub>RMS</sub>
Maximum Repetitive Isolation Voltage	V <sub>IORM</sub>		2121	2121	$V_{peak}$
Input to Output Test Voltage	$V_PR$	Method b1 $(V_{IORM} \times 1.875 = V_{PR}, 100\%$ Production Test, $t_m = 1$ sec, $Partial\ Discharge < 5\ pC)$	3976	3976	$V_{peak}$
Maximum Transient Isola- tion Voltage	V <sub>IOTM</sub>	t = 60 sec	8000	4000	$V_{peak}$
Maximum Surge Isolation Voltage	V <sub>IOSM</sub>	Test voltage is ≥ 1.3 x V <sub>IMP</sub> , mini- mum 10000 V <sub>peak</sub> and 1.2 μs/50 μs	10400	10400	$V_{peak}$
Maximum Impulse Voltage	V <sub>IMP</sub>		8000	5656	V <sub>peak</sub>
Pollution Degree		DIN VDE 0110	2	2	Ω
Insulation Resistance	R <sub>S</sub>	T <sub>AMB</sub> = T <sub>S</sub> , V <sub>IO</sub> = 500 V	>10 <sup>9</sup>	>10 <sup>9</sup>	Ω

<sup>1.</sup> This isolator is suitable for reinforced electrical isolation only within the safety limit data. Maintenance of the safety data is ensured by protective circuits. The Si8941/46/47 provides a climate classification of 40/125/21.

# 4.2 Typical Operating Characteristics




Figure 4.6. Si8941 Nonlinearity (%) vs. Temperature (°C)




Figure 4.8. Si8941B Nonlinearity (%) vs. Input Signal Amplitude (mV)




Figure 4.10. Si8946B Nonlinearity (%) vs. Input Signal Amplitude (mV)




Figure 4.7. Si8941 Nonlinearity (%) vs. VDDA Supply (V)




Figure 4.9. Si8941A Nonlinearity (%) vs. Input Signal Amplitude (mV)




Figure 4.11. Si8946A Nonlinearity (%) vs. Input Signal Amplitude (mV)




Figure 4.12. Si8947B Nonlinearity (%) vs. Input Signal Amplitude (mV)




Figure 4.13. Si8947A Nonlinearity (%) vs. Input Signal Amplitude (mV)




Figure 4.14. Si8941 Signal-to-Noise Ratio (dB) vs. Temperature (°C)




Figure 4.15. Si8941 Signal-to-Noise Ratio (dB) vs. VDDA Supply (V)




Figure 4.16. Si8941B Signal-to-Noise Ratio (dB) vs. Input Signal Amplitude (mV)




Figure 4.17. Si8941A Signal-to-Noise Ratio (dB) vs. Input Signal Amplitude (mV)




Figure 4.18. Si8941 Signal-to-Noise Ratio (dB) vs. Input Signal Frequency (kHz)




Figure 4.20. Si8941 Total Harmonic Distortion (dB) vs. Temperature (°C)




Figure 4.22. Si8941B Total Harmonic Distortion (dB) vs. Input Signal Amplitude (mV)




Figure 4.19. Si8941 Signal-to-Noise Ratio (dB) vs. MCLK (MHz)




Figure 4.21. Si8941 Total Harmonic Distortion (dB) vs. VDDA Supply (V)




Figure 4.23. Si8941A Total Harmonic Distortion (dB) vs. Input Signal Amplitude (mV)




Figure 4.24. Si8941 Total Harmonic Distortion (dB) vs. Input Signal Frequency (kHz)




Figure 4.26. Input Offset (mV) vs. Temperature (°C)




Figure 4.28. Si8941 Input Offset (mV) vs. MCLK (MHz)




Figure 4.25. Si8941 Total Harmonic Distortion (dB) vs. MCLK (MHz)




Figure 4.27. Input Offset (mV) vs. VDDA Supply (V)




Figure 4.29. Si8941 Common-Mode Rejection Ratio (dB) vs. Input Signal Frequency (kHz)




Figure 4.30. IDDA (mA) vs. Temperature (°C)




Figure 4.32. Si8941 IDDB (mA) vs. MCLK (MHz)




Figure 4.34. Si8941 Gain Error (%) vs. MCLK (MHz)




Figure 4.31. Si8941 IDDB (mA) vs. Temperature (°C)




Figure 4.33. Si8941 Gain Error (%) vs. Temperature (°C)






Figure 4.35. Si8946 Internal Clock Frequency (MHz) vs. Temperature (°C)








Figure 4.37. Si8941 Power Supply Rejection Ratio (dB) vs. Input Signal Frequency (kHz)

# 5. Pin Descriptions




Table 5.1. Si894x Pin Descriptions

Name	Pin Number	Description
VDDA	1	Input side power supply
AIP	2	Analog input high
AIN	3	Analog input low
GNDA	4	Input side ground
GNDB	5	Output side ground
ADAT	6	Delta-Sigma modulator data output
ACLK	7	Delta-Sigma modulator clock (input on Si8941, output on Si8946/47)
VDDB	8	Output side power supply

# 6. Packaging

# 6.1 Package Outline: 8-Pin Wide Body Stretched SOIC

The figure below illustrates the package details for the Si8941/46/47 in a 8-Pin Wide Body Stretched SOIC package. The table lists the values for the dimensions shown in the illustration.




Figure 6.1. 8-Pin Wide Body Stretched SOIC Package

Table 6.1. 8-Pin Wide Body Stretched SOIC Package Diagram Dimensions

Dimension	MIN	MAX
A	2.49	2.79
A1	0.36	0.46
b	0.30	0.51
С	0.20	0.33
D	5.74	5.94
E	11.25	11.76
E1	7.39	7.59
е	1.27	BSC
L	0.51	1.02
h	0.25	0.76
θ	0°	8°

Dimension	MIN	MAX
aaa	_	0.25
bbb	_	0.25
ccc	_	0.10

- 1. All dimensions shown are in millimeters (mm) unless otherwise noted.
- 2. Dimensioning and Tolerancing per ANSI Y14.5M-1994.
- 3. Recommended reflow profile per JEDEC J-STD-020C specification for small body, lead-free components.

# 6.2 Package Outline: 8-Pin Narrow Body SOIC

The figure below illustrates the package details for the Si8941/46/47 in an 8-Pin Narrow Body SOIC package. The table lists the values for the dimensions shown in the illustration.




Figure 6.2. 8-Pin Narrow Body SOIC Package

Table 6.2. 8-Pin Narrow Body SOIC Package Diagram Dimensions

Dimension	Min	Max
А	1.35	1.75
A1	0.10	0.25
A2	1.40 REF	1.55 REF
В	0.33	0.51
С	0.19	0.25
D	4.80	5.00
E	3.80	4.00
е	1.27	BSC
Н	5.80	6.20
h	0.25	0.50
L	0.40	1.27
α	0°	8°

Max Min Dimension

- 1. All dimensions shown are in millimeters (mm) unless otherwise noted.
- 2. Dimensioning and Tolerancing per ANSI Y14.5M-1982.
- 3. This drawing conforms to JEDEC Outline MS-012.
- 4. Recommended card reflow profile is per the JEDEC/IPC J-STD-020B specification for Small Body Components.

## 6.3 Land Pattern: 8-Pin Wide Body Stretched SOIC

The figure below illustrates the recommended land pattern details for the Si8941/46/47 in a 8-Pin Wide Body Stretched SOIC package. The table lists the values for the dimensions shown in the illustration.




Figure 6.3. 8-Pin Wide Body Stretched SOIC Land Pattern

Table 6.3. 8-Pin Wide Body Stretched SOIC Land Pattern Dimensions<sup>2</sup>

Dimension	Feature	(mm)
C1	Pad Column Spacing	10.60
E	Pad Row Pitch	1.27
X1	Pad Width	0.60
Y1	Pad Length	1.85

## Note:

## General

- 1. All dimensions shown are at Maximum Material Condition (MMC). Least Material Condition (LMC) is calculated based on a Fabrication Allowance of 0.05 mm.
- 2. This Land Pattern Design is based on the IPC-7351 guidelines.

## Solder Mask Design

1. All metal pads are to be non-solder mask defined (NSMD). Clearance between the solder mask and the metal pad is to be 60 µm minimum, all the way around the pad.

## Stencil Design

- 1. A stainless steel, laser-cut and electro-polished stencil with trapezoidal walls should be used to assure good solder paste release.
- 2. The stencil thickness should be 0.125 mm (5 mils).
- 3. The ratio of stencil aperture to land pad size should be 1:1 for all perimeter pins.

## **Card Assembly**

- 1. A No-Clean, Type-3 solder paste is recommended.
- 2. The recommended card reflow profile is per the JEDEC/IPC J-STD-020 specification for Small Body Components.

## 6.4 Land Pattern: 8-Pin Narrow Body SOIC

The figure below illustrates the recommended land pattern details for the Si8941/46/47 in an 8-Pin Narrow Body SOIC package. The table lists the values for the dimensions shown in the illustration.




Figure 6.4. 8-Pin Narrow Body SOIC Land Pattern

Table 6.4. 8-Pin Narrow Body SOIC Land Pattern Dimensions

Symbol	mm
C1	5.40
E	1.27
X1	0.60
Y1	1.55

- 1. This Land Pattern Design is based on IPC-7351 pattern SOIC127P600X173-8N for Density Level B (Median Land Protrusion).
- 2. All feature sizes shown are at Maximum Material Condition (MMC) and a card fabrication tolerance of 0.05 mm is assumed.

# 6.5 Top Marking: 8-Pin Wide Body Stretched SOIC

The figure below illustrates the top markings for the Si8941/46/47 in an 8-Pin Wide Body Stretched package. The table explains the top marks shown in the illustration.




Figure 6.5. Si894x 8-Pin Wide Body Stretched SOIC Top Marking

Table 6.5. 8-Pin Wide Body Stretched SOIC Top Mark Explanation

Line 1 Marking:	Customer Part Number	Si8941 or Si8946 or Si8947 Delta-Sigma Modulators  X = Clock Source/Speed  • 1 = external (Si8941)  • 6 = internal 10 MHz (Si8946)  • 7 = internal 20 MHz (Si8947)  S = Input Range:
		<ul> <li>A = ±62.5 mV</li> <li>B = ±250 mV</li> <li>V = Insulation rating:</li> <li>D = 5.0 kVrms</li> </ul>
Line 2 Marking:	TTTTTT = Mfg Code	Manufacturing Code from the Assembly Purchase Order form.
Line 3 Marking:	YY = Year  WW = Work Week  Circle = 43 mils Diameter  Left-Justified	Assigned by the Assembly House. Corresponds to the year and work week of the mold date.

# 6.6 Top Marking: 8-Pin Narrow Body SOIC

The figure below illustrates the top markings for the Si8941/46/47 in an 8-Pin Narrow Body SOIC package. The table explains the top marks shown in the illustration.




Figure 6.6. 8-Pin Narrow Body SOIC Top Marking

Table 6.6. 8-Pin Narrow Body SOIC Top Mark Explanation

Line 1 Marking:	Customer Part Number	Si8941 or Si8946 or Si8947 Delta-Sigma Modulators  X = Clock Source/Speed  • 1 = external (Si8941)  • 6 = internal 10 MHz (Si8946)  • 7 = internal 20 MHz (Si8947)  S = Input Range:  • A = ±62.5 mV  • B = ±250 mV  V = Insulation rating:  • B = 2.5 kVrms
Line 2 Marking:	CC = Country of Origin ISO Code Abbreviation  YY = Year  WW = Work Week	Assigned by the Assembly House. Corresponds to the year and work week of the mold date.
Line 3 Marking:	TTTTTT = Mfg Code  Circle = 19.7 mils Diameter  Left-Justified	Manufacturing Code from the Assembly Purchase Order form.

# 7. Revision History

## Revision 206439A

December, 2022

· Updated decimal-based revision number to alphanumeric code.

## Revision 0.8

September, 2022

- · Updated Safety Approvals on front page.
- · Updated minimum supply currents in 4. Electrical Specifications.
- · Updated 4.1 Regulatory Information.

## Revision 0.7

April, 2021

- · Updated Applications and Key Features on front page.
- Updated 4. Electrical Specifications after full characterization.
- · Added Automotive OPNs to 1. Ordering Guide.
- Updated Table 4.6 Insulation and Safety-Related Specifications on page 14.
- · Numerous clarifications throughout.

## Revision 0.5


March, 2019

- · Updated specifications.
- Added narrow body SOIC package.
- · Added timing diagram.

## Revision 0.1

January, 2018

· Initial release.





skyworksinc.com



skyworksinc.com/quality



Support & Resources skyworksinc.com/support

# Copyright © 2022 Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc. ("Skyworks") products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks' Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Skyworks products could lead to personal injury, death, physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of Skyworks' published specifications or parameters.

Skyworks, the Skyworks symbol, Sky5®, SkyOne®, SkyBlue™, Skyworks Green™, ClockBuilder®, DSPLL®, ISOmodem®, ProSLIC®, and SiPHY® are trademarks or registered trademarks of Skyworks Solutions, Inc. or its subsidiaries in the United States and other countries. Third-party brands and names are for identification purposes only and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksinc.com, are incorporated by reference.