SFH 2701

Chip LED High Speed PIN Photodiode





Applications

 Industrial Automation (Machine Controls, Light Barriers, Vision Controls)

Features:

- Package: Epoxy, diffuse
- ESD: 2 kV acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)
- Especially suitable for applications from 400 nm to 1050 nm
- Fast switching time within the specified wavelength
- Fast switching time at low reverse voltage (<5V)
- Ultra short decay time ("slow tail")
- IEC Standard 3216 Chipled package

Ordering Information

Туре	Photocurrent ¹⁾	Photocurrent	Ordering Code
		typ.	
	$E_{e} = 0.5 \text{ mW/cm}^{2}; \lambda = 650 \text{ nm}; V_{R} = 5 \text{ V}$	/ $E_{e} = 0.5 \text{ mW/cm}^{2}; \lambda = 650 \text{ nm}; V_{R} = 5 \text{ V}$	V
	l _P	l _P	
SFH 2701	≥ 0.9 µA	1.2 µA	Q65110A2960



Maximum Ratings

T _A = 25 °C			
Parameter	Symbol		Values
Operating Temperature	T _{op}	min.	-40 °C
	- 1-	max.	85 °C
Storage temperature	T _{stg}	min.	-40 °C
	otg	max.	85 °C
Reverse voltage	V _R	max.	15 V
Reverse voltage	V _R	max.	20 V
$t \le 120 \text{ s}; \text{ T}_{A} = 0 \text{ °C}$			
ESD withstand voltage	V _{ESD}	max.	2 kV
acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)	200		



Characteristics

onaraotonotioo			
T _A = 25 °C			
Parameter	Symbol		Values
Spectral sensitivity λ = 650 nm	S	typ.	0.45 A / W
Spectral sensitivity λ = 780 nm	S	typ.	0.5 A / W
Wavelength of max sensitivity	$\lambda_{_{Smax}}$	typ.	820 nm
Spectral range of sensitivity	$\lambda_{10\%}$	typ.	400 1050 nm
Photocurrent $E_e = 0.5 \text{ mW/cm}^2$; $\lambda = 780 \text{ nm}$; $V_R = 5 \text{ V}$	I _P	typ.	1.4 µA
Radiant sensitive area	А	typ.	0.36 mm ²
Dimensions of active chip area	L x W	typ.	0.6 x 0.6 mm x mm
Distance chip front to case surface	Н	typ.	0.3 mm
Half angle	φ	typ.	60 °
Dark current V _R = 5 V	Ι _R	typ. max.	0.045 nA 5 nA
Rise time V _R = 5 V; R _L = 50 Ω; λ = 650 nm; I _P = 1 mA	t,	typ.	1.8 ns
Rise time V _R = 5 V; R _L = 50 Ω; λ = 780 nm; I _P = 1 mA	t _r	typ.	2 ns
Fall time V _R = 5 V; R _L = 50 Ω; λ = 650 nm; I _P = 1 mA	t _f	typ.	1.8 ns
Fall time V _R = 5 V; R _L = 50 Ω; λ = 780 nm; I _P = 1 mA	t _f	typ.	2 ns
Forward voltage λ = 0 nm	V _F	typ.	0.8 V
Capacitance V _R = 0 V; f = 1 MHz; E = 0	C ₀	typ. max.	3 pF 5 pF
Noise equivalent power NEP = 17.9 x 10 ⁻¹⁵ x $(I_R)^{1/2}/S_\lambda$ V_R = 5 V, λ = 650 nm	NEP	typ.	0.009 pW / Hz ^{1/2}
Temperature coefficient of sensitivity $\lambda = 650 \text{ nm}$	TC	typ.	-0.03 % / K
Temperature coefficient of sensitivity λ = 780 nm	TC	typ.	-0.01 % / K



Relative Spectral Sensitivity ^{2), 3)}

 $S_{rel} = f(\lambda)$



Directional Characteristics ^{2), 3)}

 $S_{rel} = f(\phi)$





Dark Current ^{2), 3)}

 $I_{R} = f(V_{R}); E = 0$



Switching Time ^{2), 3)} t_r , $t_f = f (V_R)$; $I_P = 200 \ \mu A$; $R_L = 50 \ \Omega$; $\lambda = 650 \ nm$





Dark Current ²⁾

 $I_{R} = f(T_{A}); E = 0; V_{R} = 5 V$





Dimensional Drawing⁴⁾



1	Cathode
2	Anode

Pin



Recommended Solder Pad⁴⁾





Reflow Soldering Profile

Product complies to MSL Level 3 acc. to JEDEC J-STD-020E



Profile Feature	Symbol	Pb	b-Free (SnAgCu) Assembly		Unit
		Minimum	Recommendation	Maximum	
Ramp-up rate to preheat ^{*)} 25 °C to 150 °C			2	3	K/s
Time t _s T _{smin} to T _{Smax}	t _s	60	100	120	S
Ramp-up rate to peak ^{*)} T_{smax} to T_{p}			2	3	K/s
Liquidus temperature	TL		217		°C
Time above liquidus temperature	t		80	100	S
Peak temperature	Τ _Ρ		245	260	°C
Time within 5 °C of the specified peak temperature T_p - 5 K	t _P	10	20	30	S
Ramp-down rate* T _P to 100 °C			3	6	K/s
Time 25 °C to T _P				480	S

Discontinued

All temperatures refer to the center of the package, measured on the top of the component

* slope calculation DT/Dt: Dt max. 5 s; fulfillment for the whole T-range



SFH 2701

Taping 4)



C63062-A3843-B2-02



Tape and Reel ⁵⁾



Reel Dimensions

А	W	N _{min}	W ₁	$W_{2 \max}$	Pieces per PU
180 mm	8 + 0.3 / - 0.1 mm	60 mm	8.4 + 2 mm	14.4 mm	3000



Barcode-Product-Label (BPL)



Dry Packing Process and Materials⁴⁾





Notes

The evaluation of eye safety occurs according to the standard IEC 62471:2006 (photo biological safety of lamps and lamp systems). Within the risk grouping system of this IEC standard, the device specified in this data sheet fall into the class **exempt group (exposure time 10000 s)**. Under real circumstances (for exposure time, conditions of the eye pupils, observation distance), it is assumed that no endangerment to the eye exists from these devices. As a matter of principle, however, it should be mentioned that intense light sources have a high secondary exposure potential due to their blinding effect. When looking at bright light sources (e.g. headlights), temporary reduction in visual acuity and afterimages can occur, leading to irritation, annoyance, visual impairment, and even accidents, depending on the situation.

Subcomponents of this device contain, in addition to other substances, metal filled materials including silver. Metal filled materials can be affected by environments that contain traces of aggressive substances. Therefore, we recommend that customers minimize device exposure to aggressive substances during storage, production, and use. Devices that showed visible discoloration when tested using the described tests above did show no performance deviations within failure limits during the stated test duration. Respective failure limits are described in the IEC60810.

For further application related information please visit www.osram-os.com/appnotes



Disclaimer

Attention please!

The information describes the type of component and shall not be considered as assured characteristics. Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.

For information on the types in question please contact our Sales Organization.

If printed or downloaded, please find the latest version on the OSRAM OS website.

Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office. By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

Product and functional safety devices/applications or medical devices/applications

OSRAM OS components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.

OSRAM OS products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using OSRAM OS components in product safety devices/applications or medical devices/applications, buyer and/or customer has to inform the local sales partner of OSRAM OS immediately and OSRAM OS and buyer and /or customer will analyze and coordinate the customer-specific request between OSRAM OS and buyer and/or customer.



Glossary

- ¹⁾ **Photocurrent:** The photocurrent values are measured (by irradiating the devices with a homogenous light source and applying a voltage to the device) with a tolerance of ±11 %.
- ²⁾ **Typical Values:** Due to the special conditions of the manufacturing processes of semiconductor devices, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.
- ³⁾ **Testing temperature:** TA = 25°C (unless otherwise specified)
- ⁴⁾ **Tolerance of Measure:** Unless otherwise noted in drawing, tolerances are specified with ±0.1 and dimensions are specified in mm.
- ⁵⁾ **Tape and Reel:** All dimensions and tolerances are specified acc. IEC 60286-3 and specified in mm.



Revision History			
Version	Date	Change	
1.3	2021-09-30	Schematic Transportation Box Dimensions of Transportation Box Brand Discontinued	



SFH 2701

 Published by OSRAM Opto Semiconductors GmbH
 EU RoHS and China RoHS compliant product

 Leibnizstraße 4, D-93055 Regensburg
 www.osram-os.com © All Rights Reserved.

 此产品符合欧盟 RoHS 指令的要求;

按照中国的相关法规和标准,不含有毒有害物质或元素。

e

Discontinued