

TL061, TL061A, TL061B, TL061Y, TL062, TL062A  
 TL062B, TL062Y, TL064, TL064A, TL064B, TL064Y  
**LOW-POWER JFET-INPUT OPERATIONAL AMPLIFIERS**

SLOS078F – NOVEMBER 1978 – REVISED JANUARY 1999

- Very Low Power Consumption
- Typical Supply Current . . . 200  $\mu$ A (Per Amplifier)
- Wide Common-Mode and Differential Voltage Ranges
- Low Input Bias and Offset Currents
- Common-Mode Input Voltage Range Includes  $V_{CC+}$
- Output Short-Circuit Protection
- High Input Impedance . . . JFET-Input Stage
- Internal Frequency Compensation
- Latch-Up-Free Operation
- High Slew Rate . . . 3.5 V/ $\mu$ s Typ


### description

The JFET-input operational amplifiers of the TL06\_ series are designed as low-power versions of the TL08\_ series amplifiers. They feature high input impedance, wide bandwidth, high slew rate, and low input offset and input bias currents. The TL06\_ series feature the same terminal assignments as the TL07\_ and TL08\_ series. Each of these JFET-input operational amplifiers incorporates well-matched, high-voltage JFET and bipolar transistors in a monolithic integrated circuit.

The C-suffix devices are characterized for operation from 0°C to 70°C. The I-suffix devices are characterized for operation from -40°C to 85°C, and the M-suffix devices are characterized for operation over the full military temperature range of -55°C to 125°C.


**TL061, TL061A, TL061B**

D, JG, P, OR PW PACKAGE  
 (TOP VIEW)




**TL061 . . . U PACKAGE**

(TOP VIEW)




**TL062, TL062A, TL062B**

D, JG, P, OR PW PACKAGE  
 (TOP VIEW)



**TL062 . . . U PACKAGE**


(TOP VIEW)



**TL064 . . . D, J, N, PW, OR W PACKAGE**

**TL064A, TL064B . . . D OR N PACKAGE**

(TOP VIEW)



NC – No internal connection



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.


PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.



Copyright © 1999, Texas Instruments Incorporated

**TL061, TL061A, TL061B, TL061Y, TL062, TL062A  
TL062B, TL062Y, TL064, TL064A, TL064B, TL064Y  
LOW-POWER JFET-INPUT OPERATIONAL AMPLIFIERS**

SLOS078F – NOVEMBER 1978 – REVISED JANUARY 1999



NC – No internal connection

**AVAILABLE OPTIONS**

T <sub>A</sub>	V <sub>I0 MAX</sub> AT 25°C	PACKAGED DEVICES					CHIP FORM (Y)
		SMALL OUTLINE (D008) <sup>†</sup>	SMALL OUTLINE (D014) <sup>†</sup>	PLASTIC DIP (N)	PLASTIC DIP (P)	TSSOP (PW)	
0°C to 70°C	15 mV 6 mV 3 mV	TL061CD TL061ACD TL061BCD			TL061CP TL061ACP TL061BCP	TL061CPW	TL061Y
	15 mV 6 mV 3 mV	TL062CD TL062ACD TL062BCD			TL062CP TL062ACP TL062BCP	TL062CPW	TL062Y
	15 mV 6 mV 3 mV		TL064CD TL064ACD TL064BCD	TL064CN TL064ACN TL064BCN		TL064CPW	TL064Y


T <sub>A</sub>	V <sub>I0 MAX</sub> AT 25°C	PACKAGE								
		SMALL OUTLINE (D008) <sup>†</sup>	SMALL OUTLINE (D014) <sup>†</sup>	CHIP CARRIER (FK)	CERAMIC DIP (J)	CERAMIC DIP (JG)	PLASTIC DIP (N)	PLASTIC DIP (P)	FLAT PACK (U)	FLAT PACK (W)
-40°C to 85°C	6 mV	TL061ID TL062ID	TL064ID				TL064IN	TL061IP TL062IP		
-55°C to 125°C	6 mV 6 mV 9 mV			TL061MFK TL062MFK TL064MFK	TL064MJ	TL061MJJG TL062MJJG			TL061MU TL062MU	TL064MW

<sup>†</sup> The D package is available taped and reeled. Add the suffix R to the device type (e.g., TL061CDR).


**TL061, TL061A, TL061B, TL061Y, TL062, TL062A  
TL062B, TL062Y, TL064, TL064A, TL064B, TL064Y**  
**LOW-POWER JFET-INPUT OPERATIONAL AMPLIFIERS**

SLOS078F – NOVEMBER 1978 – REVISED JANUARY 1999

**symbol (each amplifier)**



**schematic (each amplifier)**




C1 = 10 pF on TL061, TL062, and TL064  
Component values shown are nominal.

**TL061, TL061A, TL061B, TL061Y, TL062, TL062A  
TL062B, TL062Y, TL064, TL064A, TL064B, TL064Y**  
**LOW-POWER JFET-INPUT OPERATIONAL AMPLIFIERS**

SLOS078F – NOVEMBER 1978 – REVISED JANUARY 1999


**TL061Y chip information**

This chip, when properly assembled, has characteristics similar to the TL061. Thermal compression or ultrasonic bonding can be used on the doped-aluminum bonding pads. The chips can be mounted with conductive epoxy or a gold-silicon preform.



### TL062Y chip information

This chip, when properly assembled, has characteristics similar to the TL062. Thermal compression or ultrasonic bonding can be used on the doped-aluminum bonding pads. The chips can be mounted with conductive epoxy or a gold-silicon preform.




**TL061, TL061A, TL061B, TL061Y, TL062, TL062A  
TL062B, TL062Y, TL064, TL064A, TL064B, TL064Y**  
**LOW-POWER JFET-INPUT OPERATIONAL AMPLIFIERS**

SLOS078F – NOVEMBER 1978 – REVISED JANUARY 1999

**TL064Y chip information**

This chip, when properly assembled, has characteristics similar to the TL064. Thermal compression or ultrasonic bonding can be used on the doped-aluminum bonding pads. The chips can be mounted with conductive epoxy or a gold-silicon preform.



**TL061, TL061A, TL061B, TL061Y, TL062, TL062A  
TL062B, TL062Y, TL064, TL064A, TL064B, TL064Y  
LOW-POWER JFET-INPUT OPERATIONAL AMPLIFIERS**

SLOS078F – NOVEMBER 1978 – REVISED JANUARY 1999

**absolute maximum ratings over operating free-air temperature range (unless otherwise noted)<sup>†</sup>**

	<b>TL06_C TL06_AC TL06_BC</b>	<b>TL06_I</b>	<b>TL06_M</b>	<b>UNIT</b>
Supply voltage, $V_{CC+}$ (see Note 1)	18	18	18	V
Supply voltage, $V_{CC-}$ (see Note 1)	-18	-18	-18	V
Differential input voltage, $V_{ID}$ (see Note 2)	$\pm 30$	$\pm 30$	$\pm 30$	V
Input voltage, $V_I$ (see Notes 1 and 3)	$\pm 15$	$\pm 15$	$\pm 15$	V
Duration of output short circuit (see Note 4)	unlimited	unlimited	unlimited	
Continuous total dissipation	See Dissipation Rating Table			
Storage temperature range, $T_{STG}$	-65 to 150	-65 to 150	-65 to 150	$^{\circ}\text{C}$
Case temperature for 60 seconds	FK package		260	$^{\circ}\text{C}$
Lead temperature 1.6 mm (1/16 inch) from case for 60 seconds	J, JG, U, or W package		300	$^{\circ}\text{C}$
Lead temperature 1.6 mm (1/6 inch) from case for 10 seconds	D, N, P, or PW package	260	260	$^{\circ}\text{C}$

<sup>†</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- NOTES: 1. All voltage values except differential voltages are with respect to the midpoint between  $V_{CC+}$  and  $V_{CC-}$ .  
 2. Differential voltages are at IN+ with respect to IN-.  
 3. The magnitude of the input voltage must never exceed the magnitude of the supply voltage or 15 V, whichever is less.  
 4. The output may be shorted to ground or to either supply. Temperature and/or supply voltages must be limited to ensure that the dissipation rating is not exceeded.

**DISSIPATION RATING TABLE**

<b>PACKAGE</b>	<b><math>T_A \leq 25^{\circ}\text{C}</math> POWER RATING</b>	<b>DERATING FACTOR</b>	<b>DERATE ABOVE <math>T_A</math></b>	<b><math>T_A = 70^{\circ}\text{C}</math> POWER RATING</b>	<b><math>T_A = 85^{\circ}\text{C}</math> POWER RATING</b>	<b><math>T_A = 125^{\circ}\text{C}</math> POWER RATING</b>
D (8 pin)	680 mW	5.8 mW/ $^{\circ}\text{C}$	33 $^{\circ}\text{C}$	465 mW	378 mW	N/A
D (14 pin)	680 mW	7.6 mW/ $^{\circ}\text{C}$	60 $^{\circ}\text{C}$	604 mW	490 mW	N/A
FK	680 mW	11.0 mW/ $^{\circ}\text{C}$	88 $^{\circ}\text{C}$	680 mW	680 mW	273 mW
J	680 mW	11.0 mW/ $^{\circ}\text{C}$	88 $^{\circ}\text{C}$	680 mW	680 mW	273 mW
JG	680 mW	8.4 mW/ $^{\circ}\text{C}$	69 $^{\circ}\text{C}$	672 mW	546 mW	210 mW
N	680 mW	9.2 mW/ $^{\circ}\text{C}$	76 $^{\circ}\text{C}$	680 mW	597 mW	N/A
P	680 mW	8.0 mW/ $^{\circ}\text{C}$	65 $^{\circ}\text{C}$	640 mW	520 mW	N/A
PW (8 pin)	525 mW	4.2 mW/ $^{\circ}\text{C}$	25 $^{\circ}\text{C}$	336 mW	N/A	N/A
PW (14 pin)	700 mW	5.6 mW/ $^{\circ}\text{C}$	25 $^{\circ}\text{C}$	448 mW	N/A	N/A
U	675 mW	5.4 mW/ $^{\circ}\text{C}$	25 $^{\circ}\text{C}$	432 mW	351 mW	135 mW
W	680 mW	8.0 mW/ $^{\circ}\text{C}$	65 $^{\circ}\text{C}$	640 mW	520 mW	200 mW



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

**TL061, TL061A, TL061B, TL061Y, TL062, TL062A  
TL062B, TL062Y, TL064, TL064A, TL064B, TL064Y**  
**LOW-POWER JFET-INPUT OPERATIONAL AMPLIFIERS**

SLOS078F – NOVEMBER 1978 – REVISED JANUARY 1999

**electrical characteristics,  $V_{CC\pm} = \pm 15$  V (unless otherwise noted)**

PARAMETER	TEST CONDITIONS <sup>†</sup>	TL061C TL062C TL064C			TL061AC TL062AC TL064AC			UNIT
		MIN	TYP	MAX	MIN	TYP	MAX	
$V_{IO}$ Input offset voltage	$V_O = 0$ , $R_S = 50 \Omega$	$T_A = 25^\circ C$	3	15	3	6	mV	
		$T_A = \text{Full range}$		20		7.5		
$\alpha V_{IO}$ Temperature coefficient of input offset voltage	$V_O = 0$ , $R_S = 50 \Omega$ , $T_A = \text{Full range}$		10		10		$\mu V/^{\circ}C$	
$I_{IO}$ Input offset current	$V_O = 0$	$T_A = 25^\circ C$	5	200	5	100	pA	
		$T_A = \text{Full range}$		5		3		
$I_{IB}$ Input bias current <sup>‡</sup>	$V_O = 0$	$T_A = 25^\circ C$	30	400	30	200	pA	
		$T_A = \text{Full range}$		10		7		
$V_{ICR}$ Common-mode input voltage range	$T_A = 25^\circ C$		-12 ±11 to 15		-12 ±11 to 15		V	
$V_{OM}$ Maximum peak output voltage swing	$R_L = 10 k\Omega$ , $T_A = 25^\circ C$	±10	±13.5	±10	±13.5	V		
	$R_L \geq 10 k\Omega$ , $T_A = \text{Full range}$	±10		±10				
$A_{VD}$ Large-signal differential voltage amplification	$V_O = \pm 10 V$ , $R_L \geq 10 k\Omega$	$T_A = 25^\circ C$	3	6	4	6	V/mV	
		$T_A = \text{Full range}$	3		4			
$B_1$ Unity-gain bandwidth	$R_L = 10 k\Omega$ , $T_A = 25^\circ C$		1		1		MHz	
$r_i$ Input resistance	$T_A = 25^\circ C$		$10^{12}$		$10^{12}$		$\Omega$	
CMRR Common-mode rejection ratio	$V_{IC} = V_{ICR\min}$ , $V_O = 0$ , $R_S = 50 \Omega$ , $T_A = 25^\circ C$	70	86	80	86		dB	
$k_{SVR}$ Supply-voltage rejection ratio ( $\Delta V_{CC\pm}/\Delta V_{IO}$ )	$V_{CC} = \pm 9 V$ to $\pm 15 V$ , $V_O = 0$ , $R_S = 50 \Omega$ , $T_A = 25^\circ C$	70	95	80	95		dB	
$P_D$ Total power dissipation (each amplifier)	$V_O = 0$ , $T_A = 25^\circ C$ , No load		6	7.5	6	7.5	mW	
$I_{CC}$ Supply current (each amplifier)	$V_O = 0$ , $T_A = 25^\circ C$ , No load		200	250	200	250	$\mu A$	
$V_{O1}/V_{O2}$ Crosstalk attenuation	$A_{VD} = 100$ , $T_A = 25^\circ C$		120		120		dB	

<sup>†</sup>All characteristics are measured under open-loop conditions with zero common-mode input voltage unless otherwise specified. Full range for  $T_A$  is  $0^\circ C$  to  $70^\circ C$  for TL06\_C, TL06\_AC, and TL06\_BC and  $-40^\circ C$  to  $85^\circ C$  for TL06\_I.

<sup>‡</sup>Input bias currents of a FET-input operational amplifier are normal junction reverse currents, which are temperature sensitive as shown in Figure 15. Pulse techniques are used to maintain the junction temperature as close to the ambient temperature as possible.



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

**TL061, TL061A, TL061B, TL061Y, TL062, TL062A  
TL062B, TL062Y, TL064, TL064A, TL064B, TL064Y  
LOW-POWER JFET-INPUT OPERATIONAL AMPLIFIERS**

SLOS078F – NOVEMBER 1978 – REVISED JANUARY 1999

**electrical characteristics,  $V_{CC\pm} = \pm 15$  V (unless otherwise noted)**

PARAMETER	TEST CONDITIONS <sup>†</sup>	TL061BC			TL061I			UNIT	
		TL062BC			TL062I				
		TL064BC			TL064I				
$V_{IO}$	Input offset voltage	$V_O = 0$ , $R_S = 50 \Omega$	$T_A = 25^\circ C$	2	3	3	6	mV	
			$T_A = \text{Full range}$		5		9		
$\alpha V_{IO}$	Temperature coefficient of input offset voltage	$V_O = 0$ , $R_S = 50 \Omega$ , $T_A = \text{Full range}$		10		10		$\mu V^\circ C$	
$I_{IO}$	Input offset current	$V_O = 0$	$T_A = 25^\circ C$	5	100	5	100	pA	
			$T_A = \text{Full range}$		3		10	nA	
$I_{IB}$	Input bias current <sup>‡</sup>	$V_O = 0$	$T_A = 25^\circ C$	30	200	30	200	pA	
			$T_A = \text{Full range}$		7		20	nA	
$V_{ICR}$	Common-mode input voltage range	$T_A = 25^\circ C$		$\pm 11$	$-12$ to 15	$\pm 11$	$-12$ to 15	V	
$V_{OM}$	Maximum peak output voltage swing	$R_L = 10 k\Omega$ , $T_A = 25^\circ C$		$\pm 10$	$\pm 13.5$	$\pm 10$	$\pm 13.5$	V	
		$R_L \geq 10 k\Omega$ , $T_A = \text{Full range}$		$\pm 10$		$\pm 10$			
$A_{VD}$	Large-signal differential voltage amplification	$V_O = \pm 10 V$ ,	$T_A = 25^\circ C$	4	6	4	6	V/mV	
		$R_L \geq 10 k\Omega$	$T_A = \text{Full range}$		4		4		
$B_1$	Unity-gain bandwidth	$R_L = 10 k\Omega$ , $T_A = 25^\circ C$			1		1	MHz	
$r_i$	Input resistance	$T_A = 25^\circ C$		10 <sup>12</sup>		10 <sup>12</sup>		$\Omega$	
CMRR	Common-mode rejection ratio	$V_{IC} = V_{ICR\min}$ , $V_O = 0$ , $R_S = 50 \Omega$ , $T_A = 25^\circ C$		80	86	80	86	dB	
$k_{SVR}$	Supply-voltage rejection ratio ( $\Delta V_{CC\pm}/\Delta V_{IO}$ )	$V_{CC} = \pm 9 V$ to $\pm 15 V$ , $V_O = 0$ , $R_S = 50 \Omega$ , $T_A = 25^\circ C$		80	95	80	95	dB	
$P_D$	Total power dissipation (each amplifier)	$V_O = 0$ , No load		$T_A = 25^\circ C$ ,	6	7.5	6	7.5	mW
$I_{CC}$	Supply current (each amplifier)	$V_O = 0$ , No load		$T_A = 25^\circ C$ ,	200	250	200	250	$\mu A$
$V_{O1}/V_{O2}$	Crosstalk attenuation	$A_{VD} = 100$ , $T_A = 25^\circ C$		120		120		dB	

<sup>†</sup> All characteristics are measured under open-loop conditions with zero common-mode input voltage unless otherwise specified. Full range for  $T_A$  is  $0^\circ C$  to  $70^\circ C$  for TL06\_C, TL06\_AC, and TL06\_BC and  $-40^\circ C$  to  $85^\circ C$  for TL06\_I.

<sup>‡</sup> Input bias currents of a FET-input operational amplifier are normal junction reverse currents, which are temperature sensitive as shown in Figure 15. Pulse techniques are used to maintain the junction temperature as close to the ambient temperature as possible.

**TL061, TL061A, TL061B, TL061Y, TL062, TL062A  
TL062B, TL062Y, TL064, TL064A, TL064B, TL064Y  
LOW-POWER JFET-INPUT OPERATIONAL AMPLIFIERS**

SLOS078F – NOVEMBER 1978 – REVISED JANUARY 1999

**electrical characteristics,  $V_{CC\pm} = \pm 15$  V (unless otherwise noted)**

PARAMETER	TEST CONDITIONS†	TL061M TL062M			TL064M			UNIT
		MIN	TYP	MAX	MIN	TYP	MAX	
$V_{IO}$ Input offset voltage	$V_O = 0$ , $R_S = 50 \Omega$	$T_A = 25^\circ C$	3	6	3	9	15	mV
		$T_A = -55^\circ C$ to $125^\circ C$		9				
$\alpha_{VIO}$ Temperature coefficient of input offset voltage	$V_O = 0$ , $R_S = 50 \Omega$ , $T_A = -55^\circ C$ to $125^\circ C$		10		10			$\mu V/^\circ C$
$I_{IO}$ Input offset current	$V_O = 0$	$T_A = 25^\circ C$	5	100	5	100		pA
		$T_A = -55^\circ C$		20*		20*		nA
		$T_A = 125^\circ C$		20		20		
$I_{IB}$ Input bias current‡	$V_O = 0$	$T_A = 25^\circ C$	30	200	30	200		pA
		$T_A = -55^\circ C$		50*		50*		nA
		$T_A = 125^\circ C$		50		50		
$V_{ICR}$ Common-mode input voltage range	$T_A = 25^\circ C$		-12 $\pm 11.5$	to 15	-12 $\pm 11.5$	to 15		V
$V_{OM}$ Maximum peak output voltage swing	$R_L = 10 k\Omega$ , $T_A = 25^\circ C$	$\pm 10$	$\pm 13.5$		$\pm 10$	$\pm 13.5$		V
	$R_L \geq 10 k\Omega$ , $T_A = -55^\circ C$ to $125^\circ C$	$\pm 10$			$\pm 10$			
$AVD$ Large-signal differential voltage amplification	$V_O = \pm 10 V$ , $R_L \geq 10 k\Omega$	$T_A = 25^\circ C$	4	6	4	6		V/mV
		$T_A = -55^\circ C$ to $125^\circ C$	4		4			
$B_1$ Unity-gain bandwidth	$R_L = 10 k\Omega$ , $T_A = 25^\circ C$							MHz
$r_i$ Input resistance	$T_A = 25^\circ C$		10 <sup>12</sup>		10 <sup>12</sup>			$\Omega$
CMRR Common-mode rejection ratio	$V_{IC} = V_{ICR\min}$ , $V_O = 0$ , $R_S = 50 \Omega$ , $T_A = 25^\circ C$	80	86		80	86		dB
$k_{SVR}$ Supply-voltage rejection ratio ( $\Delta V_{CC\pm}/\Delta V_{IO}$ )	$V_{CC\pm} = \pm 9 V$ to $\pm 15 V$ , $V_O = 0$ , $R_S = 50 \Omega$ , $T_A = 25^\circ C$	80	95		80	95		dB
$P_D$ Total power dissipation (each amplifier)	$V_O = 0$ , No load	$T_A = 25^\circ C$	6	7.5	6	7.5		mW
$I_{CC}$ Supply current (each amplifier)	$V_O = 0$ , No load	$T_A = 25^\circ C$	200	250	200	250		$\mu A$
$V_{O1}/V_{O2}$ Crosstalk attenuation	$AVD = 100$ , $T_A = 25^\circ C$		120		120			dB

\* This parameter is not production tested.

† All characteristics are measured under open-loop conditions with zero common-mode voltage unless otherwise specified.

‡ Input bias currents of a FET-input operational amplifier are normal junction reverse currents, which are temperature sensitive as shown in Figure 15. Pulse techniques are used to maintain the junction temperature as close to the ambient temperature as possible.

**operating characteristics,  $V_{CC\pm} = \pm 15$  V,  $T_A = 25^\circ C$**

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
SR Slew rate at unity gain (see Note 5)	$V_I = 10 V$ , $C_L = 100 pF$ , See Figure 1	2	3.5		$V/\mu s$
$t_r$ Rise time	$V_I = 20 V$ , $C_L = 100 pF$ , See Figure 1	0.2			$\mu s$
Overshoot factor		10%			
$V_n$ Equivalent input noise voltage	$R_S = 20 \Omega$ , $f = 1 kHz$	42			$nV/\sqrt{Hz}$

NOTE 5: Slew rate at  $-55^\circ C$  to  $125^\circ C$  is  $0.7 V/\mu s$  min.



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

**TL061, TL061A, TL061B, TL061Y, TL062, TL062A  
TL062B, TL062Y, TL064, TL064A, TL064B, TL064Y**  
**LOW-POWER JFET-INPUT OPERATIONAL AMPLIFIERS**

SLOS078F – NOVEMBER 1978 – REVISED JANUARY 1999

**electrical characteristics,  $V_{CC\pm} = \pm 15$  V,  $T_A = 25^\circ\text{C}$  (unless otherwise noted)**

PARAMETER	TEST CONDITIONS†	TL061Y TL062Y TL064Y			UNIT
		MIN	TYP	MAX	
$V_{IO}$	$V_O = 0$ , $R_S = 50 \Omega$		3	15	mV
$\alpha V_{IO}$	$V_O = 0$ , $R_S = 50 \Omega$		10		$\mu\text{V}/^\circ\text{C}$
$I_{IO}$	$V_O = 0$		5	200	pA
$I_{IB}$	$V_O = 0$		30	400	pA
$V_{ICR}$	Common-mode input voltage range		$\pm 11$	$-12$ to $15$	V
$V_{OM}$	$R_L = 10 \text{ k}\Omega$	$\pm 10$	$\pm 13.5$		V
$A_{VD}$	$V_O = \pm 10$ V, $R_L \geq 2 \text{ k}\Omega$	3	6		V/mV
$B_1$	$R_L = 10 \text{ k}\Omega$		1		MHz
$r_i$			$10^{12}$		$\Omega$
CMRR	$V_{IC} = V_{ICR\min}$ , $V_O = 0$ , $R_S = 50 \Omega$	70	86		dB
$k_{SVR}$	$V_{CC} = \pm 9$ V to $\pm 15$ V, $V_O = 0$ , $R_S = 50 \Omega$	70	95		dB
$P_D$	$V_O = 0$ , No load		6	7.5	mW
$I_{CC}$	$V_O = 0$ , No load		200	250	$\mu\text{A}$
$V_{O1}/V_{O2}$	$A_{VD} = 100$		120		dB

† All characteristics are measured under open-loop conditions with zero common-mode voltage unless otherwise specified.

‡ Input bias currents of a FET-input operational amplifier are normal junction reverse currents, which are temperature sensitive as shown in Figure 15. Pulse techniques are used to maintain the junction temperature as close to the ambient temperature as possible.


**operating characteristics,  $V_{CC\pm} = \pm 15$  V,  $T_A = 25^\circ\text{C}$**

PARAMETER	TEST CONDITIONS	TL061Y TL062Y TL064Y			UNIT
		MIN	TYP	MAX	
SR	$V_I = 10$ mV, $R_L = 10 \text{ k}\Omega$ , $C_L = 100 \text{ pF}$ , See Figure 1	1.5	3.5		$\text{V}/\mu\text{s}$
$t_r$	$V_I = 20$ V, $R_L = 10 \text{ k}\Omega$ , $C_L = 100 \text{ pF}$ , See Figure 1		0.2		$\mu\text{s}$
Overshoot factor			10%		
$V_n$	$R_S = 20 \Omega$ , $f = 1$ kHz		42		$\text{nV}/\sqrt{\text{Hz}}$


**TL061, TL061A, TL061B, TL061Y, TL062, TL062A  
TL062B, TL062Y, TL064, TL064A, TL064B, TL064Y  
LOW-POWER JFET-INPUT OPERATIONAL AMPLIFIERS**

SLOS078F – NOVEMBER 1978 – REVISED JANUARY 1999


**PARAMETER MEASUREMENT INFORMATION**



**Figure 1. Unity-Gain Amplifier**



**Figure 2. Gain-of-10 Inverting Amplifier**



**Figure 3. Input Offset-Voltage Null Circuit**

**TL061, TL061A, TL061B, TL061Y, TL062, TL062A  
TL062B, TL062Y, TL064, TL064A, TL064B, TL064Y  
LOW-POWER JFET-INPUT OPERATIONAL AMPLIFIERS**

SLOS078F – NOVEMBER 1978 – REVISED JANUARY 1999

**TYPICAL CHARACTERISTICS**

**Table of Graphs**

	<b>FIGURE</b>
Maximum peak output voltage vs Supply voltage	4
Maximum peak output voltage vs Free-air temperature	5
Maximum peak output voltage vs Load resistance	6
Maximum peak output voltage vs Frequency	7
Differential voltage amplification vs Free-air temperature	8
Large-signal differential voltage amplification vs Frequency	9
Phase shift vs Frequency	9
Supply current vs Supply voltage	10
Supply current vs Free-air temperature	11
Total power dissipation vs Free-air temperature	12
Common-mode rejection ratio vs Free-air temperature	13
Normalized unity-gain bandwidth vs Free-air temperature	14
Normalized slew rate vs Free-air temperature	14
Normalized phase shift vs Free-air temperature	14
Input bias current vs Free-air temperature	15
Voltage-follower large-signal pulse response vs Time	16
Output voltage vs Elapsed time	17
Equivalent input noise voltage vs Frequency	18

**TL061, TL061A, TL061B, TL061Y, TL062, TL062A  
TL062B, TL062Y, TL064, TL064A, TL064B, TL064Y**  
**LOW-POWER JFET-INPUT OPERATIONAL AMPLIFIERS**

SLOS078F – NOVEMBER 1978 – REVISED JANUARY 1999

**TYPICAL CHARACTERISTICS†**




Figure 4




Figure 5




Figure 6




Figure 7

† Data at high and low temperatures are applicable only within the specified operating free-air temperature ranges of the various devices.




POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

**TL061, TL061A, TL061B, TL061Y, TL062, TL062A  
TL062B, TL062Y, TL064, TL064A, TL064B, TL064Y**  
**LOW-POWER JFET-INPUT OPERATIONAL AMPLIFIERS**

SLOS078F – NOVEMBER 1978 – REVISED JANUARY 1999


**TYPICAL CHARACTERISTICS<sup>†</sup>**

**DIFFERENTIAL VOLTAGE AMPLIFICATION  
vs  
FREE-AIR TEMPERATURE**



**Figure 8**

**LARGE-SIGNAL  
DIFFERENTIAL VOLTAGE  
AMPLIFICATION AND PHASE SHIFT  
vs  
FREQUENCY**



**Figure 9**

<sup>†</sup> Data at high and low temperatures are applicable only within the specified operating free-air temperature ranges of the various devices.

**TL061, TL061A, TL061B, TL061Y, TL062, TL062A  
TL062B, TL062Y, TL064, TL064A, TL064B, TL064Y  
LOW-POWER JFET-INPUT OPERATIONAL AMPLIFIERS**

SLOS078F – NOVEMBER 1978 – REVISED JANUARY 1999

**TYPICAL CHARACTERISTICS<sup>†</sup>**




Figure 10




Figure 11




Figure 12




Figure 13

<sup>†</sup> Data at high and low temperatures are applicable only within the specified operating free-air temperature ranges of the various devices.

## TYPICAL CHARACTERISTICS




Figure 14




Figure 15




Figure 16

**TL061, TL061A, TL061B, TL061Y, TL062, TL062A  
 TL062B, TL062Y, TL064, TL064A, TL064B, TL064Y**  
**LOW-POWER JFET-INPUT OPERATIONAL AMPLIFIERS**

SLOS078F – NOVEMBER 1978 – REVISED JANUARY 1999

**TYPICAL CHARACTERISTICS**




Figure 17





Figure 18


## APPLICATION INFORMATION

**Table of Application Diagrams**


APPLICATION DIAGRAM	PART NUMBER	FIGURE
Instrumentation amplifier	TL064	19
0.5-Hz square-wave oscillator	TL061	20
High-Q notch filter	TL061	21
Audio-distribution amplifier	TL064	22
Low-level light detector preamplifier	TL061	23
AC amplifier	TL061	24
Microphone preamplifier with tone control	TL061	25
Instrumentation amplifier	TL062	26
IC preamplifier	TL062	27



**Figure 19. Instrumentation Amplifier**



**Figure 20. 0.5-Hz Square-Wave Oscillator**




**Figure 21. High-Q Notch Filter**


**TL061, TL061A, TL061B, TL061Y, TL062, TL062A  
TL062B, TL062Y, TL064, TL064A, TL064B, TL064Y**  
**LOW-POWER JFET-INPUT OPERATIONAL AMPLIFIERS**

SLOS078F – NOVEMBER 1978 – REVISED JANUARY 1999

**APPLICATION INFORMATION**




**Figure 22. Audio-Distribution Amplifier**




**Figure 23. Low-Level Light Detector Preamplifier**


## APPLICATION INFORMATION



**Figure 24. AC Amplifier**



**Figure 25. Microphone Preamplifier With Tone Control**



**Figure 26. Instrumentation Amplifier**

**TL061, TL061A, TL061B, TL061Y, TL062, TL062A  
TL062B, TL062Y, TL064, TL064A, TL064B, TL064Y**  
**LOW-POWER JFET-INPUT OPERATIONAL AMPLIFIERS**

SLOS078F – NOVEMBER 1978 – REVISED JANUARY 1999

## APPLICATION INFORMATION

### IC PREAMPLIFIER RESPONSE CHARACTERISTICS





Figure 27. IC Preamplifier

### **IMPORTANT NOTICE**

Texas Instruments and its subsidiaries (TI) reserve the right to make changes to their products or to discontinue any product or service without notice, and advise customers to obtain the latest version of relevant information to verify, before placing orders, that information being relied on is current and complete. All products are sold subject to the terms and conditions of sale supplied at the time of order acknowledgement, including those pertaining to warranty, patent infringement, and limitation of liability.

TI warrants performance of its semiconductor products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are utilized to the extent TI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.

CERTAIN APPLICATIONS USING SEMICONDUCTOR PRODUCTS MAY INVOLVE POTENTIAL RISKS OF DEATH, PERSONAL INJURY, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE ("CRITICAL APPLICATIONS"). TI SEMICONDUCTOR PRODUCTS ARE NOT DESIGNED, AUTHORIZED, OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT DEVICES OR SYSTEMS OR OTHER CRITICAL APPLICATIONS. INCLUSION OF TI PRODUCTS IN SUCH APPLICATIONS IS UNDERSTOOD TO BE FULLY AT THE CUSTOMER'S RISK.

In order to minimize risks associated with the customer's applications, adequate design and operating safeguards must be provided by the customer to minimize inherent or procedural hazards.

TI assumes no liability for applications assistance or customer product design. TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of TI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used. TI's publication of information regarding any third party's products or services does not constitute TI's approval, warranty or endorsement thereof.

&gt;&gt; Semiconductor Home &gt; Products &gt; Analog &amp; Mixed-Signal &gt; Amplifiers &gt; Operational Amplifiers &gt;

## TL061, Low-Power JFET-Input General-Purpose Operational Amplifier

Device Status: Active

- > [Description](#)
- > [Features](#)
- > [Datasheets](#)
- > [Pricing/Samples/Availability](#)
- > [Application Notes](#)
- > [User Manuals](#)
- > [Development Tools](#)
- > [Applications](#)

Parameter Name	TL061
delta VCC (max) (V)	36
delta VCC (min) (V)	7
IDD / ICC per channel (max) (mA)	0.25
IDD / ICC per channel (typ) (mA)	0.2
GBW (typ) (MHz)	1
Slew Rate (typ) (V/us)	3.5
VIO (Full Range) (max) (mV)	20
VIO (25 deg C) (max) (mV)	15
IIB (typ) (pA)	30
CMRR (typ) (dB)	86
Vn (typ) (nV/rtHz)	42
Number of Channels	1
Spec'd at VCC (V)	+/-15

### Description

The JFET-input operational amplifiers of the TL06\_ series are designed as low-power versions of the TL08\_ series amplifiers. They feature high input impedance, wide bandwidth, high slew rate, and low input offset and input bias currents. The TL06\_ series feature the same terminal assignments as the TL07\_ and TL08\_ series. Each of these JFET-input operational amplifiers incorporates well-matched, high-voltage JFET and bipolar transistors in a monolithic integrated circuit.

The C-suffix devices are characterized for operation from 0°C to 70°C. The I-suffix devices are characterized for operation from -40°C to 85°C, and the M-suffix devices are characterized for operation over the full military temperature range of -55°C to 125°C.

## Features

- Very Low Power Consumption
- Typical Supply Current...200 uA (Per Amplifier)
- Wide Common-Mode and Differential Voltage Ranges
- Low Input Bias and Offset Currents
- Common-Mode Input Voltage Range Includes V<sub>CC+</sub>
- Output Short-Circuit Protection
- High Input Impedance...JFET-Input Stage
- Internal Frequency Compensation
- Latch-Up-Free Operation
- High Slew Rate...3.5 V/us Typ

To view the following documents, [Acrobat Reader 3.x](#) is required.

To download a document to your hard drive, right-click on the link and choose 'Save'.

## Datasheets

Full datasheet in Acrobat PDF: [slos078f.pdf](#) (369 KB)

Full datasheet in Zipped PostScript: [slos078f.psz](#) (331 KB)

## Pricing/Samples/Availability

Orderable Device	Package	Pins	Temp (°C)	Status	Price/unit USD (100-999)	Pack Qty	DSCC Number	Availability / Samples
81023012A	FK	20	-55 TO 125	ACTIVE	12.59	1		<a href="#">Check stock or order</a>
TL061CD	D	8	0 TO 70	ACTIVE	0.42	75		<a href="#">Check stock or order</a>
TL061CDR	D	8	0 TO 70	ACTIVE	0.38	2500		<a href="#">Check stock or order</a>
TL061CP	P	8	0 TO 70	ACTIVE	0.42	50		<a href="#">Check stock or order</a>
TL061CPS	PS	8	0 TO 70	OBSOLETE				
TL061CPWLE	PW	8	0 TO 70	OBSOLETE				
TL061ID	D	8	-40 TO 85	ACTIVE	0.70	75		<a href="#">Check stock or order</a>
TL061IDR	D	8	-40 TO 85	ACTIVE	0.62	2500		<a href="#">Check stock or order</a>

TL061IP	<u>P</u>	8	-40 TO 85	ACTIVE	0.70	50		Check stock or order
TL061MJG	<u>JG</u>	8	-55 TO 125	ACTIVE	4.13	1		Check stock or order
TL061MJGB	<u>JG</u>	8	-55 TO 125	ACTIVE	4.84	1	8102301PA	Check stock or order

## Development Tools

Tool Part Number	Tool Title	Tool Type
UNIV-OPAMP-1B	Universal EVM for Single/Dual OpAmps without Shutdown in MSOP/SOIC/SOT-23 packages	Evaluation Modules (EVM)
UNIV-OPAMP-2B	Universal EVM for Single/Dual OpAmps with Shutdown in MSOP/SOIC/SOT-23 packages	Evaluation Modules (EVM)
UNIV-OPAMP-3B	Universal EVM for Single/Dual/Quad OpAmps with/without Shutdown in MSOP/TSSOP packages	Evaluation Modules (EVM)
UNIV-OPAMP-4B	Universal EVM for Single/Dual/Quad OpAmps with/without Shutdown in SOIC packages	Evaluation Modules (EVM)
UNIV-OPAMP-5B	Universal EVM for Single/Dual/Quad OpAmps with/without Shutdown in PDIP packages	Evaluation Modules (EVM)

## Application Reports

View Application Reports for [Operational Amplifiers](#)

- [Analog Applications Journal May 2000 \(SLYT015 - Updated: 04/20/2000\)](#)
- [Analog Applications Journal, September 1999 edition \(SLYT005 - Updated: 07/15/1999\)](#)
- [Analysis Of The Sallen-Key Architecture \(SLOA024A - Updated: 07/27/1999\)](#)
- [Signal Conditioning Piezoelectric Sensors \(SLOA033 - Updated: 09/27/1999\)](#)
- [Signal Conditioning Wheatstone Resistive Bridge Sensors \(SLOA034 - Updated: 09/27/1999\)](#)

## User Manuals

- [Universal Op Amp Evaluation Module Selection Guide \(SLOU060, 10 KB - Updated: 10/22/1999\)](#)
- [Universal Op Amp Single, Dual, Quad \(SOIC\) Evaluation Module With Shutdown \(SLOU061, 1160 KB - Updated: 10/22/1999\)](#)
- [Universal Operational Amplifier EVM \(SLVU006A, 387 KB - Updated: 03/22/1999\)](#)
- [Universal Operational Amplifier Single, Dual, Quad \(MSOP/TSSOP\) \(SLOU055, 1196 KB - Updated: 10/22/1999\)](#)
- [Universal Operational Amplifier Single, Dual, Quad \(PDIP\) \(SLOU062, 1211 KB - Updated: 10/22/1999\)](#)

Table Data Updated on: 9/8/2000

&gt;&gt; Semiconductor Home &gt; Products &gt; Analog &amp; Mixed-Signal &gt; Amplifiers &gt; Operational Amplifiers &gt;

## TL062, Dual Low-Power JFET-Input General-Purpose Operational Amplifier

Device Status: Active

- > [Description](#)
- > [Features](#)
- > [Datasheets](#)
- > [Pricing/Samples/Availability](#)
- > [Application Notes](#)
- > [User Manuals](#)
- > [Development Tools](#)
- > [Applications](#)

Parameter Name	TL062
delta VCC (max) (V)	36
delta VCC (min) (V)	7
IDD / ICC per channel (max) (mA)	0.25
IDD / ICC per channel (typ) (mA)	0.2
GBW (typ) (MHz)	1
Slew Rate (typ) (V/us)	3.5
VIO (Full Range) (max) (mV)	20
VIO (25 deg C) (max) (mV)	15
IIB (typ) (pA)	30
CMRR (typ) (dB)	86
Vn (typ) (nV/rtHz)	42
Number of Channels	2
Spec'd at VCC (V)	+/-15

### Description

The JFET-input operational amplifiers of the TL06\_ series are designed as low-power versions of the TL08\_ series amplifiers. They feature high input impedance, wide bandwidth, high slew rate, and low input offset and input bias currents. The TL06\_ series feature the same terminal assignments as the TL07\_ and TL08\_ series. Each of these JFET-input operational amplifiers incorporates well-matched, high-voltage JFET and bipolar transistors in a monolithic integrated circuit.

The C-suffix devices are characterized for operation from 0°C to 70°C. The I-suffix devices are characterized for operation from -40°C to 85°C, and the M-suffix devices are characterized for operation over the full military temperature range of -55°C to 125°C.

## Features

- Very Low Power Consumption
- Typical Supply Current...200 uA (Per Amplifier)
- Wide Common-Mode and Differential Voltage Ranges
- Low Input Bias and Offset Currents
- Common-Mode Input Voltage Range Includes V<sub>CC+</sub>
- Output Short-Circuit Protection
- High Input Impedance...JFET-Input Stage
- Internal Frequency Compensation
- Latch-Up-Free Operation
- High Slew Rate...3.5 V/us Typ

To view the following documents, Acrobat Reader 3.x is required.

To download a document to your hard drive, right-click on the link and choose 'Save'.

## Datasheets

Full datasheet in Acrobat PDF: [slos078f.pdf](#) (369 KB)

Full datasheet in Zipped PostScript: [slos078f.psz](#) (331 KB)

## Pricing/Samples/Availability

Orderable Device	Package	Pins	Temp (°C)	Status	Price/unit USD (100-999)	Pack Qty	DSCC Number	Availability / Samples
81023022A		20	-55 TO 125	PREVIEW				<a href="#">Check stock or order</a>
8102302HA		10	-55 TO 125	ACTIVE	11.69	1		<a href="#">Check stock or order</a>
TL062CD	<u>D</u>	8	0 TO 70	ACTIVE	0.46	75		<a href="#">Check stock or order</a>
TL062CDR	<u>D</u>	8	0 TO 70	ACTIVE	0.42	2500		<a href="#">Check stock or order</a>
TL062CJG	<u>JG</u>	8	0 TO 70	OBSOLETE				
TL062CP	<u>P</u>	8	0 TO 70	ACTIVE	0.46	50		<a href="#">Check stock or order</a>
TL062CPS	<u>PS</u>	8	0 TO 70	OBSOLETE				
TL062CPSLE	<u>PS</u>	8	0 TO 70	OBSOLETE				

TL062CPSR	<u>PS</u>	8	0 TO 70	ACTIVE	0.53	2000		<a href="#">Check stock or order</a>
TL062CPWLE	<u>PW</u>	8	0 TO 70	OBSOLETE				
TL062CPWR	<u>PW</u>	8	0 TO 70	ACTIVE	0.38	2000		<a href="#">Check stock or order</a>
TL062ID	<u>D</u>	8	-40 TO 85	ACTIVE	0.74	75		<a href="#">Check stock or order</a>
TL062IDR	<u>D</u>	8	-40 TO 85	ACTIVE	0.65	2500		<a href="#">Check stock or order</a>
TL062IJG	<u>JG</u>	8	-40 TO 85	OBSOLETE				
TL062IP	<u>P</u>	8	-40 TO 85	ACTIVE	0.74	50		<a href="#">Check stock or order</a>
TL062MFKB	<u>FK</u>	20	-55 TO 125	ACTIVE	14.33	1		<a href="#">Check stock or order</a>
TL062MJG	<u>JG</u>	8	-55 TO 125	ACTIVE	4.18	1		<a href="#">Check stock or order</a>
TL062MJGB	<u>JG</u>	8	-55 TO 125	ACTIVE	5.71	1	8102302PA	<a href="#">Check stock or order</a>

## Development Tools

Tool Part Number	Tool Title	Tool Type
UNIV-OPAMP-1B	Universal EVM for Single/Dual OpAmps without Shutdown in MSOP/SOIC/SOT-23 packages	Evaluation Modules (EVM)
UNIV-OPAMP-2B	Universal EVM for Single/Dual OpAmps with Shutdown in MSOP/SOIC/SOT-23 packages	Evaluation Modules (EVM)
UNIV-OPAMP-3B	Universal EVM for Single/Dual/Quad OpAmps with/without Shutdown in MSOP/TSSOP packages	Evaluation Modules (EVM)
UNIV-OPAMP-4B	Universal EVM for Single/Dual/Quad OpAmps with/without Shutdown in SOIC packages	Evaluation Modules (EVM)
UNIV-OPAMP-5B	Universal EVM for Single/Dual/Quad OpAmps with/without Shutdown in PDIP packages	Evaluation Modules (EVM)

## Application Reports

### [View Application Reports for Operational Amplifiers](#)

- [Analog Applications Journal May 2000 \(SLYT015 - Updated: 04/20/2000\)](#)
- [Analog Applications Journal, September 1999 edition \(SLYT005 - Updated: 07/15/1999\)](#)
- [Analysis Of The Sallen-Key Architecture \(SLOA024A - Updated: 07/27/1999\)](#)
- [Signal Conditioning Piezoelectric Sensors \(SLOA033 - Updated: 09/27/1999\)](#)
- [Signal Conditioning Wheatstone Resistive Bridge Sensors \(SLOA034 - Updated: 09/27/1999\)](#)

## User Manuals

- [Universal Op Amp Evaluation Module Selection Guide \(SLOU060, 10 KB - Updated: 10/22/1999\)](#)
- [Universal Op Amp Single, Dual, Quad \(SOIC\) Evaluation Module With Shutdown \(SLOU061, 1160 KB - Updated: 10/22/1999\)](#)
- [Universal Operational Amplifier EVM \(SLVU006A, 387 KB - Updated: 03/22/1999\)](#)
- [Universal Operational Amplifier Single, Dual, Quad \(MSOP/TSSOP\) \(SLOU055, 1196 KB - Updated: 10/22/1999\)](#)
- [Universal Operational Amplifier Single, Dual, Quad \(PDIP\) \(SLOU062, 1211 KB - Updated: 10/22/1999\)](#)

**Table Data Updated on: 9/8/2000**

© Copyright 2000 Texas Instruments Incorporated. All rights reserved. [Trademarks](#) | [Privacy Policy](#)



&gt;&gt; Semiconductor Home &gt; Products &gt; Analog &amp; Mixed-Signal &gt; Amplifiers &gt; Operational Amplifiers &gt;

## TL064, Quad Low-Power JFET-Input General-Purpose Operational Amplifier

Device Status: Active

- > [Description](#)
- > [Features](#)
- > [Datasheets](#)
- > [Pricing/Samples/Availability](#)
- > [Application Notes](#)
- > [User Manuals](#)
- > [Development Tools](#)
- > [Applications](#)

Parameter Name	TL064
delta VCC (max) (V)	36
delta VCC (min) (V)	7
IDD / ICC per channel (max) (mA)	0.25
IDD / ICC per channel (typ) (mA)	0.2
GBW (typ) (MHz)	1
Slew Rate (typ) (V/us)	3.5
VIO (Full Range) (max) (mV)	20
VIO (25 deg C) (max) (mV)	15
IIB (typ) (pA)	30
CMRR (typ) (dB)	86
Vn (typ) (nV/rtHz)	42
Number of Channels	4
Spec'd at VCC (V)	+/-15

### Description

The JFET-input operational amplifiers of the TL06\_ series are designed as low-power versions of the TL08\_ series amplifiers. They feature high input impedance, wide bandwidth, high slew rate, and low input offset and input bias currents. The TL06\_ series feature the same terminal assignments as the TL07\_ and TL08\_ series. Each of these JFET-input operational amplifiers incorporates well-matched, high-voltage JFET and bipolar transistors in a monolithic integrated circuit.

The C-suffix devices are characterized for operation from 0°C to 70°C. The I-suffix devices are characterized for operation from -40°C to 85°C, and the M-suffix devices are characterized for operation over the full military temperature range of -55°C to 125°C.

## Features

- Very Low Power Consumption
- Typical Supply Current...200 uA (Per Amplifier)
- Wide Common-Mode and Differential Voltage Ranges
- Low Input Bias and Offset Currents
- Common-Mode Input Voltage Range Includes V<sub>CC+</sub>
- Output Short-Circuit Protection
- High Input Impedance...JFET-Input Stage
- Internal Frequency Compensation
- Latch-Up-Free Operation
- High Slew Rate...3.5 V/us Typ

To view the following documents, [Acrobat Reader 3.x](#) is required.

To download a document to your hard drive, right-click on the link and choose 'Save'.

## Datasheets

Full datasheet in Acrobat PDF: [slos078f.pdf](#) (369 KB)

Full datasheet in Zipped PostScript: [slos078f.psz](#) (331 KB)

## Pricing/Samples/Availability

Orderable Device	Package	Pins	Temp (°C)	Status	Price/unit USD (100-999)	Pack Qty	DSCC Number	Availability / Samples
TL064CD	D	14	0 TO 70	ACTIVE	0.60	50		<a href="#">Check stock or order</a>
TL064CDR	D	14	0 TO 70	ACTIVE	0.53	2500		<a href="#">Check stock or order</a>
TL064CN	N	14	0 TO 70	ACTIVE	0.60	25		<a href="#">Check stock or order</a>
TL064CNS	NS	14	0 TO 70	OBSOLETE				
TL064CNSR	NS	14	0 TO 70	ACTIVE	0.59	2000		<a href="#">Check stock or order</a>
TL064CPWLE	PW	14	0 TO 70	OBSOLETE				
TL064CPWR	PW	14	0 TO 70	ACTIVE	0.50	2000		<a href="#">Check stock or order</a>
TL064ID	D	14	-40 TO 85	ACTIVE	0.80	50		<a href="#">Check stock or order</a>

TL064IDR	<u>D</u>	14	-40 TO 85	ACTIVE	0.70	2500		Check stock or order
TL064IN	<u>N</u>	14	-40 TO 85	ACTIVE	0.80	25		Check stock or order
TL064MFKB	<u>FK</u>	20	-55 TO 125	ACTIVE	15.56	1	81023032A	Check stock or order
TL064MJ	<u>J</u>	14	-55 TO 125	ACTIVE	4.59	1		Check stock or order
TL064MJB	<u>J</u>	14	-55 TO 125	ACTIVE	6.21	1	8102303CA	Check stock or order
TL064MWB	<u>W</u>	14	-55 TO 125	ACTIVE	11.69	1	8102303DA	Check stock or order

## Development Tools

Tool Part Number	Tool Title	Tool Type
UNIV-OPAMP-1B	Universal EVM for Single/Dual OpAmps without Shutdown in MSOP/SOIC/SOT-23 packages	Evaluation Modules (EVM)
UNIV-OPAMP-2B	Universal EVM for Single/Dual OpAmps with Shutdown in MSOP/SOIC/SOT-23 packages	Evaluation Modules (EVM)
UNIV-OPAMP-3B	Universal EVM for Single/Dual/Quad OpAmps with/without Shutdown in MSOP/TSSOP packages	Evaluation Modules (EVM)
UNIV-OPAMP-4B	Universal EVM for Single/Dual/Quad OpAmps with/without Shutdown in SOIC packages	Evaluation Modules (EVM)
UNIV-OPAMP-5B	Universal EVM for Single/Dual/Quad OpAmps with/without Shutdown in PDIP packages	Evaluation Modules (EVM)

## Application Reports

View Application Reports for [Operational Amplifiers](#)

- [Analog Applications Journal May 2000 \(SLYT015 - Updated: 04/20/2000\)](#)
- [Analog Applications Journal, September 1999 edition \(SLYT005 - Updated: 07/15/1999\)](#)
- [Analysis Of The Sallen-Key Architecture \(SLOA024A - Updated: 07/27/1999\)](#)
- [Signal Conditioning Piezoelectric Sensors \(SLOA033 - Updated: 09/27/1999\)](#)
- [Signal Conditioning Wheatstone Resistive Bridge Sensors \(SLOA034 - Updated: 09/27/1999\)](#)

## User Manuals

- [Universal Op Amp Evaluation Module Selection Guide \(SLOU060, 10 KB - Updated: 10/22/1999\)](#)
- [Universal Op Amp Single, Dual, Quad \(SOIC\) Evaluation Module With Shutdown \(SLOU061, 1160 KB - Updated: 10/22/1999\)](#)
- [Universal Operational Amplifier EVM \(SLVU006A, 387 KB - Updated: 03/22/1999\)](#)
- [Universal Operational Amplifier Single, Dual, Quad \(MSOP/TSSOP\) \(SLOU055, 1196 KB - Updated: 10/22/1999\)](#)
- [Universal Operational Amplifier Single, Dual, Quad \(PDIP\) \(SLOU062, 1211 KB - Updated: 10/22/1999\)](#)

Table Data Updated on: 9/8/2000