


# Multi-Band Multi-System GNSS Positioning Module

# TAU1202 TAU1205

Datasheet V1.3





## Notice, Statement and Copyright

ALLYSTAR Technology offers this document as a service to its customers, to support application and engineering efforts that use the products designed by ALLYSTAR Technology. Products and specifications discussed herein are for reference purposes only. Performance characteristics listed in this document do not constitute a warranty or guarantee of product performance.

ALLYSTAR Technology assumes no liability or responsibility for any claims or damages arising out of the use of this document, or from the use of integrated circuits based on this document, including, but not limited to claims or damages based on infringement of patents, copyrights or other intellectual property rights.

This document contains proprietary technical information which is the property of ALLYSTAR Technology, copying of this document and giving it to others and using or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. ALLYSTAR Technology reserves the right to make changes in its products, specifications and other information at any time without notice.

For more documents, please visit <a href="www.allystar.com">www.allystar.com</a>.
Copyright © ALLYSTAR Technology (Shenzhen) Co., Ltd. 2020. All rights reserved.



# **TABLE OF CONTENT**

1	SYSTEM OVERVIEW	5
	<ul> <li>1.1 Overview</li></ul>	5 5 6
2	PIN DESCRIPTION	8
	<ul><li>2.1 Pin assignment</li><li>2.2 Detailed pin descriptions</li></ul>	
3	ELECTRICAL CHARACTERISTICS	10
	3.1 Absolute Maximum Rating	10 10 10
	3.3 DC Characteristics	11
4	HARDWARE DESCRIPTION	12
	<ul> <li>4.1 Connecting power</li></ul>	12 13
5	MECHANICAL SPECIFICATION	14
6	REFERENCE DESIGN	15
	<ul> <li>6.1 Minimal Design</li> <li>6.2 PCB Footprint Reference</li> <li>6.3 Layout Notes</li> <li>6.3.1 Reflow soldering</li> </ul>	17 17
7	PRODUCT PACKAGING AND HANDLING	19
	7.1 Packaging	19 19
	7.1.3 Shipment Packaging7.2 Storage	



	7.3	Ha	andling	22
		7.3.1	ESD Handling Precautions	22
		7.3.2	ESD protection measures	22
		7.3.3	Moisture sensitivity level	22
8	REV	/ISION	N HISTORY	23
List	t of tal	oles		
	Table	1 Differer	nces between TAU1202/TAU1205-1010A00 and TAU1202/TAU1205-1010C00	5
	Table :	2 Specific	cations	6
	Table	3 Detaile	d pin descriptions	9
	Table -	4 Absolut	te rating	10
			X and PRTRG	
	Table	6 ANT_BI	AS	10
	Table	8 Operati	ng conditions	11
		•	consumption	
	Table	10 ANT_E	BIAS current range and antenna status	12
	Table	11 Reflov	v profile features	17
	Table	12 Packir	ng hierarchy	19
List	of fig	ures		
	Figure	1 TAU12	202/TAU1205 module photo	5
	Figure	2 Block	diagram	6
	Figure	3 Pin as	signment (top view)	8
	Figure	4 Dimen	sions	14
	Figure	5 Minim	al application diagram of A00 with internal power for ANT	15
	Figure	6 Minim	al application diagram of C00 with internal power for ANT	16
	Figure	7 Minim	al application diagram with external power for ANT	16
	Figure	8 PCB F	ootprint Reference	17
	Figure	9 Reflow	soldering profile (Refer to IPC/JEDEC J-STD-020E)	18
	Figure	10 Tape	dimensions	19
	Figure	11 Reel	dimensions	20



## 1 SYSTEM OVERVIEW

#### 1.1 Overview

TAU1202/TAU1205 is a high-performance dual-band GNSS positioning module, which is based on the state of the art CYNOSURE III architecture. It supports BDS-3 (BeiDou Navigation Satellite System 3). Besides, it is capable of tracking all global civil navigation systems (BDS, GPS, GLONASS, Galileo, IRNSS, and QZSS).

TAU1202/TAU1205 integrates efficient power management architecture, while providing high precision, high sensitivity and low power GNSS solutions which make it suitable for navigation applications on automotive and consumer electronics, as well as fleet management.

## 1.2 Features

- Supports all civil GNSS systems
- Supports BDS-3 signal: B1C and B2a
- Concurrent reception of L1 and L5 band signals
- Sub-meter position accuracy, superior in multipath mitigation and lower noise in city valley
- Smart jammer detection and suppression
- Highly integrated module, the best cost-effective high precision solution
- Supports single IRNSS mode (TAU1205)

## 1.3 Module photo






Figure 1 TAU1202/TAU1205 module photo

Table 1 Differences between TAU1202/TAU1205-1010A00 and TAU1202/TAU1205-1010C00

PN	Description
TAU1202/TAU1205-1010A00	RF_IN pin does not provide the power for active antenna, so a bias choke from ANT_BIAS to RF_IN pin should be used.
TAU1202/TAU1205-1010C00	A bias choke is built-in between ANT_BIAS and RF_IN pin to power the active antenna. If the active antenna is powered by a supply source other than the module, a capacitor should be used to block the DC from RF_IN.



# 1.4 Block diagram






Figure 2 Block diagram

# 1.5 Specifications

**Table 2 Specifications** 

Parameter		Specification
GNSS Tracking channel	40 channels	
		GPS/QZSS: L1C/A, L5C
	TAU1202	BDS: B1I, B2a
	TAU1202	GLONASS: L10F
CNICC recention		Galileo: E1, E5a
GNSS reception		GPS/QZSS: L1C/A, L5C
	TAU1205	BDS: B1I, B2a
	TAU1205	Galileo: E1, E5a
		IRNSS: L5
Update rate	Maximum 10Hz	
Position accuracy [1]	GNSS	<1m CEP
Valacity 9 Time accuracy	GNSS	0.1m/s CEP
Velocity & Time accuracy	1PPS	20ns
Time to First Fix(TTFF)	Hot start	1 sec
Tille to First Fix(TTFF)	Cold start	24 secs
	Cold start	-148dBm
Concitivity	Hot start	-155dBm
Sensitivity	Reacquisition	-158dBm
	Tracking & navigation	-161dBm



Operating limit	Velocity	515 m/s		
Operating limit	Altitude	18,000 m		
	Antenna short circuit and open circuit detection, and short circuit			
Safety supervision	protection			
	Low voltage detection			
	UART	1		
Serial interface	I2C	1		
	CAN [2]	1		
Drotocol	NMEA 0183 Protocol Ver.	4.00/4.10,		
Protocol	Cynosure GNSS Receiver Protocol			
	Main voltage	1.8 ~ 3.6V		
Operating condition	Digital I/O voltage	1.8 ~ 3.6V		
	Backup voltage	1.8 ~ 3.6V		
	GPS+QZSS, L1 band	22mA@3.3V		
Power consumption	GNSS, L1+L5 band	41mA@3.3V		
	Standby	12uA		
Operating temperature	-40 °C ~ +85 °C			
Storage temperature	-40 °C ~ +85 °C			
Package	10.1mm x 9.7mm x 2.5mm 18-pin stamp hole			
Certification	RoHS & REACH			

<sup>\* [1]</sup> Open sky, dual band, demonstrated with a good external LNA

<sup>\* [2]</sup> Only customized firmware supported



# 2 PIN DESCRIPTION

# 2.1 Pin assignment




Figure 3 Pin assignment (top view)



# 2.2 Detailed pin descriptions

Table 3 Detailed pin descriptions

Function	Symbol	No.	I/O	Description
	VDD	8	Power	Main supply input.
Power	GND	1,10,12	VSS	Ground
	AVDD_BAK	6	Power	Backup supply input.
Antenna	RF_IN	11	I	RF signal input. Use a controlled impedance of $50\Omega$ from connect RF_IN to the antenna or the antenna connector.
Antenna	ANT_BIAS	14	0	RF section output voltage. Used to power the external active antenna. The current is limited below 35mA.
UART	UOUT0	2	0	UART0 serial data output.
UART	UIN0	3	I	UART0 serial data input.
120 (OAN)	CANRX/SDA	16	I/O	I <sup>2</sup> C data transmission, or CAN data input. Leave it floating if not used.
I <sup>2</sup> C/CAN	CANTX/SCL	17	I/O	I <sup>2</sup> C clock, or CAN data output. Leave it floating if not used.
	PRTRG	18	I	Mode selection, or the trigger input in deep sleep mode to wake up the system
Cuatam	PRRSTX	9	I	External reset, low active
System	PPS	4	0	Time pulse output (PPS)
	EXTINT	5	I	GPIO, Default (EXTINT): a trigger pin to external interrupt, leave it floating if not used.
Reserved	Reserved	7,13,15,		Reserved, leave it floating if not used



# 3 ELECTRICAL CHARACTERISTICS

# 3.1 Absolute Maximum Rating

**Table 4 Absolute rating** 

Symbol	Parameter	Min.	Max.	Unit
VDD	Power input for the main power domain	-0.5	3.63	V
AVDD_BAK	Power input for the backup power domain	-0.5	3.63	V
T <sub>storage</sub>	Storage temperature	-40	85	°C
T <sub>solder</sub>	Solder reflow temperature	-	260	°C

## 3.2 IO Characteristics

## 3.2.1 PRRSTX and PRTRG

#### Table 5 PRRSTX and PRTRG

Symbol	Parameter	Condition	Min.	Тур.	Max.	Unit
I <sub>IZ</sub>	Input leakage current				+/-1	uA
V <sub>IH</sub>	Input high voltage		AVDD_BAK*0. 7		AVDD_BAK	V
V <sub>IL</sub>	Input low voltage		0		AVDD_BAK*0.3	V
Ci	Input capacitance				10	pF
R <sub>PU</sub>	Pull-up resistance		18		84	kOhm

## 3.2.2 ANT\_BIAS

## Table 6 ANT\_BIAS

Parameter	Condition	Min.	Тур.	Max.	Unit
RF supply current				35	mA
RF supply voltage		1.42		3.43	V

## **3.2.3** Others

#### **Table 7 Others**

Symbol	Parameter	Condition	Min.	Тур.	Max.	Unit
I <sub>IZ</sub>	Input leakage current				+/-1	uA
$V_{IH}$	Input high voltage		VDD*0.7		VDD	V
$V_{IL}$	Input low voltage		0		VDD*0.3	٧
W	V <sub>OH</sub> Output high voltage	I <sub>OH</sub> =11.9 mA, VDD=3.3V	2.64			V
V OH		I <sub>OH</sub> =2.8 mA, VDD=1.8V	1.53			V
V	Output low voltage	I <sub>OL</sub> =7.9 mA, VDD=3.3V			0.4	V
V <sub>OL</sub>	Output low voltage	I <sub>OL</sub> =3.9 mA, VDD=1.8V			0.45	V
Ci	Input capacitance				11	pF
R <sub>PU</sub>	Pull-up resistance	-	35		84	kOhm



## 3.3 DC Characteristics

## 3.3.1 Operating Conditions

## **Table 8 Operating conditions**

Symbol	Parameter	Min.	Тур.	Max.	Unit
VDD	Power input for the main power domain	1.8	3.3	3.6	V
AVDD_BAK	Power input for the backup power domain	1.8	3.3	3.6	V
ICC <sub>max</sub>	Maximum operating current @ VDD	-		200	mA
T <sub>env</sub>	Operating temperature	-40		85	°C

## 3.3.2 Power Consumption

## **Table 9 Power consumption**

Symbol	Parameter	Measure Pin	Тур.	Unit
I <sub>CCRX1</sub> <sup>[1]</sup>	Run Mode (GPS+QZSS, L1 only)	ADD[3]	22	mA
I <sub>CCRX2</sub> <sup>[2]</sup>	Run Mode (GNSS, L1+L5)	ADD <sub>[3]</sub>	41	mA
I <sub>CCDBM</sub>	Standby mode	AVDD_BAK <sup>[4]</sup>	12	uA

<sup>\* [1]</sup> GPS+QZSS, L1 band only, 16 tracking channels, position fixed

<sup>\* [2]</sup> All GNSS, L1 + L5 band, 32 tracking channels, position fixed

<sup>\* [3]</sup> Condition: VDD=3.3V@Room Temperature; All Pins Open.

<sup>\* [4]</sup> Condition: AVDD\_BAK=3.3V@Room Temperature; All Pins Open.



## 4 HARDWARE DESCRIPTION

## 4.1 Connecting power

TAU1202/TAU1205 positioning module has two power supply pins: VDD and AVDD\_BAK. The main power is supplied through the VDD pin, and the backup power is supplied through the AVDD\_BAK pin. In order to ensure the positioning performance, please control the ripple of the module power supply less than 50m Vpp. It is recommended to use the LDO above 200mA current.

If the power for VDD pin is off, the real-time clock (RTC) and battery backed RAM (BBR) are supplied through the AVDD\_BAK pin. Thus, orbit information and time can be maintained and will allow a Hot or Warm start. If no backup battery is connected, the module performs a cold start at every power up if no aiding data are sent to the module.

Note: If no backup supply is available, leave AVDD\_BAK pin floating.

## 4.2 Antenna design

There is built-in LNA and SAW in the GNSS module. It is recommended to use an active antenna with gain less than 36dB and noise figure less than 1.5dB.

The module has built-in short circuit detection and open circuit detection function, which can detect the status of normal connection, and send out antenna status prompt message in NMEA data.

#### Short circuit protection

» The module includes internal short circuit antenna detection. Once an overcurrent is detected at the ANT\_BIAS port, the module will cut off this power supply automatically to prevent permanent damages.

#### Open circuit detection

The module can detect an open circuit in the antenna. Users can judge it from antenna status messages.

Table 10 ANT\_BIAS current range and antenna status

Antenna status	Status output	ANT_BIAS current range
Open circuit	OPEN	0< ANT_BIAS ≤ 1mA
Regular circuit or open circuit	OK or OPEN	1mA< ANT_BIAS ≤ 2mA
Regular circuit	OK	$2mA < ANT_BIAS \le 40 \pm 5mA^{[1]}$
Short circuit	SHORT	40±5mA <sup>[1]</sup> < ANT_BIAS < 55mA

<sup>\* [1] ±5</sup>mA are differences between product batches.

#### TIPs:

- 1. Pulse width of the minimum detectable overshoot current should be more than 10uS.
- 2. NMEA message of antenna status output:
- OPEN: \$GNTXT,01,01,01,ANT\_OPEN\*40
- OK: \$GNTXT,01,01,01,ANT\_OK\*50
- SHORT: \$GNTXT,01,01,01,ANT\_SHORT\*06



## 4.3 Reset and mode control

The operation mode of GNSS module is controlled by PRRSTX (nRESET) and PRTRG (BOOT) pin. While the module works in normal operation, leave PRRSTX and PRTRG pins floating if there is no upgrading or reset demands, or others.

- Keep PRTRG pin floating during system power-up or the external reset (PRRSTX from low to high), and the module will enter User Normal Mode.
- When the module powers up or PRRSTX from low to high, the module will execute an external
  reset. (If the power for AVDD\_BAK is always on, the external reset will not affect the ephemeris
  data in the backup domain)
- Drive PRTRG pin to low or connect PRTRG to GND directly (not by pull-down resistance) during
  system power-up or the external reset (PRRSTX from low to high), and the system enters
  BootROM Command Mode at PRTRG pin being released from low to floating state, and ready for
  firmware upgrading command.
- When connecting PRRSTX and PRTRG to any host IO, DO NOT use the pull-up or pull-down resistance.

## 4.4 Serial interfaces


The module provides a TTL Universal Asynchronous Receiver / Transmitter (UART) interface. The data format is: 1 start bit, 8 data bits, 1 stop bit, no checksum, and the default baud rate is 115200 bps. NMEA data outputs while the module is powered on.

When the module is applied to the specific application, users can shut off the main power in order to further reduce the power consumption. To avoid the high level in serial interface influencing the normal operation, it is highly suggested to cut off the serial port when shut off the main power.

Otherwise, please set the serial port to input mode or high impedance state with pull-down resistor.



# 5 MECHANICAL SPECIFICATION



**Figure 4 Dimensions** 



## 6 REFERENCE DESIGN

## 6.1 Minimal Design

TAU1202/TAU1205 includes two versions of design (A00 and C00).

- In A00 design, RF\_IN pin does not provide the power for active antenna, so a bias choke of 82nH from ANT\_BIAS to RF\_IN pin should be used. (Refer to Figure 5)
- In C00 design, a bias choke is built-in between ANT\_BIAS and RF\_IN pin to power the active antenna. (Refer to **Figure 6**)
- If the active antenna is powered by a supply source other than the module, a capacitor should be used to block the DC from RF\_IN. (Refer to **Figure 7**)

The characteristic impedance from RF\_IN pin to the antenna connector should be  $50\Omega$ .




Figure 5 Minimal application diagram of A00 with internal power for ANT






Figure 6 Minimal application diagram of C00 with internal power for ANT





Figure 7 Minimal application diagram with external power for ANT



# **6.2** PCB Footprint Reference



**Figure 8 PCB Footprint Reference** 

## 6.3 Layout Notes

- 1) A decoupling capacitor should be placed close to VDD pin of the module, and the width of power routing should be more than 0.5mm;
- 2) The characteristic impedance of RF routing between RF port to antenna should be controlled to  $50 \Omega$ .
- 3) Do not place the module close to any EMI source, like antenna, RF routing, DC/DC or power conductor, clock signal or other high-frequency switching signal, etc.

## 6.3.1 Reflow soldering

Table 11 Reflow profile features

Profile Feature	Pb-Free Assembly	
Preheat/Soak		
Temperature Min (T <sub>smin</sub> )	150 °C	
Temperature Max (T <sub>smax</sub> )	200 °C	
Time (ts) from (Tsmin to Tsmax)	60-120s	
Ramp-up rate (T <sub>L</sub> to T <sub>p</sub> )	3 °C/second max.	
Liquidous temperature (TL)	217 °C	
Time (t <sub>L</sub> ) maintained above T <sub>L</sub>	60-150s	
Peak package body temperature (T <sub>p</sub> )	must not exceed the Classification temp $T_c^{[1]}$	
Time (t <sub>p</sub> )* within 5 °C of the specified classification	30* seconds <sup>[2]</sup>	
temperature (Tc)	30° seconds 43	
Ramp-down rate (Tp to TL)	6 °C/second max.	
Time 25 °C to peak temperature	8 minutes max.	



- \* [1] T<sub>c</sub>=260°C.
- \* [2] The time above 255 °C must not exceed 30 seconds.




Figure 9 Reflow soldering profile (Refer to IPC/JEDEC J-STD-020E)



## 7 PRODUCT PACKAGING AND HANDLING

## 7.1 Packaging

#### 7.1.1 Packaging Notes

TAU1202/TAU1205 GNSS module is a Moisture Sensitive Device (MSD) and Electrostatic Sensitive Device (ESD). During the packing and shipping, it is strictly required to take appropriate MSD handling instructions and precautions. The table below shows the general packing hierarchy for the standard shipment.

**Table 12 Packing hierarchy** 



Note: Packaging of non-standard quantities is not explained here. Take the reality as a reference.

#### 7.1.2 Tape and Reel

The TAU1202/TAU1205 modules are delivered as hermetically sealed, reeled tapes in order to enable efficient production, production lot set-up and tear-down. The figure below shows the tape dimension.




Figure 10 Tape dimensions



TAU1202/TAU1205 are deliverable in quantities of 1000pcs on a reel. The figure below shows the dimensions of reel for TAU1202/TAU1205.




Figure 11 Reel dimensions

## 7.1.3 Shipment Packaging

The reels of TAU1202/TAU1205 modules are packed in the sealed bags and shipped by shipping cartons. Up to five sealed bags (5000pcs in total) can be packed in one shipping carton.




Figure 12 Packaging



# 7.2 Storage

In order to prevent moisture intake and protect against electrostatic discharge, TAU1202/TAU1205 is packaged together with a humidity indicator card and desiccant to absorb humidity.



## 7.3 Handling

## 7.3.1 ESD Handling Precautions

TAU1202/TAU1205 module which contains highly sensitive electronic circuitry is Electrostatic Sensitive Device (ESD). Observe precautions for handling! Failure to observe these precautions may result in severe damage to the GNSS module!

- Unless there is a galvanic coupling between the local GND (i.e. the workbench) and the PCB GND, then the first point of contact when handling the PCB must always be between the local GND and PCB GND.
- Before mounting an antenna patch, connect ground of the device.
- When handling the RF pin, do not come into contact with any charged capacitors and be careful when contacting materials that can develop charges (e.g. patch antenna ~10 pF, coax cable ~50 80 pF/m, soldering iron...)
- To prevent electrostatic discharge through the RF input, do not touch any exposed antenna area. If there is any risk that such exposed antenna area is touched in non ESD protected work area, implement proper ESD protection measures in the design.
- When soldering RF connectors and patch antennas to the receiver's RF pin, make sure to use an ESD safe soldering iron (tip).



## 7.3.2 ESD protection measures

This series of GNSS positioning modules is sensitive to static electricity. Whenever handling the module, particular care must be exercised to reduce the risk of electrostatic charges. In addition to standard ESD safety practices, the following measures should be taken into account.

- Adds ESD Diodes to the RF input part to prevent electrostatics discharge.
- Do not touch any exposed antenna area.
- Adds ESD Diodes to the UART interface.

#### 7.3.3 Moisture sensitivity level

The Moisture Sensitivity Level (MSL) of the GNSS modules is MSL3.



# 8 REVISION HISTORY

Revision	Date	Reviser	Status / Comments
V1.0	2019-05	Daisy	Start version, first released
V1.1	2019-09	Vita Wu	Logo, product photos and wording update
V1.2	2019-12	Vita Wu	Adds packaging info in Section 7; Updates mechanical specification; Updates sensitivity and power consumption in Table 1 and Table 7; Updates antenna gain in Section 4.2; Adds PCB package reference and layout notes in Section 6; Updates Section 6.1;
V1.3	2020-07	Vita Wu	Adds ANT_BIAS info; Adds built-in chock design, and updates reference design; Adds reflow soldering info; Updates mechanical spec; Simplifies Pin description; Other updates;





# www.allystar.com



info.gnss@allystar.com



5F, Building No.4, Winlead Intelligent Park, No.3, FaDa road (middle), Bantian Subdistrict, LongGang District, Shenzhen City, Guangdong Province, China.

