CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-102		REV. 4.8
SUBJECT CLASS 1		or 2 BLUETOOTH MODULE	PAGE	1 of 6	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

Product Specification

Applicant / Manufacturer

Panasonic Industrial Devices Europe GmbH

Hardware

Zeppelinstrasse 19

21337 Lüneburg

Germany

Applicant / Manufacturer

Not applicable

Software

Software Version Not applicable

Contents Approval for Mass Production

Customer

Bluetooth QDL ID Qualified Design Listing (QDL) ID: B019784

As Controller Sub-System Listing for PAN13xx Series.

By purchase of any products described in this document the customer accepts the document's validity and declares their agreement and understanding of its contents and recommendations. Panasonic reserves the right to make changes as required without notification.

Power Electronics R&D Center
Wireless Connectivity
Panasonic Industrial Devices Europe GmbH

APPROVED CHECK

CLASSIFICATION	PRODUCT SPECIFICATION	No. DS-13xx-2400-102	REV. 4.8
SUBJECT CLASS	3 1 or 2 BLUETOOTH MODULE	PAGE 2 o	f 60
CUSTOMER'S CODE PAN13XX Core Specification	PANASONIC'S CODE See Chapter Ordering Information	DATE 23.09	.2015

TABLE OF CONTENTS

1	Scope of this Document		5
	1.1 New PAN13x5B, F	PAN13x6B	5
2	Key Features		6
3	Applications for the Mod	lule	7
4	Description for the Modu	ıle	7
5	Detailed Description		8
	5.1 Terminal Layout		8
	5.1.1 5.1.1. Ter	minal Layout PAN131x without antenna	8
	5.1.2 5.1.2. Ter	minal Layout PAN132x with antenna	9
	5.2 Pin Description		10
	5.3 Device Power Sup	pply	11
	5.4 Clock Inputs		12
6	Bluetooth Features		12
7	Block Diagram		13
8	Test Conditions		14
9	General Device Require	ments and Operation	14
	9.1 Absolute Maximun	n Ratings	14
	9.2 Recommended Op	perating Conditions	15
	9.3 Current Consumpt	tion	16
	9.4 General Electrical	Characteristics	17
	-	ments	
	9.6 External Digital Slo	ow Clock Requirements	17
10	Host Controller Interface)	18
11	Audio/Voice Codec Inter	rface	19
	11.1 PCM Hardware In	terface	19
	11.2 Data Format		19
	11.3 Frame Idle Period		20
	11.4 Clock-Edge Opera	ation	21
	11.5 Two-Channel PCN	/I Bus Example	21
	•		
	11.7 Improved Algorithm	m For Lost Packets	22
	11.8 Bluetooth/PCM Clo	ock Mismatch Handling	22
	11.9 Bluetooth Inter-IC	Sound (I2S)	22
	11.10Current Consumpt	tion for Different Bluetooth Scenarios	23
12	Bluetooth RF Performan	nce	23
13	Soldering Temperature-	Time Profile (for reflow soldering)	26
	13.1 For lead solder		26
	13.2 For leadfree solde	r	27
14	Module Dimension		28

CLASSIF	ICATION	PRODUCT SPECIFICATION	No. DS-13xx-24	00-102	REV 4.8
SUBJEC	T CLASS 1	or 2 BLUETOOTH MODULE	PAGE	3 of 6	50
	IER'S CODE Core Specification	PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015
	<u>'</u>	, s			
	14.1 Module Dimens	sions PAN131X without Antenna		2	28
	14.2 Module Dimens	sions PAN132X with Antenna		2	29
15	Footprint of the Modu	ıle			30
	15.1 Footprint PAN1	31x without antenna		3	30
	15.2 Footprint PAN1	32x with antenna		3	31
16	Labeling Drawing			3	32
17	Mechanical Requiren	nents		3	32
18	Recommended Foot	Pattern			33
	18.1 recommended f	foot pattern PAN131x without anten	na		33
		foot pattern PAN132x with antenna			
19					
20		tions with Antenna (PAN132x)			
21	•	NERGY) PAN1316/26			
	•	pgy			
	•	S			
		nption for different LE scenarios			
22		iption for different LL scenarios			
22		gy			
	•				
		S			
00		onsumption			
23	•	R + Bluetooth low energy or ANT) P			
0.4	·	rrent consumption			
24		ications			
		ded			
25					
26	•				
27					
	J				
		es			
	•	ns Notes			
	_				
		S			
	27.6 Other cautions.			4	45
28	Packaging			4	46
	28.1 Packaging of P.	AN131x without antenna		4	46
	28.2 Packaging for F	PAN132x with antenna			1 9
29	Ordering Information			5	50
30	Data Sheet Status			5	51
31	History for this Docur	nent			52
32	Related Documents				53
33	General Information				54

SUBJECT CLASS 1 or 2 BLUETOOTH MODULE PAGE 4 of 60 CUSTOMER'S CODE PAN13XX Core Specification PANASONIC'S CODE See Chapter Ordering Information DATE 23.09.2015 34 Regulatory Information .54 34.1 FCC for US .54 34.1.2 Caution .55 34.1.3 Labeling Requirements .55 34.1.4 Antenna Warning .55 34.1.5 Approved Antenna List (PAN1315, PAN1325) .56 34.1.6 Approved Antenna List (PAN1316, PAN1317, PAN1326, PAN1327) .56 34.2 Industry Canada Certification .57 34.2.1 IC Notice .57 34.2.2 Labeling Requirements .58 34.3 European R&TTE Declaration of Conformity .59 34.4 Japanese Radio Law and Japanese Telecommunications .60					
CUSTOMER'S CODE PAN13XX Core Specification PANASONIC'S CODE See Chapter Ordering Information DATE 23.09.2015 34 Regulatory Information 54 34.1 FCC for US 54 34.1.1 FCC Notice 54 34.1.2 Caution 55 34.1.3 Labeling Requirements 55 34.1.4 Antenna Warning 55 34.1.5 Approved Antenna List (PAN1315, PAN1325) 56 34.1.6 Approved Antenna List (PAN1316, PAN1317, PAN1326, PAN1327) 56 34.1.7 RF Exposure PAN13xx 56 34.2 Industry Canada Certification 57 34.2.1 IC Notice 57 34.2.2 Labeling Requirements 58 34.3 European R&TTE Declaration of Conformity 59 34.4 Japanese Radio Law and Japanese Telecommunications 60	CLASSIFICATION	PRODUCT SPECIFICATION	_		REV. 4.8
PAN13XX Core Specification See Chapter Ordering Information DATE 23.09.2015 34 Regulatory Information 54 34.1 FCC for US 54 34.1.1 FCC Notice 54 34.1.2 Caution 55 34.1.3 Labeling Requirements 55 34.1.4 Antenna Warning 55 34.1.5 Approved Antenna List (PAN1315, PAN1325) 56 34.1.6 Approved Antenna List (PAN1316, PAN1317, PAN1326, PAN1327) 56 34.2 Industry Canada Certification 57 34.2.1 IC Notice 57 34.2.1 IC Notice 57 34.2.2 Labeling Requirements 58 34.3 European R&TTE Declaration of Conformity 59					

CLASSIFICATION	PRODUCT SPECIFICATION	No. DS-13xx-2400-1	02	REV. 4.8
SUBJECT CLASS ?	or 2 BLUETOOTH MODULE	PAGE	5 of 6	60
CUSTOMER'S CODE PAN13XX Core Specification	PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20)15

1 SCOPE OF THIS DOCUMENT

This product specification describes Panasonic's HCI, Class 1.5, TI based, Bluetooth®¹ modules, series number 13xx.

For detailed family overview that includes part numbers see Chapter 29, Ordering Information.

Non-antenna versions will be referred to as PAN131x, versions with antenna will be referred to as PAN132x in this document.

For information and features on Bluetooth Low Energy 4.0 refer to Chapter 20, for information on ANT refer to Chapter 22.

1.1 NEW PAN13X5B, PAN13X6B

The PAN13x5B and PAN13x6B Series are based on Texas Instruments' NEW CC2560B and CC2564B controller respectively. The NEW PAN13x5B/13x6B Series Modules support assisted mode for the HFP1.6 (WBS) profile or the A2DP profile. The PAN13x6B also supports 10 LE connections (instead of 6 before).

Compatibility:

PAN1315(A/B) and PAN1316(B) are 100% footprint compatible PAN1325(A/B) and PAN1326(B) are 100% footprint compatible

NOTE: In the following chapters PAN13x5, PAN13x6 naming also considers the A and B version.

As an updated initialization script resident on the application microcontroller is required for modules based on the CC2560B and CC2564B, compatibility between the basic, A and B version is dependent on the Bluetooth stack.

BT-Stack solutions provided by software development partners are available for most processors, including linux based host systems.

For detailed family overview that includes part numbers see Chapter 29 Ordering Information.

Contact your stack provider or local Panasonic sales company for currently available Bluetooth Profiles.

PANASONIC INDUSTRIAL DEVICES EUROPE GMBH

¹ Bluetooth is a registered trademark of the Bluetooth Special Interest Group.

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-102		REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	6 of 6	06
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

2 KEY FEATURES

- Bluetooth specification v2.1 + EDR (Enhanced Data Rate)
- Surface mount type 6.5(9.5 w. Ant.) x 9.0 x 1.8 mm³
- Up to 10 dBm Tx power with transmit power control
- High sensitivity (-93 dBm typ.)
- Texas Instrument's CC256X BlueLink 7.0 inside
- Fast Connection Setup
- Extended SCO Link
- Supports convenient direct connection to battery (2.2-4.8 V), or connect to DC/DC (1.7-1.98 V) for improved power efficiency
- Internal crystal oscillator (26MHz)
- Fully shielded for immunity
- Full Bluetooth data rate up to 2,178kbps asymmetric
- Support for Bluetooth power saving modes (Sniff, Hold)
- Support for very low-power modes (deep sleep and power down)
- Optional support for ultra-low-power mode. Standby with Battery-Backup
- PCM Interface Master / Slave supporting 13 or 16 bit linear, 8 bit μ-law or A-law Codecs and CVSD transcoders on up to 3 SCO channels
- Full 8- to 128-bit encryption
- UART, I²C and PCM Interface
- IO operating voltage = 1.8 V nominal
- Bluetooth profiles such as SPP, A2DP and others are available. Refer to Panasonic's RF module <u>website</u> for a listing of the most current releases.
- Manufactured in conformance with RoHS

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-24	100-102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	7 of 6	00
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

3 APPLICATIONS FOR THE MODULE

All Embedded Wireless Applications

- Smart Phones
- Industrial Control
- Medical
- Scanners
- Wireless Sensors
- Low Power

- Cable Replacement
- Automotive
- Access Points
- Consumer Electronics
- Monitoring and Control
- Access Points

4 DESCRIPTION FOR THE MODULE

The PAN1315 and PAN1315A are short-range, Class 1 or 2, HCI modules for implementing Bluetooth functionality into various electronic devices. A block diagram can be found in Chapter 7.

Communication between the module and the host controller is carried out via UART.

New designs can be completed quickly by mating the PAN13xx series modules with Texas Instruments' MSP430BT5190 that contains Mindtree's EtherMind Bluetooth Protocol Stack and serial port profile, additional computing power can be achieved by choosing TI's Stellaris ARM7 controller that includes StoneStreet One's A2DP profile. Other BT profiles are available on custom development basis.

Additional controllers are also supported by the PAN13xx series by using a TI/Panasonic software development partner to port the Bluetooth stack and profiles. Mindtree's Software Development Kit (SDK) is available on TI's website -- www.ti.com/connectivity.com


Contact your local sales office for further details on additional options and services, by visiting www.panasonic.com/rfmodules or write an e-mail to wireless@eu.panasonic.com.

CLASSIFICATION	PRODUCT SPECIFICATION	No. DS-13xx-2400-102	REV. 4.8
SUBJECT CL	ASS 1 or 2 BLUETOOTH MODULE	PAGE 8	of 60
CUSTOMER'S CODE PAN13XX Core Specificat	PANASONIC'S CODE on See Chapter Ordering Information	DATE 23.	09.2015

5 DETAILED DESCRIPTION

5.1 TERMINAL LAYOUT

5.1.1 5.1.1. Terminal Layout PAN131x without antenna



No	Pin Name	Pull at Reset	Def. Dir. ²	I/O Type ³	Description of Options (Common)	
1	GND				Connect to Ground	
2	TX_DBG	PU	0	2 mA	Logger output	
3	HCI_CTS	PU	1	8 mA	HCI UART clear-to-send.	
4	HCI_RTS	PU	0	8 mA	HCI UART request-to-send.	
5	HCI_RX	PU	1	8 mA	HCI UART data receive	
6	HCI_TX	PU	0	8 mA	HCI UART data transmit	
7	AUD_FSYNC	PD	10	4 mA	PCM frame synch. (NC if not used)	Fail safe ⁴
8	SLOW_CLK_IN		I		32.768-kHz clock in	Fail safe
9	NC		10		Not connected	
10	MLDO_OUT		0		Main LDO output (1.8 V nom.)	
11	CL1.5_LDO_IN		1		PA LDO input	
12	GND				Connect to Ground	
13	RF		10		Bluetooth RF IO	
14	GND				Connect to Ground	
15	MLDO_IN		I		Main LDO input	
16	nSHUTD	PD	1		Shutdown input (active low).	
17	AUD_OUT	PD	0	4 mA	PCM data output. (NC if not used)	Fail safe
18	AUD_IN	PD	1	4 mA	PCM data input. (NC if not used)	Fail safe
19	AUD_CLK	PD	10	HY, 4 mA	PCM clock. (NC if not used)	Fail safe
20	GND				Connect to Ground	
21	NC				EEPROM I2C SDA (Internal)	
22	VDD_IO		PI		I/O power supply 1.8 V Nom	
23	NC				EEPROM I ² C SCL (Internal)	
24	NC		10		Not connected	


² I = input; O = output; IO = bidirectional; P = power; PU = pulled up; PD = pulled down

³ I/O Type: Digital I/O cells. HY = input hysteresis, current = typ. output current

⁴ No signals are allowed on the IO pins if no VDD_IO (Pin 22) power supplied, except pin 7, 8, 17-19.

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT C	LASS 1	or 2 BLUETOOTH MODULE	PAGE	9 of 6	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20)15

5.1.2 5.1.2. Terminal Layout PAN132x with antenna



No	Pin Name	Pull at Reset	Def. Dir. ⁵	I/O Type ⁶	Description of Options (Common)
Α	GND				Connect to Ground
В	GND				Connect to Ground
С	GND				Connect to Ground
D	GND				Connect to Ground

No 1-24 see above in Chapter 5.1.1. Except PIN 13 is not connected. For RF conducted measurements, either use the PAN1323ETU or de-solder the antenna and solder an antenna connector to the hot pin.

PANASONIC INDUSTRIAL DEVICES EUROPE GMBH

 $^{^{5}}$ I = input; O = output; IO = bidirectional; P = power; PU = pulled up; PD = pulled down

 $^{^{6}}$ I/O Type: Digital I/O cells. HY = input hysteresis, current = typ. output current

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	10 of	60
CUSTOMER'S CODE PAN13XX Core Speci		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

5.2 PIN DESCRIPTION

Pin Name	No	ESD ⁷ (V)	Pull at Reset	Def. Dir. ⁸	I/O Type ⁹	Description of Options		
Bluetooth IO SIGI	NALS							
HCI_RX	5	750	PU	1	8 mA	HCI UART data receive		
HCI_TX	6	750	PU	0	8 mA	HCI UART data transmit		
HCI_RTS	4	750	PU	0	8 mA	HCI UART request-to-send.		
HCI_CTS	3	750	PU	I	8 mA	HCI UART clear-to-send.		
AUD_FYSNC	7	500	PD	Ю	4 mA	PCM frame synch (NC if not used) Fail safe		
AUD_CLK	19	500	PD	Ю	HY, 4 mS	PCM clock (NC if not used) Fail safe		
AUD_IN	18	500	PD	I	4 mA	PCM data input (NC if not used) Fail safe		
AUD_OUT	17	500	PD	0	4 mA	PCM data output (NC if not used) Fail safe		
TV DDG	•	1000				Logger output		
TX_DBG	2	1000	PU	0	2 mA	OPTION: nTX_DBG – logger out (low = 1)		
CLOCK SIGNALS								
SLOW_CLK_IN	8	1000		ı		32.768-kHz clock in Fail safe		
Bluetooth ANALO	G SIG	NALS	<u> </u>		•			
RF	13	1000		Ю		Bluetooth RF IO (not connected with antenna)		
nSHUTD	16	1000	PD	I		Shutdown input (active low).		
Bluetooth POWEI	R AND	GND SI	IGNALS	•		, , , , , ,		
VDD_IO	22	1000		PI		I/O power supply 1.8 V Nom		
MLDO_IN	15	1000		Ι		Main LDO input Connect directly to battery or to a pre-regulated 1.8-V supply		
MLDO_OUT	10	1000		0		Main LDO output (1.8 V nom.) Can not be used as 1.8V supply due to internal connection to the RF part.		
CL1.5_LDO_IN	11	1000		I		PA LDO input Connect directly to battery or to a pre-regulated 1.8-V supply		
GND	1			Р		Connect to Ground		
GND	12			Р		Connect to Ground		
GND	14			Р		Connect to Ground		
GND	20			Р		Connect to Ground		
EEPROM IO SIG	NALS	(EEPRO	M is option	al in PA	N13x produc	t line)		
NC	23	1000	PU/PD	I	HY, 4mA	EEPROM I ² C SCL (Internal)		
NC	21	1000	PU/PD	Ю	HY, 4mA	EEPROM I ² C IRQ (Internal)		

Remark:

HCI_CTS is an input signal to the CC256X device:

- When HCI_CTS is low, then CC256X is allowed to send data to Host device.
- When HCI_CTS is high, then CC256X is not allowed to send data to Host device.

⁸ I = input; O = output; IO = bidirectional; P = power; PU = pulled up; PD = pulled down

⁷ ESD: Human Body Model (HBM). JEDEC 22-A114

⁹ I/O Type: Digital I/O cells. HY = input hysteresis, current = typ output current

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	11 of (60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

5.3 DEVICE POWER SUPPLY

The PAN13XX Bluetooth radio solution is intended to work in devices with a limited power budget such as cellular phones, headsets, hand-held PC's and other battery-operated devices. One of the main differentiators of the PAN13XX is its power management – its ability to draw as little current as possible.

The PAN13XX device requires two kinds of power sources:


- Main power supply for the Bluetooth VDD_IN = V_{BAT}
- Power source for the 1.8 V I/O ring VDD_IO

The PAN13XX includes several on-chip voltage regulators for increased noise immunity. The PAN13XX can be connected either directly to the battery or to an external 1.8-V DC to DC converter.

There are three ways to supply power:


• Full-V_{BAT} system:

Maximum RF output power, but not optimum system power:



• Full-DC2DC system:


Lower RF output power, but optimum system power:



CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT C	LASS 1	or 2 BLUETOOTH MODULE	PAGE	12 of (60
CUSTOMER'S CODE PAN13XX Core Specification	ation	PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20)15

• Mixed DC2DC-V_{BAT} system:

Maximum RF output power and optimum system power, but requires routing of V_{BAT}:



5.4 CLOCK INPUTS

The slow clock is always supplied from an external source. It is connected to the SLOW_CLK_IN pin number 8 and can be a digital signal with peak to peak of 0-1.8 V.

The slow clock's frequency accuracy must be $32.768 \text{ kHz} \pm 250 \text{ ppm}$ for Bluetooth usage (according to the Bluetooth specification).


The Slow Clock 32.768 kHz is mandatory to start the internal controller, otherwise the module does not start up.


6 BLUETOOTH FEATURES

- Support of Bluetooth2.1+EDR (Lisbon Release) up to HCI level.
- Very fast AFH algorithm for both ACL and eSCO.
- Supports typically 4 dBm Class 2 TX power w/o external PA, improving Bluetooth link robustness. Adjusting the host settings, the TX power can be increased to 10 dBm. However it is important, that the national regulations and Bluetooth specification are met.
- Digital Radio Processor (DRP) single-ended 50 ohm.
- Internal temperature detection and compensation ensures minimal variation in the RF performance over temperature.
- Flexible PCM and I2S digital audio/voice interfaces: Full flexibility of data-format (Linear, a-Law, μ-Law), data-width, data order, sampling and slot positioning, master/slave modes, high clock rates up to 15 MHz for slave mode (or 4.096 MHz for Master Mode). Lost packet concealment for improved audio.
- Proprietary low-power scan method for page and inquiry scans, achieves page and inquiry scans at 1/3rd normal power.

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-24	400-102	REV. 4.8
SUBJECT CLASS 1 or 2 BLUETOOTH MODULE			PAGE	13 of	60
CUSTOMER'S COD PAN13XX Core Spec		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

7 BLOCK DIAGRAM





Note: The Slow Clock 32.768 kHz is mandatory, otherwise the module does not start up, refer to Chapter 5.4 for additional information.

Note: The IO are 1.8V driven and might need external level shifter and LDO. The MLDO_OUT PIN can not be used as reference due to RF internal connection.

The total capacity will not exceed 2.8uF and the total inductance will not exceed 0nH. There are no voltage multiplying or voltage boosting circuits.

CLASSIFICATION	PRODUCT SPECIFICATION	No. DS-13xx-2400-10)2	REV. 4.8
SUBJECT CLASS ?	or 2 BLUETOOTH MODULE	PAGE	14 of (60
CUSTOMER'S CODE PAN13XX Core Specification	PANASONIC'S CODE See Chapter Ordering Information	DATE 2	23.09.20	015

8 TEST CONDITIONS

Measurements shall be made under room temperature and humidity unless otherwise specified.

9 GENERAL DEVICE REQUIREMENTS AND OPERATION

Temperature 25 \pm 10°C Humidity 40 to 85%RH

SW-Patch V2.30 Supply Voltage 3.3V

All specifications are over temperature and process, unless indicated otherwise.

9.1 ABSOLUTE MAXIMUM RATINGS

Over operating free-air temperature range (unless otherwise noted).

Note

All parameters are measured as follows unless stated otherwise:

 $VDD_IN^{10} = 3.3 \text{ V}, VDD_IO = 1.8 \text{ V}.$

No	See 11		Value	Unit
Rati	ngs Over Operatir			
1	VDD_IN	Supply voltage range	-0.5 to 5.5	V 12
2	VDDIO_1.8V		-0.5 to 2.145	V
3	Input voltage to I	RF (Pin 13)	-0.5 to 2.1	V

 $^{^{10}}$ VDD_IN is supplied to MLDO_IN (Pin 15) and CL1.5_LDO_IN (Pin 11), other options are described in Chapter 5.3.

¹¹ Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

Maximum allowed depends on accumulated time at that voltage: VDD_IN is defined in Reference schematics. When DC2DC supply is used, maximum voltage into MLDO_OUT and LDO_IN = 2.145 V.

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	15 of (60
CUSTOMER'S CODE PAN13XX Core Specif		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20)15

No	See ¹¹	Value	Unit
4	Operating ambient temperature range	-40 to 85 ¹³	°C
5	Storage temperature range	-40 to 125	°C
6	Bluetooth RF inputs (Pin 13)	10	dBm
7	ESD: Human Body Model (HBM). JEDEC 22-A114	500	٧

9.2 RECOMMENDED OPERATING CONDITIONS

No	Rating	Condition	Symbol	Min	Max	Unit
1	Power supply voltage 14		VDD_IN	1.7	4.8	V
2	IO power supply voltage		VDD_IO	1.62	1.92	V
3	High-level input voltage	Default	V _{IH}	0.65 x VDD_IO	VDD_IO	V
4	Low-level input voltage	Default	V _{IL}	0	0.35 x VDD_IO	V
5	IO Input rise/fall times, 10% to 90% 15		Tr/Tf	1	10	ns
		0 to 0.1 MHz			60	
		0.1 to 0.5 MHz			50	
6	Maximum ripple on VDD_IN (Sine wave) for 1.8 V (DC2DC) mode	0.5 to 2.5 MHz			30	mVp-p
	1.5 (2525) 11150	2.5 to 3.0 MHz			15	
		> 3.0 MHz			5	
7	Voltage dips on VDD_IN (V_{BAT}) (duration = 577 μ s to 2.31 ms, period = 4.6 ms)				400	mV
8	Maximum ambient operating temperature ¹⁶				85	°C
9	Minimum ambient operating temperature 17				-40	□С

¹³ Older generation parts, which are not recommended for new designs, will support a temperature range -20 to 70. See chapter 28, ordering information, for details.

¹⁴ Excluding 1.98 < VDD_IN < 2.2 V range – not allowed.

¹⁵ Asynchronous mode.

¹⁶ The device can be reliably operated for 7 years at T_{ambient} of 85°C, assuming 25% active mode and 75% sleep mode (15,400 cumulative active power-on hours).

Older generation parts, which are not recommended for new designs, will support a temperature range -20 to 70. See chapter 28, ordering information, for details.

¹⁷ The device can be reliably operated for 7 years at T_{ambient} of 85°C, assuming 25% active mode and 75% sleep mode (15,400 cumulative active power-on hours).

Older generation parts, which are not recommended for new designs, will support a temperature range -20 to 70. See chapter 28, ordering information, for details.

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	16 of (60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

9.3 CURRENT CONSUMPTION

No	Characteristics	Min 25°C	Typ 25°C	Max 25°C	Min -40°C	Typ -40°C	Max -40°C	Min +85°C	Typ +85°C	Max +85°C	Unit
1	Current consumption in shutdown mode 18		1	3						7	μА
2	Current consumption in deep sleep mode 19		40	105						700	μА
3	Total IO current consumption for active mode			1			1			1	mA
4	Current consumption during transmit DH5 full throughput		40								mA

¹⁸ Vbat + Vio

¹⁹ Vbat + Vio + Vsd (shutdown)

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	-102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	17 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

9.4 GENERAL ELECTRICAL CHARACTERISTICS

No	Rating	Rating		Condition	Min	Max	Value
1	High lovel outp	ut voltage \/		at 2/4/8 mA	0.8 x VDD_IO	VDD_IO	V
'	High-level outpo	ut voltage, v _{oh}		at 0.1 mA	VDD_IO - 0.2	VDD_IO	V
2	Law layed autau	ut valtage V		at 2/4/8 mA	0	0.2 x VDD_IO	V
2	2 Low-level output voltage, V _{OL}			at 0.1 mA	0	0.2	V
3	10 invating a large			Resistance	1		MΩ
3	IO input impeda	ance		Capacitance		5	pF
4	Output rise/fall	times,10% to 909	% (Digital pins)	C _L = 20 pF		10	Ns
		TX_DBG,	PU	typ = 6.5	3.5	9.7	
_	5 IO pull currents	PCM bus	PD	typ = 27	9.5	55	μΑ
3		All others	PU	typ = 100	100	300	
		All others	PD	typ = 100	100	360	μΑ

9.5 NSHUTD REQUIREMENTS

No	Parameter	Symbol	Min	Max	Unit
1	Operation mode level ²⁰	V _{IH}	1.42	1.98	V
2	Shutdown mode level	V _{IL}	0	0.4	V
3	Minimum time for nSHUT_DOWN low to reset the device		5		ms
4	Rise/fall times	Tr/Tf		20	μs

9.6 EXTERNAL DIGITAL SLOW CLOCK REQUIREMENTS

No	Characteristics	Condition	Symbol	Min	Тур	Max	Unit
1	Input slow clock frequency				32768		Hz
2	Input slow clock accuracy (Initial + temp + aging)	Bluetooth				±250	Ppm
3	Input transition time Tr/Tf – 10% to 90%		Tr/Tf			100	Ns
4	Frequency input duty cycle			15%	50%	85%	
5	Phase noise	at 1 kHz				-125	dBc/Hz
6	Jitter	Integrated over 300 to 15000 Hz				1	Hz
7	7 Slow clock input voltage limits	Square wave, DC coupled	V _{IH}	0.65 x VDD_IO		VDD_IO	- V peak
1		Square wave, DC coupled	V _{IL}	0		0.35 x VDD_IO	
8	Input impedance			1			MΩ
9	Input capacitance					5	pF

 $^{^{20}}$ Internal pull down retains shut down mode when no external signal is applied to this pin.

CLASSIFICATION	PR	CONTROL SPECIEICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT CI	LASS 1 or	2 BLUETOOTH MODULE	PAGE	18 of 6	60
CUSTOMER'S CODE PAN13XX Core Specification		ANASONIC'S CODE ee Chapter Ordering Information	DATE	23.09.20)15

10 HOST CONTROLLER INTERFACE

The CC256X incorporates one UART module dedicated to the host controller interface (HCI) transport layer. The HCI interface transports commands, events, ACL, and synchronous data between the Bluetooth device and its host using HCI data packets.


The UART module supports H4 (4-wires) protocol with maximum baud rate of 4 Mbps for all fast clock frequencies.

After power up the baud rate is set for 115.2 kbps, irrespective of fast clock frequency. The baud rate can thereafter be changed with a vendor specific command. The CC256X responds with a Command Complete Event (still at 115.2 kbps), after which the baud rate change takes place. HCl hardware includes the following features:

- Receiver detection of break, idle, framing, FIFO overflow, and parity error conditions
- Transmitter underflow detection
- CTS/RTS hardware flow control

The interface includes four signals: TXD, RXD, CTS, and RTS. Flow control between the host and the CC256X is byte-wise by hardware.

Flow control is obtained by the following:



When the UART RX buffer of the CC256X passes the "flow control" threshold, it will set the UART_RTS signal high to stop transmission from the host.

When the UART_CTS signal is set high, the CC256X will stop its transmission on the interface. In case HCI_CTS is set high in the middle of transmitting a byte, the CC256X will finish transmitting the byte and stop the transmission.

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-24	100-102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	19 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

11 AUDIO/VOICE CODEC INTERFACE

The codec interface is a fully-dedicated programmable serial port that provides the logic to interface to several kinds of PCM or I2S codec's. PAN13XX supports all voice coding schemes required by Bluetooth specification – Log PCM (A-Law or μ -Law) and Linear (CVSD). In addition, module also supports transparent scheme:

- Two voice channels
- · Master / slave modes
- μ-Law, A-Law, Linear, Transparent coding schemes
- · Long and short frames
- Different data sizes, order, and positions.
- High rate PCM interface for EDR
- Enlarged interface options to support a wider variety of codecs
- PCM bus sharing

11.1 PCM HARDWARE INTERFACE

The PCM interface is one implementation of the codec interface. It contains the following four lines:

- Clock—configurable direction (input or output)
- Frame Sync—configurable direction (input or output)
- Data In—Input
- Data Out—Output/3-state

The Bluetooth device can be either the master of the interface where it generates the clock and the frame-sync signals, or slave where it receives these two signals. The PCM interface is fully configured by a vendor specific command.

For slave mode, clock input frequencies of up to 16 MHz are supported. At clock rates above 12 MHz, the maximum data burst size is 32 bits. For master mode, the CC256X can generate any clock frequency between 64 kHz and 6 MHz.

When the I2S bus is used in an application, Panasonic recommends adding a low pass filter (series resistor and capacitor to GND) to the bus for better noise suppression. Connecting the host μ Controller/DSP directly with the module's I2S interface is not recommended.

The suggested low pass filter component values are:

470pf 120 ohms

11.2 DATA FORMAT

The data format is fully configurable:

• The data length can be from 8 to 320 bits, in 1-bit increments, when working with two channels, or up to 640 bits when using 1 channel. The Data length can be set independently for each channel.

CLASSIFICATION	PRODUCT SPECIFICATION	No. DS-13xx-2400-102	REV. 4.8
SUBJECT CLA	ASS 1 or 2 BLUETOOTH MODULE	PAGE 20 o	f 60
CUSTOMER'S CODE PAN13XX Core Specificat	PANASONIC'S CODE See Chapter Ordering Informatio	DATE 23.09	2015

- The data position within a frame is also configurable in with 1 clock (bit) resolution and can be set independently (relative to the edge of the Frame Sync signal) for each channel.
- The Data_In and Data_Out bit order can be configured independently. For example; Data_In can start with the MSB while Data_Out starts with LSB. Each channel is separately configurable. The inverse bit order (that is, LSB first) is supported only for sample sizes up to 24 bits.
- It is not necessary for the data in and data out size to be the same length.
- The Data_Out line is configured to 'high-Z' output between data words. Data_Out can also be set for permanent high-Z, irrespective of data out. This allows the CC256X to be a bus slave in a multi-slave PCM environment. At powerup, Data Out is configured as high-Z.

11.3 FRAME IDLE PERIOD

The codec interface has the capability for frame idle periods, where the PCM clock can "take a break" and become '0' at the end of the PCM frame, after all data has been transferred.

The CC256X supports frame idle periods both as master and slave of the PCM bus.


When CC256X is the master of the interface, the frame idle period is configurable. There are two configurable parameters:

- Clk_Idle_Start Indicates the number of PCM clock cycles from the beginning of the frame until the beginning of the idle period. After Clk_Idle_Start clock cycles, the clock will become '0'.
- Clk_Idle_End Indicates the time from the beginning of the frame till the end of the idle period. This time is given in multiples of PCM clock periods.

The delta between Clk_Idle_Start and Clk_Idle_End is the clock idle period.

For example, for PCM clock rate = 1 MHz, frame sync period = 10 kHz, Clk_Idle_Start = 60, Clk_Idle_End = 90.

Between each two frame syncs there are 70 clock cycles (instead of 100). The clock idle period starts 60 clock cycles after the beginning of the frame, and lasts 90 - 60 = 30 clock cycles. This means that the idle period ends 100 - 90 = 10 clock cycles before the end of the frame. The data transmission must end prior to the beginning of the idle period.




CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-24	100-102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	21 of	60
CUSTOMER'S CODI PAN13XX Core Spec		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

11.4 CLOCK-EDGE OPERATION


The codec interface of the CC256X can work on the rising or the falling edge of the clock. It also has the ability to sample the frame sync and the data at inversed polarity.

This is the operation of a falling-edge-clock type of codec. The codec is the master of the PCM bus. The frame sync signal is updated (by the codec) on the falling clock edge and therefore shall be sampled (by the CC256X) on the next rising clock. The data from the codec is sampled (by the CC256X) on the clock falling edge.



11.5 TWO-CHANNEL PCM BUS EXAMPLE

In below figure, a 2-channel PCM bus is shown where the two channels have different word sizes and arbitrary positions in the bus frame. (FT stands for Frame Timer)



11.6 AUDIO ENCODING

The CC256X codec interface can use one of four audio-coding patterns:

- A-Law (8-bit)
- µ-Law (8-bit)
- Linear (8- or 16-bit)

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT C	LASS 1	or 2 BLUETOOTH MODULE	PAGE	22 of (60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

11.7 IMPROVED ALGORITHM FOR LOST PACKETS

The CC256X features an improved algorithm for improving voice quality when received voice data packets are lost. There are two options:

- Repeat the last sample possible only for sample sizes up to 24 bits. For sample sizes >24 bits, the last byte is repeated.
- Repeat a configurable sample of 8 to 24 bits (depends on the real sample size), in order to simulate silence (or anything else) in the PCM bus. The configured sample will be written in a specific register for each channel.

The choice between those two options is configurable separately for each channel.

11.8 BLUETOOTH/PCM CLOCK MISMATCH HANDLING

In Bluetooth RX, the CC256X receives RF voice packets and writes these to the codec I/F. If the CC256X receives data faster than the codec I/F output allows, an overflow will occur. In this case, the Bluetooth has two possible behaviour modes: 'allow overflow' and 'don't allow overflow'.

- If overflow is allowed, the Bluetooth will continue receiving data and will overwrite any data not yet sent to the codec.
- If overflow is not allowed, RF voice packets received when buffer is full will be discarded.

11.9 BLUETOOTH INTER-IC SOUND (I2S)

The CC256X can be configured as an Inter-IC Sound (I2S) serial interface to an I2S codec device. In this mode, the CC256X audio codec interface is configured as a bi-directional, full-duplex interface, with two time slots per frame: Time slot 0 is used for the left channel audio data and time slot 1 for the right channel audio data. Each time slot is configurable up to 40 serial clock cycles in length and the frame is configurable up to 80 serial clock cycles in length.

Do not connect the the microcontroller/DSP directly to the module's PCM interface, a simple RC low pass filter is recommended to improve noise suppression.

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	23 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

11.10 CURRENT CONSUMPTION FOR DIFFERENT BLUETOOTH SCENARIOS

The following table gives average current consumption for different Bluetooth scenarios. Conditions: VDD_IN = 3.6 V, 25°C, 26-MHz fast clock, nominal unit, 4 dBm output power.

Mode Description	Master/Slave	Average Current	Unit
Idle current (ARM off)	Master/Slave	2.5	mA
SCO link HV3	Master/Slave	12	mA
eSCO link EV3 64 kbps, no retransmission	Master/Slave	11.5	mA
eSCO link 2-EV3 64 kbps, no retransmission	Master/Slave	8.3	mA
GFSK full throughput: TX = DH1, RX = DH5	Master/Slave	38.5	mA
EDR full throughput: TX = 2-DH1, RX = 2-DH5	Master/Slave	39.2	mA
EDR full throughput: TX = 3-DH1, RX = 3-DH5	Master/Slave	39.2	mA
Sniff, 1 attempt, 1.28 s	Master/Slave	76/100	μА
Page or Inquiry Scan 1.28 s, 11.25 ms	Master/Slave	300	μА
Page (1.28 s) and Inquiry (2.56 s) scans, 11.25 ms	Master/Slave	430	μА
Low power scan, 1.28-s interval, quiet environment	Master/Slave	135	μА

12 BLUETOOTH RF PERFORMANCE

No	Characteristics	Тур	BT Spec Max	BT Spec Min
			Class1	Class1
1	Average Power Hopping DH5 [dBm] ^{22, 23}	7.2	20	4
2	Average Power: Ch0 [dBm] ^{22, 23}	7.5	20	4
3	Peak Power: Ch0 [dBm] ^{22, 23}	7.7	23	
4	Average Power: Ch39 [dBm] ^{22, 23}	7.0	20	4
5	Peak Power: Ch39 [dBm] ^{22, 23}	7.2	23	
6	Average Power: Ch78 [dBm] ^{22, 23}	6.7	20	4
7	Peak Power: Ch78 [dBm] ^{22, 23}	7.0	23	
8	Max. Frequency Tolerance: Ch0 [kHz]	-2.6	75	-75
9	Max. Frequency Tolerance: Ch39 [kHz]	-2.2	75	-75
10	Max. Frequency Tolerance: Ch78 [kHz]	-2.1	75	-75
11	Max. Drift: Ch0_DH1 [kHz]	3.6	25	-25
12	Max. Drift: Ch0_DH3 [kHz]	3.7	40	-40
13	Max. Drift: Ch0_DH5 [kHz]	4.0	40	-40
14	Max. Drift Rate: Ch0_DH1 [kHz]	-2.6	20	-20
15	Max. Drift Rate: Ch0_DH3 [kHz]	-3.2	20	-20
16	Max. Drift Rate: Ch0_DH5 [kHz]	-3.3	20	-20
17	Max. Drift: Ch39_DH1 [kHz]	4.0	25	-25
18	Max. Drift: Ch39_DH3 [kHz]	4.3	40	-40
19	Max. Drift: Ch39_DH5 [kHz]		40	-40
20	Max. Drift Rate: Ch39_DH1 [kHz]	-3.1	20	-20
21	Max. Drift Rate: Ch39_DH3 [kHz]	-3.6	20	-20

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-24	100-102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	24 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

No	Characteristics	Тур	BT Spec Max	BT Spec Min
			Class1	Class1
22	Max. Drift Rate: Ch39_DH5 [kHz]	-3.7	20	-20
23	Max. Drift: Ch78_DH1 [kHz]		25	-25
24	Max. Drift: Ch78_DH3 [kHz]	4.5	40	-40
25	Max. Drift: Ch78_DH5 [kHz]	4.4	40	-40
26	Max. Drift Rate: Ch78_DH1 [kHz]	-3.4	20	-20
27	Max. Drift Rate: Ch78_DH3 [kHz]	-3.9	20	-20
28	Max. Drift Rate: Ch78_DH5 [kHz]	-4.1	20	-20
29	Delta F1 Avg: Ch0 [kHz]	159.5	175	140
30	Delta F2 Max.: Ch0 [%]	100.0		99.9
31	Delta F2 Avg/Delta F1 Avg: Ch0	0.9		0.8
32	Delta F1 Avg: Ch39 [kHz]	159.8	175	140
33	Delta F2 Max.: Ch39 [%]	100.0		99.9
34	Delta F2 Avg/Delta F1 Avg: Ch39	0.9		0.8
35	Delta F1 Avg: Ch78 [kHz]	159.1	175	140
36	Delta F2 Max.: Ch78 [%]	100.0		99.9
37	Delta F2 Avg/Delta F1 Avg: Ch78	0.9		0.8
45	Sensitivity	-93.0		-81
46	f(H)-f(L): Ch0 [kHz]	918.4	1000	
47	f(H)-f(L): Ch39 [kHz]	918.3	1000	
48	f(H)-f(L): Ch78 [kHz]	918.2	1000	
49	ACPower -3: Ch3 [dBm]	-51.5	-40	
50	ACPower -2: Ch3 [dBm]	-50.4	-40	
51	ACPower -1: Ch3 [dBm]	-18.5		
52	ACPower Center: Ch3 [dBm]	8.1	20	4
53	ACPower +1: Ch3 [dBm]	-19.2		
54	ACPower +2: Ch3 [dBm]	-50.7	-40	
55	ACPower +3: Ch3 [dBm]	-53.3	-40	
56	ACPower -3: Ch39 [dBm]	-51.6	-40	
57	ACPower -2: Ch39 [dBm]	-50.7	-40	
58	ACPower -1: Ch39 [dBm]	-19.0		
59	ACPower Center: Ch39 [dBm]	7.7	20	4
60	ACPower +1: Ch39 [dBm]	-19.7		
61	ACPower +2: Ch39 [dBm]	-50.9	-40	
62	ACPower +3: Ch39 [dBm]	-53.2	-40	
63	ACPower -3: Ch75 [dBm]	-51.7	-40	
64	ACPower -2: Ch75 [dBm]	-50.7	-40	
65	ACPower -1: Ch75 [dBm]	-19.2		
66	ACPower Center: Ch75 [dBm]	7.5	20	4
67	ACPower +1: Ch75 [dBm]	-20.0		
68	ACPower +2: Ch75 [dBm]	-51.0	-40	
69	ACPower +3: Ch75 [dBm]	-53.4	-40	
70	omega i 2-DH5: Ch0 [kHz]	-4.7	75	-75
71	omega o + omega i 2-DH5: Ch0 [kHz]	-6.0	75	-75
72	omega o 2-DH5: Ch0 [kHz]	-1.5	10	-10
73	DEVM RMS 2-DH5: Ch0 [%]	0.0	0.2	

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-24	100-102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	25 of	60
CUSTOMER'S COD PAN13XX Core Spec		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

No	Characteristics	Тур	BT Spec Max	BT Spec Min
			Class1	Class1
74	DEVM Peak 2-DH5: Ch0 [%]		0.35	
75	DEVM 99% 2-DH5: Ch0 [%]	100.0		99
76	omega i 3-DH5: Ch0 [kHz]	-3.7	75	-75
77	omega o + omega i 3-DH5: Ch0 [kHz]	-5.8	75	-75
78	omega o 3-DH5: Ch0 [kHz]	-2.6	10	-10
79	DEVM RMS 3-DH5: Ch0 [%]	0.0	0.13	
80	DEVM Peak 3-DH5: Ch0 [%]	0.1	0.25	
81	DEVM 99% 3-DH5: Ch0 [%]	100.0		99
82	omega i 2-DH5: Ch39 [kHz]	-4.8	75	-75
83	omega o + omega i 2-DH5: Ch39 [kHz]	-6.1	75	-75
84	omega o 2-DH5: Ch39 [kHz]	-1.4	10	-10
85	DEVM RMS 2-DH5: Ch39 [%]	0.0	0.2	
86	DEVM Peak 2-DH5: Ch39 [%]	0.1	0.35	
87	DEVM 99% 2-DH5: Ch39 [%]	100.0		99
88	omega i 3-DH5: Ch39 [kHz]	-3.8	75	-75
89	omega o + omega i 3-DH5: Ch39 [kHz]	-5.9	75	-75
90	omega o 3-DH5: Ch39 [kHz]	-2.6	10	-10
91	DEVM RMS 3-DH5: Ch39 [%]	0.0	0.13	
92	DEVM Peak 3-DH5: Ch39 [%]	0.1	0.25	
93	DEVM 99% 3-DH5: Ch39 [%]	100.0		99
94	omega i 2-DH5: Ch78 [kHz]	-4.9	75	-75
95	omega o + omega i 2-DH5: Ch78 [kHz]	-6.2	75	-75
96	omega o 2-DH5: Ch78 [kHz]	-1.4	10	-10
97	DEVM RMS 2-DH5: Ch78 [%]	0.0	0.2	
98	DEVM Peak 2-DH5: Ch78 [%]	0.1	0.35	
99	DEVM 99% 2-DH5: Ch78 [%]	100.0		99
100	omega i 3-DH5: Ch78 [kHz]	-3.8	75	-75
101	omega o + omega i 3-DH5: Ch78 [kHz]	-6.0	75	-75
102	omega o 3-DH5: Ch78 [kHz]	-2.7	10	-10
103	DEVM RMS 3-DH5: Ch78 [%]	0.0	0.13	
104	DEVM Peak 3-DH5: Ch78 [%]	0.1	0.25	
105	DEVM 99% 3-DH5: Ch78 [%]	100.0		99


No	Characteristics	Condition	Min	Тур	Max	BT Spec	Unit
1	Operation frequency range		2402		2480		MHz
2	Channel spacing			1			MHz
3	Input impedance			50			Ω
		GFSK, BER = 0.1%		-93.0		-70	
4	4 Sensitivity, Dirty Tx on	Pi/4-DQPSK, BER = 0.01%		-92.5		-70	dBm
		8DPSK, BER = 0.01%		-85.5		-70	

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	26 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

No	Characteristics	Condition	Тур	Max	Unit
1	Tx and Rx out-of-band emissions	30 kHz to 1 GHz ²¹ , ²² , ²³		-30	dBm
Output signal = 7dBn	Output signal = 7dBm	1 to 12.75 GHz ^{21, 22, 23}		-30	UDIII
2	2 nd harmonic	at 7dBm output power ^{21, 22, 23}		-30	dBm
3	3 rd harmonic	at 7dBm output power ^{21, 22, 23}		-30	dBm

The values are measured conducted. Better suppression of the spurious emissions with an antenna can be expected as, antenna frequently have band pass filter characteristics.

13 SOLDERING TEMPERATURE-TIME PROFILE (FOR REFLOW SOLDERING) 13.1 FOR LEAD SOLDER




²¹ Includes effects of frequency hopping

²² Average according FCC, IC and ETSI requirements. Above +7dBm output power (refer also to 23) the customer has to verify the final product against national regulations.

²³ +7dBm related to power register value 18, according to TI service pack 2.30

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-24	00-102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	27 of	60
CUSTOMER'S COD PAN13XX Core Spec		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.2	015

13.2 FOR LEADFREE SOLDER



Reflow permissible cycle: 2 Opposite side reflow is prohibited due to module weight.

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-24	100-102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	28 of	60
CUSTOMER'S COD PAN13XX Core Spec		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015


14 MODULE DIMENSION


14.1 MODULE DIMENSIONS PAN131X WITHOUT ANTENNA


No.	Item	Dimension	Tolerance	Remark
1	Width	6.50	± 0.20	
2	Lenght	9.00	± 0.20	
3	Height	1.80	± 0.20	With case

PAN131X Module Drawing










CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-24	100-102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	29 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015


14.2 MODULE DIMENSIONS PAN132X WITH ANTENNA

No.	Item	Dimension	Tolerance	Remark
1	Width	9.50	± 0.20	
2	Lenght	9.00	± 0.20	
3	Height	1.80	± 0.20	With case

PAN132X Module Drawing








CLASSIFICATION	F	PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	30 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

15 FOOTPRINT OF THE MODULE

15.1 FOOTPRINT PAN131X WITHOUT ANTENNA

All dimensions are in millimeters. The outer dimensions have a tolerance of \pm 0.2mm.

The layout is symetric to center. The inner pins (2,4,6,9,11,14,16,18,21,23) are shifted to the center by 1mm.




CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	-102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	31 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

15.2 FOOTPRINT PAN132X WITH ANTENNA


All dimensions are in millimeters. The outer dimensions have a tolerance of \pm 0.2mm.


The layout is symetric to center. The inner pins (2,4,6,9,11,14,16,18,21,23) are



CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	32 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015


16 LABELING DRAWING





The above pictures show the laser marking on the top case, this is only an example from PAN1315.

For the antenna versions the label includes the MIC certification numbers. For example:



17 MECHANICAL REQUIREMENTS


No.	Item	Limit	Condition
1	Solderability	More than 75% of the soldering area shall be coated by solder	Reflow soldering with recommendable temperature profile
2	Resistance to soldering heat	It shall be satisfied electrical requirements and not be mechanical damage	See Chapter 13.2

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-24	100-102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	33 of (60
CUSTOMER'S COD PAN13XX Core Spec		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

18 RECOMMENDED FOOT PATTERN

18.1 RECOMMENDED FOOT PATTERN PAN131X WITHOUT ANTENNA

Dimensions in mm.



The land pattern dimensions above are meant to serve only as a guide. This information is provided without any legal liability.

For the solder paste screen, use as a first guideline the same foot print as shown in the figure above. Solder paste screen cutouts (with slightly different dimensions) might be optimum depending on your soldering process. For example, the solder paste screen thickness chosen might have an effect. The solder screen thickness depends on your production standard 120µm to 150µm is recommended.

IMPORTANT:

Although the bottom side of PAN131X is fully coated, no copper such as through hole vias, planes or tracks on the board component layer should be located below the PAN131X to avoid creating a short. In cases where a track or through hole via has to be located under the module, it must be kept away from PAN131X bottom pads. The PAN131X multilayer pcb contains an inner RF shielding plane, therefore no pcb shielding plane below the module is needed.

When using an onboard ceramic antenna, place the antenna on the edge of your carrier board (if allowable).


If you have any questions on these points, contact your local Panasonic representative.

Schematics and layouts may be sent to <u>wireless@eu.panasonic.com</u> for final review.

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT (CT CLASS 1 or 2 BLUETOOTH MODULE			34 of (60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

18.2 RECOMMENDED FOOT PATTERN PAN132X WITH ANTENNA

Dimensions in mm.



The land pattern dimensions above are meant to serve only as a guide.

For the solder paste screen, use as a first guideline the same foot print as shown in the Figure above. Solder paste screen cutouts (with slightly different dimensions) might be optimum depending on your soldering process. For example, the solder paste screen thickness chosen might have an effect. The solder screen thickness depends on your production standard 120µm to 150µm is recommended.

IMPORTANT: In cases where a track or through hole via has to be located under the module, it must be kept away from PAN132X bottom pads. The PAN132X multilayer pcb contains an inner RF shielding plane, therefore no pcb shielding plane below the module is needed.

If you have any questions on these points, contact your local Panasonic representative.

Schematics and layouts may be sent to wireless@eu.panasonic.com for final review.

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-24	100-102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	35 of	60
CUSTOMER'S COD PAN13XX Core Spec		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

19 RADIATION PATTERN

4.2 Antenna gain(3D measurement)

Table. 1 Condition 1: LDA21K

BT					[dBi]	[dB]
LINEAR		YZ-r	olane	ZX-p	olane	Total
POLARIZATION		hor.	ver.	hor.	ver.	Efficiency
2400 MHz	MAX	-0.2	-14.8	-1.4	-3.3	
2400 11112	AVE	-3.3	-20.4	-6.4	-6.4	-3.1
2442 MHz	MAX	0.9	-12.5	-0.6	-2.1	
2442 WINZ	AVE	-2.4	-19.1	-5.6	-5.1	-2.2
2484 MHz	MAX	-0.4	-13.2	-1.9	-3.1	
2404 WIIIZ	AVE	-3.4	-19.3	-6.8	-5.8	-3.2

4.3 Radiation Pattern(3D measurement)




Fig. 5 Condition 1: LDA21K

CLASSIFICATION	Ī	PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	36 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

20 LAYOUT RECOMMENDATIONS WITH ANTENNA (PAN132X)

PAN132x WITH ANTENNA **PLACEMENT** If possible place PAN132x in the center of mother PCB. Min. 15mm Min. 15mm 5.00 9.00 D С 8 Restricted Area No copper any layer lace PAN132x at the edge of Α В 19 15 mother PCB 9.50 20 12 16 14 21 Pad = 28 x 0.60mm x 0.60mm 11 Min. 40mm 24 8 Use a Ground plane in the area surrounding the PAN132x module wherever

Dimensions are in mm.

possible.

21 BLUETOOTH LE (LOW ENERGY) PAN1316/26

21.1 NETWORK TOPOLOGY

Bluetooth Low Energy is designed to reduce power consumption. It can be put into a sleep mode and is only activated for event activities such as sending files to a gateway, PC or mobile phone. Furthermore the maximum power consumption is set to less than 15 mA and the average power consumption is about 1 uA. The benefit of low energy consumption are short messages and establishing very fast connections (few ms). Using these techniques, energy consumption is reduced to a tenth of a Classic Bluetooth unit. Thus, a small coin cell – such as a CR2032 – is capable of powering a device for up to 10 years of operation.

To be backwards compatible with Classic Bluetooth and to be able to offer an affordable solution for very inexpensive devices, Panasonic Low Energy Bluetooth modules are offered in two versions:

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT C	LASS 1	or 2 BLUETOOTH MODULE	PAGE	37 of (60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

Dual-mode: Bluetooth Low Energy technology combined with Classic Bluetooth functionality on a single module. Dual mode devices act as gateways between these two technologies.

Single Mode: Bluetooth Low Energy technology to optimize power consumption, which is particularly useful for products powered by small batteries. These modules have embedded controllers allowing the module to operate autonomously in low cost applications that lack intelligence.

This data sheet describes dual-mode Bluetooth Low Energy technology combined with Classic Bluetooth functionality on a single module. Additional information on Panasonic's single mode products can be found by visiting www.panasonic.com/rfmodules or write an e-mail to wireless@eu.panasonic.com.

21.2 MODULE FEATURES

Fully compliant with Bluetooth 4.0:

- Optimized for proximity and sports use
- Supports up to 10 simultaneous connections
- Multiple sniff instances are tightly coupled to minimize power consumption
- Independent buffering allows a large number of multiple connections without affecting BR/EDR performance
- Includes built-in coexistence and prioritization handling for BR/EDR and LE

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	38 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

21.3 CURRENT CONSUMPTION FOR DIFFERENT LE SCENARIOS

Conditions: VDD_IN = 3.6 V, 25°C, 26-MHz fast clock, nominal unit, 10 dBm output power

Mode	Description	Average Current	Unit
Advertising, non-connectable	Advertising in all 3 channels 1.28msec advertising interval 15Bytes advertise Data	104	μΑ
Advertising, discoverable	Advertising in all 3 channels 1.28msec advertising interval 15Bytes advertise Data	121	μΑ
Scanning	Listening to a single frequency per window 1.28msec scan interval 11.25msec scan window	302	μΑ
Connected (master role)	500msec connection interval 0msec Slave connection latency Empty Tx/Rx LL packets	169	μΑ

22 ANT PAN1317/27

ANT+ (sometimes ANT + or ANT Plus) is an interoperability function that can be added to the base ANT protocol (a proprietary wireless sensor network technology).[

22.1 NETWORK TOPOLOGY

ANTTM is a wireless sensor network protocol operating in the 2.4 GHz spectrum. Designed for ultra-low power, ease of use, efficiency and scalability, ANT supports peer-to-peer, star, tree and fixed mesh topologies. It provides reliable data communications, flexible and adaptive network operation and cross-talk immunity. The ANT protocol stack is compact, requiring minimal microcontroller resources to reduce system costs, lighten the computational burden and improve efficiency. Low-level security is implemented to allow user-defined network security.

PAN1317/1327 provides the first wireless, single-chip solution with dual-mode ANT and Bluetooth connectivity with inclusion of TI's CC2564 device. This solution wirelessly connects 13 million ANT-based devices to the more than 3 billion Bluetooth endpoint devices used by people every day, creating new market opportunities for companies building ANT products and Bluetooth products alike. CC2564 requires 80% less board area than a design with two single-mode solutions (one ANT+, one Bluetooth) and increases the wireless transmission range up to two times the distance of a single-mode ANT+ solution.

CLASSIFICATION	ſ	PRODUCT SPECIFICATION	No. DS-13xx-2400	-102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	39 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

22.2 MODULE FEATURES

Fully compliant with ANT protocol:

- ANT solution optimized for fitness, health and consumers use cases
- Supports up to eight simultaneous connections, various network topologies and high-resolution proximity pairing
- Includes built-in coexistence and prioritization handling for BR/EDR and ANT

Features	Benefits
Dual-mode ANT+ and Bluetooth (Bluetooth v2.1 + EDR) on a single chip	Requires 80% less board area than any dual module or device design Reduces costs associated with incorporating two wireless technologies
Fully validated optimized single antenna solution	- Enables simultaneous operation of ANT+ and Bluetooth without the need for two devices or modules - Includes built-in coexistence
Best-in-class Bluetooth and ANT RF performance: - +10 dBm Tx power with transmit power control93 dBm sensitivity	Delivers twice the distance between the aggregator and ANT sensor device than competitive single-mode ANT solutions Enables a robust and high-throughput connection with extended range
Support for: - ANT+ ultra low power (master and slave devices) - Bluetooth power saving modes (park, sniff, hold) - Bluetooth ultra low power modes (deep sleep, power down)	- Improves battery life and power efficiency of the finished product
Turnkey solution: - Fully integrated module - Complete development kit with software and documentation - TI MSP430 hardware and software platform integration (optional)	Ease of integration into system allows quick time to market Reduces costs and time associated with certification

22.3 ANT CURRENT CONSUMPTION

Mode	Description	Average Current	Unit
Rx message mode	250msec interval	380	μΑ
Rx message mode	500msec interval	205	μΑ
Rx message mode	1000msec interval	118	μΑ

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	40 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

23 TRIPLE MODE (BR/EDR + BLUETOOTH LOW ENERGY OR ANT) PAN1323

The PAN1323 has been engineered to give designers the flexibility to implement Bluetooth Classic (BR/EDR), Bluetooth Low Energy or ANT into an application using a single module, reducing cost and footprint area. Refer to the paragraphs above for complete descriptions on each of the three protocols. The module is fully hardware compatible with the PAN1315, 16, 17, 25, 26 and 27. A highly efficent single RF block serves all three protocols. Protocols access the RF block using time division multiplexing. The application layer determines the priority and timing of the RF block. Customers interested in this unique module are encouraged to contact StoneStreetOne for a Bluetooth SIG certified stack. Note ANT and BLE can not be used simultaniously.

23.1 TRIPLE MODE CURRENT CONSUMPTION

The current consumption of the PAN1323 is a function of the protocol that the module is running at any point in time. Refer to the paragraphs above for details on current consumption for each of the three protocols or software vendor.


CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	41 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

24 DEVELOPMENT OF APPLICATIONS

Mindtree Ltd. Has developed a Bluetooth SPP freeware for Tis MSP430 and Panasonics PAN1315 and PAN1325. For other software refer to Chapter 25 or visit the following link www.panasonic.com/rfmodules.

24.1 TOOLS TO BE NEEDED

Tool	Source
TI – MSP-EXP430F5438 – Experimenter Board	MSP-EXP430F5438
TI – MSP-FET430UIF430 – Debugging Interface	MSP-FET430UIF430
DANIA 222 EMIC Direct of the Evaluation Madula Vit for MCD 420	ті <u>РАN1323EMK</u>
PAN1323EMK – Bluetooth Evaluation Module Kit for MSP430	Panasonic PAN1323ETU



MSP-EXP430F5438 MSP430F5438 Experimenter Board





PAN1323ETU

In addition you need the software development environment, e.g. IAR Embedded Workbench, refer to:

http://processors.wiki.ti.com/index.php/CC256x_Bluetooth http://processors.wiki.ti.com/index.php/IAR_Embedded_Workbench_for_TI_MSP430

Evaluation kits and modules are available through Panasonic's network of authorized distributors. For any additional information, please visit www.panasonic.com/rfmodules.

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	42 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

25 LIST OF PROFILES

The PAN13xx series is capable of running all Bluetooth profiles, BLE and Classic. Contact a software developer for availability.

26 RELIABILITY TESTS

The measurement should be done after being exposed to room temperature and humidity for 1 hour.

No.	Item	Limit	Condition
1	Vibration test	Electrical parameter should be in specification	a) Freq.:10~50Hz,Amplitude:1.5mm a) 20min. / cycle,1hrs. each of XYZ axis b) Freq.:30~100Hz, 6G b) 20min. / cycle,1hrs. each of XYZ axis
2	Shock test	the same as above	Dropped onto hard wood from height of 50cm for 3 times
3	Heat cycle test	the same as above	-40°C for 30min. and +85°C for 30min.; each temperature 300 cycles
4	Moisture test	the same as above	+60°C, 90% RH, 300h
5	Low temp. test	the same as above	-40°C, 300h
6	High temp. test	the same as above	+85°C, 300h

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	43 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

27 CAUTIONS

Failure to follow the guidelines set forth in this document may result in degrading of the product's functions and damage to the product.

27.1 DESIGN NOTES

- (1) Follow the conditions written in this specification, especially the control signals of this module.
- (2) The supply voltage has to be free of AC ripple voltage (for example from a battery or a low noise regulator output). For noisy supply voltages, provide a decoupling circuit (for example a ferrite in series connection and a bypass capacitor to ground of at least 47uF directly at the module).
- (3) This product should not be mechanically stressed when installed.
- (4) Keep this product away from heat. Heat is the major cause of decreasing the life of these products.
- (5) Avoid assembly and use of the target equipment in conditions where the products' temperature may exceed the maximum tolerance.
- (6) The supply voltage should not be exceedingly high or reversed. It should not carry noise and/or spikes.
- (7) Keep this product away from other high frequency circuits.

27.2 INSTALLATION NOTES

- (1) Reflow soldering is possible twice based on the conditions in Chapter 15. Set up the temperature at the soldering portion of this product according to this reflow profile.
- (2) Carefully position the products so that their heat will not burn into printed circuit boards or affect the other components that are susceptible to heat.
- (3) Carefully locate these products so that their temperatures will not increase due to the effects of heat generated by neighboring components.
- (4) If a vinyl-covered wire comes into contact with the products, then the cover will melt and generate toxic gas, damaging the insulation. Never allow contact between the cover and these products to occur.
- (5) This product should not be mechanically stressed or vibrated when reflowed.
- (6) To repair a board by hand soldering, keep the conditions of this chapter.
- (7) Do not wash this product.
- (8) Refer to the recommended pattern when designing a board.
- (9) Pressing on parts of the metal cover or fastening objects to the metal will cause damage to the unit.

CLASSIFICATION	PI	RODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT CL	_ASS 1 o	r 2 BLUETOOTH MODULE	PAGE	44 of (60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20)15

27.3 USAGE CONDITIONS NOTES

- (1) Take measures to protect the unit against static electricity. If pulses or other transient loads (a large load applied in a short time) are applied to the products, check and evaluate their operation befor assembly on the final products.
- (2) Do not use dropped products.
- (3) Do not touch, damage or soil the pins.
- (4) Follow the recommended condition ratings about the power supply applied to this product.
- (5) Electrode peeling strength: Do not add pressure of more than 4.9N when soldered on PCB.
- (6) Pressing on parts of the metal cover or fastening objects to the metal cover will cause damage.
- (7) These products are intended for general purpose and standard use in general electronic equipment, such as home appliances, office equipment, information and communication equipment.

27.4 STORAGE NOTES

- (1) The module should not be stressed mechanically during storage.
- (2) Do not store these products in the following conditions or the performance characteristics of the product, such as RF performance will be adversely affected:
 - Storage in salty air or in an environment with a high concentration of corrosive gas, such as Cl2, H2S, NH3, SO2, or NOX
 - Storage in direct sunlight
 - Storage in an environment where the temperature may be outside the range of 5°C to 35°C range, or where the humidity may be outside the 45 to 85% range.
 - Storage of the products for more than one year after the date of delivery Storage period: check the adhesive strength of the embossed tape and soldering after 6 months of storage.
- (3) Keep this product away from water, poisonous gas and corrosive gas.
- (4) This product should not be stressed or shocked when transported.
- (5) Follow the specification when stacking packed crates (max. 10).

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT (CLASS 1	or 2 BLUETOOTH MODULE	PAGE	45 of (60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20)15

27.5 SAFETY CAUTIONS

These specifications are intended to preserve the quality assurance of products and individual components.

Before use, check and evaluate the operation when mounted on your products. Abide by these specifications, without deviation when using the products. These products may short-circuit. If electrical shocks, smoke, fire, and/or accidents involving human life are anticipated when a short circuit occurs, then provide the following failsafe functions, as a minimum.

- (1) Ensure the safety of the whole system by installing a protection circuit and a protection device.
- (2) Ensure the safety of the whole system by installing a redundant circuit or another system to prevent a single fault causing an unsafe status.

27.6 OTHER CAUTIONS


- (1) This specification sheet is copyrighted.
- (2) Do not use the products for other purposes than those listed.
- (3) Be sure to provide an appropriate fail-safe function on your product to prevent an additional damage that may be caused by the abnormal function or the failure of the product.
- (4) This product has been manufactured without any ozone chemical controlled under the Montreal Protocol.
- (5) These products are not intended for other uses, other than under the special conditions shown below. Before using these products under such special conditions, check their performance and reliability under the said special conditions carefully to determine whether or not they can be used in such a manner.
 - In liquid, such as water, salt water, oil, alkali, or organic solvent, or in places where liquid may splash.
 - In direct sunlight, outdoors, or in a dusty environment
 - In an environment where condensation occurs.
 - In an environment with a high concentration of harmful gas (e.g. salty air, HCI, Cl2, SO2, H2S, NH3, and NOX)
- (6) If an abnormal voltage is applied due to a problem occurring in other components or circuits, replace these products with new products because they may not be able to provide normal performance even if their electronic characteristics and appearances appear satisfactory.
- (7) When you have any question or uncertainty, contact Panasonic.

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT C	LASS 1	or 2 BLUETOOTH MODULE	PAGE	46 of (60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20)15


28 PACKAGING

28.1 PACKAGING OF PAN131X WITHOUT ANTENNA

Tape Dimension



Packing in Tape




Empty spaces in component packed area shall be less than two per reel and those spaces shall not be consecutive.


Top cover tape shall not be found on reel holes and shall not stick out from reel.

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	-102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	47 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

Component direction




Reel dimension



TAPE SIZE	A MAX	B MIN	С	D MIN	N ±1.0	W1	W2 MAX	W3	Assembly Method
			13 +0.5			25.0 +2.0		24.4 +3.0	
24mm	330.0	1.5	-0.2	20.2	100.0	-0.0	30.4	-0.5	*Latch
All dimensions in	millimeters unless	otherwise stated							*Latch (2PC)


CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	48 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

Label for Package



(1T)	Lotcode [YYWWDLL]	Example from above:
	YY year	printed 08
	WW normal calendar week	printed 01
	D day	printed 5 (Friday)
	L line identifier, if more as one	printed 1
	L lot identifier per day	printed 1
(1P)	Customer Order Code, if any, otherwise	se company name will be printed
(2P)	Panasonic Order Code refer to chapte	er 29 Ordering Information
(9D)	Datecode as [YYWW]	
(Q)	Quantity [XXXX], variable max. 1500	
(HW/SW)	Hardware /Software Release	


Total Package




CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-24	100-102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	49 of	60
CUSTOMER'S COD PAN13XX Core Spec		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

28.2 PACKAGING FOR PAN132X WITH ANTENNA

Tape Dimension



Packing in Tape



All other packaging information is similar to Chapter 28.1

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	50 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

29 ORDERING INFORMATION

Model	Temp.	Part Number	TI-Device	Remark
PAN1315A	-20°C to +70°C	ENW89829C2JF	CC2560A	NR for new designs
PAN1315A	-40°C to +85°C	ENW89829C2KF	CC2560A	NR for new designs
PAN1315B	-40°C to +85°C	ENW89829C3KF	CC2560B	Recommended for new designs
PAN1316	-20°C to +70°C	ENW89823C2JF	CC2564	NR for new designs
PAN1316	-40°C to +85°C	ENW89823C2KF	CC2564	NR for new designs
PAN1316B	-40°C to +85°C	ENW89823C3KF	CC2564B	Recommended for new designs
PAN1317	-20°C to +70°C	ENW89827C2JF	CC2564	NR for new designs
PAN1317	-40°C to +85°C	ENW89827C2KF	CC2564	NR for new designs
PAN1323	-20°C to +70°C	ENW89842A2JF	CC2564	NR for new designs
PAN1323	-40°C to +85°C	ENW89842A2KF	CC2564	NR for new designs
PAN1325A	-20°C to +70°C	ENW89829A2JF	CC2560A	NR for new designs
PAN1325A	-40°C to +85°C	ENW89829A2KF	CC2560A	NR for new designs
PAN1325B	-40°C to +85°C	ENW89829A3KF	CC2560B	Recommended for new designs
PAN1326	-20°C to +70°C	ENW89823A2JF	CC2564	NR for new designs
PAN1326	-40°C to +85°C	ENW89823A2KF	CC2564	NR for new designs
PAN1326B	-40°C to +85°C	ENW89823A3KF	CC2564B	Recommended for new designs
PAN1327	-20°C to +70°C	ENW89827A2JF	CC2564	NR for new designs
PAN1327	-40°C to +85°C	ENW89827A2KF	CC2564	NR for new designs

NR: Not recommended

ETU: Easy to use development board

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	51 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

RoHS Declaration

Declaration of environmental compatibility for supplied products:

Hereby we declare to our best present knowledge based on declaration of our suppliers that this product do not contain by now the following substances which are banned by Directive 2002/95/EC (RoHS) or if contain a maximum concentration of 0,1% by weight in homogeneous materials for

- Lead and lead compounds
- Mercury and mercury compounds
- Chromium (VI)
- PBB (polybrominated biphenyl) category
- PBDE (polybrominated biphenyl ether) category

And a maximum concentration of 0,01% by weight in homogeneous materials for

Cadmium and cadmium compounds

30 DATA SHEET STATUS

This data sheet contains the final specification (RELEASE).

Panasonic reserves the right to make changes at any time without notice in order to improve design and supply the best possible product.

Supplementary data will be published at a later date.

Consult the most recently issued data sheet before initiating or completing a design.

Use this URL to search for the most recent version of this data sheet: PAN13xx Latest Data Sheet!

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400)-102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	52 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

31 HISTORY FOR THIS DOCUMENT

Revision	Date	Modification / Remarks
1.00	04.11.2010	1 st internal Release.
1.01	03.12.2010	Included reference to PAN1325 Application Note. AN-1325-2420-111.pdf.
1.02	10.01.2011	Changed wording in Chapter 34.2 "Industry Canada Certification".
1.03	23.05.2011	Included DOC for PAN1315 series. Included PAN13xx ANT and BLE Addendum Rev1.x.pdf reference. Included Note for IO voltage and MLD_OUT pin.
1.04	02.07.2011	Corrected wording in Chapter 34.3 European R&TTE Declaration of Conformity.
1.05	28.10.2011	Including CC2560A silicon PAN1315A HW40 at Chapter 1.1, Chapter New PAN13x5 and Chapter 0. Deleted ES label in Chapter.
1.06	15.11.2011	Added overview for the core specification and their addendums. Updated front page. Updated Related Documents.
3.00	11.01.2012	Merging PAN13xx documents into this specification and correct some format.
3.10	16.01.2012	Minor mistakes fixed.
3.20	29.05.2012	DoC replaced with revised version.
3.30	11.06.2012	Added triple mode stack Module PAN1323, add PAN1323 to ordering and software information overview, Software Block Diagram added, Bluetooth Inter IC-Sound chapter information added Layout Recommandations with Antenna added, Application Note LGA added
3.31	27.06.2012	Added design information to use low pass filter (chapter 11.1 / 11.9) for better noise surpression when using PCM interface.
3.40	18.07.2012	Re-organize chapter Regulatory Information and added 2 chapters.
3.50	31.10.2012	Changed the Overview in chapter Ordering Information Included -40°C to 85°C Version ENW898xxA2KF. So called K-Version.
3.60	17.05.2013	Changed FCC-ID for models ENW89823xxx and ENW89827xxx.
3.70	31.05.2013	DoC replaced with revised version, updated links.
3.71	15.08.2013	Added component values for low pass filter on PCM interface.
3.80	11.11.2013	Changed CC2567 to CC2564 in chapter ordering information.
3.90	03.12.2013	Included CC2560/4B PAN1325/6B in chapter 1.1.
4.00	19.12.2013	Updated chapter European R&TTE Declaration of Conformity.
4.10	10.01.2014	Added chapter 19 Radiation Pattern.
4.20	28.02.2014	Changed chapter Key Features according to EN regulations.
4.3	24.09.2014	Added chapter 27.
4.4	06.11.2014	Added DoC.
4.5	29.04.2015	Removed chapter 27 and updated chapter 7 Block Diagram.
4.6	07.05.2015	Removed Taiwan Regulatory chapter.
4.61	19.05.2015	Deleted Chapter 2.1 Software Blockdiagram.
4.7	11.06.2015	Changed the wording in chapter 7 Block Diagram.
4.8	23.09.2015	Added Japanese radio law requirements for labeling.

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	53 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

32 RELATED DOCUMENTS

For an update, search in the suitable homepage.

- [1] PAN1323ETU Design-Guide: http://www.panasonic.com/industrial/includes/pdf/PAN1323ETUDesignGuide.pdf
- [2] CC2560 Product Bulletin: http://focus.ti.com/pdfs/wtbu/cc2560_slyt377.pdf
- [3] Bluetooth SW for MSP430 is supported by IAR IDE service pack 5.10.6 and later. Use full IAR version edition (not the kick-start version). You can find info on IAR at http://www.iar.com/website1/1.0.1.0/3/1/ and www.MSP430.com. Note, that there is an option for a 30-day free version of IAR evaluation edition.
- [4] PAN13xx CAD data: http://www.pedeu.panasonic.de/pdf/174ext.zip
- [5] To aide in the implementation of this reference design, Eagle formatted application and layout files are available on the web at the address below.
- [6] www.panasonic.com/industrial/includes/pdf/PAN1323ETU_Eagle_Ver1_1.zip
- [7] Application Note Land Grid Array: http://www.pedeu.panasonic.de/pdf/184ext.pdf

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400	-102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	54 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

33 GENERAL INFORMATION

© Panasonic Industrial Devices Europe GmbH.

All rights reserved.

This document may contain errors. Panasonic reserves the right to make corrections, modifications, enhancements, improvements, and other changes to its literature at any time. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to Panasonic's terms and conditions of sale supplied at the time of order acknowledgment.

If we deliver ES samples to the customer, these samples have the status Engineering Samples. This means, the design of this product is not yet concluded. Engineering Samples may be partially or fully functional, and there may be differences to be published Data Sheet.

Engineering Samples are not qualified and are not to be used for reliability testing or series production.

Disclaimer:

Customer acknowledges that samples may deviate from the Data Sheet and may bear defects due to their status of development and the lack of qualification mentioned above. Panasonic rejects any liability or product warranty for Engineering Samples. In particular, Panasonic disclaims liability for damages caused by

- the use of the Engineering Sample other than for Evaluation Purposes, particularly the installation or integration in an other product to be sold by Customer,
- deviation or lapse in function of Engineering Sample,
- improper use of Engineering Samples.

Panasonic disclaimes any liability for consequential and incidental damages. Panasonic assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using Panasonic components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards. In case of any questions, contact your local sales representative.

34 REGULATORY INFORMATION

34.1 FCC FOR US

34.1.1 FCC Notice



The devices PAN13xx, for details refer to Chapter 28 in this document, including the antennas, which are listed in Chapter 34.1.5 of this data sheet, complies with Part 15 of the FCC Rules. The device meets the requirements for modular transmitter approval as detailed in FCC public Notice DA00-1407.transmitter. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) This device must accept any interference received, including interference that may cause undesired operation.

CLASSIFICATION	PRODUCT SPECIFICATION	No. DS-13xx-2400-102	REV. 4.8
SUBJECT CLASS	or 2 BLUETOOTH MODULE	PAGE 55 (of 60
CUSTOMER'S CODE PAN13XX Core Specification	PANASONIC'S CODE See Chapter Ordering Information	DATE 23.09	.2015

34.1.2 Caution



The FCC requires the user to be notified that any changes or modifications made to this device that are not expressly approved by Panasonic Industrial Devices Europe GmbH may void the user's authority to operate the equipment.

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to Part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help

34.1.3 Labeling Requirements



The Original Equipment Manufacturer (OEM) must ensure that FCC labelling requirements are met. This includes a clearly visible label on the outside of the OEM enclosure specifying the appropriate Panasonic FCC identifier for this product as well as the FCC Notice above. The FCC identifiers are:

FCC ID: T7V1315 for PAN1315 and PAN1325

FCC ID: T7V1316 for PAN1316, PAN1317, PAN1326 and PAN1327

This FCC identifiers are valid for all PAN13xx modules, for details, see the Chapter 29. Ordering Information. In any case the end product must be labelled exterior with "Contains FCC ID: T7V1315" (PAN1315, PAN1325) or

"Contains FCC ID: T7V1316" (PAN1316, PAN1317, PAN1326 and PAN1327).

34.1.4 Antenna Warning



For the related part number of PAN13xx refer to Chapter 29. Ordering Information.

These devices are tested with a standard SMA connector and with the antennas listed below. When integrated in the OEMs product, these fixed antennas require installation preventing end-users from replacing them with non-approved antennas. Any antenna not in the following tables must be tested to comply with FCC Section 15.203 for unique antenna connectors and Section 15.247 for emissions. The FCC identifier for this device with the antenna listed below are the same (FCC ID: T7V1315 or T7V1316).

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	56 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

34.1.5 Approved Antenna List (PAN1315, PAN1325)

Note: We are able to qualify your antenna and will add to this list as that process is completed.

Item	Part Number	Manufacturer	Frequency Band	Туре	Gain (dBi)
1	2450AT43B100	Johanson Technologies	2.4GHz	Chip-Antenna	+1.3
2	LDA212G3110K	Murata	2.4GHz	Chip-Antenna	+0.9
3	4788930245	Würth Elektronik	2.4GHz	Chip-Antenna	+0.5

34.1.6 Approved Antenna List (PAN1316, PAN1317, PAN1326, PAN1327)

Note: We are able to qualify your antenna and will add to this list as that process is completed.

	Item	Part Number	Manufacturer	Frequency Band	Туре	Gain (dBi)
Ī	1	LDA212G3110K	Murata	2.4GHz	Chip-Antenna	+0.9

34.1.7 RF Exposure PAN13xx



To comply with FCC RF Exposure requirements, the Original Equipment Manufacturer (OEM) must ensure that the approved antenna in the previous tables must be installed.

The preceding statement must be included as a CAUTION statement in manuals for products operating with the approved antennas in the previous table to alert users on FCC RF Exposure compliance.

Any notification to the end user of installation or removal instructions about the integrated radio module is not allowed.

The radiated output power of PAN13xx with mounted ceramic antenna (FCC ID: T7V1315 or T7V1316) is far below the FCC radio frequency exposure limits. Nevertheless, the PAN13xx shall be used in such a manner that the potential for human contact during normal operation is minimized.

End users may not be provided with the module installation instructions. OEM integrators and end users must be provided with transmitter operating conditions for satisfying RF exposure compliance.

CLASSIFICATION	PF	RODUCT SPECIFICATION	No. DS-13xx-2400-	102	REV. 4.8
SUBJECT CL	ASS 1 o	r 2 BLUETOOTH MODULE	PAGE	57 of 6	60
CUSTOMER'S CODE PAN13XX Core Specifica		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20)15

34.2 INDUSTRY CANADA CERTIFICATION

34.2.1 IC Notice

This device complies with Industry Canada RSS-210 (Rev.8). Operation is subject to the following two conditions

- 1) this device may not cause interference, and
- 2) this device must accept any interference, including interference that may cause undesired operation of the device.

PAN131x is licensed to meet the regulatory requirements of Industry Canada (IC), license:

IC: 216Q-1315 (PAN1315, PAN1325)

IC: 216Q-1316 (PAN1316, PAN1317, PAN1326, PAN1327)

Manufacturers of mobile, fixed or portable devices incorporating this module are advised to clarify any regulatory questions and ensure compliance for SAR and/or RF exposure limits. Users can obtain Canadian information on RF exposure and compliance from www.ic.gc.ca.

This device has been designed to operate with the antennas listed in Tables 34.1.5 and 34.1.6 above, having a maximum gain of 1.3 dBi (PAN13x6: 0.9dBi). Antennas not included in this list or having a gain greater than 1.3 dBi (PAN13x6: 0.9dBi) are strictly prohibited for use with this device. The required antenna impedance is 50 ohms. The antenna used for this transmitter must not be co-located or operating in conjunction with any other antenna or transmitter. Due to the model size the IC identifier is displayed in the installation instruction.

Le présent appareil est conforme aux CNR d'Industrie Canada applicables aux appareils radio exempts de licence. L'exploitation est autorisée aux deux conditions suivantes :

- (1) l'appareil ne doit pas produire de brouillage, et
- (2) l'utilisateur de l'appareil doit accepter tout brouillage radioélectrique subi, même si le brouillage est susceptible d'en compromettre le fonctionnement.

PAN131x est garanti conforme aux dispositions règlementaires d'Industry Canada (IC), licences:

IC: 216Q-1315 (PAN1315, PAN1325)

IC: 216Q-1316 (PAN1316, PAN1317, PAN1326, PAN1327)

Il est recommandé aux fabricants d'appareils fixes, mobiles ou portables de consulter la réglementation en vigueur et de vérifier la conformité de leurs produits relativement aux limites d'exposition aux rayonnements radiofréquence ainsi qu'au débit d'absorption spécifique maximum autorisé.

Des informations pour les utilisateurs sur la réglementation Canadienne concernant l'exposition aux rayonnements RF sont disponibles sur le site www.ic.gc.ca.

Ce produit a été développé pour fonctionner spécifiquement avec les antennes listées dans le tableau ci-dessus, présentant un gain maximum de 1.3dBi (PAN13x6:0.9dBi).

CLASSIFICATION	PRODUCT SPECIFICATION	No. DS-13xx-2400-102	REV. 4.8
SUBJECT CLA	SS 1 or 2 BLUETOOTH MODULE	PAGE 58	of 60
CUSTOMER'S CODE PAN13XX Core Specificat	PANASONIC'S CODE See Chapter Ordering Information	DATE 23.	09.2015

Des antennes autres que celles listées ici, ou présentant un gain supérieur a 1.3dBi (PAN13x6: 0.9dBi) ne doivent en aucune circonstance être utilises en combinaison avec ce produit. L'impédance des antennes compatibles est 50Ohm. L'antenne utilisée avec ce produit ne doit ni être située à proximité d'une autre antenne ou d'un autre émetteur, ni être utilisée conjointement avec une autre antenne ou un autre émetteur. En raison de la taille du produit, l'identifiant IC est fourni dans le manuel d'installation.

34.2.2 Labeling Requirements



The Original Equipment Manufacturer (OEM) must ensure that IC labelling requirements are met. This includes a clearly visible label on the outside of the OEM enclosure specifying the appropriate Panasonic IC identifier for this product as well as the IC Notice above. The IC identifiers are:

IC: 216Q-1315 (PAN1315, PAN1325)

IC: 216Q-1316 (PAN1316, PAN1317, PAN1326, PAN1327)

This IC identifiers are valid for all PAN13xx modules, for details, see the Chapter 29. Ordering Information. In any case the end product must be labelled exterior with

"Contains IC: 216Q-1315" (PAN1315, PAN1325) or

"Contains IC: 216Q-1316" (PAN1316, PAN1317, PAN1326 and PAN1327).

Obligations d'étiquetage

Les fabricants d'équipements (OEM) doivent s'assurer que les obligations d'étiquetage du produit final sont remplies. Ces obligations incluent une étiquette clairement visible à l'extérieur de l'emballage externe, comportant l'identifiant IC du module Panasonic inclus, ainsi que la notification ci-dessus.

Les identifiants IC sont:

IC: 216Q-1315 (PAN1315, PAN1325)

IC: 216Q-1316 (PAN1316, PAN1317, PAN1326, PAN1327)

Ces identifiants sont valides pour tous les modules PAN13xx (Chapter 29. Ordering Information). Dans tous les cas les produits finaux doivent indiquer sur leur emballage externe une des mentions suivantes:

"Contient IC: 216Q-1315" (PAN1315, PAN1325) ou

"Contient IC: 216Q-1316" (PAN1316, PAN1317, PAN1326, PAN1327).

CLASSIFICATION		PRODUCT SPECIFICATION	No. DS-13xx-24	100-102	REV. 4.8
SUBJECT	CLASS 1	or 2 BLUETOOTH MODULE	PAGE	59 of	60
CUSTOMER'S CODE PAN13XX Core Specification		PANASONIC'S CODE See Chapter Ordering Information	DATE	23.09.20	015

34.3 EUROPEAN R&TTE DECLARATION OF CONFORMITY

Declaration of Conformity (DoC) 1999/5/EC

Wireless Con	nectivity, Power Electronics R&D Center	
	se 19, 21337 Lueneburg, Germany	
749 	responsibility that the product:	
Type of equipment:	Bluetooth Module	
Brand name:	PAN1315 PAN1316 PAN1325 PAN132	K
brand name.	PANISIS PANISIO PANISZS PANISZ	0
Model name:	ENW89823C2KF ENW89829C2KF ENV	W89823C3KF ENW89829C3KF
	ENW89823A2KF ENW89829A2KF EN	W89823A3KF ENW89829A3KF
1999/5/EC	er provisions of the European Council Di	tions Terminal Equipment Directive (R&TTE)
	4 ************************************	
The conformity assess	sment procedure used for this declaration	is Annex IV of this Directive.
Product compliance h	as been demonstrated on the basis of:	
		T
- EN 60950-1: 2006+	A11:2009+A1:2010+A12:2011+A2:2013	
- EN 62311:2008		For article 3.1a: Safety/Health
		For article 3.1a: Safety/Health
- EN 62311:2008	2.1:2012-09	
- EN 62311:2008 - EN 62479: 2010		
- EN 62311:2008 - EN 62479: 2010 - EN 301 489-17 V2.2 - EN 300 328 V1.8.1:	2012-06	For article 3.1b: Electromagnetic Compatibility
- EN 62311:2008 - EN 62479: 2010 - EN 301 489-17 V2.2 - EN 300 328 V1.8.1: The technical contruct	2012-06 tion file is kept available at:	For article 3.1b: Electromagnetic Compatibility For article 3.2: Radio
- EN 62311:2008 - EN 62479: 2010 - EN 301 489-17 V2.2 - EN 300 328 V1.8.1: The technical contruct	2012-06	For article 3.1b: Electromagnetic Compatibility For article 3.2: Radio
- EN 62311:2008 - EN 62479: 2010 - EN 301 489-17 V2.2 - EN 300 328 V1.8.1: The technical contructor panasonic Industrial De	2012-06 tion file is kept available at: vices Europe GmbH, Zeppelinstrasse 19, 21:	For article 3.1b: Electromagnetic Compatibility For article 3.2: Radio
- EN 62311:2008 - EN 62479: 2010 - EN 301 489-17 V2.2 - EN 300 328 V1.8.1: The technical contruct Panasonic Industrial De	2012-06 tion file is kept available at:	For article 3.1b: Electromagnetic Compatibility For article 3.2: Radio
- EN 62311:2008 - EN 62479: 2010 - EN 301 489-17 V2.2 - EN 300 328 V1.8.1: The technical contruct	2012-06 tion file is kept available at: vices Europe GmbH, Zeppelinstrasse 19, 21:	For article 3.1b: Electromagnetic Compatibility For article 3.2: Radio
- EN 62311:2008 - EN 62479: 2010 - EN 301 489-17 V2.2 - EN 300 328 V1.8.1: The technical contructor Panasonic Industrial Desired Contractors on:	2012-06 tion file is kept available at: vices Europe GmbH, Zeppelinstrasse 19, 21:	For article 3.1b: Electromagnetic Compatibility For article 3.2: Radio 337 Lueneburg, Germany
- EN 62311:2008 - EN 62479: 2010 - EN 301 489-17 V2.2 - EN 300 328 V1.8.1: The technical contruct Panasonic Industrial De Issued on: Signed by the manufa	2012-06 tion file is kept available at: vices Europe GmbH, Zeppelinstrasse 19, 21: 29.10.2014 cturer: Panasonic Industrial Device	For article 3.1b: Electromagnetic Compatibility For article 3.2: Radio 337 Lueneburg, Germany
- EN 62311:2008 - EN 62479: 2010 - EN 301 489-17 V2.2 - EN 300 328 V1.8.1: The technical contruct Panasonic Industrial De Issued on: Signed by the manufa (Company name)	2012-06 tion file is kept available at: vices Europe GmbH, Zeppelinstrasse 19, 21: 29.10.2014 cturer: Panasonic Industrial Device	For article 3.1b: Electromagnetic Compatibility For article 3.2: Radio 337 Lueneburg, Germany
- EN 62311:2008 - EN 62479: 2010 - EN 301 489-17 V2.2 - EN 300 328 V1.8.1: The technical contruct Panasonic Industrial De Issued on: Signed by the manufat (Company name) (Signature)	2012-06 tion file is kept available at: vices Europe GmbH, Zeppelinstrasse 19, 21: 29.10.2014 cturer: Panasonic Industrial Device	For article 3.1b: Electromagnetic Compatibility For article 3.2: Radio 337 Lueneburg, Germany
- EN 62311:2008 - EN 62479: 2010 - EN 301 489-17 V2.2 - EN 300 328 V1.8.1: The technical contruct Panasonic Industrial De Issued on: Signed by the manufa (Company name)	2012-06 tion file is kept available at: vices Europe GmbH, Zeppelinstrasse 19, 21: 29.10.2014 cturer: Panasonic Industrial Device (2) 31 (2) (2) (2) (2) (2) (2) (2) (2) (2) (2)	For article 3.1b: Electromagnetic Compatibility For article 3.2: Radio 337 Lueneburg, Germany

CLASSIFICATION	PRODUCT SPECIFICATION	No. DS-13xx-2400-102	REV. 4.8
SUBJECT CLA	SS 1 or 2 BLUETOOTH MODULE	PAGE 60 of	60
CUSTOMER'S CODE PAN13XX Core Specification	PANASONIC'S CODE See Chapter Ordering Information	DATE 23.09.2	015

As a result of the conformity assessment procedure described in Annex III of the Directive 1999/5/EC, the end-customer equipment should be labelled as follows:

C€

PAN13xx and their versions in the specified reference design can be used in the following countries: Austria, Belgium, Cyprus, Czech Republic, Denmark, Estonia, Finland, France, Germany, Greece, Hungary, Ireland, Italy, Latvia, Lithuania, Luxembourg, Malta, Poland, Portugal, Slovakia, Slovenia, Spain, Sweden, The Netherlands, the United Kingdom, Switzerland, and Norway.

34.4 JAPANESE RADIO LAW AND JAPANESE TELECOMMUNICATIONS BUSINESS LAW COMPLIANCE:

This device is granted pursuant to the Japanese Radio Law (電皮) and the Japanese Telecommunications Business Law (電気通言事業)

This device should not be modified (otherwise the granted designation number will become invalid)

The following models are qualified for Japanese market:

ENW89823A2KF MIC ID: [R]202-LSD072 ENW89823A3KF MIC ID: [R]202-LSD072 ENW89829A2KF MIC ID: [R]202-LSD073 ENW89829A3KF MIC ID: [R]202-LSD073

34.5 BLUETOOTH SIG STATEMENT

The Design is listed as Controller Subsystem with QDID: B019784 https://www.bluetooth.org/tpg/QLI_viewQDL.cfm?qid=19784

35 LIFE SUPPORT POLICY

This Panasonic product is not designed for use in life support appliances, devices, or systems where malfunction can reasonably be expected to result in a significant personal injury to the user, or as a critical component in any life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness. Panasonic customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panasonic for any damages resulting.