

## High-Speed CMOS Logic Decade Counter/Divider with 10 Decoded Outputs

### Features

- Fully Static Operation
- Buffered Inputs
- Common Reset
- Positive Edge Clocking
- Typical  $f_{MAX} = 50\text{MHz}$  at  $V_{CC} = 5\text{V}$ ,  $C_L = 15\text{pF}$ ,  $T_A = 25^\circ\text{C}$
- Fanout (Over Temperature Range)
  - Standard Outputs . . . . . 10 LSTTL Loads
  - Bus Driver Outputs . . . . . 15 LSTTL Loads
- Wide Operating Temperature Range . . .  $-55^\circ\text{C}$  to  $125^\circ\text{C}$
- Balanced Propagation Delay and Transition Times
- Significant Power Reduction Compared to LSTTL Logic ICs
- HC Types
  - 2V to 6V Operation
  - High Noise Immunity:  $N_{IL} = 30\%$ ,  $N_{IH} = 30\%$  of  $V_{CC}$  at  $V_{CC} = 5\text{V}$

### Description

The 'HC4017 is a high speed silicon gate CMOS 5-stage Johnson counter with 10 decoded outputs. Each of the decoded outputs is normally low and sequentially goes high on the low to high transition clock period of the 10 clock period cycle. The CARRY (TC) output transitions low to high after OUTPUT 10 goes from high to low, and can be used in conjunction with the CLOCK ENABLE ( $\overline{CE}$ ) to cascade several stages. The CLOCK ENABLE input disables counting when in the high state. A RESET (MR) input is also provided which when taken high sets all the decoded outputs, except "0", low.

The device can drive up to 10 low power Schottky equivalent loads.


### Ordering Information

| PART NUMBER   | TEMP. RANGE<br>( $^\circ\text{C}$ ) | PACKAGE      |
|---------------|-------------------------------------|--------------|
| CD54HC4017F3A | -55 to 125                          | 16 Ld CERDIP |
| CD74HC4017E   | -55 to 125                          | 16 Ld PDIP   |
| CD74HC4017M   | -55 to 125                          | 16 Ld SOIC   |
| CD74HC4017MT  | -55 to 125                          | 16 Ld SOIC   |
| CD74HC4017M96 | -55 to 125                          | 16 Ld SOIC   |
| CD74HC4017NSR | -55 to 125                          | 16 Ld SOP    |
| CD74HC4017PW  | -55 to 125                          | 16 Ld TSSOP  |
| CD74HC4017PWR | -55 to 125                          | 16 Ld TSSOP  |


NOTE: When ordering, use the entire part number. The suffixes 96 and R denote tape and reel. The suffix T denotes a small-quantity reel of 250.

### Pinout

CD54HC4017 (CERDIP)  
CD74HC4017 (PDIP, SOIC, SOP, TSSOP)  
TOP VIEW



## Functional Diagram



TRUTH TABLE

| CP | $\overline{CE}$ | MR | OUTPUT STATE †        |
|----|-----------------|----|-----------------------|
| L  | X               | L  | No Change             |
| X  | H               | L  | No Change             |
| X  | X               | H  | "0" = H, "1"- "9" = L |
| ↑  | L               | L  | Increments Counter    |
| ↓  | X               | L  | No Change             |
| X  | ↑               | L  | No Change             |
| H  | ↓               | L  | Increments Counter    |

H = High Level

L = Low Level

↑ = High to Low Transition

↓ = Low to High Transition

X = Don't Care.

† If  $n < 5$  TC = H, Otherwise = L

# CD54HC4017, CD74HC4017

## Absolute Maximum Ratings

DC Supply Voltage,  $V_{CC}$  ..... -0.5V to 7V  
 DC Input Diode Current,  $I_{IK}$   
     For  $V_I < -0.5V$  or  $V_I > V_{CC} + 0.5V$  .....  $\pm 20mA$   
 DC Output Diode Current,  $I_{OK}$   
     For  $V_O < -0.5V$  or  $V_O > V_{CC} + 0.5V$  .....  $\pm 20mA$   
 DC Output Source or Sink Current per Output Pin,  $I_O$   
     For  $V_O > -0.5V$  or  $V_O < V_{CC} + 0.5V$  .....  $\pm 25mA$   
 DC  $V_{CC}$  or Ground Current,  $I_{CC}$  or  $I_{GND}$  .....  $\pm 50mA$

## Thermal Information

Package Thermal Impedance,  $\theta_{JA}$  (see Note 1):  
     E (PDIP) Package .....  $67^{\circ}C/W$   
     M (SOIC) Package .....  $73^{\circ}C/W$   
     NS (SOP) Package .....  $64^{\circ}C/W$   
     PW (TSSOP) Package .....  $108^{\circ}C/W$   
 Maximum Junction Temperature .....  $150^{\circ}C$   
 Maximum Storage Temperature Range .....  $-65^{\circ}C$  to  $150^{\circ}C$   
 Maximum Lead Temperature (Soldering 10s) .....  $300^{\circ}C$   
     (SOIC - Lead Tips Only)

## Operating Conditions

Temperature Range,  $T_A$  .....  $-55^{\circ}C$  to  $125^{\circ}C$   
 Supply Voltage Range,  $V_{CC}$   
     HC Types ..... 2V to 6V  
     HCT Types ..... 4.5V to 5.5V  
 DC Input or Output Voltage,  $V_I$ ,  $V_O$  ..... 0V to  $V_{CC}$   
 Input Rise and Fall Time  
     2V ..... 1000ns (Max)  
     4.5V ..... 500ns (Max)  
     6V ..... 400ns (Max)

*CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress only rating and operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied.*

### NOTE:

1. The package thermal impedance is calculated in accordance with JESD 51-7.

## DC Electrical Specifications

| PARAMETER                               | SYMBOL          | TEST CONDITIONS                    |                     | V <sub>CC</sub> (V) | 25°C |     |      | -40°C TO 85°C |      | -55°C TO 125°C |      | UNITS |
|-----------------------------------------|-----------------|------------------------------------|---------------------|---------------------|------|-----|------|---------------|------|----------------|------|-------|
|                                         |                 | V <sub>I</sub> (V)                 | I <sub>O</sub> (mA) |                     | MIN  | TYP | MAX  | MIN           | MAX  | MIN            | MAX  |       |
| High Level Input Voltage                | V <sub>IH</sub> | -                                  | -                   | 2                   | 1.5  | -   | -    | 1.5           | -    | 1.5            | -    | V     |
|                                         |                 |                                    |                     | 4.5                 | 3.15 | -   | -    | 3.15          | -    | 3.15           | -    | V     |
|                                         |                 |                                    |                     | 6                   | 4.2  | -   | -    | 4.2           | -    | 4.2            | -    | V     |
| Low Level Input Voltage                 | V <sub>IL</sub> | -                                  | -                   | 2                   | -    | -   | 0.5  | -             | 0.5  | -              | 0.5  | V     |
|                                         |                 |                                    |                     | 4.5                 | -    | -   | 1.35 | -             | 1.35 | -              | 1.35 | V     |
|                                         |                 |                                    |                     | 6                   | -    | -   | 1.8  | -             | 1.8  | -              | 1.8  | V     |
| High Level Output Voltage<br>CMOS Loads | V <sub>OH</sub> | V <sub>IH</sub> or V <sub>IL</sub> | -0.02               | 2                   | 1.9  | -   | -    | 1.9           | -    | 1.9            | -    | V     |
|                                         |                 |                                    | -0.02               | 4.5                 | 4.4  | -   | -    | 4.4           | -    | 4.4            | -    | V     |
|                                         |                 |                                    | -0.02               | 6                   | 5.9  | -   | -    | 5.9           | -    | 5.9            | -    | V     |
| High Level Output Voltage<br>TTL Loads  |                 |                                    | -                   | -                   | -    | -   | -    | -             | -    | -              | -    | V     |
|                                         |                 |                                    | -4                  | 4.5                 | 3.98 | -   | -    | 3.84          | -    | 3.7            | -    | V     |
|                                         |                 |                                    | -5.2                | 6                   | 5.48 | -   | -    | 5.34          | -    | 5.2            | -    | V     |
| Low Level Output Voltage<br>CMOS Loads  | V <sub>OL</sub> | V <sub>IH</sub> or V <sub>IL</sub> | 0.02                | 2                   | -    | -   | 0.1  | -             | 0.1  | -              | 0.1  | V     |
|                                         |                 |                                    | 0.02                | 4.5                 | -    | -   | 0.1  | -             | 0.1  | -              | 0.1  | V     |
|                                         |                 |                                    | 0.02                | 6                   | -    | -   | 0.1  | -             | 0.1  | -              | 0.1  | V     |
| Low Level Output Voltage<br>TTL Loads   |                 |                                    | -                   | -                   | -    | -   | -    | -             | -    | -              | -    | V     |
|                                         |                 |                                    | 4                   | 4.5                 | -    | -   | 0.26 | -             | 0.33 | -              | 0.4  | V     |
|                                         |                 |                                    | 5.2                 | 6                   | -    | -   | 0.26 | -             | 0.33 | -              | 0.4  | V     |
| Input Leakage Current                   | I <sub>I</sub>  | V <sub>CC</sub> or GND             | -                   | 6                   | -    | -   | ±0.1 | -             | ±1   | -              | ±1   | µA    |
| Quiescent Device Current                | I <sub>CC</sub> | V <sub>CC</sub> or GND             | 0                   | 6                   | -    | -   | 8    | -             | 80   | -              | 160  | µA    |

# CD54HC4017, CD74HC4017

## Prerequisite for Switching Specifications

| PARAMETER                | SYMBOL           | TEST CONDITIONS | V <sub>CC</sub><br>(V) | 25°C |     |     | -40°C TO 85°C |     | -55°C TO 125°C |     | UNITS |
|--------------------------|------------------|-----------------|------------------------|------|-----|-----|---------------|-----|----------------|-----|-------|
|                          |                  |                 |                        | MIN  | TYP | MAX | MIN           | MAX | MIN            | MAX |       |
| Maximum Clock Frequency  | f <sub>MAX</sub> | -               | 2                      | 6    | -   | -   | 5             | -   | 4              | -   | MHz   |
|                          |                  |                 | 4.5                    | 30   | -   | -   | 35            | -   | 20             | -   | MHz   |
|                          |                  |                 | 6                      | 35   | -   | -   | 49            | -   | 23             | -   | MHz   |
| CP Pulse Width           | t <sub>W</sub>   | -               | 2                      | 80   | -   | -   | 100           | -   | 120            | -   | ns    |
|                          |                  |                 | 4.5                    | 16   | -   | -   | 20            | -   | 24             | -   | ns    |
|                          |                  |                 | 6                      | 14   | -   | -   | 17            | -   | 20             | -   | ns    |
| MR Pulse Width           | t <sub>W</sub>   | -               | 2                      | 80   | -   | -   | 100           | -   | 120            | -   | ns    |
|                          |                  |                 | 4.5                    | 16   | -   | -   | 20            | -   | 24             | -   | ns    |
|                          |                  |                 | 6                      | 14   | -   | -   | 17            | -   | 20             | -   | ns    |
| Set-up Time,<br>CE to CP | t <sub>SU</sub>  | -               | 2                      | 75   | -   | -   | 95            | -   | 110            | -   | ns    |
|                          |                  |                 | 4.5                    | 15   | -   | -   | 19            | -   | 22             | -   | ns    |
|                          |                  |                 | 6                      | 13   | -   | -   | 16            | -   | 19             | -   | ns    |
| Hold Time,<br>CE to CP   | t <sub>H</sub>   | -               | 2                      | 0    | -   | -   | 0             | -   | 0              | -   | ns    |
|                          |                  |                 | 4.5                    | 0    | -   | -   | 0             | -   | 0              | -   | ns    |
|                          |                  |                 | 6                      | 0    | -   | -   | 0             | -   | 0              | -   | ns    |
| MR Removal Time          | t <sub>REM</sub> | -               | 2                      | 5    | -   | -   | 5             | -   | 5              | -   | ns    |
|                          |                  |                 | 4.5                    | 5    | -   | -   | 5             | -   | 5              | -   | ns    |
|                          |                  |                 | 6                      | 5    | -   | -   | 5             | -   | 5              | -   | ns    |

## Switching Specifications Input t<sub>r</sub>, t<sub>f</sub> = 6ns

| PARAMETER                               | SYMBOL                                 | TEST CONDITIONS       | V <sub>CC</sub><br>(V) | 25°C |     |     | -40°C TO 85°C |     | -55°C TO 125°C |     | UNITS |
|-----------------------------------------|----------------------------------------|-----------------------|------------------------|------|-----|-----|---------------|-----|----------------|-----|-------|
|                                         |                                        |                       |                        | MIN  | TYP | MAX | MIN           | MAX | MIN            | MAX |       |
| Propagation Delay<br>CP to any Dec. Out | t <sub>PLH</sub> ,<br>t <sub>PHL</sub> | C <sub>L</sub> = 50pF | 2                      | -    | -   | 230 | -             | 290 | -              | 345 | ns    |
|                                         |                                        | C <sub>L</sub> = 50pF | 4.5                    | -    | -   | 46  | -             | 58  | -              | 69  | ns    |
|                                         |                                        | C <sub>L</sub> = 15pF | 5                      | -    | 19  | -   | -             | -   | -              | -   | ns    |
|                                         |                                        | C <sub>L</sub> = 50pF | 6                      | -    | -   | 39  | -             | 49  | -              | 59  | ns    |
| CP to TC                                | t <sub>PLH</sub> ,<br>t <sub>PHL</sub> | C <sub>L</sub> = 50pF | 2                      | -    | -   | 230 | -             | 290 | -              | 345 | ns    |
|                                         |                                        | C <sub>L</sub> = 50pF | 4.5                    | -    | -   | 46  | -             | 58  | -              | 69  | ns    |
|                                         |                                        | C <sub>L</sub> = 15pF | 5                      | -    | 19  | -   | -             | -   | -              | -   | ns    |
|                                         |                                        | C <sub>L</sub> = 50pF | 6                      | -    | -   | 39  | -             | 49  | -              | 59  | ns    |
| CE to any Dec. Out                      | t <sub>PLH</sub> ,<br>t <sub>PHL</sub> | C <sub>L</sub> = 50pF | 2                      | -    | -   | 250 | -             | 315 | -              | 375 | ns    |
|                                         |                                        | C <sub>L</sub> = 50pF | 4.5                    | -    | -   | 50  | -             | 63  | -              | 75  | ns    |
|                                         |                                        | C <sub>L</sub> = 15pF | 5                      | -    | 21  | -   | -             | -   | -              | -   | ns    |
|                                         |                                        | C <sub>L</sub> = 50pF | 6                      | -    | -   | 43  | -             | 54  | -              | 64  | ns    |
| CE to TC                                | t <sub>PLH</sub> ,<br>t <sub>PHL</sub> | C <sub>L</sub> = 50pF | 2                      | -    | -   | 250 | -             | 315 | -              | 375 | ns    |
|                                         |                                        | C <sub>L</sub> = 50pF | 4.5                    | -    | -   | 50  | -             | 63  | -              | 75  | ns    |
|                                         |                                        | C <sub>L</sub> = 15pF | 5                      | -    | 21  | -   | -             | -   | -              | -   | ns    |
|                                         |                                        | C <sub>L</sub> = 50pF | 6                      | -    | -   | 43  | -             | 54  | -              | 64  | ns    |


**Switching Specifications** Input  $t_r, t_f = 6\text{ns}$  (Continued)

| PARAMETER                                     | SYMBOL             | TEST CONDITIONS     | $V_{CC}$<br>(V) | 25°C |     |     | -40°C TO 85°C |     | -55°C TO 125°C |     | UNITS |
|-----------------------------------------------|--------------------|---------------------|-----------------|------|-----|-----|---------------|-----|----------------|-----|-------|
|                                               |                    |                     |                 | MIN  | TYP | MAX | MIN           | MAX | MIN            | MAX |       |
| MR to any Dec. Out                            | $t_{PLH}, t_{PHL}$ | $C_L = 50\text{pF}$ | 2               | -    | -   | 230 | -             | 290 | -              | 345 | ns    |
|                                               |                    | $C_L = 50\text{pF}$ | 4.5             | -    | -   | 46  | -             | 58  | -              | 69  | ns    |
|                                               |                    | $C_L = 15\text{pF}$ | 5               | -    | 19  | -   | -             | -   | -              | -   | ns    |
|                                               |                    | $C_L = 50\text{pF}$ | 6               | -    | -   | 39  | -             | 49  | -              | 59  | ns    |
| MR to TC                                      | $t_{PLH}, t_{PHL}$ | $C_L = 50\text{pF}$ | 2               | -    | -   | 230 | -             | 290 | -              | 345 | ns    |
|                                               |                    | $C_L = 50\text{pF}$ | 4.5             | -    | -   | 46  | -             | 58  | -              | 69  | ns    |
|                                               |                    | $C_L = 15\text{pF}$ | 5               | -    | 19  | -   | -             | -   | -              | -   | ns    |
|                                               |                    | $C_L = 50\text{pF}$ | 6               | -    | -   | 39  | -             | 49  | -              | 59  | ns    |
| Transition Time TC, Dec. Out                  | $t_{TLH}, t_{THL}$ | $C_L = 50\text{pF}$ | 2               | -    | -   | 75  | -             | 95  | -              | 110 | ns    |
|                                               |                    | $C_L = 50\text{pF}$ | 4.5             | -    | -   | 15  | -             | 19  | -              | 22  | ns    |
|                                               |                    | $C_L = 50\text{pF}$ | 6               | -    | -   | 13  | -             | 16  | -              | 19  | ns    |
| Input Capacitance                             | $C_{IN}$           | $C_L = 50\text{pF}$ | -               | -    | -   | 10  | -             | 10  | -              | 10  | pF    |
| Maximum CP Frequency                          | $f_{MAX}$          | $C_L = 15\text{pF}$ | 5               | -    | 60  | -   | -             | -   | -              | -   | MHz   |
| Power Dissipation Capacitance<br>(Notes 2, 3) | $C_{PD}$           | $C_L = 15\text{pF}$ | 5               | -    | 39  | -   | -             | -   | -              | -   | pF    |

NOTES:


2.  $C_{PD}$  is used to determine the dynamic power consumption, per package.
3.  $P_D = V_{CC}^2 f_i \sum C_L V_{CC}^2 f_o$  where  $f_i$  = input frequency,  $f_o$  = output frequency,  $C_L$  = output load capacitance,  $V_{CC}$  = supply voltage.

**Test Circuits and Waveforms**



NOTE: Outputs should be switching from 10%  $V_{CC}$  to 90%  $V_{CC}$  in accordance with device truth table. For  $f_{MAX}$ , input duty cycle = 50%.

**FIGURE 1. HC CLOCK PULSE RISE AND FALL TIMES AND PULSE WIDTH**



**FIGURE 2. HC TRANSITION TIMES AND PROPAGATION DELAY TIMES, COMBINATION LOGIC**


**Test Circuits and Waveforms** (Continued)

FIGURE 3. HC SETUP TIMES, HOLD TIMES, REMOVAL TIME, AND PROPAGATION DELAY TIMES FOR EDGE TRIGGERED SEQUENTIAL LOGIC CIRCUITS


**Timing Diagrams**

FIGURE 4.




FIGURE 5.

## PACKAGING INFORMATION

| Orderable Device | Status<br>(1) | Package Type | Package<br>Drawing | Pins | Package<br>Qty | Eco Plan<br>(2)     | Lead finish/<br>Ball material<br>(6) | MSL Peak Temp<br>(3) | Op Temp (°C) | Device Marking<br>(4/5)    | Samples                 |
|------------------|---------------|--------------|--------------------|------|----------------|---------------------|--------------------------------------|----------------------|--------------|----------------------------|-------------------------|
| 8601101EA        | ACTIVE        | CDIP         | J                  | 16   | 25             | Non-RoHS<br>& Green | SNPB                                 | N / A for Pkg Type   | -55 to 125   | 8601101EA<br>CD54HC4017F3A | <a href="#">Samples</a> |
| CD54HC4017F3A    | ACTIVE        | CDIP         | J                  | 16   | 25             | Non-RoHS<br>& Green | SNPB                                 | N / A for Pkg Type   | -55 to 125   | 8601101EA<br>CD54HC4017F3A | <a href="#">Samples</a> |
| CD74HC4017E      | ACTIVE        | PDIP         | N                  | 16   | 25             | RoHS & Green        | NIPDAU                               | N / A for Pkg Type   | -55 to 125   | CD74HC4017E                | <a href="#">Samples</a> |
| CD74HC4017EE4    | ACTIVE        | PDIP         | N                  | 16   | 25             | RoHS & Green        | NIPDAU                               | N / A for Pkg Type   | -55 to 125   | CD74HC4017E                | <a href="#">Samples</a> |
| CD74HC4017M      | LIFEBUY       | SOIC         | D                  | 16   | 40             | RoHS & Green        | NIPDAU                               | Level-1-260C-UNLIM   | -55 to 125   | HC4017M                    |                         |
| CD74HC4017M96    | ACTIVE        | SOIC         | D                  | 16   | 2500           | RoHS & Green        | NIPDAU                               | Level-1-260C-UNLIM   | -55 to 125   | HC4017M                    | <a href="#">Samples</a> |
| CD74HC4017MT     | LIFEBUY       | SOIC         | D                  | 16   | 250            | RoHS & Green        | NIPDAU                               | Level-1-260C-UNLIM   | -55 to 125   | HC4017M                    |                         |
| CD74HC4017MTE4   | LIFEBUY       | SOIC         | D                  | 16   | 250            | RoHS & Green        | NIPDAU                               | Level-1-260C-UNLIM   | -55 to 125   | HC4017M                    |                         |
| CD74HC4017NSR    | ACTIVE        | SO           | NS                 | 16   | 2000           | RoHS & Green        | NIPDAU                               | Level-1-260C-UNLIM   | -55 to 125   | HC4017M                    | <a href="#">Samples</a> |
| CD74HC4017PW     | LIFEBUY       | TSSOP        | PW                 | 16   | 90             | RoHS & Green        | NIPDAU                               | Level-1-260C-UNLIM   | -55 to 125   | HJ4017                     |                         |
| CD74HC4017PWR    | ACTIVE        | TSSOP        | PW                 | 16   | 2000           | RoHS & Green        | NIPDAU                               | Level-1-260C-UNLIM   | -55 to 125   | HJ4017                     | <a href="#">Samples</a> |
| CD74HC4017PWRE4  | ACTIVE        | TSSOP        | PW                 | 16   | 2000           | RoHS & Green        | NIPDAU                               | Level-1-260C-UNLIM   | -55 to 125   | HJ4017                     | <a href="#">Samples</a> |
| CD74HC4017PWT    | LIFEBUY       | TSSOP        | PW                 | 16   | 250            | RoHS & Green        | NIPDAU                               | Level-1-260C-UNLIM   | -55 to 125   | HJ4017                     |                         |

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

**NRND:** Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBsolete:** TI has discontinued the production of the device.

(2) **RoHS:** TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

**RoHS Exempt:** TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

**Green:** TI defines "Green" to mean the content of Chlorine (Cl) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- <sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- <sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- <sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "-" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- <sup>(6)</sup> Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**OTHER QUALIFIED VERSIONS OF CD54HC4017, CD74HC4017 :**

- Catalog : [CD74HC4017](#)
- Automotive : [CD74HC4017-Q1](#), [CD74HC4017-Q1](#)
- Enhanced Product : [CD74HC4017-EP](#), [CD74HC4017-EP](#)
- Military : [CD54HC4017](#)

**NOTE: Qualified Version Definitions:**

- Catalog - TI's standard catalog product
- Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects
- Enhanced Product - Supports Defense, Aerospace and Medical Applications
- Military - QML certified for Military and Defense Applications

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device        | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|---------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| CD74HC4017M96 | SOIC         | D               | 16   | 2500 | 330.0              | 16.4               | 6.5     | 10.3    | 2.1     | 8.0     | 16.0   | Q1            |
| CD74HC4017NSR | SO           | NS              | 16   | 2000 | 330.0              | 16.4               | 8.2     | 10.5    | 2.5     | 12.0    | 16.0   | Q1            |
| CD74HC4017PWR | TSSOP        | PW              | 16   | 2000 | 330.0              | 12.4               | 6.9     | 5.6     | 1.6     | 8.0     | 12.0   | Q1            |
| CD74HC4017PWT | TSSOP        | PW              | 16   | 250  | 330.0              | 12.4               | 6.9     | 5.6     | 1.6     | 8.0     | 12.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device        | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|---------------|--------------|-----------------|------|------|-------------|------------|-------------|
| CD74HC4017M96 | SOIC         | D               | 16   | 2500 | 340.5       | 336.1      | 32.0        |
| CD74HC4017NSR | SO           | NS              | 16   | 2000 | 356.0       | 356.0      | 35.0        |
| CD74HC4017PWR | TSSOP        | PW              | 16   | 2000 | 356.0       | 356.0      | 35.0        |
| CD74HC4017PWT | TSSOP        | PW              | 16   | 250  | 356.0       | 356.0      | 35.0        |

## TUBE



\*All dimensions are nominal

| Device        | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|---------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| CD74HC4017E   | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC4017E   | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC4017EE4 | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC4017EE4 | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC4017M   | D            | SOIC         | 16   | 40  | 507    | 8      | 3940   | 4.32   |
| CD74HC4017PW  | PW           | TSSOP        | 16   | 90  | 530    | 10.2   | 3600   | 3.5    |




# PACKAGE OUTLINE

NS0016A

SOP - 2.00 mm max height

SOP



## NOTES:

1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm, per side.





SOLDER PASTE EXAMPLE  
 BASED ON 0.125 mm THICK STENCIL  
 SCALE:7X

4220735/A 12/2021

NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
8. Board assembly site may have different recommendations for stencil design.

J (R-GDIP-T\*\*)

14 LEADS SHOWN

# CERAMIC DUAL IN-LINE PACKAGE



| PINS **<br>DIM | 14                     | 16                     | 18                     | 20                     |
|----------------|------------------------|------------------------|------------------------|------------------------|
| A              | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC |
| B MAX          | 0.785<br>(19,94)       | .840<br>(21,34)        | 0.960<br>(24,38)       | 1.060<br>(26,92)       |
| B MIN          | —                      | —                      | —                      | —                      |
| C MAX          | 0.300<br>(7,62)        | 0.300<br>(7,62)        | 0.310<br>(7,87)        | 0.300<br>(7,62)        |
| C MIN          | 0.245<br>(6,22)        | 0.245<br>(6,22)        | 0.220<br>(5,59)        | 0.245<br>(6,22)        |



4040083/F 03/03

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - C. This package is hermetically sealed with a ceramic lid using glass frit.
  - D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
  - E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.

## N (R-PDIP-T\*\*)

16 PINS SHOWN

## PLASTIC DUAL-IN-LINE PACKAGE



| PINS **             | 14               | 16               | 18               | 20               |
|---------------------|------------------|------------------|------------------|------------------|
| DIM                 |                  |                  |                  |                  |
| A MAX               | 0.775<br>(19,69) | 0.775<br>(19,69) | 0.920<br>(23,37) | 1.060<br>(26,92) |
| A MIN               | 0.745<br>(18,92) | 0.745<br>(18,92) | 0.850<br>(21,59) | 0.940<br>(23,88) |
| MS-001<br>VARIATION | AA               | BB               | AC               | AD               |



4040049/E 12/2002

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
  - The 20 pin end lead shoulder width is a vendor option, either half or full width.


D (R-PDSO-G16)

PLASTIC SMALL OUTLINE



4040047-6/M 06/11

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - C. Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
  - D. Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
  - E. Reference JEDEC MS-012 variation AC.



4220204/A 02/2017

## NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-153.

# EXAMPLE BOARD LAYOUT


PW0016A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 10X



4220204/A 02/2017

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

# EXAMPLE STENCIL DESIGN

PW0016A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE: 10X

4220204/A 02/2017

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

# MECHANICAL DATA

NS (R-PDSO-G\*\*)

PLASTIC SMALL-OUTLINE PACKAGE

14-PINS SHOWN



- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2023, Texas Instruments Incorporated