# Series 70 *Flexible. Tactile and reliable.*

https://eao.com/70





# 7( **0** Information about the Series

### Key advantages

- Full-face illumination
- Excellent tactile feedback
- Almost limitless design possibilitiesEasy-to-clean, UV-resistant films
- PCB mount switches

### Typical application areas

- Machinery
- Public transportation
- Heavy duty and special vehicles
- Marine
- Telecommunications
- Medical technology
- Energy supply Automation
- Building infrastructure
- Food and beverage industry

### Functions

- Pushbutton
- Illuminated pushbutton
- Indicator

#### Design

Flush

### IP front protection

IP40

### Raitings

• 42 VAC (100 mA)

### Terminal

PCB

### Lens Material

Plastic

### Markings

Printed insert film legends

### Conformities

- CE
- 2011/65/EU (RoHS)



# Index 70

802
804
806
808
810
811
813

# **70** PCB

### Switching element without illumination



Product can differ from the current configuration.





7.5

Dimensions [mm] A = For Part No. 70-100.0 B = For Part No. 70-101.0 C = For Part No. 70-201.0 5.08

12.8 x 12.8

Equipment consisting of (schematic overview)

Spacer cap



Page 810

Each Part Number listed below includes all the black components shown in the 3D-drawing.

Switching element

To obtain a complete unit, please select the red components from the pages shown.

# General information

Contact normally open

 Dimensions with fitted spacing cap see details Spacing cap



## Switching element

Product attributes	Contact material	Switching action	Terminal	Part No.	Wiring diagram	Com- ponent Layout
Operation without spacing cap	Silver	Momentary	PCB terminal	70-100.0	331	80



### Switching element

						Com-
					Wiring	ponent
Product attributes	Contact material	Switching action	Terminal	Part No.	diagram	Layout
Operation with spacing cap	Silver	Momentary	PCB terminal	70-101.0	331	80



### Switching element

Product attributes	Contact material	Switching action	Terminal	Part No.	Wiring diagram	Com- ponent Layout
Operation with spacing cap	Gold	Momentary	PCB terminal	70-201.0	332	79

# РСВ 70

### Wiring diagrams



## **Component layouts**



- B = Drilling plan (component side)
- C = Occupancy plan (component side) D = Hole for switching element

C Ο 2 1 • 3 4 Ø1.3 (4x)

- A = Switching element without illumination with
- B = Drilling plan (component side)
- C = Occupancy plan (component side) D = Hole for centering pins non-metallic
- E = Hole for switching element

# **70** PCB

### Switching element with illumination



Product can differ from the current configuration.



Dimensions [mm]



To obtain a complete unit, please select the red components from the pages shown.

### General information

- The customer has to decide what series resistor shall be used to the LED
- Luminosity and wave length variations caused by LED manufacturing processes may cause slight differences regarding the illumination. The customer has to decide what resistor shall be used to the LED
- Dimensions with fitted spacing cap see details Spacing cap
- Contact normally open



### Switching element

Forward voltage	Contact ma- terial	Lumi. Inten- sity	Dom. Wavelength	Switching action	Terminal	Illumination colour	Part No.	Wiring diagram	Com- ponent Layout
2.0 VDC @ 20 mA	Gold	160 mcd	625 nm	Momentary	PCB ter- minal	Red	70-220.2S	333	82
2.9 VDC @ 20 mA	Gold	600 mcd	580 nm	Momentary	PCB ter- minal	Yellow	70-220.4S	333	82
3.2 VDC @ 20 mA	Gold	650 mcd	525 nm	Momentary	PCB ter- minal	Green	70-220.5S	333	82
3.0 VDC @ 20 mA	Gold	250 mcd	467 nm	Momentary	PCB ter- minal	Blue	70-220.6S	333	82
3.2 VDC @ 20 mA	Gold	500 mcd	x: 0.31 / y: 0.32 nm	Momentary	PCB ter- minal	White	70-220.9S	333	82



### Switching element

<b>.</b>				Wiring	Com- ponent
Contact material	Switching action	Terminal	Part No.	diagram	Layout
Gold	Momentary	PCB terminal	92-851.342	332	82

# РСВ 70

## Wiring diagrams



## **Component layouts**



Dimensions [mm]

- A = Switching element with illumination
- B = Single LED
- C = Drilling plan (component side)
- D = Hole for switching element, Pad max. Ø 2.5 mm E = Hole for LED

# **70** PCB

## Indicator element



Product can differ from the current configuration.



Dimensions [mm]



Each Part Number listed below includes all the black components shown in the 3D-drawing.

To obtain a complete unit, please select the red components from the pages shown.

### General information

- The customer has to decide what series resistor shall be used to the LED
- Contact normally open
- Luminosity and wave length variations caused by LED manufacturing processes may cause slight differences regarding the illumination. The customer has to decide what resistor shall be used to the LED



### Indicator element

Illumination colour	Forward voltage	Lumi. Intensity	Dom. Wavelength	Terminal	Part No.	Wiring diagram	Com- ponent Layout
Red	2.0 VDC @ 20 mA	160 mcd	625 nm	PCB terminal	70-820.2S	330	81
Green	3.2 VDC @ 20 mA	650 mcd	525 nm	PCB terminal	70-820.5S	330	81

## AP.

### Indicator element

		Wiring	Com- ponent
Terminal	Part No.	diagram	Layout
PCB terminal	92-800.042	330	79

### Wiring diagrams



# рсв 70

### **Component layouts**



#### Dimensions [mm]

- A = Switching element without illumination
- B = Drilling plan (component side)
- C = Occupancy plan (component side)
- D = Hole for switching element



Dimensions [mm]

- A = Illumination element
- B = Single LED
- C = Drilling plan (component side)
- D = Hole for centering pins non-metallic
- $\mathsf{E}=\mathsf{Hole}\;\mathsf{for}\;\mathsf{LED}$





Your Expert Partner for Human Machine Interfaces

www.eao.com/70

# 70 Components



### Lens plastic square

Lens material	Lens colour	Lens optics	Lens shape	Lens illumination	Dimensions	Part No.
Plastic	White	translucent	flush	illuminative	19.05 mm x 19.05 mm	70-920.9
	Red	translucent	flush	illuminative	15,4 mm x 15,4 mm	70-921.2
	Orange	translucent	flush	illuminative	15,4 mm x 15,4 mm	70-921.3
	Yellow	translucent	flush	illuminative	15,4 mm x 15,4 mm	70-921.4
	Green	translucent	flush	illuminative	15,4 mm x 15,4 mm	70-921.5
	Blue	translucent	flush	illuminative	15,4 mm x 15,4 mm	70-921.6
	White	translucent	flush	illuminative	15,4 mm x 15,4 mm	70-921.9
	Red	translucent	flush	illuminative	12,4 mm x 12,4 mm	70-922.2
	Orange	translucent	flush	illuminative	12,4 mm x 12,4 mm	70-922.3
	Yellow	translucent	flush	illuminative	12,4 mm x 12,4 mm	70-922.4
	Green	translucent	flush	illuminative	12,4 mm x 12,4 mm	70-922.5
	Blue	translucent	flush	illuminative	12,4 mm x 12,4 mm	70-922.6
	White	translucent	flush	illuminative	12,4 mm x 12,4 mm	70-922.9



Dimensions [mm] A = Front dimension



70

### Lens round

Lens material	Lens colour	Lens optics	Lens shape	Lens illumination	Dimensions	Part No.
Plastic	Red	translucent	flush	illuminative	Ø 15,4 mm	70-911.2
	Orange	translucent	flush	illuminative	Ø 15,4 mm	70-911.3
	Yellow	translucent	flush	illuminative	Ø 15,4 mm	70-911.4
	Green	translucent	flush	illuminative	Ø 15,4 mm	70-911.5
	White	translucent	flush	illuminative	Ø 15,4 mm	70-911.9
	Red	translucent	flush	illuminative	Ø 12,4 mm	70-912.2
	Orange	translucent	flush	illuminative	Ø 12,4 mm	70-912.3
	Yellow	translucent	flush	illuminative	Ø 12,4 mm	70-912.4
	Green	translucent	flush	illuminative	Ø 12,4 mm	70-912.5
	White	translucent	flush	illuminative	Ø 12,4 mm	70-912.9



Dimensions [mm] A = Front dimension

# Components 70



## Single-LED, T1 3/4 MG

Illumination colour	Lumi. Intensity	Dom. Wavelength	Forward voltage	Part No.	Wiring diagram
Red	160 mcd	625 nm	2.0 VDC @ 20 mA	10-2601.3172S	70
Amber	165 mcd	605 nm	2.0 VDC @ 20 mA	10-2601.3173S	70
Yellow	600 mcd	580 nm	2.9 VDC @ 20 mA	10-2603.3174S	70
Green	650 mcd	525 nm	3.2 VDC @ 20 mA	10-2603.3175S	70
Blue	250 mcd	467 nm	3.0 VDC @ 20 mA	10-2603.3176S	70
White	500 mcd	x: 0.31 / y: 0.32 nm	3.2 VDC @ 20 mA	10-2603.3178S	70

#### Additional information

- The customer has to decide what series resistor shall be used to the LED
- Luminosity and wave length variations caused by LED manufacturing processes may cause slight differences regarding the illumination. The customer has to decide what resistor shall be used to the LED

### Wiring diagrams



# 70 Accessories

## Front side

Spacing cap

Product attributes	Dimensions	Part No.
Without recesses for LED	18.9 mm	70-901.0
2 recesses for LED	9 mm	70-910.0
	13 mm	70-911.0
	22.5 mm	70-912.0



Dimensions [mm]

# Technical data 70

### Switching element illuminated Part No. 92-851.342

### Switching system

Short-travel switching system with two independent contact points and tactile operation. Guarantees reliable switching even of very light loads 1 normally open contact

### Material

Material of contact Gold-plated silver

Switching element Plastic

#### Mechanical characteristics

Actuating force With overlay foil 4 N  $\pm$ 1.5 N Max. actuating force >50 N, as per DIN 42115

#### Actuating travel Approx. 0.4 mm

Approx. 0.411111

### Resistance to heat of soldering

250 °C, 3 s (PCB assembly) 320 °C, 3 s (when using a soldering iron)

#### Mechanical lifetime

 $\geq$  5 Mio. operations (switching element without overlay)  $\geq$  1 Mio. operations (switching element under overlay)

Protection IP40 (only switching element) IP65 front side with overlay foil

### **Electrical characteristics**

Electrical life

$\geq$ 500 000 cycles of operation at 42 VDC, 50 mA,
as per IEC 60512-5-9c
When attention is paid to the direction of current flow from terminal
3/4 to 1/2 the electrical life can be prolonged.

Switching voltage and switching current				
Switching voltage	min. 50 mVAC/DC			
	max. 42VAC/DC			
Switching current	min. 10µA AC/DC			
	max. 100 mA AC/DC			
Power rating	max. 2W			

Electric strength 500 VAC, 50 Hz, 1 minute, as per IEC 60512-2-4a

Ambient conditions

Storage temperature -40 °C ... +85 °C

Operating temperature  $-25^{\circ}C \dots + 70^{\circ}C$ 

### Approvals

Conformities CE 2011/65/EC (RoHS)

### Switching element non-illuminated Part No. 70-100.0 and 70-101.0

### Switching system

Short-travel switching system with two independent contact points and tactile operation. Guarantees reliable switching even of very light loads 1 normally open contact

Material

### Mechanical characteristics

Actuating force With overlay foil  $5N \pm 2N$  Max. actuating force >50 N, as per DIN 42115

Actuating travel 0.3 mm

# 70

# 70 Technical data

### **Electrical characteristics**

Electrical life at 5 VDC, 1 mA 500 000 cycles of operation

Switching voltage and switching current Max. 12 VDC, 50 mA Min. 1 VDC, 10 mA

Electric strength 250 VAC for 1 minute

### Ambient conditions

Storage temperature -30 °C ... +85 °C

Operating temperature  $-20 \degree C \dots + 70 \degree C$ 

### Approvals

Conformities CE 2011/65/EC (RoHS)

### Switching element non-illuminated Part No. 70-201.0

### Switching system

Short-travel switching system with two independent contact points and tactile operation. Guarantees reliable switching even of very light loads 1 normally open contact

### Material

Material of contact Gold-plated silver

Switching element Plastic

### Mechanical characteristics

Actuating force With overlay foil  $2.1 \text{ N} \pm 0.2 \text{ N}$ Max. actuating force >50 N, as per DIN 42115

Actuating travel Approx. 0.5 mm

Resistance to heat of soldering 260 °C, 3s, as per IEC 60068-2-20

#### Mechanical lifetime

 $\geq$  5 Mio. cycles of operation (switching element without overlay)  $\geq$  1 Mio. cycles of operation (switching element under overlay)

Protection IP40 (only switching element) IP65 front side with overlay foil

### Electrical characteristics

#### Electrical life

 $\geq$  500 000 cycles of operation at 42 VDC, 50 mA, as per IEC 60512-5-9c When attention is paid to the direction of current flow from terminal  $_34$  to  $_{12}$  the electrical life can be prolonged.

#### Switching voltage and switching current

Switching voltage	min. 50 mVAC/DC
	max. 42VAC/DC
Switching current	min. 10 µA AC/DC
	max. 100 mA AC/DC
Power rating	max. 2W

#### Electric strength

500 VAC, 50 Hz, 1 minute, as per IEC 60512-2-4a

### Ambient conditions

Storage temperature  $-40 \degree C \dots + 85 \degree C$ 

# Operating temperature $-25 \,^{\circ}\text{C} \dots + 70 \,^{\circ}\text{C}$

-25°C...+70°C

#### Approvals

#### Conformities

CE 2011/65/EC (RoHS)

EAO reserves the right to alter specifications without further notice.

# Application Guidelines 70

### Suppressor circuits

When switching inductive loads such as relays, DC motors, and DC solenoids, it is always important to absorb surges (e.g. with a diode) to protect the contacts. When these inductive loads are switched off, a counter emf can severely damage switch contacts and greatly shorten lifetime.

Fig. 1 shows an inductive load with a free-wheeling diode connected in parallel. This free-wheeling diode provides a path for the inductor current to flow when the current is interrupted by the switch. Without this free-wheeling diode, the voltage across the coil will be limited only by dielectric breakdown voltages of the circuit or parasitic elements of the coil. This voltage can be kilovolts in amplitude even when nominal circuit voltages are low (e.g. 12 VDC) see Fig. 2.

The free-wheeling diode should be chosen so that the reverse breakdown voltage is greater than the voltage driving the inductive load. The DC blocking voltage (VR) of the free-wheeling diode can be found in the datasheet of a diode. The forward current should be equal or greater than the maximum current flowing through the load.

To get an efficient protection, the free-wheeling diode must be connected as close as possible to the inductive load!



(Temperature must not exceed during the entire processing)	
Preheating phase (t1 t2): Ramp up:	70 120 sec typ.+1°C/sec
Ramp up to maximum temperature (t2 t3):	not defined
Maximum temperature on the soldering side (Temp 3): Maximum time of soldering process (t3 t4):	250 °C 3 sec
Ramp down at 170 °C:	typ. −2°C/sec

# 70 Application Guidelines

Temperature curve wave soldering



Green curve: Red curve:	Temperature on the component side of the pcb Temperature on the soldering side of the pcb		
Room temperature:	Temp 1		
Preheating:	Temperature process = Process time =		
Ramp up to soldering temperature:	Process time =	t2 t3	
Soldering phase:	Temperature process = Process time =	1	

#### Iron soldering

Basic specification for iron soldering IEC 60068-2-20

Maximum	temperature at tip of iron:	320 °C
Maximum	soldering time:	3 sec

#### Cleaning/Lacquering

The switching elements are not sealed. Cleaning up the PCB may damage the contacts in the switching elements. For this reason, the following points should be noted:

- When soldering make sure that the flux does not pass on the upper side of the PCB.
- When cleaning the PCB with detergents ensure that no dust or other debris may get inside of the switching elements.
- Ensure that no lacquer penetrates into the interior of the switching element when lacquering the PCB.

#### Storage of components

To obtain the optimum solderability of the components, the following points should be noted during storage:

- Do not store components in locations with high temperature or humidity.
- Do not expose components to corrosive gases.
- Avoid direct sunlight for a long period.