

8-Channel Analog Multiplexer/Demultiplexer with injection-current effect control

1 FEATURES

- **Qualified for Automotive Applications**
- **AEC-Q100 Qualified with the Grade 1**
- **Injection-Current Cross Coupling <1mV/mA**
- **Low Crosstalk Between Switches**
- **Supply Operation: 2V to 6V**
- **Operating Temperature Range: -40°C to +125°C**
- **PACKAGES: TSSOP-16, QFN2.5x3.5-16L**

2 APPLICATIONS

- **Analog and Digital Multiplexing and Demultiplexing**
- **Diagnostics and Monitoring**
- **Zonal Architecture**
- **Body Control Modules**
- **Battery Management Systems (BMS)**
- **HVAC Control Module**
- **Automotive Head Unit**
- **Telematics**
- **On-Board (OBC) and Wireless Charging**

3 DESCRIPTIONS

This eight-channel CMOS analog multiplexer/demultiplexer is pin compatible with the RS2251 function and, additionally, features injection-current effect control, which has excellent value in automotive applications where voltages in excess of normal supply voltages are common.

The injection-current effect control allows signals at disabled analog input channels to exceed the supply voltage without affecting the signal of the enabled analog channel. This eliminates the need for external diode/resistor networks typically used to keep the analog channel signals within the supply-voltage range.

The RS2260-Q1 is available in Green TSSOP-16 and QFN2.5x3.5-16L packages. It operates over an ambient temperature range of -40°C to +125°C.

Device Information ⁽¹⁾

| PART NUMBER | PACKAGE | BODY SIZE (NOM) |
|-------------|----------------|-----------------|
| RS2260-Q1 | TSSOP-16 | 5.00mm×4.40mm |
| | QFN2.5x3.5-16L | 2.50mm×3.50mm |

(1) For all available packages, see the orderable addendum at the end of the data sheet.

4 Functional Diagrams




Table of Contents

| | |
|--|----|
| 1 FEATURES | 1 |
| 2 APPLICATIONS | 1 |
| 3 DESCRIPTIONS | 1 |
| 4 Functional Diagrams | 2 |
| 5 Revision History | 4 |
| 6 PACKAGE/ORDERING INFORMATION ⁽¹⁾ | 5 |
| 7 PIN CONFIGURATIONS (TOP VIEW) | 6 |
| 7.1 PIN DESCRIPTION..... | 6 |
| 7.2 FUNCTION TABLE | 6 |
| 8 SPECIFICATIONS | 7 |
| 8.1 Absolute Maximum Ratings | 7 |
| 8.2 ESD Ratings | 7 |
| 8.3 Recommended Operating Conditions..... | 8 |
| 8.4 ELECTRICAL CHARACTERISTICS | 9 |
| 8.5 Injection Current Coupling Specifications..... | 10 |
| 8.6 Switching Characteristics, $V_{CC} = 2\text{ V}$ | 12 |
| 8.7 Switching Characteristics, $V_{CC} = 3\text{ V}$ | 12 |
| 8.8 Switching Characteristics, $V_{CC} = 3.3\text{ V}$ | 12 |
| 8.9 Switching Characteristics, $V_{CC} = 4.5\text{ V}$ | 13 |
| 8.10 Switching Characteristics, $V_{CC} = 6\text{ V}$ | 13 |
| 9 Operating Characteristics | 13 |
| 10 APPLICATION INFORMATION | 14 |
| 11 Parameter Measurement Information | 15 |
| 12 PACKAGE OUTLINE DIMENSIONS | 20 |
| 13 TAPE AND REEL INFORMATION | 22 |

5 Revision History

Note: Page numbers for previous revisions may differ from page numbers in the current version.

| VERSION | Change Date | Change Item |
|---------|-------------|---|
| A.0 | 2023/02/17 | Initial version completed |
| A.0.1 | 2023/08/24 | Add O _{ISO} , XTALK, BW PARAMETER |
| A.0.2 | 2023/09/18 | Update PIN CONFIGURATIONS |
| A.1 | 2023/11/16 | 1. Update ESD Ratings 2. Update ELECTRICAL CHARACTERISTICS 3. Added Marking Information |

6 PACKAGE/ORDERING INFORMATION (1)


| PRODUCT | ORDERING NUMBER | TEMPERATURE RANGE | PACKAGE LEAD | Lead finish/Ball material (2) | MSL Peak Temp (3) | PACKAGE MARKING (4) | PACKAGE OPTION |
|---------------|---------------------|-------------------|--------------------|-------------------------------|-------------------------|---------------------|-----------------------|
| RS2260 -Q1 | RS2260XTS S16-Q1 | -40°C ~+125°C | TSSOP-16 | NIPDAUAG | MSL1-260°- Unlimited | RS2260 | Tape and Reel,4000 |
| | RS2260XT QW16-Q1 | -40°C ~+125°C | QFN2.5x3. 5-16L | NIPDAUAG | MSL1-260°- Unlimited | RS2260 | Tape and Reel,5000 |

NOTE:


- (1) This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the right-hand navigation.
- (2) Lead finish/Ball material. Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.
- (3) MSL Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the lot trace code information (data code and vendor code), the logo or the environmental category on the device.

Marking Information



(1) TSSOP-16



(2) QFN2.5x3.5-16L



7 PIN CONFIGURATIONS (TOP VIEW) (TOP VIEW)



7.1 PIN DESCRIPTION

| NAME | PIN | FUNCTION |
|-------|--------------------------|--|
| | TSSOP-16/ QFN2.5x3.5-16L | |
| Y0-Y7 | 13,14,15,12,1,5,2,4 | Analog Switch Inputs Y0-Y7. |
| COM | 3 | Analog Switch Output. |
| Vcc | 16 | Positive Analog and Digital Supply Voltage Input |
| A | 11 | Digital Address "A" Input. |
| B | 10 | Digital Address "B" Input. |
| C | 9 | Digital Address "C" Input. |
| GND | 8 | Ground. Connect to digital ground. |
| NC | 7 | No Connect. |
| INH | 6 | Digital Enable Input. Normally connected to GND. |

7.2 FUNCTION TABLE

| INH | INPUT STATES | | | ON CHANNEL(S) |
|-----|--------------|---|---|---------------|
| | C | B | A | |
| 1 | X | X | X | NONE |
| 0 | 0 | 0 | 0 | Y0 |
| 0 | 0 | 0 | 1 | Y1 |
| 0 | 0 | 1 | 0 | Y2 |
| 0 | 0 | 1 | 1 | Y3 |
| 0 | 1 | 0 | 0 | Y4 |
| 0 | 1 | 0 | 1 | Y5 |
| 0 | 1 | 1 | 0 | Y6 |
| 0 | 1 | 1 | 1 | Y7 |

X=Don't care

NOTE: Input and output pins are identical and inter-changeable. Either may be considered an input or output; signals pass equally well in either direction.

8 SPECIFICATIONS

8.1 Absolute Maximum Ratings

Over operating free-air temperature range (unless otherwise noted) ⁽¹⁾

| SYMBOL | PARAMETER | | MIN | MAX | UNIT |
|------------------|---|--|------|----------------------|------|
| V _{CC} | Supply Voltage range | | -0.5 | 7 | V |
| V _I | Input Voltage range ⁽²⁾ | | -0.5 | V _{CC} +0.5 | |
| V _{IO} | Switch I/O voltage range ⁽²⁾⁽³⁾ | | -0.5 | V _{CC} +0.5 | |
| I _{IK} | Input clamp current | V _I < 0 or V _I > V _{CC} | | ±20 | mA |
| I _{IOK} | I/O diode current | V _{IO} < 0 or V _{IO} > V _{CC} | | ±20 | |
| I _T | Switch through current | V _{IO} = 0 to V _{CC} | | ±25 | |
| | Continuous current through V _{CC} or GND | | | ±50 | |
| θ _{JA} | Package thermal impedance ⁽⁴⁾ | TSSOP-16 | | 45 | °C/W |
| T _J | Junction Temperature ⁽⁵⁾ | | -40 | 150 | °C |
| T _{stg} | Storage temperature | | -65 | +150 | |

(1) Stresses above these ratings may cause permanent damage. Exposure to absolute maximum conditions for extended periods may degrade device reliability. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those specified is not implied.

(2) The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

(3) This value is limited to 5.5 V maximum.

(4) The package thermal impedance is calculated in accordance with JESD-51.

(5) The maximum power dissipation is a function of T_{J(MAX)}, R_{θJA}, and T_A. The maximum allowable power dissipation at any ambient temperature is P_D = (T_{J(MAX)} - T_A) / R_{θJA}. All numbers apply for packages soldered directly onto a PCB.

8.2 ESD Ratings

The following ESD information is provided for handling of ESD-sensitive devices in an ESD protected area only.

| | | | VALUE | UNIT |
|--------------------|-------------------------|---|-------|------|
| V _(ESD) | Electrostatic discharge | Human-Body Model (HBM), per AEC Q100-002 ⁽¹⁾ | ±2500 | V |
| | | Charged-Device Model (CDM), per AEC Q100-011 | ±1000 | |
| | | Latch-Up (LU), per AEC Q100-004 | ±100 | mA |

(1) AEC Q100-002 indicates that HBM stressing shall be in accordance with the ANSI/ESDA/JEDEC JS-001 specification.



ESD SENSITIVITY CAUTION

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

8.3 Recommended Operating Conditions

Over operating free-air temperature range (unless otherwise noted) ⁽¹⁾

| SYMBOL | PARAMETER | TEST CONDITIONS | MIN | MAX | UNIT |
|-----------------|---|-----------------------|------|-----------------|------|
| V _{CC} | Supply Voltage | | 2 | 6 | V |
| V _{IH} | High-level input voltage control inputs | V _{CC} =2V | 1.6 | | V |
| | | V _{CC} =3V | 2.2 | | |
| | | V _{CC} =3.3V | 2.4 | | |
| | | V _{CC} =4.5V | 3.15 | | |
| | | V _{CC} =6V | 4.2 | | |
| V _{IL} | Low-level input voltage control inputs | V _{CC} =2V | | 0.5 | V |
| | | V _{CC} =3V | | 0.9 | |
| | | V _{CC} =3.3V | | 1 | |
| | | V _{CC} =4.5V | | 1.35 | |
| | | V _{CC} =6V | | 1.8 | |
| V _I | Control input voltage | | 0 | V _{CC} | V |
| V _{IO} | Input/output voltage | | 0 | V _{CC} | V |
| Δt/Δv | Input transition rise or fall time | V _{CC} =2V | | 1000 | ns |
| | | V _{CC} =3V | | 800 | |
| | | V _{CC} =3.3V | | 700 | |
| | | V _{CC} =4.5V | | 500 | |
| | | V _{CC} =6V | | 400 | |
| T _A | Operating temperature | | -40 | 125 | °C |

(1) All unused inputs of the device must be held at V_{CC} or GND to ensure proper device operation.

8.4 ELECTRICAL CHARACTERISTICS

over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER | SYMBOL | TEST CONDITIONS | V _{CC} | T _A =25°C | | | UP TO 85°C | | UP TO 125°C | | UNIT |
|--|---------------------|---|-----------------|----------------------|-----|------|------------|------|-------------|-----|------|
| | | | | MIN | TYP | MAX | MIN | MAX | MIN | MAX | |
| On-state switch resistance | R _{ON} | I _T = 2mA, V _I =V _{CC} to GND, V _{INH} =V _{IL} | 2V | | 470 | 650 | | 670 | | 700 | Ω |
| | | | 3V | | 210 | 280 | | 320 | | 360 | |
| | | 3.3V | | 155 | 215 | | 250 | | 260 | | |
| | | 4.5V | | 105 | 130 | | 140 | | 150 | | |
| | | I _T ≤ 2mA, V _I =V _{CC} to GND, V _{INH} =V _{IL} | 6V | | 85 | 95 | | 110 | | 120 | |
| | | | | | | | | | | | |
| Difference in on-state resistance between switches | ΔR _{ON} | I _T = 2mA, V _I =V _{CC} /2, V _{INH} =V _{IL} | 2V | | 4 | 10 | | 15 | | 20 | Ω |
| | | | 3V | | 2 | 8 | | 12 | | 16 | |
| | | 3.3V | | 2 | 8 | | 12 | | 16 | | |
| | | 4.5V | | 2 | 8 | | 12 | | 16 | | |
| | | I _T ≤ 2mA, V _I =V _{CC} /2, V _{INH} =V _{IL} | 6V | | 3 | 9 | | 13 | | 18 | |
| | | | | | | | | | | | |
| Control input current | I _I | V _I = V _{CC} or GND | 6V | | | ±0.1 | | ±0.1 | | ±1 | μA |
| Off-state switch leakage current (any one channel) | I _{S(OFF)} | V _I =V _{CC} or GND, V _{INH} =V _{IH} | 6V | | | ±0.1 | | ±0.5 | | ±1 | μA |
| Off-state switch leakage current (common channel) | | | | | | ±0.2 | | ±2 | | ±4 | |
| On-state switch leakage current | I _{S(ON)} | V _I =V _{CC} or GND, V _{INH} =V _{IL} | 6V | | | ±0.1 | | ±0.5 | | ±1 | μA |
| Supply current | I _{CC} | V _I =V _{CC} or GND | 6V | | | 2 | | 5 | | 20 | μA |
| Control input capacitance | C _{IC} | A, B, C, INH | | | 3.5 | 10 | | 10 | | 10 | pF |
| Common terminal capacitance | C _{IS} | Switch off | | | 22 | 40 | | 40 | | 40 | |
| Switch terminal capacitance | C _{OS} | Switch off | | | 6.7 | 15 | | 15 | | 15 | |

ELECTRICAL CHARACTERISTICS

over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER | SYMBOL | TEST CONDITIONS | V _{CC} | -40°C to 125°C | | | UNIT |
|----------------|------------------|-----------------------------|-----------------|----------------|-----|-----|------|
| | | | | MIN | TYP | MAX | |
| Off Isolation | O _{ISO} | R _L =50Ω, f=1MHz | 5V | | -75 | | dB |
| Cross talk | XTALK | R _L =50Ω, f=1MHz | 5V | | -77 | | dB |
| -3dB Bandwidth | BW | R _L =50Ω | 5V | | 150 | | MHz |
| | | | 3.3V | | 140 | | MHz |

8.5 Injection Current Coupling Specifications

 $T_A = -40^{\circ}\text{C}$ to 125°C

| PARAMETER | SYMBOL | TEST CONDITIONS | V _{CC} | MIN | TYP ⁽¹⁾ | MAX | UNIT | |
|---|----------------|--------------------------------|--------------------------------------|------|--------------------|------|------|----|
| Maximum shift of output voltage of enabled analog channel | V Δ out | R _s ≤ 3.9K Ω | I _I ⁽²⁾ ≤ 1mA | 3.3V | | 0.17 | 1 | mV |
| | | | | 5V | | 0.30 | 1 | |
| | | | I _I ⁽²⁾ ≤ 10mA | 3.3V | | 0.34 | 5 | |
| | | | | 5V | | 0.38 | 5 | |
| | | R _s ≤ 20K Ω | I _I ⁽²⁾ ≤ 1mA | 3.3V | | 0.81 | 2 | |
| | | | | 5V | | 0.86 | 2 | |
| | | | I _I ⁽²⁾ ≤ 10mA | 3.3V | | 2.27 | 20 | |
| | | | | 5V | | 2.34 | 20 | |

(1) Typical values are measured at T_A = 25°C.

(2) I_I = total current injected into all disabled channels.

8.6 Switching Characteristics, $V_{CC} = 2\text{ V}$

over recommended operating free-air temperature range, $C_L = 50\text{ pF}$ (unless otherwise noted).⁽¹⁾

| PARAMETER | | FROM (INPUT) | TO (OUTPUT) | $T_A = 25^\circ\text{C}$ | | | UP TO 85°C | | UP TO 125°C | | UNIT |
|-----------|------------------------|----------------|-------------|--------------------------|------|------|--------------------------|-------|---------------------------|------|------|
| | | | | MIN | TYP | MAX | MIN | MAX | MIN | MAX | |
| t_{PLH} | Propagation delay time | COM or Yn | Yn or COM | | 19.5 | 31.5 | | 33 | | 34.5 | ns |
| t_{PHL} | | | | | | | | | | | |
| t_{PLH} | Propagation delay time | Channel Select | COM or Yn | | 36 | 59 | | 62.5 | | 66 | ns |
| t_{PHL} | | | | | | | | | | | |
| t_{PZH} | Enable delay time | INH | COM or Yn | | | 49.5 | | 52 | | 54 | ns |
| t_{PZL} | | | | | | | | | | | |
| t_{PHZ} | Disable delay time | INH | COM or Yn | | | 153 | | 178.5 | | 204 | ns |
| t_{PLZ} | | | | | | | | | | | |

(1) This parameter is ensured by design and/or characterization and is not tested in production.

8.7 Switching Characteristics, $V_{CC} = 3\text{ V}$

over recommended operating free-air temperature range, $C_L = 50\text{ pF}$ (unless otherwise noted).⁽¹⁾

| PARAMETER | | FROM (INPUT) | TO (OUTPUT) | $T_A = 25^\circ\text{C}$ | | | UP TO 85°C | | UP TO 125°C | | UNIT |
|-----------|------------------------|----------------|-------------|--------------------------|-----|-------|--------------------------|-------|---------------------------|-----|------|
| | | | | MIN | TYP | MAX | MIN | MAX | MIN | MAX | |
| t_{PLH} | Propagation delay time | COM or Yn | Yn or COM | | 9.5 | 16.5 | | 18 | | 19 | ns |
| t_{PHL} | | | | | | | | | | | |
| t_{PLH} | Propagation delay time | Channel Select | COM or Yn | | 18 | 28.5 | | 33 | | 37 | ns |
| t_{PHL} | | | | | | | | | | | |
| t_{PZH} | Enable delay time | INH | COM or Yn | | | 22 | | 24.5 | | 27 | ns |
| t_{PZL} | | | | | | | | | | | |
| t_{PHZ} | Disable delay time | INH | COM or Yn | | | 121.5 | | 143.5 | | 165 | ns |
| t_{PLZ} | | | | | | | | | | | |

(1) This parameter is ensured by design and/or characterization and is not tested in production.

8.8 Switching Characteristics, $V_{CC} = 3.3\text{ V}$

over recommended operating free-air temperature range, $C_L = 50\text{ pF}$ (unless otherwise noted).⁽¹⁾

| PARAMETER | | FROM (INPUT) | TO (OUTPUT) | $T_A = 25^\circ\text{C}$ | | | UP TO 85°C | | UP TO 125°C | | UNIT |
|-----------|------------------------|----------------|-------------|--------------------------|------|------|--------------------------|------|---------------------------|------|------|
| | | | | MIN | TYP | MAX | MIN | MAX | MIN | MAX | |
| t_{PLH} | Propagation delay time | COM or Yn | Yn or COM | | 8.5 | 15 | | 16 | | 16.5 | ns |
| t_{PHL} | | | | | | | | | | | |
| t_{PLH} | Propagation delay time | Channel Select | COM or Yn | | 15.5 | 25 | | 26.5 | | 28.5 | ns |
| t_{PHL} | | | | | | | | | | | |
| t_{PZH} | Enable delay time | INH | COM or Yn | | | 20.5 | | 22.5 | | 24 | ns |
| t_{PZL} | | | | | | | | | | | |
| t_{PHZ} | Disable delay time | INH | COM or Yn | | | 120 | | 130 | | 159 | ns |
| t_{PLZ} | | | | | | | | | | | |

(1) This parameter is ensured by design and/or characterization and is not tested in production.

8.9 Switching Characteristics, $V_{CC} = 4.5\text{ V}$

over recommended operating free-air temperature range, $C_L = 50\text{ pF}$ (unless otherwise noted).⁽¹⁾

| PARAMETER | | FROM (INPUT) | TO (OUTPUT) | $T_A = 25^\circ\text{C}$ | | | UP TO 85°C | | UP TO 125°C | | UNIT |
|-----------|------------------------|----------------|--------------|--------------------------|-----|-------|--------------------------|------|---------------------------|------|------|
| | | | | MIN | TYP | MAX | MIN | MAX | MIN | MAX | |
| t_{PLH} | Propagation delay time | COM or Y_n | Y_n or COM | | 7.5 | 13.5 | | 14 | | 14.5 | ns |
| t_{PHL} | | | | | | | | | | | |
| t_{PLH} | Propagation delay time | Channel Select | COM or Y_n | | 11 | 19.5 | | 20.5 | | 21 | ns |
| t_{PHL} | | | | | | | | | | | |
| t_{PZH} | Enable delay time | INH | COM or Y_n | | | 14.5 | | 16.5 | | 18 | ns |
| t_{PZL} | | | | | | | | | | | |
| t_{PHZ} | Disable delay time | INH | COM or Y_n | | | 121.5 | | 124 | | 126 | ns |
| t_{PLZ} | | | | | | | | | | | |

(1) This parameter is ensured by design and/or characterization and is not tested in production.

8.10 Switching Characteristics, $V_{CC} = 6\text{ V}$

over recommended operating free-air temperature range, $C_L = 50\text{ pF}$ (unless otherwise noted).⁽¹⁾

| PARAMETER | | FROM (INPUT) | TO (OUTPUT) | $T_A = 25^\circ\text{C}$ | | | UP TO 85°C | | UP TO 125°C | | UNIT |
|-----------|------------------------|----------------|--------------|--------------------------|-----|-------|--------------------------|-------|---------------------------|------|------|
| | | | | MIN | TYP | MAX | MIN | MAX | MIN | MAX | |
| t_{PLH} | Propagation delay time | COM or Y_n | Y_n or COM | | 5 | 12 | | 13 | | 14 | ns |
| t_{PHL} | | | | | | | | | | | |
| t_{PLH} | Propagation delay time | Channel Select | COM or Y_n | | 9.5 | 17.5 | | 18.5 | | 19 | ns |
| t_{PHL} | | | | | | | | | | | |
| t_{PZH} | Enable delay time | INH | COM or Y_n | | | 9 | | 11 | | 12.5 | ns |
| t_{PZL} | | | | | | | | | | | |
| t_{PHZ} | Disable delay time | INH | COM or Y_n | | | 112.5 | | 114.5 | | 117 | ns |
| t_{PLZ} | | | | | | | | | | | |

(1) This parameter is ensured by design and/or characterization and is not tested in production.

9 Operating Characteristics

$T_A = 25^\circ\text{C}$ (see Figure 12)

| SYMBOL | PARAMETER | V_{CC} | TEST CONDITIONS | TYP | UNIT |
|----------|-------------------------------|----------|-----------------|-----|------|
| C_{PD} | Power dissipation capacitance | 3.3V | No load | 15 | pF |
| | | 5V | | 13 | |

10 APPLICATION INFORMATION




Figure 1. Injection-Current Coupling Specification

11 Parameter Measurement Information




Figure 2. On-State-Resistance Test Circuit




Figure 3. Maximum Off-Channel Leakage Current, Any One Channel, Test Setup




Figure 4. Maximum Off-Channel Leakage Current, Common Channel, Test Setup

Parameter Measurement Information (continued)




Figure 5. Maximum On-Channel Leakage Current, Channel to Channel, Test Setup





Figure 6. Propagation Delays, Channel Select to Analog Out



(1) Includes all probe and jig capacitance

Figure 7. Propagation-Delay Test Setup, Channel Select to Analog Out

Parameter Measurement Information (continued)





Figure 8. Propagation Delays, Analog In to Analog Out



(1) Includes all probe and jig capacitance

Figure 9. Propagation-Delay Test Setup, Analog In to Analog Out




Figure 10. Propagation Delays, Enable to Analog Out

Parameter Measurement Information (continued)




Figure 11. Propagation-Delay Test Setup, Enable to Analog Out




Figure 12. Power-Dissipation Capacitance Test Setup

Parameter Measurement Information (continued)




Figure 13. Off Isolation Measurement Setup




Figure 14. Channel-to-Channel Crosstalk Measurement Setup





Figure 15. Bandwidth Measurement Setup

12 PACKAGE OUTLINE DIMENSIONS





TSSOP-16⁽²⁾



| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|------------------|---------------------------|-------|----------------------|-------|
| | Min | Max | Min | Max |
| A ⁽¹⁾ | | 1.100 | | 0.043 |
| A ₁ | 0.050 | 0.150 | 0.002 | 0.006 |
| A ₂ | 0.800 | 0.950 | 0.031 | 0.037 |
| A ₃ | 0.25 | | 0.010 | |
| b _p | 0.190 | 0.300 | 0.007 | 0.012 |
| c | 0.100 | 0.200 | 0.004 | 0.008 |
| D ⁽¹⁾ | 4.900 | 5.100 | 0.193 | 0.201 |
| E ⁽¹⁾ | 4.300 | 4.500 | 0.169 | 0.177 |
| H _E | 6.200 | 6.600 | 0.244 | 0.260 |
| e | 0.650 | | 0.026 | |
| L | 1 | | 0.039 | |
| L _P | 0.500 | 0.750 | 0.020 | 0.030 |
| Q | 0.300 | 0.400 | 0.012 | 0.016 |
| Z | 0.060 | 0.400 | 0.002 | 0.016 |
| y | 0.1 | | 0.004 | |
| θ | 0° | 8° | 0° | 8° |

NOTE:

1. Plastic or metal protrusions of 0.15mm maximum per side are not included.
2. This drawing is subject to change without notice.

QFN2.5x3.5-16L⁽⁴⁾

TOP VIEW

BOTTOM VIEW

SIDE VIEW

RECOMMENDED LAND PATTERN (Unit: mm)

| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|------------------|---------------------------|-------|---------------------------|-------|
| | Min | Max | Min | Max |
| A ⁽¹⁾ | 0.800 | 1.000 | 0.031 | 0.039 |
| A1 | 0.000 | 0.050 | 0.000 | 0.002 |
| A2 | 0.600 | 0.700 | 0.024 | 0.028 |
| A3 | 0.203(REF) ⁽²⁾ | | 0.008(REF) ⁽²⁾ | |
| D ⁽¹⁾ | 2.400 | 2.600 | 0.094 | 0.102 |
| E ⁽¹⁾ | 3.400 | 3.600 | 0.134 | 0.142 |
| e | 0.500(BSC) ⁽³⁾ | | 0.020(BSC) ⁽³⁾ | |
| b | 0.180 | 0.300 | 0.007 | 0.012 |
| L | 0.300 | 0.500 | 0.012 | 0.020 |
| D1 | 0.850 | 1.150 | 0.033 | 0.045 |
| E1 | 1.850 | 2.150 | 0.073 | 0.085 |


NOTE:

1. Plastic or metal protrusions of 0.075mm maximum per side are not included.
2. REF is the abbreviation for Reference.
3. BSC (Basic Spacing between Centers), "Basic" spacing is nominal.
4. This drawing is subject to change without notice.

13 TAPE AND REEL INFORMATION

REEL DIMENSIONS

TAPE DIMENSION



NOTE: The picture is only for reference. Please make the object as the standard.

KEY PARAMETER LIST OF TAPE AND REEL

| Package Type | Reel Diameter | Reel Width(mm) | A0 (mm) | B0 (mm) | K0 (mm) | P0 (mm) | P1 (mm) | P2 (mm) | W (mm) | Pin1 Quadrant |
|----------------|---------------|----------------|---------|---------|---------|---------|---------|---------|--------|---------------|
| TSSOP-16 | 13" | 12.4 | 6.90 | 5.60 | 1.20 | 4.0 | 8.0 | 2.0 | 12.0 | Q1 |
| QFN2.5x3.5-16L | 13" | 12.3 | 2.80 | 3.80 | 1.15 | 4.0 | 8.0 | 2.0 | 12.0 | Q1 |

NOTE:

1. All dimensions are nominal.
2. Plastic or metal protrusions of 0.15mm maximum per side are not included.

IMPORTANT NOTICE AND DISCLAIMER

Jiangsu Runic Technology Co., Ltd. will accurately and reliably provide technical and reliability data (including data sheets), design resources (including reference designs), application or other design advice, WEB tools, safety information and other resources, without warranty of any defect, and will not make any express or implied warranty, including but not limited to the warranty of merchantability Implied warranty that it is suitable for a specific purpose or does not infringe the intellectual property rights of any third party.

These resources are intended for skilled developers designing with Runic products You will be solely responsible for: (1) Selecting the appropriate products for your application; (2) Designing, validating and testing your application; (3) Ensuring your application meets applicable standards and any other safety, security or other requirements; (4) Runic and the Runic logo are registered trademarks of Runic Incorporated. All trademarks are the property of their respective owners; (5) For change details, review the revision history included in any revised document. The resources are subject to change without notice. Our company will not be liable for the use of this product and the infringement of patents or third-party intellectual property rights due to its use.