

# 250mA, Ultra-Low Noise, Low Quiescent Current, LDO Regulator


### **General Description**

The RT9086 is a high performance positive low dropout (LDO) regulator designed for applications requiring very low dropout voltage and ultra-high Power Supply Ripple Rejection (PSRR) low noise, low quiescent current that can supply up to 250mA output current. The input voltage range is from 2.2V to 5.5V. The device is designed to work with a  $1\mu F$  input and a  $1\mu F$  output ceramic capacitor (no separate noise bypass capacitor is required).

The RT9086 features a precise 2% output regulation over line, load, and temperature variations in WL-CSP-4B 0.67x0.67 (BSC) package. The output voltage is available from 1.2V to 4.5V in 25mV steps.

The recommended junction temperature range is  $-40^{\circ}$ C to 125°C, and the ambient temperature range is  $-40^{\circ}$ C to 85°C.


### **Ordering Information**



### Note:

Richtek products are Richtek Green Policy compliant and compatible with the current requirements of IPC/JEDEC J-STD-020.

# **Simplified Application Circuit**



#### **Features**

- Input Voltage Range : 2.2V to 5.5V
- Adjustable Output Voltage: 1.2V to 4.5V
- PSRR
  - ▶ 85dB @ 1kHz (20mA)
  - ▶ 80dB @ 10kHz (20mA)
- Output Current : 250mA
- Very Low Dropout: 120mV
- Very Low IQ (Enabled) : 16μA
- Virtually Zero IQ (Disable): < 1μΑ</li>
- Very Low IG (Enabled): 16μA
- Start-up Time: 80μs
- -40°C to 125°C Operating Junction Temperature Range
- Excellent Noise Immunity
- Fast Response Overload and Line Transient
- Stable with a 1μF Input and Output Ceramic Capacitors
- Accurate Output Voltage 2% Overload, Line, Process, and Temperature Variations
- Over-Current Protection
- Over-Temperature Protection

### **Applications**

- Mobile Phones, Tablets
- Digital Cameras and Audio Devices
- Portable and Battery-Powered Equipment
- Portable Medical Equipment
- Smart Meters
- IP Cameras
- Drones
- Telecom/Networking Cards
- · Wireless Infrastructures
- Medical Equipments

# Marking Information


For marking information, contact our sales representative directly or through a Richtek distributor located in your area.


Copyright © 2023 Richtek Technology Corporation. All rights reserved. RICHTEK is a registered trademark of Richtek Technology Corporation.



# **Pin Configuration**

(TOP VIEW)







SOT-23-5 ZQFN-4L 1x1 WL-CSP-4B 0.67x0.67 (BSC)

# **Functional Pin Description**

Pin No.				
SOT-23-5	ZQFN-4L 1x1	WL-CSP-4B 0.67x0.67	Pin Name	Pin Function
1	4	A1	VIN	Supply input. A minimum of $1\mu F$ ceramic capacitor should be placed as close as possible to this pin for better noise rejection.
2	2	B2	GND	Common ground.
3	3	B1	EN	Enable control input. Connecting this pin to logic high enables the regulator or driving this pin low puts it into shutdown mode. EN can be connected to GND if not used.
4			NC	No internal connection.
5	1	A2	VOUT	Output of the regulator. Decouple this pin to GND with at least $1\mu F$ for stability.
	(- \		GND	Thermal pad for ZQFN-4L 1x1 package, connect to GND.

www.richtek.com



# **RT9086 Output Voltage Table**

Vout = 1.2V to 1.575V	
Vouт	Output Voltage Code
1.2	12
1.225	1A
1.25	1B
1.275	1C
1.3	13
1.325	1D
1.35	1E
1.375	1F
1.4	14
1.425	1G
1.45	1H
1.475	1J
1.5	15
1.525	1K
1.55	1M
1.575	1N

Vout = 1.6V to 1.975V	
Vouт	Output Voltage Code
1.6	16
1.625	1P
1.65	1Q
1.675	1R
1.7	17
1.725	1S
1.75	1T
1.775	1U
1.8	18
1.825	1V
1.85	1W
1.875	1Y
1.9	19
1.925	1Z
1.95	2A
1.975	2B

Vout = 2V to 2.375V		
Vоит	Output Voltage Code	
2	20	
2.025	2C	
2.05	2D	
2.075	2E	
2.1	21	
2.125	2F	
2.15	2G	
2.175	2H	
2.2	22	
2.225	2J	
2.25	2K	
2.275	2M	
2.3	23	
2.325	2N	
2.35	2P	
2.375	2Q	

Vout =	= 2.4V to 2.775V
Vouт	Output Voltage Code
2.4	24
2.425	2R
2.45	2S
2.475	2T
2.5	25
2.525	2U
2.55	2V
2.575	2W
2.6	26
2.625	2Y
2.65	2Z
2.675	3A
2.7	27
2.725	3B
2.75	3C
2.775	3D

Vout =	2.8V to 3.175V
Vоит	Output Voltage Code
2.8	28
2.825	3E
2.85	3F
2.875	3G
2.9	29
2.925	3H
2.95	3J
2.975	3K
3	30
3.025	3M
3.05	3N
3.075	3P
3.1	31
3.125	3Q
3.15	3R
3.175	3S

Vout = 3.2V to 3.575V		
Vоит	Output Voltage Code	
3.2	32	
3.225	3T	
3.25	3U	
3.275	3V	
3.3	33	
3.325	3W	
3.35	3Y	
3.375	3Z	
3.4	34	
3.425	4A	
3.45	4B	
3.475	4C	
3.5	35	
3.525	4D	
3.55	4E	
3.575	4F	

Copyright © 2023 Richtek Technology Corporation. All rights reserved. RICHTEK is a registered trademark of Richtek Technology Corporation.




Vout =	= 3.6V to 3.975V
Vоит	Output Voltage Code
3.6	36
3.625	4G
3.65	4H
3.675	4J
3.7	37
3.725	4K
3.75	4M
3.775	4N
3.8	38
3.825	4P
3.85	4Q
3.875	4R
3.9	39
3.925	4S
3.95	4T
3.975	4U

Vout	= 4V to 4.375V
Vouт	Output Voltage Code
4	40
4.025	4V
4.05	4W
4.075	4Y
4.1	41
4.125	4Z
4.15	5A
4.175	5B
4.2	42
4.225	5C
4.25	5D
4.275	5E
4.3	43
4.325	5F
4.35	5G
4.375	5H

V <sub>OUT</sub> = 4.4V to 4.5V		
Vоит	Output Voltage Code	
4.4	44	
4.425	5J	
4.45	5K	
4.475	5M	
4.5	45	



### **Functional Block Diagram**



### Operation

### **Basic Operation**

The RT9086 is a high performance positive low dropout (LDO) regulator designed for applications requiring very low dropout voltage, ultra-high Power Supply Ripple Rejection (PSRR), low noise and low quiescent current that can supply up to 250mA output current. The input voltage range is from 2.2V to 5.5V. The RT9086 features a precise 2% output regulation over line, load, and temperature variations. The output voltage is available from 1.2V to 4.5V in 25mV steps. The minimum required output capacitance for stable operation is  $1\mu F$  (X5R or X7R) effective capacitance after consideration of the temperature and voltage coefficient of the capacitor.

#### **Enable and Shutdown Operation**

The RT9086 goes into shutdown mode when the EN pin is in a logic low condition. In this condition, the pass transistor, error amplifier, and bandgap are all turned off, reducing the supply current to only  $1\mu A$  (max.). If the shutdown mode is not required, the EN pin can be directly tied to VIN pin to keep the LDO on.

### **Over-Temperature Protection (OTP)**

The over-temperature protection function will turn off the P-MOSFET when the junction temperature exceeds 160°C (typ.), and the output current exceeds 250mA. Once the junction temperature cools down by approximately 26°C (typ.), the regulator will automatically resume operation.

#### **Current Limit Protection**

The RT9086 provides current limit function to prevent the device from damages during overload or shorted-circuit condition. This current is detected by an internal sensing transistor.

#### **Error Amplifier**

The Error Amplifier compares the internal reference voltage with the output feedback voltage from the internal divider, and controls the Gate voltage of P-MOSFET to support good line regulation and load regulation at output voltage.

### **Output Automatic Discharge**

The RT9086 output employs an internal  $10\Omega$  (typ.) pull down resistance to discharge the output when the EN pin is low, and the device is disabled.

Copyright © 2023 Richtek Technology Corporation. All rights reserved. RICHTEK is a registered trademark of Richtek Technology Corporation.



# Absolute Maximum Ratings (Note 1)

• VIN, EN to GND	-0.3V to $6V$
• VOUT to GND	-0.3V to 6V
<ul> <li>Power Dissipation, PD @ TA = 25°C</li> </ul>	
SOT-23-5	0.45W
ZQFN-4L 1x1	1.07W
WL-CSP-4B 0.67x0.67 (BSC)	0.46W
Package Thermal Resistance (Note 2)	
SOT-23-5, θJA	218.1°C/W
SOT-23-5, θJC	28.5°C/W
ZQFN-4L 1x1, θJA	92.7°C/W
ZQFN-4L 1x1, θJC	62.3°C/W
WL-CSP-4B 0.67x0.67 (BSC), θJA	214.9°C/W
• Lead Temperature (Soldering, 10 sec.)	260°C
Junction Temperature	150°C
Storage Temperature Range	−65°C to 150°C
• ESD Susceptibility (Note 3)	
HBM (Human Body Model)	2kV
Decembered Operating Conditions (V. 19)	
Recommended Operating Conditions (Note 4)	0.01/1. 5.51/
Input Voltage Range	2.2V to 5.5V

•	Input Voltage Range	2.2V to 5.5V
•	Output Current	0mA to 250mA
•	EN Voltage	0V to VIN
•	Ambient Temperature Range	-40°C to 85°C
•	Junction Temperature Range	-40°C to 125°C

### **Electrical Characteristics**

 $(V_{IN} = V_{OUT} + 1V, V_{EN} = 1.2V, I_{OUT} = 1 mA, C_{IN} = 1 \mu F, C_{OUT} = 1 \mu F, T_{A} = 25 ^{\circ}C, unless otherwise specified)$ 

Parameter	Symbol	Test Conditions	Min	Тур	Max	Unit
Input Voltage	VIN	V <sub>IN</sub> = V <sub>OUT</sub> + 1V	2.2		5.5	V
Output Voltage Accuracy	Volt. 400	VIN = (VOUT + 1V) to 5.5V, IOUT = 1 mA to 250mA, package : WL-CSP-4B 0.67x0.67 (BSC)	-2		2	%Vout
(Note 5)	Vout_acc	V <sub>IN</sub> = (V <sub>OUT</sub> + 1V) to 5.5V, I <sub>OUT</sub> = 1 mA to 250mA, package : SOT-23-5 and ZQFN-4L 1x1	-3	-3 3		70 V O U T
Line Regulation	VOUT_LineReg	VIN = (VOUT + 1V) to 5.5V, IOUT = 1mA		0.02		%/V
Load Regulation	VOUT_LoadReg	I <sub>OUT</sub> = 1mA to 250mA		0.001		%/mA
LOAD Current	Іоит	Operation in stable and regulated output voltage	0		250	mA
Maximum Output Current	IOUT_MAX		250			mA



Parameter	Symbol	Test Conditions	Min	Тур	Max	Unit
		VEN = 1.2V, IOUT = 0mA		16	25	
Quiescent Current (Note 6)	IQ	V <sub>EN</sub> = 1.2V, I <sub>OUT</sub> = 250mA (Note 7)		300	425	μΑ
(14010-0)		V <sub>EN</sub> = 0.3V (Disable)		0.2	1	
Ground Current (Note 8)	IG	VEN = 1.2V, IOUT = 0mA		16		μА
		Vout ≥ 2.2V, lout = 100mA	-	50	1	
Dropout Voltage (Note 9)	VDROP	V <sub>OUT</sub> ≥ 2.2V, I <sub>OUT</sub> = 250mA (SOT-23-5 and WL-CSP-4B 0.67x0.67 (BSC) package)		120	200	mV
		Vouт ≥ 2.2V, Iouт = 250mA (ZQFN-4L 1x1 package)			250	
		f = 100Hz, Iout = 20mA		88		
Power Supply Rejection	DCDD	f = 1kHz, Iout = 20mA		85		-ID
Ration (Note 7)	PSRR	f = 10kHz, Iout = 20mA		80		dB
		f = 100kHz, Iout = 20mA		60		
Output Noise Voltage		BW = 10Hz to 100kHz, IOUT = 1mA		10		) (mag a
(Note 7)	eN	BW = 10Hz to 100kHz, I <sub>OUT</sub> = 250mA		6.5		μVrms
Output Automatic Discharge Pulldown Resistance	RAD	VEN < 0.3V		10		Ω
EN Pin Logic Input Thre	shold					
Low Input Threshold	VIL	VIN = 2.2 to 5.5V, VEN falling until the output is disabled			0.4	V
High Input Threshold	ViH	V <sub>IN</sub> = 2.2 to 5.5V, V <sub>EN</sub> rising until the output is enabled	1.2			V
Inner Command at EN DIN	1	VEN = 5.5V and VIN = 5.5V		5.5		
Input Current at EN PIN	IEN	VEN = 0V and VIN = 5.5V		0.001		μΑ
Transient Characteristic	s					
Line Transient	A)/0.17 1	$V_{IN} = V_{OUT} + 1V$ to $V_{OUT} + 1.6V$ in $30\mu s$	-1			\
(Note 7)	$\Delta VOUT\_Line$	$V_{IN}$ = $V_{OUT}$ + 1.6 $V$ to $V_{OUT}$ + 1 $V$ in 30 $\mu$ s			1	mV
Load Transient	43/200	IOUT = 1mA to 250mA in 10μs	-40			\/
(Note 7)	$\Delta V$ OUT_Load	IOUT = 250mA to 1mA in 10μs			40	mV
Overshoot on Start-Up (Note 7)	ΔVOUT_Startup	Stated as a percentage of V <sub>OUT(NOM)</sub>			5	%
Start-Up Time	tstart	From VEN > VIH to VOUT = 95% of VOUT		80	150	μS
Protection	•					-
Short Circuit Current Limit	Isc	Temp = 25°C	250	500		mA
Thermal Shutdown	TsD		-	160	1	°C
Thermal Hysteresis	T <sub>SD_H</sub>			26	-	°C

Copyright © 2023 Richtek Technology Corporation. All rights reserved. RICHTEK is a registered trademark of Richtek Technology Corporation.


# **RT9086**



- Note 1. Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions may affect device reliability.
- Note 2.  $\theta_{JA}$  is measured under natural convection (still air) at  $T_A$  = 25°C with the component mounted on a high effective-thermal-conductivity four-layer test board on a JEDEC 51-7 thermal measurement standard.  $\theta_{JC}$  is measured at the top of the package.
- Note 3. Devices are ESD sensitive.
- Note 4. The device is not guaranteed to function outside its operating conditions.
- Note 5. Maximum available load IouT SUPPORT with different VIN due to thermal consideration refers to the curves at Typical Operating Characteristics.
- Note 6. Quiescent current is defined here as the difference in current between the input voltage source and the load at VOUT.
- Note 7. This specification is guaranteed by design.
- Note 8. Ground current is defined here as the total current flowing to ground as a result of all input voltages applied to the
- Note 9. Dropout voltage is the voltage difference between the input and the output at which the output voltage drops to 100mV below its nominal value.



# **Typical Application Circuit**





### **BOM List**


Reference	Part Number	Value	Package	Manufacturer	
CIN, COUT	GRM155R61A105KE01	1μF/10V/X5R	0402	MURATA	





# **Typical Operating Characteristics**


















2023



















Copyright © 2023 Richtek Technology Corporation. All rights reserved. RICHTEK is a registered trademark of Richtek Technology Corporation.









### **Application Information**

Richtek's component specification does not include the following information in the Application Information section. Thereby no warranty is given regarding its validity and accuracy. Customers should take responsibility to verify their own designs and reserve suitable design margin to ensure the functional suitability of their components and systems.

Like any low dropout linear regulator, the RT9086's external input and output capacitors must be properly selected for stability and performance. Use a  $1\mu F$  (X5R or X7R) or larger input capacitor and place it close to the IC's VIN and GND pins. Output capacitor effective capacitance larger than  $1\mu F$  (X5R or X7R) requirement may be used. Place the output capacitor close to the IC's VOUT and GND pins. Increasing capacitance and decreasing ESR can improve the circuit's PSRR and line transient response.

### **Chip Enable Operation**

The RT9086 EN pin internal resistor is  $1M\Omega$  to GND The EN pin is the chip enable input. Pull the EN pin low (< 0.4V) will shutdown the device. During shutdown mode, the RT9086 quiescent current drops to lower than  $1\mu$ A. Drive the EN pin to high (> 1.2V, < 5.5V) will turn on the device again.

#### **Dropout Voltage**

The dropout voltage refers to the voltage difference between the VIN and VOUT pins while operating at specific output current. The dropout voltage VDROP also can be expressed as the voltage drop on the pass-FET at specific output current (IRATED) while the pass-FET is fully operating at ohmic region and the pass-FET can be characterized as an resistance RDS(ON). Thus the dropout voltage can be defined as  $(VDROP = VVIN - VVOUT = RDS(ON) \times IRATED)$ . For normal operation, the suggested LDO operating range is (VVIN > VVOUT + VDROP) for good transient response and PSRR ability. Vice versa, while operating at the ohmic region will degrade these performance severely. Output discharge automatilly the RT9086 output employs an internal  $10\Omega$  pull-down resistance to discharge the output when EN pin is low, and the device is disabled.

#### CIN and COUT Selection

Like any low dropout regulator, the external capacitors of the RT9086 must be carefully selected for regulator stability and performance. Using a capacitor of at least  $1\mu F$  (X5R or X7R) is suitable. With a reasonable PCB layout, the ceramic output capacitor can be placed up to 5cm and the ceramic input capacitor can be placed up to 1cm of the chip. Any good quality ceramic capacitor can be used. However, a capacitor with larger value and lower ESR (Equivalent Series Resistance) is recommended since it will provide better PSRR and line transient response.

The RT9086 is designed specifically to work with low ESR ceramic output capacitor for space saving and performance consideration. Using a ceramic capacitor with capacitance of at least  $1\mu F$  (X5R or X7R) on the RT9086 output ensures stability.

### Minimum Operating Input Voltage (VIN)

The RT9086 does not include any dedicated UVLO circuitry. The RT9086 internal circuitry is not fully functional until VIN is at least 2.2V. The output voltage is not regulated until VIN has reached at least the greater of 2.2 V or (VOUT + VDROP).

#### **Thermal Considerations**

The junction temperature should never exceed the absolute maximum junction temperature T<sub>J</sub>(MAX), listed under Absolute Maximum Ratings, to avoid permanent damage to the device. The maximum allowable power dissipation depends on the thermal resistance of the IC package, the PCB layout, the rate of surrounding airflow, and the difference between the junction and ambient temperatures. The maximum power dissipation can be calculated using the following formula:

 $P_{D(MAX)} = (T_{J(MAX)} - T_{A}) / \theta_{JA}$ 

Copyright © 2023 Richtek Technology Corporation. All rights reserved. RICHTEK is a registered trademark of Richtek Technology Corporation.



where T<sub>J</sub>(MAX) is the maximum junction temperature, TA is the ambient temperature, and  $\theta_{JA}$  is the junction-to-ambient thermal resistance.

For continuous operation, the maximum operating junction temperature indicated under Recommended Conditions is 125°C. The Operating junction-to-ambient thermal resistance,  $\theta_{JA}$ , is highly package dependent. For a SOT-23-5 package, the thermal resistance,  $\theta$ JA, is 218.1°C/W on a standard 51-7 high effective-thermal-conductivity four-layer test board. For a ZQFN-4L 1x1 package, the thermal resistance,  $\theta JA$ , is  $92.7^{\circ}C/W$  on a standard 51-7 high effective-thermal-conductivity four-layer test board. For a WL-CSP-4B 0.67x0.67 (BSC) package, the thermal resistance,  $\theta_{JA}$ , is 214.9°C/W on a standard JEDEC 51-7 high effective-thermal-conductivity four-layer test board. The maximum power dissipation at TA = 25°C can be calculated as below:

 $PD(MAX) = (125^{\circ}C - 25^{\circ}C) / (218.1^{\circ}C/W) = 0.45W$  for a SOT-23-5 package.

 $P_{D(MAX)} = (125^{\circ}C - 25^{\circ}C) / (92.7^{\circ}C/W) = 1.07W$  for a ZQFN-4L 1x1 package.

 $P_{D(MAX)} = (125^{\circ}C - 25^{\circ}C) / (214.9^{\circ}C/W) = 0.46W$  for a WL-CSP-4B 0.67x0.67 (BSC) package.

The maximum power dissipation depends on the operating ambient temperature for the fixed T<sub>J(MAX)</sub> and the thermal resistance,  $\theta_{JA}$ . The derating curves in Figure 1 allows the designer to see the effect of rising ambient temperature on the maximum dissipation.





Figure 1. Derating Curve of Maximum Power Dissipation

### **Layout Considerations**

The dynamic performance of the RT9086 is dependent on the layout of the PCB. PCB layout practices that are adequate for typical LDOs may degrade the PSRR, noise, or transient performance of the RT9086.

Best performance is achieved by placing CIN and COUT on the same side of the PCB as the RT9086, and as close to the package as is practical. The ground connections for CIN and COUT must be back to the RT9086 ground pin using as wide and short a copper trace as is practical.


Connections using long trace lengths, narrow trace widths, and/or connections through vias must be avoided. These add parasitic inductances and resistance that results in inferior performance especially during transient conditions.



GND Pin (2) connect to second layer ground path by Via to increase cooling area directly.


Figure 2. SOT-23-5 Layout Guide





GND Pad (2) and (5) connect to second layer ground path by Via to increase cooling area directly.

Figure 3. ZQFN-4L 1x1 Layout Guide




GND ball (B2) connect to second layer ground path by Via to increase cooling area directly.

Figure 4. WL-CSP-4B 0.67x0.67 (BSC) Layout Guide




# **Outline Dimension**




Cumahad	Dimensions I	In Millimeters	Dimension	s In Inches
Symbol	Min	Min Max		Max
Α	0.889	1.295	0.035	0.051
A1	0.000	0.152	0.000	0.006
В	1.397	1.803	0.055	0.071
b	0.356	0.559	0.014	0.022
С	2.591	2.997	0.102	0.118
D	2.692	3.099	0.106	0.122
е	0.838	1.041	0.033	0.041
Н	0.080	0.254	0.003	0.010
L	0.300	0.610	0.012	0.024

**SOT-23-5 Surface Mount Package** 







Pin #1 ID and Tie Bar Mark Options


Note: The configuration of the Pin #1 identifier is optional, but must be located within the zone indicated.

Council of	Dimensions I	In Millimeters	Dimension	s In Inches	
Symbol	Min	Max	Min	Max	
Α	0.300	0.400	0.012	0.016	
A1	0.000	0.050	0.000	0.002	
A3	0.117	0.162	0.005	0.006	
b	0.175	0.275	0.007	0.011	
D	0.900	1.100	0.035	0.043	
D2	0.450	0.550	0.018	0.022	
E	0.900	1.100	0.035	0.043	
E2	0.450	0.550	0.018	0.022	
е	0.6	625	0.0	)25	
L	0.200	0.300	0.008	0.012	
Н	0.0	)39	0.002		
H1	0.0	)64	0.0	003	

Z-Type 4L QFN 1x1 Package

Copyright © 2023 Richtek Technology Corporation. All rights reserved. DS9086-10 November 2023






Symbol	Dimensions I	In Millimeters	Dimension	s In Inches	
Symbol	Min	Max	Min	Max	
Α	0.355	0.445	0.014	0.018	
A1	0.135	0.165	0.005	0.006	
b	0.190	0.230	0.007	0.009	
D	0.630	0.710 0.025		0.028	
D1	0.3	350	0.0	)14	
E	0.630	0.710	0.025	0.028	
E1	0.3	350	0.0	)14	
е	0.3	350	0.014		

4B WL-CSP 0.67x0.67 Package (BSC)




# **Footprint Information**




Dookogo	Number of	of Footprint Dimension (mm)							Tolerance	
Package	Pin	P1	P2	Α	В	С	D	М	Tolerance	
TSOT-25/TSOT-25(FC)/SOT-25	5	0.95	1.90	3.60	1.60	1.00	0.70	2.60	±0.10	





Dooleage	Number of		Footprint Dimension (mm)						Toloropoo				
Package	Pin P Ax Ay Bx By C C1 D D1 Sx Sy					Tolerance							
U/X/ZQFN1x1-4	4	0.625	1.800	0.900	0.450	0.350	0.675	0.474	0.275	0.074	0.400	0.400	±0.050





Dookogo	Number of	Tuno	Footpri	nt Dimensio	Toloropoo		
Package	Pin	Type	е	Α	В	Tolerance	
WL-CSP0.67x0.67-4(BSC)	4	NSMD	0.350	0.200	0.300	±0.025	
WL-C3P0.07X0.07-4(B3C)	4	SMD	0.330	0.230	0.200	±0.025	

### **Richtek Technology Corporation**

14F, No. 8, Tai Yuen 1st Street, Chupei City Hsinchu, Taiwan, R.O.C.

Tel: (8863)5526789

Richtek products are sold by description only. Richtek reserves the right to change the circuitry and/or specifications without notice at any time. Customers should obtain the latest relevant information and data sheets before placing orders and should verify that such information is current and complete. Richtek cannot assume responsibility for use of any circuitry other than circuitry embodied in a Richtek product. Information furnished by Richtek is believed to be accurate and reliable. However, no responsibility is assumed by Richtek or its subsidiaries for its use; nor for any infringements of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Richtek or its subsidiaries.

Copyright © 2023 Richtek Technology Corporation. All rights reserved. RICHTEK is a registered trademark of Richtek Technology Corporation.



### **Datasheet Revision History**

Version	Date	Description	Item
09	2023/10/24	Modify	General Description on P1 Ordering Information on P1 Recommended Operating Conditions on P6 Application Information on P13
10	2023/11/13	Modify	Electrical Characteristics on P7