

RF-BM-S02I 模块硬件规格书



信驰达科技有限公司

更新日期：2018 年 08 月 02 日

目录

目录.....	2
概述.....	3
模块参数.....	4
模块引脚及定义.....	5
PCB 封装尺寸（四层板工艺）	6
天线.....	7
推荐操作条件.....	9
回流焊条件.....	10
静电放电警示.....	11
版本更新记录.....	12
联系我们.....	12
附录 A：模块原理图.....	13
附录 B：FCC 认证.....	14
附录 C：RoHS 认证.....	15
附录 D：End Product Listing.....	16
附录 E：REACH 认证.....	17

● 概述

RF-BM-S02I 蓝牙模块是基于 TI 公司 CC2540 芯片研发的低功耗蓝牙 (BLE) 射频模块, 可广泛应用于短距离无线通信领域。具有功耗低、体积小、传输距离远、抗干扰能力强等特点。模块采用半孔形式硬件接口设计, 带 IPEX 1 代天线座。

该模块可用于开发基于蓝牙 4.0 (BLE, 低功耗蓝牙) 的消费类电子产品, 手机外设产品等, 能提高操作的可靠性; 提高信号的传输距离和抗干扰性; 还能实现解决不同电子产品间的互操作问题, 电池寿命也可显著延长。为客户产品与智能移动设备通讯提供快速的 BLE 解决方案。软件开发可参考基于 TI 提供的标准 BLE 协议栈, LIB 底层库以及 API 调用接口。源码级 profile, APP Demo 等资料可有效缩短开发投入时间。

此模块的设计目的是迅速桥接电子产品和智能移动设备, 可广泛应用于有此需求的各种电子设备, 如仪器仪表, 物流跟踪, 健康医疗, 智能家居, 运动计量, 汽车电子, 休闲玩具等。用户可借此模块, 以最短的开发周期整合现有方案或产品, 以最快的速度占领市场, 同时为企业的发展注入崭新的技术力量。

● 模块参数

以德州仪器设计为参考 TA = 25℃, VDD = 3 V and Fc = 2440MHz;

工作电压	2.0V ~ 3.6V
工作频段	2400 ~ 2483.5MHz
最大发射功率	+4dBm (-23dBm~+4dBm, 可编程)
接收灵敏度(低增益模式)	-87dBm
接收灵敏度(高增益模式)	-93dBm
频率误差	±20kHz
工作温度	-20℃ ~ +70℃ (芯片支持-40℃~+85℃, 可通过更换晶体调整工作温度)
储存温度	-40℃ ~ +85℃ (芯片支持-40℃~+125℃, 可通过更换晶体调整存储温度)
接收电流 RX	19.6mA
发射电流 TX (-6dBm)	24mA
功率模式 1 (4μs Wake-Up)	235μA
功率模式 2 (SleepTimerOn)	0.9μA
功率模式 3 (External Interrupts)	0.4μA

● 模块引脚及定义

如图 1 显示的是模块的引脚图，表 1 为其各引脚定义。




图 1 引脚定义

表 1 引脚定义

脚位	名称	功能	备注
Pin1	GND	模块地	模块地
Pin2	VCC	电源正极输入	模块电源，2V-3.6V
Pin3	P22	I/O	
Pin4	P21	I/O	
Pin5	RESET	复位脚	
Pin6	P20	I/O	
Pin7	P17	I/O	
Pin8	USB_P	USB+	CC2540 芯片支持 USB_P
Pin9	USB_N	USB-	CC2540 芯片支持 USB_N
Pin10	P12	I/O	
Pin11	P11	I/O	
Pin12	P07	I/O	
Pin13	P06	I/O	
Pin14	P05	I/O	
Pin15	P04	I/O	
Pin16	P03	I/O	
Pin17	P02	I/O	
Pin18	P01	I/O	

*注：此模块为追求小尺寸的精简版，部分 IO 没有引出。

● PCB 封装尺寸（四层板工艺）

模块为邮票半孔封装，如图 2 为模块尺寸，模块厚度为 $1.7\text{mm} \pm 0.2\text{mm}$ 。




图 2 尺寸图

● 天线

RF-BM-S02I 模块使用 IPEX 1 代天线座，天线座的规格如图 3 所示：




图 3 IPEX 板端规格

IPEX 线端规格如图 4 所示：




图 4 IPEX 线端规格

常用的天线有：





图 5 常用天线

● 推荐操作条件

功能操作在以下表格中各条件参数值的极限之外不能保证其性能，长期在这个极限之外操作或多或少会影响模块的可靠性。

注意：

- 1、操作温度受晶体频率的变化限制；
- 2、为了确保无线射频性能，电源上纹波必须小于 $\pm 200\text{mV}$ 。

标识	条件	最小值	典型值	最大值	单位
电源与 IO	电池模式	1.8	3.3	3.8	V
操作温度	/	-40	25	85	°C
环境热摆		-20		20	°C/分钟

● 回流焊条件

- 1、加热方法：常规对流或 IR 对流；
- 2、允许回流焊次数：2 次，基于以下回流焊(条件)(见图 4)；
- 3、温度曲线：回流焊应按照下列温度曲线(见图 4)；
- 4、最高温度：245°C。




图 4 部件的焊接耐热性温度曲线(焊接点)

● 静电放电警示



模块会因静电释放而被损坏，RF-star 建议所有模块应在以下 3 个预防措施下处理：

- 1、必须遵循防静电措施，不可以裸手拿模块。
- 2、模块必须放置在能够预防静电的放置区。
- 3、在产品设计时应该考虑高电压输入或者高频输入处的防静电电路。

静电可能导致的结果为细微的性能下降到整个设备的故障。由于非常小的参数变化都可能导致设备不符合其认证要求的值限，从而模块会更容易受到损害。

● 版本更新记录

版本号	文档日期	更新内容
V1.0	2018/02/07	✓ 更新模块实物图 ✓ 更新模块工作与存储温度范围
V1.0	2018/02/26	✓ 更正模块工作与存储温度范围
V1.0	2018/08/02	✓ 更新公司地址

● 联系我们

深圳市信驰达科技有限公司

SHENZHEN RF STAR TECHNOLOGY CO.,LTD.


Tel: 0755-8632 9829 Web: www.szrfstar.com

Fax: 0755-86329413 E-mail: sales@szrfstar.com

地址: 深圳市南山区高新园科技南一道创维大厦 C 座 601 室

Add: Room 601,Block C,Skyworth Building,Nanshan High-Tech Park,Shenzhen.

附录 A：模块原理图



RF-BM-S02

深圳信驰达科技有限公司

附录 B: FCC 认证

TCB
**GRANT OF EQUIPMENT
AUTHORIZATION**
TCB

Certification
 Issued Under the Authority of the
 Federal Communications Commission
 By:

Nemko Canada Inc.
 303 River Road
 Ottawa, Ontario, K1V 1H2
 Canada

Date of Grant: 01/07/2016

Application Dated: 01/05/2016

ShenZhen RF-STAR Technology CO.,LTD
 2F,BLDG.8,Zone A,BaoAn Internet Industry Base,
 BaoYuan Road,XiXiang, BaoAn DIST,
 ShenZhen,
 China

Attention: Aroo woo

NOT TRANSFERABLE

EQUIPMENT AUTHORIZATION is hereby issued to the named GRANTEE, and is
 VALID ONLY for the equipment identified hereon for use under the Commission's
 Rules and Regulations listed below.

FCC IDENTIFIER: 2ABN2-RFBMS02A
 Name of Grantee: ShenZhen RF-STAR Technology CO.,LTD
 Equipment Class: Digital Transmission System
 Notes: Bluetooth Module
 Modular Type: Limited Single Modular

Grant Notes	FCC Rule Parts	Frequency Range (MHZ)	Output Watts	Frequency Tolerance	Emission Designator
	15C	2402.0 - 2480.0	0.000731		

Limited Single Modular Approval. Power output listed is conducted. Approval is limited to OEM installation only. Compliance of this device in all final host configurations is the responsibility of the Grantee. The antenna(s) used for this transmitter must not be co-located or operating in conjunction with any other transmitter. OEM integrators must be provided with antenna installation instructions and labeling requirements for finished products. OEM integrators and End-users must be provided with transmitter operation conditions for satisfying RF exposure compliance. This grant is valid only when the device is sold to OEM integrators and the OEM integrators are instructed to ensure that the end user has no manual instructions to remove or install the device. Separate approval is required for all other operating configurations, including portable configurations with respect to 2.1093 and different antenna configurations.

附录 C: RoHS 认证

BTS

TEST REPORT

REPORT No.: **BTS201312302663** Date: 2014-01-09 Page 1 of 8

Client Company: Shenzhen RF-STAR Technology Co., LTD

Client Address: 2F,BLDG.8, Zone A, BaoAn Internet Industry Base,
BaoYuan Road, XiXiang, BaoAn DIST, ShenZhen


Report on the submitted samples said to be:

Sample Name	: Bluetooth 4.0 (BLE) Module
Style/ Item No.	: RF-BM-S01; RF-BM-S01_V1.1
Product Rating	: DC3.3V, Max40mA; Max0.132w; 2483.5MHz
Operating Frequency Range	: 2402-2483.5MHz
RF Output Power	: -23dBm-4dBm
Sample Receiving Date	: December 30, 2013
Testing Period	: December 30, 2013 to January 09, 2014
Results	: See next pages

Summary of Test Results:

TEST REQUEST	CONCLUSION
A EU RoHS Directive 2011/65/EU and its amendment directives	Pass

Signed for and on behalf of
BTS


Liping Xu



This document is issued by the Company subject to its General Conditions of service of service printed overleaf, available on request for electronic format documents, subject to terms and conditions for electronic documents. is drawn to the limitation of liability indemnification and jurisdiction issues defined therein. any holder of this document is advised that information contained hereon reflects the company's findings at the time of its intervention only and within the limits of client's instructions. if any, the company's sole responsibility is to its client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. this document cannot be reproduced except in full, without prior written approval of the company. any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. unless otherwise stated the results shown in this test report refer only to the sample(s) tested.

Bestow Technology Service Co., LTD (BTS)
716# of General Building, Bantian Hi-Tech. Industry park, Longgang District, Shenzhen
City, Guangdong Province, P.R. China
深圳贝思特技术服务有限公司 中国广东省深圳市龙岗区坂田高新技术产业园综合楼716# 邮编/post code: 518129 电话/telephone: 0755-89500120-8015 传真/fax: 0755-89589101 chaxun@bestow.cn

附录 D: End Product Listing

EPL Bluetooth® End Product Listing

The Bluetooth SIG Hereby Recognizes

ShenZhen RF STAR Technology CO.,LTD.

Member Company

RF-BM-S01_v1.1

Qualified Design Name

Qualified Design ID(s): **B016552**

Contact Person: **Aroo Wong**

Series: **V1.1**

Publish Date: **13 November 2013**

EPL Type: **Other**

This certificate acknowledges the *Bluetooth*® Specifications declared by the member were achieved in accordance with the *Bluetooth* Qualification Process as specified within the *Bluetooth* Specifications and as required within the current PRD



附录 E: REACH 认证

Verification of Conformity	
Applicant Name:	SHENZHEN RFSTAR TECHNOLOGY CO.,LTD
Address:	2F,BLOCK8,DIST.A,INTERNET INDUSTRY BASE,BAOYUAN ROAD ,BAOAN DIST.,SHENZHEN,CHINA
hereby declares that the product	
Product Tested:	BLE BLUETOOTH MODULE ZIGBEE MODULE WIFI MODULE
Model Number:	RF-BM-S01;RF-BM-S02;RF-BM-S02A;RF-BM-S03;RF-BM-S02D; RF-BM-S03S; RF-BM-S02I;RF-BM-26405X5B1;RF-WM-3200B1;RF-WM-7681B1;RF-WM-7681 B2;RF-DG-2540B1;RF-ZM-2530B1;RF-ZMPA-2530B1;RF-BMPA-2540B1;RF-BM -51822B1
Ratings and principal characteristics:	The mixed test result is PASS,Conform to the requirements of the regulations
Conforms to the following specifications	
Relevant Standards/ Specifications/ Directives	Article 33 of Regulation (EC) No 1907/2006 requires supplier of an article containing a substance meeting the criteria in Article 57 and identified in accordance with Article 59(1) in a concentration above 0.1% weight (w/w) shall provide the recipient of the article with sufficient information, available to the supplier, to allow safe use of the article including, as a minimum, the name of that substance.
Verification Issuing Office Name & Address	Eurones Consumer Products Testing Service Co.,Ltd 3F,Huafeng Building,No.77, Hetian Avenue Houjie Town, Dongguan City, Guangdong Province,China
Date of tests Report no.	Sep 22, 2015 C150918025001
	
Signature: <u>Will Pan</u>	
Name: Will Pan	
Position: CPST	
Date: <u>2015-9-22</u>	