

ACT™ 1 Field Programmable **Gate Arrays**

T-46-19-11

Features

- Up to 2000 Gate Array Gates (6000 PLD/LCATM equivalent gates)
- · Replaces up to 53 TTL Packages
- Replaces up to 17 20-Pin PALTM Packages
- Design Library with over 250 Functions
- Gate Array Architecture Allows Completely Automatic Place and Route
- Up to 547 Programmable Logic Modules
- Up to 273 Flip-Flops
- Flip-Flop Toggle Rates to 100 MHz
- Two In-Circuit Diagnostic Probe Pins Support Speed Analysis to 50 MHz
- Built-In High Speed Clock Distribution Network
- I/O Drive to 4 mA
- Nonvolatile, User Programmable
- · Logic Fully Tested Prior to Shipment

Product Family Profile

Device	A1010A	A1020A
Capacity		
Gate Array Equivalent Gates	1200	2000
PLD/LCA Equivalent Gates	3000	6000
TTL Equivalent Packages	34	53
20-Pin PAL Equivalent Packages	12	17
Logic Modules	295	547
Flip-Flops (maximum)	147	273
Routing Resources		
Horizontal Tracks/Channel	22	2
Vertical Tracks/Column	13	13
PLICE Antifuse Elements	112,000	186,000
User I/Os (maximum)	57	6:
Packages	44 PLCC	44 PLC
	68 PLCC	68 PLC
		84 PLC
	100 PQFP	100 PQF
	44 JQCC	44 JQC
	68 JQCC	68 JQC
		84 JQC
		84 CQF
	84 CPGA	84 CPG
Performance		
Flip-Flop Toggle Rate (maximum)	95 MHz	95 MH
System Speed (maximum)	40 MHz	40 MH
CMOS Process	1.2 µm	1.2 µr

1. See Product Plan on pages 1-6 for package availability.

Description

The ACTTM 1 family of field programmable gate arrays (FPGAs) offers a variety of package, speed, and application combinations. Devices are implemented in silicon gate, 1.2-micron or 2-micron two-level metal CMOS, and they employ Actel's PLICE $^{\text{TM}}$ antifuse technology. The unique architecture offers gate array flexibility, high performance, and instant turnaround through user programming. Device utilization is typically 95% of available logic modules.

ACT 1 devices also provide system designers with unique on-chip diagnostic probe capabilities, allowing convenient testing and debugging. Additional features include an on-chip clock driver with a hardwired distribution network. The network provides efficient clock distribution with minimum skew.

The user-definable I/Os are capable of driving at both TTL and CMOS drive levels. Available packages include plastic and ceramic J-leaded chip carriers, ceramic and plastic quad flatpacks, and ceramic pin grid array.

A security fuse may be programmed to disable all further programming and to protect the design from being copied or reverse engineered.

The Action Logic System

The ACT 1 device family is supported by Actel's Action LogicTM System (ALS), allowing logic design implementation with minimum effort. The ALS interfaces with the resident CAE system to provide a complete gate array design environment: schematic capture, simulation, fully automatic place and route, timing verification, and device programming. The Action Logic System is available for 386TM PC and for ApolloTM and SunTM workstations and for running Viewlogic®, Mentor Graphics®, Valid™, and OrCADTM.

T-46-19-11




Figure 1. Partial View of an ACT 1 Device

ACT 1 Device Structure

A partial view of an ACT 1 device (Figure 1) depicts four logic modules and distributed horizontal and vertical interconnect tracks. PLICE antifuses, located at intersections of the horizontal and vertical tracks, connect logic module inputs and outputs. During programming, these antifuses are addressed and programmed to make the connections required by the circuit application.

The Actel Logic Module

The Actel logic module is an 8-input, one-output logic circuit chosen for the wide range of functions it implements and for its efficient use of interconnect routing resources (Figure 2).

The logic module can implement the four basic logic functions (NAND, AND, OR, and NOR) in gates of two, three, or four inputs. Each function may have many versions, with different combinations of active-low inputs. The logic module can also implement a variety of D-latches, exclusivity function, AND-ORs, and OR-ANDs. No dedicated hardwired latches or flip-flops are required in the array since latches and flip-flops may be constructed from logic modules wherever needed in the application.




Figure 2. ACT 1 Logic Module

ACT 1 Array Performance

T-46-19-11

I/O Buffers

Each I/O pin is available as an input, output, three-state, or bidirectional buffer. Input and output levels are compatible with standard TTL and CMOS specifications. Outputs sink or source 4 mA at TTL levels. See Electrical Specifications for additional I/O buffer specifications.

Device Organization

ACT 1 devices consist of a matrix of logic modules arranged in rows separated by wiring channels. This array is surrounded by a ring of peripheral circuits including I/O buffers, testability circuits, and diagnostic probe circuits providing real-time diagnostic capability. Between rows of logic modules are routing channels containing sets of segmented metal tracks with PLICE antifuses. Each channel has 22 signal tracks. Vertical routing is permitted via 13 vertical tracks per logic module column. The resulting network allows arbitrary and flexible interconnections between logic modules and I/O modules.

Probe Pin

ACT 1 devices have two independent diagnostic probe pins. These pins allow the user to observe any two internal signals by entering the appropriate net name in the diagnostic software. Signals may be viewed on a logic analyzer using Actel's ActionprobeTM diagnostic tools. The probe pins can also be used as user-defined I/Os when debugging is finished.

Temperature and Voltage Effects


Worst-case delays for ACT 1 arrays are calculated in the same manner as for masked array products. A typical delay parameter is multiplied by a derating factor to account for temperature, voltage, and processing effects. However, in an ACT 1 array, temperature and voltage effects are less dramatic than with masked devices. The electrical characteristics of module interconnections on ACT 1 devices remain constant over voltage and temperature fluctuations.

As a result, the total derating factor from typical to worst case for a standard speed ACT 1 array is only 1.19 to 1, compared to 2 to 1 for a masked gate array.

Logic Module Size

Logic module size also affects performance. A mask programmed gate array cell with four transistors usually implements only one logic level. In the more complex logic module (similar to the complexity of a gate array macro) of an ACT 1 array, implementation of multiple logic levels within a single module is possible. This eliminates interlevel wiring and associated RC delays. The effect is termed "net compression."

Ordering information





Product Plan

T-46-19-11

	Speed Grade*					Application	1	
	Std	-1	-2	С	ı	M	В	E
A1010A Device								
44-pin Plastic Leaded Chip Carrier (PL)	<u> </u>	<u> </u>	<i>w</i>	<i>ν</i>	<i>y</i>	_	_	_
68-pin Plastic Leaded Chip Carrier (PL)	~	~	سو	سو	سو	_	_	_
100-pin Plastic Quad Flatpack (PQ)	~	-	صد	· •	صو	-	_	
84-pin Ceramic Pin Grid Array (PG)	w	-	_	-	-	M	1	_
A1020A Device								
44-pin Plastic Leaded Chip Carrier (PL)	<u> </u>	<u> </u>	~	<u> </u>	<u> </u>	_		
68-pin Plastic Leaded Chip Carrier (PL)	~	سا	-	-	1	_	_	
84-pin Plastic Leaded Chip Carrier (PL)	~	-	-	-	1	_	_	_
100-pin Plastic Quad Flatpack (PQ)	_	1	مسو	مو	pro-	_	_	ـ ـ
84-pin Ceramic Pin Grid Array (PG)	مو	-	-	200	_	سو	100	- -
84-pin Ceramic Quad Flatpack (CQ)		1	_	مو	_	-	1	_
44-pin J-leaded Cerquad Chip Carrier (JQ)		200	_	-	_	-	مر	_
68-pin J-leaded Cerquad Chip Carrier (JQ)		40	_	· •	-	-	1	_
84-pin J-leaded Cerguad Chip Carrier (JQ)	1	100	_	<u> </u>	_	<u> </u>	<u> </u>	_

Applications: C = Commercial

* Speed Grade: -1 = 15% faster than Standard -2 = 25% faster than Standard

i = Industrial

P = Planned -- = Not Planned

M = Military
B = MIL-STD-883
E = Extended Flow

STD-883

E = Extended Fix

Device Resources

-			User I/Os					
Device Series	Logic Modules	Gates	44-pin	6 8-pin	84-pin	100-pin		
A1010A	295	1200	34	57	57	57		
A1020A	547	2000	34	57	69	69		

3E D ■ 0192496 0000377 779 ■ ACT

Pin Description

CLK Clock (Input)

TTL Clock input for global clock distribution network. The Clock input is buffered prior to clocking the logic modules. This pin can also be used as an I/O.

DCLK Diagnostic Clock (Input)

TTL Clock input for diagnostic probe and device programming. DCLK is active when the MODE pin is HIGH. This pin functions as an I/O when the MODE pin is LOW.

GND Ground (Input)

Input LOW supply voltage.

i/O Input/Output (Input, Output)

I/O pin functions as an input, output, three-state, or bidirectional buffer. Input and output levels are compatible with standard TTL and CMOS specifications. Unused I/O pins are automatically driven LOW by the ALS software.

MODE Mode (Input)

The MODE pin controls the use of multi-function pins (DCLK, PRA, PRB, SDI). When the MODE pin is HIGH, the special functions are active. When the MODE pin is LOW, the pins function as I/O.

NC No Connection

This pin is not connected to circuitry within the device.

PRA Probe A (Output) T-46-19-11

ACT 1 FPGAs

The Probe A pin is used to output data from any user-defined design node within the device. This independent diagnostic pin is used in conjunction with the Probe B pin to allow real-time diagnostic output of any signal path within the device. The Probe A pin can be used as a user-defined I/O when debugging has been completed. The pin's probe capabilities can be permanently disabled to protect the programmed designs confidentiality. PRA is active when the MODE pin is HIGH. This pin functions as an I/O when the MODE pin is LOW.

PRB Probe B (Output)

The Probe B pin is used to output data from any user-defined design node within the device. This independent diagnostic pin is used in conjunction with the Probe A pin to allow real-time diagnostic output of any signal path within the device. The Probe B pin can be used as a user-defined I/O when debugging has been completed. The pin's probe capabilities can be permanently disabled to protect the programmed design's confidentiality. PRB is active when the MODE pin is HIGH. This pin functions as an I/O when the MODE pin is LOW.

SDI Serial Data Input (Input)

Serial data input for diagnostic probe and device programming. SDI is active when the MODE pin is HIGH. This pin functions as an I/O when the MODE pin is LOW.

V_{CC} Supply Voltage (Input)

Input HIGH supply voltage.

V_{PP} Programming Voltage (input)

Input supply voltage used for device programming. This pin must be connected to V_{CC} during normal operation.





T-46-19-11

Absolute Maximum Ratings

Free air temperature range

Symbol	Parameter	Limits	Units
Vcc	DC Supply Voltage ¹	-0.5 to +7.0	Volts
Vi	Input Voltage	-0.5 to V _{CC} +0.5	Volts
V _O	Output Voltage	-0.5 to V _{CC} +0.5	Volts
I _{IK}	Input Clamp Current	±20	mA
юк	Output Clamp Current	±20	mA
l _{ok}	Continuous Output Current	±25	mA
TSTG	Storage Temperature	-65 to +150	°C

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. Exposure to absolute maximum rated conditions for extended periods may affect device reliability. Device should not be operated outside the Recommended Operating Conditions.

1. V_{PP} = V_{CC}, except during device programming.

Recommended Operating Conditions

Parameter	Commercial	Industrial	Military	Units
Temperature Range ¹	0 to +70	-40 to +85	-55 to +125	۰c
Power Supply Tolerance	±5	±10	±10	%V _{CC}

Note:

1. Ambient temperature (TA) used for commercial and industrial; case temperature (T_C) used for military.

Electrical Specifications

Dana	meter	Com	mercial	Ind	ustrial	M	litary	
raja		Min.	Max.	Min.	Max.	Min.	Max.	Unita
v. 1	$(I_{OH} = -4 \text{ mA})$	3.84				- <u> </u>		٧
V _{OH} ¹	$(I_{OH} = -3.2 \text{ mA})$			3.7		3.7		٧
V _{OL} ¹	(l _{OL} = 4 mA)		0.33	,	0.40		0.40	٧
V _{IL}		-0.3	0.8	-0.3	0.8	-0.3	0.8	V
VIH		2.0	V _{CC} + 0.3	2.0	V _{CC} + 0.3	2.0	V _∞ + 0.3	٧
Input Transition TI	me t _R , t _F 2		500		500		500	ns
C _{IO} I/O Capacitar	1Ce ^{2, 3}		10		10		10	pF
Standby Current,	lcc⁴		10		20		25	mA
Leakage Current ⁵		-10	10	-10	10	-10	10	μA
los Output Short . Circuit Current ⁶	(Vo = Voc)	20	140	20	140	20	140	mA
	(Vo = GND)	-10	-100	-10	-100	-10	-100	mA

- 1. Only one output tested at a time. $V_{CC} = min$.
- 2. Not tested, for information only.
- 3. Includes worst-case 84-pin PLCC package capacitance. $V_{OUT}=0$ V, f=1 MHz. 4. Typical standby current = 3 mA. All outputs unloaded. All inputs = V_{CC} or GND.
- 5. V_0 , $V_{IN} = V_{CC}$ or GND.
- 6. Only one output tested at a time. Min. at $V_{CC} = 4.5 \text{ V}$; Max. at $V_{CC} = 5.5 \text{ V}$.

Package Thermal Characteristics

The device junction to case thermal characteristic is θ jc, and the junction to ambient air characteristic is θ ja. The thermal characteristics for θ ja are shown with two different air flow rates.

Maximum junction temperature is 150°C.

A sample calculation of the maximum power dissipation for an 84-pin plastic leaded chip carrier at commercial temperature is as follows:

T-46-19-11

$$\frac{\text{Max. junction temp. (°C) - Max. commercial temp. (°C)}}{\theta \text{ia (°C/W)}} = \frac{150 \text{°C} - 70 \text{°C}}{44 \text{°C/W}} = 1.82 \text{ W}$$

Package Type	Pin Count	θjc	θja Still air	θja 300 ft/min.	Units
Plastic J-leaded Chip Carrier	44 68 84	15 13 12	52 45 44	40 35 33	.c/M .c/M .c/M
Plastic Quad Flatpack	100	13	55	47	°C/W
Ceramic Pin Grid Array	84	8	33	20	°C/W
Ceramic Quad Flatpack	84	5	40	30	°C/W
J-leaded Cerquad Chip Carrier	44 68 84	8 8 8	38 35 34	30 25 24	°C/W °C/W °C/W

Power Dissipation

The following formula is used to calculate total device dissipation. Total Device Power $(mW) = (0.20 \times N \times F1) + (0.085 \times M \times F2) + (0.80 \times P \times F3)$

Where:

F1 = Average logic module switching rate in MHz

F2 = CLKBUF macro switching rate in MHz

F3 = Average I/O module switching rate in MHz

M = Number of logic modules connected to the CLKBUF

N = Total number of logic modules used in the design (including M)

P = Number of outputs loaded with 50 pF

Average switching rate of logic modules and of I/O modules is some fraction of the device operating frequency (usually CLKBUF). Logic modules and I/O modules switch states (from low-to-high or from high-to-low) only if the input data changes when the module is enabled. A conservative estimate for average logic module and I/O module switching rates (variables F1 and F3, respectively) is 10% of device clock driver frequency.

If the CLKBUF macro is not used in the design, eliminate the second term (including F2 and M variables) from the formula.

Sample A1020 Device Power Calculation

To illustrate the power calculation, consider a large design operating at high frequency. This sample design utilizes 85% of available logic modules on the A1020-series device (.85 x 547 = 465 logic modules used). The design contains 104 flip-flops (208 logic modules). Operating frequency of the design is 16 MHz. In this design, the CLKBUF macro drives the clock network. Logic modules and I/O modules are switching states at approximately 10% of the clock frequency rate (.10 x 16 MHz = 1.6 MHz). Sixteen outputs are loaded with 50 pF.

To summarize the design described above: N=464; M=208; F2=16; F1=4; F3=4; P=16. Total device power can be calculated by substituting these values for variables in the device dissipation formula.

Total device power for this example =

 $(0.20 \times 465 \times 1.6) + (0.085 \times 208 \times 16) + (0.80 \times 16 \times 1.6) = 452 \text{ mW}$



T-46-19-11

Functional Timing Tests


AC timing for logic module internal delays is determined after place and route. The ALS Timer utility displays actual timing parameters for circuit delays. ACT 1 devices are AC tested to a "binning" circuit specification.


The circuit consists of one input buffer + n logic modules + one output buffer (n=16 for A1010A; n=28 for A1020A). The logic

modules are distributed along two sides of the device, as inverting or non-inverting buffers. The modules are connected through programmed antifuses with typical capacitive loading.

Propagation delay $[t_{PD} = (t_{PLH} + t_{PHL})/2]$ is tested to the following AC test specifications.

Output Buffer Performance Derating





Military, worst-case values at 125°C, 4.5 V. Commercial, worst-case values at 70°C, 4.75 V.

Note:

The above curves are based on characterizations of sample devices and are not completely tested on all devices.

Timing Derating

Operating temperature, operating voltage, and device processing conditions, along with device die size and speed grade, account for variations in array timing characteristics. These variations are summarized into a derating factor for ACT 1 array typical timing specifications. The derating factors shown in the table below are

T-46-19-11


based on the recommended operating conditions for ACT 1 commercial, industrial, and military applications. The derating curves show worst-to-best case operating voltage range and best-to-worst case operating temperature range.


Timing Derating Factor (x typical)

	Commercial		Indu	strial	Military	
Device	Best-Case	Worst-Case	Best-Case	Worst-Case	Best-Case	Worst-Case
A1010A, A1020A Standard Speed -1 Speed Grade -2 Speed Grade	0.45 0.45 0.45	1.54 1.28 1.13	0.40 0.40 0.40	1.65 1.37 1.20	0.37 0.37 0.37	1.79 1.49 1.32


Note:

"Best-case" reflects maximum operating voltage, minimum operating temperature, and best-case processing. "Worst-case" reflects minimum operating voltage, maximum operating temperature, and worst-case processing. Best-case derating is based on sample data only and is not guaranteed.







Output Buffer Delays






T-46-19-11







Timing Characteristics

Timing is design-dependent; actual delay values are determined after place and route of the design using the ALS Timer utility. The following delay values use statistical estimates for wiring delays based on 85% to 90% module utilization. Device utilization above 95% will result in performance degradation.

With ALS place and route programs, the user can assign criticality level to a net, based on timing requirements. Delays for both typical

T-46-19-11

and critical (speed-sensitive) nets are given below. Most nets will fall into the "typical" category.

Less than 1% of all routing in a design requires the use of "long tracks." Long tracks, long vertical or horizontal routing paths, are used by the autorouter only as needed. Delays due to the use of long tracks range from 15 ns to 35 ns. Long tracks may be used to route the least critical nets in a given design.

Logic Module Timing

 V_{CC} = 5.0 V; T_{J} = 25°C; Process = Typical; t_{PD} = 3.0 ns @ FO = 0

Single Logic Module Macros (e.g., most gates, latches, multiplexors)¹

		,					
Parameter	Output Net	FO = 1	FO = 2	FO = 3	FO = 4	FO = 8	Units
t _{PD}	Critical	5.4	5.8	6.2	8.5	Note 2	ns
t _{PD}	Typical	6.3	6.7	7.7	8.6	10.8	ns

Dual Logic Module Macros (e.g., adders, wide input gates)¹

		,					
Parameter	Output Net	FO = 1	FO = 2	FO = 3	FO = 4	FO = 8	Units
t _{PO}	Critical	9.2	9.6	10.0	12.3	Note 2	ns
t _{PD}	Typical	10.2	10.6	11.6	12.5	14.6	ns

Sequential Element Timing Characteristics

		Fan-Out						
	Parameter	FO = 1	FO = 2	FO = 3	FO = 4	FO = 8	Units	
tsu	Set Up Time, Data Latches	3.5	3.9	4.2	4.5	4.8	ns	
t _{S∪}	Set Up Time, Flip-Flops	3.9	3.9	3.9	3.9	3.9	ns	
t _H	Hold Time	0	0	0	0	0 -	ns	
tw	Pulse Width, Minimum ³	7.7	8.5	9.2	10.0	14.0	ns	
too	Delay, Critical Net	5.4	5.8	6.2	8.5	Note 2	ns	
tco	Delay, Typical Net	6.3	6.7	7.7	8.6	10.8	ns	

Notes:

- 1. Most flip-flops exhibit single module delays.
- 2. Critical nets have a maximum fan-out of six.
- 3. Minimum pulse width, tw, applies to CLK, PRE, and CLR inputs.



I/O Buffer Timing

 $V_{CC} = 5.0 \text{ V; } T_J = 25^{\circ}\text{C; Process} = \text{Typical}$

T-46-19-11

INBUF Macros

Parameter	From - To	FO = 1	FO = 2	FO = 3	FO = 4	FO = 8	Units
t _{PHL}	Pad to Y	6.9	7.6	8.9	10.7	14.3	ns
Т РИН	Pad to Y	5.9	6.5	7.7	8.4	12.4	ns

CLKBUF (High Fan-Out Clock Buffer) Macros

Parameter	FO = 40	FO = 160	FO = 320	Units
t _{PHL}	9.0	12.0	15.0	ns
t _{РСН}	9.0	12.0	15.0	ns

Notes:

OUTBUF, TRIBUFF, and BIBUF Macros¹

C_L = 50 pF

Parameter	From - To	CMOS	TTL	Unite
t _{PHL}	D to Pad	3.9	4.9	ns
фин	D to Pad	7.2	5.7	ns
t _{PHZ}	E to Pad	5.2	3.4	ns
tеzн	E to Pad	6.5	4.9	ns
tplz	E to Pad	6.9	5.2	ns
t _{PZL}	E to Pad	4.9	5.9	: ns

Change in Propagation Delay with Load Capacitance²

Parameter	From - To	CMOS	TTL	Units
t _{PHL}	D to Pad	0.03	0.046	ns/pF
t _{PUH}	D to Pad	0.07	0.039	ns/pF
t _{ritiz}	E to Pad	0.08	0.046	ns/pF
t _{PZH}	E to Pad	0.07	0.039	ns/pF
t _{PLZ}	E to Pad	0.07	0.039	ns/pF
t _{PZL}	E to Pad	0.03	0.039	ns/pF

Notes:

Load capacitance delay delta can be extrapolated down to 15 pF minimum.

Example:

Delay for OUTBUF driving a 100-pF TTL load:

 $t_{PHL} = 4.9 + (.046 \times (100-50)) = 4.9 + 2.3 = 7.2 \text{ ns}$

 $t_{PLH} = 5.7 + (.039 \times (100-50)) = 5.7 + 2.0 = 7.7 \text{ ns}$

^{1.} A clock balancing feature is provided to minimize clock skew.

There is no limit to the number of loads that may be connected to the CLKBUF macro.

The BIBUF macro input section exhibits the same delays as the INBUF macro.

T-46-19-11

oft Macro Li	brary Overview	[-46-19-11
Macro Name	Modules Required	Description	Levels of Logic
Counters			
CNT4A	17	4-bit loadable binary counter with clear	4
CNT4B	15	4-bit loadable bin counter w/ clr, active low carry in & carry out	4
UDCNT4A	24	4-bit up/down entr w/ sync active low load, carry in & carry out	6
Decoders			
DEC2X4	4	2 to 4 decoder	1
DEC2X4A	4	2 to 4 decoder with active low outputs	1
DEC3X8	8	3 to 8 decoder	1
DEC3X8A	8	3 to 8 decoder with active low outputs	1
DEC4X16A	20	4 to 16 decoder with active low outputs	2
DECE2X4	4	2 to 4 decoder with enable	1
DECE2X4A	4	2 to 4 decoder with enable and active low outputs	1
DECE3X8	11	3 to 8 decoder with enable	2
DECE3X8A	11	3 to 8 decoder with enable and active low outputs	2
Latches and R	egisters		
DLC8A	8	Octal latch with clear	1
DLE8	8	Octal latch with enable	1
DLM8	8	Octal latch with mulitplexed inputs	1
REGE8A	20	Octal register with preset and clear, active high enable	2
REGE8B	20	Octal register with active low clock, preset and clear, active high enable	2
Adders			
FA1	3	One bit full adder	3
FADD8	37	8-bit fast adder	4
FADD12	62	12-bit fast adder	5
FADD16	78	16-bit fast adder	5
FADD24	120	24-bit fast adder	6
FADD32	160	32-bit fast adder	7
Comparators			
ICMP4	5	4-bit identity comparator	2
ICMP8	9	8-bit identity comparator	3
MCMP16	93	16-bit magnitude comparator	5
MCMPC2	9	2-bit magnitude comparator with enables	3
MCMPC4	18	4-bit magnitude comparator with enables	4
MCMPC8	36	8-bit magnitude comparator with enables	6
Multiplexors			
мхв	3	8 to 1 multiplexor	2
MX8A	3	8 to 1 multiplexor with an active low output	2
MX16	5	16 to 1 multiplexor	2
Multipliers			
SMULT8	235	8 x 8 two's complement multiplier	Varies



Soft Macro Library Overview (continued)

T-46-19-11

Macro Name	Modules Required	Description	Levels of Logic
Shift Registers)		
SREG4A	8	4-bit shift register with clear	2
SREG8A	18	8-bit shift register with clear	2
TTL Replacem	ents	;	
TA138	12	3 to 8 decoder with 3 enables and active low outputs	2
TA139	4	2 to 4 decoder with an enable and active low outputs	1
TA151	5	8 to 1 multiplexor with enable, true, and complementary outputs	3
TA153	2	4 to 1 multiplexor with active low enable	2
TA157	1	2 to 1 multiplexor with enable	1
TA161	22	4-bit sync counter w/ load, clear, count enables & ripple carry out	3
TA164	18	8-bit serial in, parallel out shift register	1
TA169	25	4-bit synchronous up / down counter	6
TA181	31	4-bit ALU	4
TA194	14	4-bit shift register	1
TA195	10	4-bit shift register	1
TA269	50	8-bit up/down cntr w/ clear, load, ripple carry output & enables	8
TA273	18	Octal register with clear	1
TA280	9	Parity generator and checker	4
TA377	16	Octal register with active low enable	1
Super Macros			
MC	102	DRAM Controller	Varies
DMA	225	Direct Memory Access Controller	Varies
SINT	180	SCSI Interface Controller	Varies

Hard Macro Library Overview

The following illustrations show all the available Hard Macros.


T-46-19-11

2-Input Gates (Module Count = 1)

3-Input Gates (Module Count = 1, unless indicated otherwise)

② Indicates 2-module macro

▲ Indicates extra delay input









T-46-19-11


4-Input Gates (Module Count = 1, unless indicated otherwise)

2 Indicates 2-module macro ▲ Indicates extra delay input







AND-XOR Gates (Module Count = 1)




T-46-19-11


2 Indicates 2-module macro







AND-OR Gates (Module Count = 1)
















































OR-AND Gates (Module Count = 1)


T-46-19-11


② Indicates 2-module macro


A Indicates extra delay input



















Buffers (Module Count = 1)













I/O Buffers (I/O Module Count = 1)




Multiplexors (Module Count = 1)






Latches (Module Count = 1)


T-46-19-11




D-Latches with Clear (Module Count = 1)




D-Latches with Enable (Module Count = 1)



Mux Latches (Module Count = 1)



Adders (Module Count = 2)




Macros FA1A, FA1B, and FA2A have two level delays from the inputs to the S outputs, as indicated by the▲

D-Type Flip-Flops (Module Count = 2)


T-46-19-11

D-Type Flip-Flops with Clear

D-Type Filp-Flops with Preset




D-Type Flip-Flops with Preset and Clear







D-Type Filip-Flops with Enable (Module Count = 2)




JK Flip-Flops (Module Count = 2)



Mux Flip-Flops (Module Count = 2)





CLKBUF Interface Macros (Module Count = 1)




Package Pin Assignments (Top View)

T-46-19-11








Notes:

- 1. VPP must be terminated to VCC, except during device programming.
- MODE must be terminated to circuit ground, except during device programming or debugging.
- 3. Unused I/O pins are designated as outputs by ALS and are driven low.
- 4. All unassigned pins are available for use as I/Os.



Package Pin Assignments (continued) (Top View)

T-46-19-11





Notes:

- 1. V_{PP} must be terminated to V_{CC} , except during device programming.
- MODE must be terminated to circuit ground, except during device programming or debugging.
- 3. Unused I/O pins are designated as outputs by ALS and are driven low.
- 4. All unassigned pins are available for use as I/Os.

Package Pin Assignments (continued)

T-46-19-11






Notes

- 1. V_{PP} must be terminated to V_{CC} , except during device programming.
- MODE must be terminated to circuit ground, except during device programming or debugging.
- 3. Unused I/O pins are designated as outputs by ALS and are driven low.
- 4. All unassigned pins are available for use as I/Os.

Package Pin Assignments (continued)

T-46-19-11



Signal	A1010-Series Devices	A1020-Series Devices
PRA	A11	A11
PRE	B10,	B10
MODE	E11	E11
SDI	B11	B11
DCLK	C10	C10
V _{PP}	К2	К2
CLK or I/O	F9	F9
GND	B7, E2, E3, K5, F10, G10	B7, E2, E3, K5, F10, G10

B1, B2, C1, C2, K1, J2, L1, J10, K10, K11, C11, D10, D11

B5, F1, G2, K7, E9, E10

Notes:

Vcc

N/C (No Connection)

- 1. V_{PP} must be terminated to V_{CC}, except during device programming.
- MODE must be terminated to circuit ground, except during device programming or debugging.
- 3. Unused I/O pins are designated as outputs by ALS and are driven low.


B2

B5, F1, G2, K7, E9, E10

4. All unassigned pins are available for use as I/Os.

Package Pin Assignments (continued)

T-46-19-11



Notes:


- 1. VPP must be terminated to VCC, except during device programming.
- MODE must be terminated to circuit ground, except during device programming or debugging.
- 3. Unused I/O pins are designated as outputs by ALS and are driven low.
- 4. All unassigned pins are available for use as I/Os.





Package Mechanical Details (continued)

Plastic Quad Flatpack

T-46-19-11








1,150" ± .008"


Package Mechanical Details J-Leaded Cerquad Chip Carrier

T-46-19-11



1.190" ± .005"

Plastic J-Leaded Chip Carrier




84

Lead Count	D, E	D1, E1
44	.690" ± .005"	.655" ± .005"
68	.990" ± .005"	.955" ± .005"
84	1.190" ± .005"	1.155" ± .005"




Package Mechanical Details (continued) Ceramic Pin Grid Array

T-46-19-11



Package Mechanical Details (continued) Ceramic Quad Flatpack

T-46-19-11



Lead Count	D, E	D1, E1
84	1.350" ± .030"	0.650" ± .010"