## **Description**

The 3120-N...-...T1-... thermal circuit breaker/switch combination unites overcurrent protection and the function of an ON/OFF switch within a single component. The trip element is a thermobimetal. Type 3120-N...-...T1-... is ideally suited for overload protection of motors, pumps, transformers and cables. After tripping, it can reliably, easily and quickly be reset. The positively trip-free mechanism ensures reliable disconnection of the circuit even with the actuator blocked.

The 3120-N type is also available with thermal-magnetic trip. (technical data p. 21 ff.)

Type 3120-N is also available as a switch in accordance EN IEC 61058 (see data sheet switch 3120-N...Q1).



## **Typical applications**

Medical and laboratory equipment, apparatus and machine construction, professional tools, household and garden appliances, offices machines, audio equipment, machine tools

## **Features**

- Single or double pole thermal circuit breaker/switch combination
- Voltage ratings: AC 240 V, DC 50 V (AC 415 V upon request)
- Current rating range: 0.1 ... 20 A (up to 30 A upon request)
- Optional: push-in terminals for easy and quick wiring with a longterm stability
- Expandable functionality through appliance inlet module
- Functional extension options with add-on modules for low voltage release, auxiliary contact function, remote trip or fast magnetic trip
- Suitable for use in medical equipment according to IEC/EN 60601

## **Approval logos**











## **Conformity**



## Your benefits

- Maximum equipment availability is ensured by overload protection perfectly matched with the loads (prevention of nuisance tripping) and quick resettability
- · Reduced mounting and wiring time
- Space saving design
- Reduced disposition and storage costs
- Increased overall reliability

## **Further information**

The current data sheet as well as other relevant documents are available on our website: www.e-t-a.de/e016

## **Technical data**

For detailed technical information please see www.e-t-a.de/ti_			
Rated voltage	AC 240 V, DC 50 V (AC 415 V upon request)		
Current rating range	0.1 20 A (up to 30A upon request for 1-pole devices only)		

## Typical life 1-pole (EN 60934)

AC 240 V:	0.1 20 A	30,000 cycles at 1 x I <sub>N</sub> , inductive
DC 50 V:	0.1 4 A	30,000 cycles at 1 x I <sub>N</sub> , inductive
	4.5 16 A	30,000 cycles at 1 x I <sub>N</sub> , resistive
DC 28 V:	0.1 20 A	30,000 cycles at 1 x I <sub>N</sub> , inductive

## Typical life 2-pole (EN 60934)

AC 240 V:	0.1 16 A	50,000 cycles at 1 x I <sub>N</sub> , inductive		
	17 20 A	30,000 cycles at 1 x I <sub>N</sub> , inductive		
DC 50 V:	0.1 16 A	50,000 cycles at 1 x I <sub>N</sub> , inductive		
	17 20 A	10,000 cycles at 1 x I <sub>N</sub> , inductive		
A 1: 11 00 00 00				

Ambient	temperatu	ıre	-30	•••	60	°C

Insulation coordination (IEC 60664) 2.5 kV /2 reinforced insulation at operating area

### Dielectric strength

Operating area pole to pole (2-pole) Test voltage AC 3,000 V Test voltage AC 1,500 V Insulation resistance  $> 100 \text{ M}\Omega$  (DC 500 V)

## Rupture capacity I<sub>cn</sub> (IEC/EN 60934)

	I <sub>N</sub>	$U_N$	I <sub>cn</sub>		
1-pole, 2-pole	0.1 2 A	AC 240 V / DC 50 V	10 x I <sub>N</sub>		
1-pole	2.5 10 A	DC 50 V	50 A		
1-pole	2.5 20 A	AC 240 V / DC 28 V	200 A		
2-pole	2.5 20 A	DC 50 V	250 A		
2-pole	2.5 20 A	AC 240 V / DC 28 V	300 A		
Later and the control of the desired					

## Interrupting capacity $I_{\rm nc}$ (UL 1077)

	I <sub>N</sub>	$U_N$	I <sub>nc</sub>
1-pole, 2-pole	0.1 20 A	AC 250 V	5,000 A, C, 1
1-pole, 2-pole	0.1 20 A	DC 50 V	1,000 A, C, 1

## Degree of protection (IEC 60529)

Operating area IP40 Terminal area IP00

Other degrees of protection possible, depending on selected variant, see further details in data sheet.

Vibration	8 g (57-500 Hz), ± 0.61 mm (10-57 Hz) Test to IEC 60068-2-6, Test Fc 10 frequency cycles/axis
Shock	30 g (11 ms) Test to IEC 60068-2-27, Test Ea
Corrosion	96 hours at 5 % salt mist, Test to IEC 60068-2-11, Test Ka
Humidity	240 hours in 95 % RH Test to IEC 60068-2-78, Test Cab
Mass	approx. 27 g (1-pole) approx. 31 g (2-pole) approx. 42 g (2-pole with PT terminals)

## **Current ratings and internal resistance values**

Current rating (A)	Internal resistance per pole (Ω)	Current rating (A)	Internal resistance per pole (Ω)
0.1	94	4	0.0435
0.2	24	4.5	0.0435
0.3	12	5	0.0325
0.4	5.30	6	0.0215
0.5	4.20	7	0.0165
0.6	2.90	8	0.0165
0.8	1.50	10	< 0.02
1	0.9	12	< 0.02
1.2	0.80	14	< 0.02
1.5	0.45	15	< 0.02
2	0.27	16	< 0.02
2.5	0.0785	18	< 0.02
3	0.0595	20	< 0.02
3.5	0.0565		



## **Ordering information**

Type no
Type no. 3120 Thermal rocker-actuated circuit breaker/switch combination
Mounting method
N3 Snap-in, mounting cut-out 50.5 x 21.5 mm
N5 Snap-in, mounting cut-out 44.5 x 22 mm
Number of poles
1 1-pole switching, 1-pole thermally protected
2 2-pole switching, 2-pole thermally protected
5 2-pole switching, 1-pole thermally protected
Style
1 Standard 3 With actuator guard
4 With accordion-style seal, IP65
6 Version with shorter flange
(only for mounting method N5)
7 With water splash cover (IP54 in the actuation
area) and shorter flange
A With actuator guard and cross-hole (for optional
interlock)
Terminal design
PT Push-in terminals
P7 Blade terminals
H7As P7, terminals 11 and 21 with flat head screws M3.5 - standard for devices with
undervoltage release module
N7 As P7, with additional shunt terminals 12(i)
and 22(i)
G7As N7, terminals 11 and 21 with additional flat
head screws M3.5
Trip curve
T1 Thermal trip
Actuator
WRocker
Rocker colour and illumination
Opaque 01. Black without illumination
02. White without illumination
04 . Red without illumination
Translucent (when named with Y/R/T/G
the rocker is illuminated)
12 . (Y) White without illumination
(illuminated)
14 . (R) Red without illumination
(illuminated)
15. (Y) Orange without illumination
(illuminated)
16 . (T) Blue without illumination
(illuminated)  19 . (G) Green without illumination
(illuminated)
Marking of rocker
A (not for style 4)
D C C C C C C C C C C C C C C C C C C C
F FINE PARTY
K O OFF O OF
X A D F K L X
2400 NF 0 4 PT T4 W 40 P C
3120-N5 2 4 - PT T1-W 19 D G Ordering example

3120-N5 2 4 - PT T1-W 19 D G ... Ordering example Illumination voltage (= operating voltage) 1 DC 12 V 2 DC 24 V 3 AC 115 V 4 AC 230 V 5 DC 48 V 6 AC 400 V (for 2-pole versions up to 16 A) **Current rating** 0.1 ... 20 A **Terminal shroud** (optional) A With terminal shroud, mounted\* 3120-N5 2 4 - PT T1-W 19 D G 4-16 A - (A) Ordering - example

\* Optional. If -A is added to the order designation, the 3120 is supplied with the mounted terminal shroud. Only available in combination with -P7 or -N7 terminal design variants.



## **Ordering information**

### Type no.

3120 Thermal circuit breaker/switch combination with push button actuation

## **Mounting method**

- N3 Snap-in, mounting cut-out 50.5 x 21.5 mm
- N5 Snap-in, mounting cut-out 44.5 x 22 mm

## Number of poles

- 1 1-pole switching, 1-pole thermally protected
- 2 2-pole switching, 2-pole thermally protected
- 5 2-pole switching, 1-pole thermally protected Style
  - With actuator guard
  - E With actuator guard and water splash cover IP54
  - F With power-on protection
  - With power-on protection and water splash cover IP54

### Terminal design

- PT Push-in terminals
- P7 Blade terminals
- H7As P7, terminals 11 and 21 with flat head screws M3.5 - standard for units with undervoltage release module
- N7As P7, with additional shunt terminals 12(i) and 22(i)
- G7As N7, terminals 11 and 21 with additional flat head screws M3.5

### Trip curve

T1 Thermal trip

## **Actuator**

S Two push buttons

Colour of push button/illumination (Style D and F without water splash protection)

GRD Green/red without illumination
GRDG Green with LED illumination/red
without illumination

Colour of push button/illumination (Style E and V with water splash protection)

GRX Green/red without illumination
GRXG Green with LED illumination/red
without illumination

Illumination voltage range

## (= operating voltage)

- 1 DC 12 V
- 2 DC 24 V
- 3 AC 115 V
- 4 AC 230 V
- 5 DC 48 V
- 6 AC 400 V (for 2-pole versions up

## to 16 A)

Current rating 0.1 ... 20 A

Terminal shroud

(optional)

A With terminal shroud, mounted\*

3120-N3 5 V - PT T1-S GRD - 20 A - (A) Ordering - example



## **Ordering information**

### Type no.

3120 Thermal resettable circuit breaker with push button

### Mounting method

- N3 Snap-in, mounting cut-out 50.5 x 21.5 mm
- N5 Snap-in, mounting cut-out 44.5 x 22 mm

### Number of poles

- 1 1-pole thermally protected
- 2 2-pole thermally protected
- 5 2-pole, 1-pole thermally protected

### Style

G Resettable circuit breaker

## Terminal design

PT Push-in terminals

P7 Blade terminals

H7As P7, terminals 11 and 21 with flat head screws M3.5 - standard for units with undervoltage release module

N7 As P7, with additional shunt terminals 12(i) and 22(i)

G7As N7, terminals 11 and 21 with additional flat head screws M3.5

## Trip curve

T1 Thermal trip

### Actuator

D One push button

Colour of push button

01 Black

02 White opaque

04 Red opaque (UL/CSA approval only)

09 Green opaque

Marking of the push button

X Without marking Current rating

0.1 20 A

0.1 ... 20 A

Terminal shroud (optional)

A With terminal shroud, mounted\*

3120-N3 2 G - PT T1 - D 01 - X 20 A - (A) Ordering - example

Please observe our minimum ordering quantities.

\* Optional. If -A is added to the order designation, the 3120 is supplied with the mounted terminal shroud. Only available in combination with -P7 or -N7 terminal design variants.

## **Customer-specific solutions**


Looking for a version you cannot find in our order numbering code? Please get in touch.

## **Approvals**


Approval authority	Standard	Rated voltage	Current rating range	Appr marks
VDE	IEC/EN 60934	AC 240 V DC 50 V DC 50 V DC 28 V	0.1 A 20 A 0.1 20 A (2-pole) 0.1 16 A (1-pole) 0.1 A 20 A	
UL	UL 1077	AC 250 V AC 250 V DC 50 V AC 250 V	0.1 A 16 A (TC1, OL1) 17 A 20 A (TC1, OL0) 0.1 A 20 A(TC1, OL0) 30 A* (TC1, OL0)	<b>91</b> °
CSA	C22.2 No 235	AC 250 V AC 250 V DC 50 V AC 250 V	0.1 A 16 A (TC1, OL1) 17 A 20 A (TC1, OL0) 0.1 A 20 A(TC1, OL0) 30 A* (TC1, OL0)	<b>⊕</b> ¾
CQC	GB 17701	AC 240 V DC 50 V	0.1 A 20 A 0.1 A 20 A	<b>(W</b> )
KTL	KC60934	AC 240 V	0.1 20 A (2-pole)	

<sup>\* 2</sup> poles in parallel


## **Mounting method**



## **Schematic diagrams**



## **Time/current characteristics**




The time/current characteristic depends on the ambient temperature. In order to eliminate nuisance or late tripping, please multiply the current rating of the circuit breaker by a temperature factor (see chapter Technical Information) For detailed technical information please see www.e-t-a.de/ti\_e

Ambient temperature [°C]	-30	-20	-10	0	23	40	50	60
Temperature factor	0.8	0.84	0.88	0.92	1	1.08	1.14	1.23

1


## 

## **Dimensions**





## া ভানি বিশ্ব 3120-N...-...T1-... Thermal Circuit Breaker


## **Dimensions**




## **Dimensions**











## 3120-N5.V-P7...




## **Dimensions**




## **Cable cross sections PT terminals**

Cable	Cross section with direct push-in wiring
rigid	14 mm <sup>2</sup> (stripping length: 10 mm)
flexible with wire end ferrule (with or without plastic sleeve)	0.52.5 mm <sup>2</sup> , length of metal sleeve 8 - 12 mm
Cable	Cross section when opening the push-in terminals
rigid	0.54 mm <sup>2</sup> (stripping length: 10 mm)
flexible without wire end ferrule	0.52.5 mm <sup>2</sup>
flexible with wire end ferrule (with or without plastic sleeve)	0.52.5 mm <sup>2</sup> , length of metal sleeve 8 - 12 mm


## **Installation drawing**



## **Terminal types**



## **Terminal shroud**





Optionally available in combination with -P7 or -N7 terminal design variants. For details, see ordering information.

## **Accessories**


# Terminal adapter order no. Y 303 862 01

## Cover for -N3 mounting cut-out order no. Y 303 885 31






## Cover for terminal area (IP20) order no. Y 304 275 01




## **Accessories**



- \* Y 303 675 01 can only be used for mounting panel thickness < 2 mm
- \* Y 303 675 02 can only be used for mounting panel thickness < 4 mm

The snap-in frame is used in special cases to ensure a tight fit of the circuit breaker in the mounting cut-out, e.g. in case of dimensional tolerances, soft materials or if the specified edge condition cannot be maintained.

### Snap-in frame mounting



All information and data given on our products are accurate and reliable to the best of our knowledge, but E-T-A does not accept any responsibility for the use in applications which are not in accordance with the present specification. E-T-A reserves the right to change specifications at any time in the interest of improved design and performance. Dimensions are subject to change without notice. Please enquire for the latest dimensional drawing with tolerances if required. All dimensions, data, pictures and descriptions are for information only and are not binding. Amendments, errors and omissions excepted. Part numbers of the devices may differ from their marking.


## © টিনিঐ 3120-N...-...T1-... Thermal Circuit Breaker


## **Accessories**


### **Connection adapter**


### Order number Y 31214001


For pre-assembly of the connection cables. Two snap-in hooks ensure a firm plug-in connection.











### Benefits:

- Time and cost savings during final assembly
- · Quick replacement of devices
- Cover for the blade terminals (IP20)

## Note:


Supplied without female contacts.


The chamber dimensions for the female contacts (plug width 6.3 mm) are in accordance with DIN 46340 Part 3. Form A.


Examples of suitable receptacles: Stocko RSB 7916 F6.3-1. Klauke type 2730. Vogt type 3832d.67.

TE FASTON Terminals 250 Series. Delphi Packard 58 Series;

Connection adapter plugged onto circuit breaker:







## Description - appliance inlet module X3120 A/B

The X3120 appliance inlet module with 3120- N5 circuit breaker combines up to four functions within a single component: A C14/C20 appliance inlet, an ON/ OFF switch, resettable overcurrent protection and a line filter. Screw-type mounting from the front or from the rear.

## **Typical applications**

Electrical medical apparatus, laboratory equipment, professional audio equipment and office machines.

## **Approvals**

X3120-A - C14 inlet plugs				
Approval authority	Standard	Rated voltage	Max. current rating	
ENEC	IEC/EN 60320-1	AC 240 V	10 A	
UL/CSA <sup>1)</sup>	UL 60320-1, CSA C22.2 no. 60320-1	AC 250 V	15 A	
CQC	CCC	AC 250 V	10 A	

X3120-A0400 also available with overall approval according to UL 60320-1 at max.
 A rated current.

### X3120-A - filter

Design to UL 1283, CSA 22.2 No. 8 1986, IEC/EN 60939

X3120-B - C20 inlet plugs				
Approval authority	Standard	Rated voltage	Max. current rating	
ENEC	IEC/EN 60320-1	AC 240 V	16 A	
UL/CSA <sup>2)</sup>	UL 60320-1, CSA C22.2 no. 60320-1	AC 240 V	20 A	

<sup>2)</sup> X3120-B0400 also available with overall approval according to UL 60320-1 at max. 20 A rated current.

Please note: the current rating of the circuit breaker must not exceed the max. current of the filter/inlet plug, depending on the approval.

## Selection of filter rating

Current rating of circuit breaker	Min. rating of filter
0.1 1 A	1 A
1.2 3 A	3 A
3.5 6 A	6 A
7 8 A	8 A
9 10 A	10 A
12 A	12 A
14 15 A	15 A

The current rating of the circuit breaker must not be higher than the filter current rating. For best attenuation a filter with the smallest possible current rating should be selected. Depending on the IEC/EN or UL/CSA approval, other maximum values are permissible for the inlet plug. The table above serves as orientation.

For protection of the filter in the event of higher overcurrents, we recommend 3120- N circuit breakers with thermal-magnetic trip (3120- N...-M1...).

For further technical information please refer to page 21.



## **Ordering information**

### Type no.

X3120 Appliance inlet module for circuit breaker type 3120- N

Module

A C14 appliance inlet (can be combined with 3120-N5.6/-N5.7/-N5.G)

B C20 appliance inlet

(without filter, can be combined with 3120-N5.6/-N5.G)

### **Mounting method**

04 Screw-type mounting

Filters

00 Without filter

01 Standard line filter

03 Standard line filter for medical equipment

06 High-power line filter for medical equipment

Current rating for filter (only with module A)

01 1 A 03 3 A

06 6 A 08 8 A

10 10 A 12 12 A

15 15 A

Version

Not wired, mounting position 3120: OFF position at connector

Wired; mounting position 3120: OFF position at connector

Supply status

M Module supplied with mounted
 3120 circuit breaker and connector

X3120- A 04 01 08 01 M Ordering example


Note: the power entry module is only available as a ready-to-use unit including the 3120 circuit breaker, C14/C20 appliance inlet and wiring (if selected).

All information and data given on our products are accurate and reliable to the best of our knowledge, but E-T-A does not accept any responsibility for the use in applications which are not in accordance with the present specification. E-T-A reserves the right to change specifications at any time in the interest of improved design and performance. Dimensions are subject to change without notice. Please enquire for the latest dimensional drawing with tolerances if required. All dimensions, data, pictures and descriptions are for information only and are not binding. Amendments, errors and omissions excepted. Part numbers of the devices may differ from their marking.


## **Technical data**

	X3120-A0400 (without filter)	X3120-A040x	X3120-B0400
Rated voltage	AC 250 V	AC 250 V	AC 250 V
Current rating (appliance inlet)	10 A (IEC/EN) 15 A (UL/CSA)	10 A (IEC/EN) 15 A (UL/CSA)	16 A (IEC/EN) 20 A (UL/CSA)
Ratings of filter		1 A, 3 A, 6 A, 8 A, 10 A, 12 A, 15 A	
Operating temperature	-25°C +60°C	-25°C +60°C	-25°C +60°C
Number of poles	L, N + mass	L, N + mass	L, N + mass
Degree of protection	I	I	1
Mounting method	Screw-type mounting (from the front or from the rear)	Screw-type mounting (from the front or from the rear)	Screw-type mounting (from the front or from the rear)
Terminals	DIN46244 blade terminal 6.3 mm x 0.8 mm	DIN46244 blade terminal 6.3 mm x 0.8 mm	DIN46244 blade terminal 6.3 mm x 0.8 mm
Housing material	Thermoplastics, black, UL94V-0	Thermoplastics, black, UL94V-0	Thermoplastics, black, UL94V-0
Appliance inlet:	C14 to IEC/EN 60320-1, UL 60320-1, CSA C22.2 no. 60320 - 1	C14 with line filter to IEC/EN 60939, UL 1283, CSA 22.2 no. 8	C20 to IEC/EN 60320-1, UL 60320-1, CSA C22.2 no. 60320-1
Main switch	circuit breaker for equipment protection 3120-N5.6 3120-N5.7 3120-N5.G	circuit breaker for equipment protection 3120-N5.6 3120-N5.7 3120-N5.G	circuit breaker for equipment protection 3120-N5.6 3120-N5.G


## X3120-A0400 dimensional drawing (in fig. with 3120-N5.6)




## X3120-A040x dimensional drawing (in fig. with 3120-N5.6)



## X3120-B0400 dimensional drawing (in fig. with 3120-N5.6)



## **Mounting cut-out**




## Schematic diagram X3120-A

## X3120-A0401 Standard filter 2xL 2xCy N' 11 ⊸ PE 3120 -o 22 (K) P' 21 load line X3120-A0403 and X3120-A0406 Line filter for medical equipment -0 12 (K) $\bigcirc$ **⊢**○PE 3120 -o 22 (K)

## X3120-A0401 and X3120-A0403 - standard filters

Typical filter attenuation: to CISPR 17 A = 50  $\Omega$  / 50  $\Omega$  sym; B = 50  $\Omega$  / 50  $\Omega$  asym; C = 0.1  $\Omega$  / 100  $\Omega$  sym; D = 100  $\Omega$  / 0.1  $\Omega$  sym 1 and 3 A models 6 - 10 A models 12 and 15 A models 70 70 70 60 60 60 50 50 50 40 40 40 30 30 30 20 20 20 10 10 

## X3120-A0406 - high-power filters



## Filter selection table

Filters	Current rating 50 °C (25 °C)	Leakage current 250VAC/50Hz		Capacity Cx	Capacity Cy	Resistance R
	A (25°C)	μΑ	mH	μF	nF	kΩ
X3120-A040101M	1 (1.2)	373	12	0.1	2.2	
X3120-A040103M	3 (3.5)	373	2.5	0.1	2.2	
X3120-A040106M	6 (7.2)	373	0.78	0.1	2.2	
X3120-A040108M	8 (10.6)	373	0.5	0.1	2.2	
X3120-A040110M	10 (11.6)	373	0.225	0.1	2.2	
X3120-A040112M	12 (12)	373	0.11	0.1	2.2	
X3120-A040115M	15 (15)	373	0.075	0.1	2.2	
X3120-A040301M	1 (1.2)	2	12	0.1		1000
X3120-A040303M	3 (3.5)	2	2.5	0.1		1000
X3120-A040306M	6 (7.2)	2	0.78	0.1		1000
X3120-A040308M	8 (10.6)	2	0.5	0.1		1000
X3120-A040310M	10 (11.6)	2	0.225	0.1		1000
X3120-A040312M	12 (12)	2	0.11	0.1		1000
X3120-A040315M	15 (15)	2	0.075	0.1		1000
X3120-A040601M	1 (1.2)	2	59.53	0.1		1000
X3120-A040603M	3 (3.5)	2	13.45	0.1		1000
X3120-A040606M	6 (7.2)	2	4.1	0.1		1000
X3120-A040608M	8 (10.6)	2	2.3	0.1		1000
X3120-A040610M	10 (11.6)	2	1.02	0.1		1000
X3120-A040612M	12 (12)	2	0.58	0.1		1000
X3120-A040615M	15 (15)	2	0.4	0.1		1000

## Description X3120-U undervoltage release module

The undervoltage release module reliably excludes personal injury through automatic re-start after voltage dip or power failure.

**Note:** 3120- N...-H7 or -G7 basic device requires screw terminals. Not possible in combination with PT terminals.

Applies in combination with design variant 4 (accordion-style): In the event of voltage dip or power failure, the undervoltage release module switches Circuit breaker off. The rocker actuator will go into centre position. Reset is effected in two steps:

Step 1: Switch rocker into OFF position.

Step 2: Reset circuit breaker.

Not possible with style configurations D and E.

## **Typical applications**

All machines that could cause personal injury upon automatic re-start, e.g. drilling machines, electric saws, meat cutting machines etc.


The X3120-U02 version allows set up of a cost-effective safety circuit via the physically isolated undervoltage release module, which enables implementation for example of a remote disconnection with emergency stop.

## **Ordering information**


Type n		
X3120	Module for 3120-N device	
	Module	
	Undervoltage release module	
	Design	
	00 Standard (without separate connections)	
	01 1 blade terminals 2.8x0.8	
	02 2 blade terminals 2.8x0.8	
	Rated voltage	
	00 AC 230/240 V 50/60 Hz	
	01 AC 120 V 50/60 Hz	
	02 AC 100 V 50/60 Hz	
	03 DC 24 V	
	04 AC 400 V 50/60 Hz	
	Supply status	
	M Module mounted to circuit breaker 3120	
X3120-	U 00 00 M Ordering example	

All information and data given on our products are accurate and reliable to the best of our knowledge, but E-T-A does not accept any responsibility for the use in applications which her not in accordance with the present specification. E-T-A reserves the right to change specifications at any time in the interest of improved design and performance. Dimensions are subject to change without notice. Please enquire for the latest dimensional drawing with tolerances if required. All dimensions, data, pictures and descriptions are for information only and are not binding. Amendments, errors and omissions excepted. Part numbers of the devices may differ from their marking.

## Dimensions - undervoltage release module



## **Schematic diagrams**



## **Technical data**

Voltage ratings:	AC 100 V; AC 120 V; AC 230/240 V; AC 400 V (50/60 Hz) DC 24 V
Voltage tolerances	+ 10 %/- 15 %
Typical life	20,000 cycles
Current consumption	approx. 2.5 mA
Release values	$0.2 \times U_N < U < 0.7 \times U_N$ (at a rated voltage of AC 100 V the device can trip at 70 V and must trip at 20 V)
Trip time	< 20 ms
Latch-in values	≥ 85 % U <sub>N</sub>
Ambient temperature	-30 60 °C
Vibration	8 g (57-500 Hz), ± 0.61 mm (10-57 Hz) Test to IEC 60068-2-6, Test Fc 10 frequency cycles/axis
Shock	30 g (11 ms) Test to IEC 60068-2-27, Test Ea
Corrosion	48 hours at 5 % salt mist, Test to IEC 60068-2-11, Test Ka
Humidity	240 hours in 95 % RH Test to IEC 60068-2-78, Test Cab
Mass	approx. 56 g (including base device)
	-

## Description X3120-S auxiliary contact module


Add-on module for circuit breaker type 3120-F. The auxiliary contact module has a change-over contact as signal contact and is operated with actuation of the CBE.

Note: Only possible with terminal versions N7 and P7.

## **Typical applications**


Status monitoring of CBE and/or the connected loads.

## **Ordering information**




## All information and data given on our products are accurate and reliable to the best of our knowledge, but E-T-A does not accept any responsibility for the use in applications which are not in accordance with the present specification. E-T-A reserves the right to change specifications at any time in the interest of improved design and performance. Dimensions are subject to change without notice. Please enquire for the latest dimensional drawing with tolerances if required. All dimensions, data, pictures and descriptions are for information only and are not binding. Amendments, errors and omissions excepted. Part numbers of the devices may differ from their marking.

## **Dimensions – auxiliary contact module**



## **Schematic diagram**



Technical data	
Rated voltage	AC 250 V, DC 250 V
Current rating	0.14 A / 5100 mA
Typical life	50,000 cycles
Ambient temperature	-30 60 °C
Dielectric strength	
between main and auxiliary circuit	Test voltage AC 3,000 V
Insulation resistance	> 100 MΩ (DC 500 V)
Vibration	6 g (57-500 Hz), ± 0.46 mm (10-57 Hz) Test to IEC 60068-2-6, Test Fc 10 frequency cycles/axis
Shock	15 g (11 ms) Test to IEC 60068-2-27, Test Ea
Corrosion	96 hours at 5 % salt mist, Test to IEC 60068-2-11, Test Ka
Humidity	240 hours in 95 % RH Test to IEC 60068-2-78, Test Cab
Mass	approx. 41 g (including base device)

## **Description X3120-M remote trip module**

By applying voltage (pulse) to the remote trip module the 3120-N circuit breaker can be tripped electrically.

Note: Not possible in combination with PT terminals.

## **Typical applications**

Electrical remote trip of safety systems.

## **Ordering information**

## X3120 Module for 3120-N device Module M Magnetic relay trip module 2 Magnetic coil physically isolated from device Terminal design P7 Blade terminals **Supply status** M Module is only supplied mounted to base device Rated voltage AC 120, 230 V DC 12, 24 V X3120- M 2 P7 M -12 V


Ordering example

## Standard voltage ratings and typical internal resistance values


Rated voltage	Internal resistance (Ω)	Rated voltage	Internal resistance (Ω)
DC 12 V	0.78	AC 120 V	71.0
DC 24 V	3.3	AC 230 V	312

All information and data given on our products are accurate and reliable to the best of our knowledge, but E-T-A does not accept any responsibility for the use in applications which are not in accordance with the present specification. E-T-A reserves the right to change specifications at any time in the interest of improved design and performance. Dimensions are subject to change without notice. Please enquire for the latest dimensional drawing with tolerances if required. All dimensions, data, pictures and descriptions are for information only and are not binding. Amendments, errors and omissions excepted. Part numbers of the devices may differ from their marking.

## **Dimensions - remote trip module**



## **Schematic diagram**



## **Technical data**

Voltage ratings	AC 120230 V; DC 1224 V
Power consumption	approx. 200 Watt
Pulse operation	$\begin{array}{l} \textrm{20 ms} < t_{\textrm{on}} < \textrm{100 ms} \\ t_{\textrm{off}} > \textrm{10 sec} \end{array}$
Trip time	< 20 ms
Typical life	50,000 operations at U <sub>N</sub>
Ambient temperature	-30 60 °C
Dielectric strength	
between main and trip current circuit	Test voltage AC 3,000 V
Insulation resistance	> 100 MΩ (DC 500 V)
Vibration	8 g (57-500 Hz), ± 0.61 mm (10-57 Hz) Test to IEC 60068-2-6, Test Fc 10 frequency cycles/axis
Shock	30 g (11 ms) Test to IEC 60068-2-27, Test Ea
Corrosion	96 hours at 5 % salt mist, Test to IEC 60068-2-11, Test Ka
Humidity	240 hours in 95 % RH Test to IEC 60068-2-78, Test Cab
Mass	approx. 56 g (including base device)

## ❷ E 币A 3120-N...-...M1-...thermal-magnetic circuit breaker

## **Description**

The 3120- N...-...M1-... thermal-magnetic circuit breaker/switch combination unites overcurrent protection and the function of an ON/ OFF switch within a single component. The integral thermobimetal ensures ideally matched overload protection. The magnetic trip module trips the circuit breaker/switch combination at overload currents from four times rated current within milliseconds.

The 3120- N...-...M1-... meets the fire resistance requirements to EN 60335-1: 2007-02 Safety of household and similar electrical




## **Typical applications**

Electric motors, household appliances and office machines, electrical tools, power supplies, charging rectifiers

## **Current ratings and internal resistance values**


Current rating (A)	Internal resistance per pole (Ω)			
	Thermal-magnetic	Thermal		
0.1	165	94		
0.2	42.5	24		
0.3	20.2	12		
0.4	9.7	5.40		
0.5	7.17	4.30		
0.6	4.9	3		
0.8	2.65	1.50		
1	1.49	0.9		
1.2	1.25	0.7		
1.5	0.74	0.45		
2	0.49	0.29		
2.5	0.20	0.0785		
3	0.14	0.0595		
3.5	0.114	0.0565		
4	0.092	0.0435		
5	0.06	0.0325		
6	0.043	0.0215		
7	0.030	0.0215		
8	0.029	0.02		
10	0.021	0.02		
12	< 0.02	< 0.02		
14	< 0.02	< 0.02		
15	< 0.02	< 0.02		
16	< 0.02	< 0.02		

## **Dimensions - magnetic trip module**




## Schematic diagrams


- 1-pole thermal-magnetically protected
- 1-pole thermally protected




1-pole thermal-magnetically protected



- 1-pole thermal-magnetically protected
- 1-pole thermally unprotected





## © ┗Ū® 3120-N...-...M1-...thermal-magnetic circuit breaker

## **Technical data**

For detailed technical information please see www.e-t-a.de/ti_	_e
--	----

Rated voltage	AC 240 V, DC 50 V (AC 415 V upon request)	
Current rating range	0.1 16 A	

## Typical life 1-pole

AC 240 V:	0.1 16 A	30,000 cycles at 1 x I <sub>N</sub> , inductive
DC 50 V:	0.1 4 A	30,000 cycles at 1 x I <sub>N</sub> , inductive
	4.5 16 A	30,000 cycles at 1 x I <sub>N</sub> , resistive
DC 28 V:	0.1 16 A	30,000 cycles at 1 x I <sub>N</sub> , inductive

## Typical life 2-pole

Insulation resistance

AC 240 V:	0.1 16 A 50,000 cycles at 1 x I <sub>N</sub> , inductive
DC 50 V:	0.1 16 A 50,000 cycles at 1 x I <sub>N</sub> , inductive

Ambient temperature	-30 60 °C
Insulation coordination (IEC 60664)	2.5 kV / 2 Reinforced insulation in the operating area
Dielectric strength Operating area Current path/current path	Test voltage AC 3000 V

> 100 MΩ (DC 500 V)

## Rupture capacity I<sub>cn</sub> (IEC/EN 60934)

	I <sub>N</sub>	U <sub>N</sub>	I <sub>cn</sub>
1-pole, 2-pole	0.1 2 A	AC 240 V / DC 28 V	100 x I <sub>N</sub>
1-pole	0.1 10 A	DC 50 V	50 A
1-pole	2.5 16 A	AC 240 V / DC 28 V	200 A
2-pole	0.1 2 A	DC 50 V	10 x I <sub>N</sub>
2-pole	2.5 16 A	DC 50 V	250 A
2-pole	2.5 16 A	AC 240 V / DC 28 V	300 A

## Interrupting capacity $I_{\rm NC}$ (UL 1077)

	I <sub>N</sub>	U <sub>N</sub>	I <sub>nc</sub>
1-pole, 2-pole	0.1 10 A	AC 250 V	2,000 A, C, 1
1-pole, 2-pole	0.1 16 A	AC 125 V	1,000 A, C, 1

## Degree of protection (IEC 60529)


Operating area	IP40
	With water splash protection IP65
Terminal area	IP00
	With water splash protection IP64
Vibration	8 g (57-500 Hz) ± 0.61 mm (10-57 Hz) Test to IEC 60068-2-6, Test Fc 10 frequency cycles/axis
Shock resistance	30 g (11 ms) Test to IEC 60068-2-27, Test Ea
Corrosion	96 hours in 5 % salt mist Test to IEC 60068-2-11, Test Ka
Humidity	240 hours in 95 % RH Test to IEC 60068-2-78, Test Cab
Mass	approx. 53 g (2-pole) approx. 50 g (1-pole)


## **Approvals**

Approval authority	Standard	Rated voltage	Current rating range
VDE	IEC/EN 60934	AC 240 V DC 50 V	0.1 16 A 0.1 16 A
UL	UL 1077	AC 250 V AC 125 V	0.1 10 A 0.1 16 A
CSA	C22.2 No 235	AC 250 V AC 125 V	0.1 10 A 0.1 16 A
CQC (CCC)	GB 17701	AC 240 V DC 50 V	0.1 16 A 0.1 16 A

## **Time/current characteristics**

Total switch-off time at rated voltage and 1- or 2-pole load Ambient temperature 23 °C





<sup>11</sup>With DC, the magnetic response values are higher by a factor of approx. 1.25.

The time/current characteristics depend on the ambient temperature. In order to eliminate nuisance or late tripping, please multiply the current rating of the circuit breaker by a temperature factor (also refer to chapter Technical Information).

ambient temperature [°C]	-30	-20	-10	0	23	40	50	60
Temperature factor	0.8	0.84	0.88	0.92	1	1.08	1.14	1.23

## **② E** □ A 3120-N...-...M1-...thermal-magnetic circuit breaker



## **Ordering information**

20								
	rocker actuation							
	Mounting method N3 Snap-in, mounting cut-out 50.5 x 21.5 mm							
	N5 Snap-in, mounting cut-out 44.5 x 22 mm							
	Number of poles							
	1 1-pole switching, 1-pole thermal-magnetically protected							
	2 2-pole switching, 2-pole protected							
	(pole 1: thermal-magnetically protected,							
	pole 2: thermally protected)							
	5 2-pole switching, 1-pole thermal-magnetically							
	protected							
	Style							
	1 Standard							
	3 With actuator guard							
	4 With accordion-style seal, IP65							
	6 Version with shorter flange (only for mounting method N5)							
	With actuator guard and cross-hole							
	Terminal design							
	P7 Blade terminals							
	H7As P7, terminals 11 and 21 with additional							
	flat head screws M3.5							
	N7As P7, with additional shunt terminals 12(i)							
	and 22(i)							
	G7As N7, terminals 11 and 21 with additional flat							
	head screws M3.5							
	Trip curve M1 Medium delay, thermal 1.01-1.4 x I <sub>N</sub> ;							
	magnetic 4-9 x I <sub>N</sub> AC							
	Actuator							
	WRocker							
	Rocker colour and illumination							
	Opaque							
	01. Black without illumination							
	02. White without illumination							
	04 . Red without illumination							
	Translucent(when named with Y/R/T/G							
	the rocker is illuminated)  12 . (Y) White (illuminated)							
	12 . (Y) White (illuminated) 14 . (R) Red (illuminated)							
	15 . (Y) Orange (illuminated)							
	16 . (T) Blue (illuminated)							
	19 . (G) Green (illuminated)							
	Marking of rocker							
	A (not for mounting method 4)							
	F ( ON  OFF  O OFF  O OFF							
	A D F K L X							
	X A D I K L X							

3120-N5	2 4 -	P7 <b>M</b> 1	I-W 19 D	G Orderir	ng example
				Illumination volta	ige range
				(= operating vo	tage)
				1 DC 12 V	
				2 DC 24 V	
				3 AC 115 V	
				4 AC 230 V	
				5 DC 48 V	
				6 AC 400 V	
				(for 2-pole versi	ions)
				Current rating	
				0.1 16 A	
3120-N5	2 4 -	P7 M1	I-W 19 D	<b>G 4 - 16 A</b> Orderir	ng example



## **Ordering information**

3120 Thermal-magnetic circuit breaker/switch combination with push button actuation

### Mounting method

- N3 Snap-in, mounting cut-out 50.5 x 21.5 mm
- N5 Snap-in, mounting cut-out 44.5 x 22 mm

### **Number of poles**

- 1 1-pole switching, 1-pole thermal-magnetically
- 2 2-pole switching, 2-pole protected (pole 1: thermal-magnetically protected, pole 2: thermally protected)
- 5 2-pole switching, 1-pole thermal-magnetically protected

## Style

- With actuator guard
- With actuator guard and water splash cover IP54
- With power-on protection
- With power-on protection and water splash cover IP54

## Terminal design

- P7 Blade terminals
- H7 As P7, terminals 11 and 21 with additional flat head screws M3.5
- N7As P7, with additional shunt terminals 12(i)
- G7As N7, terminals 11 and 21 with additional flat head screws M3.5

M1 Medium delay, thermal 1.01-1.4 x I<sub>N</sub>; magnetic 4-9 x I<sub>N</sub> AC

### Actuator

S Two push buttons

Colour of push button/illumination (Style D and F without water splash protection)

GRD Green/red without illumination **GRDXG** Green with LED illumination/red without illumination

Colour of push button/illumination (Style E and V with water splash protection)

Green/red without illumination **GRDXG** Green with LED illumination/red without illumination

> Illumination voltage range (= operating voltage)

- DC 12 V
- DC 24 V
- 3 AC 115 V
- 4 AC 230 V
- DC 48 V
- AC 400 V (for 2-pole versions)

**Current rating** 

0.1...16 A

3120-N3 5 V - P7 M1-S GRXG - 16 A

Please observe our minimum ordering quantities.

## **Ordering information**

3120 Thermal magnetic resettable circuit breaker with push button Mounting method

- Snap-in, mounting cut-out 50.5 x 21.5 mm
- N5 Snap-in, mounting cut-out 44.5 x 22 mm

## **Number of poles**

- 1 1-pole thermal-magnetically protected
- 2 2-pole protected
  - (1 1: thermal-magnetically protected, pole 2: thermally protected)

5 2-pole, 1-pole thermal-magnetically protected

## G Resettable circuit breaker

Terminal design

P7 Blade terminals

H7 As P7, terminals 11 and 21 with additional flat head screws M3.5

N7 As P7, with additional shunt terminals 12(i) and 22(i)

G7 As N7, terminals 11 and 21 with additional flat head screws M3.5

M1 Medium delay, thermal- 1.01-1.4 x I<sub>N</sub>; magnetic 4-9 x I<sub>N</sub> AC

Actuator

## D One push button

- Colour of push button
- 01 Black
- 02 White opaque
- 04 Red opaque (UL/CSA approval only)
- 09 Green opaque

Marking of the push button X Without marking **Current rating** 0.1...16 A

3120-N3 2 G - P7 M1-D 01 - X 16 A

Ordering example

Please observe our minimum ordering quantities.

## **Customer-specific solutions**

Looking for a version you cannot find in our order numbering code? Please get in touch.