

## Product Specification

XBLW SN74LVC1G3157

Single-Pole Double-Throw Analog Switch

WEB | [www.xinboleic.com](http://www.xinboleic.com)




## Description

The SN74LVC1G3157 provides one analog multiplexer/demultiplexer with one digital select input (S), two independent inputs/outputs (Y0, Y1) and a common input/output (Z).

Schmitt trigger action at the select input makes the circuit tolerant of slower input rise and fall times across the entire VCC range from 1.65V to 5.5V.

## Feature

- Wide supply voltage range from 1.65 V to 5.5 V
- Very low ON resistance:  
7.5Ω (typical) at Vcc=2.7V  
6.5Ω (typical) at Vcc=3.3V  
6Ω (typical) at Vcc=5V
- Break-before-make switching
- CMOS low power consumption
- control input accepts voltages up to 5.5V
- Switch current capability of 32mA
- TTL interface compatibility at 3.3V
- Spec'd from -40 °C to +105 °C
- Packaging information: SOT-23-6/SOT-363



## Applications

- Wearables and mobile devices
- Audio signal routing
- Home automation
- I2C/SPI/UART bus multiplexing
- Internet of things (IoT)
- Portable computing
- Portable medical equipment
- Remote radio unit
- Surveillance
- Wireless charging

## Ordering Information

| Product Model          | Package Type | Marking | Packing | Packing Qty  |
|------------------------|--------------|---------|---------|--------------|
| XBLW SN74LVC1G3157T236 | SOT-23-6     | CNXX    | Tape    | 3000Pcs/Reel |
| XBLW SN74LVC1G3157T363 | SOT-363      | CNXX    | Tape    | 3000Pcs/Reel |

## Block Diagram




Figure 1. Logic symbol





Figure 2.ICE Logic symbol

## Pin Configurations



## Pin Description

| Pin No. | Pin Name | Description                 |
|---------|----------|-----------------------------|
| 1       | Y1       | independent input or output |
| 2       | GND      | ground (0 V)                |
| 3       | Y0       | independent input or output |
| 4       | Z        | common output or input      |
| 5       | Vcc      | supply voltage              |
| 6       | S        | select input                |

## Function Table

| Input S | Channel on |
|---------|------------|
| L       | Y0         |
| H       | Y1         |

Note: H=HIGH voltage level; L=LOW voltage level.

## Electrical Parameter

### Absolute Maximum Ratings

(Tamb=25°C, All voltage referenced to GND, unless otherwise specified)

| Characteristic          | Symbol           | Conditions                                                       | Min. | Max.                 | Unit |
|-------------------------|------------------|------------------------------------------------------------------|------|----------------------|------|
| supply voltage          | V <sub>CC</sub>  | -                                                                | -0.5 | +6.5                 | V    |
| input voltage           | V <sub>I</sub>   | -[1]                                                             | -0.5 | +6.5                 | V    |
| input clamping current  | I <sub>IK</sub>  | V <sub>I</sub> <-0.5V or V <sub>I</sub> >V <sub>CC</sub> +0.5V   | -50  | -                    | mA   |
| switch clamping current | I <sub>SK</sub>  | V <sub>I</sub> <-0.5V or V <sub>I</sub> >V <sub>CC</sub> +0.5V   | -    | ±50                  | mA   |
| switch voltage          | V <sub>SW</sub>  | enable and disable mode[2]                                       | -0.5 | V <sub>CC</sub> +0.5 | V    |
| switch current          | I <sub>SW</sub>  | V <sub>SW</sub> >-0.5V or V <sub>SW</sub> <V <sub>CC</sub> +0.5V | -    | ±50                  | mA   |
| supply current          | I <sub>CC</sub>  | -                                                                | -    | 100                  | mA   |
| ground current          | I <sub>GND</sub> | -                                                                | -100 | -                    | mA   |
| storage temperature     | T <sub>stg</sub> | -                                                                | -65  | +150                 | °C   |
| total power dissipation | P <sub>tot</sub> | -                                                                | -    | 250                  | mW   |
| soldering temperature   | T <sub>L</sub>   | 10s                                                              | 250  |                      | °C   |

Note:

[1] The minimum input voltage rating may be exceeded if the input current rating is observed.

[2] The minimum and maximum switch voltage ratings may be exceeded if the switch clamping current rating is observed.

### Recommended Operating Conditions

| Characteristic                      | Symbol           | Conditions                                    | Min. | Typ. | Max.            | Unit |
|-------------------------------------|------------------|-----------------------------------------------|------|------|-----------------|------|
| supply voltage                      | V <sub>CC</sub>  | -                                             | 1.65 | -    | 5.5             | V    |
| input voltage                       | V <sub>I</sub>   | -                                             | 0    | -    | 5.5             | V    |
| switch voltage                      | V <sub>SW</sub>  | enable and disable mode <sup>[1]</sup>        | 0    | -    | V <sub>CC</sub> | V    |
| ambient temperature                 | T <sub>amb</sub> | -                                             | -40  | -    | +105            | °C   |
| input transition rise and fall rate | Δt/ΔV            | V <sub>CC</sub> =1.65V to 2.7V <sup>[2]</sup> | -    | -    | 20              | ns/V |
|                                     |                  | V <sub>CC</sub> =2.7V to 5.5V <sup>[2]</sup>  | -    | -    | 10              | ns/V |

Note:

[1] To avoid sinking GND current from terminal Z when switch current flows in terminal Yn, the voltage drop across the bidirectional switch must not exceed 0.4V. If the switch current flows into terminal Z, no GND current will flow from terminal Yn. In this case, there is no limit for the voltage drop across the switch

[2] Applies to control signal levels.

## ESD Ratings

| Parameter          |                         | Defintion                                                                                | Vaue  | Unit |
|--------------------|-------------------------|------------------------------------------------------------------------------------------|-------|------|
| V <sub>(ESD)</sub> | Electrostatic discharge | Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins <sup>(1)</sup>              | ±2000 | V    |
|                    |                         | Charged device model (CDM), per JEDEC specification JESD22-C101, all pins <sup>(2)</sup> | ±1000 |      |

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

## Electrical Characteristics

### DC Characteristics 1

(Tamb=-40°C to +85°C, voltages are referenced to GND (ground=0V), unless otherwise specified)

| Parameter                 | Symbol              | Conditions                                                                                                                  | Min.                | Typ. <sup>[1]</sup> | Max.                | Unit |
|---------------------------|---------------------|-----------------------------------------------------------------------------------------------------------------------------|---------------------|---------------------|---------------------|------|
| HIGH-level input voltage  | V <sub>IH</sub>     | V <sub>CC</sub> =1.65V to 1.95V                                                                                             | 0.65V <sub>CC</sub> |                     | -                   | V    |
|                           |                     | V <sub>CC</sub> =2.3V to 2.7V                                                                                               | 1.7                 |                     | -                   | V    |
|                           |                     | V <sub>CC</sub> =3V to 3.6V                                                                                                 | 2.0                 |                     | -                   | V    |
|                           |                     | V <sub>CC</sub> =4.5V to 5.5V                                                                                               | 0.7V <sub>CC</sub>  |                     | -                   | V    |
| LOW-level input voltage   | V <sub>IL</sub>     | V <sub>CC</sub> =1.65V to 1.95V                                                                                             | -                   |                     | 0.35V <sub>CC</sub> | V    |
|                           |                     | V <sub>CC</sub> =2.3V to 2.7V                                                                                               | -                   |                     | 0.7                 | V    |
|                           |                     | V <sub>CC</sub> =3V to 3.6V                                                                                                 | -                   |                     | 0.8                 | V    |
|                           |                     | V <sub>CC</sub> =4.5V to 5.5V                                                                                               | -                   |                     | 0.3V <sub>CC</sub>  | V    |
| input leakage current     | I <sub>I</sub>      | pin S; V <sub>i</sub> = 5.5 V or GND; V <sub>CC</sub> = 0 V to 5.5 V <sup>[2]</sup>                                         | -                   | ±0.1                | ±1                  | uA   |
| supply current            | I <sub>CC</sub>     | V <sub>i</sub> =5.5V or GND; V <sub>SW</sub> =GND or V <sub>CC</sub> ; V <sub>CC</sub> =1.65V to 5.5V <sup>[2]</sup>        | -                   | 0.1                 | 4                   | uA   |
| additional supply current | ΔI <sub>CC</sub>    | pin S; V <sub>i</sub> =V <sub>CC</sub> -0.6V; V <sub>CC</sub> =5.5V; V <sub>SW</sub> =GND or V <sub>CC</sub> <sup>[2]</sup> | -                   | 5                   | 500                 | uA   |
| input capacitance         | C <sub>I</sub>      | -                                                                                                                           | -                   | 2.5                 | -                   | pF   |
| OFF-state capacitance     | C <sub>S(OFF)</sub> | -                                                                                                                           | -                   | 6.0                 | -                   | pF   |
| ON-state capacitance      | C <sub>S(ON)</sub>  | -                                                                                                                           | -                   | 18                  | -                   | pF   |
| OFF-state                 | I <sub>S(OFF)</sub> | V <sub>CC</sub> =5.5V; see Figure 3 <sup>[2]</sup>                                                                          | -                   | ±0.1                | ±0.2                | uA   |
| ON-state                  | I <sub>S(ON)</sub>  | V <sub>CC</sub> =5.5V; see Figure 4 <sup>[2]</sup>                                                                          | -                   | ±0.1                | ±1                  | uA   |

Note:

[1] Typical values are measured at Tamb=25°C

[2] These typical values are measured at V<sub>CC</sub>=3.3V

## DC Characteristics 2

(Tamb=-40°C to +105°C, voltages are referenced to GND (ground=0V), unless otherwise specified)

| Parameter                 | Symbol          | Conditions                                                                            | Min.         | Typ. | Max.         | Unit    |
|---------------------------|-----------------|---------------------------------------------------------------------------------------|--------------|------|--------------|---------|
| HIGH-level input voltage  | $V_{IH}$        | $V_{CC}=1.65V$ to $1.95V$                                                             | $0.65V_{CC}$ |      | -            | V       |
|                           |                 | $V_{CC}=2.3V$ to $2.7V$                                                               | 1.7          |      | -            | V       |
|                           |                 | $V_{CC}=3V$ to $3.6V$                                                                 | 2.0          |      | -            | V       |
|                           |                 | $V_{CC}=4.5V$ to $5.5V$                                                               | $0.7V_{CC}$  |      | -            | V       |
| LOW-level input voltage   | $V_{IL}$        | $V_{CC}=1.65V$ to $1.95V$                                                             | -            |      | $0.35V_{CC}$ | V       |
|                           |                 | $V_{CC}=2.3V$ to $2.7V$                                                               | -            |      | 0.7          | V       |
|                           |                 | $V_{CC}=3V$ to $3.6V$                                                                 | -            |      | 0.8          | V       |
|                           |                 | $V_{CC}=4.5V$ to $5.5V$                                                               | -            |      | $0.3V_{CC}$  | V       |
| input leakage current     | $I_I$           | pin S; $V_I = 5.5V$ or GND; $V_{CC} = 0V$ to $5.5V$ <sup>[1]</sup>                    | -            | -    | $\pm 1$      | $\mu A$ |
| OFF-state                 | $I_{S(OFF)}$    | $V_{CC}=5.5V$ ; see Figure 3 <sup>[1]</sup>                                           | -            | -    | $\pm 0.5$    | $\mu A$ |
| ON-state                  | $I_{S(ON)}$     | $V_{CC}=5.5V$ ; see Figure 4 <sup>[1]</sup>                                           | -            | -    | $\pm 2$      | $\mu A$ |
| supply current            | $I_{CC}$        | $V_I=5.5V$ or GND; $V_{SW}=GND$ or $V_{CC}$ ; $V_{CC}=1.65V$ to $5.5V$ <sup>[1]</sup> | -            | -    | 4            | $\mu A$ |
| additional supply current | $\Delta I_{CC}$ | pin S; $V_I=V_{CC}-0.6V$ ; $V_{CC}=5.5V$ ; $V_{SW}=GND$ or $V_{CC}$ <sup>[1]</sup>    | -            | -    | 500          | $\mu A$ |

## ON Resistance 1

(Tamb=-40°C to +85°C, voltages are referenced to GND (ground=0V), unless otherwise specified)

| Parameter                | Symbol                | Conditions                                            |                                                       | Min. | Typ. <sup>[1]</sup> | Max. | Unit |
|--------------------------|-----------------------|-------------------------------------------------------|-------------------------------------------------------|------|---------------------|------|------|
| ON resistance (peak)     | R <sub>ON(peak)</sub> | V <sub>I</sub> =GND to V <sub>CC</sub> ; see Figure 5 | I <sub>SW</sub> =4mA;<br>V <sub>CC</sub> =1.65V~1.95V | -    | 34.0                | 130  | Ω    |
|                          |                       |                                                       | I <sub>SW</sub> =8mA;<br>V <sub>CC</sub> =2.3V~2.7V   | -    | 12.0                | 30   | Ω    |
|                          |                       |                                                       | I <sub>SW</sub> =12mA;<br>V <sub>CC</sub> =2.7V       | -    | 10.4                | 25   | Ω    |
|                          |                       |                                                       | I <sub>SW</sub> =24mA;<br>V <sub>CC</sub> =3V~3.6V    | -    | 7.8                 | 20   | Ω    |
|                          |                       |                                                       | I <sub>SW</sub> =32mA;<br>V <sub>CC</sub> =4.5V~5.5V  | -    | 6.2                 | 15   | Ω    |
| ON resistance (rail)     | R <sub>ON(rail)</sub> | V <sub>I</sub> =GND; see Figure 5                     | I <sub>SW</sub> =4mA;<br>V <sub>CC</sub> =1.65V~1.95V | -    | 8.2                 | 18   | Ω    |
|                          |                       |                                                       | I <sub>SW</sub> =8mA;<br>V <sub>CC</sub> =2.3V~2.7V   | -    | 7.1                 | 16   | Ω    |
|                          |                       |                                                       | I <sub>SW</sub> =12mA;<br>V <sub>CC</sub> =2.7V       | -    | 6.9                 | 14   | Ω    |
|                          |                       |                                                       | I <sub>SW</sub> =24mA;<br>V <sub>CC</sub> =3V~3.6V    | -    | 6.5                 | 12   | Ω    |
|                          |                       |                                                       | I <sub>SW</sub> =32mA;<br>V <sub>CC</sub> =4.5V~5.5V  | -    | 5.8                 | 10   | Ω    |
|                          |                       | V <sub>I</sub> =V <sub>CC</sub> ; see Figure 5        | I <sub>SW</sub> =4mA;<br>V <sub>CC</sub> =1.65V~1.95V | -    | 10.4                | 30   | Ω    |
|                          |                       |                                                       | I <sub>SW</sub> =8mA;<br>V <sub>CC</sub> =2.3V~2.7V   | -    | 7.6                 | 20   | Ω    |
|                          |                       |                                                       | I <sub>SW</sub> =12mA;<br>V <sub>CC</sub> =2.7V       | -    | 7.0                 | 18   | Ω    |
|                          |                       |                                                       | I <sub>SW</sub> =24mA;<br>V <sub>CC</sub> =3V~3.6V    | -    | 6.1                 | 15   | Ω    |
|                          |                       |                                                       | I <sub>SW</sub> =32mA;<br>V <sub>CC</sub> =4.5V~5.5V  | -    | 4.9                 | 10   | Ω    |
| ON resistance (flatness) | R <sub>ON(flat)</sub> | V <sub>I</sub> =GND to V <sub>CC</sub> <sup>[2]</sup> | I <sub>SW</sub> =4mA;<br>V <sub>CC</sub> =1.65V~1.95V | -    | 26.0                | -    | Ω    |
|                          |                       |                                                       | I <sub>SW</sub> =8mA;<br>V <sub>CC</sub> =2.3V~2.7V   | -    | 5.0                 | -    | Ω    |
|                          |                       |                                                       | I <sub>SW</sub> =12mA;<br>V <sub>CC</sub> =2.7V       | -    | 3.5                 | -    | Ω    |
|                          |                       |                                                       | I <sub>SW</sub> =24mA;<br>V <sub>CC</sub> =3V~3.6V    | -    | 2.0                 | -    | Ω    |
|                          |                       |                                                       | I <sub>SW</sub> =32mA;<br>V <sub>CC</sub> =4.5V~5.5V  | -    | 1.5                 | -    | Ω    |

Note:

[1] Typical values are measured at Tamb=25°C and nominal V<sub>CC</sub>.

[2] Flatness is defined as the difference between the maximum and minimum value of ON resistance measured at identical V<sub>CC</sub> and temperature.

## ON Resistance 2

(Tamb=-40°C to +105°C, voltages are referenced to GND (ground=0V), unless otherwise specified)

| Parameter            | Symbol                | Conditions                                            |                                                       | Min. | Typ. | Max. | Unit |
|----------------------|-----------------------|-------------------------------------------------------|-------------------------------------------------------|------|------|------|------|
| ON resistance (peak) | R <sub>ON(peak)</sub> | V <sub>I</sub> =GND to V <sub>CC</sub> ; see Figure 5 | I <sub>SW</sub> =4mA;<br>V <sub>CC</sub> =1.65V~1.95V | -    | -    | 195  | Ω    |
|                      |                       |                                                       | I <sub>SW</sub> =8mA;<br>V <sub>CC</sub> =2.3V~2.7V   | -    | -    | 45   | Ω    |
|                      |                       |                                                       | I <sub>SW</sub> =12mA;<br>V <sub>CC</sub> =2.7V       | -    | -    | 38   | Ω    |
|                      |                       |                                                       | I <sub>SW</sub> =24mA;<br>V <sub>CC</sub> =3V~3.6V    | -    | -    | 30   | Ω    |
|                      |                       |                                                       | I <sub>SW</sub> =32mA;<br>V <sub>CC</sub> =4.5V~5.5V  | -    | -    | 23   | Ω    |
| ON resistance (rail) | R <sub>ON(rail)</sub> | V <sub>I</sub> =GND; see Figure 5                     | I <sub>SW</sub> =4mA;<br>V <sub>CC</sub> =1.65V~1.95V | -    | -    | 27   | Ω    |
|                      |                       |                                                       | I <sub>SW</sub> =8mA;<br>V <sub>CC</sub> =2.3V~2.7V   | -    | -    | 24   | Ω    |
|                      |                       |                                                       | I <sub>SW</sub> =12mA;<br>V <sub>CC</sub> =2.7V       | -    | -    | 21   | Ω    |
|                      |                       |                                                       | I <sub>SW</sub> =24mA;<br>V <sub>CC</sub> =3V~3.6V    | -    | -    | 18   | Ω    |
|                      |                       |                                                       | I <sub>SW</sub> =32mA;<br>V <sub>CC</sub> =4.5V~5.5V  | -    | -    | 15   | Ω    |
|                      |                       | V <sub>I</sub> =V <sub>CC</sub> ; see Figure 5        | I <sub>SW</sub> =4mA;<br>V <sub>CC</sub> =1.65V~1.95V | -    | -    | 45   | Ω    |
|                      |                       |                                                       | I <sub>SW</sub> =8mA;<br>V <sub>CC</sub> =2.3V~2.7V   | -    | -    | 30   | Ω    |
|                      |                       |                                                       | I <sub>SW</sub> =12mA;<br>V <sub>CC</sub> =2.7V       | -    | -    | 27   | Ω    |
|                      |                       |                                                       | I <sub>SW</sub> =24mA;<br>V <sub>CC</sub> =3V~3.6V    | -    | -    | 23   | Ω    |
|                      |                       |                                                       | I <sub>SW</sub> =32mA;<br>V <sub>CC</sub> =4.5V~5.5V  | -    | -    | 15   | Ω    |

## AC Characteristics 1

(Tamb=-40°C to +85°C, voltages are referenced to GND (ground=0V), unless otherwise specified)

| Parameter               | Symbol           | Conditions                                          |                              | Min. | Typ. <sup>[1]</sup> | Max. | Unit |
|-------------------------|------------------|-----------------------------------------------------|------------------------------|------|---------------------|------|------|
| propagation delay       | t <sub>pd</sub>  | Z to Yn or Yn to Z; see Figure 12 <sup>[2][3]</sup> | V <sub>CC</sub> =1.65V~1.95V |      |                     | 2    | ns   |
|                         |                  |                                                     | V <sub>CC</sub> =2.3V~2.7V   |      |                     | 1.2  | ns   |
|                         |                  |                                                     | V <sub>CC</sub> =2.7V        |      |                     | 1.0  | ns   |
|                         |                  |                                                     | V <sub>CC</sub> =3V~3.6V     |      |                     | 0.8  | ns   |
|                         |                  |                                                     | V <sub>CC</sub> =4.5V~5.5V   |      |                     | 0.6  | ns   |
| enable time             | t <sub>en</sub>  | S to Yn; see Figure 13 <sup>[4]</sup>               | V <sub>CC</sub> =1.65V~1.95V | 3.1  | 8.7                 | 20.8 | ns   |
|                         |                  |                                                     | V <sub>CC</sub> =2.3V~2.7V   | 2.2  | 5.3                 | 11.5 | ns   |
|                         |                  |                                                     | V <sub>CC</sub> =2.7V        | 2.1  | 4.9                 | 9.3  | ns   |
|                         |                  |                                                     | V <sub>CC</sub> =3V~3.6V     | 1.8  | 4.0                 | 7.6  | ns   |
|                         |                  |                                                     | V <sub>CC</sub> =4.5V~5.5V   | 1.5  | 3.0                 | 5.7  | ns   |
| disable time            | t <sub>dis</sub> | S to Yn; see Figure 13 <sup>[5]</sup>               | V <sub>CC</sub> =1.65V~1.95V | 3.0  | 6.0                 | 11.4 | ns   |
|                         |                  |                                                     | V <sub>CC</sub> =2.3V~2.7V   | 2.1  | 4.4                 | 7.3  | ns   |
|                         |                  |                                                     | V <sub>CC</sub> =2.7V        | 2.1  | 4.2                 | 6.3  | ns   |
|                         |                  |                                                     | V <sub>CC</sub> =3V~3.6V     | 1.7  | 3.6                 | 5.3  | ns   |
|                         |                  |                                                     | V <sub>CC</sub> =4.5V~5.5V   | 1.3  | 2.9                 | 3.8  | ns   |
| break-before emake time | t <sub>b-m</sub> | see Figure 14 <sup>[6]</sup>                        | V <sub>CC</sub> =1.65V~1.95V | 0.5  |                     |      | ns   |
|                         |                  |                                                     | V <sub>CC</sub> =2.3V~2.7V   | 0.5  |                     |      | ns   |
|                         |                  |                                                     | V <sub>CC</sub> =2.7V        | 0.5  |                     |      | ns   |
|                         |                  |                                                     | V <sub>CC</sub> =3V~3.6V     | 0.5  |                     |      | ns   |
|                         |                  |                                                     | V <sub>CC</sub> =4.5V~5.5V   | 0.5  |                     |      | ns   |

Note:

- [1] Typical values are measured at Tamb=25°C and nominal Vcc.
- [2]  $t_{pd}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ .
- [3] Propagation delay is the calculated Rc time constant of the typical ON resistance of the switch and the specified capacitance when driven by an ideal voltage source (zero output impedance).
- [4]  $t_{en}$  is the same as  $t_{PZH}$  and  $t_{PZL}$ .
- [5]  $t_{dis}$  is the same as  $t_{PLZ}$  and  $t_{PHZ}$ .
- [6] Break-before-make specified by design.

## AC Characteristics 2

(Tamb=-40°C to +105°C, voltages are referenced to GND (ground=0V), unless otherwise specified)

| Parameter              | Symbol    | Conditions                                          | Min.               | Typ. <sup>[1]</sup> | Max. | Unit |
|------------------------|-----------|-----------------------------------------------------|--------------------|---------------------|------|------|
| propagation delay      | $t_{pd}$  | Z to Yn or Yn to Z; see Figure 12 <sup>[2][3]</sup> | Vcc=1.65V to 1.95V |                     | 3.0  | ns   |
|                        |           |                                                     | Vcc=2.3V to 2.7V   |                     | 2.0  | ns   |
|                        |           |                                                     | Vcc=2.7V           |                     | 1.5  | ns   |
|                        |           |                                                     | Vcc=3V to 3.6V     |                     | 1.5  | ns   |
|                        |           |                                                     | Vcc=4.5V to 5.5V   |                     | 1.0  | ns   |
| enable time            | $t_{en}$  | S to Yn; see Figure 13 <sup>[4]</sup>               | Vcc=1.65V to 1.95V | 3.1                 | 22.0 | ns   |
|                        |           |                                                     | Vcc=2.3V to 2.7V   | 2.2                 | 12.5 | ns   |
|                        |           |                                                     | Vcc=2.7V           | 2.1                 | 10.5 | ns   |
|                        |           |                                                     | Vcc=3V to 3.6V     | 1.8                 | 9.0  | ns   |
|                        |           |                                                     | Vcc=4.5V to 5.5V   | 1.5                 | 6.1  | ns   |
| disable time           | $t_{dis}$ | S to Yn; see Figure 13 <sup>[5]</sup>               | Vcc=1.65V to 1.95V | 3.0                 | 11.7 | ns   |
|                        |           |                                                     | Vcc=2.3V to 2.7V   | 2.1                 | 7.6  | ns   |
|                        |           |                                                     | Vcc=2.7V           | 2.1                 | 6.6  | ns   |
|                        |           |                                                     | Vcc=3V to 3.6V     | 1.7                 | 5.9  | ns   |
|                        |           |                                                     | Vcc=4.5V to 5.5V   | 1.3                 | 4.3  | ns   |
| break-before make time | $t_{b-m}$ | see Figure 14 <sup>[6]</sup>                        | Vcc=1.65V to 1.95V | 0.5                 |      | ns   |
|                        |           |                                                     | Vcc=2.3V to 2.7V   | 0.5                 |      | ns   |
|                        |           |                                                     | Vcc=2.7V           | 0.5                 |      | ns   |
|                        |           |                                                     | Vcc=3V to 3.6V     | 0.5                 |      | ns   |
|                        |           |                                                     | Vcc=4.5V to 5.5V   | 0.5                 |      | ns   |

Note:

- [1] Typical values are measured at Tamb=25°C and nominal Vcc.
- [2]  $t_{pd}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ .
- [3] Propagation delay is the calculated Rc time constant of the typical ON resistance of the switch and the specified capacitance when driven by an ideal voltage source (zero output impedance).
- [4]  $t_{en}$  is the same as  $t_{PZH}$  and  $t_{PZL}$ .
- [5]  $t_{dis}$  is the same as  $t_{PLZ}$  and  $t_{PHZ}$ .
- [6] Break-before-make specified by design.

### Additional AC Characteristics

(Tamb=25°C, voltages are referenced to GND (ground=0V), unless otherwise specified)

| Parameter                 | Symbol              | Conditions                                                                                                               | Min.                  | Typ.  | Max. | Unit |
|---------------------------|---------------------|--------------------------------------------------------------------------------------------------------------------------|-----------------------|-------|------|------|
| total harmonic distortion | THD                 | $f_i=600\text{Hz}\sim 20\text{kHz};$<br>$R_L=600\Omega;$<br>$C_L=50\text{pF}; V_i=0.5\text{V(p-p)};$<br>see Figure 16    | $V_{CC}=1.65\text{V}$ | 0.260 |      | %    |
|                           |                     |                                                                                                                          | $V_{CC}=2.3\text{V}$  | 0.078 |      | %    |
|                           |                     |                                                                                                                          | $V_{CC}=3.0\text{V}$  | 0.078 |      | %    |
|                           |                     |                                                                                                                          | $V_{CC}=4.5\text{V}$  | 0.078 |      | %    |
| -3 dB frequency response  | $f_{(-3\text{dB})}$ | $R_L=50\Omega;$ see Figure 17                                                                                            | $V_{CC}=1.65\text{V}$ | 200   |      | MHz  |
|                           |                     |                                                                                                                          | $V_{CC}=2.3\text{V}$  | 300   |      | MHz  |
|                           |                     |                                                                                                                          | $V_{CC}=3.0\text{V}$  | 300   |      | MHz  |
|                           |                     |                                                                                                                          | $V_{CC}=4.5\text{V}$  | 300   |      | MHz  |
| isolation (OFF-state)     | $\alpha_{iso}$      | $R_L=50\Omega; C_L=5\text{pF};$<br>$f_i=10\text{MHz};$<br>see Figure 18                                                  | $V_{CC}=1.65\text{V}$ | -42   |      | dB   |
|                           |                     |                                                                                                                          | $V_{CC}=2.3\text{V}$  | -42   |      | dB   |
|                           |                     |                                                                                                                          | $V_{CC}=3.0\text{V}$  | -40   |      | dB   |
|                           |                     |                                                                                                                          | $V_{CC}=4.5\text{V}$  | -40   |      | dB   |
| charge injection          | $Q_{inj}$           | $C_L=0.1\text{nF}; V_{gen}=0\text{V};$<br>$R_{gen}=0\Omega;$<br>$f_i=1\text{MHz}; R_L=1\text{M}\Omega;$<br>see Figure 19 | $V_{CC}=1.8\text{V}$  | 3.3   |      | pc   |
|                           |                     |                                                                                                                          | $V_{CC}=2.5\text{V}$  | 4.1   |      | pc   |
|                           |                     |                                                                                                                          | $V_{CC}=3.3\text{V}$  | 5.0   |      | pc   |
|                           |                     |                                                                                                                          | $V_{CC}=4.5\text{V}$  | 6.4   |      | pc   |
|                           |                     |                                                                                                                          | $V_{CC}=5.5\text{V}$  | 7.5   |      | pc   |

## Testing Circuit

### DC Testing Circuit




Figure 3. Test circuit for measuring OFF-state leakage current




Figure 4. Test circuit for measuring ON-state leakage current

## ON Resistance Test Circuit And Graphs






Figure 5. Test circuit for measuring ON resistance




- (1) V<sub>CC</sub> = 1.8 V
- (2) V<sub>CC</sub> = 2.5 V
- (3) V<sub>CC</sub> = 2.7 V
- (4) V<sub>CC</sub> = 3.3 V
- (5) V<sub>CC</sub> = 5.0 V

Figure 6. Typical ON resistance as a function of input voltage; Tamb=25°C




- (1)  $T_{amb} = 125\text{ }^{\circ}\text{C}$
- (2)  $T_{amb} = 85\text{ }^{\circ}\text{C}$
- (3)  $T_{amb} = 25\text{ }^{\circ}\text{C}$
- (4)  $T_{amb} = -40\text{ }^{\circ}\text{C}$

Figure 7.ON resistance as a function of input voltage;  
 $V_{CC} = 1.8\text{ V}$




- (1)  $T_{amb} = 125\text{ }^{\circ}\text{C}$
- (2)  $T_{amb} = 85\text{ }^{\circ}\text{C}$
- (3)  $T_{amb} = 25\text{ }^{\circ}\text{C}$
- (4)  $T_{amb} = -40\text{ }^{\circ}\text{C}$

Figure 8.ON resistance as a function of input voltage;  
 $V_{CC} = 2.5\text{ V}$



- (1)  $T_{amb} = 125\text{ }^{\circ}\text{C}$
- (2)  $T_{amb} = 85\text{ }^{\circ}\text{C}$
- (3)  $T_{amb} = 25\text{ }^{\circ}\text{C}$
- (4)  $T_{amb} = -40\text{ }^{\circ}\text{C}$

Figure 9.ON resistance as a function of input voltage;  
 $V_{CC} = 2.7\text{ V}$



- (1)  $T_{amb} = 125\text{ }^{\circ}\text{C}$
- (2)  $T_{amb} = 85\text{ }^{\circ}\text{C}$
- (3)  $T_{amb} = 25\text{ }^{\circ}\text{C}$
- (4)  $T_{amb} = -40\text{ }^{\circ}\text{C}$

Figure 10.ON resistance as a function of input voltage;  
 $V_{CC} = 3.3\text{ V}$





Figure .ON resistance as a function of input voltage;  $V_{CC} = 5.0\text{ V}$


#### AC Testing Waveforms



Measurement points are given in [Table 10](#).

Logic levels:  $V_{OL}$  and  $V_{OH}$  are typical output voltage levels that occur with the output load.

Figure .12.Input (Yn or Z) to output (Z or Yn) propagation delays




Logic levels:  $V_{OL}$  and  $V_{OH}$  are typical output voltage levels that occur with the output load.

Figure .13.Enable and disable times


### Measurement Points

| Supply voltage  | Input               | Output              |                          |                          |
|-----------------|---------------------|---------------------|--------------------------|--------------------------|
| $V_{CC}$        | $V_M$               | $V_M$               | $V_X$                    | $V_Y$                    |
| 1.65 V to 5.5 V | $0.5 \times V_{CC}$ | $0.5 \times V_{CC}$ | $V_{OL} + 0.3 \text{ V}$ | $V_{OH} - 0.3 \text{ V}$ |

### AC Testing Circuit




a. Test circuit



b. Input and output measurement points

Figure .14.Test circuit for measuring break-before-make timing



Definitions test circuit:

$R_T$  = Termination resistance should be equal to output impedance  $Z_o$  of the pulse generator;

$C_L$  = Load capacitance including jig and probe capacitance;

$R_L$  = Load resistance;

$V_{EXT}$  = External voltage for measuring switching times.

Figure .15. Test circuit for measuring switching times

#### Tese data

| Supply voltage   | Input    |               | Load  |              | $V_{EXT}$          |                    |                    |
|------------------|----------|---------------|-------|--------------|--------------------|--------------------|--------------------|
| $V_{CC}$         | $V_I$    | $t_r, t_f$    | $C_L$ | $R_L$        | $t_{PLH}, t_{PHL}$ | $t_{PZH}, t_{PHZ}$ | $t_{PZL}, t_{PLZ}$ |
| 1.65 V to 1.95 V | $V_{CC}$ | $\leq 2.0$ ns | 50 pF | 500 $\Omega$ | open               | GND                | $2 \times V_{CC}$  |
| 2.3 V to 2.7 V   | $V_{CC}$ | $\leq 2.0$ ns | 50 pF | 500 $\Omega$ | open               | GND                | $2 \times V_{CC}$  |
| 2.7 V            | $V_{CC}$ | $\leq 2.5$ ns | 50 pF | 500 $\Omega$ | open               | GND                | $2 \times V_{CC}$  |
| 3 V to 3.6 V     | $V_{CC}$ | $\leq 2.5$ ns | 50 pF | 500 $\Omega$ | open               | GND                | $2 \times V_{CC}$  |
| 4.5 V to 5.5 V   | $V_{CC}$ | $\leq 2.5$ ns | 50 pF | 500 $\Omega$ | open               | GND                | $2 \times V_{CC}$  |

### Additional AC Testing Circuit






Figure .16. Test circuit for measuring total harmonic distortion




Adjust  $f_i$  voltage to obtain 0 dBm level at output. Increase  $f_i$  frequency until dB meter reads -3 dB.

Figure .17. Test circuit for measuring the frequency response when switch is in ON-state




Adjust  $f_i$  voltage to obtain 0 dBm level at input.

Figure .18. Test circuit for measuring isolation (OFF-state)



a. Test circuit

$Q_{inj} = \Delta V_O \times C_L$ ;  
 $\Delta V_O$  = output voltage variation;  
 $R_{gen}$  = generator resistance;  
 $V_{gen}$  = generator voltage.




b. Input and output pulse definitions

Figure .19. Test circuit for measuring charge injection

## Package Information


- SOT23-6

| SIZE<br>SYMBOL | Dimensions In Millimeters |          | SIZE<br>SYMBOL | Dimensions In Inches |          |
|----------------|---------------------------|----------|----------------|----------------------|----------|
|                | MIN (mm)                  | MAX (mm) |                | MIN (mm)             | MAX (mm) |
| A              | 1.050                     | 1.250    | A              | 0.041                | 0.049    |
| A1             | 0.000                     | 0.100    | A1             | 0.000                | 0.004    |
| A2             | 1.050                     | 1.150    | A2             | 0.041                | 0.045    |
| b              | 0.300                     | 0.500    | b              | 0.012                | 0.020    |
| c              | 0.100                     | 0.200    | c              | 0.004                | 0.008    |
| D              | 2.820                     | 3.020    | D              | 0.111                | 0.119    |
| E              | 1.500                     | 1.700    | E              | 0.059                | 0.067    |
| E1             | 2.650                     | 2.950    | E1             | 0.104                | 0.116    |
| e              | 0.950 (BSC)               |          | e              | 0.037 (BSC)          |          |
| e1             | 1.800                     | 2.000    | e1             | 0.071                | 0.079    |
| L              | 0.300                     | 0.600    | L              | 0.012                | 0.024    |
| θ              | 0°                        | 8°       | θ              | 0°                   | 8°       |



• SOT-363

| Size<br>Symbol | Dimensions In Millimeters |          | Size<br>Symbol | Dimensions In Inches |          |
|----------------|---------------------------|----------|----------------|----------------------|----------|
|                | Min (mm)                  | Max (mm) |                | Min (in)             | Max (in) |
| A              | 0.900                     | 1.100    | A              | 0.035                | 0.043    |
| A1             | 0.000                     | 0.100    | A1             | 0.000                | 0.004    |
| A2             | 0.900                     | 1.000    | A2             | 0.035                | 0.039    |
| b              | 0.150                     | 0.350    | b              | 0.006                | 0.014    |
| c              | 0.080                     | 0.150    | C              | 0.003                | 0.006    |
| D              | 2.000                     | 2.200    | D              | 0.079                | 0.087    |
| E              | 1.150                     | 1.350    | E              | 0.045                | 0.053    |
| E1             | 2.150                     | 2.450    | E1             | 0.085                | 0.096    |
| e              | 0.650 (TYP)               |          | e              | 0.026 (TYP)          |          |
| e1             | 1.200                     | 1.400    | e1             | 0.047                | 0.055    |
| L              | 0.525 (REF)               |          | L              | 0.021 (REF)          |          |
| L1             | 0.260                     | 0.460    | L1             | 0.010                | 0.018    |
| θ              | 0°                        | 8°       | θ              | 0°                   | 8°       |



## Statement:

- XBLW reserves the right to modify the product manual without prior notice! Before placing an order, customers need to confirm whether the obtained information is the latest version and verify the completeness of the relevant information.
- Any semi-guide product is subject to failure or malfunction under specified conditions. It is the buyer's responsibility to comply with safety standards when using XBLW products for system design and whole machine manufacturing. And take the appropriate safety measures to avoid the potential in the risk of loss of personal injury or loss of property situation!
- XBLW products have not been licensed for life support, military, and aerospace applications, and therefore XBLW is not responsible for any consequences arising from the use of this product in these areas.
- If any or all XBLW products (including technical data, services) described or contained in this document are subject to any applicable local export control laws and regulations, they may not be exported without an export license from the relevant authorities in accordance with such laws.
- The specifications of any and all XBLW products described or contained in this document specify the performance, characteristics, and functionality of said products in their standalone state, but do not guarantee the performance, characteristics, and functionality of said products installed in Customer's products or equipment. In order to verify symptoms and conditions that cannot be evaluated in a standalone device, the Customer should ultimately evaluate and test the device installed in the Customer's product device.
- XBLW documentation is only allowed to be copied without any alteration of the content and with the relevant authorization. XBLW assumes no responsibility or liability for altered documents.
- XBLW is committed to becoming the preferred semiconductor brand for customers, and XBLW will strive to provide customers with better performance and better quality products.