

**PART NUMBER****100331VYA-ROCA****Rochester Electronics****Manufactured Components**

Rochester branded components are manufactured using either die/wafers purchased from the original suppliers or Rochester wafers recreated from the original IP. All re-creations are done with the approval of the Original Component Manufacturer. (OCM)

Parts are tested using original factory test programs or Rochester developed test solutions to guarantee product meets or exceeds the OCM data sheet.

**Quality Overview**

- ISO-9001
- AS9120 certification
- Qualified Manufacturers List (QML) MIL-PRF-38535
  - Class Q Military
  - Class V Space Level

**Qualified Suppliers List of Distributors (QSLD)**

- Rochester is a critical supplier to DLA and meets all industry and DLA standards.

Rochester Electronics, LLC is committed to supplying products that satisfy customer expectations for quality and are equal to those originally supplied by industry manufacturers.

*The original manufacturer's datasheet accompanying this document reflects the performance and specifications of the Rochester manufactured version of this device. Rochester Electronics guarantees the performance of its semiconductor products to the original OCM specifications. 'Typical' values are for reference purposes only. Certain minimum or maximum ratings may be based on product characterization, design, simulation, or sample testing.*

## **Rochester Electronics Manufactured Components**

Rochester branded components are manufactured using either die/wafers purchased from the original suppliers or Rochester wafers recreated from the original IP. All recreations are done with the approval of the OCM.

Parts are tested using original factory test programs or Rochester developed test solutions to guarantee product meets or exceeds the OCM data sheet.

## **Quality Overview**

- ISO-9001
- AS9120 certification
- Qualified Manufacturers List (QML) MIL-PRF-35835
  - Class Q Military
  - Class V Space Level
- Qualified Suppliers List of Distributors (QSLD)
  - Rochester is a critical supplier to DLA and meets all industry and DLA standards.

Rochester Electronics, LLC is committed to supplying products that satisfy customer expectations for quality and are equal to those originally supplied by industry manufacturers.

The original manufacturer's datasheet accompanying this document reflects the performance and specifications of the Rochester manufactured version of this device. Rochester Electronics guarantees the performance of its semiconductor products to the original OEM specifications. 'Typical' values are for reference purposes only. Certain minimum or maximum ratings may be based on product characterization, design, simulation, or sample testing.

# 100331 Low Power Triple D Flip-Flop

## General Description


The 100331 contains three D-type, edge-triggered master/slave flip-flops with true and complement outputs, a Common Clock ( $CP_C$ ), and Master Set (MS) and Master Reset (MR) inputs. Each flip-flop has individual Clock ( $CP_n$ ), Direct Set ( $SD_n$ ) and Direct Clear ( $CD_n$ ) inputs. Data enters a master when both  $CP_n$  and  $CP_C$  are LOW and transfers to a slave when  $CP_n$  or  $CP_C$  (or both) go HIGH. The Master Set, Master Reset and individual  $CD_n$  and  $SD_n$  inputs override the Clock inputs. All inputs have 50 k $\Omega$  pull-down resistors.

## Features

- 35% power reduction of the 100131
- 2000V ESD protection
- Pin/function compatible with 100131
- Voltage compensated operating range = -4.2V to -5.7V
- Available to industrial grade temperature range
- Available to MIL-STD-883

## Ordering Code:


## Logic Symbol





| Pin Names                 | Description                    |
|---------------------------|--------------------------------|
| $CP_0$ – $CP_2$           | Individual Clock Inputs        |
| $CP_C$                    | Common Clock Input             |
| $D_0$ – $D_2$             | Data Inputs                    |
| $CD_0$ – $CD_2$           | Individual Direct Clear Inputs |
| $SD_n$                    | Individual Direct Set Inputs   |
| MR                        | Master Reset Input             |
| MS                        | Master Set Input               |
| $Q_0$ – $Q_2$             | Data Outputs                   |
| $\bar{Q}_0$ – $\bar{Q}_2$ | Complementary Data Outputs     |

## Connection Diagrams


### 24-Pin DIP/SOIC



## Connection Diagrams (Continued)



## Logic Diagram



## Truth Tables

### Synchronous Operation

(Each Flip-Flop)

| Inputs         |                 |                 |                       |                       | Outputs                |
|----------------|-----------------|-----------------|-----------------------|-----------------------|------------------------|
| D <sub>n</sub> | CP <sub>n</sub> | CP <sub>C</sub> | MS<br>SD <sub>n</sub> | MR<br>CD <sub>n</sub> | Q <sub>n</sub> (t + 1) |
| L              | ↗               | L               | L                     | L                     | L                      |
| H              | ↗               | L               | L                     | L                     | H                      |
| L              | L               | ↗               | L                     | L                     | L                      |
| H              | L               | ↗               | L                     | L                     | H                      |
| X              | L               | L               | L                     | L                     | Q <sub>n</sub> (t)     |
| X              | H               | X               | L                     | L                     | Q <sub>n</sub> (t)     |
| X              | X               | H               | L                     | L                     | Q <sub>n</sub> (t)     |

H = HIGH Voltage Level  
L = LOW Voltage Level  
X = Don't Care  
U = Undefined  
t = Time before CP Positive Transition  
t + 1 = Time after CP Positive Transition  
↗ = LOW to HIGH Transition

### Asynchronous Operation

(Each Flip-Flop)

| Inputs         |                 |                 |                       |                       | Outputs                |
|----------------|-----------------|-----------------|-----------------------|-----------------------|------------------------|
| D <sub>n</sub> | CP <sub>n</sub> | CP <sub>C</sub> | MS<br>SD <sub>n</sub> | MR<br>CD <sub>n</sub> | Q <sub>n</sub> (t + 1) |
| X              | X               | X               | H                     | L                     | H                      |
| X              | X               | X               | L                     | H                     | L                      |
| X              | X               | X               | H                     | H                     | U                      |

## Absolute Maximum Ratings (Note 1)

Above which the useful life may be impaired

Storage Temperature ( $T_{STG}$ )  $-65^{\circ}\text{C}$  to  $+150^{\circ}\text{C}$

Maximum Junction Temperature ( $T_J$ )

Ceramic  $+175^{\circ}\text{C}$

Plastic  $+150^{\circ}\text{C}$

Pin Potential to

Ground Pin ( $V_{EE}$ )  $-7.0\text{V}$  to  $+0.5\text{V}$

Input Voltage (DC)  $V_{EE}$  to  $+0.5\text{V}$

Output Current

(DC Output HIGH)  $-50\text{ mA}$

ESD (Note 2)  $\leq 2000\text{V}$

## Recommended Operating Conditions

Case Temperature ( $T_C$ )

Commercial  $0^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$

Industrial  $-40^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$

Military  $-55^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$

Supply Voltage ( $V_{EE}$ )  $-5.7\text{V}$  to  $-4.2\text{V}$

**Note 1:** Absolute maximum ratings are those values beyond which the device may be damaged or have its useful life impaired. Functional operation under these conditions is not implied.

**Note 2:** ESD testing conforms to MIL-STD-883, Method 3015.

## Commercial Version

### DC Electrical Characteristics

$V_{EE} = -4.2\text{V}$  to  $-5.7\text{V}$ ,  $V_{CC} = V_{CCA} = \text{GND}$ ,  $T_C = 0^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$  (Note 3)

| Symbol           | Parameter               | Min   | Typ   | Max   | Units | Conditions                               |                              |
|------------------|-------------------------|-------|-------|-------|-------|------------------------------------------|------------------------------|
| V <sub>OH</sub>  | Output HIGH Voltage     | −1025 | −955  | −870  | mV    | V <sub>IN</sub> = V <sub>IH</sub> (Max)  | Loading with<br>50Ω to −2.0V |
| V <sub>OL</sub>  | Output LOW Voltage      | −1830 | −1705 | −1620 | mV    | or V <sub>IL</sub> (Min)                 |                              |
| V <sub>OHC</sub> | Output HIGH Voltage     | −1035 |       |       | mV    | V <sub>IN</sub> = V <sub>IH</sub> (Min)  | Loading with<br>50Ω to −2.0V |
| V <sub>OLC</sub> | Output LOW Voltage      |       |       | −1610 | mV    | or V <sub>IL</sub> (Max)                 |                              |
| V <sub>IH</sub>  | Input HIGH Voltage      | −1165 |       | −870  | mV    | Guaranteed HIGH Signal<br>for All Inputs |                              |
| V <sub>IL</sub>  | Input LOW Voltage       | −1830 |       | −1475 | mV    | Guaranteed LOW Signal<br>for All Inputs  |                              |
| I <sub>IL</sub>  | Input LOW Current       | 0.5   |       |       | μA    | V <sub>IN</sub> = V <sub>IL</sub> (Min)  |                              |
| I <sub>IH</sub>  | Input HIGH Current      |       |       | 240   | μA    | V <sub>IN</sub> = V <sub>IH</sub> (Max)  |                              |
| I <sub>EE</sub>  | Power Supply<br>Current | −122  |       | −65   | mA    | Inputs Open                              |                              |

**Note 3:** The specified limits represent the "worst case" value for the parameter. Since these values normally occur at the temperature extremes, additional noise immunity and guardbanding can be achieved by decreasing the allowable system operating ranges. Conditions for testing shown in the tables are chosen to guarantee operation under "worst case" conditions.

## DIP AC Electrical Characteristics

$V_{EE} = -4.2\text{V}$  to  $-5.7\text{V}$ ,  $V_{CC} = V_{CCA} = \text{GND}$

| Symbol           | Parameter                                                        | T <sub>C</sub> = 0°C |      | T <sub>C</sub> = +25°C |      | T <sub>C</sub> = +85°C |      | Units | Conditions                            |                 |
|------------------|------------------------------------------------------------------|----------------------|------|------------------------|------|------------------------|------|-------|---------------------------------------|-----------------|
|                  |                                                                  | Min                  | Max  | Min                    | Max  | Min                    | Max  |       |                                       |                 |
| f <sub>max</sub> | Toggle Frequency                                                 | 375                  |      | 375                    |      | 375                    |      | MHz   | Figures 2, 3                          |                 |
| t <sub>PLH</sub> | Propagation Delay<br>CP <sub>C</sub> to Output                   | 0.75                 | 2.00 | 0.75                   | 2.00 | 0.75                   | 2.00 | ns    | Figures 1, 3                          |                 |
| t <sub>PHL</sub> | Propagation Delay<br>CP <sub>n</sub> to Output                   | 0.75                 | 2.00 | 0.75                   | 2.00 | 0.75                   | 2.00 | ns    |                                       |                 |
| t <sub>PLH</sub> | Propagation Delay<br>CD <sub>n</sub> , SD <sub>n</sub> to Output | 0.70                 | 1.70 | 0.70                   | 1.70 | 0.70                   | 1.80 | ns    | CP <sub>n</sub> , CP <sub>C</sub> = L | Figures<br>1, 4 |
| t <sub>PHL</sub> |                                                                  | 0.70                 | 2.00 | 0.70                   | 2.00 | 0.70                   | 2.00 |       | CP <sub>n</sub> , CP <sub>C</sub> = H |                 |
| t <sub>PLH</sub> | Propagation Delay<br>MS, MR to Output                            | 1.10                 | 2.60 | 1.10                   | 2.60 | 1.10                   | 2.60 | ns    | CP <sub>n</sub> , CP <sub>C</sub> = L |                 |
| t <sub>PHL</sub> |                                                                  | 1.10                 | 2.80 | 1.10                   | 2.80 | 1.10                   | 2.80 |       | CP <sub>n</sub> , CP <sub>C</sub> = H |                 |
| t <sub>TLH</sub> | Transition Time                                                  | 0.35                 | 1.30 | 0.35                   | 1.30 | 0.35                   | 1.30 | ns    | Figures 1, 3, 4                       |                 |
| t <sub>THL</sub> | 20% to 80%, 80% to 20%                                           |                      |      |                        |      |                        |      |       |                                       |                 |

## DIP AC Electrical Characteristics (Continued)

$V_{EE} = -4.2V$  to  $-5.7V$ ,  $V_{CC} = V_{CCA} = GND$

| Symbol      | Parameter                                     | $T_C = 0^\circ C$ |     | $T_C = +25^\circ C$ |     | $T_C = +85^\circ C$ |     | Units | Conditions   |
|-------------|-----------------------------------------------|-------------------|-----|---------------------|-----|---------------------|-----|-------|--------------|
|             |                                               | Min               | Max | Min                 | Max | Min                 | Max |       |              |
| $t_S$       | Setup Time                                    |                   |     |                     |     |                     |     |       | Figure 5     |
|             | $D_n$                                         | 0.40              |     | 0.40                |     | 0.40                |     |       |              |
|             | $CD_n$ , $SD_n$ (Release Time)                | 1.30              |     | 1.30                |     | 1.30                |     | ns    | Figure 4     |
|             | MS, MR (Release Time)                         | 2.30              |     | 2.30                |     | 2.30                |     |       |              |
| $t_H$       | Hold Time $D_n$                               | 0.5               |     | 0.5                 |     | 0.7                 |     | ns    | Figure 5     |
| $t_{pw(H)}$ | Pulse Width HIGH                              |                   |     |                     |     |                     |     |       |              |
|             | $CP_n$ , $CP_C$ , $CD_n$ ,<br>$SD_n$ , MR, MS | 2.00              |     | 2.00                |     | 2.00                |     | ns    | Figures 3, 4 |

## SOIC, PCC and Cerpak AC Electrical Characteristics

$V_{EE} = -4.2V$  to  $-5.7V$ ,  $V_{CC} = V_{CCA} = GND$

| Symbol             | Parameter                                                                      | T <sub>C</sub> = 0°C |      | T <sub>C</sub> = +25°C |      | T <sub>C</sub> = +85°C |      | Units | Conditions                            |              |
|--------------------|--------------------------------------------------------------------------------|----------------------|------|------------------------|------|------------------------|------|-------|---------------------------------------|--------------|
|                    |                                                                                | Min                  | Max  | Min                    | Max  | Min                    | Max  |       |                                       |              |
| f <sub>max</sub>   | Toggle Frequency                                                               | 400                  |      | 400                    |      | 400                    |      | MHz   | Figures 2, 3                          |              |
| t <sub>PLH</sub>   | Propagation Delay                                                              | 0.75                 | 1.80 | 0.75                   | 1.80 | 0.75                   | 1.80 | ns    | Figures 1, 3                          |              |
| t <sub>PHL</sub>   | CP <sub>C</sub> to Output                                                      |                      |      |                        |      |                        |      |       |                                       |              |
| t <sub>PLH</sub>   | Propagation Delay                                                              | 0.75                 | 1.80 | 0.75                   | 1.80 | 0.75                   | 1.80 | ns    |                                       |              |
| t <sub>PHL</sub>   | CP <sub>n</sub> to Output                                                      |                      |      |                        |      |                        |      |       |                                       |              |
| t <sub>PLH</sub>   | Propagation Delay                                                              | 0.70                 | 1.50 | 0.70                   | 1.50 | 0.70                   | 1.60 | ns    | CP <sub>n</sub> , CP <sub>C</sub> = L | Figures 1, 4 |
| t <sub>PHL</sub>   | CD <sub>n</sub> , SD <sub>n</sub> to Output                                    |                      |      |                        |      |                        |      |       |                                       |              |
| t <sub>PLH</sub>   |                                                                                | 0.80                 | 1.80 | 0.70                   | 1.80 | 0.70                   | 1.80 |       | CP <sub>n</sub> , CP <sub>C</sub> = H |              |
| t <sub>PHL</sub>   |                                                                                |                      |      |                        |      |                        |      |       |                                       |              |
| t <sub>PLH</sub>   | Propagation Delay                                                              | 1.10                 | 2.40 | 1.10                   | 2.40 | 1.10                   | 2.40 | ns    | CP <sub>n</sub> , CP <sub>C</sub> = L |              |
| t <sub>PHL</sub>   | MS, MR to Output                                                               |                      |      |                        |      |                        |      |       |                                       |              |
| t <sub>PLH</sub>   |                                                                                | 1.10                 | 2.60 | 1.10                   | 2.60 | 1.10                   | 2.60 |       |                                       |              |
| t <sub>THL</sub>   | Transition Time                                                                | 0.35                 | 1.10 | 0.35                   | 1.10 | 0.35                   | 1.10 | ns    | Figures 1, 3, 4                       |              |
| t <sub>THL</sub>   | 20% to 80%, 80% to 20%                                                         |                      |      |                        |      |                        |      |       |                                       |              |
| t <sub>S</sub>     | Setup Time                                                                     |                      |      |                        |      |                        |      | ns    | Figure 5                              |              |
|                    | D <sub>n</sub>                                                                 | 0.30                 |      | 0.30                   |      | 0.30                   |      |       | Figure 4                              |              |
|                    | CD <sub>n</sub> , SD <sub>n</sub> (Release Time)                               | 1.20                 |      | 1.20                   |      | 1.20                   |      |       |                                       |              |
|                    | MS, MR (Release Time)                                                          | 2.20                 |      | 2.20                   |      | 2.20                   |      |       |                                       |              |
| t <sub>H</sub>     | Hold Time D <sub>n</sub>                                                       | 0.5                  |      | 0.5                    |      | 0.7                    |      | ns    | Figure 5                              |              |
| t <sub>pw(H)</sub> | Pulse Width HIGH                                                               |                      |      |                        |      |                        |      | ns    | Figures 3, 4                          |              |
|                    | CP <sub>n</sub> , CP <sub>C</sub> , CD <sub>n</sub> , SD <sub>n</sub> , MR, MS | 2.00                 |      | 2.00                   |      | 2.00                   |      |       |                                       |              |
| t <sub>PLH</sub>   | Propagation Delay                                                              | 0.75                 | 1.40 | 0.75                   | 1.40 | 0.80                   | 1.50 | ns    | Figures 1, 3 PCC Only                 |              |
| t <sub>PHL</sub>   | CP <sub>C</sub> to Output                                                      |                      |      |                        |      |                        |      |       |                                       |              |
| t <sub>PLH</sub>   | Propagation Delay                                                              | 0.70                 | 1.40 | 0.75                   | 1.40 | 0.80                   | 1.50 | ns    |                                       |              |
| t <sub>PHL</sub>   | CP <sub>n</sub> to Output                                                      |                      |      |                        |      |                        |      |       |                                       |              |

## SOIC, PCC and Cerpak AC Electrical Characteristics (Continued)

$V_{EE} = -4.2V$  to  $-5.7V$ ,  $V_{CC} = V_{CCA} = GND$

| Symbol                 | Parameter                                                                                     | $T_C = 0^\circ C$ |      | $T_C = +25^\circ C$ |      | $T_C = +85^\circ C$ |      | Units | Conditions                                        |                 |
|------------------------|-----------------------------------------------------------------------------------------------|-------------------|------|---------------------|------|---------------------|------|-------|---------------------------------------------------|-----------------|
|                        |                                                                                               | Min               | Max  | Min                 | Max  | Min                 | Max  |       |                                                   |                 |
| $t_{PLH}$<br>$t_{PHL}$ | Propagation Delay<br>CD <sub>n</sub> , SD <sub>n</sub> to Output                              | 0.70              | 1.50 | 0.70                | 1.50 | 0.80                | 1.60 | ns    | CP <sub>n</sub> , CP <sub>C</sub> = L<br>PCC Only | Figures<br>1, 4 |
| $t_{PLH}$<br>$t_{PHL}$ |                                                                                               | 0.80              | 1.70 | 0.80                | 1.70 | 0.80                | 1.80 |       | CP <sub>n</sub> , CP <sub>C</sub> = H<br>PCC Only |                 |
| $t_{PLH}$<br>$t_{PHL}$ | Propagation Delay<br>MS, MR to Output                                                         | 1.10              | 2.00 | 1.10                | 2.00 | 1.20                | 2.10 | ns    | CP <sub>n</sub> , CP <sub>C</sub> = L<br>PCC Only |                 |
| $t_{PLH}$<br>$t_{PHL}$ |                                                                                               | 1.20              | 2.10 | 1.20                | 2.10 | 1.30                | 2.20 |       | CP <sub>n</sub> , CP <sub>C</sub> = H<br>PCC Only |                 |
| $t_{OSHL}$             | Maximum Skew Common<br>Edge<br>Output-to-Output Variation<br>Common Clock to Output<br>Path   |                   | 100  |                     | 100  |                     | 100  | ps    | PCC Only<br>(Note 4)                              |                 |
| $t_{OSHL}$             | Maximum Skew Common<br>Edge<br>Output-to-Output Variation<br>CP <sub>n</sub> to Output Path   |                   | 235  |                     | 235  |                     | 235  | ps    | PCC Only<br>(Note 4)                              |                 |
| $t_{OSLH}$             | Maximum Skew Common<br>Edge<br>Output-to-Output Variation<br>Common Clock to Output<br>Path   |                   | 120  |                     | 120  |                     | 120  | ps    | PCC Only<br>(Note 4)                              |                 |
| $t_{OSLH}$             | Maximum Skew Common<br>Edge<br>Output-to-Output Variation<br>CP <sub>n</sub> to Output Path   |                   | 275  |                     | 275  |                     | 275  | ps    | PCC Only<br>(Note 4)                              |                 |
| $t_{OST}$              | Maximum Skew Opposite<br>Edge<br>Output-to-Output Variation<br>Common Clock to Output<br>Path |                   | 125  |                     | 125  |                     | 125  | ps    | PCC Only<br>(Note 4)                              |                 |
| $t_{OST}$              | Maximum Skew Opposite<br>Edge<br>Output-to-Output Variation<br>CP <sub>n</sub> to Output Path |                   | 265  |                     | 265  |                     | 265  | ps    | PCC Only<br>(Note 4)                              |                 |
| $t_{ps}$               | Maximum Skew<br>Pin (Signal) Transition<br>Variation<br>Common Clock to Output<br>Path        |                   | 90   |                     | 90   |                     | 90   | ps    | PCC Only<br>(Note 4)                              |                 |
| $t_{ps}$               | Maximum Skew<br>Pin (Signal) Transition<br>Variation<br>CP <sub>n</sub> to Output Path        |                   | 90   |                     | 90   |                     | 90   | ps    | PCC Only<br>(Note 4)                              |                 |

**Note 4:** Output-to-Output Skew is defined as the absolute value of the difference between the actual propagation delay for any outputs within the same packaged device. The specifications apply to any outputs switching in the same direction either HIGH to LOW ( $t_{OSHL}$ ), or LOW to HIGH ( $t_{OSLH}$ ), or in opposite directions both HL and LH ( $t_{OST}$ ). Parameters  $t_{OST}$  and  $t_{ps}$  guaranteed by design.

## Industrial Version

### PCC DC Electrical Characteristics

$V_{EE} = -4.2V$  to  $-5.7V$ ,  $V_{CC} = V_{CCA} = GND$ ,  $T_C = -40^{\circ}C$  to  $+85^{\circ}C$  (Note 5)

| Symbol           | Parameter            | T <sub>C</sub> = -40°C |       | T <sub>C</sub> = 0°C to +85°C |       | Units | Conditions                                                          |                              |
|------------------|----------------------|------------------------|-------|-------------------------------|-------|-------|---------------------------------------------------------------------|------------------------------|
|                  |                      | Min                    | Max   | Min                           | Max   |       |                                                                     |                              |
| V <sub>OH</sub>  | Output HIGH Voltage  | -1085                  | -870  | -1025                         | -870  | mV    | V <sub>IN</sub> = V <sub>IH</sub> (Max)<br>or V <sub>IL</sub> (Min) | Loading with<br>50Ω to -2.0V |
| V <sub>OL</sub>  | Output LOW Voltage   | -1830                  | -1575 | -1830                         | -1620 | mV    |                                                                     |                              |
| V <sub>OHC</sub> | Output HIGH Voltage  | -1095                  |       | -1035                         |       | mV    | V <sub>IN</sub> = V <sub>IH</sub> (Min)<br>or V <sub>IL</sub> (Max) | Loading with<br>50Ω to -2.0V |
| V <sub>OLC</sub> | Output LOW Voltage   |                        | -1565 |                               | -1610 | mV    |                                                                     |                              |
| V <sub>IH</sub>  | Input HIGH Voltage   | -1170                  | -870  | -1165                         | -870  | mV    | Guaranteed HIGH Signal<br>for All Inputs                            |                              |
| V <sub>IL</sub>  | Input LOW Voltage    | -1830                  | -1480 | -1830                         | 1475  | mV    | Guaranteed LOW Signal<br>for All Inputs                             |                              |
| I <sub>IL</sub>  | Input LOW Current    | 0.5                    |       | 0.5                           |       | μA    | V <sub>IN</sub> = V <sub>IL</sub> (Min)                             |                              |
| I <sub>IH</sub>  | Input HIGH Current   |                        | 300   |                               | 240   | μA    | V <sub>IN</sub> = V <sub>IH</sub> (Max)                             |                              |
| I <sub>EE</sub>  | Power Supply Current | -122                   | -60   | -122                          | -65   | mA    | Inputs Open                                                         |                              |

**Note 5:** The specified limits represent the "worst case" value for the parameter. Since these values normally occur at the temperature extremes, additional noise immunity and guardbanding can be achieved by decreasing the allowable system operating ranges. Conditions for testing shown in the tables are chosen to guarantee operation under "worst case" conditions.

### PCC AC Electrical Characteristics

$V_{EE} = -4.2V$  to  $-5.7V$ ,  $V_{CC} = V_{CCA} = GND$

| Symbol             | Parameter                                             | T <sub>C</sub> = −40°C |      | T <sub>C</sub> = +25°C |      | T <sub>C</sub> = +85°C |      | Units | Conditions                            |              |
|--------------------|-------------------------------------------------------|------------------------|------|------------------------|------|------------------------|------|-------|---------------------------------------|--------------|
|                    |                                                       | Min                    | Max  | Min                    | Max  | Min                    | Max  |       |                                       |              |
| f <sub>max</sub>   | Toggle Frequency                                      | 375                    |      | 400                    |      | 400                    |      | MHz   | Figures 2, 3                          |              |
| t <sub>PLH</sub>   | Propagation Delay                                     | 0.75                   | 1.80 | 0.75                   | 1.80 | 0.75                   | 1.80 | ns    | Figures 1, 3                          |              |
| t <sub>PHL</sub>   | CP <sub>C</sub> to Output                             |                        |      |                        |      |                        |      |       |                                       |              |
| t <sub>PLH</sub>   | Propagation Delay                                     | 0.70                   | 1.80 | 0.75                   | 1.80 | 0.75                   | 1.80 | ns    |                                       |              |
| t <sub>PHL</sub>   | CP <sub>n</sub> to Output                             |                        |      |                        |      |                        |      |       |                                       |              |
| t <sub>PLH</sub>   | Propagation Delay                                     | 0.60                   | 1.50 | 0.70                   | 1.50 | 0.70                   | 1.60 | ns    | CP <sub>n</sub> , CP <sub>C</sub> = L | Figures 1, 4 |
| t <sub>PHL</sub>   | CD <sub>n</sub> , SD <sub>n</sub> to Output           |                        |      |                        |      |                        |      |       | CP <sub>n</sub> , CP <sub>C</sub> = H |              |
| t <sub>PLH</sub>   | Propagation Delay<br>MS, MR to Output                 | 0.70                   | 1.80 | 0.70                   | 1.80 | 0.70                   | 1.80 | ns    |                                       |              |
| t <sub>PHL</sub>   |                                                       |                        |      |                        |      |                        |      |       |                                       |              |
| t <sub>PLH</sub>   |                                                       |                        |      |                        |      |                        |      |       |                                       |              |
| t <sub>PHL</sub>   |                                                       |                        |      |                        |      |                        |      |       |                                       |              |
| t <sub>PLH</sub>   | Propagation Delay<br>MS, MR to Output                 | 1.10                   | 2.40 | 1.10                   | 2.40 | 1.10                   | 2.40 | ns    | CP <sub>n</sub> , CP <sub>C</sub> = L |              |
| t <sub>PHL</sub>   |                                                       |                        |      |                        |      |                        |      |       |                                       |              |
| t <sub>PLH</sub>   |                                                       | 1.10                   | 2.60 | 1.10                   | 2.60 | 1.10                   | 2.60 |       | CP <sub>n</sub> , CP <sub>C</sub> = H |              |
| t <sub>PHL</sub>   |                                                       |                        |      |                        |      |                        |      |       |                                       |              |
| t <sub>TLH</sub>   | Transition Time                                       | 0.20                   | 1.40 | 0.35                   | 1.10 | 0.35                   | 1.10 | ns    | Figures 1, 3, 4                       |              |
| t <sub>THL</sub>   | 20% to 80%, 80% to 20%                                |                        |      |                        |      |                        |      |       |                                       |              |
| t <sub>S</sub>     | Setup Time                                            |                        |      |                        |      |                        |      |       | Figure 5                              |              |
|                    | D <sub>n</sub>                                        | 1.00                   |      | 0.30                   |      | 0.30                   |      | ns    |                                       |              |
|                    | CD <sub>n</sub> , SD <sub>n</sub> (Release Time)      | 1.50                   |      | 1.20                   |      | 1.20                   |      |       | Figure 4                              |              |
|                    | MS, MR (Release Time)                                 | 2.50                   |      | 2.20                   |      | 2.20                   |      |       |                                       |              |
| t <sub>H</sub>     | Hold Time D <sub>n</sub>                              | 0.7                    |      | 0.5                    |      | 0.7                    |      | ns    | Figure 5                              |              |
| t <sub>pw(H)</sub> | Pulse Width HIGH                                      |                        |      |                        |      |                        |      |       |                                       |              |
|                    | CP <sub>n</sub> , CP <sub>C</sub> , CD <sub>n</sub> , | 2.00                   |      | 2.00                   |      | 2.00                   |      | ns    | Figures 3, 4                          |              |
|                    | SD <sub>n</sub> , MR, MS                              |                        |      |                        |      |                        |      |       |                                       |              |



## Military Version

### DC Electrical Characteristics

$V_{EE} = -4.2V$  to  $-5.7V$ ,  $V_{CC} = V_{CCA} = GND$ ,  $T_C = -55^{\circ}C$  to  $+125^{\circ}C$

| Symbol           | Parameter            | Min   | Max   | Units | T <sub>C</sub>  | Conditions                                                          |                           | Notes              |                                                                     |                           |                 |
|------------------|----------------------|-------|-------|-------|-----------------|---------------------------------------------------------------------|---------------------------|--------------------|---------------------------------------------------------------------|---------------------------|-----------------|
| V <sub>OH</sub>  | Output HIGH Voltage  | -1025 | -870  | mV    | 0°C to +125°C   | V <sub>IN</sub> = V <sub>IH</sub> (Max)<br>or V <sub>IL</sub> (Min) | Loading with 50Ω to -2.0V | (Notes 6, 7, 8)    |                                                                     |                           |                 |
|                  |                      | -1085 | -870  | mV    | -55°C           |                                                                     |                           |                    |                                                                     |                           |                 |
| V <sub>OL</sub>  | Output LOW Voltage   | -1830 | -1620 | mV    | 0°C to +125°C   |                                                                     |                           |                    | V <sub>IN</sub> = V <sub>IH</sub> (Min)<br>or V <sub>IL</sub> (Max) | Loading with 50Ω to -2.0V | (Notes 6, 7, 8) |
|                  |                      | -1830 | -1555 | mV    | -55°C           |                                                                     |                           |                    |                                                                     |                           |                 |
| V <sub>OHC</sub> | Output HIGH Voltage  | -1035 |       | mV    | 0°C to +125°C   | V <sub>IN</sub> = V <sub>IH</sub> (Min)<br>or V <sub>IL</sub> (Max) | Loading with 50Ω to -2.0V | (Notes 6, 7, 8)    |                                                                     |                           |                 |
|                  |                      | -1085 |       | mV    | -55°C           |                                                                     |                           |                    |                                                                     |                           |                 |
| V <sub>OLC</sub> | Output LOW Voltage   |       | -1610 | mV    | 0°C to +125°C   |                                                                     |                           |                    | V <sub>IN</sub> = V <sub>IH</sub> (Min)<br>or V <sub>IL</sub> (Max) | Loading with 50Ω to -2.0V | (Notes 6, 7, 8) |
|                  |                      |       | -1555 | mV    | -55°C           |                                                                     |                           |                    |                                                                     |                           |                 |
| V <sub>IH</sub>  | Input HIGH Voltage   | -1165 | -870  | mV    | -55°C to +125°C | Guaranteed HIGH Signal for all Inputs                               |                           | (Notes 6, 7, 8, 9) |                                                                     |                           |                 |
| V <sub>IL</sub>  | Input LOW Voltage    | -1830 | -1475 | mV    | -55°C to +125°C | Guaranteed LOW Signal for all Inputs                                |                           | (Notes 6, 7, 8, 9) |                                                                     |                           |                 |
| I <sub>IL</sub>  | Input LOW Current    | 0.50  |       | μA    | -55°C to +125°C | V <sub>EE</sub> = -4.2V<br>V <sub>IN</sub> = V <sub>IL</sub> (Min)  |                           | (Notes 6, 7, 8)    |                                                                     |                           |                 |
| I <sub>IH</sub>  | Input HIGH Current   |       | 240   | μA    | 0°C to +125°C   | V <sub>EE</sub> = -5.7V<br>V <sub>IN</sub> = V <sub>IH</sub> (Max)  |                           | (Notes 6, 7, 8)    |                                                                     |                           |                 |
|                  |                      |       | 340   | μA    | -55°C           |                                                                     |                           |                    |                                                                     |                           |                 |
| I <sub>EE</sub>  | Power Supply Current | -130  | -50   | mA    | -55°C to +125°C | Inputs Open                                                         |                           | (Notes 6, 7, 8)    |                                                                     |                           |                 |

**Note 6:** F100K 300 Series cold temperature testing is performed by temperature soaking (to guarantee junction temperature equals  $-55^{\circ}C$ ), then testing immediately without allowing for the junction temperature to stabilize due to heat dissipation after power-up. This provides "cold start" specs which can be considered a worst case condition at cold temperatures.

**Note 7:** Screen tested 100% on each device at  $-55^{\circ}C$ ,  $+25^{\circ}C$ , and  $+125^{\circ}C$ , Subgroups, 1, 2, 3, 7 and 8.

**Note 8:** Sampled tested (Method 5005, Table I) on each manufactured lot at  $-55^{\circ}C$ ,  $+25^{\circ}C$ , and  $+125^{\circ}C$ , Subgroups A1, 2, 3, 7 and 8.

**Note 9:** Guaranteed by applying specified input condition and testing  $V_{OH}/V_{OL}$ .

## AC Electrical Characteristics

$V_{EE} = -4.2V$  to  $-5.7V$ ,  $V_{CC} = V_{CCA} = GND$

| Symbol                               | Parameter                                                                                             | T <sub>C</sub> = −55°C |      | T <sub>C</sub> = +25°C |      | T <sub>C</sub> = +125°C |      | Units | Conditions                            |              | Notes              |
|--------------------------------------|-------------------------------------------------------------------------------------------------------|------------------------|------|------------------------|------|-------------------------|------|-------|---------------------------------------|--------------|--------------------|
|                                      |                                                                                                       | Min                    | Max  | Min                    | Max  | Min                     | Max  |       |                                       |              |                    |
| f <sub>max</sub>                     | Toggle Frequency                                                                                      | 400                    |      | 400                    |      | 400                     |      | MHz   | Figures 2, 3                          |              | (Note 13)          |
| t <sub>PLH</sub><br>t <sub>PHL</sub> | Propagation Delay<br>CP <sub>C</sub> to Output                                                        | 0.50                   | 2.20 | 0.60                   | 2.00 | 0.50                    | 2.40 | ns    | Figures 1, 3                          |              | (Notes 10, 11, 12) |
| t <sub>PLH</sub><br>t <sub>PHL</sub> | Propagation Delay<br>CP <sub>n</sub> to Output                                                        | 0.50                   | 2.20 | 0.60                   | 2.00 | 0.50                    | 2.40 | ns    |                                       |              |                    |
| t <sub>PLH</sub><br>t <sub>PHL</sub> | Propagation Delay<br>CD <sub>n</sub> , SD <sub>n</sub> to Output                                      | 0.50                   | 2.20 | 0.60                   | 2.00 | 0.50                    | 2.40 | ns    | CP <sub>n</sub> , CP <sub>C</sub> = L | Figures 1, 4 |                    |
| t <sub>PLH</sub><br>t <sub>PHL</sub> |                                                                                                       | 0.50                   | 2.40 | 0.60                   | 2.10 | 0.50                    | 2.50 |       | CP <sub>n</sub> , CP <sub>C</sub> = H |              |                    |
| t <sub>PLH</sub><br>t <sub>PHL</sub> | Propagation Delay<br>MS, MR to Output                                                                 | 0.70                   | 2.70 | 0.80                   | 2.60 | 0.80                    | 2.90 | ns    | CP <sub>n</sub> , CP <sub>C</sub> = L |              |                    |
| t <sub>PLH</sub><br>t <sub>PHL</sub> |                                                                                                       | 0.70                   | 2.90 | 0.80                   | 2.80 | 0.80                    | 3.10 |       | CP <sub>n</sub> , CP <sub>C</sub> = H |              |                    |
| t <sub>TLH</sub><br>t <sub>THL</sub> | Transition Time<br>20% to 80%, 80% to 20%                                                             | 0.20                   | 1.40 | 0.20                   | 1.40 | 0.20                    | 1.40 | ns    | Figures 1, 3, 4                       |              |                    |
| t <sub>s</sub>                       | Setup Time                                                                                            |                        |      |                        |      |                         |      |       | Figure 5                              |              | (Note 13)          |
|                                      | D <sub>n</sub>                                                                                        | 1.00                   |      | 0.80                   |      | 0.90                    |      | ns    |                                       |              |                    |
|                                      | CD <sub>n</sub> , SD <sub>n</sub> (Release Time)<br>MS, MR (Release Time)                             | 1.50<br>2.50           |      | 1.30<br>2.30           |      | 1.60<br>2.50            |      |       | Figure 4                              |              |                    |
| t <sub>h</sub>                       | Hold Time D <sub>n</sub>                                                                              | 1.50                   |      | 1.30                   |      | 1.60                    |      | ns    | Figure 5                              |              |                    |
| t <sub>pw(H)</sub>                   | Pulse Width HIGH<br>CP <sub>n</sub> , CP <sub>C</sub> , CD <sub>n</sub> ,<br>SD <sub>n</sub> , MR, MS | 2.00                   |      | 2.00                   |      | 2.00                    |      | ns    | Figures 3, 4                          |              |                    |


**Note 10:** F100K 300 Series cold temperature testing is performed by temperature soaking (to guarantee junction temperature equals  $-55^\circ C$ ), then testing immediately without allowing for the junction temperature to stabilize due to heat dissipation after power-up. This provides "cold start" specs which can be considered a worst case condition at cold temperatures.

**Note 11:** Screen tested 100% on each device at  $+25^\circ C$ . Temperature only, Subgroup A9.

**Note 12:** Sample tested (Method 5005, Table I) on each Mfg. lot at  $+25^\circ C$ , Subgroup A9, and at  $+125^\circ C$ , and  $-55^\circ C$  Temp., Subgroups A10 and A11.


**Note 13:** Not tested at  $+25^\circ C$ ,  $+125^\circ C$  and  $-55^\circ C$  Temperature (design characterization data).

## Test Circuits



DS010262-6

FIGURE 1. AC Test Circuit



DS010262-7

### Notes:

$V_{CC}, V_{CCA} = +2V, V_{EE} = -2.5V$

$L1$  and  $L2$  = Equal length 50 $\Omega$  impedance lines

$R_T = 50\Omega$  terminator internal to scope


Decoupling 0.1  $\mu F$  from GND to  $V_{CC}$  and  $V_{EE}$

All unused outputs are loaded with 50 $\Omega$  to GND


$C_L$  = Fixture and stray capacitance  $\leq 3$  pF

FIGURE 2. Toggle Frequency Test Circuit


## Switching Waveforms



**FIGURE 3. Propagation Delay (Clock) and Transition Times**



**FIGURE 4. Propagation Delay (Resets)**




**FIGURE 5. Data Setup and Hold Time**

**Note 14:**  $t_s$  is the minimum time before the transition of the clock that information must be present at the data input.

**Note 15:**  $t_h$  is the minimum time after the transition of the clock that information must remain unchanged at the data input.


## Ordering Information

The device number is used to form part of a simplified purchasing code where a package type and temperature range are defined as follows:




DS010262-11

**Physical Dimensions** inches (millimeters) unless otherwise noted




**24-Lead Ceramic Dual-In-Line Package (0.400" Wide) (D)**  
**Package Number J24E**




**24-Lead Molded Package (0.300" Wide) (S)**  
**Package Number M24B**

## Physical Dimensions inches (millimeters) unless otherwise noted (Continued)




**24-Lead Plastic Dual-In-Line Package (P)**  
**Package Number N24E**



**28-Lead Plastic Chip Carrier (Q)**  
**Package Number V28A**

## Physical Dimensions inches (millimeters) unless otherwise noted (Continued)



W24B (REV D)

24-Lead Quad Cerpak (F)  
Package Number W24B

### LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Fairchild Semiconductor  
Corporation  
Americas  
Customer Response Center  
Tel: 1-888-522-5372

Fairchild Semiconductor  
Europe  
Fax: +49 (0) 1 80-530 85 86  
Email: europe.support@nsc.com  
Deutsch Tel: +49 (0) 8 141-35-0  
English Tel: +44 (0) 1 793-85-68-56  
Italy Tel: +39 (0) 2 57 5631

Fairchild Semiconductor  
Hong Kong Ltd.  
13th Floor, Straight Block,  
Ocean Centre, 5 Canton Rd.  
Tsimshatsui, Kowloon  
Hong Kong  
Tel: +852 2737-7200  
Fax: +852 2314-0061

National Semiconductor  
Japan Ltd.  
Tel: 81-3-5620-6175  
Fax: 81-3-5620-6179

[www.fairchildsemi.com](http://www.fairchildsemi.com)