



SN74HC/HCT279 (LX)

Quad $\overline{R}/\overline{S}$ Latches

Product Specification

Specification Revision History:

Version	Date	Description
2024-04-A0	2024-04	New
2024-09-A1	2024-09	Modify the parameters



Contents

1、General Description.....	1
2、Block Diagram And Pin Description	3
2.1、Block Diagram	3
2.2、Pin Configurations.....	3
2.3、Pin Description.....	4
2.3、Function Table.....	4
3、Electrical Parameter	5
3.1、Absolute Maximum Ratings.....	5
3.2、Recommended Operating Conditions.....	5
3.3、Electrical Characteristics.....	6
3.3.1、DC Characteristics 1	6
3.3.2、DC Characteristics 2.....	7
3.3.3、AC Characteristics 1.....	8
3.3.4、AC Characteristics 2.....	9
4、Testing Circuit.....	10
4.1、AC Testing Circuit	10
4.2、Test Data	10
4.3、AC Testing Waveforms.....	11
4.4、Measurement Points	11
5、Package Information.....	12
5.1、DIP16	12
5.2、SOP16	13
5.3、TSSOP16.....	14
6、Statements And Notes	15
6.1、The name and content of Hazardous substances or Elements in the product	15
6.2、Notes	15



1、General Description

The SN74HC/HCT279 is a quad $\overline{R}-\overline{S}$ latches.

Features:

- Supply voltage range:
SN74HC279: 2V to 6V
HCT279: 4.5V to 5.5V
- Input levels:
SN74HC279: CMOS level
HCT279: TTL level
- Temperature range: -40°C to +125°C
- Packaging information: DIP16/SOP16/TSSOP16

Ordering Information:

Tube packing specifications:

Part number	Packaging form	Marking code	Tube quantity	Boxed tube quantity	Boxed quantity	Notes
SN74HC279AN(LX)	DIP16	SN74HC279AN	25 PCS/tube	40 tube/box	1000 PCS/box	Dimensions of plastic enclosure: 19.0mm × 6.4mm Pin spacing: 2.54mm
SN74HCT279AN(LX)	DIP16	SN74HCT279AN	25 PCS/tube	40 tube/box	1000 PCS/box	Dimensions of plastic enclosure: 19.0mm × 6.4mm Pin spacing: 2.54mm

**Reel packing specifications:**

Part number	Packaging form	Marking code	Reel quantity	Boxed reel quantity	Notes
SN74HC279ADR(LX)	SOP16	HC279A	2500 PCS/reel	5000 PCS/box	Dimensions of plastic enclosure: 10.0mm×3.9mm Pin spacing: 1.27mm
SN74HCT279ADR(LX)	SOP16	HCT279A	2500 PCS/reel	5000 PCS/box	Dimensions of plastic enclosure: 10.0mm×3.9mm Pin spacing: 1.27mm
SN74HC279APW(LX)	TSSOP16	HC279A	5000 PCS/reel	10000 PCS/box	Dimensions of plastic enclosure: 5.0mm×4.4mm Pin spacing: 0.65mm
SN74HCT279APW(LX)	TSSOP16	HCT279A	5000 PCS/reel	10000 PCS/box	Dimensions of plastic enclosure: 5.0mm×4.4mm Pin spacing: 0.65mm

Note: If the physical information is inconsistent with the ordering information, please refer to the actual product.



2、Block Diagram And Pin Description

2.1、Block Diagram




Figure 1. Block Diagram

2.2、Pin Configurations

1R	1	16	V _{CC}
1S1	2	15	4S
1S2	3	14	4R
1Q	4	13	4Q
2R	5	12	3S2
2S	6	11	3S1
2Q	7	10	3R
GND	8	9	3Q



2.3、Pin Description

Pin No.	Pin Name	Description
1	$\overline{1R}$	data input
2	1S1	data input
3	1S2	data input
4	1Q	data output
5	$\overline{2R}$	data input
6	2S	data input
7	2Q	data output
8	GND	ground (0V)
9	3Q	data output
10	$\overline{3R}$	data input
11	3S1	data input
12	3S2	data input
13	4Q	data output
14	$\overline{4R}$	data input
15	4S	data input
16	V _{CC}	supply voltage

2.3、Function Table

Input		Output
$\overline{S}^{[1]}$	$\overline{R}$	Q
H	H	Q0 ^[2]
L	H	H
H	L	L
L	L	H

Note:

H=HIGH voltage level; L=LOW voltage level.

[1] For latches with doubles $\overline{S}$ input, H=both of $\overline{S}$ inputs are high; L=either or both of $\overline{S}$ are low.

[2] Q0: The level of Q before the indicated input condition were established.



3、Electrical Parameter

3.1、Absolute Maximum Ratings

(Voltages are referenced to GND (ground=0V), unless otherwise specified.)

Parameter	Symbol	Conditions	Min.	Max.	Unit
supply voltage	V_{CC}	-	-0.5	+7	V
supply current	I_{CC}	-	-	50	mA
ground current	I_{GND}	-	-50	-	mA
input clamping current	I_{IK}	$V_I < -0.5V$ or $V_I > V_{CC}+0.5V$	-	± 20	mA
output clamping current	I_{OK}	$V_O < -0.5V$ or $V_O > V_{CC}+0.5V$	-	± 20	mA
output current	I_O	$-0.5V < V_O < V_{CC}+0.5V$	-	± 25	mA
storage temperature	T_{stg}	-	-65	+150	$^{\circ}C$
soldering temperature	T_L	10s	DIP		245
			SOP/TSSOP		260
					$^{\circ}C$

3.2、Recommended Operating Conditions

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
SN74HC279						
supply voltage	V_{CC}	-	2.0	5.0	6.0	V
input voltage	V_I	-	0	-	V_{CC}	V
output voltage	V_O	-	0	-	V_{CC}	V
ambient temperature	T_{amb}	-	-40	-	+125	$^{\circ}C$
SN74HCT279						
supply voltage	V_{CC}	-	4.5	5.0	5.5	V
input voltage	V_I	-	0	-	V_{CC}	V
output voltage	V_O	-	0	-	V_{CC}	V
ambient temperature	T_{amb}	-	-40	-	+125	$^{\circ}C$



3.3、Electrical Characteristics

3.3.1、DC Characteristics 1

($T_{amb} = -40^{\circ}\text{C}$ to $+85^{\circ}\text{C}$, voltages are referenced to GND (ground=0V), unless otherwise specified.)

Parameter	Symbol	V_{CC}	Conditions	Min.	Typ.	Max.	Unit
SN74HC279							
HIGH-level input voltage	V_{IH}	2.0V	-	1.5	1.2	-	V
		4.5V	-	3.15	2.4	-	V
		6.0V	-	4.2	3.2	-	V
LOW-level input voltage	V_{IL}	2.0V	-	-	0.8	0.5	V
		4.5V	-	-	2.1	1.35	V
		6.0V	-	-	2.8	1.8	V
HIGH-level output voltage	V_{OH}	2.0V	$I_O = -20\mu\text{A}$	1.9	2.0	-	V
		4.5V	$I_O = -20\mu\text{A}$	4.4	4.5	-	V
		6.0V	$I_O = -20\mu\text{A}$	5.9	6.0	-	V
		4.5V	$I_O = -4.0\text{mA}$	3.84	4.32	-	V
		6.0V	$I_O = -5.2\text{mA}$	5.34	5.81	-	V
LOW-level output voltage	V_{OL}	2.0V	$I_O = 20\mu\text{A}$	-	0	0.1	V
		4.5V	$I_O = 20\mu\text{A}$	-	0	0.1	V
		6.0V	$I_O = 20\mu\text{A}$	-	0	0.1	V
		4.5V	$I_O = 4.0\text{mA}$	-	0.15	0.33	V
		6.0V	$I_O = 5.2\text{mA}$	-	0.16	0.33	V
input leakage current	I_I	6.0V	$V_I = V_{CC}$ or GND	-	-	± 2	μA
supply current	I_{CC}	6.0V	$V_I = V_{CC}$ or GND; $I_O = 0\text{A}$	-	-	2	μA
SN74HCT279							
HIGH-level input voltage	V_{IH}	4.5~5.5V	-	2.0	1.6	-	V
LOW-level input voltage	V_{IL}	4.5~5.5V	-	-	1.2	0.8	V
HIGH-level output voltage	V_{OH}	4.5V	$I_O = -20\mu\text{A}$	4.4	4.5	-	V
			$I_O = -4.0\text{mA}$	3.84	4.32	-	V
LOW-level output voltage	V_{OL}	4.5V	$I_O = 20\mu\text{A}$	-	0	0.1	V
			$I_O = 4.0\text{mA}$	-	0.15	0.33	V
input leakage current	I_I	5.5V	$V_I = V_{CC}$ or GND	-	-	± 2	μA
supply current	I_{CC}	6.0V	$V_I = V_{CC}$ or GND; $I_O = 0\text{A}$	-	-	2	μA
additional supply current	ΔI_{CC}	4.5~5.5V	One input at $V_I = V_{CC} - 2.1\text{V}$; Other inputs at V_{CC} or GND; $I_O = 0\text{A}$	-	-	135	μA



3.3.2、DC Characteristics 2

(T_{amb}=-40℃ to +125℃, voltages are referenced to GND (ground=0V), unless otherwise specified.)

Parameter	Symbol	V _{CC}	Conditions	Min.	Typ.	Max.	Unit
SN74HC279							
HIGH-level input voltage	V _{IH}	2.0V	-	1.5	-	-	V
		4.5V	-	3.15	-	-	V
		6.0V	-	4.2	-	-	V
LOW-level input voltage	V _{IL}	2.0V	-	-	-	0.5	V
		4.5V	-	-	-	1.35	V
		6.0V	-	-	-	1.8	V
HIGH-level output voltage	V _{OH}	2.0V	I _O =-20uA	1.9	-	-	V
		4.5V	I _O =-20uA	4.4	-	-	V
		6.0V	I _O =-20uA	5.9	-	-	V
		4.5V	I _O =-4.0mA	3.7	-	-	V
		6.0V	I _O =-5.2mA	5.2	-	-	V
LOW-level output voltage	V _{OL}	2.0V	I _O =20uA	-	-	0.1	V
		4.5V	I _O =20uA	-	-	0.1	V
		6.0V	I _O =20uA	-	-	0.1	V
		4.5V	I _O =4.0mA	-	-	0.4	V
		6.0V	I _O =5.2mA	-	-	0.4	V
input leakage current	I _I	6.0V	V _I =V _{CC} or GND	-	-	±4	uA
supply current	I _{CC}	6.0V	V _I =V _{CC} or GND; I _O =0A	-	-	4	uA
SN74HCT279							
HIGH-level input voltage	V _{IH}	4.5~5.5V	-	2.0	-	-	V
LOW-level input voltage	V _{IL}	4.5~5.5V	-	-	-	0.8	V
HIGH-level output voltage	V _{OH}	4.5V	I _O =-20uA	4.4	-	-	V
			I _O =-4.0mA	3.7	-	-	V
LOW-level output voltage	V _{OL}	4.5V	I _O =20uA	-	-	0.1	V
			I _O =4.0mA	-	-	0.4	V
input leakage current	I _I	5.5V	V _I =V _{CC} or GND	-	-	±4	uA
supply current	I _{CC}	6.0V	V _I =V _{CC} or GND; I _O =0A	-	-	4	uA
additional supply current	ΔI _{CC}	4.5~5.5V	One input at V _I =V _{CC} -2.1V; Other inputs at V _{CC} or GND; I _O =0A	-	-	147	uA



3.3.3、AC Characteristics 1

($T_{amb} = -40^{\circ}\text{C}$ to $+85^{\circ}\text{C}$, voltages are referenced to GND (ground=0V), unless otherwise specified.)

Parameter	Symbol	V _{CC}	Conditions	Min.	Typ.	Max.	Unit	
SN74HC279								
propagation delay, $\bar{S}1$, $\bar{S}2$ to Q	t_{PLH} , t_{PHL}	2.0V	$C_L=50\text{pF}$	see Figure 4	-	-	165	ns
		4.5V	$C_L=50\text{pF}$		-	-	33	ns
		5.0V	$C_L=15\text{pF}$		-	-	22	ns
		6.0V	$C_L=50\text{pF}$		-	-	28	ns
propagation delay, $\bar{S}$ to Q	t_{PLH} , t_{PHL}	2.0V	$C_L=50\text{pF}$	see Figure 4	-	-	125	ns
		4.5V	$C_L=50\text{pF}$		-	-	25	ns
		5.0V	$C_L=15\text{pF}$		-	-	17	ns
		6.0V	$C_L=50\text{pF}$		-	-	21	ns
propagation delay, $\bar{R}$ to Q	t_{PLH} , t_{PHL}	2.0V	$C_L=50\text{pF}$	see Figure 4	-	-	150	ns
		4.5V	$C_L=50\text{pF}$		-	-	30	ns
		5.0V	$C_L=15\text{pF}$		-	-	20	ns
		6.0V	$C_L=50\text{pF}$		-	-	26	ns
transition time	t_{THL} , t_{TLH}	2.0V	$C_L=50\text{pF}$	see Figure 4	-	-	95	ns
		4.5V	$C_L=50\text{pF}$		-	-	19	ns
		6.0V	$C_L=50\text{pF}$		-	-	16	ns
SN74HCT279								
propagation delay, $\bar{S}1$, $\bar{S}2$ to Q	t_{PLH} , t_{PHL}	4.5V	$C_L=50\text{pF}$	see Figure 4	-	-	33	ns
		5.0V	$C_L=15\text{pF}$		-	-	22	ns
propagation delay, $\bar{S}$ to Q	t_{PLH} , t_{PHL}	4.5V	$C_L=50\text{pF}$	see Figure 4	-	-	25	ns
		5.0V	$C_L=15\text{pF}$		-	-	17	ns
propagation delay, $\bar{R}$ to Q	t_{PLH} , t_{PHL}	4.5V	$C_L=50\text{pF}$	see Figure 4	-	-	30	ns
		5.0V	$C_L=15\text{pF}$		-	-	20	ns
transition time	t_{THL} , t_{TLH}	4.5V	$C_L=50\text{pF}$	see Figure 4	-	-	19	ns

**3.3.4、AC Characteristics 2**(T_{amb}=-40°C to +125°C, voltages are referenced to GND (ground=0V), unless otherwise specified.)

Parameter	Symbol	V _{CC}	Conditions		Min.	Typ.	Max.	Unit
SN74HC279								
propagation delay, $\bar{S}1$, $\bar{S}2$ to Q	t_{PLH} , t_{PHL}	2.0V	$C_L=50pF$	see Figure 4	-	-	182	ns
		4.5V	$C_L=50pF$		-	-	36	ns
		6.0V	$C_L=50pF$		-	-	31	ns
propagation delay, $\bar{S}$ to Q	t_{PLH} , t_{PHL}	2.0V	$C_L=50pF$	see Figure 4	-	-	138	ns
		4.5V	$C_L=50pF$		-	-	28	ns
		6.0V	$C_L=50pF$		-	-	23	ns
propagation delay, $\bar{R}$ to Q	t_{PLH} , t_{PHL}	2.0V	$C_L=50pF$	see Figure 4	-	-	165	ns
		4.5V	$C_L=50pF$		-	-	33	ns
		6.0V	$C_L=50pF$		-	-	29	ns
transition time	t_{THL} , t_{TLH}	2.0V	$C_L=50pF$	see Figure 4	-	-	105	ns
		4.5V	$C_L=50pF$		-	-	21	ns
		6.0V	$C_L=50pF$		-	-	18	ns
SN74HCT279								
propagation delay, $\bar{S}1$, $\bar{S}2$ to Q	t_{PLH} , t_{PHL}	4.5V	$C_L=50pF$	see Figure 4	-	-	36	ns
propagation delay, $\bar{S}$ to Q	t_{PLH} , t_{PHL}	4.5V	$C_L=50pF$	see Figure 4	-	-	28	ns
propagation delay, $\bar{R}$ to Q	t_{PLH} , t_{PHL}	4.5V	$C_L=50pF$	see Figure 4	-	-	33	ns
transition time	t_{THL} , t_{TLH}	4.5V	$C_L=50pF$	see Figure 4	-	-	21	ns



4、Testing Circuit

4.1、AC Testing Circuit




Figure 3. Test circuit for measuring switching times

C_L includes probe and jig capacitance.

4.2、Test Data

Type	Input		Load		V_{EXT}		
	V_I	$t_r = t_f$	C_L	R_L	t_{PLH}/t_{PHL}	t_{PLZ}/t_{PZL}	t_{PHZ}/t_{PZH}
SN74HC279	V_{CC}	3.0ns	15pF, 50pF	1K Ω	Open	V_{CC}	GND
SN74HCT279	3.0V	3.0ns	15pF, 50pF	1K Ω	Open	V_{CC}	GND



灵星芯微 用心经营

4.3、AC Testing Waveforms




Figure 4. Propagation delay, output transition time

4.4、Measurement Points

Type	Input	Output
	V_M	V_M
SN74HC279	$0.5 \times V_{CC}$	$0.5 \times V_{CC}$
SN74HCT279	1.3V	1.3V



灵星芯微 专注经营


深圳市灵星芯微电子科技有限公司

Shenzhen Lingxing Microelectronics Technology Co., Ltd.

Tab: 835-12-B5

5、Package Information

5.1、DIP16




2023/12/A	Dimensions In Millimeters	
Symbol	Min	Max
A2	3.00	3.60
A1	0.51	—
A	3.60	5.33
L	3.00	3.60
b	0.36	0.56
B1	1.52	
D	18.80	19.94
E1	6.20	6.60
e	2.54	
c	0.20	0.36
eB	7.62	9.30



灵星芯微 用户手册

5.2、SOP16



2023/12/A	Dimensions In Millimeters	
Symbol	Min.	Max.
A	1.35	1.80
A1	0.10	0.25
A2	1.25	1.55
b	0.33	0.51
c	0.19	0.25
D	9.50	10.10
E	5.80	6.30
E1	3.70	4.10
e	1.27	
L	0.35	0.89
θ	0°	8°






灵星芯微 专注经营

深圳市灵星芯微电子科技有限公司

Shenzhen Lingxing Microelectronics Technology Co., Ltd.

Tab: 835-12-B5

5.3、TSSOP16



2023/12/A	Dimensions In Millimeters	
	Min	Max
A	—	1.20
A1	0.05	0.15
A2	0.80	1.05
b	0.19	0.30
c	0.09	0.20
D	4.90	5.10
E1	4.30	4.50
E	6.20	6.60
e	0.65	
L	0.45	0.75
θ	0°	8°



6、Statements And Notes

6.1、The name and content of Hazardous substances or Elements in the product

Part name	Hazardous substances or Elements									
	Lead and lead compounds	Mercury and mercury compounds	Cadmium and cadmium compounds	Hexavalent chromium compounds	Polybrominated biphenyls	Polybrominated biphenyl ethers	Dibutyl phthalate	Butylbenzyl phthalate	Di-2-ethylhexyl phthalate	Diisobutyl phthalate
Lead frame	○	○	○	○	○	○	○	○	○	○
Plastic resin	○	○	○	○	○	○	○	○	○	○
Chip	○	○	○	○	○	○	○	○	○	○
The lead	○	○	○	○	○	○	○	○	○	○
Plastic sheet installed	○	○	○	○	○	○	○	○	○	○
explanation	○: Indicates that the content of hazardous substances or elements in the detection limit of the following the SJ/T11363-2006 standard. ×: Indicates that the content of hazardous substances or elements exceeding the SJ/T11363-2006 Standard limit requirements.									

6.2、Notes

We recommend you to read this chapter carefully before using this product.

The information in this chapter is provided for reference only and Lingxing disclaims any express or implied warranties, including but not limited to applicability, special application or non-infringement of third party rights.

This product is not suitable for critical equipment such as life-saving, life-sustaining or safety equipment. It is also not suitable for applications that may result in personal injury, death, or serious property or environmental damage due to product malfunction or failure. Lingxing will not be liable for any damages incurred by the customers at their own risk for such applications.

The customer is responsible for conducting all necessary tests Lingxing's application to avoid failure in the application or the application of the customer's third party users. Lingxing does not accept any liability.

The Company reserves the right to change or improve the information published in this chapter at any time. The information in this chapter are subject to change without notice. We recommend the customer to consult our sales staff before purchasing.

Please obtain related materials form Lingxing's regular channels and we are not responsible for its content if it is provided by sources other than our company.

In case of any conflict between the Chinese and English version, the version is subject to the Chinese one.