


**HIGH VOLTAGE
SINGLE CONTACT
CONNECTORS
Y, S, E AND 05 SERIES**



Precision modular connectors to suit your application


Since its creation in Switzerland in 1946 the LEMO Group has been recognized as a global leader of circular Push-Pull connectors and connector solutions. Today LEMO and its affiliated companies, REDEL and COELVER, are active in more than 80 countries with the help of over 40 subsidiaries and distributors.

Over 75000 connectors

The modular design of the LEMO range provides over 75000 connectors from miniature \varnothing 3 mm to \varnothing 50 mm, capable of handling cable diameters up to 30 mm and for up to 114 contacts. This vast portfolio enables you to select the ideal connector configuration to suit almost any specific requirement in most markets, including medical devices, test and measurement instruments, machinery, audio video broadcast, telecommunications and military.

LEMO's Push-Pull Self-Latching Connection System



This self-latching system is renowned worldwide for its easy and quick mating and unmating features. It provides absolute security against vibration, shock or pull on the cable, and facilitates operation in a very limited space.



UL Recognition

LEMO connectors are recognized by the Underwriters Laboratories (UL). The approval of the complete system (LEMO connector, cable and your equipment) will be easier because LEMO connectors are recognized.

CE marking

CE marking  means that the appliance or equipment bearing it complies with the protection requirements of one or several European safety directives. CE marking  applies to complete products or equipment, **but not to electromechanical components, such as connectors.**

RoHS

LEMO connector specifications conform to the requirements of the RoHS directive (2011/65/EU) of the European Parliament and the latest amendments. This directive specifies the restrictions of the use of hazardous substances in electrical and electronic equipment marketed in Europe.

Product safety notice & disclaimers

Please read and follow all instructions specified on the last page or on our [website](http://www.lemo.com) carefully and consult all relevant national and international safety regulations for your application. Improper handling, cable assembly, or wrong use of connectors can result in hazardous situations.

LEMO products and services are provided "as is." LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security.

In no event shall LEMO be liable for any direct, indirect, punitive, incidental, special consequential damages, to property or life, whatsoever arising out of or connected with the use or misuse of LEMO's products.

LEMO high voltage connectors (single contact)

LEMO's High Voltage Y series connector have been designed in the 70's for the CERN, European Organization for Nuclear Research, one of the largest and most respected centers for scientific research.

All the series presented in this catalogue (S series, E series, Y series and 05 series) are Push-Pull connectors that offer reliable construction, made of high grade materials. The design of these product increases the creepage distance of the interconnection enabling to guarantee high voltage working conditions

Table of Contents

Y Series

Technical characteristics	6
Part Numbering system	8
Models without safety locking ring	9
Models with safety locking ring	13
Vacuumtight models	15
Insert configuration	17
Collets, Accessories	18
Tooling, Cable assembly	19

S Series

Technical characteristics	21
Part Numbering system	22
Models	23
Watertight or vacuumtight models	28

E Series

Technical characteristics	31
Part Numbering system	32
Models	33
Watertight or vacuumtight models	34

S and E Series

Insert configuration	35
Contacts.....	36
Collets.....	37
Variant	38
Accessories	39

05 Series

Technical characteristics	41
Models	42
Accessories	43
Tooling.....	44
Termination instructions.....	45

Product safety notice	47
-----------------------------	----

Y series (HV single contact)


This family of single contact connectors are high voltage connectors designed for operating voltages ranging from 5 to 50 kV DC. They offer a great deal of security. The long housing permits a mechanical mating long before the contacts are engaged, thus ensuring safe mating. Furthermore, the socket in the series 3Y can be provided with a microswitch to prevent power from being turned on before the plug is mated.

Models without safety locking ring

405-410 type


Models (page 9)

Straight plugs




FFA.1Y


Fixed sockets



ERA.1Y



ERY.1Y



PSA.1Y

415-430 type


Models (page 9)

Straight plugs




FFA.3Y


Fixed sockets



ERA.3Y



ERD.3Y




PSA.3Y


Part Section Showing Internal Components

Fixed socket

- 1 shell
- 2 earthing crown
- 3 castellated nut
- 4 hexagonal ring
- 5 circlip
- 6 insulator
- 7 female contact
- 8 silicone ring
- 9 o-ring



ERA.1Y



FFA.1Y

Straight plug

- 1 outer shell
- 2 inner shell
- 3 latch sleeve
- 4 collet nut
- 5 centre-piece
- 6 insulator
- 7 male contact
- 8 circlip
- 9 collet

Note: other connector shells are available on request.

Requirements in the field of nuclear research have given LEMO the opportunity to design a new generation of high voltage unipole connector in this Y series.

They are mainly characterized by their extremely favourable size/test voltage ratio.

The use of insulating material such as PEEK and silicone rubber in a new design of insulators allows to propose connectors withstanding up to 52 kV DC in the 3Y series.


Models with safety locking ring

416-425 type


Models (page 13)

Straight plug


Fixed sockets




FFR.1Y/3Y



ERA.1Y/3Y




ERA.1Y/3Y




PEP.1Y/3Y

Watertight or vacuumtight models (page 15)


Fixed sockets




EWB.1Y




VPP.1Y/3Y



HGP.1Y/3Y



VCP.3Y




HGP.1Y

450 type


Models (page 14)

Straight plug

Fixed socket



FFB.6Y




ERA.6Y


Part Section Showing Internal Components

Fixed socket

- 1 shell
- 2 earthing crown
- 3 hexagonal ring
- 4 insulator
- 5 female contact
- 6 o-ring



ERA.1Y



FFR.1Y

Straight plug

- 1 outer shell
- 2 latch sleeve
- 3 collet nut
- 4 insulator
- 5 male contact
- 6 circlip
- 7 bend relief
- 8 safety locking ring

Note: other connector shells are available on request.

Technical characteristics

Materials and treatments

Component	Material (Standard)	Thickness of surface treatment (µm)								
		chrome			nickel		gold			
		Cu	Ni	Cr	Cu	Ni	Cu	Ni	Au	
Outer shell, collet nut, conical nut	Brass (UNS C 38500)	0.5	3	0.3						
Innershell	Brass (UNS C 38500)				0.5	3				
Earthing crown	Beryllium Copper (UNS C 17300)							2	0.1	
Latch sleeve	Special bronze/brass	0.5	3	0.3						
Locking washer	Bronze (UNS C 52100)				0.5	3				
Hexagonal nut	Brass (UNS C 38500)				0.5	3				
Other metallic components	Brass (UNS C 38500)				0.5	3				
Male contact	Brass (UNS C 34500)						0.5	3	1.0	
Female contact	Bronze (UNS C 54400) or Cu-Be (UNS C 17300)						0.5	3	1.5	
Clips	Cu-Be or special steel	without treatment								
Insulator	PTFE, PEEK									
	Silicone rubber (LSR)									
O-ring and gaskets	Silicone MQ/MVQ									

Mechanical and Climatical

Characteristics	Value	Standard
Endurance	> 1000 cycles	IEC 60512-5 test 9a
Humidity	up to 95% at 60° C	
Operating temperature	- 40° C to +80° C ¹⁾	
	- 55° C to +230° C ²⁾	
Salt spray corrosion test	1000 h	IEC 60512-6 test 11f
Protection index (mated)	IP 50	IEC 60529
Climatical category		IEC 60068-1

Notes: ¹⁾ with «F» silicone insulator. ²⁾ with «L» PEEK insulator or «T» Teflon insulator (PTFE).

Electrical

Characteristics	Value	Standard
Test voltage	See page 17	
Shell electrical continuity	1Y	1.0 mΩ IEC 60512-2 test 2f
	3Y	0.7 mΩ IEC 60512-2 test 2f
	6Y	0.1 mΩ IEC 60512-2 test 2f
Contact resistance ¹⁾	ø 0.9 mm	< 4.5 mΩ IEC 60512-2 test 2a
	ø 1.3 mm	< 3.5 mΩ IEC 60512-2 test 2a
	ø 1.6 mm	< 3.5 mΩ IEC 60512-2 test 2a
	ø 4.5 mm	< 2 mΩ IEC 60512-2 test 2a
	ø 7.0 mm	< 0.4 mΩ IEC 60512-2 test 2a

Notes: Insulation resistance > 10¹² Ω IEC 60512-2 test 3a. ¹⁾ after 1000 mating cycles and the salt spray test according to IEC 60512-6 test 11 f.

Nominal and maximum operating voltage


Nominal voltage and maximum operating voltage to be determined by customer according to the application / equipment / regulation / standards.

Recommended cables

Models	Recommended cables	Colour	Outer diameter (mm)	Standard	Operating voltage
FFA.1Y.410.CTAC57	TV-20 Sumitomo	Red	5.75	UL 3239	
FFA.1Y.410.CTLC57	TV-20 Sumitomo	Red	5.75	UL 3239	
FFR.1Y.416.CFAE55R	CHT.99.574.710				
HGP.1Y.416.CLL37	CHT.99.574.710				
PEP.1Y.416.CLLY10	CHT.99.574.710				
FFR.3Y.425.CFAE55Z	JJC40003 / LEDE cable 130660	Red	5.40		30kV DC
FFR.1Y.416.CFAE55Z	JJC40003 / LEDE cable 130660	Red	5.40		30kV DC
FFR.1Y.416.CFAE55G	JJC40019 / LEDE cable 130666	Red	6.00	UL 1152	30kV DC
FFR.1Y.416.CFAE55B	JJC40003 / LEDE cable 130660	Red	5.40		30kV DC
FFR.1Y.416.CFAE63	NEK 20KV (07506)				
FFR.1Y.416.CFAE64	Lynenwerk 2YCH 20KV				
FFR.1Y.416.CFAE67G	HTC 50-5-1	Red	3.20	CERN/DESY	5kV DC
FFR.3Y.425.CFAE55G	Belden 8866	Red	5.30	–	40kV DC
FFR.3Y.425.CFAE76	Lynenwerk 2YCH 30KV				
FFR.3Y.425.CFAE88	CHH.99.NEK.HTC				
	CHT.99.554.075				
	CHT.02.053.048				
	CHT.40.090.38060RB				40kV DC
	CHT.18.150.65088GB / LEDE 315650				18kV DC
FFA.1Y.405.C●●C32	LEDE 140470	Red	2.90		3kV DC
FFA.1Y.405.C●●C42	CHT.03.075.20040RB / LEDE 150470	Red	4.00		3kV DC
FFA.1Y.410.CLLC47	CHT.09.060.28046RB / LEDE 106330		4.60		9kV DC

Notes: Outer insulation cable diameter (mm) must be adapted to the inner silicone insulator diameter (mm).

Part Numbering System



Note: ¹⁾ only for the plugs of the 1Y.416 and 3Y.425 series.

● First choice alternative ○ Special order alternative

FFA.1Y.405.CTAC52 = straight plug with cable collet, 1Y series, high voltage type, 10.5 kV DC test voltage, chrome-plated brass housing, PTFE insulator, male solder contact, C type collet for 5.2 mm max diameter cable.


ERA.3Y.430.CLL = fixed socket, nut fixing, 3Y series, high voltage type, 42 kV DC test voltage, chrome-plated brass housing, PEEK insulator, female solder contact.

Note: As standard, plugs are fitted with a male contact and sockets with a female contact. Some of these series Y models can be supplied with a female contact for plugs and a male contact for sockets.




Models without safety locking ring

FFA.1Y Straight plug, cable collet




Part number	Dimensions (mm)				Cable ø	
	A	L	M	S1	min.	max.
FFA.1Y.405.C●AC--	13	54.0	27.5	9	1.2	6.8
FFA.1Y.405.C●LC--	13	67.0	30.5	9	1.2	6.8
FFA.1Y.410.C●AC--	13	63.7	27.7	9	1.2	6.8
FFA.1Y.410.C●LC--	13	85.0	39.3	9	1.2	6.8

FFA.3Y Straight plug, cable collet




Part number	Dimensions (mm)				Cable ø	
	A	L	M	S1	min.	max.
FFA.3Y.415.C●AC--	19	98	42	15	2.6	10.5
FFA.3Y.415.C●LC--	19	116	52	15	2.6	10.5
FFA.3Y.430.C●AC--	19	115	42	15	2.6	10.5
FFA.3Y.430.C●LC--	19	200	105	15	2.6	10.5

ERA.1Y Fixed socket, nut fixing



Part number	Dimensions (mm)					
	A	e	E	L	M	S1
ERA.1Y.405.C●A	20	M16x1.0	6.5	61.0	4.5	19
ERA.1Y.405.C●L	20	M16x1.0	6.5	51.0	4.5	19
ERA.1Y.410.C●A	20	M16x1.0	6.5	79.5	4.5	19
ERA.1Y.410.C●L	20	M16x1.0	6.5	69.8	4.5	19


ERA.3Y Fixed socket, nut fixing



Part number	Dimensions (mm)						
	A	e	E	L	M	S1	S2
ERA.3Y.415.C●A ¹⁾	31	M24x1.0	12	77	6.5	20	30
ERA.3Y.415.C●L	31	M24x1.0	12	103	6.5	20	30
ERA.3Y.430.C●A ¹⁾	31	M24x1.0	12	108	6.5	20	30
ERA.3Y.430.C●L	31	M24x1.0	12	151	6.5	20	30



Note: ¹⁾ Male contact version does not include extended Teflon® tube.

ERA.3Y.260.CZZ Microswitch for fitting onto fixed socket








ERY.1Y Fixed socket, screw fixing, visible shell




Part number	Dimensions (mm)			
	A	e	L	S1
ERY.1Y.410.CTA	20	M16x1.0	79.5	18

ERD.3Y Fixed socket with two nuts and microswitch (back panel mounting)




Part number	Dimensions (mm)				Panel cut-out	
	A	e	L	S3	B	C
ERD.3Y.415.CTLM	40	M24x1.0	103.5	27	22.6	24.1
ERD.3Y.415.CTYM	40	M24x1.0	77.0	27	22.6	24.1

PSA.1Y Fixed socket, nut fixing, cable collet



Part number	Dimensions (mm)					Cable ø	
	A	e	L	S1	S2	min.	max.
PSA.1Y.405.C●AC--	20	M16x1.0	71	9	19	1.2	6.8
PSA.1Y.405.C●LC--	20	M16x1.0	74	9	19	1.2	6.8
PSA.1Y.410.C●AC--	20	M16x1.0	81	9	19	1.2	6.8
PSA.1Y.410.C●LC--	20	M16x1.0	93	9	19	1.2	6.8

PSA.3Y Fixed socket, nut fixing, cable collet




Part number	Dimensions (mm)					Cable ø	
	A	e	L	S1	S2	min.	max.
PSA.3Y.430.C●LC--	31	M24x1.0	150	15	30	2.6	10.5



Models with safety locking ring



FFR Straight plug for cable crimping with bend relief and safety locking ring



Part number	Dimensions (mm)				Cable ø	
	A	L	M	S1	min.	max.
FFR.1Y.416.CFAE---	13	83	64.7	9	3.3	6.6
FFR.1Y.416.CFAE67G	13	100	82.0	12	–	9.0
FFR.3Y.425.CFAE---	19	120	92.0	15	3.0	10.5



Note: FFR.1Y.416.CFAE52R is delivered with red bend relief (page 18).
Some specific model may accept larger dimensions.

ERA Fixed socket, nut fixing




Part number	Dimensions (mm)						Panel cut-out	
	A	e	L	M	S1	S2	B	C
ERA.1Y.416.CLL	20	M16x1.0	34	4.5	14.5	19	14.6	16.1
ERA.3Y.425.CLL	31	M24x1.0	50	6.5	22.5	30	22.6	24.1

ERA Fixed socket, nut fixing, for non-screened cable




Part number	Dim. (mm)			Panel cut-out		Cable ø
	A	e	L	B	C	
ERA.1Y.416.CLL37	20	M16x1.0	42	14.6	16.1	3.7 ± 0.1
ERA.3Y.425.CLL47	31	M24x1.0	60	22.6	24.1	4.7 ± 0.1

PEP Fixed socket, nut fixing, with cable clamp nut (back panel mounting)




Part number	Dimensions (mm)			Panel cut-out		Cable ø	
	A	e	L	B	C	min.	max.
PEP.1Y.416.CLLY---	20	M16x1.0	70.5	14.6	16.1	7	10
PEP.3Y.425.CLLY---	31	M24x1.0	85.0	22.6	24.1	7	15

FFB.6Y Straight plug with cable collet and safety locking ring



Part number	Dimensions (mm)					Cable ø	
	A	B	L	M	S1	min.	max.
FFB.6Y.450.CLAC---	47	50	215	89.2	36	11.0	31.3

ERA.6Y Fixed socket, nut fixing



Part number	Dimensions (mm)						
	A	e	E	L	M	N	S1
ERA.6Y.450.CLL	65	M55x2.0	45	206	10	29	65



Watertight or vacuumtight models

HGP, EWB, VPP, VCP socket models allow the device on which they are fitted to reach a protection index of IP68 as per IEC 60529.

They are fully compatible with plugs of the same series and are widely used for portable radios, military, laboratory equipment, aviation, research institutes, etc.



Note: ¹⁾ only for vacuumtight models.
Residual traces of grease used during (He) leak testing are on the o-ring.
Please contact us for further details.

Technical Characteristics

Mechanical and Climatical



Characteristics	Value	Standard
Endurance	> 1000 cycles	IEC 60512-5 test 9a
Humidity	up to 95% at 60°C	
Temperature range	-40°C to +80°C	
Salt spray corrosion test	1000 h	IEC 60512-6 test 11f
Climatical category	20/80/21	IEC 60068-1
Leakage rate (He) ¹⁾	< 10 ⁻⁷ mbar.l.s ⁻¹	IEC 60512-7 test 14b

EWB.1Y Fixed socket, nut fixing, vacuumtight, for print




Part number	Dimensions (mm)					Panel cut-out	
	A	e	L	S1	S2	B	C
EWB.1Y.416.CLN	20	M16x1.0	37.5	14.5	19	14.6	16.1

HGP Fixed socket, nut fixing, vacuumtight




Part number	Dimensions (mm)					Panel cut-out	
	A	e	L	S1	S2	B	C
HGP.1Y.416.CLL	20	M16x1.0	34	14.5	19	14.6	16.1
HGP.3Y.425.CLL	31	M24x1.0	50	22.5	30	22.6	24.1

HGP Fixed socket, nut fixing, vacuumtight




Part number	Dim. (mm)			Panel cut-out		Cable \varnothing
	A	e	L	B	C	
HGP.1Y.416.CLL37	20	M16x1.0	42	14.6	16.1	3.7 \pm 0.1

VPP Fixed socket, nut fixing, with cable clamp nut, vacuumtight (back panel mounting)



Part number	Dimensions (mm)			Panel cut-out		Cable \varnothing	
	A	e	L	B	C	min.	max.
VPP.1Y.416.CLLY10	20	M16x1.0	70.5	14.6	16.1	7	10
VPP.3Y.425.CLLY--	31	M24x1.0	85.0	22.6	24.1	7	15

VCP.3Y Fixed socket, nut fixing, vacuumtight, for non-screened cable (back panel mounting)




Part number	Dimensions (mm)				Panel cut-out		Cable \varnothing
	A	e	L	M	B	C	
VCP.3Y.425.CLL47	31	M24x1	59	3.5	22.6	24.1	4.7 \pm 0.1

[illegible]

Note.


- 1) some specific model may accept larger dimensions, please contact us.
- 2) test voltage U_e is measured according to IEC 60512-2 test 4a, in mated condition and at see level.
- 3) creepage distance is measured in the mated condition.
- 4) value for male contact plug mated with female contact socket.



Collets

Type C collets

C



1Y.405 / 3Y.410

Type	Cable ø	
	min.	max.
C22	1.2	2.2
C32	2.3	3.2
C42	3.5	4.2
C52	4.2	5.2
C62	5.4	6.2
C66	6.5	6.6
C68	6.7	6.8

3Y.415 / 3Y.430


Type	Cable ø	
	min.	max.
C42	2.6	4.2
C57	4.2	5.7
C72	5.7	7.2
C87	7.2	8.7
C97	8.5	9.7
C10	9.7	10.5

6Y.450


Type	Cable ø	
	min.	max.
C12	11.0	12.0
C21	20.0	21.0
C29	27.9	28.8
C30	29.0	30.0
C31	30.3	31.3

Fixing system type E or Y (1Y.416 and 3Y.425, for FFR, PEP and VPP models)

E




Y



Type	Cable dimension			
	Sheath ø		Max. dielec. ø (± 0.1)	Max. cond. ø
	Min.	Max.		
1Y	E52	–	6.6	3.6
	E55	–	6.0	3.9
	E63	–	6.6	3.6
	E64	–	6.6	3.6
	E67	–	9.0	4.5
	E10	–	10.5	4.6
	Y10	7.0	10.0	–
3Y	E55	–	6.0	4.0
	E76	–	8.0	4.6
	E88	–	9.0	5.5
	E10	–	10.5	4.6
	Y90	7.0	9.0	–
	Y15	12.0	15.0	–
	Y15	12.0	15.0	–

Accessories

GMA Bend relief (TPU)



A bend relief made from thermoplastic polyurethane elastomer can be fitted over LEMO plugs and sockets that are supplied with nut for fitting such bend relief. Use the part numbers shown below to order this accessory separately.

Main characteristics


- Material: TPU (Thermoplastic Polyurethane)
- Temperature range in dry atmosphere: -40°C +80°C

Part number	Bend relief		Cable ø	
	A	L	min.	max.
GMA.1B.054.DG	5.4	30	5.4	6.0
GMA.1B.065.DG¹⁾	6.5	30	6.5	7.0
GMA.1Y.087.DG	8.7	30	8.7	9.0

Note: All dimensions are in millimetres. ¹⁾ Design may differ from other bend relief, model without stripes. The last letter «G» of the part number indicates the grey colour of the bend relief. For ordering a bend relief with another colour, see table below and replace the letter «G» by the letter of the required colour.

Ref.	Colour	Ref.	Colour	Ref.	Colour
A	blue	J	yellow	R	red
B	white	M	brown	S	orange
G	grey	N	black	V	green

GBB Tapered washers



Part number	Dimensions (mm)		
	A	C	L
GBB.1E.250.LN	19	16.2	4

● Material: Nickel-plated brass (3 μ m)

Note: To order this accessory separately, use the above part numbers. The panel cut out diameter is larger when using tapered washer.

Tooling

DP● Crimping tool with die




This tool is needed for the termination of the cable, (crimping over the screen) of the plug FFR.

Part number	Series	Crimp collet ref.
DPE.99.007.0K	1Y.416	E55
DPE.99.127.4K	1Y. 416	E52, E63, E64, E67
DPE.99.007.0K	3Y.425	E55
DPA.99.209.5K	3Y.425	E76
DPA.99.011.6K	3Y.425	E10
DPD.91.010.5K	3Y.425	E88


Cable assembly

Cable stripping lengths for shielded cable



Models	Cable stripping lengths (mm)		
	L	S	T
FFA.1Y.405.CTAC--	34.5	8	8.0
PSA.1Y.410.CTLC62	45.0	6	8.0
PEP.1Y.416.CLLY10	17.9	8	3.9
VPP.1Y.416.CLLY10	24.0	8	4.0
FFA.3Y.415.CTAC--	79.0	6	15.0
FFA.3Y.415.CTYC77	73.0	6	15.0
PEP.3Y.425.CLLY15	41.3	12	4.3
VPP.3Y.425.CLLY15	41.3	12	4.3
FFA.3Y.430.CTAC--	97.0	12	14.0
FFA.3Y.430.CTLC--	92.0	12	11.0
PSA.3Y.430.CTLC--	56.0	7	8.0
FFB.6Y.450.CLAC--	119.0	12	30.0

Cable stripping lengths for non shielded cable




Models	Cable stripping lengths (mm)	
	L	T
ERD.1Y.416.CLL	33.9	3.9
ERA.3Y.425.CLL	32.0	4.5
HGP.3Y.425.CLL	32.0	4.5
ERA.3Y.430.CTA	85.5	14.5
ERA.3Y.430.CLL	—	6.5
ERA.3Y.430.CTL	—	6.5

S series (HV single contact)


S series connectors have main features as follows:

- security of the Push-Pull self-latching system
- solder contacts
- 360° screening for full EMC shielding
- wide range of models satisfying most applications.

Models (page 23)




Watertight or vacuumtight model (page 28)



Part Section Showing Internal Components


Fixed socket

- 1 outer shell
- 2 earthing crown
- 3 retaining ring
- 4 hexagonal nut
- 5 locking washer
- 6 insulator
- 7 female contact



Straight plug

- 1 outer shell
- 2 latch sleeve
- 3 collet nut
- 4 centre-piece
- 5 insulator
- 6 male contact
- 7 collet



Note: other connector shells are available on request.

Technical characteristics

Materials and treatments

Component	Material (Standard)	Thickness of surface treatment (µm)							
		chrome			nickel		gold		
		Cu	Ni	Cr	Cu	Ni	Cu	Ni	Au
Outer shell, collet nut, conical nut	Brass (UNS C 38500)	0.5	3	0.3					
Innershell	Brass (UNS C 38500)				0.5	3			
Earthing crown	Beryllium Copper (UNS C 17300)						0.5	3	1.0
Latch sleeve	Special bronze/brass	0.5	3	0.3					
Locking washer	Bronze (UNS C 52100)				0.5	3			
Hexagonal nut	Brass (UNS C 38500)				0.5	3			
Other metallic components	Brass (UNS C 38500)				0.5	3			
Male contact	Brass (UNS C 34500)						0.5	3	1.0
Female contact	Bronze (UNS C 54400) or Cu-Be (UNS C 17300)						0.5	3	1.5
Clips	Cu-Be or special steel								
Insulator	PTFE, PEEK								
	Silicone rubber (LSR)								
O-ring and gaskets	Silicone MQ/MVQ								

Mechanical and Climatical

Characteristics	Value	Standard
Endurance	> 1000 cycles	IEC 60512-5 test 9a
Humidity	up to 95% at 60°C	
Temperature range	-55°C +250°C	
Resistance to vibrations	10-2000 Hz, 15 g	IEC 60512-4 test 6d
Shock resistance	100g, 6 ms	IEC 60512-4 test 6c
Salt spray corrosion test	1000 h	IEC 60512-6 test 11f
Protection index (mated)	IP 50	IEC 60529
Climatical category	55/175/21	IEC 60068-1


Electrical

Characteristics	Value	Standard
Shielding efficiency	at 10 MHz	> 75 dB
	at 1 GHz	> 40 dB
		IEC 60169-1-3

Recommended cables

Type	Series										Type of cable	Operating voltage
	0S.403	0S.405	1S.405	1S.408	2S.408	3S.405	3S.410	3S.415	3S.460	4S.410		
017420	●	●	●								RG174	depending on manufacturer
140470	●										High voltage cable	3kV DC
150470	●		●	●	●						High voltage cable	3kV DC
106330		●			●			●			High voltage cable	9kV DC
158490											RG58	depending on manufacturer
130666			●			●					High voltage cable	30kV DC
130660			●			●	●	●			High voltage cable	30kV DC
213000											RG213	depending on manufacturer

Part Numbering System



FFB.1S.405.CTAC32 = straight plug with cable collet and safety locking ring, 1S series, high voltage, type 10.5 kV DC test voltage, chrome-plated brass housing, PTFE insulator, male solder contact, C type collet for a 3.2 mm diameter cable.

PCA.0S.403.CTLC22 = free socket with cable collet, 0S series, high voltage, type 6 kV DC test voltage, chrome-plated brass housing, PTFE insulator, female solder contact, C type collet for a 2.2 mm diameter cable.


ERA.2S.408.CTL = fixed socket, nut fixing, 2S series, high voltage, type 12 kV DC test voltage, chrome-plated brass housing, PTFE insulator, female solder contact.

Note: ¹⁾ the «Variant» position of the part number is used to specify the presence of a nut for fitting a bend relief. For models with collet nut for fitting a bend relief, a «Z» should be indicated and a bend relief can be ordered separately as indicated in the «Accessories» section. An order for a connector with bend relief should thus include two part numbers.




Models

FFA Straight plug, cable collet



Reference			Dimensions (mm)				Cable ø	
Model	Series	Type	A	L	M	S2	min.	max.
FFA	0S	403	9	34.7	24.7	6.5	1.3	4.4


FFA Straight plug, cable collet and nut for fitting a bend relief ¹⁾



Reference			Dimensions (mm)				Cable ø	
Model	Series	Type	A	L	M	S2	min.	max.
FFA	0S	403	9	33.5	23.5	7.0	1.3	4.4


Note: ¹⁾ to order, add a «Z» at the end of the reference.
The bend relief must be ordered separately (see page 39).

FFB Straight plug with cable collet and safety locking ring



Reference			Dimensions (mm)				Cable ø	
Model	Series	Type	A	L	M	S2	min.	max.
FFB	0S	403	9.0	36.8	26.8	6.5	1.3	4.4
FFB	1S	405	12.0	45.0	34.0	8.5	1.2	6.8
FFB	2S	408	14.8	55.5	43.5	11.0	1.3	8.7
FFB	3S	405	17.8	65.0	50.0	14.0	2.7	10.7
FFB	3S	410	17.8	75.0	60.0	14.0	2.7	10.7
FFB	3S	415	17.8	77.0	60.0	14.0	2.7	10.7
FFB	3S	460	17.8	65.0	50.0	14.0	2.7	10.7
FFB	4S	410	24.8	89.0	71.0	19.0	4.1	13.0


FFR Straight plug, safety locking ring, with cable crimping



Reference			Dimensions (mm)				Cable ø	
Model	Series	Type	A	L	M	S2	min.	max.
FFR	0S	405	9	42	32	6.5	1.3	4.4
FFR	1S	408	12	53	42	8.5	1.2	6.8

Note: Only available with male contact. For crimp ferrules see page 37.


FAA Fixed plug non-latching, nut fixing



Reference			Dimensions (mm)					Panel cut-out	
Model	Series	Type	A	e	E	L	M	B	C
FAA	0S	403	10	M9x0.6	2.0	27.0	11.2	8.3	9.1
FAA	1S	405	14	M12x1.0	2.5	34.0	12.5	10.6	12.1
FAA	3S	405	22	M18x1.0	3.6	44.0	17.0	16.6	18.2
FAA	3S	410	22	M18x1.0	3.6	55.6	17.0	16.6	18.2
FAA	3S	415	22	M18x1.0	3.6	55.0	17.0	16.6	18.2


Note: For the 3S.410 and 3S.415, the contact solder pot is inside the rear insulator.

ERA Fixed socket, nut fixing




Reference			Dimensions (mm)					Panel cut-out	
Model	Series	Type	A	e	E	L	M	B	C
ERA	0S	403	10	M9x0.6	7.0	25.0	1.2	8.3	9.1
ERA	0S	405	10	M9x0.6	7.0	25.1	1.2	8.3	9.1
ERA	1S	405	14	M12x1.0	7.5	32.0	1.5	10.6	12.1
ERA	1S	408	14	M12x1.0	7.5	29.9	1.5	10.6	12.1
ERA	2S	408	18	M15x1.0	8.5	41.5	1.8	13.6	15.1
ERA	3S	405	22	M18x1.0	11.5	41.5	2.0	16.6	18.2
ERA	3S	410	22	M18x1.0	11.5	46.5	2.0	16.6	18.2
ERA	3S	415	22	M18x1.0	11.5	52.0	2.0	16.6	18.2
ERA	3S	460	22	M18x1.0	11.5	38.0	2.0	16.6	18.2
ERA	4S	410	28	M25x1.0	12.0	56.5	2.5	23.6	25.2

EHP Fixed socket, nut fixing, protruding shell



Reference			Dimensions (mm)					Panel cut-out	
Model	Series	Type	A	e	E	L	M	B	C
EHP	0S	403	10	M9x0.6	2.0	25.0	12.5	8.2	9.1
EHP	1S	405	14	M12x1.0	3.5	31.5	12.0	10.5	12.1
EHP	3S	460	22	M18x1.0	4.0	38.0	18.7	—	18.2

EHR Fixed socket, nut fixing, protruding shell





Reference			Dimensions (mm)					Panel cut-out	
Model	Series	Type	A	e	E	L	M	B	C
EHR	3S	460	22	M18x1.0	4.4	43.6	18.7	—	18.2

Note: Only available with female contact.





ERD Fixed socket with two nuts (back panel mounting)



Panel cut-out

Reference			Dimensions (mm)					Panel cut-out	
Model	Series	Type	A	e	E	L	M	B	C
ERD	0S	403	12	M9x0.6	5.5	25.0	2.5	8.3	9.1
ERD	1S	405	16	M12x1.0	6.0	32.0	3.5	10.6	12.1
ERD	1S	408	16	M12x1.0	6.0	29.9	3.5	10.6	12.1
ERD	2S	408	20	M15x1.0	5.5	41.5	3.5	13.6	15.1
ERD	3S	415	24	M18x1.0	9.0	48.5	4.5	16.6	18.2


ECP Fixed socket with two nuts, long threaded shell (back panel mounting)



Panel cut-out


Reference			Dimensions (mm)					Panel cut-out	
Model	Series	Type	A	e	E	L	M	B	C
ECP	0S	403	12	M9x0.6	9.0	25.0	2.5	8.3	9.1
ECP	1S	405	16	M12x1.0	9.5	31.5	3.5	10.6	12.1

PCA Free socket, cable collet



Reference			Dimensions (mm)			Cable ø	
Model	Series	Type	A	L	S2	min.	max.
PCA	0S	403	8.9	33.5	6.5	1.3	4.4
PCA	1S	405	11.9	41.5	8.5	1.2	6.8
PCA	2S	408	14.8	54.0	11.0	1.3	8.7
PCA	3S	405	17.8	59.0	14.0	2.7	10.5
PCA	3S	410	17.8	64.0	14.0	2.7	10.5
PCA	3S	415	17.8	73.0	14.0	2.7	10.5
PCA	3S	460	17.8	65.0	14.0	2.7	10.5
PCA	4S	410	24.8	78.3	19.0	4.1	13.0


PCA Free socket, cable collet and nut for fitting a bend relief ¹⁾



Reference			Dimensions (mm)			Cable ø	
Model	Series	Type	A	L	S2	min.	max.
PCA	0S	403	8.9	36	7	1.3	4.4
PCA	1S	405	11.9	44	9	1.2	6.8

Note: ¹⁾ to order, add a «Z» at the end of the reference.
The bend relief must be ordered separately (see page 39).


PCS Free socket with cable crimping



Reference			Dimensions (mm)			Cable ϕ	
Model	Series	Type	A	L	S2	min.	max.
PCS	0S	405	9	38	6.5	1.7	3.4
PCS	1S	408	12	52	8.5	2.3	4.6

Note: Only available with female contact. For crimp ferrules see p. 37.


PSA Fixed socket, nut fixing, cable collet



Reference			Dimensions (mm)					Panel cut-out	
Model	Series	Type	A	e	E	L	M	B	C
PSA	0S	403	10	M9x0.6	7.0	33.5	1.2	8.3	9.1
PSA	1S	405	14	M12x1.0	7.5	41.5	1.5	10.6	12.1
PSA	2S	408	18	M15x1.0	8.5	54.0	1.8	13.6	15.1
PSA	3S	405	22	M18x1.0	11.5	59.0	2.0	16.6	18.2
PSA	3S	410	22	M18x1.0	11.5	64.0	2.0	16.6	18.2
PSA	3S	415	22	M18x1.0	11.5	73.0	2.0	16.6	18.2
PSA	4S	410	28	M25x1.0	12.0	78.3	2.5	23.6	25.2

Note: The dimension «S2» is the same as the PCA models.

PSP Fixed socket, nut fixing, cable collet and inner anti-rotating device




Reference			Dimensions (mm)					Panel cut-out	
Model	Series	Type	A	e	E	L	M	B	C
PSP	1S	405	14	M12x1.0	7.5	40.5	1.5	10.6	12.1
PSP	1S	410	14	M12x1.0	7.5	40.5	1.5	10.6	12.1

Note: The dimension «S2» is the same as the PCA models.




PSS Free socket, nut fixing for cable crimping



Reference			Dimensions (mm)					Panel cut-out	
Model	Series	Type	A	e	L	M	S2	B	C
PSS	0S	405	10	M9x0.6	38	1.2	6.5	8.3	9.1
PSS	1S	408	14	M12x1.0	52	1.5	8.5	10.6	12.1


Note: Only available with female contact. For crimp ferrules see p. 37.

RAD Fixed coupler, nut fixing



Reference			Dimensions (mm)					Panel cut-out	
Model	Series	Type	A	e	E	L	M	B	C
RAD	0S	403	10	M9x0.6	7.0	25.0	1.2	8.3	9.1
RAD	1S	405	14	M12x1.0	7.5	28.5	1.5	10.6	12.1

Note: see page 36 for the available plug and contact configuration.



Watertight or vacuumtight models

HGP, EWB, EWF, HCP, SWH socket or coupler models allow the device on which they are fitted to reach a protection index of IP68 as per IEC 60529.

They are fully compatible with plugs of the same series and are widely used for portable radios, military, laboratory equipment, aviation, etc.

These models are identified by a letter «P» at the end of the reference.

Most of these models are also available in a vacuumtight version. Such models are identified by an additional letter «V» at the end of the part number (certificate on request). Epoxy resin is used to seal these models.

Part number example:

Watertight socket: HGP.1S.405.CTLP

Vacuumtight socket: HGP.1S.405.CTLPV

Note:

¹⁾ only for vacuumtight models. Residual traces of grease used during (He) leak testing are on the o-ring. Please contact us for further details.


²⁾ this value corresponds to the maximum allowed pressure difference for the assembled socket.

Technical Characteristics

Mechanical and Climatical


Characteristics	Value	Standard
Endurance	> 1000 cycles	IEC 60512-5 test 9a
Humidity	up to 95% at 60°C	
Temperature range	-20°C to +80°C	
Salt spray corrosion test	1000 h	IEC 60512-6 test 11f
Climatical category	20/80/21	IEC 60068-1
Leakage rate (He) ¹⁾	< 10 ⁻⁷ mbar.l.s ⁻¹	IEC 60512-7 test 14b
Maximum operating pressure ²⁾	0S 60 bars	IEC 60512-7 test 14d
	1S 60 bars	IEC 60512-7 test 14d
	2S 40 bars	IEC 60512-7 test 14d
	3S 30 bars	IEC 60512-7 test 14d

HGP Fixed socket, nut fixing, watertight or vacuumtight



Reference			Dimensions (mm)					Panel cut-out	
Model	Series	Type	A	e	E	L	M	B	C
HGP	0S	403	18	M12x1.0	11.0	25.0	4	10.6	12.1
HGP	1S	405	20	M14x1.0	15.5	31.5	4	12.6	14.1
HGP	2S	408	20	M16x1.0	17.0	41.5	4	14.6	16.1
HGP	3S	410	28	M20x1.0	18.0	54.5	6	18.6	20.2
HGP	3S	415	28	M20x1.0	18.0	59.0	6	18.6	20.2

EWB Fixed socket, nut fixing, with two flats on the flange, watertight or vacuumtight





Reference			Dimensions (mm)					Panel cut-out	
Model	Series	Type	A	e	E	L	M	B	C
EWB	0S	405	13	M9x0.6	11.0	34.0	3.5	9.1	12.1
EWB	1S	405	20	M14x1.0	15.5	31.5	4.0	12.6	14.1
EWB	1S	408	18	M12x1.0	12.5	40.0	4.0	—	14.1

Note: Only available with female contact.
The 1S.408 model is without flats.




EWF Fixed socket with earthing tag, nut fixing, vacuumtight (back panel mounting)



Reference			Dimensions (mm)					Panel cut-out	
Model	Series	Type	A	e	E	L	P	B	C
EWF	0S	405	12.5	M12x1.0	10	34	12.5	–	12.1

Note: Only available with female contact.


HCP Fixed socket, nut fixing, watertight or vacuumtight (back panel mounting)



Reference			Dimensions (mm)					Panel cut-out	
Model	Series	Type	A	e	E	L	M	B	C
HCP	1S	408	18	M14x1.0	8.6	32	3.5	–	14.1

Note: Only available with female contact.

SWH Fixed coupler, nut fixing, watertight or vacuumtight



Reference			Dimensions (mm)					Panel cut-out	
Model	Series	Type	A	e	E	L	M	B	C
SWH	0S	403	14	M10x0.75	17	34	2.0	9.1	10.1
SWH	1S	405	17	M12x1.00	28	39	2.5	10.6	12.1
SWH	1S	408	17	M12x1.00	28	39	2.5	10.6	12.1
SWH	3S	405	25	M20x1.00	30	53	4.0	18.6	20.2
SWH	3S	410	25	M20x1.00	30	53	4.0	18.6	20.2

Note: see page 36 for the available plug and contact configuration.

E series (HV single contact)



E series connectors have been specifically designed for outdoor applications.

They include an inner sleeve and two seals to prevent penetration of solids or liquids into the housing formed by the plug, free socket, fixed socket or coupler. All models of these series are watertight when mated and give a protection index of IP 68 as per IEC 60529 standard (in mated condition) when correctly assembled to an appropriate cable (IP 66 otherwise).



- security of the Push-Pull latching system
- watertight connection (IP 68/IP 66)
- wide range of models satisfying most applications
- 360° screening for full EMC shielding
- rugged housing for extreme working condition.

Models (page 33)

Straight plugs




Fixed sockets



Watertight or vacuumtight model (page 34)



Fixed socket



Part Section Showing Internal Components

Fixed socket

- 1 outer shell
- 2 earthing crown
- 3 retaining ring
- 4 hexagonal nut
- 5 insulator
- 6 female contact
- 7 O ring



Straight plug

- 1 outer shell
- 2 latch sleeve
- 3 inner shell
- 4 circlip
- 5 collet nut
- 6 centre piece
- 7 insulator
- 8 male contact
- 9 earthing cone
- 10 collet
- 11 gasket

Note: other connector shells are available on request.

Technical characteristics

Materials and treatments

Component	Material (Standard)	Thickness of surface treatment (µm)				
		chrome			nickel	
		Cu	Ni	Cr	Cu	Ni
Outer shell, collet nut, conical nut	Brass (UNS C 38500)	0.5	3	0.3		
Innershell	Brass (UNS C 38500)				0.5	3
Earthing crown	Beryllium Copper (UNS C 17300)					0.5
Latch sleeve	Special bronze/brass	0.5	3	0.3		
Locking washer	Bronze (UNS C 52100)				0.5	3
Hexagonal nut	Brass (UNS C 38500)				0.5	3
Other metallic components	Brass (UNS C 38500)				0.5	3
Male contact	Brass (UNS C 34500)					0.5
Female contact	Bronze (UNS C 54400) or Cu-Be (UNS C 17300)					0.5
Clips	Cu-Be or special steel					
Insulator	PTFE, PEEK					
	Silicone rubber (LSR)					
O-ring and gaskets	Silicone MQ/MVQ					

Mechanical and Climatical

Characteristics	Value	Standard
Endurance	1000 cycles	IEC 60512-5 test 9a
Humidity	up to 95% at 60°C	
Temperature range	-55°C +200°C	
Resistance to vibrations	10-2000 Hz, 15 g	IEC 60512-4 test 6d
Shock resistance	100g, 6 ms	IEC 60512-4 test 6c
Salt spray corrosion test	1000 h	IEC 60512-6 test 11f
Protection index (mated)	IP 68 / IP 66	IEC 60529
Climatical category	50/175/21	IEC 60068-1


Electrical

Characteristics	Value	Standard
Shielding efficiency	at 10 MHz	> 95 dB
	at 1 GHz	> 80 dB

Recommended cables

Type	Series					Type of cable	Operating voltage
	0E.403	1E.405	2E.408	3E.405	3E.410		
017420	●	●				RG174	depending on manufacturer
140470	●					High voltage cable	3kV DC
150470	●	●	●			High voltage cable	3kV DC
106330			●			High voltage cable	9kV DC
158490						RG58	depending on manufacturer
130666		●		●		High voltage cable	30kV DC
130660		●		●	●	High voltage cable	30kV DC
213000						RG213	depending on manufacturer

Part Numbering System



FFA.1E.405.CLAC35 = straight plug with cable collet, 1E series, high voltage, type 10.5 kV DC test voltage, chrome-plated brass housing, PEEK insulator, male solder contact, C type collet for a 3.5 mm diameter cable.

PCA.0E.403.CLLC35 = free socket with cable collet, 0E series, high voltage, type 6 kV DC test voltage, chrome-plated brass housing, PEEK insulator, female solder contact, C type collet for a 3.5 mm diameter cable.


ERA.2E.408.CLL = fixed socket, nut fixing, 2E series, high voltage, type 12 kV DC test voltage, chrome-plated brass housing, PEEK insulator, female solder contact.

Note: ¹⁾ the «Variant» position of the part number is used to specify the presence of a nut for fitting a bend relief. For models with collet nut for fitting a bend relief, a «Z» should be indicated and a bend relief can be ordered separately as indicated in the «Accessories» section. An order for a connector with bend relief should thus include two part numbers.




Models

FFA Straight plug, cable collet



Reference			Dimensions (mm)				Cable ϕ	
Model	Series	Type	A	L	M	S2	min.	max.
FFA	0E	403	11	34.0	23.0	8	1.0	5.0
FFA	1E	405	13	43.0	29.0	9	1.3	6.5
FFA	2E	408	16	52.5	36.5	12	1.3	8.5
FFA	3E	410	19	62.5	42.5	15	2.6	10.5



FFA Straight plug, cable collet and nut for fitting a bend relief ¹⁾



Reference			Dimensions (mm)				Cable ϕ	
Model	Series	Type	A	L	M	S2	min.	max.
FFA	0E	403	11	34.0	23.0	7	1.0	5.0
FFA	1E	405	13	43.0	29.0	9	1.3	6.5
FFA	3E	410	19	61.5	41.5	15	2.6	10.5



Note: ¹⁾ to order, add a «Z» at the end of the reference.
The bend relief must be ordered separately (see page 39).

ERA Fixed socket, nut fixing




Reference			Dimensions (mm)					Panel cut-out	
Model	Series	Type	A	e	E	L	M	B	C
ERA	0E	403	18	M14x1.0	5.5	26.5	4.0	12.6	14.1
ERA	1E	405	20	M16x1.0	9.0	35.5	4.5	14.6	16.1
ERA	2E	408	25	M20x1.0	9.0	45.5	5.0	18.6	20.2
ERA	3E	410	31	M24x1.0	11.0	52.0	6.0	22.6	24.2

PSA Fixed socket, nut fixing, cable collet



Reference			Dimensions (mm)					Panel cut-out	
Model	Series	Type	A	e	E	L	M	B	C
PSA	1E	405	20	M16x1.0	9.0	46.0	4.5	14.6	16.1
PSA	3E	410	31	M24x1.0	11.5	67.7	6.0	22.6	24.2

Note: The dimension «S2» is the same as the FFA models.



Watertight or vacuumtight models

HGP and SWH socket or coupler models allow the device on which they are fitted to reach a protection index of IP 68 as per IEC 60529. They are fully compatible with plugs of the same series and are widely used for portable radios, military, laboratory equipment, aviation, etc. These models are identified by a letter «P» at the end of the reference. Most of these models are also available in a vacuumtight version. Such models are identified by an additional letter «V» at the end of the part number (certificate on request). Epoxy resin is used to seal these models.

Part number example:
Watertight socket: HGP.0E.403.CTLP
Vacuumtight socket: HGP.0E.403.CTLPV


Note: ¹⁾ only for vacuumtight models. Residual traces of grease used during (He) leak testing are on the o-ring. Please contact us for further details.
²⁾ this value corresponds to the maximum allowed pressure difference for the assembled socket.

Technical Characteristics

Mechanical and Climatical

Characteristics	Value	Standard
Endurance	> 1000 cycles	IEC 60512-5 test 9a
Humidity	up to 95% at 60°C	
Temperature range	-20°C to +80°C	
Salt spray corrosion test	1000 h	IEC 60512-6 test 11f
Climatical category	20/80/21	IEC 60068-1
Leakage rate (He) ¹⁾	< 10 ⁻⁷ mbar.l.s ⁻¹	IEC 60512-7 test 14b
Max. operating pressure ²⁾	60 bars	IEC 60512-7 test 14d

HGP Fixed socket, nut fixing, watertight or vacuumtight















Reference			Dimensions (mm)					Panel cut-out	
Model	Series	Type	A	e	E	L	M	B	C
HGP	0E	403	18	M14x1.0	5.5	24.5	4	12.6	14.1



Insert configuration (S and E series)

High Voltage (single contact)

Male solder contacts	Female solder contacts	Reference	Series		Contact ø (mm)	Contact gender for plug	Conductor ø maxi (mm) ¹⁾	Dielectric ø maxi (mm) ¹⁾	Cable sheath ø maxi (mm) ¹⁾	Standard insulator material	Creepage dist. min. (mm) ³⁾	Test voltage Ue (kV DC) ²⁾	Rated current (A)
			Standard	Watertight									
		403	0S	0E	0.9	A/L	0.75	2.9	5.0	T	7.0	6.0	4
		405	0S	–	0.7	A	1.05	2.9	4.7	L	13.5	12.0	4
			1S	1E	1.3	A/L	1.05	4.0 ⁵⁾	6.5	T	10.5	10.5	8
			3S	3E	4.0	A/L	2.95	7.5	10.5	T	12.5	10.5	15
		408	1S	–	0.9	A	0.95	4.0	6.0	L	20.0	18.0	6
			2S	2E	2.0	A/L	1.75	5.1 ⁵⁾	8.5	T	11.5	12.0	10
		410	3S	3E	2.0	A/L	2.15	7.3	10.5	T	16.5	15.0	10
			4S	–	2.5	A	2.95	9.5	13.0	T	tbd	15.0	12
		415	3S	–	1.3	A/L	1.30	7.3 ⁵⁾	10.5	T	28.5	21.0	8
		460	3S	–	1.4	A	1.05	4.2	10.5	L	1.7 5.5	2.25 ⁴⁾ 7.50	10

Note:

- ¹⁾ some specific model may accept larger dimensions, please contact us.
- ²⁾ test voltage Ue is measured according to IEC 60512-2 test 4a, in mated condition and at sea level.
- ³⁾ creepage distance is measured in the mated condition.
- ⁴⁾ between screen.
- ⁵⁾ dielectric diameters are linked to the clamping size see page 38.



Contacts (S and E series)

Contacts for plugs, free or fixed sockets

Ref.	Contact type
A	Male solder
L	Female solder


Contacts for couplers

Ref.	Contact type
C	Male - Male
A	Male - Female


Ref.	Contact type
L	Female - Male
M	Female - Female

Contacts reference for fixed and free couplers RAD and SWH


A Male - Female




L Female - Male



C Male - Male



M Female - Female




Use of plugs for mating with RAD and SWH couplers

- Reference M for coupling two identical plugs fitted with male contact (contact reference A).
- Reference L for coupling a plug fitted with male contacts (contact reference A) at the flange end for RAD and SWH and an inverted plug fitted with female contacts (contact reference L) at the other end.
- Reference A for the inverted version of code L.
- Reference C for the inverted version of code M.



Collets (S and E series)

Type C collets (S series)



	Type	Cable ø	
		min.	max.
0S	C22	1.3	2.2
	C32	> 2.2	3.2
	C37	> 3.2	3.7
	C44	> 3.7	4.4
1S	C22	1.4	2.2
	C32	> 2.2	3.2
	C42	> 3.2	4.2
	C52	> 4.2	5.2
	C57	> 5.2	5.7
	C62	> 5.7	6.2
2S	C27	1.3	2.7
	C32	> 2.5	3.2
	C42	> 3.2	4.2
	C52	> 4.2	5.2
	C62	> 5.2	6.2
	C72	> 6.2	7.2
	C82	> 7.2	8.2
	C87	> 8.2	8.7
3S	C42	2.6	4.2
	C57	4.3	5.7
	C72	5.8	7.2
	C87	7.3	8.7
	C97	8.8	9.7
	C11	9.8	10.5
4S	C52	4.1	5.0
	C62	5.1	6.0
	C72	6.1	7.0
	C82	7.1	8.0
	C92	8.1	9.0
	C10	9.1	10.0
	C11	10.1	11.0
	C12	11.1	12.0
	C13	12.6	13.0

Type C collets (E series)





	Type	Cable ø	
		min.	max.
0E	C10	1.0	1.2
	C15	1.3	1.5
	C20	1.6	2.0
	C25	2.1	2.5
	C30	2.6	3.0
	C35	3.1	3.5
1E	C15	1.3	1.5
	C20	1.6	2.0
	C25	2.1	2.5
	C30	2.6	3.0
	C35	3.1	3.5
	C40	3.6	4.0
	C45	4.1	4.5
	C50	4.6	5.0
	C55	5.1	5.5
	C60	5.6	6.0
2E	C15	1.3	1.5
	C20	1.6	2.0
	C25	2.1	2.5
	C30	2.6	3.0
	C35	3.1	3.5
	C40	3.6	4.0
	C45	4.1	4.5
	C50	4.6	5.0
	C55	5.1	5.5
	C60	5.6	6.0
3E	C15	1.3	1.5
	C20	1.6	2.0
	C25	2.1	2.5
	C30	2.6	3.0
	C35	3.1	3.5
	C40	3.6	4.0
	C45	4.1	4.5
	C50	4.6	5.0
	C55	5.1	5.5
	C60	5.6	6.0

Crimp ferrules (0S.405 and 1S.408 series)



	Type	Cable dimension			
		Sheath ø		Max. dielec. ø (± 0.1)	Max. cond. ø
		Min.	Max.		
0S	E33	2.6	3.3	1.6	0.55
	E34	2.8	3.3	1.6	0.55
	E43	3.5	4.3	2.1	1.00
	E48	4.2	4.8	3.0	1.00
1S	E46	4.0	4.6	2.3	0.90
	E61	5.2	6.1	4.0	0.90

Barrel contact and dielectric diameter



Sub assembly part number	Barrel contact Ø A (mm)	Inner insulator Ø B (mm)	Delivered with clamping
0S.403	0.8	3.0	C22 to C44
1S.405	1.1	2.4	C22, C32, C42
		3.1	C52
		4.1	C62
2S.408	1.8	3.2	C27, C32
		5.2	C42 to C87

Sub assembly part number	Barrel contact Ø A (mm)	Inner insulator Ø B (mm)	Delivered with clamping
3S.405	3.0	7.6	C42 to C11
3S.410	2.2	7.4	C42 to C11
3S.415	1.35	4.1	C42 to C57
		4.9	C72 to C87
		6.5	C96 to C11
4S.410	3.0	9.6	C52 to C13

Note: please consult us for other inner insulators and clamping arrangements.



Variant (S and E series)

Bend relief for S series models with collet

		Need to be ordered	
		Need to be ordered separately (see page 39)	
Ref.	Collet		
Type	Code		
0S	Z	C	32 to 44
			GMA.0B.0...D●
1S	Z	C	32 to 62
			GMA.1B.0...D●

Note: All dimensions are in millimetres.

Bend relief for E series models with collet

		Need to be ordered	
		Need to be ordered separately (see page 39)	
Ref.	Collet		
Type	Code		
0E	Z	C	30 to 50
			GMA.0B....●●
1E	Z	C	30 to 65
			GMA.1B....●●
3E	Z	C	35 to 85
			GMA.3B....●●

Watertight and vacuumtight socket and coupler models (S and E series)

	Reference		Model
	Watertight	Vacuumtight	
S	P	PV	EWB, HCP, HGP, EWF, SWH
E	P	PV	HGP


O-ring and gasket material (E series)

Standard connectors are delivered with silicone o-ring and gaskets. The vacuumtight models, identified with the letter «PV», are delivered with Viton® gaskets. Other gaskets material can be delivered upon special request.

Ref.	O-ring material
H	FPM (Viton®)
E	EPDM
D	FPM (Viton®) and collet nut for bend relief

Accessories

GMA Bend relief (TPU)



A bend relief made from thermoplastic polyurethane elastomer can be fitted over LEMO plugs and sockets that are supplied with nut for fitting such bend relief. Use the part numbers shown below to order this accessory separately.

Main characteristics

- Material: TPU (Thermoplastic Polyurethane)
- Temperature range in dry atmosphere: -40°C +80°C

Part number	Series	Bend relief		Cable ϕ	
		A	L	min.	max.
GMA.0B.025.DG	0S-0E	2.5	24	2.5	2.9
GMA.0B.030.DG		3.0	24	3.0	3.4
GMA.0B.035.DG		3.5	24	3.5	3.9
GMA.0B.040.DG ¹⁾		4.0	24	4.0	4.4
GMA.0B.045.DG ¹⁾		4.5	24	4.5	5.2
GMA.1B.025.DG	1S-1E	2.5	30	2.5	2.9
GMA.1B.030.DG		3.0	30	3.0	3.4
GMA.1B.035.DG		3.5	30	3.5	3.9
GMA.1B.040.DG		4.0	30	4.0	4.4
GMA.1B.045.DG		4.5	30	4.5	4.9
GMA.1B.054.DG		5.4	30	5.4	6.0
GMA.1B.065.DG ¹⁾		6.5	30	6.5	7.0

Part number	Series	Bend relief		Cable ϕ	
		A	L	min.	max.
GMA.3B.050.DG ¹⁾	3E	4.5	42	4.5	5.2
GMA.3B.060.DG		6.0	42	6.0	6.9
GMA.3B.070.DG		7.0	42	7.0	7.9
GMA.3B.080.DG		8.0	42	8.0	8.9
GMA.3B.090.DG		9.0	42	9.0	10.0

Note: all dimensions are in millimetres.

Ref.	Colour	Ref.	Colour	Ref.	Colour
A	blue	J	yellow	R	red
B	white	M	brown	S	orange
G	grey	N	black	V	green

Note: ¹⁾ Design may differ from other bend relief, model without stripes.

The last letter «G» of the part number indicates the grey colour of the bend relief. For ordering a bend relief with another colour, see table above and replace the letter «G» by the letter of the required colour.

05 series (HV single contact)

High voltage connectors of the new 05 miniature series have been specifically developed to meet the requirements of experimental nuclear research programme.

The 05 series contains a miniature HV 12kV DC (test voltage) contacts. This crimp contact is removable from the shell and is inserted in a PEEK insulator. The actual mating is provided by the LEMO Push-Pull system, renowned for its reliability worldwide and a red locking ring to secure the connection.

The compact design of these connectors makes them ideal for applications where minimal mass and space saving are critical factors.

Interconnections

Models (page 42)

Straight plug


Fixed socket



Part Section Showing Internal Components


Fixed socket

- 1 shell
- 2 crimp back end
- 3 hexagonal nut
- 4 conical nut
- 5 insulator
- 6 HV female contact
- 7 crimp ferrule



Straight plug


- 1 outer shell
- 2 latch sleeve
- 3 locking ring
- 4 crimp back end
- 5 insulator
- 6 HV male contact
- 7 crimp ferrule
- 8 earthing crown



HV Contact


Female contact

- 1 female contact
- 2 insulator
- 3 clips



Male contact

- 1 male contact
- 2 insulator
- 3 clips
- 4 sealing gland



Technical Characteristics

Materials and Treatments – Connector

Component	Material (Standard)	Surface treat. (µm)
Outer shell + crimpend	Aluminium (AA 6262A)	5
Safety nut	Aluminium (AA 6262A)	Anodized red
Earthing crown	Aluminium special	5
Latch sleeve	Aluminium special	5
Hexagonal and conical nut	Aluminium (AA 6262A)	Anodized natural
Insulator	PEEK	–
Crimp ferrule	Aluminium (AA 6262A)	5

Mechanical and Environmental

Characteristics	Value	Standard
Working temperature	-20°C +125°C	
Mechanical life	> 200 cycles	IEC 60512-5 test 9a
Climatic class	20/125/21	IEC 60068-1
Radiation resistance	> 10 ⁶ Gy	

Contact

Component	Material (Standard)	Surface treat. (µm)		
		Cu	Ni	Au
Male contact	Brass (UNS C38500)	0.5	3	1.0
Female contact	Bronze (UNS C54400)	0.5	3	1.5
Contact clips	Cu-Be (QQ-C-530)	–		
Insulator	PEEK	–		
Sealing gland	Silicone PVMQ	–		

Electrical

Characteristics	Value	Standard
Test voltage (1 min.)	12 kV DC	IEC 60512-2 test 4a
Rated current	4 A	IEC 60512-3 test 5a
Contact resistance	≤ 8 mΩ	IEC 60512-2 test 2a
Screen resistance	≤ 150 mΩ	IEC 60512-2 test 2f
Insulation resistance	≥ 10 ¹² mΩ	IEC 60512-2 test 3a


Recommended cables

Cable group	Manufacturer part number	CERN type	Construction and dimensions									
			Conductor			Dielectric		Screen		Sheath		Corona screen
			Constr.	Mat.	ø	Mat.	ø	Mat.		Mat.	ø	
1	ABBNK - 45/94	HTC 50-1-1	7x0.17	CuSn	0.51	PE solid	1.5	CuSn 16x4x0.1		Polyolefine	3.30	yes
2	HABIA 31789-004-001	HFI 150 mini coax	Mono	Cu	0.16	HFI150	0.5	Drain 2x0.1 + Alu polyester		HFI150	1.15	no





Models

FFR.05 Straight plug for cable crimping with locking ring



Part number	Cable group
FFR.05.403.LLAE141	1
FFR.05.403.LLAE142	2

PES.05 Fixed socket, with two nuts, for cable crimping





Panel cut-out

Part number	Cable group
PES.05.403.LLLE141	1
PES.05.403.LLLE142	2

Recommended mounting nut torque: 0.8 Nm.



Accessories

FFA-ERA High voltage contacts



Contact part number		Cable group	L (mm)
Male contact	Female contact		
FFA.05.403.ZLA1	ERA.05.403.ZLL1	1	4
FFA.05.403.ZLA2	ERA.05.403.ZLL2	2	6

GMA Heatshrink tube





Part number	Cable group	Supplier		ø D	L
		Name	Product ref.		
GMA.30.010.ST	1-2	RAYCHEM®	RNF 3000 3/1	3.0	13
GMA.15.010.ST	2	RAYCHEM®	RNF 3000 1.5/0.5	1.5	9

Note: All dimensions are in millimetres. Shall be ordered separately. For cable group 2, the two heatshrink tubes are necessary.

- Material: Polyolefin transparent


FFS Crimp ferrule



Part number	Cable group	Model
FFS.05.160.PM	1	1
FFS.05.161.PM	2	2

- Material: Aluminium alloy (AA 6262A) nickel plated


GEC Conical nut



Part number
GEC.05.241.PT

- Material: Aluminium alloy (AA 6262A) natural anodized.

GEA Hexagonal nut




Part number

GEA.05.241.PT

- Material: Aluminium alloy (AA 6262A) natural anodized.

Tooling

DCH Spanner for conical nut




Part number

DCH.91.113.9TN

- Material: Blackened steel.

DCC Manual extractors for HV contacts



Part number


DCC.13.15B.LAG

DPH Crimping tool with die



Part number	Applications	Cable group	Marking on die
DPH.99.005.2K	Shield	1-2	DPH.91.005.2K
DPH.99.060.11K	Centre contact	1	DPH.91.001.16K
DPH.99.065.11K	Centre contact	2	DPK.91.001.16K



DPN Dies and positioner







Part number	Applications	Cable group	Marking on die
DPN.99.005.2K	Shield	1-2	DPH.91.005.2K
DPN.99.060.11K	Centre contact	1	DPH.91.001.16K
DPN.99.065.11K	Centre contact	2	DPK.91.001.16K

- Dies material: Blackened steel

Termination instructions cable group 1



Dimensions in mm.



1. Strip the cable according to the given dimensions, remove carefully the cable corona screen, making sure that the cable dielectric is not damaged. Remove also the aluminium foil and the textile tape. Clean the dielectric with isopropyl alcohol.



2. Place the crimp ferrule ① on the cable. Widen completely the shield braid and fold it back over the jacket. Introduce the cable center conductor into the HV contact ④ until the contact end rests against the dielectric and the conductor is visible through the contact inspection hole. Crimp with the LEMO crimping tool DPH.99.060.11K. Cover the crimp section of the contact and the Peek end of the HV contact with a layer of insulating laquer. Let the laquer dry, approx. 15 min.
Note: We recommend the laquer Urethan ref: Cellpack n° 912110

3. Slide the heatshrink tube ③ over the HV contact until it rests against the contact insulator. One end of the heatshrink tube shall be located at the position A of the HV contact insulator. Shrink the tube.


4. Fully introduce the HV contact into the connector shell ⑤. Check that the contact is correctly located and remains in position when given a gentle pull. Place the cable shield braid strand over the shell crimp back end, cut the length of braid in excess.

5. Slide the crimp ferrule over the cable shield until it rests against the connector shell. Crimp with the LEMO crimping tool DPH.99.005.2K.


Termination instructions cable group 2




1. Strip the cable according to the given dimensions, cut the aluminium foil making sure that the dielectric is not damaged. Do not damage the 2 drain wires. Fold the drain wires back over the outer jacket and slide over the small heatshrink tube ②. Clean the dielectric with isopropyl alcohol.




2. Place the crimp ferrule ① introducing first the small diameter on the cable. Introduce the cable center conductor and a part of the dielectric into the HV contact ④ until the conductor is fully visible through the contact inspection hole. Crimp with the LEMO crimping tool DPH.99.065.11K. Cover the crimp section of the contact and a short length of the dielectric with a layer of insulating laquer. Let the laquer dry, approx. 15 min.
Note: We recommend the laquer Urethan ref: Cellpack n° 912110
Slide the heatshrink tube ② over the HV contact until it rests against the contact insulator at the position B. Shrink the tube. Cover the Peek end of the HV contact and the first heatshrink tube with a layer of the insulating laquer. Let the laquer dry, approx. 15 min.



3. Slide the heatshrink tube ③ over the HV contact until it rests against the contact insulator. One end of the heatshrink tube shall be located at the position A of the HV contact insulator. Shrink the tube.



4. Fully introduce the HV contact into the connector shell ⑤. Check that the contact is correctly located and remains in position when given a gentle pull. Place the 2 drain wire around the shell crimp back end.



5. Slide the crimp ferrule over the cable shield until it rests against the connector shell. Crimp with the LEMO crimping tool DPH.99.005.2K.

Product safety notice

PLEASE READ AND FOLLOW ALL INSTRUCTIONS CAREFULLY AND CONSULT ALL RELEVANT NATIONAL AND INTERNATIONAL SAFETY REGULATIONS FOR YOUR APPLICATION. IMPROPER HANDLING, CABLE ASSEMBLY, OR WRONG USE OF CONNECTORS CAN RESULT IN HAZARDOUS SITUATIONS.

1. SHOCK AND FIRE HAZARD

Incorrect wiring, the use of damaged components, presence of foreign objects (such as metal debris), and / or residue (such as cleaning fluids), can result in short circuits, overheating, and / or risk of electric shock. Mated components should never be disconnected while live as this may result in an exposed electric arc and local overheating, resulting in possible damage to components.

2. HANDLING

Connectors and their components should be visually inspected for damage prior to installation and assembly. Suspect components should be rejected or returned to the factory for verification. Connector assembly and installation should only be carried out by properly trained personnel. Proper tools must be used during installation and / or assembly in order to obtain safe and reliable performance.


3. USE


Connectors with exposed contacts should never be live (or on the current supply side of a circuit). Under general conditions voltages above 30 VAC and 42 VDC are considered hazardous and proper measures should be taken to eliminate all risk of transmission of such voltages to any exposed metal part of the connector.

4. TEST AND OPERATING VOLTAGES

The maximum admissible operating voltage depends upon the national or international standards in force for the application in question. Air and creepage distances impact the operating voltage; reference values are indicated in the catalog however these may be influenced by PC board design and / or wiring harnesses. The test voltage indicated in the catalog is 75% of the mean breakdown voltage; the test is applied at 500 V/s and the test duration is 1 minute.

5. CE MARKING

CE marking  means that the appliance or equipment bearing it complies with the protection requirements of one or several European safety directives.

CE marking  applies to complete products or equipment, **but not to electromechanical components, such as connectors.**

6. PRODUCT IMPROVEMENTS

The LEMO Group reserves the right to modify and improve to our products or specifications without providing prior notification.

7. **WARNING (Prop 65 State of California)**

Proposition 65 requires businesses to provide warnings to Californians about significant exposures to chemicals that cause cancer, birth defects or other reproductive harm. LEMO products are exempt from proposition 65 warnings because they are manufactured, marketed, and sold solely for commercial and industrial use. For further information, please visit <https://www.lemo.com/quality/LEMO-Prop-65-compliance-declaration.pdf>.

Disclaimers

LEMO works constantly to improve the quality of its products; the information and illustrations figuring in this document may therefore vary and are not binding. In any case, LEMO makes no specific warranty of merchantability, fitness for a particular purpose, third party components as such or included in assembly, non-infringement, title, accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO component.

In no event shall LEMO, its affiliates, officers, agents or employees be liable for any incidental, indirect, special or consequential damages in connection with the products or services provided by LEMO, including (without limitation) loss of profits or revenues, interruption of business, loss of use of the products or any associated equipment, materials, components or products, damages to associated equipment or in combination with other components, materials.

Reproduction of significant portions of LEMO information in LEMO data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. LEMO is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

LEMO HEADQUARTERS

SWITZERLAND

LEMO SA

Chemin des Champs-Courbes 28 - P.O. Box 194 - CH-1024 Ecublens
Tel. +41 21 695 16 00 - e-mail: info@lemo.com

LEMO SUBSIDIARIES

AUSTRIA

LEMO Elektronik GesmbH

Lemböckgasse 49/E6-3

1230 Wien

Tel: +43 1 914 23 20 0

Fax: +43 1 914 23 20 11

salesAT@lemo.com

BRAZIL

LEMO Latin America Ltda

Av. Dr. Adhemar de Barros,

566 – Sala 1407, Vila Adyana

CEP: 12245-011

São José dos Campos - SP - Brazil

Tel: +55 11 94242 4293

info-la@lemo.com

CANADA

LEMO Canada Inc

44 East Beaver Creek Road, unit 20

Richmond Hill, Ontario L4B 1G8

Tel: +1 905 889 56 78

Fax: +1 905 889 49 70

info-canada@lemo.com

CHINA / HONG KONG

LEMO Electronics (Shanghai) Co., Ltd

First Floor, Block E,

18 Jindian Road, Pudong

Shanghai, China, 201206

Tel: +86 21 5899 7721

Fax: +86 21 5899 7727

cn.sales@lemo.com

DENMARK

LEMO Denmark A/S

Mandal Allé 16A

5500 Middelfart

Tel: +45 45 20 44 00

Fax: +45 45 20 44 01

info-dk@lemo.com

FRANCE

LEMO France Sàrl

24/28 Avenue Graham Bell

Bâtiment Balthus 4

Bussy Saint Georges

77607 Marne la Vallée Cedex 3

Tel: +33 1 60 94 60 94

Fax: +33 1 60 94 60 90

info-fr@lemo.com

GERMANY

LEMO Elektronik GmbH

Hanns-Schwindt-Str. 6

81829 München

Tel: +49 89 42 77 03

Fax: +49 89 420 21 92

infoDE@lemo.com

HUNGARY

REDEL Elektronika Kft

Nagysándor József u. 6-12

1201 Budapest

Tel: +36 1 421 47 10

Fax: +36 1 421 47 57

info-hu@lemo.com

INDIA

LEMO India Private Ltd

Sixth floor, Sunrise Tower, C-10 Central

Road Marol MIDC Andheri East,

Mumbai, Mumbai Suburban,

Maharashtra, 400093

Tel: +91 22 69380203

info-india@lemo.com

ITALY

LEMO Italia srl

Viale Lunigiana 25

20125 Milano

Tel: +39 02 66 71 10 46

Fax: +39 02 37 90 80 46

sales.it@lemo.com

JAPAN

LEMO Japan Ltd

2-7-22, Mita,

Minato-ku, Tokyo, 108-0073

Tel: +81 3 54 46 55 10

Fax: +81 3 54 46 55 11

info-jp@lemo.com

NETHERLANDS / BELGIUM

LEMO Connectors Nederland B.V.

Jacques Meuwissenweg 6

2031 AD Haarlem

Tel. +31 23 206 07 01

info-nl@lemo.com

NORWAY / ICELAND

LEMO Norway A/S

Soerumsandvegen 69,

1920 Soerumsand

Tel: +47 22 91 70 40

Fax: +47 22 91 70 41

info-no@lemo.com

SINGAPORE

LEMO Asia Pte Ltd

4 Leng Kee Road,

#06-09 SiS Building

Singapore 159088

Tel: +65 6476 0672

Fax: +65 6474 0672

sg.sales@lemo.com

SPAIN / PORTUGAL

IBERLEMO SAU

Brasil, 45, 08402 Granollers

Barcelona

Tel: +34 93 860 44 20

Fax: +34 93 879 10 77

info-es@lemo.com

SWEDEN / FINLAND

LEMO Nordic AB

Gunnebogatan 30

163 53 Spånga

Tel: +46 8 635 60 60

Fax: +46 8 635 60 61

info-se@lemo.com

SWITZERLAND

LEMO Verkauf AG

Grundstrasse 22 B,

6343 Rotkreuz

Tel: +41 41 790 49 40

ch.sales@lemo.com

TAIWAN

TAOYUAN TAIWAN

Tel: +886 967 132 824

speng@lemo.com

UNITED ARAB EMIRATES

LEMO Middle East Connectors LLC

Concorde Tower 11th Floor,

Office 1102, Dubai Media City,

P.O. Box 449849

Dubai, United Arab Emirates

Tel: +971 4 568 1904

info-me@lemo.com

UNITED KINGDOM

LEMO UK Ltd

12-20 North Street, Worthing,

West Sussex, BN11 1DU

Tel: +44 1903 23 45 43

lemouk@lemo.com

USA

LEMO USA Inc

P.O. Box 2408

Rohnert Park, CA 94927-2408

Tel: +1 707 578 88 11

+1 800 444 53 66

Fax: +1 707 578 08 69

info-US@lemo.com

LEMO DISTRIBUTORS

ARGENTINA, AUSTRALIA, BRAZIL, CHILE, COLOMBIA, CZECH REPUBLIC,
GREECE, ISRAEL, NEW ZEALAND, PERU, POLAND, SOUTH AFRICA,
SOUTH KOREA, TURKEY, UKRAINE

www.lemo.com

