

1624043

https://www.phoenixcontact.com/us/products/1624043

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CHARX connect, Infrastructure charging socket, for charging electric vehicles (EV) with alternating current (AC), Type 2, IEC 62196-2, 32 A / 480 V (AC), length: 1 m, locking actuator: 12 V, 4-pos., Rear panel mounting, PHOENIX CONTACT logo

Product description

Infrastructure charging socket for charging electric vehicles (EV) with alternating current (AC), compatible with type 2 Infrastructure Plugs, for installation at charging stations for E-Mobility (EVSE)

Your advantages

- · Complete product range
- · Uniform, space-saving installation space
- · Available with your logo on request for consistent branding of your charging station
- · Integrated interlock during charging
- · Manual emergency release of the locking actuator
- · Developed and produced in accordance with the IATF 16949 automotive standard and ISO 9001

Commercial data

Item number	1624043
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	EM01
Product key	XWBADC
GTIN	4055626228129
Weight per piece (including packing)	760.2 g
Weight per piece (excluding packing)	760.2 g
Customs tariff number	85444290
Country of origin	DE



1624043

https://www.phoenixcontact.com/us/products/1624043

Technical data

Product properties

Product type	Infrastructure charging socket
Product family	CHARX connect
Application	for charging electric vehicles (EV) with alternating current (AC)
	compatible with infrastructure charging plugs
Affixed logo	PHOENIX CONTACT logo
Charging standard	Type 2
Charging mode	Mode 3, Case B

Electrical properties

Type of signal transmission	Pulse width modulation
Note on the connection method	Crimp connection, cannot be disconnected
Type of charging current	AC 3-phase
Charging power	26.6 kW
Charging current	32 A

Power contact

Number	5 (L1, L2, L3, N, PE)
Rated voltage	480 V AC
Rated current	32 A

Signal contact

Number	2 (CP, PP)
Rated voltage	30 V AC
Rated current	2 A

Locking actuator

Operating voltage	12 V
Note number of positions	4-pos.
Position of the locking actuator	top center

Locking actuator		
Operating voltage	12 V	
Note number of positions	4-pos.	
Position of the locking actuator	top center	
Possible power supply range at the motor	9 V 16 V	
Maximum voltage for locking detection	30 V	
Typical motor current for locking	0.2 A	
Reverse current of the motor	max. 1 A	
Max. dwell time with reverse current	1000 ms	
Recommended adaptation time	600 ms	
Pause time after entry or exit path	3 s	



1624043

https://www.phoenixcontact.com/us/products/1624043

Service life insertion cycles	> 10000 load cycles
Lock recognition	available
Mechanical emergency release	available
Ambient temperature (operation)	-30 °C 50 °C
Cable length	0.5 m
Cable structure	4 x 0.5 mm²

Cable/line

Cable length	1 m (AC cables)
	0.5 m (Locking actuator cables)
Cable structure	5x 6.0 mm² + 2x 0.5 mm²

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 10000
Insertion force	< 100 N
Withdrawal force	< 100 N

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-30 °C 50 °C
Ambient temperature (storage/transport)	-40 °C 80 °C
Altitude	5000 m (above sea level)

Standards and regulations

Standards

Standards/regulations	IEC 62196-2
S .	

Mounting


Mounting type Infrastructure charging socket	Rear panel mounting (0 to 90 degree frontal inclination possible)
	Front mounting (only possible when the locking actuator is removed (see EV-T2M3SEE00 versions))
Mounting type Protective cover	rear (available separately)
Mounting hole diameter	7.00 mm (ø)



1624043

https://www.phoenixcontact.com/us/products/1624043

Drawings




Operating instructions




1624043

https://www.phoenixcontact.com/us/products/1624043



Hole image

Connection diagram




Pin assignment of infrastructure charging socket



1624043

https://www.phoenixcontact.com/us/products/1624043




Detection of the Infrastructure Plug



1624043

https://www.phoenixcontact.com/us/products/1624043




Locking states of the locking actuator




1624043

https://www.phoenixcontact.com/us/products/1624043


Dimensional drawing





Dimensional drawing

Schematic diagram




Installation positions



1624043

https://www.phoenixcontact.com/us/products/1624043

Schematic diagram



Rear mounting with rear protective cover screw connection


The screw connection for a protective cover from the accessories range (EV-T2SC) only supports rear mounting. The panel thickness must not exceed 5 mm. The sealing frame that is slid on from the rear must contact the housing panel flush with the flat side and must completely surround the infrastructure socket outlet.



1624043

https://www.phoenixcontact.com/us/products/1624043






Front mounting with rear protective cover screw connection

Front mounting is only possible when the locking actuator is removed. We recommend using an infrastructure socket outlet without pre-assembled locking actuator (EV-T2M3SE-...E0..., e.g., 1621729).

The screw connection for a protective cover from the accessories range (EV-T2SC) only supports rear mounting. The panel thickness must not exceed 10 mm. The sealing frame that is slid on from the front must contact the housing panel flush with the flat side and must completely surround the infrastructure socket outlet.

Block diagram




Block diagram of the locking actuator



1624043

https://www.phoenixcontact.com/us/products/1624043

Schematic diagram




Panel thickness for rear mounting (max. 50 mm, with Phoenix Contact protective cover, max. 22 mm)



1624043

https://www.phoenixcontact.com/us/products/1624043

Schematic diagram



Panel thickness for front mounting (in mm)



1624043

https://www.phoenixcontact.com/us/products/1624043

Classifications

ECLASS

	ECLASS-11.0	27144706		
1U	UNSPSC			
	UNSPSC 21.0	39121522		



1624043

https://www.phoenixcontact.com/us/products/1624043

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)



1624043

https://www.phoenixcontact.com/us/products/1624043

Accessories

EV-LABEL-C-SO - Label

1315521

https://www.phoenixcontact.com/us/products/1315521

CHARX connect, Label, Accessories, for AC type 2 infrastructure charging socket and for AC type 2 infrastructure charging plug, DIN EN 17186



EV-T2SC - Protective cover

1405217

https://www.phoenixcontact.com/us/products/1405217



CHARX connect basic, Protective cover, square, Accessories, with self-locking mechanism, for attaching to infrastructure charging sockets, Type 2, IEC 62196-2, Front mounting, M5 thread, housing: black, Embossed PHOENIX CONTACT logo



1624043

https://www.phoenixcontact.com/us/products/1624043

EV-T2SF - Panel-mount frame

1405218

https://www.phoenixcontact.com/us/products/1405218



CHARX connect basic, Panel-mount frame, Accessories, for attaching to infrastructure charging sockets, Type 2, IEC 62196-2, Front mounting, M5 thread, housing: black, Without logo

EV-GBSCO - Protective cover

1623415

https://www.phoenixcontact.com/us/products/1623415



CHARX connect basic, Protective cover, circular, Accessories, with self-opening mechanism, for attaching to infrastructure charging sockets, GB/T, Type 2, GB/T 20234.2, IEC 62196-2, Front mounting, housing: black, Adhered "PHOENIX CONTACT" sticker



1624043

https://www.phoenixcontact.com/us/products/1624043

EV-GBSC - Protective cover

1623416

https://www.phoenixcontact.com/us/products/1623416



CHARX connect basic, Protective cover, circular, Accessories, with self-locking mechanism, for attaching to infrastructure charging sockets, GB/T, Type 2, GB/T 20234.2, IEC 62196-2, Front mounting, housing: black, Adhered "PHOENIX CONTACT" sticker

EV-GBSC-D6,5MM - Protective cover

1623888

https://www.phoenixcontact.com/us/products/1623888



CHARX connect basic, Protective cover, circular, Accessories, with self-locking mechanism, for attaching to infrastructure charging sockets, GB/T, Type 2, GB/T 20234.2, IEC 62196-2, Front mounting, housing: black, Adhered "PHOENIX CONTACT" sticker



1624043

https://www.phoenixcontact.com/us/products/1624043

EV-T2M3S-E-LOCK12V - Locking

1624129

https://www.phoenixcontact.com/us/products/1624129



CHARX connect modular, Locking, Accessories, for attaching to infrastructure charging sockets, Type 2, GB/T, IEC 61851-1, Single wires, length: 0.5 m, locking actuator: 12 V, 4-pos.

EV-T2M3S-E-LOCK24V - Locking

1622317

https://www.phoenixcontact.com/us/products/1622317



CHARX connect modular, Locking, Accessories, with single-core wires, without holder, for locking infrastructure charging sockets when plug is inserted, Type 2, GB/T, IEC 61851-1, Single wires, length: 0.5 m, locking actuator: 24 V, 4-pos.



1624043

https://www.phoenixcontact.com/us/products/1624043

EV-T2M3S-DRAINAGE-GASKET - Seal

1621668

https://www.phoenixcontact.com/us/products/1621668




CHARX connect basic, Seal, For the discharge nozzle below the infrastructure charging socket if there is no drainage tube present, Type 2, IEC 62196-2

EV-T2M3S-E-LOCK-GASKET - Seal

1621465

https://www.phoenixcontact.com/us/products/1621465







1624043

https://www.phoenixcontact.com/us/products/1624043

EM-CP-PP-ETH - AC charging controller

2902802

https://www.phoenixcontact.com/us/products/2902802



EV charge control is used to charge electrical vehicles on the 3-phase AC mains power supply according to IEC 61851-1 Mode 3. All necessary control functions are integrated. Additional functions are available for various charging applications.

EV-CC-AC1-M3-CBC-SER-HS - AC charging controller

1622452

https://www.phoenixcontact.com/us/products/1622452



The EV-CC-AC1-M3-CBC-SER-HS charging controller with housing for DIN rail mounting is used for charging electric vehicles at 3-phase AC networks according to IEC 61851-1, Mode 3. All charging functions, comprehensive configuration settings as well as a locking controller are already integrated.



1624043

https://www.phoenixcontact.com/us/products/1624043

EV-CC-AC1-M3-CBC-SER-PCB - AC charging controller

1622453

https://www.phoenixcontact.com/us/products/1622453



The EV-CC-AC1-M3-CBC-SER-PCB charging controller as PCB is used for charging electric vehicles at 3-phase AC networks according to IEC 61851-1, Mode 3. All charging functions, comprehensive configuration settings as well as a locking controller are already integrated.

EV-CC-AC1-M3-CBC-SER-PCB-XC-25 - AC charging controller

1627743

https://www.phoenixcontact.com/us/products/1627743



The EV-CC-AC1-M3-CBC-SER-PCB charging controller as PCB is used for charging electric vehicles at 3-phase AC networks according to IEC 61851-1, Mode 3. All charging functions, comprehensive configuration settings as well as a locking controller are already integrated.



1624043

https://www.phoenixcontact.com/us/products/1624043

EV-CC-AC1-M3-CBC-SER-PCB-MSTB - AC charging controller

1627353

https://www.phoenixcontact.com/us/products/1627353



The EV-CC-AC1-M3-CBC-SER-PCB-MSTB charging controller as a PCB for charging electric vehicles according to IEC 61851-1, Mode 3, Case B (Socket Outlet) or C (Vehicle Connector). Connection via PCB connector on header.

Phoenix Contact 2024 @ - all rights reserved https://www.phoenixcontact.com

Phoenix Contact USA 586 Fulling Mill Road Middletown, PA 17057, United States (+717) 944-1300 info@phoenixcon.com