

### Features

- Supply Voltage: 3V to 36V
- Offset Voltage:  $\pm 2\text{mV}$  Maximum
- Differential Input Voltage Range to Supply Rail, can Work as Comparator
- Bandwidth: 1.5MHz, Slew Rate:  $0.5\text{V}/\mu\text{s}$
- Input Rail to  $-V_s$ , No Internal ESD Diode to  $+V_s$
- Low  $1/f$  Noise:  $50\text{ nV}/\sqrt{\text{Hz}}$  at 10Hz
- High PSRR+: 60dB at 100KHz
- No significant output glitch when power on and off
- $-40^\circ\text{C}$  to  $125^\circ\text{C}$  Operation Temperature Range


### Applications

- Instrumentation
- Sensor Interface
- Motor Control
- Industrial Control






### Description

The TPA264X series amplifiers are newest high supply voltage amplifiers with 2mV offset, low noise and immunity to high frequency noise from power supply. They incorporate 3PEAK's proprietary and patented design techniques to achieve very good AC performance with 1.5MHz bandwidth,  $0.5\text{V}/\mu\text{s}$  slew rate and low distortion while drawing only  $550\mu\text{A}$  of quiescent current per amplifier.

The input common-mode voltage range extends to  $-V_s$ , and no internal ESD diode between input and  $+V_s$ . This feature can block the current path from input to  $+V_s$  when power down but the signal still in input pin, it's usual in battery related application.



### Pin Configuration



The thermal pad of DFN package is recommended to be left float or connected to  $-V_s$

## Table of Contents

|                                                  |    |
|--------------------------------------------------|----|
| Features .....                                   | 1  |
| Applications .....                               | 1  |
| Description .....                                | 1  |
| Pin Configuration .....                          | 1  |
| Table of Contents .....                          | 2  |
| Revision History .....                           | 3  |
| Order Information .....                          | 3  |
| Absolute Maximum Ratings <sup>Note 1</sup> ..... | 4  |
| ESD and Latch Up Rating .....                    | 4  |
| Thermal Information .....                        | 4  |
| Electrical Characteristics .....                 | 5  |
| Typical Performance Characteristics .....        | 7  |
| Tape and Reel Information .....                  | 12 |
| Package Outline Dimensions .....                 | 13 |
| SOT23-5 .....                                    | 13 |
| SOP8 .....                                       | 14 |
| TSSOP8 .....                                     | 15 |
| MSOP8 .....                                      | 16 |
| SOP14 .....                                      | 17 |
| TSSOP14 .....                                    | 18 |
| IMPORTANT NOTICE AND DISCLAIMER .....            | 19 |

## Revision History

| Date      | Revision | Notes                                                                                                                                                                                                                                           |
|-----------|----------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 2020/4/26 | Rev.A.0  | Initial version                                                                                                                                                                                                                                 |
| 2023/4/9  | Rev.A.1  | The following updates are all about the new datasheet formats or typo, the actual product remains unchanged.<br>Updated Package Outline Dimensions.                                                                                             |
| 2023/11/5 | Rev.A.2  | The following updates are all about the new datasheet formats or typo, the actual product remains unchanged.<br>Updated Input Voltage Noise in Electrical Characteristics: $1\mu\text{V}_{\text{RMS}} \rightarrow 1.6\mu\text{V}_{\text{PP}}$ . |

## Order Information

| Order Number                   | Operating Temperature Range | Package       | Marking Information | MSL | Transport Media, Quantity |
|--------------------------------|-----------------------------|---------------|---------------------|-----|---------------------------|
| TPA2641-S5TR                   | -40 to 125°C                | 5-Pin SOT23   | 641                 | 3   | Tape and Reel, 3000       |
| TPA2641U-S5TR                  | -40 to 125°C                | 5-Pin SOT23   | 64U                 | 3   | Tape and Reel, 3000       |
| TPA2642-SO1R                   | -40 to 125°C                | 8-Pin SOIC    | A2642               | 3   | Tape and Reel, 4000       |
| TPA2642-DF4R <sup>Note 1</sup> | -40 to 125°C                | 8-Pin DFN 2*2 | 642                 | 3   | Tape and Reel, 3000       |
| TPA2642-TS1R <sup>Note 1</sup> | -40 to 125°C                | 8-Pin TSSOP   | A2642               | 3   | Tape and Reel, 3000       |
| TPA2642-VS1R                   | -40 to 125°C                | 8-Pin MSOP    | A2642               | 3   | Tape and Reel, 3000       |
| TPA2644-SO2R                   | -40 to 125°C                | 14-Pin SOIC   | A2644               | 3   | Tape and Reel, 2500       |
| TPA2644-TS2R                   | -40 to 125°C                | 14-Pin TSSOP  | A2644               | 3   | Tape and Reel, 3000       |

Note 1: For future product, contact the 3PEAK factory for more information and samples.

## Absolute Maximum Ratings <sup>Note 1</sup>

| Parameters                                                           | Rating                                               |
|----------------------------------------------------------------------|------------------------------------------------------|
| Supply Voltage, (+V <sub>S</sub> )– (–V <sub>S</sub> )               | 40 V                                                 |
| Input Voltage                                                        | (–V <sub>S</sub> ) – 0.3 to 40V                      |
| Input Current: +I <sub>IN</sub> , –I <sub>IN</sub> <sup>Note 2</sup> | ±10mA                                                |
| Output Voltage                                                       | (–V <sub>S</sub> ) – 0.3 to (+V <sub>S</sub> ) + 0.3 |
| Output Short-Circuit Duration <sup>Note 3</sup>                      | Infinite                                             |
| Maximum Junction Temperature                                         | 150°C                                                |
| Operating Temperature Range                                          | –40 to 125°C                                         |
| Storage Temperature Range                                            | –65 to 150°C                                         |
| Lead Temperature (Soldering, 10 sec)                                 | 260°C                                                |

Note 1: Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. Exposure to any Absolute Maximum Rating condition for extended periods may affect device reliability and lifetime.

Note 2: The inputs are protected by ESD protection diodes to negative power supply. If the input extends more than 300mV beyond the negative power supply, the input current should be limited to less than 10mA.

Note 3: A heat sink may be required to keep the junction temperature below the absolute maximum. This depends on the power supply voltage and how many amplifiers are shorted. Thermal resistance varies with the amount of PC board metal connected to the package. The specified values are for short traces connected to the leads.

## ESD and Latch Up Rating

| Symbol | Parameter                | Condition              | Minimum Level | Unit |
|--------|--------------------------|------------------------|---------------|------|
| HBM    | Human Body Model ESD     | ANSI/ESDA/JEDEC JS-001 | 2             | kV   |
| CDM    | Charged Device Model ESD | ANSI/ESDA/JEDEC JS-002 | 1             | kV   |

## Thermal Information

| Package Type  | $\theta_{JA}$ | $\theta_{JC}$ | Unit |
|---------------|---------------|---------------|------|
| 5-Pin SOT23   | 250           | 81            | °C/W |
| 8-Pin SOIC    | 158           | 43            | °C/W |
| 8-Pin MSOP    | 210           | 45            | °C/W |
| 8-Pin TSSOP   | 191           | 44            | °C/W |
| 8-Pin DFN 2*2 | 100           | 60            | °C/W |
| 14-Pin SOIC   | 120           | 36            | °C/W |
| 14-Pin TSSOP  | 180           | 35            | °C/W |

## Electrical Characteristics

All test condition is at  $T_A = 25^\circ\text{C}$ ,  $R_L = 10\text{k}\Omega$ ,  $C_L = 100\text{pF}$ , unless otherwise noted.

| Symbol                 | Parameter                               | Conditions                                        | T <sub>A</sub> | Min                | Typ | Max                  | Unit  |
|------------------------|-----------------------------------------|---------------------------------------------------|----------------|--------------------|-----|----------------------|-------|
| Power Supply           |                                         |                                                   |                |                    |     |                      |       |
| V <sub>S</sub>         | Supply Voltage Range                    |                                                   |                | 3                  |     | 36                   | V     |
| I <sub>Q</sub>         | Quiescent Current per Amplifier         | V <sub>S</sub> = 5V to 36V                        |                |                    | 350 | 550                  | μA    |
|                        |                                         |                                                   | -40°C to 125°C |                    |     | 650                  | μA    |
| PSRR                   | Power Supply Rejection Ratio            | V <sub>S</sub> = 5V to 36V                        |                | 100                | 120 |                      | dB    |
|                        |                                         |                                                   | -40°C to 125°C | 95                 |     |                      | dB    |
| Input Characteristics  |                                         |                                                   |                |                    |     |                      |       |
| V <sub>OS</sub>        | Input Offset Voltage                    | V <sub>S</sub> = 36V, V <sub>CM</sub> = 0V to 28V |                | -2                 | 0.1 | 2                    | mV    |
|                        |                                         |                                                   | -40°C to 85°C  | -3                 |     | 3                    | mV    |
|                        |                                         |                                                   | -40°C to 125°C | -3.5               |     | 3.5                  | mV    |
|                        |                                         | V <sub>S</sub> = 5V, V <sub>CM</sub> = 2.5V       |                | -2                 | 0.1 | 2                    | mV    |
|                        |                                         |                                                   | -40°C to 85°C  | -3                 |     | 3                    |       |
|                        |                                         |                                                   | -40°C to 125°C | -3.5               |     | 3.5                  | mV    |
| V <sub>OS</sub> TC     | Input Offset Voltage Drift              |                                                   | -40°C to 125°C |                    | 5   |                      | μV/°C |
| I <sub>B</sub>         | Input Bias Current                      | V <sub>S</sub> = 36V, V <sub>CM</sub> = 18V       |                |                    | 15  | 30                   | nA    |
|                        |                                         |                                                   | -40°C to 125°C |                    |     | 50                   | nA    |
| I <sub>OS</sub>        | Input Offset Current                    | V <sub>S</sub> = 36V, V <sub>CM</sub> = 18V       |                |                    | 1   | 10                   | nA    |
|                        |                                         |                                                   | -40°C to 125°C |                    |     | 30                   | nA    |
| I <sub>B</sub>         | Input Bias Current                      | V <sub>S</sub> = 36V, V <sub>CM</sub> = 0V        |                |                    | 20  | 50                   | nA    |
|                        |                                         |                                                   | -40°C to 125°C |                    |     | 100                  | nA    |
| I <sub>OS</sub>        | Input Offset Current                    | V <sub>S</sub> = 36V, V <sub>CM</sub> = 0V        |                |                    | 1   | 30                   | nA    |
|                        |                                         |                                                   | -40°C to 125°C |                    |     | 50                   | nA    |
| I <sub>IN</sub>        | Different Input Current                 | V <sub>S</sub> = 36V, V <sub>ID</sub> = 36V       |                | -300               | 50  | 300                  | nA    |
|                        |                                         | V <sub>S</sub> = 36V, V <sub>ID</sub> = 36V       | -40°C to 125°C | -500               |     | 500                  | nA    |
| C <sub>IN</sub>        | Input Capacitance                       | Differential Mode                                 |                |                    | 5   |                      | pF    |
|                        |                                         | Common Mode                                       |                |                    | 5   |                      | pF    |
| A <sub>v</sub>         | Open-loop Voltage Gain                  |                                                   |                | 110                | 130 |                      | dB    |
|                        |                                         | -40°C to 125°C                                    | 100            |                    |     | dB                   |       |
| V <sub>CMR</sub>       | Common-mode Input Voltage Range         |                                                   | -40°C to 125°C | (-V <sub>S</sub> ) |     | (+V <sub>S</sub> )-2 | V     |
| CMRR                   | Common Mode Rejection Ratio             | V <sub>CM</sub> = 0V to 28V                       |                | 85                 | 110 |                      | dB    |
|                        |                                         |                                                   | -40°C to 125°C | 80                 |     |                      | dB    |
| Output Characteristics |                                         |                                                   |                |                    |     |                      |       |
|                        | Output Voltage Swing from Positive Rail | I <sub>LOAD</sub> = 50μA to V <sub>S</sub> /2     |                |                    | 1.1 | 1.2                  | V     |
|                        |                                         |                                                   | -40°C to 125°C |                    |     | 1.4                  | V     |
|                        |                                         | I <sub>LOAD</sub> = 1mA to V <sub>S</sub> /2      |                |                    | 1.3 | 1.5                  | V     |
|                        |                                         |                                                   | -40°C to 125°C |                    |     | 1.7                  | V     |

|          |                                         |                                                 |                |  |     |     |    |
|----------|-----------------------------------------|-------------------------------------------------|----------------|--|-----|-----|----|
|          |                                         | $I_{LOAD} = 5mA \text{ to } V_S/2$              |                |  | 1.9 | 2.4 | V  |
|          |                                         |                                                 | -40°C to 125°C |  |     | 2.5 | V  |
|          | Output Voltage Swing from Negative Rail | $I_{LOAD} = 50\mu A \text{ to } V_S/2$          |                |  | 70  | 100 | mV |
|          |                                         |                                                 | -40°C to 125°C |  |     | 150 | mV |
|          |                                         | $I_{LOAD} = 1mA \text{ to } V_S/2$              |                |  | 0.9 | 1   | V  |
|          |                                         |                                                 | -40°C to 125°C |  |     | 1.1 | V  |
|          |                                         | $I_{LOAD} = 5mA \text{ to } V_S/2$              |                |  | 1.2 | 1.5 | V  |
|          |                                         |                                                 | -40°C to 125°C |  |     | 1.6 | V  |
| $I_{SC}$ | Output Short-Circuit Current            | $V_S = 5V, R_{LOAD} = 10k\Omega \text{ to } 0V$ |                |  | 5   | 10  | mV |
|          |                                         |                                                 | -40°C to 125°C |  |     | 15  | mV |
|          |                                         |                                                 |                |  | 50  |     | mA |
|          |                                         |                                                 | -40°C to 125°C |  | 30  |     | mA |

| AC Specifications |                                     |                                                        |  |  |      |  |                 |
|-------------------|-------------------------------------|--------------------------------------------------------|--|--|------|--|-----------------|
| GBW               | Gain-Bandwidth Product              |                                                        |  |  | 1.5  |  | MHz             |
| SR                | Slew Rate                           | $G = 1, 2V \text{ step}$                               |  |  | 0.5  |  | V/ $\mu s$      |
| $t_{OR}$          | Overload Recovery                   | From positive rail                                     |  |  | 1.5  |  | $\mu s$         |
|                   |                                     | From negative rail                                     |  |  | 8    |  | $\mu s$         |
| $t_s$             | Settling Time, 0.1%                 | $G = 1, 2V \text{ step}$                               |  |  | 3    |  | $\mu s$         |
|                   | Settling Time, 0.01%                |                                                        |  |  | 4    |  | $\mu s$         |
| PM                | Phase Margin                        | $R_L = 10K, C_L = 100pF$                               |  |  | 60   |  | °               |
| GM                | Gain Margin                         | $R_L = 10K, C_L = 100pF$                               |  |  | 15   |  | dB              |
|                   | Channel Separation                  | $f = 100 \text{ kHz}$                                  |  |  | 120  |  | dB              |
| Noise Performance |                                     |                                                        |  |  |      |  |                 |
| $E_N$             | Input Voltage Noise                 | $f = 0.1Hz \text{ to } 10Hz$                           |  |  | 1.6  |  | $\mu V_{PP}$    |
| $e_N$             | Input Voltage Noise Density         | $f = 1kHz$                                             |  |  | 50   |  | nV/ $\sqrt{Hz}$ |
| $i_N$             | Input Current Noise                 | $f = 1kHz$                                             |  |  | 200  |  | fA/ $\sqrt{Hz}$ |
| THD+N             | Total Harmonic Distortion and Noise | $f = 1kHz, G = 1, R_L = 10k\Omega, V_{OUT} = 6V_{RMS}$ |  |  | 0.01 |  | %               |

## Typical Performance Characteristics

$V_S = \pm 15V$ ,  $V_{CM} = 0V$ ,  $R_L = 10k\Omega$ , unless otherwise specified.




Figure 1. Offset Voltage vs. Common Mode Voltage,  $V_S = 5V$




Figure 2. Offset Voltage vs. Common Mode Voltage,  $V_S = 30V$




Figure 3. Offset Voltage vs. Temperature,  $V_S = 30V$ ,  $V_{CM} = 15V$




Figure 4.  $I_q$  vs. Temperature,  $\pm 15V$  Supply, TPA2642




Figure 5.  $I_B$  vs. Common Mode Voltage,  $V_S = 30V$




Figure 6.  $I_B$  and  $I_{OS}$  vs. Temperature,  $V_S = 30V$ ,  $V_{CM} = 15V$




Figure 7. -3dB Bandwidth,  $G = 1$ ,  $V_s = 30V$




Figure 8. Open Loop Gain and Phase vs. Frequency




Figure 9. PSRR vs. Frequency




Figure 10. CMRR vs. Frequency




Time: 10μs/div, Measure Time: 1.4μs,  $G=11$

Figure 11. Positive Overload Recovery



Time: 10μs/div, Measure Time: 7.8μs,  $G=11$

Figure 12. Negative Overload Recovery



Voltage: 200mV/div, Time: 5μs/div  
 $R_L=100K$ ,  $C_L=1nF$ ,  $G=1$   
 Figure 13. 1V Signal Step Response



Voltage: 2mV/div, Time: 5μs/div  
 $C_L=50pF$ ,  $G=1$   
 Figure 14. 10mV Signal Step Response




Figure 15. Voltage Noise Density vs. Frequency




Figure 16. 0.1 to 10Hz Voltage Noise




Figure 17.  $V_{OUT}$  vs.  $I_{OUT}$ , Source




Figure 18.  $V_{OUT}$  vs.  $I_{OUT}$ , Sink

Power On and Off Behavior, 36V Single Supply,  $G = 1$ , Input =  $V_s / 2$ , Yellow:  $V_s$ , Green: Output



Figure 19. 2ms Power On and Off Time



Figure 20. 10ms Power On and Off Time



Figure 21. 100ms Power On and Off Time



Figure 22. 1s Power On and Off Time

Power On and Off Behavior, +18V and -18V Dual Supply, G = 1, Input = Ground, Green: +Vs, Red: -Vs, Yellow: Output.



Figure 23. 1ms Power On and Off Time



Figure 24. 10ms Power On and Off Time




Figure 25. 100ms Power On and Off Time



Figure 26. 1s Power On and Off Time

## Tape and Reel Information




| Order Number  | Package      | D1    | W1   | A0  | B0  | K0  | P0  | W0   | Pin1<br>Quadrant |
|---------------|--------------|-------|------|-----|-----|-----|-----|------|------------------|
| TPA2641-S5TR  | 5-Pin SOT23  | 180.0 | 13.1 | 3.2 | 3.2 | 1.4 | 4.0 | 8.0  | Q3               |
| TPA2641U-S5TR | 5-Pin SOT23  | 180.0 | 13.1 | 3.2 | 3.2 | 1.4 | 4.0 | 8.0  | Q3               |
| TPA2642-SO1R  | 8-Pin SOIC   | 330.0 | 17.6 | 6.4 | 5.4 | 2.1 | 8.0 | 12.0 | Q1               |
| TPA2642-DF4R  | 8-Pin DFN2*2 | 180.0 | 13.1 | 2.3 | 2.3 | 1.1 | 4.0 | 8.0  | Q1               |
| TPA2642-TS1R  | 8-Pin TSSOP  | 330.0 | 17.6 | 6.8 | 3.3 | 1.2 | 8.0 | 12.0 | Q1               |
| TPA2642-VS1R  | 8-Pin MSOP   | 330.0 | 17.6 | 5.2 | 3.3 | 1.5 | 8.0 | 12.0 | Q1               |
| TPA2644-SO2R  | 14-Pin SOIC  | 330.0 | 21.6 | 6.5 | 9.0 | 2.1 | 8.0 | 16.0 | Q1               |
| TPA2644-TS2R  | 14-Pin TSSOP | 330.0 | 17.6 | 6.8 | 5.4 | 1.2 | 8.0 | 12.0 | Q1               |

## Package Outline Dimensions

### SOT23-5

#### Package Outline Dimensions





#### S5T(SOT23-5-A)



| Symbol | Dimensions<br>In Millimeters |       | Dimensions<br>In Inches |       |
|--------|------------------------------|-------|-------------------------|-------|
|        | MIN                          | MAX   | MIN                     | MAX   |
| A      | 1.050                        | 1.250 | 0.041                   | 0.049 |
| A1     | 0.000                        | 0.150 | 0.000                   | 0.006 |
| A2     | 1.000                        | 1.200 | 0.039                   | 0.047 |
| b      | 0.280                        | 0.500 | 0.011                   | 0.020 |
| c      | 0.100                        | 0.230 | 0.004                   | 0.009 |
| D      | 2.820                        | 3.020 | 0.111                   | 0.119 |
| E      | 2.600                        | 3.000 | 0.102                   | 0.118 |
| E1     | 1.500                        | 1.720 | 0.059                   | 0.068 |
| e      | 0.950 BSC                    |       | 0.037 BSC               |       |
| L      | 0.300                        | 0.600 | 0.012                   | 0.024 |
| θ      | 0                            | 8°    | 0                       | 8°    |

#### NOTES




1. Do not include mold flash or protrusion.
2. This drawing is subject to change without notice.

**SOP8**
**Package Outline Dimensions**
**SO1(SOP-8-A)**


| Symbol   | Dimensions<br>In Millimeters |       | Dimensions<br>In Inches |       |
|----------|------------------------------|-------|-------------------------|-------|
|          | MIN                          | MAX   | MIN                     | MAX   |
| A        | 1.350                        | 1.750 | 0.053                   | 0.069 |
| A1       | 0.050                        | 0.250 | 0.002                   | 0.010 |
| A2       | 1.250                        | 1.550 | 0.049                   | 0.061 |
| b        | 0.330                        | 0.510 | 0.013                   | 0.020 |
| c        | 0.170                        | 0.250 | 0.007                   | 0.010 |
| D        | 4.700                        | 5.100 | 0.185                   | 0.201 |
| E        | 5.800                        | 6.200 | 0.228                   | 0.244 |
| E1       | 3.800                        | 4.000 | 0.150                   | 0.157 |
| e        | 1.270 BSC                    |       | 0.050 BSC               |       |
| L        | 0.400                        | 1.000 | 0.016                   | 0.039 |
| $\theta$ | 0                            | 8°    | 0                       | 8°    |

**NOTES**





1. Do not include mold flash or protrusion.
2. This drawing is subject to change without notice.

**TSSOP8**
**Package Outline Dimensions**
**TS1(TSSOP-8-A)**


| Symbol | Dimensions<br>In Millimeters |       | Dimensions<br>In Inches |       |
|--------|------------------------------|-------|-------------------------|-------|
|        | MIN                          | MAX   | MIN                     | MAX   |
| A      | 0.900                        | 1.200 | 0.035                   | 0.047 |
| A1     | 0.050                        | 0.150 | 0.002                   | 0.006 |
| A2     | 0.800                        | 1.050 | 0.031                   | 0.041 |
| b      | 0.190                        | 0.300 | 0.007                   | 0.012 |
| c      | 0.090                        | 0.200 | 0.004                   | 0.008 |
| D      | 2.900                        | 3.100 | 0.114                   | 0.122 |
| E      | 6.200                        | 6.600 | 0.244                   | 0.260 |
| E1     | 4.300                        | 4.500 | 0.169                   | 0.177 |
| e      | 0.650 BSC                    |       | 0.026 BSC               |       |
| L      | 0.450                        | 0.750 | 0.018                   | 0.030 |
| θ      | 0                            | 8°    | 0                       | 8°    |

**NOTES**


1. Do not include mold flash or protrusion.
2. This drawing is subject to change without notice.

**MSOP8**
**Package Outline Dimensions**
**VS1(MSOP-8-A)**


| Symbol   | Dimensions<br>In Millimeters |       | Dimensions<br>In Inches |       |
|----------|------------------------------|-------|-------------------------|-------|
|          | MIN                          | MAX   | MIN                     | MAX   |
| A        | 0.800                        | 1.100 | 0.031                   | 0.043 |
| A1       | 0.050                        | 0.150 | 0.002                   | 0.006 |
| A2       | 0.750                        | 0.950 | 0.030                   | 0.037 |
| b        | 0.250                        | 0.380 | 0.010                   | 0.015 |
| c        | 0.090                        | 0.230 | 0.004                   | 0.009 |
| D        | 2.900                        | 3.100 | 0.114                   | 0.122 |
| E        | 4.700                        | 5.100 | 0.185                   | 0.201 |
| E1       | 2.900                        | 3.100 | 0.114                   | 0.122 |
| e        | 0.650 BSC                    |       | 0.026 BSC               |       |
| L        | 0.400                        | 0.800 | 0.016                   | 0.031 |
| $\theta$ | 0                            | 8°    | 0                       | 8°    |

**NOTES**




1. Do not include mold flash or protrusion.
2. This drawing is subject to change without notice.

**SOP14**
**Package Outline Dimensions**
**SO2(SOP-14-A)**


| Symbol | Dimensions<br>In Millimeters |       | Dimensions<br>In Inches |       |
|--------|------------------------------|-------|-------------------------|-------|
|        | MIN                          | MAX   | MIN                     | MAX   |
| A      | 1.350                        | 1.750 | 0.053                   | 0.069 |
| A1     | 0.050                        | 0.250 | 0.002                   | 0.010 |
| A2     | 1.250                        | 1.650 | 0.049                   | 0.065 |
| b      | 0.310                        | 0.510 | 0.012                   | 0.020 |
| c      | 0.100                        | 0.250 | 0.004                   | 0.010 |
| D      | 8.450                        | 8.850 | 0.333                   | 0.348 |
| E      | 5.800                        | 6.200 | 0.228                   | 0.244 |
| E1     | 3.800                        | 4.000 | 0.150                   | 0.157 |
| e      | 1.270 BSC                    |       | 0.050 BSC               |       |
| L      | 0.400                        | 1.270 | 0.016                   | 0.050 |
| θ      | 0                            | 8°    | 0                       | 8°    |

**NOTES**

1. Do not include mold flash or protrusion.
2. This drawing is subject to change without notice.

**TSSOP14**
**Package Outline Dimensions**
**TS2(TSSOP-14-A)**


| Symbol | Dimensions<br>In Millimeters |       | Dimensions<br>In Inches |       |
|--------|------------------------------|-------|-------------------------|-------|
|        | MIN                          | MAX   | MIN                     | MAX   |
| A      | 0.900                        | 1.200 | 0.035                   | 0.047 |
| A1     | 0.050                        | 0.150 | 0.002                   | 0.006 |
| A2     | 0.800                        | 1.050 | 0.031                   | 0.041 |
| b      | 0.190                        | 0.300 | 0.007                   | 0.012 |
| c      | 0.090                        | 0.200 | 0.004                   | 0.008 |
| D      | 4.900                        | 5.100 | 0.193                   | 0.201 |
| E      | 6.200                        | 6.600 | 0.244                   | 0.260 |
| E1     | 4.300                        | 4.500 | 0.169                   | 0.177 |
| e      | 0.650 BSC                    |       | 0.026 BSC               |       |
| L      | 0.450                        | 0.750 | 0.018                   | 0.030 |
| θ      | 0                            | 8°    | 0                       | 8°    |

**NOTES**

1. Do not include mold flash or protrusion.
2. This drawing is subject to change without notice.

## IMPORTANT NOTICE AND DISCLAIMER

**Copyright**© 3PEAK 2012-2023. All rights reserved.

**Trademarks.** Any of the 思瑞浦 or 3PEAK trade names, trademarks, graphic marks, and domain names contained in this document /material are the property of 3PEAK. You may NOT reproduce, modify, publish, transmit or distribute any Trademark without the prior written consent of 3PEAK.

**Performance Information.** Performance tests or performance range contained in this document/material are either results of design simulation or actual tests conducted under designated testing environment. Any variation in testing environment or simulation environment, including but not limited to testing method, testing process or testing temperature, may affect actual performance of the product.

**Disclaimer.** 3PEAK provides technical and reliability data (including data sheets), design resources (including reference designs), application or other design recommendations, networking tools, security information and other resources "As Is". 3PEAK makes no warranty as to the absence of defects, and makes no warranties of any kind, express or implied, including without limitation, implied warranties as to merchantability, fitness for a particular purpose or non-infringement of any third-party's intellectual property rights. Unless otherwise specified in writing, products supplied by 3PEAK are not designed to be used in any life-threatening scenarios, including critical medical applications, automotive safety-critical systems, aviation, aerospace, or any situations where failure could result in bodily harm, loss of life, or significant property damage. 3PEAK disclaims all liability for any such unauthorized use.