



# EVQ2179A-QH-00A

## 3A, 6V, 2.4MHz, AAM Mode, Synchronous Step-Down Converter Evaluation Board, AEC-Q100 Qualified

### DESCRIPTION

The EVQ2179A-QH-00A is an evaluation board designed to demonstrate the capabilities of the MPQ2179AGQHE-AEC1, a monolithic, step-down switch-mode converter with built-in internal power MOSFETs.

The MPQ2179A achieves 3A of output current ( $I_{OUT}$ ) from a 2.5V to 6V input voltage ( $V_{IN}$ ) range, with excellent load and line regulation. The output voltage ( $V_{OUT}$ ) can be regulated to as low as 0.6V. A 100% maximum duty cycle can be reached in low-dropout (LDO) mode.

Constant-on-time (COT) control offers a simpler control loop and faster transient response. By using  $V_{IN}$  feed-forward, the MPQ2179A maintains a nearly constant switching frequency ( $f_{SW}$ ) across the input and load ranges.

Advanced asynchronous modulation (AAM) mode provides high efficiency by reducing switching losses at light loads.

An open-drain power good (PG) signal indicates nominal voltage after the soft-start time. PG pulls high after the feedback voltage ( $V_{FB}$ ) reaches 90% of the reference voltage ( $V_{REF}$ ); PG pulls to GND when  $V_{FB}$  drops to 85% of  $V_{REF}$ .

Full protection features include cycle-by-cycle current limiting, short-circuit protection (SCP), reliable over-voltage protection (OVP), and thermal protection with automatic recovery.

The EVQ2179A-QH-00A is a fully assembled and tested evaluation board. The MPQ2179A is available in a QFN-8 (1.5mmx2mm) package, and is available in AEC-Q100 Grade 1.


### PERFORMANCE SUMMARY

Specifications are at  $T_A = 25^\circ\text{C}$ , unless otherwise noted.

Parameters	Conditions	Value
Input voltage ( $V_{IN}$ ) range		2.5V to 6V
Output voltage ( $V_{OUT}$ )	$V_{IN} = 2.5\text{V to }6\text{V}, I_{OUT} = 0\text{A to }3\text{A}$	1.2V
Maximum output current ( $I_{OUT}$ )	$V_{IN} = 2.5\text{V to }6\text{V}$	3A
Typical efficiency	$V_{IN} = 3.3\text{V}, V_{OUT} = 1.2\text{V}, I_{OUT} = 3\text{A}$	79.1%
Peak efficiency	$V_{IN} = 2.5\text{V}, V_{OUT} = 1.2\text{V}, I_{OUT} = 0.2\text{A}$	93%
Switching frequency ( $f_{SW}$ )		2.4MHz



**EVQ2179A-QH-00A EVALUATION BOARD**




**LxWxH (6.3cmx6.3cmx1cm)**

Board Number	MPS IC Number
EVQ2179A-QH-00A	MPQ2179AGQHE-AEC1

## QUICK START GUIDE

The EVQ2179A-QH-00A evaluation board is easy to set up and use to evaluate the MPQ2179A's performance. For proper measurement equipment set-up, refer to Figure 2 on page 4 and follow the steps below:

1. Preset the power supply ( $V_{IN}$ ) between 2.5V and 6V, then turn off the power supply.
2. Set the load current between 0A and 3A. Electronic loads represent a negative impedance to the regulator, and setting a current too high may trigger cycle-by-cycle over-current protection (OCP).
3. If longer cables (>0.5m total) are used between the source and the evaluation board, place a damping capacitor at the input terminals.
4. Connect the power supply terminals to:
  - a. Positive (+): VEMI
  - b. Negative (-): GND
5. Connect the load terminals to:
  - a. Positive (+): VOUT
  - b. Negative (-): GND
6. After making the connections, turn on the power supply.
7. To use the enable function, apply a digital input to the EN pin. Drive EN above 0.9V to turn the regulator on; drive EN below 0.65V to turn the regulator off. If the enable function is not used, EN can be connected directly to  $V_{IN}$ .
8. The external resistor divider sets the output voltage ( $V_{OUT}$ ) (see Figure 1).



**Figure 1: Feedback Divider Network with Adjustable Output**

R5 is selected to be between 10k $\Omega$  and 100k $\Omega$ . R6 can then be calculated with Equation (1):

$$R6 = \frac{R5}{\frac{V_{OUT}}{0.6} - 1} \quad (1)$$

Refer to the Application Information section in the MPQ2179A's datasheet to calculate the inductance and output capacitance for different  $V_{OUT}$  values. Figure 2 on page 4 shows the proper measurement equipment set-up.




Figure 2: Measurement Equipment Set-Up



### EVALUATION BOARD SCHEMATIC





Figure 3: Evaluation Board Schematic

### PACKAGE REFERENCE





## EVQ2179A-QH-00A BILL OF MATERIALS

Qty	Ref	Value	Description	Package	Manufacturer	Manufacturer PN
1	CIN1	1nF	Ceramic capacitor, 50V, C0G	0603	Murata	GRM1885C1H102JA01D
1	CIN2	10nF	Ceramic capacitor, 50V, X7R	0603	Murata	GRM188R71H103KA01D
2	CIN3, CIN4	4.7µF	Ceramic capacitor, 16V, X7R	0805	Murata	GCM21BR71C475KA73L
1	CIN5	22µF	Electrical capacitor; 63V	SMD	Jianghai	VTD-63V22
1	C1A	22µF	Ceramic capacitor, 16V, X5R	0805	Murata	GRM21BR61C226ME44L
1	C1B	100nF	Ceramic capacitor, 16V, X7R	0805	Murata	GRM219R71C104KA01D
3	C2C, C2D, C2E	0.1µF	Ceramic capacitor, 16V, X7R	0603	Murata	GRM188R71C104KA01D
1	C2A	22µF	Ceramic capacitor, 6.3V, X5R	0805	Murata	GRM21BR60J226ME39L
1	C3	2.2nF	Ceramic capacitor, 50V, X7R	0603	Murata	GRM188R71H222KA01D
2	C4, C2B	NS				
1	C5	0Ω	Film resistor, 1%;	0603	Yageo	RC0603FR-070RL
1	R4	10Ω	Film resistor, 1%	0603	Yageo	RC0603FR-0710RL
5	R1, R2, R3, R5, R6	100kΩ	Film resistor, 1%	0603	Yageo	RC0603FR-07100KL
1	L1	1µH	Inductor, 13.25mΩ, 9A	SMD	Coilcraft	XEL4020-102MEB
1	L2	1µH	Inductor, 35mΩ, 3.8A	SMD	Cyntec	VCTA25201B-1R0MS6-99
4	VEMI, GND, VOUT, GND	2mm	Golden pin	DIP	Custom <sup>(1)</sup>	
3	EN, PG, GND	1mm	Golden pin	DIP	Custom <sup>(1)</sup>	
1	U1	MPQ2179A- AEC1	3A, 6V, step-down converter	QFN-8 (1.5mmx 2mm)	MPS	MPQ2179AGQHE-AEC1

**Note:**

1) MPS custom-produces these pins. Contact an MPS FAE for more information.




## EVB TEST RESULTS

Performance curves and waveforms are tested on the evaluation board.  $V_{IN} = 3.3V$ ,  $V_{OUT} = 1.2V$ ,  $T_A = 25^\circ C$ , unless otherwise noted.


### Efficiency vs. Load Current

$V_{OUT} = 1.2V$ ,  $L = 1\mu H$   
(XEL4020-102MEB, DCR = 13.25m $\Omega$ )




### Efficiency vs. Load Current vs. Power Loss

$V_{OUT} = 1.2V$ ,  $L = 1\mu H$   
(XEL4020-102MEB, DCR = 13.25m $\Omega$ )




### Efficiency vs. Load Current vs. Power Loss

$V_{OUT} = 1.2V$ ,  $L = 1\mu H$   
(XEL4020-102MEB, DCR = 13.25m $\Omega$ )




### Case Temperature Rise

$V_{OUT} = 1.2V$




### Load Regulation

$V_{OUT} = 1.2V$



### Line Regulation

$V_{OUT} = 1.2V$




### EVB TEST RESULTS *(continued)*

Performance curves and waveforms are tested on the evaluation board.  $V_{IN} = 3.3V$ ,  $V_{OUT} = 1.2V$ ,  $T_A = 25^{\circ}C$ , unless otherwise noted.


#### Thermal Performance

$I_{OUT} = 1.5A$ , no forced airflow,  $T_{CASE} = 38.1^{\circ}C$



#### Thermal Performance

$I_{OUT} = 3A$ , no forced airflow,  $T_{CASE} = 63.2^{\circ}C$






## EVB TEST RESULTS (continued)

Performance curves and waveforms are tested on the evaluation board.  $V_{IN} = 6V$ ,  $V_{OUT} = 1.2V$ ,  $T_A = 25^\circ C$ , unless otherwise noted.


### CISPR25 Class 5 Peak Conducted Emissions

150kHz to 108MHz




### CISPR25 Class 5 Average Conducted Emissions

150kHz to 108MHz




### CISPR25 Class 5 Peak Radiated Emissions

150kHz to 30MHz




### CISPR25 Class 5 Average Radiated Emissions

150kHz to 30MHz




### CISPR25 Class 5 Peak Radiated Emissions

Horizontal, 30MHz to 1GHz



### CISPR25 Class 5 Average Radiated Emissions

Horizontal, 30MHz to 1GHz






## EVB TEST RESULTS *(continued)*

Performance curves and waveforms are tested on the evaluation board.  $V_{IN} = 6V$ ,  $V_{OUT} = 1.2V$ ,  $T_A = 25^{\circ}C$ , unless otherwise noted.


### CISPR25 Class 5 Peak Radiated Emissions

Vertical, 30MHz to 1GHz



### CISPR25 Class 5 Average Radiated Emissions

Vertical, 30MHz to 1GHz






### EVB TEST RESULTS (continued)

Performance curves and waveforms are tested on the evaluation board.  $V_{IN} = 3.3V$ ,  $V_{OUT} = 1.2V$ ,  $T_A = 25^\circ C$ , unless otherwise noted.


#### Steady State

$I_{OUT} = 0A$




#### Steady State

$I_{OUT} = 3A$




#### Start-Up through VIN

$I_{OUT} = 0A$




#### Start-Up through VIN

$I_{OUT} = 3A$




#### Shutdown through VIN

$I_{OUT} = 0A$



#### Shutdown through VIN

$I_{OUT} = 3A$






### EVB TEST RESULTS (continued)

Performance curves and waveforms are tested on the evaluation board.  $V_{IN} = 3.3V$ ,  $V_{OUT} = 1.2V$ ,  $T_A = 25^{\circ}C$ , unless otherwise noted.

#### Start-Up through EN


$I_{OUT} = 0A$



1ms/div.

#### Start-Up through EN


$I_{OUT} = 3A$



1ms/div.

#### Shutdown through EN


$I_{OUT} = 0A$



20ms/div.

#### Shutdown through EN


$I_{OUT} = 3A$



20µs/div.

#### SCP Entry


$I_{OUT} = 0A$



400µs/div.

#### SCP Entry

$I_{OUT} = 3A$



400µs/div.




### EVB TEST RESULTS (continued)

Performance curves and waveforms are tested on the evaluation board.  $V_{IN} = 3.3V$ ,  $V_{OUT} = 1.2V$ ,  $T_A = 25^\circ C$ , unless otherwise noted.


#### SCP Recovery

$I_{OUT} = 0A$




#### SCP Recovery

$I_{OUT} = 3A$




#### Short-Circuit Protection




#### PG Start-Up through VIN

$I_{OUT} = 3A$




#### PG Shutdown through VIN

$I_{OUT} = 3A$



#### PG Start-Up through EN

$I_{OUT} = 3A$






## EVB TEST RESULTS *(continued)*

Performance curves and waveforms are tested on the evaluation board.  $V_{IN} = 3.3V$ ,  $V_{OUT} = 1.2V$ ,  $T_A = 25^{\circ}C$ , unless otherwise noted.


### PG Shutdown through EN

$I_{OUT} = 3A$



### Load Transient Response

$I_{OUT} = 1.5$  to  $3A$ ,  $1A/\mu s$



PCB LAYOUT (2)




Figure 4: Top Silk and Top Layer




Figure 5: Mid-Layer 1




Figure 6: Mid-Layer 2




Figure 7: Bottom Layer and Bottom Silk

Note:

2) The copper thickness is 2oz.



## REVISION HISTORY

Revision #	Revision Date	Description	Pages Updated
1.0	11/14/2023	Initial Release	-

**Notice:** The information in this document is subject to change without notice. Please contact MPS for current specifications. Users should warrant and guarantee that third-party Intellectual Property rights are not infringed upon when integrating MPS products into any application. MPS will not assume any legal responsibility for any said applications.