



SAMXON BRAND ALUMINUM ELECTROLYTIC CAPACITORS

PRODUCT SPECIFICATION

規格書

CUSTOMER :

(客戶) :

DATE :

(日期) : 2025-01-09

CATEGORY (品名) : ALUMINUM ELECTROLYTIC CAPACITORS

DESCRIPTION (型号) : RT 450V33 μ F(ϕ 16X19.5)

VERSION (版本) : 01

Customer P/N :

SUPPLIER :

SUPPLIER

PREPARED
(拟定)

CHECKED
(审核)

莫璐瑶

付婷婷

CUSTOMER



APPROVAL
(批准)

SIGNATURE
(签名)

MAN YUE ELECTRONICS COMPANY LIMITED	ELECTROLYTIC CAPACITOR SPECIFICATION RT SERIES	SAMXON

Table 1 Product Dimensions and Characteristics

Unit: mm



α	$\alpha=1.7;$
β	$\phi D < 20 : \beta = 0.5; \phi D \geq 20 : \beta = 1.0$

* If it is flat rubber, there is no bulge from the flat rubber surface.

Table 1:

N o.	SAMXON Part No.	WV (Vdc)	Cap. (μ F)	Cap tolerance	Temp. range($^{\circ}$ C)	$\tan \delta$ (120Hz, 20 $^{\circ}$ C)	Leakage Current (μ A,2min)	Max Ripple Current at 105 $^{\circ}$ C 100KHz (mA rms)	Load lifetime (Hrs)	Dimension (mm)			Sleeve
										D $\times$ L	F	ϕd	
1	ERT336M2WK1JRRD0A-R	450	33	-20%~+20%	-25~105	0.20	322	881	5000	16X19.5	7.5	0.8	PET

Version	01		Page	2
---------	----	--	------	---

MAN YUE ELECTRONICS COMPANY LIMITED	ELECTROLYTIC CAPACITOR SPECIFICATION RT SERIES	SAMXON

CONTENTS

	Sheet
1. Application	4
2. Part Number System	4
3. Construction	5
4. Characteristics	5~10
4.1 Rated voltage & Surge voltage	
4.2 Capacitance (Tolerance)	
4.3 Leakage current	
4.4 $\tan \delta$	
4.5 Terminal strength	
4.6 Temperature characteristic	
4.7 Load life test	
4.8 Shelf life test	
4.9 Surge test	
4.10 Vibration	
4.11 Solderability test	
4.12 Resistanc to solder heat	
4.13 Change of temperature	
4.14 Damp heat test	
4.15 Vent test	
4.16 Maximum permissible (ripple current)	
5. List of “Environment-related Substances to be Controlled (‘Controlled Substances’)”	11
Attachment: Application Guidelines	12~15

1. Application


This specification applies to polar Aluminum electrolytic capacitor (foil type) used in electronic equipment. Designed capacitor's quality meets IEC60384.

2. Part Number System

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17
E G S			1 0 5			M	1 H		D 1 1			T C		S A		P
SERIES			CAPACITANCE			TOLERANCE	VOLTAGE		CASE SIZE			TYPE		SAMXON PRODUCT LINE		SLEEVE MATERIAL
Series	Cap (uF)	Code	Tol. (%)	Code	Vol. (W.V.)	Code	Case Size		Feature	Code	SAMXON Product Line		Sleeve Material	Code		
EKF	0.1	104	±5	J	2	0D	Diameter(±)	Code	Radial bulk	RR	For Internal use only (The product lines we have H,A,B,C,D,E,M or 0,1,2,3,4,5,9).		PET	P		
EKS	0.22	224	±10	K	2.5	0E	3	B	Ammo Taping				PVC	If this sleeve material is PVC, there will be blank in seventeenth digit.		
EGS	0.33	334	±15	L	4	0G	3.5	1	2.0mm Pitch							
EKM	0.47	474	±20	M	6.3	0J	4	C	2.5mm Pitch							
EKG	1	105	±30	N	8	0K	5	D	3.5mm Pitch							
EOM	2.2	225	-40 0	W	10	1A	6.3	E	5.0mm Pitch							
EGF	3.3	335	-20 0	A	12.5	1B	8	F	Lead Cut & Form							
ESF	4.7	475	-20 +10	C	16	1C	10	G	CB-Type							
EGT	10	106	-20 +40	X	20	1D	12.5	I	CE-Type							
EGK	22	226	-20 +50	S	25	1E	13	J	HE-Type							
ESK	33	336	-10 0	B	30	1I	14	4	KD-Type							
ESH	47	476	-10 +20	V	32	13	14.5	A	FD-Type							
ESK	100	107	-10 +30	Q	35	1V	16	K	EH-Type							
ERS	220	227	-10 +50	T	40	1G	16.5	7	PCB Terminal							
EGY	330	337	+13 +50	E	42	1M	18	L	Snap-In	SW						
ERF	470	477	-5 +15	F	50	1H	18.5	8		SX						
ERR	2200	228	-5 +20	G	57	1L	20	M	Lug	SZ						
ERT	33000	339	0 +20	R	63	1J	20.5	N		SG						
ERE	47000	479	0 +30	O	71	15	21	O	Screw	O5						
ERD	100000	10T	0 +50	I	75	1T	22	P		O6						
ERH	150000	15T	+5 +15	Z	80	1K	22.5	Q		T5						
EBD	220000	22T	+5 +20	D	85	1R	23	S		T6						
ERA	330000	33T	+10 +50	H	90	19	23.5	T		D5						
ERB	470000	47T			90	2A	24	U		D6						
ERC	1000000	10M			100	20	25	V								
EFA	1500000	15M			120	20	25.5	W								
ENP	2200000	22M			125	2B	26	X								
ENH	3300000	33M			150	2Z	27	Y								
ERW					160	2C	27.5	Z	Len. (mm)		Code					
ERY					160	2C	4.5	45								
ELP					180	2P	5	05								
EAP					180	2P	5.4	54								
EQP					200	2D	7	07								
EDP					200	2D	7.7	77								
ETP					215	22	10.2	T2								
EHP					220	2N	11	11								
EUP					220	2N	11.5	1A								
EKP					230	23	12	12								
EPK					250	2E	12.5	1B								
EFP					275	2T	13	13								
ESP					300	2I	13.5	1C								
EVP					310	2R	20	20								
EGP					315	2F	25	25								
EWR					330	2U	29.5	2J								
EWI					350	2V	30	30								
EWT					375	2Q	31.5	3A								
EWX					385	2Y	35	35								
EWV					400	2G	35.5	3E								
EWL					420	2M	50	50								
EWB					450	2W	80	80								
VS1					500	2H	100	1L								
VT1					550	25	105	1K								
VTD					600	26	110	1M								
VTG					630	2J	120	1N								
VZ2							130	1P								
VTL							140	1Q								
							150	1R								
							155	1E								
							160	1S								
							165	1F								
							170	1T								
							180	1U								
							190	1V								
							200	2L								
							215	2A								
							210	2M								
							220	2N								
							240	2Q								
							250	2R								
							260	2S								
							270	2T								

3. Construction

Single ended type to be produced to fix the terminals to anode and cathode foil, and wind together with paper, and then wound element to be impregnated with electrolyte will be enclosed in an aluminum case. Finally sealed up tightly with end seal rubber, then finished by putting on the vinyl sleeve.



RT 33UF450V 16X19.5 RR 铆接拆解说明

项目	拆解图片	铆接说明
阳极铝箔铆接情况		结合紧密，无松动损伤，无孔洞，无毛刺
阴极铝箔铆接情况		结合紧密，无松动损伤，无孔洞，无毛刺

No	Component	Material
1	Lead line	Tinned CP wire (Pb Free)
2	Terminal	Aluminum wire
3	Sealing Material	Rubber
4	Al-Foil (+)	Formed aluminum foil $\geq 620\text{VF}$
5	Al-Foil (-)	Etched aluminum foil or formed aluminum foil
6	Case	Aluminum case
7	Sleeve	PET
8	Separator	Electrolyte paper

4. Characteristics

Standard atmospheric conditions

Unless otherwise specified, the standard range of atmospheric conditions for making measurements and tests are as follows:

Ambient temperature	: 15°C to 35°C
Relative humidity	: 45% to 85%
Air Pressure	: 86kPa to 106kPa

If there is any doubt about the results, measurement shall be made within the following conditions:

Ambient temperature	: 20°C $\pm$ 2°C
Relative humidity	: 60% to 70%
Air Pressure	: 86kPa to 106kPa

Operating temperature range

The ambient temperature range at which the capacitor can be operated continuously at rated voltage
See table 1 temperature range.

As to the detailed information, please refer to table 2.


MAN YUE ELECTRONICS COMPANY LIMITED	ELECTROLYTIC CAPACITOR SPECIFICATION RT SERIES	SAMXON

Table 2

ITEM		PERFORMANCE																		
4.1	Rated voltage (WV)	<table><tr><td>WV (V.DC)</td><td>160</td><td>200</td><td>220</td><td>250</td><td>350</td><td>400</td><td>420</td><td>450</td></tr><tr><td>SV (V.DC)</td><td>200</td><td>250</td><td>270</td><td>300</td><td>400</td><td>450</td><td>470</td><td>500</td></tr></table>	WV (V.DC)	160	200	220	250	350	400	420	450	SV (V.DC)	200	250	270	300	400	450	470	500
	WV (V.DC)		160	200	220	250	350	400	420	450										
	SV (V.DC)		200	250	270	300	400	450	470	500										
Surge voltage (SV)																				
4.2	Nominal capacitance (Tolerance)	<Condition> Measuring Frequency : 120Hz ± 12Hz Measuring Voltage : Not more than 0.5Vrms Measuring Temperature : 20 ± 2℃ <Criteria> Shall be within the specified capacitance tolerance.																		
4.3	Leakage current	<Condition> Connecting the capacitor with a protective resistor (1k Ω ± 10 Ω) in series for 2 minutes, and then, measure Leakage Current. <Criteria> Refer to Table 1																		
4.4	tan δ	<Condition> See 4.2, Norm Capacitance, for measuring frequency, voltage and temperature. <Criteria> Refer to Table 1																		
4.5	Terminal strength	<Condition> Tensile Strength of Terminals Fixed the capacitor, applied force to the terminal in lead out direction for 10 ± 1 seconds. Bending Strength of Terminals. Fixed the capacitor, applied force to bent the terminal (1~4 mm from the rubber) for 90° within 2~3 seconds, and then bent it for 90° to its original position within 2~3 seconds. <table><tr><td>Diameter of lead wire</td><td>Tensile force N (kgf)</td><td>Bending force N (kgf)</td></tr><tr><td>0.5mm and less</td><td>5 (0.51)</td><td>2.5 (0.25)</td></tr><tr><td>Over 0.5mm to 0.8mm</td><td>10 (1.0)</td><td>5 (0.51)</td></tr></table> <Criteria> No noticeable changes shall be found, no breakage or looseness at the terminal.	Diameter of lead wire	Tensile force N (kgf)	Bending force N (kgf)	0.5mm and less	5 (0.51)	2.5 (0.25)	Over 0.5mm to 0.8mm	10 (1.0)	5 (0.51)									
Diameter of lead wire	Tensile force N (kgf)	Bending force N (kgf)																		
0.5mm and less	5 (0.51)	2.5 (0.25)																		
Over 0.5mm to 0.8mm	10 (1.0)	5 (0.51)																		

4.6	Temperature characteristics	<Condition> <table><tr><th>STEP</th><th>Testing Temperature(°C)</th><th>Time</th></tr><tr><td>1</td><td>20±2</td><td>Time to reach thermal equilibrium</td></tr><tr><td>2</td><td>-40(-25) ±3</td><td>Time to reach thermal equilibrium</td></tr><tr><td>3</td><td>20±2</td><td>Time to reach thermal equilibrium</td></tr><tr><td>4</td><td>105±2</td><td>Time to reach thermal equilibrium</td></tr><tr><td>5</td><td>20±2</td><td>Time to reach thermal equilibrium</td></tr></table> <Criteria> a. In step 4, tan δ shall be within the limit of Item 4.4The leakage current measured shall not more than 8 times of its specified value. b. In step 5, tan δ shall be within the limit of Item 4.4The leakage current shall not more than the specified value. c. In step 2,At-40°C (-25°C), impedance (z) ratio shall not exceed the value of the following table. <table><tr><th>Working Voltage (V)</th><td>160</td><td>200</td><td>250</td><td>350</td><td>400</td><td>450</td></tr><tr><th>Z-25°C/Z+20°C</th><td>3</td><td>3</td><td>3</td><td>5</td><td>5</td><td>6</td></tr></table> For capacitance value > 1000 μ F, Add 0.5 per another 1000 μ F for Z-25/Z+20°C, Add 1.0 per another 1000 μ F for Z-40°C/Z+20°C. Capacitance, tan δ , and impedance shall be measured at 120Hz.	STEP	Testing Temperature(°C)	Time	1	20±2	Time to reach thermal equilibrium	2	-40(-25) ±3	Time to reach thermal equilibrium	3	20±2	Time to reach thermal equilibrium	4	105±2	Time to reach thermal equilibrium	5	20±2	Time to reach thermal equilibrium	Working Voltage (V)	160	200	250	350	400	450	Z-25°C/Z+20°C	3	3	3	5	5	6
STEP	Testing Temperature(°C)	Time																																
1	20±2	Time to reach thermal equilibrium																																
2	-40(-25) ±3	Time to reach thermal equilibrium																																
3	20±2	Time to reach thermal equilibrium																																
4	105±2	Time to reach thermal equilibrium																																
5	20±2	Time to reach thermal equilibrium																																
Working Voltage (V)	160	200	250	350	400	450																												
Z-25°C/Z+20°C	3	3	3	5	5	6																												
4.7	Load life test	<Condition> According to IEC60384-4No.4.13 methods, The capacitor is stored at a temperature of 105 °C ±2 with DC bias voltage plus the rated ripple current for Table 1 load life time hours. (The sum of DC and ripple peak voltage shall not exceed the rated working voltage) Then the product should be tested after 16 hours recovering time at atmospheric conditions. The result should meet the following table: <Criteria> The characteristic shall meet the following requirements. <table><tr><td>Leakage current</td><td>Value in 4.3 shall be satisfied</td></tr><tr><td>Capacitance Change</td><td>Within ±20% of initial value.</td></tr><tr><td>tan δ</td><td>Not more than 200% of the specified value.</td></tr><tr><td>Appearance</td><td>There shall be no leakage of electrolyte.</td></tr></table>	Leakage current	Value in 4.3 shall be satisfied	Capacitance Change	Within ±20% of initial value.	tan δ	Not more than 200% of the specified value.	Appearance	There shall be no leakage of electrolyte.																								
Leakage current	Value in 4.3 shall be satisfied																																	
Capacitance Change	Within ±20% of initial value.																																	
tan δ	Not more than 200% of the specified value.																																	
Appearance	There shall be no leakage of electrolyte.																																	
4.8	Shelf life test	<Condition> The capacitors are then stored with no voltage applied at a temperature of 105±2°C for 1000+48/0 hours. Following this period the capacitors shall be removed from the test chamber and be allowed to stabilized at room temperature for 4~8 hours. Next they shall be connected to a series limiting resistor(1k±100 Ω) with D.C. rated voltage applied for 30min. After which the capacitors shall be discharged, and then, tested the characteristics.																																

MAN YUE ELECTRONICS COMPANY LIMITED	ELECTROLYTIC CAPACITOR SPECIFICATION RT SERIES	SAMXON

4.8	Shelf life test	<Criteria> The characteristic shall meet the following requirements. <table><tr><td>Leakage current</td><td>Value in 4.3 shall be satisfied</td></tr><tr><td>Capacitance Change</td><td>Within $\pm 20\%$ of initial value.</td></tr><tr><td>$\tan \delta$</td><td>Not more than 200%of the specified value.</td></tr><tr><td>Appearance</td><td>There shall be no leakage of electrolyte.</td></tr></table> Remark: If the capacitors are stored more than 1 year, the leakage current may increase. Please apply voltage through about 1 kΩ resistor, if necessary.	Leakage current	Value in 4.3 shall be satisfied	Capacitance Change	Within $\pm 20\%$ of initial value.	$\tan \delta$	Not more than 200%of the specified value.	Appearance	There shall be no leakage of electrolyte.
Leakage current	Value in 4.3 shall be satisfied									
Capacitance Change	Within $\pm 20\%$ of initial value.									
$\tan \delta$	Not more than 200%of the specified value.									
Appearance	There shall be no leakage of electrolyte.									
4.9	Surge test	<Condition> Applied a surge voltage to the capacitor connected with a $(100 \pm 50)/C_R$ (kΩ) resistor. The capacitor shall be submitted to 1000 cycles, each consisting of charge of 30 ± 5s, followed discharge of 5 min 30s. The test temperature shall be 15~35°C. C_R :Nominal Capacitance (μ F) <Criteria> <table><tr><td>Leakage current</td><td>Not more than the specified value.</td></tr><tr><td>Capacitance Change</td><td>Within $\pm 15\%$ of initial value.</td></tr><tr><td>$\tan \delta$</td><td>Not more than the specified value.</td></tr><tr><td>Appearance</td><td>There shall be no leakage of electrolyte.</td></tr></table> Attention: This test simulates over voltage at abnormal situation only. It is not applicable to such over voltage as often applied.	Leakage current	Not more than the specified value.	Capacitance Change	Within $\pm 15\%$ of initial value.	$\tan \delta$	Not more than the specified value.	Appearance	There shall be no leakage of electrolyte.
Leakage current	Not more than the specified value.									
Capacitance Change	Within $\pm 15\%$ of initial value.									
$\tan \delta$	Not more than the specified value.									
Appearance	There shall be no leakage of electrolyte.									
4.10	Vibration test	<Condition> The following conditions shall be applied for 2 hours in each 3 mutually perpendicular directions. Vibration frequency range : 10Hz ~ 55Hz Peak to peak amplitude : 1.5mm Sweep rate : 10Hz ~ 55Hz ~ 10Hz in about 1 minute Mounting method: The capacitor with diameter greater than 12.5mm or longer than 25mm must be fixed in place with a bracket.  <Criteria> After the test, the following items shall be tested: <table><tr><td>Inner construction</td><td>No intermittent contacts, open or short circuiting. No damage of tab terminals or electrodes.</td></tr><tr><td>Appearance</td><td>No mechanical damage in terminal. No leakage of electrolyte or swelling of the case. The markings shall be legible.</td></tr></table>	Inner construction	No intermittent contacts, open or short circuiting. No damage of tab terminals or electrodes.	Appearance	No mechanical damage in terminal. No leakage of electrolyte or swelling of the case. The markings shall be legible.				
Inner construction	No intermittent contacts, open or short circuiting. No damage of tab terminals or electrodes.									
Appearance	No mechanical damage in terminal. No leakage of electrolyte or swelling of the case. The markings shall be legible.									


MAN YUE ELECTRONICS COMPANY LIMITED	ELECTROLYTIC CAPACITOR SPECIFICATION RT SERIES	SAMXON

4.11	Solderability test	<Condition> The capacitor shall be tested under the following conditions: Sn-Cu solder Soldering temperature : 250±3°C Dipping depth : 2mm Dipping speed : 25±2.5mm/s Dipping time : 3±0.5s <Criteria> <table><tr><td>Coating quality</td><td>A minimum of 95% of the surface being immersed</td></tr></table>	Coating quality	A minimum of 95% of the surface being immersed														
Coating quality	A minimum of 95% of the surface being immersed																	
4.12	Resistance to solder heat test	<Condition> Terminals of the capacitor shall be immersed into solder bath at 260±5°C for 10±1 seconds or 400±10°C for 3⁺¹₋₀ seconds to 1.5~2.0mm from the body of capacitor . Then the capacitor shall be left under the normal temperature and normal humidity for 1~2 hours before measurement. <Criteria> <table><tr><td>Leakage current</td><td>Not more than the specified value.</td></tr><tr><td>Capacitance Change</td><td>Within ±10% of initial value.</td></tr><tr><td>tan δ</td><td>Not ore than the specified value.</td></tr><tr><td>Appearance</td><td>There shall be no leakage of electrolyte.</td></tr></table>	Leakage current	Not more than the specified value.	Capacitance Change	Within ±10% of initial value.	tan δ	Not ore than the specified value.	Appearance	There shall be no leakage of electrolyte.								
Leakage current	Not more than the specified value.																	
Capacitance Change	Within ±10% of initial value.																	
tan δ	Not ore than the specified value.																	
Appearance	There shall be no leakage of electrolyte.																	
4.13	Change of temperature test	<Condition> Temperature Cycle:According to IEC60384-4No.4.7methods, capacitor shall be placed in an oven, the condition according as below: <table><tr><th>Temperature</th><th>Time</th></tr><tr><td>(1)+20℃</td><td>≤ 3 Minutes</td></tr><tr><td>(2)Rated low temperature (-40℃) (-25℃)</td><td>30±2 Minutes</td></tr><tr><td>(3)Rated high temperature (+105℃)</td><td>30±2 Minut s</td></tr><tr><td colspan="2">(1) to (3)=1 cycle, total 5 cycle</td></tr></table> <Criteria> The characteristic shall meet the following requirement <table><tr><td>Leakage current</td><td>Not more than the specified value.</td></tr><tr><td>tan δ</td><td>Not more than the specified value.</td></tr><tr><td>Appearance</td><td>There shall be no leakage of electrolyte.</td></tr></table>	Temperature	Time	(1)+20℃	≤ 3 Minutes	(2)Rated low temperature (-40℃) (-25℃)	30±2 Minutes	(3)Rated high temperature (+105℃)	30±2 Minut s	(1) to (3)=1 cycle, total 5 cycle		Leakage current	Not more than the specified value.	tan δ	Not more than the specified value.	Appearance	There shall be no leakage of electrolyte.
Temperature	Time																	
(1)+20℃	≤ 3 Minutes																	
(2)Rated low temperature (-40℃) (-25℃)	30±2 Minutes																	
(3)Rated high temperature (+105℃)	30±2 Minut s																	
(1) to (3)=1 cycle, total 5 cycle																		
Leakage current	Not more than the specified value.																	
tan δ	Not more than the specified value.																	
Appearance	There shall be no leakage of electrolyte.																	
4.14	Damp heat test	<Condition> Humidity Test: According to IEC60384-4No.4.12methods, capacitor shall be exposed for 500±8 hours in an atmosphere of 90~95%R H .at 40±2℃, the characteristic change shall meet the following requirement. <Criteria> <table><tr><td>Le kage current</td><td>Not more than the specified value.</td></tr><tr><td>Capacitance Change</td><td>Within ±20% of initial value.</td></tr><tr><td>tan δ</td><td>Not more than 120% of the specified value.</td></tr><tr><td>Appearance</td><td>There shall be no leakage of electrolyte.</td></tr></table>	Le kage current	Not more than the specified value.	Capacitance Change	Within ±20% of initial value.	tan δ	Not more than 120% of the specified value.	Appearance	There shall be no leakage of electrolyte.								
Le kage current	Not more than the specified value.																	
Capacitance Change	Within ±20% of initial value.																	
tan δ	Not more than 120% of the specified value.																	
Appearance	There shall be no leakage of electrolyte.																	

MAN YUE ELECTRONICS COMPANY LIMITED	ELECTROLYTIC CAPACITOR SPECIFICATION RT SERIES	SAMXON

4.15	Vent test	<Condition> The following test only apply to those products with vent products at diameter ≥Ø6.3 with vent. D.C. test The capacitor is connected with its polarity reversed to a DC power source. Then a current selected from below table is applied. <Table 3> <table><tr><th>Diameter (mm)</th><th>DC Current (A)</th></tr><tr><td>22.4 or less</td><td>1</td></tr><tr><td>Over 22.4</td><td>10</td></tr></table> <Criteria> The vent shall operate with no dangerous conditions such as flames or dispersion of pieces of the capacitor and/or case.	Diameter (mm)	DC Current (A)	22.4 or less	1	Over 22.4	10																																											
Diameter (mm)	DC Current (A)																																																		
22.4 or less	1																																																		
Over 22.4	10																																																		
4.16	Maximum permissible (ripple current)	<Condition> The maximum permissible ripple current is the maximum A.C current at 120Hz and can be applied at maximum operating temperature Table-1 The combined value of D.C voltage and the peak A.C voltage shall not exceed the rated voltage and shall not reverse voltage. Frequency Multipliers: <table><tr><th>Coefficient \ Freq. (Hz)</th><th>120</th><th>1k</th><th>10k</th><th>100k</th></tr><tr><th>Cap. (µ F)</th><td></td><td></td><td></td><td></td></tr><tr><td>1~5.6</td><td>0.20</td><td>0.40</td><td>0.80</td><td>1.00</td></tr><tr><td>6.8~180</td><td>0.40</td><td>0.75</td><td>0.90</td><td>1.00</td></tr><tr><td>220~</td><td>0.50</td><td>0.85</td><td>0.94</td><td>1.00</td></tr></table> Temperature Coefficient: <table><tr><th>Capacitor ambient temperature</th><th>≤ 65°C</th><th>75°C</th><th>85°C</th><th>95°C</th><th>105°C</th></tr><tr><td>Temperature coefficient</td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>Actural rms ripple</td><td>1.73</td><td>1.73</td><td>1.73</td><td>1.41</td><td>1.00</td></tr><tr><td>Rated rms max.ripple</td><td></td><td></td><td></td><td></td><td></td></tr></table>	Coefficient \ Freq. (Hz)	120	1k	10k	100k	Cap. (µ F)					1~5.6	0.20	0.40	0.80	1.00	6.8~180	0.40	0.75	0.90	1.00	220~	0.50	0.85	0.94	1.00	Capacitor ambient temperature	≤ 65°C	75°C	85°C	95°C	105°C	Temperature coefficient						Actural rms ripple	1.73	1.73	1.73	1.41	1.00	Rated rms max.ripple					
Coefficient \ Freq. (Hz)	120	1k	10k	100k																																															
Cap. (µ F)																																																			
1~5.6	0.20	0.40	0.80	1.00																																															
6.8~180	0.40	0.75	0.90	1.00																																															
220~	0.50	0.85	0.94	1.00																																															
Capacitor ambient temperature	≤ 65°C	75°C	85°C	95°C	105°C																																														
Temperature coefficient																																																			
Actural rms ripple	1.73	1.73	1.73	1.41	1.00																																														
Rated rms max.ripple																																																			

Packing Information



PACKING QUANTITY (TAPING TYPE)

Φ D x L (mm)	L (mm)	W (mm)	H (mm)	Inner Box Quantity	Outer Box Quantity
3 x 5	330	229	51	3,000	30,000
4 x 5 ~ 7	330	229	51	2,500	25,000
5 x 5 ~ 11	330	229	51	2,000	20,000
6.3 x 5 ~ 12	330	229	51	1,500	15,000
8 x 5 ~ 12	330	229	51	1,000	10,000
8 x 14 ~ 20	330	229	64	1,000	8,000
10 x 12.5	330	191	51	500	5,000
10 x 16	330	191	56	500	5,000
10 x 20 ~ 25	323	191	64	500	4,000
10 x 30	330	191	69	500	4,000
12.5 x 20	325	267	58	500	2,000
12.5 x 25	325	270	63	500	2,000
12.5 x 35	325	270	74	500	2,000
16 x 25	315	221	63	250	1,000
16 x 30 ~ 35	315	221	76	250	1,500
18 x 20 ~ 25	343	275	63	250	1,000
18 x 30 ~ 35	343	275	73	250	500
18 x 40	343	275	73	250	500

PACKING QUANTITY (BULK TYPE)

Long Lead Wire Product			
Φ D x L (mm)	Plastic Bag Quantity	Inner Box Quantity	Outer Box Quantity
3 x 5	1,000	24,000	96,000
4 x 5	1,000	16,000	64,000
4 x 7	1,000	14,000	56,000
5 x 5	1,000	12,000	48,000
5 x 7	1,000	10,000	40,000
5 x 11	1,000	8,000	32,000
6.3 x 5 ~ 7	1,000	8,000	32,000
6.3 x 11	1,000	6,000	24,000
8 x 5 ~ 7	1,000	6,000	24,000
8 x 9	500	4,000	16,000
8 x 10 ~ 16	500	3,000	12,000
8 x 20	200	1,600	6,400
8 x 25	200	1,200	4,800
10 x 12.5	400	2,400	9,600
10 x 15 ~ 20	200	1,200	7,200
10 x 25 ~ 30	200	1,200	4,800
12.5 x 20	150	1,200	4,800
12.5 x 25	150	900	3,600
12.5 x 30 ~ 35	100	600	2,400
12.5 x 40	—	300	1,800
16 x 20	—	200	2,000
16 x 25 ~ 30	—	200	1,600
16 x 35 ~ 40	—	200	1,200
18 x 15 ~ 20	—	150	1,500
18 x 25 ~ 30	—	150	1,200
18 x 35 ~ 50	—	150	900

MAN YUE ELECTRONICS COMPANY LIMITED	ELECTROLYTIC CAPACITOR SPECIFICATION RT SERIES	SAMXON

5. It refers to the latest document of “Environment-related Substances standard”(WI-HSPM-QA-072).

Substances	
Heavy metals	Cadmium and cadmium compounds
	Lead and lead compounds
	Mercury and mercury compounds
	Hexavalent chromium compounds
Chlorinated organic compounds	Polychlorinated biphenyls (PCB)
	Polychlorinated naphthalenes (PCN)
	Polychlorinated terphenyls (PCT)
	Short-chain chlorinated paraffins (SCCP)
	Other chlorinated organic compounds
Brominated organic compounds	Polybrominated biphenyls (PBB)
	Polybrominated diphenylethers (PBDE) (including decabromodiphenyl ether [DecaBDE])
	Other brominated organic compounds
Tributyltin compounds (TBT)	
Triphenyltin compounds (TPT)	
Asbestos	
Specific azo compounds	
Formaldehyde	
Beryllium oxide	
Beryllium copper	
Specific phthalates (DEHP, DBP, BBP, DINP, DIDP, DNOP, DNHP)	
Hydrofluorocarbon (HFC), Perfluorocarbon (PFC)	
Perfluorooctane sulfonates (PFOS)	
Specific Benzotriazole	

MAN YUE ELECTRONICS COMPANY LIMITED	ELECTROLYTIC CAPACITOR SPECIFICATION RT SERIES	SAMXON

Attachment: Application Guidelines

1.Circuit Design

1.1 Operating Temperature and Frequency

Electrolytic capacitor electrical parameters are normally specified at 20°C temperature and 120Hz frequency. These parameters vary with changes in temperature and frequency. Circuit designers should take these changes into consideration.

- (1) Effects of operating temperature on electrical parameters
 - a) At higher temperatures, leakage current and capacitance increase while equivalent series resistance (ESR) decreases.
 - b) At lower temperatures, leakage current and capacitance decrease while equivalent series resistance (ESR) increases.
- (2) Effects of frequency on electrical parameters
 - a) At higher frequencies capacitance and impedance decrease while $\tan\delta$ increases.
 - b) At lower frequencies, ripple current generated heat will rise due to an increase in equivalent series resistance (ESR).

1.2 Operating Temperature and Life Expectancy

See the file: Life calculation of aluminum electrolytic capacitor

1.3 Common Application Conditions to Avoid

The following misapplication load conditions will cause rapid deterioration to capacitor electrical parameters. In addition, rapid heating and gas generation within the capacitor can occur causing the pressure relief vent to operate and resultant leakage of electrolyte. Under Leaking electrolyte is combustible and electrically conductive.

- (1) Reverse Voltage
DC capacitors have polarity. Verify correct polarity before insertion. For circuits with changing or uncertain polarity, use DC bipolar capacitors. DC bipolar capacitors are not suitable for use in AC circuits.
- (2) Charge / Discharge Applications
Standard capacitors are not suitable for use in repeating charge / discharge applications. For charge / discharge applications consult us and advise actual conditions.
- (3) Over voltage
Do not apply voltages exceeding the maximum specified rated voltage. Voltages up to the surge voltage rating are acceptable for short periods of time. Ensure that the sum of the DC voltage and the superimposed AC ripple voltage does not exceed the rated voltage.
- (4) Ripple Current
Do not apply ripple currents exceeding the maximum specified value. For high ripple current applications, use a capacitor designed for high ripple currents or contact us with your requirements. Ensure that allowable ripple currents superimposed on low DC bias voltages do not cause reverse voltage conditions.
- (5) Pulse Current
The pulse current cannot exceed 10 times the rated ripple current at 120Hz.

1.4 Using Two or More Capacitors in Series or Parallel

- (1) Capacitors Connected in Parallel
The circuit resistance can closely approximate the series resistance of the capacitor causing an imbalance of ripple current loads within the capacitors. Careful design of wiring methods can minimize the possibility of excessive ripple currents applied to a capacitor.
- (2) Capacitors Connected in Series
Normal DC leakage current differences among capacitors can cause voltage imbalances. The use of voltage divider shunt resistors with consideration to leakage current can prevent capacitor voltage imbalances.

1.5 Capacitor Mounting Considerations

- (1) Double Sided Circuit Boards
Avoid wiring pattern runs, which pass between the mounted capacitor and the circuit board.
When dipping into a solder bath, excess solder may collect under the capacitor by capillary action and short circuit the anode and cathode terminals.
- (2) Circuit Board Hole Positioning
The vinyl sleeve of the capacitor can be damaged if solder passes through a lead hole for subsequently processed parts. Special care when locating hole positions in proximity to capacitors is recommended.
- (3) Circuit Board Hole Spacing
The circuit board holes spacing should match the capacitor lead wire spacing within the specified tolerances. Incorrect spacing can cause excessive lead wire stress during the insertion process. This may result in premature capacitor failure due to short or open circuit, increased leakage current, or electrolyte leakage.
- (4) Clearance for Case Mounted Pressure Relief vents
Capacitors with case mounted pressure relief vents require sufficient clearance to allow for proper vent operation. The minimum clearances are dependent on capacitor diameters as proper vent operation. The minimum clearances are dependent on capacitor diameters as follows.
 $\phi 6.3 \sim \phi 16\text{mm}$: 2mm minimum, $\phi 18 \sim \phi 35\text{mm}$: 3mm minimum, $\phi 40\text{mm}$ or greater: 5mm minimum.
- (5) Clearance for Seal Mounted Pressure Relief Vents
A hole in the circuit board directly under the seal vent location is required to allow proper release of pressure.

Version	01		Page	14
---------	----	--	------	----

MAN YUE ELECTRONICS COMPANY LIMITED	ELECTROLYTIC CAPACITOR SPECIFICATION RT SERIES	SAMXON

(6) Wiring Near the Pressure Relief Vent

Avoid locating high voltage or high current wiring or circuit board paths above the pressure relief vent. Flammable, high temperature gas exceeding 100°C may be released which could dissolve the wire insulation and ignite.

(7) Circuit Board patterns Under the Capacitor

Avoid circuit board runs under the capacitor as electrolyte leakage could cause an electrical short.

(8) Screw Terminal Capacitor Mounting

Do not orient the capacitor with the screw terminal side of the capacitor facing downwards.

Tighten the terminal and mounting bracket screws within the torque range specified in the specification.

1.6 Electrical Isolation of the Capacitor

Completely isolate the capacitor as follows.

- (1) Between the cathode and the case (except for axially leaded B types) and between the anode terminal and other circuit paths
- (2) Between the extra mounting terminals (on T types) and the anode terminal, cathode terminal, and other circuit paths.

1.7 The Product endurance should take the sample as the standard.

1.8 If conduct the load or shelf life test, must be collect date code within 6 months products of sampling.

1.9 Capacitor Sleeve

The vinyl sleeve or laminate coating is intended for marking and identification purposes and is not meant to electrically insulate the capacitor.

The sleeve may split or crack if immersed into solvents such as toluene or xylene, and then exposed to high temperatures.

CAUTION!

Always consider safety when designing equipment and circuits. Plan for worst case failure modes such as short circuits and open circuits which could occur during use.

- (1) Provide protection circuits and protection devices to allow safe failure modes.
- (2) Design redundant or secondary circuits where possible to assure continued operation in case of main circuit failure.

2.Capacitor Handling Techniques

2.1 Considerations Before Using

- (1) Capacitors have a finite life. Do not reuse or recycle capacitors from used equipment.
- (2) Transient recovery voltage may be generated in the capacitor due to dielectric absorption. If required, this voltage can be discharged with a resistor with a value of about 1kΩ.
- (3) Capacitors stored for long periods of time may exhibit an increase in leakage current. This can be corrected by gradually applying rated voltage in series with a resistor of approximately 1kΩ.
- (4) If capacitors are dropped, they can be damaged mechanically or electrically. Avoid using dropped capacitors.
- (5) Dented or crushed capacitors should not be used. The seal integrity can be compromised and loss of electrolyte / shortened life can result.

2.2 Capacitor Insertion

- (1) Verify the correct capacitance and rated voltage of the capacitor.
- (2) Verify the correct polarity of the capacitor before inserting.
- (3) Verify the correct hole spacing before insertion (land pattern size on chip type) to avoid stress on the terminals.
- (4) Ensure that the auto insertion equipment lead clinching operation does not stress the capacitor leads where they enter the seal of the capacitor.

For chip type capacitors, excessive mounting pressure can cause high leakage current, short circuit, or disconnection.

2.3 Manual Soldering

- (1) Observe temperature and time soldering specifications or do not exceed temperatures of 400 °C for 3 seconds or less.
- (2) If lead wires must be formed to meet terminal board hole spacing, avoid stress on the lead wire where it enters the capacitor seal.
- (3) If a soldered capacitor must be removed and reinserted, avoid excessive stress to the capacitor leads.
- (4) Avoid touching the tip of the soldering iron to the capacitor, to prevent melting of the vinyl sleeve.

2.4 Flow Soldering

- (1) Do not immerse the capacitor body into the solder bath as excessive internal pressure could result.
- (2) Observe proper soldering conditions (temperature, time, etc.) Do not exceed the specified limits.
- (3) Do not allow other parts or components to touch the capacitor during soldering.

2.5 Other Soldering Considerations

Rapid temperature rises during the preheat operation and resin bonding operation can cause cracking of the capacitor vinyl sleeve. For heat curing, do not exceed 150°C for a maximum time of 2 minutes.

Version	01		Page	15
---------	----	--	------	----

MAN YUE ELECTRONICS COMPANY LIMITED	ELECTROLYTIC CAPACITOR SPECIFICATION RT SERIES	SAMXON

2.6 Capacitor Handling after Solder

- (1). Avoid movement of the capacitor after soldering to prevent excessive stress on the lead wires where they enter the seal.
- (2). Do not use capacitor as a handle when moving the circuit board assembly.
- (3). Avoid striking the capacitor after assembly to prevent failure due to excessive shock.

2.7 Circuit Board Cleaning

- (1) Circuit boards can be immersed or ultrasonically cleaned using suitable cleaning solvents for up to 5 minutes and up to 60°C maximum temperatures. The boards should be thoroughly rinsed and dried. The use of ozone depleting cleaning agents is not recommended in the interest of protecting the environment.
- (2) Avoid using the following solvent groups unless specifically allowed for in the specification;
 - Halogenated cleaning solvents: except for solvent resistant capacitor types, halogenated solvents can permeate the seal and cause internal capacitor corrosion and failure. For solvent resistant capacitors, carefully follow the temperature and time requirements of the specification. 1-1-1 trichloroethane should never be used on any aluminum electrolytic capacitor.
 - Alkali solvents : could attack and dissolve the aluminum case.
 - Petroleum based solvents: deterioration of the rubber seal could result.
 - Xylene : deterioration of the rubber seal could result.
 - Acetone : removal of the ink markings on the vinyl sleeve could result.
- (3) A thorough drying after cleaning is required to remove residual cleaning solvents which may be trapped between the capacitor and the circuit board. Avoid drying temperatures, which exceed the maximum rated temperature of the capacitor.
- (4) Monitor the contamination levels of the cleaning solvents during use by electrical conductivity, pH, specific gravity, or water content. Chlorine levels can rise with contamination and adversely affect the performance of the capacitor. Please consult us for additional information about acceptable cleaning solvents or cleaning methods.

2.8 Mounting Adhesives and Coating Agents

When using mounting adhesives or coating agents to control humidity, avoid using materials containing halogenated solvents. Also, avoid the use of chloroprene based polymers. After applying adhesives or coatings, dry thoroughly to prevent residual solvents from being trapped between the capacitor and the circuit board.

3. Precautions for using capacitors

3.1 Environmental Conditions

Capacitors should not be stored or used in the following environments.

- (1) Temperature exposure above the maximum rated or below the minimum rated temperature of the capacitor.
- (2) Direct contact with water, salt water, or oil.
- (3) High humidity conditions where water could condense on the capacitor.
- (4) Exposure to toxic gases such as hydrogen sulfide, sulfuric acid, nitric acid chlorine, or ammonia.
- (5) Exposure to ozone, radiation, or ultraviolet rays.
- (6) Vibration and shock conditions exceeding specified requirements.

3.2 Electrical Precautions

- (1) Avoid touching the terminals of the capacitor as possible electric shock could result. The exposed aluminum case is not insulated and could also cause electric shock if touched.
- (2) Avoid short circuit the area between the capacitor terminals with conductive materials including liquids such as acids or alkaline solutions.

4. Emergency Procedures

- (1) If the pressure relief vent of the capacitor operates, immediately turn off the equipment and disconnect from the power source. This will minimize additional damage caused by the vaporizing electrolyte.
- (2) Avoid contact with the escaping electrolyte gas which can exceed 100°C temperatures.
 - If electrolyte or gas enters the eye, immediately flush the eyes with large amounts of water.
 - If electrolyte or gas is ingested by mouth, gargle with water.
 - If electrolyte contacts the skin, wash with soap and water.

5. Long Term Storage

Leakage current of a capacitor increases with long storage times. The aluminum oxide film deteriorates as a function of temperature and time. If used without reconditioning, an abnormally high current will be required to restore the oxide film. This current surge could cause the circuit or the capacitor to fail. After one year, a capacitor should be reconditioned by applying rated voltage in series with a 1000Ω, current limiting resistor for a time period of 30 minutes. If the expired date of products date code is over eighteen months, the products should be return to confirmation.

5.1 Environmental Conditions

Version	01		Page	16
---------	----	--	------	----

MAN YUE ELECTRONICS COMPANY LIMITED	ELECTROLYTIC CAPACITOR SPECIFICATION RT SERIES	SAMXON

- The capacitor shall be not use in the following condition:
- (1) Temperature exposure above the maximum rated or below the minimum rated temperature of the capacitor.
 - (2) Direct contact with water, salt water, or oil.
 - (3) High humidity conditions where water could condense on the capacitor.
 - (4) Exposure to toxic gases such as hydrogen sulfide, sulfuric acid, nitric acid, chlorine, or ammonia.
 - (5) Exposure to ozone, radiation, or ultraviolet rays.
 - (6) Vibration and shock conditions exceeding specified requirements.

6. Capacitor Disposal

When disposing of capacitors, use one of the following methods.
 Incinerate after crushing the capacitor or puncturing the can wall (to prevent explosion due to internal pressure rise).
 Capacitors should be incinerated at high temperatures to prevent the release of toxic gases such as chlorine from the polyvinyl chloride sleeve, etc.
 Dispose of as solid waste.
 NOTE: Local laws may have specific disposal requirements, which must be followed.

BOS表

[illegible]




Load Life Test

Items Description:RT-450V33uF
Test:High Temp Loading
Testing Period:2024-04-23~2024-11-19
Testing Instrument:TH2816; DU-2310
Requirement Before Testing:
Requirement After Testing:

Dimension:Φ16x19.5
Testing Condition:The capacitor is stored at a temperature of 105±2℃ with DC bias voltage plus the rated ripple current for 5000 +48/0 hours.
(the sum of DC and ripple peak voltage not exceed the rated working voltage)
Measuring environment: 0h: 24℃,1000h: 24℃,2000h: 24℃,3000h: 24℃,4000h: 23℃,5000h: 25℃.
1. Co=26.4~39.6uF
1.ΔC/C0≤20%

Testing Voltage:450V
Testing Frequency:120Hz
3. LC/ 2min≤322uA
3. LC/ 2min≤322uA
4.Appearance:No leakage of electrolyte.

Time Data No.	0h			1000h				2000h				3000h				4000h				5000h			
	C0(uF)	DF(%)	LC/2min (μA)	C1(uF)	ΔC/C0 (%)	DF(%)	LC/2min (μA)	C2(uF)	ΔC/C0 (%)	DF(%)	LC/2min (μA)	C3(uF)	ΔC/C0 (%)	DF(%)	LC/2min (μA)	C4(uF)	ΔC/C0 (%)	DF(%)	LC/2min (μA)	C5(uF)	ΔC/C0 (%)	DF(%)	LC/2min (μA)
1	30.24	4.68	17.0	29.74	-1.64	5.02	15.7	28.92	-4.35	5.95	11.1	28.31	-6.37	6.42	9.3	27.94	-7.60	7.15	5.3	27.14	-10.27	7.84	2.7
2	30.23	4.60	15.9	29.65	-1.90	5.01	15.2	29.14	-3.62	5.69	10.5	28.48	-5.78	6.35	8.6	27.79	-8.06	7.07	4.7	27.25	-9.85	7.80	1.9
3	30.39	4.64	16.5	29.57	-2.71	4.96	15.5	29.09	-4.28	6.03	10.9	28.34	-6.74	6.69	9.1	27.96	-8.00	7.07	4.9	27.32	-10.09	8.02	4.2
4	30.18	4.30	16.5	29.54	-2.13	5.23	15.5	29.10	-3.59	5.73	11.3	28.41	-5.88	6.40	8.2	27.94	-7.42	7.34	4.5	27.24	-9.73	8.11	3.2
5	30.26	4.31	16.2	29.73	-1.74	5.33	13.6	29.04	-4.03	6.03	11.1	28.47	-5.91	6.62	7.2	27.86	-7.94	7.16	4.5	27.16	-10.24	7.79	2.6
6	30.32	4.34	18.4	29.63	-2.29	5.39	14.3	29.13	-3.94	5.78	10.4	28.40	-6.34	6.44	8.4	27.94	-7.85	7.32	6.3	27.32	-9.91	7.89	2.4
7	30.17	4.50	16.1	29.51	-2.19	5.00	13.5	28.94	-4.06	5.97	11.7	28.46	-5.66	6.61	7.3	27.80	-7.85	7.33	4.9	27.30	-9.52	7.87	3.1
8	30.19	4.30	18.3	29.59	-2.00	5.26	15.5	29.04	-3.81	5.85	10.2	28.56	-5.41	6.35	8.6	27.81	-7.88	7.03	4.9	27.27	-9.67	7.79	1.7
9	30.22	4.70	17.7	29.65	-1.87	4.95	13.4	29.17	-3.46	5.78	10.2	28.34	-6.22	6.32	8.2	27.82	-7.94	7.41	4.6	27.18	-10.06	7.77	3.1
10	30.22	4.67	17.8	29.76	-1.51	5.02	14.2	29.09	-3.75	5.99	11.9	28.55	-5.53	6.34	8.3	27.75	-8.18	7.40	4.7	27.16	-10.12	8.00	2.9
AVR	30.24	4.50	17.0	29.64	-2.00	5.12	14.6	29.07	-3.89	5.88	10.9	28.43	-5.98	6.45	8.3	27.86	-7.87	7.23	4.9	27.23	-9.95	7.89	2.8
Max	30.39	4.70	18.4	29.76	-1.51	5.39	15.7	29.17	-3.46	6.03	11.9	28.56	-5.41	6.69	9.3	27.96	-7.42	7.41	6.3	27.32	-9.52	8.11	4.2
Min	30.17	4.30	15.9	29.51	-2.71	4.95	13.4	28.92	-4.35	5.69	10.2	28.31	-6.74	6.32	7.2	27.75	-8.18	7.03	4.5	27.14	-10.27	7.77	1.7
Remark																							





Shelf Life Test

Items Description: RT-450V33uF

Dimension: $\Phi 16 \times 19.5$

Testing Voltage: 450V

Testing Frequency: 120Hz

Test: Storage at High Temp.

Testing Condition: The capacitor is stored at a temp. of $105^{\circ}\text{C} \pm 2^{\circ}\text{C}$ unloaded for 1000+48/0hr.

Testing Instrument: TH2816; DU-2310

Testing Period: 2024-04-23~2024-06-04

Measuring environment: 0h: 24°C , 500h: 25°C , 1000h: 24°C .

Requirement Before Testing:

1. $C_0=26.4\sim 39.6\mu\text{F}$

2. $\text{DF} \leq 20\%$

3. $\text{LC}/2\text{min} \leq 322\mu\text{A}$

Requirement After Testing:




1. $|\Delta C/C_0| \leq 20\%$

2. $\text{DF} \leq 40\%$

3. $\text{LC}/2\text{min} \leq 322\mu\text{A}$

4. Appearance: No leakage of electrolyte.

Time	0h			500h				1000h			
Data No.	CAP(μF)	DF(%)	LC/2min(μA)	C1(μF)	$\Delta C/C_0(\%)$	DF(%)	LC/2min(μA)	C2(μF)	$\Delta C/C_0(\%)$	DF(%)	LC/2min(μA)
1	30.28	4.63	17.8	29.84	-1.46	5.13	24.4	29.33	-3.12	5.63	31.4
2	30.28	4.65	17.8	29.77	-1.69	4.97	24.1	29.37	-2.99	5.93	32.2
3	30.16	4.71	17.3	30.01	-0.51	5.25	22.8	29.41	-2.48	5.62	30.3
4	30.39	4.42	18.1	29.96	-1.43	4.92	24.1	29.43	-3.15	5.72	31.0
5	30.13	4.37	16.6	30.01	-0.41	5.25	22.4	29.50	-2.09	5.98	31.8
6	30.24	4.37	17.6	29.80	-1.46	4.92	23.2	29.48	-2.51	5.69	31.8
7	30.20	4.38	17.4	29.97	-0.77	5.19	22.2	29.35	-2.80	5.83	30.8
8	30.17	4.28	16.0	29.81	-1.20	5.22	23.4	29.43	-2.45	5.66	31.2
9	30.36	4.55	16.3	29.82	-1.79	5.00	22.6	29.30	-3.50	5.76	32.5
10	30.30	4.42	16.2	29.76	-1.79	5.21	23.3	29.38	-3.02	5.98	30.2
AVR	30.25	4.48	17.1	29.87	-1.25	5.11	23.3	29.40	-2.81	5.78	31.3
MAX	30.39	4.71	18.1	30.01	-0.41	5.25	24.4	29.50	-2.09	5.98	32.5
MIN	30.13	4.28	16.0	29.76	-1.79	4.92	22.2	29.30	-3.50	5.62	30.2
Remark	Appearance: No leakage of electrolyte.										



Judgement: OK

Measured By: Dong Achun

Checked By: Fu Tingting