

Single 2-input OR Gate**CJ74LVC1G32**      Logic**1 Introduction**

The CJ74LVC1G32 provides one 2-input OR function. Inputs can be driven from either 3.3V or 5V devices. This feature allows the use of these devices as translators in mixed 3.3V and 5V applications.

**2 Available Packages**

| PART NUMBER | PACKAGE       |
|-------------|---------------|
| CJ74LVC1G32 | SOT-23-5L     |
|             | SOT-353       |
|             | DFN0.8x0.8-4L |
|             | DFN1x1-6L     |
|             | SOT-553       |


**Note:** For all available packages, please refer to the part Orderable Information.

**3 Features**

- Wide supply voltage range from 1.65V to 5.5V
- $\pm 24\text{mA}$  output drive ( $V_{CC}=3.0\text{V}$ )
- CMOS low power consumption
- Input accepts voltages up to 5V
- Specified from  $-40^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$

**4 Applications**

- Blu-ray Player and Home Theater
- Embedded PC
- IP Phone: Wireless
- TV: LCD/Digital and High-Definition (HDTV)
- Video Conferencing: IP-Based HD
- Wireless Headset, Keyboard, Mouse, and Repeater



Block diagram

## 5 Orderable Information

| DEVICE         | PACKAGE       | OP TEMP   | ECO PLAN     | MSL              | PACKING OPTION                      | SORT   |
|----------------|---------------|-----------|--------------|------------------|-------------------------------------|--------|
| CJ74LVC1G32M5N | SOT-23-5L     | -40~125°C | RoHS & Green | Level 3<br>168HR | Tape and Reel<br>3000 Units / Reel  | Active |
| CJ74LVC1G32R5N | SOT-353       | -40~125°C | RoHS & Green | Level 3<br>168HR | Tape and Reel<br>3000 Units / Reel  | Active |
| CJ74LVC1G32DJN | DFN0.8x0.8-4L | -40~125°C | RoHS & Green | Level 3<br>168HR | Tape and Reel<br>12000 Units / Reel | Active |
| CJ74LVC1G32DKN | DFN1x1-6L     | -40~125°C | RoHS & Green | Level 3<br>168HR | Tape and Reel<br>5000 Units / Reel  | Active |
| CJ74LVC1G32S5N | SOT-553       | -40~125°C | RoHS & Green | Level 3<br>168HR | Tape and Reel<br>3000 Units / Reel  | Active |

**Note:**

**ECO PLAN:** For the RoHS and Green certification standards of this product, please refer to the official report provided by JSCJ.

**MSL:** Moisture Sensitivity Level. Determined according to JEDEC industry standard classification.

**SORT:** Specifically defined as follows:

Active: Recommended for new products;

Customized: Products manufactured to meet the specific needs of customers;

Preview: The device has been released and has not been fully mass produced. The sample may or may not be available;

NoRD: It is not recommended to use the device for new design. The device is only produced for the needs of existing customers;

Obsolete: The device has been discontinued.

## 6 Pin Configuration and Marking Information

### 6.1 Pin Configuration





Figure 6-1 Pin configuration

### 6.2 Pin Function

| PIN       |        |      | I/O <sup>(1)</sup> | DESCRIPTION    |
|-----------|--------|------|--------------------|----------------|
| No.       |        | NAME |                    |                |
| DFN1x1-6L | Others |      |                    |                |
| 1         | 1      | B    | I                  | Data input     |
| 2         | 2      | A    | I                  | Data input     |
| 3         | 3      | GND  | G                  | Ground (0V)    |
| 4         | 4      | Y    | O                  | Data output    |
| 5         | -      | N.C. | -                  | Not connected  |
| 6         | 5      | VCC  | P                  | Supply voltage |

(1) I-Input, O-Output, P-Power, G-Ground

### 6.3 Marking Information



XXXX or XX: Code, indicates weekly record information.

## 7 Specifications

### 7.1 Absolute Maximum Ratings

Voltages are referenced to GND (ground=0V), unless otherwise specified.

| SYMBOL           | PARAMETER               | CONDITIONS                                              | MIN. | MAX.                 | UNIT |
|------------------|-------------------------|---------------------------------------------------------|------|----------------------|------|
| V <sub>CC</sub>  | Supply voltage          | -                                                       | -0.5 | +6.5                 | V    |
| V <sub>I</sub>   | Input voltage           | -                                                       | -0.5 | +6.5                 | V    |
| V <sub>O</sub>   | Output voltage          | Active mode                                             | -0.5 | V <sub>CC</sub> +0.5 | V    |
|                  |                         | Power-down mode; V <sub>CC</sub> =0V                    | -0.5 | +6.5                 | V    |
| I <sub>IK</sub>  | Input clamping current  | V <sub>I</sub> < 0V                                     | -50  | -                    | mA   |
| I <sub>OK</sub>  | Output clamping current | V <sub>O</sub> > V <sub>CC</sub> or V <sub>O</sub> < 0V | -    | ±50                  | mA   |
| I <sub>O</sub>   | Output current          | V <sub>O</sub> =0V to V <sub>CC</sub>                   | -    | ±50                  | mA   |
| I <sub>CC</sub>  | Supply current          | -                                                       | -    | 100                  | mA   |
| I <sub>GND</sub> | Ground current          | -                                                       | -100 | -                    | mA   |
| T <sub>stg</sub> | Storage temperature     | -                                                       | -65  | +150                 | °C   |
| P <sub>tot</sub> | Total power dissipation | -                                                       | -    | 250                  | mW   |
| T <sub>L</sub>   | Soldering temperature   | 10s                                                     | -    | 260                  | °C   |

**Note:** Absolute maximum ratings indicate sustained limits beyond which damage to the device may occur. All voltage parameters are absolute voltages referenced to GND. The thermal resistance and power dissipation ratings are measured under board mounted and still air conditions.

### 7.2 Recommended Operating Conditions

| SYMBOL           | PARAMETER           | CONDITIONS                           | MIN. | TYP. | MAX.            | UNIT |
|------------------|---------------------|--------------------------------------|------|------|-----------------|------|
| V <sub>CC</sub>  | Supply voltage      | -                                    | 1.65 | -    | 5.5             | V    |
| V <sub>I</sub>   | Input voltage       | -                                    | 0    | -    | 5.5             | V    |
| V <sub>O</sub>   | Output voltage      | Active mode                          | 0    | -    | V <sub>CC</sub> | V    |
|                  |                     | Power-down mode; V <sub>CC</sub> =0V | 0    | -    | 5.5             | V    |
| T <sub>amb</sub> | Ambient temperature | -                                    | -40  | -    | +125            | °C   |

### 7.3 ESD Ratings

| SYMBOL               | ESD RATINGS             |                                       | VALUE | UNIT |
|----------------------|-------------------------|---------------------------------------|-------|------|
| V <sub>ESD-HBM</sub> | Electrostatic discharge | Human body model (HBM) <sup>(1)</sup> | ±2000 | V    |

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

## 7.4 Electrical Characteristics

### 7.4.1 DC Characteristics 1

$T_{amb} = -40^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$ , voltages are referenced to GND (ground=0V), unless otherwise specified.

| SYMBOL           | PARAMETER                 | CONDITIONS                                                                                           |                                                           | MIN.                 | TYP. | MAX.                 | UNIT |
|------------------|---------------------------|------------------------------------------------------------------------------------------------------|-----------------------------------------------------------|----------------------|------|----------------------|------|
| V <sub>IH</sub>  | HIGH-level input voltage  | V <sub>CC</sub> =1.65V to 1.95V                                                                      |                                                           | 0.65xV <sub>CC</sub> | -    | -                    | V    |
|                  |                           | V <sub>CC</sub> =2.3V to 2.7V                                                                        |                                                           | 1.7                  | -    | -                    | V    |
|                  |                           | V <sub>CC</sub> =2.7V to 3.6V                                                                        |                                                           | 2.0                  | -    | -                    | V    |
|                  |                           | V <sub>CC</sub> =4.5V to 5.5V                                                                        |                                                           | 0.7xV <sub>CC</sub>  | -    | -                    | V    |
| V <sub>IL</sub>  | LOW-level input voltage   | V <sub>CC</sub> =1.65V to 1.95V                                                                      |                                                           | -                    | -    | 0.35xV <sub>CC</sub> | V    |
|                  |                           | V <sub>CC</sub> =2.3V to 2.7V                                                                        |                                                           | -                    | -    | 0.7                  | V    |
|                  |                           | V <sub>CC</sub> =2.7V to 3.6V                                                                        |                                                           | -                    | -    | 0.8                  | V    |
|                  |                           | V <sub>CC</sub> =4.5V to 5.5V                                                                        |                                                           | -                    | -    | 0.3xV <sub>CC</sub>  | V    |
| V <sub>OH</sub>  | HIGH-level output voltage | V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>                                                  | I <sub>O</sub> =-100uA;<br>V <sub>CC</sub> =1.65V to 5.5V | V <sub>CC</sub> -0.1 | -    | -                    | V    |
|                  |                           |                                                                                                      | I <sub>O</sub> =-4mA; V <sub>CC</sub> =1.65V              | 1.2                  | -    | -                    | V    |
|                  |                           |                                                                                                      | I <sub>O</sub> =-8mA; V <sub>CC</sub> =2.3V               | 1.9                  | -    | -                    | V    |
|                  |                           |                                                                                                      | I <sub>O</sub> =-12mA; V <sub>CC</sub> =2.7V              | 2.2                  | -    | -                    | V    |
|                  |                           |                                                                                                      | I <sub>O</sub> =-24mA; V <sub>CC</sub> =3.0V              | 2.3                  | -    | -                    | V    |
|                  |                           |                                                                                                      | I <sub>O</sub> =-32mA; V <sub>CC</sub> =4.5V              | 3.8                  | -    | -                    | V    |
| V <sub>OL</sub>  | LOW-level output voltage  | V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>                                                  | I <sub>O</sub> =100uA;<br>V <sub>CC</sub> =1.65V to 5.5V  | -                    | -    | 0.10                 | V    |
|                  |                           |                                                                                                      | I <sub>O</sub> =4mA; V <sub>CC</sub> =1.65V               | -                    | -    | 0.45                 | V    |
|                  |                           |                                                                                                      | I <sub>O</sub> =8mA; V <sub>CC</sub> =2.3V                | -                    | -    | 0.30                 | V    |
|                  |                           |                                                                                                      | I <sub>O</sub> =12mA; V <sub>CC</sub> =2.7V               | -                    | -    | 0.40                 | V    |
|                  |                           |                                                                                                      | I <sub>O</sub> =24mA; V <sub>CC</sub> =3.0V               | -                    | -    | 0.55                 | V    |
|                  |                           |                                                                                                      | I <sub>O</sub> =32mA; V <sub>CC</sub> =4.5V               | -                    | -    | 0.55                 | V    |
| I <sub>I</sub>   | Input leakage current     | V <sub>I</sub> =5.5V or GND;<br>V <sub>CC</sub> =0V to 5.5V                                          |                                                           | -                    | -    | ±1                   | uA   |
| I <sub>OFF</sub> | Power-off leakage current | V <sub>I</sub> or V <sub>O</sub> =5.5V; V <sub>CC</sub> =0V                                          |                                                           | -                    | -    | ±2                   | uA   |
| I <sub>CC</sub>  | Supply current            | V <sub>I</sub> =5.5V or GND; I <sub>O</sub> =0A;<br>V <sub>CC</sub> =1.65V to 5.5V                   |                                                           | -                    | -    | 4                    | uA   |
| ΔI <sub>CC</sub> | Additional supply current | Per pin; V <sub>I</sub> =V <sub>CC</sub> -0.6V; I <sub>O</sub> =0A;<br>V <sub>CC</sub> =2.3V to 5.5V |                                                           | -                    | -    | 500                  | uA   |
| C <sub>I</sub>   | Input capacitance         | V <sub>CC</sub> =3.3V; V <sub>I</sub> =GND to V <sub>CC</sub>                                        |                                                           | -                    | 5    | -                    | pF   |

(1) All typical values are measured at  $V_{CC}=3.3\text{V}$  and  $T_{amb}=25^{\circ}\text{C}$ .

## 7.4.2 DC Characteristics 2

T<sub>amb</sub>=−40°C to +125°C, voltages are referenced to GND (ground=0V), unless otherwise specified.

| SYMBOL           | PARAMETER                 | CONDITIONS                                                                                           |                                                           | MIN.                 | TYP. | MAX.                 | UNIT |
|------------------|---------------------------|------------------------------------------------------------------------------------------------------|-----------------------------------------------------------|----------------------|------|----------------------|------|
| V <sub>IH</sub>  | HIGH-level input voltage  | V <sub>CC</sub> =1.65V to 1.95V                                                                      |                                                           | 0.65xV <sub>CC</sub> | -    | -                    | V    |
|                  |                           | V <sub>CC</sub> =2.3V to 2.7V                                                                        |                                                           | 1.7                  | -    | -                    | V    |
|                  |                           | V <sub>CC</sub> =2.7V to 3.6V                                                                        |                                                           | 2.0                  | -    | -                    | V    |
|                  |                           | V <sub>CC</sub> =4.5V to 5.5V                                                                        |                                                           | 0.7xV <sub>CC</sub>  | -    | -                    | V    |
| V <sub>IL</sub>  | LOW-level input voltage   | V <sub>CC</sub> =1.65V to 1.95V                                                                      |                                                           | -                    | -    | 0.35xV <sub>CC</sub> | V    |
|                  |                           | V <sub>CC</sub> =2.3V to 2.7V                                                                        |                                                           | -                    | -    | 0.7                  | V    |
|                  |                           | V <sub>CC</sub> =2.7V to 3.6V                                                                        |                                                           | -                    | -    | 0.8                  | V    |
|                  |                           | V <sub>CC</sub> =4.5V to 5.5V                                                                        |                                                           | -                    | -    | 0.3xV <sub>CC</sub>  | V    |
| V <sub>OH</sub>  | HIGH-level output voltage | V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>                                                  | I <sub>O</sub> =-100uA;<br>V <sub>CC</sub> =1.65V to 5.5V | V <sub>CC</sub> -0.1 | -    | -                    | V    |
|                  |                           |                                                                                                      | I <sub>O</sub> =-4mA; V <sub>CC</sub> =1.65V              | 0.95                 | -    | -                    | V    |
|                  |                           |                                                                                                      | I <sub>O</sub> =-8mA; V <sub>CC</sub> =2.3V               | 1.7                  | -    | -                    | V    |
|                  |                           |                                                                                                      | I <sub>O</sub> =-12mA; V <sub>CC</sub> =2.7V              | 1.9                  | -    | -                    | V    |
|                  |                           |                                                                                                      | I <sub>O</sub> =-24mA; V <sub>CC</sub> =3.0V              | 2.0                  | -    | -                    | V    |
|                  |                           |                                                                                                      | I <sub>O</sub> =-32mA; V <sub>CC</sub> =4.5V              | 3.4                  | -    | -                    | V    |
| V <sub>OL</sub>  | LOW-level output voltage  | V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>                                                  | I <sub>O</sub> =100uA;<br>V <sub>CC</sub> =1.65V to 5.5V  | -                    | -    | 0.10                 | V    |
|                  |                           |                                                                                                      | I <sub>O</sub> =4mA; V <sub>CC</sub> =1.65V               | -                    | -    | 0.70                 | V    |
|                  |                           |                                                                                                      | I <sub>O</sub> =8mA; V <sub>CC</sub> =2.3V                | -                    | -    | 0.45                 | V    |
|                  |                           |                                                                                                      | I <sub>O</sub> =12mA; V <sub>CC</sub> =2.7V               | -                    | -    | 0.60                 | V    |
|                  |                           |                                                                                                      | I <sub>O</sub> =24mA; V <sub>CC</sub> =3.0V               | -                    | -    | 0.80                 | V    |
|                  |                           |                                                                                                      | I <sub>O</sub> =32mA; V <sub>CC</sub> =4.5V               | -                    | -    | 0.80                 | V    |
| I <sub>I</sub>   | Input leakage current     | V <sub>I</sub> =5.5V or GND;<br>V <sub>CC</sub> =0V to 5.5V                                          |                                                           | -                    | -    | ±1                   | uA   |
| I <sub>OFF</sub> | Power-off leakage current | V <sub>I</sub> or V <sub>O</sub> =5.5V; V <sub>CC</sub> =0V                                          |                                                           | -                    | -    | ±2                   | uA   |
| I <sub>CC</sub>  | Supply current            | V <sub>I</sub> =5.5V or GND; I <sub>O</sub> =0A;<br>V <sub>CC</sub> =1.65V to 5.5V                   |                                                           | -                    | -    | 4                    | uA   |
| ΔI <sub>CC</sub> | Additional supply current | Per pin; V <sub>I</sub> =V <sub>CC</sub> -0.6V; I <sub>O</sub> =0A;<br>V <sub>CC</sub> =2.3V to 5.5V |                                                           | -                    | -    | 500                  | uA   |

### 7.4.3 AC Characteristics 1

$T_{amb} = -40^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$ , voltages are referenced to GND (ground=0V), unless otherwise specified.

| SYMBOL    | PARAMETER                      | CONDITIONS     |                                       | MIN. | TYP. <sup>(1)</sup> | MAX. | UNIT |
|-----------|--------------------------------|----------------|---------------------------------------|------|---------------------|------|------|
| $t_{PHL}$ | A, B to Y<br>propagation delay | See Figure 8-5 | $V_{CC}=1.65\text{V to }1.95\text{V}$ | -    | 12.5                | 18.8 | ns   |
|           |                                |                | $V_{CC}=2.3\text{V to }2.7\text{V}$   | -    | 10.5                | 15.8 | ns   |
|           |                                |                | $V_{CC}=2.7\text{V}$                  | -    | 10                  | 15   | ns   |
|           |                                |                | $V_{CC}=3.0\text{V to }3.6\text{V}$   | -    | 9.5                 | 14.3 | ns   |
|           |                                |                | $V_{CC}=4.5\text{V to }5.5\text{V}$   | -    | 9                   | 13.5 | ns   |
| $t_{PLH}$ | A, B to Y<br>propagation delay | See Figure 8-5 | $V_{CC}=1.65\text{V to }1.95\text{V}$ | -    | 14                  | 21   | ns   |
|           |                                |                | $V_{CC}=2.3\text{V to }2.7\text{V}$   | -    | 10                  | 15   | ns   |
|           |                                |                | $V_{CC}=2.7\text{V}$                  | -    | 9.5                 | 14.3 | ns   |
|           |                                |                | $V_{CC}=3.0\text{V to }3.6\text{V}$   | -    | 8.5                 | 12.8 | ns   |
|           |                                |                | $V_{CC}=4.5\text{V to }5.5\text{V}$   | -    | 7.5                 | 11.3 | ns   |

(1) Typical values are measured at  $T_{amb}=25^{\circ}\text{C}$  and  $V_{CC}=1.8\text{V}$ ,  $2.5\text{V}$ ,  $2.7\text{V}$ ,  $3.3\text{V}$  and  $5.0\text{V}$  respectively.

### 7.4.4 AC Characteristics 2

$T_{amb} = -40^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$ , voltages are referenced to GND (ground=0V), unless otherwise specified.

| SYMBOL    | PARAMETER                      | CONDITIONS     |                                       | MIN. | TYP. | MAX. | UNIT |
|-----------|--------------------------------|----------------|---------------------------------------|------|------|------|------|
| $t_{PHL}$ | A, B to Y<br>propagation delay | See Figure 8-5 | $V_{CC}=1.65\text{V to }1.95\text{V}$ | -    | -    | 20.8 | ns   |
|           |                                |                | $V_{CC}=2.3\text{V to }2.7\text{V}$   | -    | -    | 17.8 | ns   |
|           |                                |                | $V_{CC}=2.7\text{V}$                  | -    | -    | 17   | ns   |
|           |                                |                | $V_{CC}=3.0\text{V to }3.6\text{V}$   | -    | -    | 16.3 | ns   |
|           |                                |                | $V_{CC}=4.5\text{V to }5.5\text{V}$   | -    | -    | 15.5 | ns   |
| $t_{PLH}$ | A, B to Y<br>propagation delay | See Figure 8-5 | $V_{CC}=1.65\text{V to }1.95\text{V}$ | -    | -    | 23   | ns   |
|           |                                |                | $V_{CC}=2.3\text{V to }2.7\text{V}$   | -    | -    | 17   | ns   |
|           |                                |                | $V_{CC}=2.7\text{V}$                  | -    | -    | 16.3 | ns   |
|           |                                |                | $V_{CC}=3.0\text{V to }3.6\text{V}$   | -    | -    | 14.8 | ns   |
|           |                                |                | $V_{CC}=4.5\text{V to }5.5\text{V}$   | -    | -    | 13.3 | ns   |

## 8 Detailed Description

### 8.1 Overview

The CJ74LVC1G32 provides one 2-input OR function.

Inputs can be driven from either 3.3V or 5V devices. This feature allows the use of these devices as translators in mixed 3.3V and 5V applications.

### 8.2 Functional Block Diagram




Figure 8-1 Logic symbol




Figure 8-2 IEC logic symbol




Figure 8-3 Logic diagram

### 8.3 Function Table

| INPUT |   | OUTPUT |
|-------|---|--------|
| A     | B | Y      |
| L     | L | L      |
| L     | H | H      |
| H     | L | H      |
| H     | H | H      |

(1) H=HIGH voltage level; L=LOW voltage level.

### 8.4 Testing Circuit

#### 8.4.1 AC Testing Circuit




Figure 8-4 Test circuit for measuring switching times

Definitions for test circuit:

$R_L$ =Load resistance.

$C_L$ =Load capacitance including jig and probe capacitance.

$R_T$ =Termination resistance should be equal to the output impedance  $Z_o$  of the pulse generator.

$V_{EXT}$ =External voltage for measuring switching times.

## 8.4.2 AC Testing Waveforms




Figure 8-5 The input A, B to output Y propagation delays

## 8.4.3 Measurement Points

| SUPPLY VOLTAGE | INPUT               | OUTPUT              |
|----------------|---------------------|---------------------|
| $V_{CC}$       | $V_M$               | $V_M$               |
| 1.65V to 1.95V | $0.5 \times V_{CC}$ | $0.5 \times V_{CC}$ |
| 2.3V to 2.7V   | $0.5 \times V_{CC}$ | $0.5 \times V_{CC}$ |
| 2.7V           | 1.5V                | 1.5V                |
| 3.0V to 3.6V   | 1.5V                | 1.5V                |
| 4.5V to 5.5V   | $0.5 \times V_{CC}$ | $0.5 \times V_{CC}$ |


## 8.4.4 Test Data

| SUPPLY VOLTAGE | INPUT    |             | LOAD  |              | $V_{EXT}$          |
|----------------|----------|-------------|-------|--------------|--------------------|
| $V_{CC}$       | $V_I$    | $t_r = t_f$ | $C_L$ | $R_L$        | $t_{PLH}, t_{PHL}$ |
| 1.65V to 1.95V | $V_{CC}$ | $\leq 3ns$  | 30pF  | 1k $\Omega$  | Open               |
| 2.3V to 2.7V   | $V_{CC}$ | $\leq 3ns$  | 30pF  | 500 $\Omega$ | Open               |
| 2.7V           | 2.7V     | $\leq 3ns$  | 50pF  | 500 $\Omega$ | Open               |
| 3.0V to 3.6V   | 2.7V     | $\leq 3ns$  | 50pF  | 500 $\Omega$ | Open               |
| 4.5V to 5.5V   | $V_{CC}$ | $\leq 3ns$  | 50pF  | 500 $\Omega$ | Open               |

## 9 Mechanical Information

### 9.1 SOT-23-5L Mechanical Information


#### 9.1.1 SOT-23-5L Outline Dimensions



| SYMBOL   | Dimensions In Millimeters |      |      |
|----------|---------------------------|------|------|
|          | Min.                      | Typ. | Max. |
| A        | -                         | -    | 1.26 |
| A1       | 0.00                      | -    | 0.12 |
| A2       | 1.00                      | -    | 1.20 |
| b        | 0.30                      | -    | 0.50 |
| c        | 0.10                      | -    | 0.20 |
| D        | 2.82                      | -    | 3.02 |
| E        | 2.60                      | -    | 3.00 |
| E1       | 1.50                      | -    | 1.70 |
| e        | 0.95 BSC                  |      |      |
| e1       | 1.80                      | -    | 2.00 |
| L        | 0.30                      | -    | 0.60 |
| $\theta$ | 0°                        | -    | 8°   |
| Unit: mm |                           |      |      |

## 9.2 SOT-353 Mechanical Information


### 9.2.1 SOT-353 Outline Dimensions



| SYMBOL   | Dimensions In Millimeters |       |       |
|----------|---------------------------|-------|-------|
|          | Min.                      | Typ.  | Max.  |
| A        | 0.90                      | -     | 1.10  |
| A1       | 0.00                      | -     | 0.10  |
| A2       | 0.90                      | -     | 1.00  |
| b        | 0.15                      | -     | 0.35  |
| c        | 0.11                      | -     | 0.175 |
| D        | 2.00                      | -     | 2.20  |
| E        | 2.15                      | -     | 2.45  |
| E1       | 1.15                      | -     | 1.35  |
| e        | 0.65 BSC                  |       |       |
| e1       | 1.20                      | -     | 1.40  |
| L        | -                         | 0.525 | -     |
| L1       | 0.26                      | -     | 0.46  |
| θ        | 0°                        | -     | 8°    |
| Unit: mm |                           |       |       |

### 9.3 DFN0.8x0.8-4L Mechanical Information


#### 9.3.1 DFN0.8x0.8-4L Outline Dimensions



| SYMBOL   | Dimensions In Millimeters |       |      |
|----------|---------------------------|-------|------|
|          | Min.                      | Typ.  | Max. |
| A        | 0.37                      | -     | 0.43 |
| A1       | 0.00                      | -     | 0.05 |
| b        | 0.15                      | -     | 0.25 |
| c        | -                         | 0.127 | -    |
| D        | 0.75                      | -     | 0.85 |
| D2       | 0.20                      | -     | 0.40 |
| E        | 0.75                      | -     | 0.85 |
| E2       | 0.20                      | -     | 0.40 |
| e        | 0.50 BSC                  |       |      |
| L        | 0.15                      | -     | 0.25 |
| L1       | -                         | 0.05  | -    |
| L2       | -                         | 0.20  | -    |
| L3       | -                         | 0.055 | -    |
| L4       | -                         | 0.10  | -    |
| R        | -                         | 0.05  | -    |
| Unit: mm |                           |       |      |

## 9.4 DFN1x1-6L Mechanical Information


### 9.4.1 DFN1x1-6L Outline Dimensions



| SYMBOL   | Dimensions In Millimeters |       |      |
|----------|---------------------------|-------|------|
|          | Min.                      | Typ.  | Max. |
| A        | 0.41                      | -     | 0.50 |
| A1       | 0.00                      | -     | 0.05 |
| A3       | -                         | 0.127 | -    |
| b        | 0.11                      | -     | 0.21 |
| D        | -                         | 1.00  | -    |
| E        | -                         | 1.00  | -    |
| e        | 0.35 BSC                  |       |      |
| L        | 0.26                      | -     | 0.36 |
| L1       | 0.31                      | -     | 0.41 |
| L2       | 0.02                      | -     | 0.12 |
| Unit: mm |                           |       |      |

## 9.5 SOT-553 Mechanical Information

### 9.5.1 SOT-553 Outline Dimensions



| SYMBOL   | Dimensions In Millimeters |      |      |
|----------|---------------------------|------|------|
|          | Min.                      | Typ. | Max. |
| A        | 0.525                     | -    | 0.60 |
| A1       | 0                         | -    | 0.05 |
| b        | 0.17                      | -    | 0.27 |
| c        | 0.09                      | -    | 0.16 |
| D        | 1.50                      | -    | 1.70 |
| E        | 1.50                      | -    | 1.70 |
| E1       | 1.10                      | -    | 1.30 |
| e        | 0.45                      | -    | 0.55 |
| L        | 0.10                      | -    | 0.30 |
| Θ        | 0°                        | -    | 7°   |
| Unit: mm |                           |      |      |

## **10 Notes and Revision History**

### **10.1 Associated Product Family and Others**

To view other products of the same type or IC products of other types, click the official website of JSCJ -- <https://www.jscj-elec.com> for more details.

### **10.2 Notes**

#### **Electrostatic Discharge Caution**



This IC may be damaged by ESD. Relevant personnel shall comply with correct installation and use specifications to avoid ESD damage to the IC. If appropriate measures are not taken to prevent ESD damage, the hazards caused by ESD include but are not limited to degradation of integrated circuit performance or complete damage of integrated circuit. For some precision integrated circuits, a very small parameter change may cause the whole device to be inconsistent with its published specifications.

### **10.3 Revision History**

**June, 2025: rev - 1.3, Correct package parameters in 9.2 Mechanical information.**

**July, 2025: rev - 1.5, Change pin configuration and marking information.**

# DISCLAIMER

## IMPORTANT NOTICE, PLEASE READ CAREFULLY

The information in this data sheet is intended to describe the operation and characteristics of our products. JSCJ has the right to make any modification, enhancement, improvement, correction or other changes to any content in this data sheet, including but not limited to specification parameters, circuit design and application information, without prior notice.

Any person who purchases or uses JSCJ products for design shall: 1. Select products suitable for circuit application and design; 2. Design, verify and test the rationality of circuit design; 3. Procedures to ensure that the design complies with relevant laws and regulations and the requirements of such laws and regulations. JSCJ makes no warranty or representation as to the accuracy or completeness of the information contained in this data sheet and assumes no responsibility for the application or use of any of the products described in this data sheet.

Without the written consent of JSCJ, this product shall not be used in occasions requiring high quality or high reliability, including but not limited to the following occasions: medical equipment, military facilities and aerospace. JSCJ shall not be responsible for casualties or property losses caused by abnormal use or application of this product.

Official Website: [www.jscj-elec.com](http://www.jscj-elec.com)

Copyright © JIANGSU CHANGJING ELECTRONICS TECHNOLOGY CO., LTD