

1、General Description

The 74LVC1G74 is a single positive edge triggered D-type flip-flop with individual data (D) inputs, clock (CP) inputs, set (\bar{S} D) and reset (\bar{R} D) inputs, and complementary Q and \bar{Q} outputs.

The set and reset are asynchronous active LOW inputs and operate independently of the clock input. Information on the data input is transferred to the Q output on the LOW-to-HIGH transition of the clock pulse. The D inputs must be stable one set-up time prior to the LOW-to-HIGH clock transition for predictable operation.

Features:

- Wide supply voltage range from 1.65V to 5.5V
- 5 V tolerant outputs for interfacing with 5V logic
- $\pm 24\text{mA}$ output drive ($V_{CC}=3.0\text{V}$)
- CMOS low power consumption
- Input accepts voltages up to 5V
- Specified from -40°C to $+125^{\circ}\text{C}$
- Packaging information:

TSSOP8/VSSOP8/SOP8/XSON8 (1*1.35*0.32)-0.35/XSON8 (1*1.95*0.5)-0.5

Ordering Information

Ordernumber	Package	Marking	Operation Temperature Range	MSL Grade	Ship,Quantity	Green
74LVC1G74DC,125-JSM	VSSOP-8	ASXX	-40 to 125°C	3	3000PCS/reel	Rohs
74LVC1G74DP-JSM	TSSOP-8	ASXX	-40 to 125°C	3	3000PCS/reel	Rohs

2、Block Diagram And Pin Description

2.1、Block Diagram




Figure 1. Logic symbol




Figure 2. IEC logic symbol





Figure 3. Logic diagram

2.2、Pin Configurations



2.3、Pin Description

Pin No.	Pin Name	Description
1	CP	clock input (LOW-to-HIGH, edge-triggered)
2	D	data input
3	\bar{Q}	complement output
4	GND	ground (0V)
5	Q	true output
6	$\bar{R}D$	asynchronous reset-direct input (active LOW)
7	$\bar{S}D$	asynchronous set-direct input (active LOW)
8	V _{CC}	supply voltage

2.4、Function Table

Function table for asynchronous operation

Input				Output	
$\bar{S}D$	$\bar{R}D$	CP	D	Q	\bar{Q}
L	H	X	X	H	L
H	L	X	X	L	H
L	L	X	X	H	H

Note: H=HIGH voltage level; L=LOW voltage level; X=don't care.

Function table for synchronous operation

Input				Output	
$\bar{S}D$	$\bar{R}D$	CP	D	Q _{n+1}	\bar{Q} _{n+1}
H	H	↑	L	L	H
H	H	↑	H	H	L

Note: H=HIGH voltage level; L=LOW voltage level; ↑= LOW-to-HIGH CP transition;
 Q_{n+1} = state after the next LOW-to-HIGH CP transition.

3、Electrical Parameter

3.1、Absolute Maximum Ratings

(Voltages are referenced to GND (ground=0V), unless otherwise specified.)

Parameter	Symbol	Conditions	Min.	Max.	Unit
supply voltage	V_{CC}	-	-0.5	+6.5	V
input voltage	V_I	-	-0.5	+6.5	V
output voltage	V_O	Active mode	-0.5	$V_{CC}+0.5$	V
		Power-down mode	-0.5	+6.5	V
input clamping current	I_{IK}	$V_I < 0V$	-50	-	mA
output clamping current	I_{OK}	$V_O > V_{CC}$ or $V_O < 0V$	-	± 50	mA
output current	I_O	$V_O=0V$ to V_{CC}	-	± 50	mA
supply current	I_{CC}	-	-	100	mA
ground current	I_{GND}	-	-100	-	mA
storage temperature	T_{stg}	-	-65	+150	°C
total power dissipation	P_{tot}	-	-	300	mW
Soldering temperature	T_L	10s	260		°C

Note: When $V_{CC}=0V$ (Power-down mode), the output voltage can be 5.5V in normal operation

3.2、Recommended Operating Conditions

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
supply voltage	V_{CC}	-	1.65	-	5.5	V
input voltage	V_I	-	0	-	5.5	V
output voltage	V_O	Active mode	0	-	V_{CC}	V
		Power-down mode; $V_{CC}=0V$	0	-	5.5	V
ambient temperature	T_{amb}	-	-40	-	+125	°C

3.3、Electrical Characteristics
3.3.1、DC Characteristics 1

 (T_{amb}=-40°C to +85°C, voltages are referenced to GND (ground=0V), unless otherwise specified.)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit	
HIGH-level input voltage	V _{IH}	V _{CC} =1.65V to 1.95V	0.65× V _{CC}	-	-	V	
		V _{CC} =2.3V to 2.7V	1.7	-	-	V	
		V _{CC} =2.7V to 3.6V	2.0	-	-	V	
		V _{CC} =4.5V to 5.5V	0.7× V _{CC}	-	-	V	
LOW-level input voltage	V _{IL}	V _{CC} =1.65V to 1.95V	-	-	0.35× V _{CC}	V	
		V _{CC} =2.3V to 2.7V	-	-	0.7	V	
		V _{CC} =2.7V to 3.6V	-	-	0.8	V	
		V _{CC} =4.5V to 5.5V	-	-	0.3× V _{CC}	V	
HIGH-level output voltage	V _{OH}	V _I = V _{IH} or V _{IL}	I _O =-100uA; V _{CC} =1.65V to 5.5V	V _{CC} - 0.1	-	-	V
			I _O =-4mA; V _{CC} =1.65V	1.2	1.54	-	V
			I _O =-8mA; V _{CC} =2.3V	1.9	2.15	-	V
			I _O =-12mA; V _{CC} =2.7V	2.2	2.50	-	V
			I _O =-24mA; V _{CC} =3.0V	2.3	2.62	-	V
			I _O =-32mA; V _{CC} =4.5V	3.8	4.11	-	V
LOW-level output voltage	V _{OL}	V _I = V _{IH} or V _{IL}	I _O =100uA; V _{CC} =1.65V to 5.5V	-	-	0.10	V
			I _O =4mA; V _{CC} =1.65V	-	0.07	0.45	V
			I _O =8mA; V _{CC} =2.3V	-	0.12	0.30	V
			I _O =12mA; V _{CC} =2.7V	-	0.17	0.40	V
			I _O =24mA; V _{CC} =3.0V	-	0.33	0.55	V
			I _O =32mA; V _{CC} =4.5V	-	0.39	0.55	V
input leakage current	I _I	V _I =5.5V or GND; V _{CC} =0V to 5.5V	-	-	±1	uA	
power-off leakage current	I _{OFF}	V _I or V _O =5.5V; V _{CC} =0V	-	-	±2	uA	
supply current	I _{CC}	V _I =5.5V or GND; I _O =0A; V _{CC} =1.65V to 5.5V	-	-	4	uA	
additional supply current	ΔI _{CC}	per pin; V _I =V _{CC} -0.6V; I _O =0A; V _{CC} =2.3V to 5.5V	-	-	500	uA	
input capacitance	C _I	-	-	4.0	-	pF	

 Note: All typical values are measured at T_{amb}=25°C.

3.3.2、DC Characteristics 2

 (T_{amb}=-40°C to +125°C, voltages are referenced to GND (ground=0V), unless otherwise specified.)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit	
HIGH-level input voltage	V _{IH}	V _{CC} =1.65V to 1.95V	0.65× V _{CC}	-	-	V	
		V _{CC} =2.3V to 2.7V	1.7	-	-	V	
		V _{CC} =2.7V to 3.6V	2.0	-	-	V	
		V _{CC} =4.5V to 5.5V	0.7× V _{CC}	-	-	V	
LOW-level input voltage	V _{IL}	V _{CC} =1.65V to 1.95V	-	-	0.35× V _{CC}	V	
		V _{CC} =2.3V to 2.7V	-	-	0.7	V	
		V _{CC} =2.7V to 3.6V	-	-	0.8	V	
		V _{CC} =4.5V to 5.5V	-	-	0.3× V _{CC}	V	
HIGH-level output voltage	V _{OH}	V _I = V _{IH} or V _{IL}	I _O =-100uA; V _{CC} =1.65V to 5.5V	V _{CC} - 0.1	-	-	V
			I _O =-4mA; V _{CC} =1.65V	0.95	-	-	V
			I _O =-8mA; V _{CC} =2.3V	1.7	-	-	V
			I _O =-12mA; V _{CC} =2.7V	1.9	-	-	V
			I _O =-24mA; V _{CC} =3.0V	2.0	-	-	V
			I _O =-32mA; V _{CC} =4.5V	3.4	-	-	V
LOW-level output voltage	V _{OL}	V _I = V _{IH} or V _{IL}	I _O =100uA; V _{CC} =1.65V to 5.5V	-	-	0.10	V
			I _O =4mA; V _{CC} =1.65V	-	-	0.70	V
			I _O =8mA; V _{CC} =2.3V	-	-	0.45	V
			I _O =12mA; V _{CC} =2.7V	-	-	0.60	V
			I _O =24mA; V _{CC} =3.0V	-	-	0.80	V
			I _O =32mA; V _{CC} =4.5V	-	-	0.80	V
input leakage current	I _I	V _I =5.5V or GND; V _{CC} =0V to 5.5V	-	-	±1	uA	
power-off leakage current	I _{OFF}	V _I or V _O =5.5V; V _{CC} =0V	-	-	±2	uA	
supply current	I _{CC}	V _I =5.5V or GND; I _O =0A; V _{CC} =1.65V to 5.5V	-	-	4	uA	
additional supply current	ΔI _{CC}	per pin; V _I =V _{CC} -0.6V; I _O =0A; V _{CC} =2.3V to 5.5V	-	-	500	uA	

3.3.3、AC Characteristics 1

 (T_{amb}=-40°C to +85°C, voltages are referenced to GND (ground=0V), unless otherwise specified.)

Parameter	Symbol	Conditions	Min.	Typ. ^[1]	Max.	Unit	
propagation delay	t _{PHL}	CP to Q, \bar{Q} ; see Figure 5	V _{CC} =1.65V to 1.95V	-	12.5	18.8	ns
			V _{CC} =2.3V to 2.7V	-	10.5	15.8	ns
			V _{CC} =2.7V	-	10	15	ns
			V _{CC} =3.0V to 3.6V	-	9.5	14.3	ns
			V _{CC} =4.5V to 5.5V	-	9	13.5	ns
		$\bar{S}D$ to Q, \bar{Q} ; see Figure 6	V _{CC} =1.65V to 1.95V	-	12.5	18.8	ns
			V _{CC} =2.3V to 2.7V	-	10.5	15.8	ns
			V _{CC} =2.7V	-	10	15	ns
			V _{CC} =3.0V to 3.6V	-	9.5	14.3	ns
			V _{CC} =4.5V to 5.5V	-	9	13.5	ns
		$\bar{R}D$ to Q, \bar{Q} ; see Figure 6	V _{CC} =1.65V to 1.95V	-	12.5	18.8	ns
			V _{CC} =2.3V to 2.7V	-	10.5	15.8	ns
			V _{CC} =2.7V	-	10	15	ns
			V _{CC} =3.0V to 3.6V	-	9.5	14.3	ns
			V _{CC} =4.5V to 5.5V	-	9	13.5	ns
propagation delay	t _{PLH}	CP to Q, \bar{Q} ; see Figure 5	V _{CC} =1.65V to 1.95V	-	14	21	ns
			V _{CC} =2.3V to 2.7V	-	10	15	ns
			V _{CC} =2.7V	-	9.5	14.3	ns
			V _{CC} =3.0V to 3.6V	-	8.5	12.8	ns
			V _{CC} =4.5V to 5.5V	-	7.5	11.3	ns
		$\bar{S}D$ to Q, \bar{Q} ; see Figure 6	V _{CC} =1.65V to 1.95V	-	14	21	ns
			V _{CC} =2.3V to 2.7V	-	10	15	ns
			V _{CC} =2.7V	-	9.5	14.3	ns
			V _{CC} =3.0V to 3.6V	-	8.5	12.8	ns
			V _{CC} =4.5V to 5.5V	-	7.5	11.3	ns
		$\bar{R}D$ to Q, \bar{Q} ; see Figure 6	V _{CC} =1.65V to 1.95V	-	14	21	ns
			V _{CC} =2.3V to 2.7V	-	10	15	ns
			V _{CC} =2.7V	-	9.5	14.3	ns
			V _{CC} =3.0V to 3.6V	-	8.5	12.8	ns
			V _{CC} =4.5V to 5.5V	-	7.5	11.3	ns
pulse width	t _w	CP HIGH or LOW; see Figure 5	V _{CC} =1.65V to 1.95V	6.2	-	-	ns
			V _{CC} =2.3V to 2.7V	2.7	-	-	ns
			V _{CC} =2.7V	2.7	-	-	ns
			V _{CC} =3.0V to 3.6V	2.7	1.3	-	ns
			V _{CC} =4.5V to 5.5V	2.0	-	-	ns
		$\bar{S}D$ and $\bar{R}D$ LOW; see Figure 6	V _{CC} =1.65V to 1.95V	6.2	-	-	ns
			V _{CC} =2.3V to 2.7V	2.7	-	-	ns
			V _{CC} =2.7V	2.7	-	-	ns
			V _{CC} =3.0V to 3.6V	2.7	1.6	-	ns
			V _{CC} =4.5V to 5.5V	2.0	-	-	ns
recovery time	t _{rec}	$\bar{S}D$ or $\bar{R}D$; see Figure 6	V _{CC} =1.65V to 1.95V	1.9	-	-	ns
			V _{CC} =2.3V to 2.7V	1.4	-	-	ns

			$V_{CC}=2.7V$	1.3	-	-	ns
			$V_{CC}=3.0V$ to $3.6V$	+1.2	-3.0	-	ns
			$V_{CC}=4.5V$ to $5.5V$	1.0	-	-	ns
set-up time	t_{su}	D to CP; see Figure 5	$V_{CC}=1.65V$ to $1.95V$	2.9	-	-	ns
			$V_{CC}=2.3V$ to $2.7V$	1.7	-	-	ns
			$V_{CC}=2.7V$	1.7	-	-	ns
			$V_{CC}=3.0V$ to $3.6V$	1.3	0.5	-	ns
			$V_{CC}=4.5V$ to $5.5V$	1.1	-	-	ns
hold time	t_h	D to CP; see Figure 5	$V_{CC}=1.65V$ to $1.95V$	1.5	-	-	ns
			$V_{CC}=2.3V$ to $2.7V$	1.0	-	-	ns
			$V_{CC}=2.7V$	1.0	-	-	ns
			$V_{CC}=3.0V$ to $3.6V$	1.0	0.6	-	ns
			$V_{CC}=4.5V$ to $5.5V$	1.0	-	-	ns
maximum frequency	f_{max}	CP; see Figure 5	$V_{CC}=1.65V$ to $1.95V$	80	-	-	MHz
			$V_{CC}=2.3V$ to $2.7V$	175	-	-	MHz
			$V_{CC}=2.7V$	175	-	-	MHz
			$V_{CC}=3.0V$ to $3.6V$	175	280	-	MHz
			$V_{CC}=4.5V$ to $5.5V$	200	-	-	MHz

Note:

[1] Typical values are measured at $T_{amb}=25^{\circ}C$ and $V_{CC}=1.8V, 2.5V, 2.7V, 3.3V$ and $5.0V$ respectively.

3.3.4. AC Characteristics 2

($T_{amb}=-40^{\circ}C$ to $+125^{\circ}C$, voltages are referenced to GND (ground=0V), unless otherwise specified.)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit		
propagation delay	t_{PHL}	CP to Q, \bar{Q} ; see Figure 5	$V_{CC}=1.65V$ to $1.95V$	-	-	20.8	ns	
			$V_{CC}=2.3V$ to $2.7V$	-	-	17.8	ns	
			$V_{CC}=2.7V$	-	-	17	ns	
			$V_{CC}=3.0V$ to $3.6V$	-	-	16.3	ns	
			$V_{CC}=4.5V$ to $5.5V$	-	-	15.5	ns	
		\bar{SD} to Q, \bar{Q} ; see Figure 6	$V_{CC}=1.65V$ to $1.95V$	-	-	20.8	ns	
			$V_{CC}=2.3V$ to $2.7V$	-	-	17.8	ns	
			$V_{CC}=2.7V$	-	-	17	ns	
			$V_{CC}=3.0V$ to $3.6V$	-	-	16.3	ns	
			$V_{CC}=4.5V$ to $5.5V$	-	-	15.5	ns	
		\bar{RD} to Q, \bar{Q} ; see Figure 6	$V_{CC}=1.65V$ to $1.95V$	-	-	20.8	ns	
			$V_{CC}=2.3V$ to $2.7V$	-	-	17.8	ns	
			$V_{CC}=2.7V$	-	-	17	ns	
			$V_{CC}=3.0V$ to $3.6V$	-	-	16.3	ns	
			$V_{CC}=4.5V$ to $5.5V$	-	-	15.5	ns	
propagation delay	t_{PLH}	CP to Q, \bar{Q} ; see Figure 5	$V_{CC}=1.65V$ to $1.95V$	-	-	23	ns	
			$V_{CC}=2.3V$ to $2.7V$	-	-	17	ns	
			$V_{CC}=2.7V$	-	-	16.3	ns	
			$V_{CC}=3.0V$ to $3.6V$	-	-	14.8	ns	
			$V_{CC}=4.5V$ to $5.5V$	-	-	13.3	ns	
		-	-	$V_{CC}=1.65V$ to $1.95V$	-	-	23	ns

		see Figure 6	$V_{CC}=2.3V$ to $2.7V$	-	-	17	ns
			$V_{CC}=2.7V$	-	-	16.3	ns
			$V_{CC}=3.0V$ to $3.6V$	-	-	14.8	ns
			$V_{CC}=4.5V$ to $5.5V$	-	-	13.3	ns
		$\bar{R}D$ to Q , \bar{Q} ; see Figure 6	$V_{CC}=1.65V$ to $1.95V$	-	-	23	ns
			$V_{CC}=2.3V$ to $2.7V$	-	-	17	ns
			$V_{CC}=2.7V$	-	-	16.3	ns
			$V_{CC}=3.0V$ to $3.6V$	-	-	14.8	ns
pulse width	t_w	CP HIGH or LOW; see Figure 5	$V_{CC}=1.65V$ to $1.95V$	6.2	-	-	ns
			$V_{CC}=2.3V$ to $2.7V$	2.7	-	-	ns
			$V_{CC}=2.7V$	2.7	-	-	ns
			$V_{CC}=3.0V$ to $3.6V$	2.7	-	-	ns
		$\bar{S}D$ and $\bar{R}D$ LOW; see Figure 6	$V_{CC}=4.5V$ to $5.5V$	2.0	-	-	ns
			$V_{CC}=1.65V$ to $1.95V$	6.2	-	-	ns
			$V_{CC}=2.3V$ to $2.7V$	2.7	-	-	ns
			$V_{CC}=2.7V$	2.7	-	-	ns
recovery time	t_{rec}	$\bar{S}D$ or $\bar{R}D$; see Figure 6	$V_{CC}=3.0V$ to $3.6V$	2.7	-	-	ns
			$V_{CC}=4.5V$ to $5.5V$	2.0	-	-	ns
			$V_{CC}=1.65V$ to $1.95V$	1.9	-	-	ns
			$V_{CC}=2.3V$ to $2.7V$	1.4	-	-	ns
			$V_{CC}=2.7V$	1.3	-	-	ns
set-up time	t_{su}	D to CP; see Figure 5	$V_{CC}=3.0V$ to $3.6V$	+1.2	-	-	ns
			$V_{CC}=4.5V$ to $5.5V$	1.0	-	-	ns
			$V_{CC}=1.65V$ to $1.95V$	2.9	-	-	ns
			$V_{CC}=2.3V$ to $2.7V$	1.7	-	-	ns
			$V_{CC}=2.7V$	1.7	-	-	ns
hold time	t_h	D to CP; see Figure 5	$V_{CC}=3.0V$ to $3.6V$	1.3	-	-	ns
			$V_{CC}=4.5V$ to $5.5V$	1.1	-	-	ns
			$V_{CC}=1.65V$ to $1.95V$	1.5	-	-	ns
			$V_{CC}=2.3V$ to $2.7V$	1.0	-	-	ns
			$V_{CC}=2.7V$	1.0	-	-	ns
maximum frequency	f_{max}	CP; see Figure 5	$V_{CC}=3.0V$ to $3.6V$	175	-	-	MHz
			$V_{CC}=4.5V$ to $5.5V$	200	-	-	MHz
			$V_{CC}=1.65V$ to $1.95V$	80	-	-	MHz
			$V_{CC}=2.3V$ to $2.7V$	175	-	-	MHz
			$V_{CC}=2.7V$	175	-	-	MHz

4、Testing Circuit

4.1、AC Testing Circuit




Figure 4. Test circuit for measuring switching times

Definitions for test circuit:

R_L =Load resistance.

C_L =Load capacitance including jig and probe capacitance.

R_T =Termination resistance; should be equal to the output impedance Z_o of the pulse generator.

V_{EXT} =External voltage for measuring switching times.

4.2、AC Testing Waveforms




Figure 5. The clock input (CP) to output (Q, \bar{Q}) propagation delays, the clock pulse width, the D to CP set-up, the CP to D hold times and the maximum frequency





Figure 6. The set ($\bar{S}D$) and reset ($\bar{R}D$) input to output (Q , \bar{Q}) propagation delays, the set and reset pulse widths and the $\bar{R}D$ to CP recovery time

4.3、 Measurement Points

Supply voltage	Input	Output
V_{CC}	V_M	V_M
1.65V to 1.95V	$0.5 \times V_{CC}$	$0.5 \times V_{CC}$
2.3V to 2.7V	$0.5 \times V_{CC}$	$0.5 \times V_{CC}$
2.7V	1.5V	1.5V
3.0V to 3.6V	1.5V	1.5V
4.5V to 5.5V	$0.5 \times V_{CC}$	$0.5 \times V_{CC}$

4.4、 Test Data


Supply voltage	Input		Load		V_{EXT}		
	V_I	$t_r = t_f$	C_L	R_L	t_{PLH} , t_{PHL}	t_{PZH} , t_{PHZ}	t_{PZL} , t_{PLZ}
1.65V to 1.95V	V_{CC}	$\leq 3ns$	30pF	1k Ω	open	GND	$2 \times V_{CC}$
2.3V to 2.7V	V_{CC}	$\leq 3ns$	30pF	500 Ω	open	GND	$2 \times V_{CC}$
2.7V	2.7V	$\leq 3ns$	50pF	500 Ω	open	GND	6V
3.0V to 3.6V	2.7V	$\leq 3ns$	50pF	500 Ω	open	GND	6V
4.5V to 5.5V	V_{CC}	$\leq 3ns$	50pF	500 Ω	open	GND	$2 \times V_{CC}$

5、Package Information
5.1、TSSOP8


2023/12/A	Dimensions In Millimeters	
Symbol	Min	Max
A	—	1.10
A1	0	0.15
A2	0.75	0.95
A3	0.25	
bp	0.22	0.38
c	0.08	0.18
D	2.90	3.10
E	2.90	3.10
HE	3.90	4.10
L	0.50	
Lp	0.33	0.47
e	0.65	
Z	0.35	0.70
θ	0°	8°

Note: The package dimensions do not include flash and burrs, and the dimensions of flash and burrs shall not exceed 0.15mm.


5.2、VSSOP8


 NOTES
 1.0 COP
 DIE ATTA
 2.0 DE

2023/12/A	Dimensions In Millimeters	
	Symbol	Min
A	—	1.00
A1	0.00	0.15
A2	0.60	0.85
A3	0.12	
Q	0.19	0.21
b	0.17	0.27
c	0.08	0.23
D	1.90	2.10
E	2.20	2.40
HE	3.00	3.20
HE1	3.00	3.40
e	0.50	
L	0.40	
L1	0.15	0.40
Y	0.10	
Z	0.10	0.40
θ	0°	8°

Note: The package dimensions do not include flash and burrs, and the dimensions of flash and burrs shall not exceed 0.15mm.


5.3、SOP8



2023/12/A Symbol	Dimensions In Millimeters	
	Min.	Max.
A	1.35	1.80
A1	0.05	0.25
A2	1.25	1.55
D	4.70	5.10
E	5.80	6.30
E1	3.70	4.10
b	0.306	0.51
c	0.19	0.25
e	1.27	
L	0.40	0.89
θ	0°	8°


Note: The package dimensions do not include flash and burrs, and the dimensions of flash and burrs shall not exceed 0.15mm.

5.4、XSON8 (1*1.35*0.32)-0.35



2023/12/A	Dimensions In Millimeters	
Symbol	Min	Max
A	0.28	0.32
A1	0.00	0.05
A3	0.10	
b	0.11	0.21
D	1.35	
E	1.00	
e	0.35	
L	0.25	0.35
L1	0.275	0.475
L2	0.30	0.40
L3	0.325	0.525

Note: The package dimensions do not include flash and burrs, and the dimensions of flash and burrs shall not exceed 0.15mm.

5.5、XSON8 (1*1.95*0.5)-0.5


2023/12/A	Dimensions In Millimeters	
Symbol	Min	Max
A	0.45	0.55
A1	0	0.05
A3	0.127	
b	0.15	0.25
D	1.95	
E	1.00	
e	0.50	
L	0.25	0.35
L1	0.25	0.45
L2	0.30	0.40
L3	0.30	0.50

Note: The package dimensions do not include flash and burrs, and the dimensions of flash and burrs shall not exceed 0.15mm.

6、Statements And Notes
6.1、The name and content of Hazardous substances or Elements in the product

Part name	Hazardous substances or Elements									
	Lead and lead compounds	Mercury and mercury compounds	Cadmium and cadmium compounds	Hexavalent chromium compounds	Polybrominated biphenyls	Polybrominated biphenyl ethers	Dibutyl phthalate	Butylbenzyl phthalate	Di-2-ethylhexyl phthalate	Diisobutyl phthalate
Lead frame	○	○	○	○	○	○	○	○	○	○
Plastic resin	○	○	○	○	○	○	○	○	○	○
Chip	○	○	○	○	○	○	○	○	○	○
The lead	○	○	○	○	○	○	○	○	○	○
Plastic sheet installed	○	○	○	○	○	○	○	○	○	○
explanation	○: Indicates that the content of hazardous substances or elements in the detection limit of the following the SJ/T11363-2006 standard. ×: Indicates that the content of hazardous substances or elements exceeding the SJ/T11363-2006 Standard limit requirements.									

Revision History

Rev.	Change	Date
V1.0	Initial version	2/23/2024

Important Notice

JSMSEMI Semiconductor (JSMSEMI) PRODUCTS ARE NEITHER DESIGNED NOR INTENDED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS UNLESS THE SPECIFIC JSMSEMI PRODUCTS ARE SPECIFICALLY DESIGNATED BY JSMSEMI FOR SUCH USE. BUYERS ACKNOWLEDGE AND AGREE THAT ANY SUCH USE OF JSMSEMI PRODUCTS WHICH JSMSEMI HAS NOT DESIGNATED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS IS SOLELY AT THE BUYER' S RISK.

JSMSEMI assumes no liability for application assistance or customer product design. Customers are responsible for their products and applications using JSMSEMI products.

Resale of JSMSEMI products or services with statements diferent from or beyond the parameters stated by JSMSEMI for that product or service voids all express and any implied warranties for the associated JSMSEMI product or s ervice. JSMSEMI is not responsible or liable for any such statements.

JSMSEMI All Rights Reserved. Information and data in this document are owned by JSMSEMI wholly and may not be edited, reproduced, or redistributed in any way without the express written consent from JSMSEMI.

Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the JSMSEMI product that you intend to use.

For additional information please contact Kevin@jsmsemi.com or visit www.jsmsemi.com