

## Single Supply Translating Buffer/Line Driver: 3-state

# CJ74LV1T125 Logic

## 1 Introduction

The CJ74LV1T125 is a single, level translating buffer/line driver with 3-state output. The low threshold inputs support 1.8V input logic at  $V_{CC}=3.3V$  and can be used in 1.8V to 3.3V level up translation. In addition, the 5V tolerant input pins enable down translation (3.3V to 2.5V output at  $V_{CC}=2.5V$ ). The 3-state output is controlled by the output enable input (/OE). A HIGH-level at /OE causes the output to assume a high-impedance OFF-state. The output level is referenced to the supply voltage and supports 1.8V, 2.5V, 3.3V and 5.0V CMOS levels. The wide  $V_{CC}$  range permits the generation of output levels to connect to controllers or processors.

## 2 Available Packages

| PART NUMBER | PACKAGE   |
|-------------|-----------|
| CJ74LV1T125 | SOT-23-5L |
|             | SOT-353   |


**Note:** For all available packages, please refer to the part Orderable Information.

## 3 Features

- Single supply voltage translator at 1.8V, 2.5V, 3.3V and 5.0V
- Up translation
  - 1.2V to 1.8V at  $V_{CC}=1.8V$
  - 1.5V to 2.5V at  $V_{CC}=2.5V$
  - 1.8V to 3.3V at  $V_{CC}=3.3V$
  - 3.3V to 5.0V at  $V_{CC}=5.0V$
- Down translation
  - 3.3V to 1.8V at  $V_{CC}=1.8V$
  - 3.3V to 2.5V at  $V_{CC}=2.5V$
  - 5.0V to 3.3V at  $V_{CC}=3.3V$
- 5V tolerant inputs
- Specified from  $-40^{\circ}C$  to  $+125^{\circ}C$

## 4 Applications

- Telecom
- Portable applications
- Servers
- PC and notebooks



Logic diagram

## 5 Orderable Information

| DEVICE         | PACKAGE   | OP TEMP   | ECO PLAN     | MSL              | PACKING OPTION                     | SORT   |
|----------------|-----------|-----------|--------------|------------------|------------------------------------|--------|
| CJ74LV1T125M5N | SOT-23-5L | -40~125°C | RoHS & Green | Level 3<br>168HR | Tape and Reel<br>3000 Units / Reel | Active |
| CJ74LV1T125R5N | SOT-353   | -40~125°C | RoHS & Green | Level 3<br>168HR | Tape and Reel<br>3000 Units / Reel | Active |

**Note:**

**ECO PLAN:** For the RoHS and Green certification standards of this product, please refer to the official report provided by JSCJ.

**MSL:** Moisture Sensitivity Level. Determined according to JEDEC industry standard classification.

**SORT:** Specifically defined as follows:

Active: Recommended for new products;

Customized: Products manufactured to meet the specific needs of customers;

Preview: The device has been released and has not been fully mass produced. The sample may or may not be available;

NoRD: It is not recommended to use the device for new design. The device is only produced for the needs of existing customers;

Obsolete: The device has been discontinued.

## 6 Pin Configuration and Marking Information

### 6.1 Pin Configuration





Figure 6-1 Pin configuration

### 6.2 Pin Function

| PIN |                 | I/O <sup>(1)</sup> | DESCRIPTION         |
|-----|-----------------|--------------------|---------------------|
| No. | NAME            |                    |                     |
| 1   | $\overline{OE}$ | I                  | Output enable input |
| 2   | A               | I                  | Data input          |
| 3   | GND             | G                  | Ground (0V)         |
| 4   | Y               | O                  | Data output         |
| 5   | VCC             | P                  | Supply voltage      |

(1) I-Input, O-Output, P-Power, G-Ground

### 6.3 Marking Information



XXXX or XX: Code, indicates weekly record information.

## 7 Specifications

### 7.1 Absolute Maximum Ratings

Voltages are referenced to GND (ground=0V), unless otherwise specified.

| SYMBOL    | PARAMETER               | CONDITIONS                                  | MIN. | MAX.         | UNIT |
|-----------|-------------------------|---------------------------------------------|------|--------------|------|
| $V_{CC}$  | Supply voltage          | -                                           | -0.5 | +7.0         | V    |
| $V_I$     | Input voltage           | -                                           | -0.5 | +7.0         | V    |
| $V_O$     | Output voltage          | Output HIGH or LOW state                    | -0.5 | $V_{CC}+0.5$ | V    |
|           |                         | Output in 3-state or power-off state        | -0.5 | 4.6          | V    |
| $I_{IK}$  | Input clamping current  | $V_I < 0V$                                  | -20  | -            | mA   |
| $I_{OK}$  | Output clamping current | $V_O < 0V$ or $V_O > V_{CC}$                | -    | $\pm 20$     | mA   |
| $I_O$     | Output current          | $V_O = 0V$ to $V_{CC}$                      | -    | $\pm 25$     | mA   |
| $I_{CC}$  | Supply current          | -                                           | -    | 50           | mA   |
| $I_{GND}$ | Ground current          | -                                           | -50  | -            | mA   |
| $T_{stg}$ | Storage temperature     | -                                           | -65  | +150         | °C   |
| $P_{tot}$ | Total power dissipation | $T_{amb} = -40^{\circ}C$ to $+125^{\circ}C$ | -    | 250          | mW   |
| $T_L$     | Soldering temperature   | 10s                                         | -    | 260          | °C   |

**Note:** Absolute maximum ratings indicate sustained limits beyond which damage to the device may occur. All voltage parameters are absolute voltages referenced to GND. The thermal resistance and power dissipation ratings are measured under board mounted and still air conditions.

### 7.2 Recommended Operating Conditions

| SYMBOL              | PARAMETER                           | CONDITIONS                | MIN. | TYP. | MAX.     | UNIT |
|---------------------|-------------------------------------|---------------------------|------|------|----------|------|
| $V_{CC}$            | Supply voltage                      | -                         | 1.6  | 5.0  | 5.5      | V    |
| $V_I$               | Input voltage                       | -                         | 0    | -    | 5.5      | V    |
| $V_O$               | Output voltage                      | Output HIGH or LOW state  | 0    | -    | $V_{CC}$ | V    |
| $T_{amb}$           | Ambient temperature                 | -                         | -40  | -    | +125     | °C   |
| $\Delta t/\Delta V$ | Input transition rise and fall rate | $V_{CC} = 1.8V$ to $5.0V$ | -    | -    | 20       | ns/V |

### 7.3 ESD Ratings

| SYMBOL        | ESD RATINGS             |                                       | VALUE      | UNIT |
|---------------|-------------------------|---------------------------------------|------------|------|
| $V_{ESD-HBM}$ | Electrostatic discharge | Human body model (HBM) <sup>(1)</sup> | $\pm 2000$ | V    |

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

## 7.4 Electrical Characteristics

### 7.4.1 DC Characteristics 1

$T_{amb}=25^{\circ}\text{C}$ , voltages are referenced to GND (ground=0V), unless otherwise specified.

| SYMBOL   | PARAMETER                 | CONDITIONS                                                           |                                                          | MIN.         | TYP. | MAX.    | UNIT          |
|----------|---------------------------|----------------------------------------------------------------------|----------------------------------------------------------|--------------|------|---------|---------------|
| $V_{IH}$ | HIGH-level input voltage  | $V_{CC}=1.65\text{V to }1.8\text{V}$                                 |                                                          | 0.94         | -    | -       | V             |
|          |                           | $V_{CC}=2.0\text{V}$                                                 |                                                          | 0.99         | -    | -       | V             |
|          |                           | $V_{CC}=2.25\text{V to }2.5\text{V}$                                 |                                                          | 1.135        | -    | -       | V             |
|          |                           | $V_{CC}=2.75\text{V}$                                                |                                                          | 1.21         | -    | -       | V             |
|          |                           | $V_{CC}=3.0\text{V to }3.3\text{V}$                                  |                                                          | 1.35         | -    | -       | V             |
|          |                           | $V_{CC}=3.6\text{V}$                                                 |                                                          | 1.47         | -    | -       | V             |
|          |                           | $V_{CC}=4.5\text{V to }5.0\text{V}$                                  |                                                          | 2.02         | -    | -       | V             |
|          |                           | $V_{CC}=5.5\text{V}$                                                 |                                                          | 2.10         | -    | -       | V             |
| $V_{IL}$ | LOW-level input voltage   | $V_{CC}=1.65\text{V to }2.0\text{V}$                                 |                                                          | -            | -    | 0.58    | V             |
|          |                           | $V_{CC}=2.25\text{V to }2.75\text{V}$                                |                                                          | -            | -    | 0.75    | V             |
|          |                           | $V_{CC}=3.0\text{V to }3.6\text{V}$                                  |                                                          | -            | -    | 0.80    | V             |
|          |                           | $V_{CC}=4.5\text{V to }5.5\text{V}$                                  |                                                          | -            | -    | 0.80    | V             |
| $V_{OH}$ | HIGH-level output voltage | $V_I = V_{IH} \text{ or } V_{IL}$                                    | $V_{CC}=1.65\text{V to }5.5\text{V}; I_O=-20\mu\text{A}$ | $V_{CC}-0.1$ | -    | -       | V             |
|          |                           |                                                                      | $V_{CC}=1.65\text{V}; I_O=-2\text{mA}$                   | 1.28         | -    | -       | V             |
|          |                           |                                                                      | $V_{CC}=1.8\text{V}; I_O=-2\text{mA}$                    | 1.5          | -    | -       | V             |
|          |                           |                                                                      | $V_{CC}=2.3\text{V}; I_O=-2.3\text{mA}$                  | 2.0          | -    | -       | V             |
|          |                           |                                                                      | $V_{CC}=2.3\text{V}; I_O=-3\text{mA}$                    | 2.0          | -    | -       | V             |
|          |                           |                                                                      | $V_{CC}=2.5\text{V}; I_O=-3\text{mA}$                    | 2.25         | -    | -       | V             |
|          |                           |                                                                      | $V_{CC}=3.0\text{V}; I_O=-3\text{mA}$                    | 2.78         | -    | -       | V             |
|          |                           |                                                                      | $V_{CC}=3.0\text{V}; I_O=-5.5\text{mA}$                  | 2.6          | -    | -       | V             |
|          |                           |                                                                      | $V_{CC}=3.3\text{V}; I_O=-5.5\text{mA}$                  | 2.9          | -    | -       | V             |
|          |                           |                                                                      | $V_{CC}=4.5\text{V}; I_O=-4\text{mA}$                    | 4.2          | -    | -       | V             |
|          |                           |                                                                      | $V_{CC}=4.5\text{V}; I_O=-8\text{mA}$                    | 4.1          | -    | -       | V             |
|          |                           |                                                                      | $V_{CC}=5.0\text{V}; I_O=-8\text{mA}$                    | 4.6          | -    | -       | V             |
| $V_{OL}$ | LOW-level output voltage  | $V_I = V_{IH} \text{ or } V_{IL}$                                    | $V_{CC}=1.65\text{V to }5.5\text{V}; I_O=20\mu\text{A}$  | -            | -    | 0.1     | V             |
|          |                           |                                                                      | $V_{CC}=1.65\text{V}; I_O=2\text{mA}$                    | -            | -    | 0.2     | V             |
|          |                           |                                                                      | $V_{CC}=2.3\text{V}; I_O=2.3\text{mA}$                   | -            | -    | 0.1     | V             |
|          |                           |                                                                      | $V_{CC}=2.3\text{V}; I_O=3\text{mA}$                     | -            | -    | 0.15    | V             |
|          |                           |                                                                      | $V_{CC}=3.0\text{V}; I_O=3\text{mA}$                     | -            | -    | 0.1     | V             |
|          |                           |                                                                      | $V_{CC}=3.0\text{V}; I_O=5.5\text{mA}$                   | -            | -    | 0.2     | V             |
|          |                           |                                                                      | $V_{CC}=4.5\text{V}; I_O=4\text{mA}$                     | -            | -    | 0.15    | V             |
|          |                           |                                                                      | $V_{CC}=4.5\text{V}; I_O=8\text{mA}$                     | -            | -    | 0.3     | V             |
| $I_I$    | Input leakage current     | $V_I=V_{CC} \text{ or } \text{GND}; V_{CC}=0\text{V to }5.5\text{V}$ |                                                          | -            | -    | $\pm 1$ | $\mu\text{A}$ |
| $I_{OZ}$ | OFF-state output current  | -                                                                    |                                                          | -            | -    | $\pm 1$ | $\mu\text{A}$ |

|                 |                           |                                                                                                            |   |   |      |         |
|-----------------|---------------------------|------------------------------------------------------------------------------------------------------------|---|---|------|---------|
| $I_{CC}$        | Supply current            | $V_I = V_{CC}$ or GND; $I_O = 0A$ ;<br>$V_{CC} = 1.8V, 2.5V, 3.3V, 5.0V$                                   | - | - | 1    | $\mu A$ |
| $\Delta I_{CC}$ | Additional supply current | Per input pin; $V_{CC} = 1.8V$ ;<br>$V_I = 0.3V$ or $1.1V$ ; $I_O = 0A$ ;<br>Other pins at $V_{CC}$ or GND | - | - | 10   | $\mu A$ |
|                 |                           | Per input pin; $V_{CC} = 5.5V$ ;<br>$V_I = 0.3V$ or $3.4V$ ; $I_O = 0A$ ;<br>Other pins at $V_{CC}$ or GND | - | - | 1.35 | mA      |

#### 7.4.2 DC Characteristics 2

$T_{amb} = -40^{\circ}C$  to  $+85^{\circ}C$ , voltages are referenced to GND (ground=0V), unless otherwise specified.

| SYMBOL   | PARAMETER                 | CONDITIONS                  |                                                  | MIN.           | TYP. | MAX. | UNIT |
|----------|---------------------------|-----------------------------|--------------------------------------------------|----------------|------|------|------|
| $V_{IH}$ | HIGH-level input voltage  | $V_{CC} = 1.65V$ to $1.8V$  |                                                  | 1.0            | -    | -    | V    |
|          |                           | $V_{CC} = 2.0V$             |                                                  | 1.03           | -    | -    | V    |
|          |                           | $V_{CC} = 2.25V$ to $2.5V$  |                                                  | 1.18           | -    | -    | V    |
|          |                           | $V_{CC} = 2.75V$            |                                                  | 1.23           | -    | -    | V    |
|          |                           | $V_{CC} = 3.0V$ to $3.3V$   |                                                  | 1.37           | -    | -    | V    |
|          |                           | $V_{CC} = 3.6V$             |                                                  | 1.48           | -    | -    | V    |
|          |                           | $V_{CC} = 4.5V$ to $5.0V$   |                                                  | 2.03           | -    | -    | V    |
|          |                           | $V_{CC} = 5.5V$             |                                                  | 2.11           | -    | -    | V    |
| $V_{IL}$ | LOW-level input voltage   | $V_{CC} = 1.65V$ to $2.0V$  |                                                  | -              | -    | 0.55 | V    |
|          |                           | $V_{CC} = 2.25V$ to $2.75V$ |                                                  | -              | -    | 0.71 | V    |
|          |                           | $V_{CC} = 3.0V$ to $3.6V$   |                                                  | -              | -    | 0.65 | V    |
|          |                           | $V_{CC} = 4.5V$ to $5.5V$   |                                                  | -              | -    | 0.80 | V    |
| $V_{OH}$ | HIGH-level output voltage | $V_I = V_{IH}$ or $V_{IL}$  | $V_{CC} = 1.65V$ to $5.5V$ ;<br>$I_O = -20\mu A$ | $V_{CC} - 0.1$ | -    | -    | V    |
|          |                           |                             | $V_{CC} = 1.65V$ ; $I_O = -2mA$                  | 1.21           | -    | -    | V    |
|          |                           |                             | $V_{CC} = 1.8V$ ; $I_O = -2mA$                   | 1.45           | -    | -    | V    |
|          |                           |                             | $V_{CC} = 2.3V$ ; $I_O = -2.3mA$                 | 2.0            | -    | -    | V    |
|          |                           |                             | $V_{CC} = 2.3V$ ; $I_O = -3mA$                   | 1.93           | -    | -    | V    |
|          |                           |                             | $V_{CC} = 2.5V$ ; $I_O = -3mA$                   | 2.15           | -    | -    | V    |
|          |                           |                             | $V_{CC} = 3.0V$ ; $I_O = -3mA$                   | 2.7            | -    | -    | V    |
|          |                           |                             | $V_{CC} = 3.0V$ ; $I_O = -5.5mA$                 | 2.49           | -    | -    | V    |
|          |                           |                             | $V_{CC} = 3.3V$ ; $I_O = -5.5mA$                 | 2.8            | -    | -    | V    |
|          |                           |                             | $V_{CC} = 4.5V$ ; $I_O = -4mA$                   | 4.1            | -    | -    | V    |
|          |                           |                             | $V_{CC} = 4.5V$ ; $I_O = -8mA$                   | 3.95           | -    | -    | V    |
|          |                           |                             | $V_{CC} = 5.0V$ ; $I_O = -8mA$                   | 4.5            | -    | -    | V    |
| $V_{OL}$ | LOW-level output voltage  | $V_I = V_{IH}$ or $V_{IL}$  | $V_{CC} = 1.65V$ to $5.5V$ ;<br>$I_O = 20\mu A$  | -              | -    | 0.1  | V    |
|          |                           |                             | $V_{CC} = 1.65V$ ; $I_O = 2mA$                   | -              | -    | 0.25 | V    |
|          |                           |                             | $V_{CC} = 2.3V$ ; $I_O = 2.3mA$                  | -              | -    | 0.15 | V    |
|          |                           |                             | $V_{CC} = 2.3V$ ; $I_O = 3mA$                    | -              | -    | 0.2  | V    |
|          |                           |                             | $V_{CC} = 3.0V$ ; $I_O = 3mA$                    | -              | -    | 0.15 | V    |

|                 |                           |                                                                                                   |                          |   |   |           |         |
|-----------------|---------------------------|---------------------------------------------------------------------------------------------------|--------------------------|---|---|-----------|---------|
|                 |                           |                                                                                                   | $V_{CC}=3.0V; I_O=5.5mA$ | - | - | 0.252     | V       |
|                 |                           |                                                                                                   | $V_{CC}=4.5V; I_O=4mA$   | - | - | 0.2       | V       |
|                 |                           |                                                                                                   | $V_{CC}=4.5V; I_O=8mA$   | - | - | 0.35      | V       |
| $I_I$           | Input leakage current     | $V_I=V_{CC}$ or GND; $V_{CC}=0V$ to 5.5V                                                          |                          | - | - | $\pm 1$   | $\mu A$ |
| $I_{OZ}$        | OFF-state output current  | -                                                                                                 |                          | - | - | $\pm 2.5$ | $\mu A$ |
| $I_{CC}$        | Supply current            | $V_I=V_{CC}$ or GND; $I_O=0A$ ;<br>$V_{CC}=1.8V, 2.5V, 3.3V, 5.0V$                                |                          | - | - | 10        | $\mu A$ |
| $\Delta I_{CC}$ | Additional supply current | Per input pin; $V_{CC}=1.8V$ ;<br>$V_I=0.3V$ or 1.1V; $I_O=0A$ ;<br>Other pins at $V_{CC}$ or GND |                          | - | - | 10        | $\mu A$ |
|                 |                           | Per input pin; $V_{CC}=5.5V$ ;<br>$V_I=0.3V$ or 3.4V; $I_O=0A$ ;<br>Other pins at $V_{CC}$ or GND |                          | - | - | 1.5       | mA      |

### 7.4.3 DC Characteristics 3

$T_{amb}=-40^{\circ}C$  to  $+125^{\circ}C$ , voltages are referenced to GND (ground=0V), unless otherwise specified.

| SYMBOL   | PARAMETER                 | CONDITIONS                 |                                           | MIN.         | TYP. | MAX. | UNIT |
|----------|---------------------------|----------------------------|-------------------------------------------|--------------|------|------|------|
| $V_{IH}$ | HIGH-level input voltage  | $V_{CC}=1.65V$ to 1.8V     |                                           | 1.0          | -    | -    | V    |
|          |                           | $V_{CC}=2.0V$              |                                           | 1.03         | -    | -    | V    |
|          |                           | $V_{CC}=2.25V$ to 2.5V     |                                           | 1.18         | -    | -    | V    |
|          |                           | $V_{CC}=2.75V$             |                                           | 1.23         | -    | -    | V    |
|          |                           | $V_{CC}=3.0V$ to 3.3V      |                                           | 1.37         | -    | -    | V    |
|          |                           | $V_{CC}=3.6V$              |                                           | 1.48         | -    | -    | V    |
|          |                           | $V_{CC}=4.5V$ to 5.0V      |                                           | 2.03         | -    | -    | V    |
|          |                           | $V_{CC}=5.5V$              |                                           | 2.11         | -    | -    | V    |
| $V_{IL}$ | LOW-level input voltage   | $V_{CC}=1.65V$ to 2.0V     |                                           | -            | -    | 0.55 | V    |
|          |                           | $V_{CC}=2.25V$ to 2.75V    |                                           | -            | -    | 0.71 | V    |
|          |                           | $V_{CC}=3.0V$ to 3.6V      |                                           | -            | -    | 0.65 | V    |
|          |                           | $V_{CC}=4.5V$ to 5.5V      |                                           | -            | -    | 0.80 | V    |
| $V_{OH}$ | HIGH-level output voltage | $V_I = V_{IH}$ or $V_{IL}$ | $V_{CC}=1.65V$ to 5.5V;<br>$I_O=-20\mu A$ | $V_{CC}-0.1$ | -    | -    | V    |
|          |                           |                            | $V_{CC}=1.65V; I_O=-2mA$                  | 1.21         | -    | -    | V    |
|          |                           |                            | $V_{CC}=1.8V; I_O=-2mA$                   | 1.45         | -    | -    | V    |
|          |                           |                            | $V_{CC}=2.3V; I_O=-2.3mA$                 | 2.0          | -    | -    | V    |
|          |                           |                            | $V_{CC}=2.3V; I_O=-3mA$                   | 1.93         | -    | -    | V    |
|          |                           |                            | $V_{CC}=2.5V; I_O=-3mA$                   | 2.15         | -    | -    | V    |
|          |                           |                            | $V_{CC}=3.0V; I_O=-3mA$                   | 2.7          | -    | -    | V    |
|          |                           |                            | $V_{CC}=3.0V; I_O=-5.5mA$                 | 2.49         | -    | -    | V    |
|          |                           |                            | $V_{CC}=3.3V; I_O=-5.5mA$                 | 2.8          | -    | -    | V    |
|          |                           |                            | $V_{CC}=4.5V; I_O=-4mA$                   | 4.1          | -    | -    | V    |
|          |                           |                            | $V_{CC}=4.5V; I_O=-8mA$                   | 3.95         | -    | -    | V    |
|          |                           |                            | $V_{CC}=5.0V; I_O=-8mA$                   | 4.5          | -    | -    | V    |

|                  |                           |                                                                                                                                    |                                                         |   |   |       |    |
|------------------|---------------------------|------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------|---|---|-------|----|
| V <sub>OL</sub>  | LOW-level output voltage  | V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>                                                                                | V <sub>CC</sub> =1.65V to 5.5V;<br>I <sub>O</sub> =20uA | - | - | 0.1   | V  |
|                  |                           |                                                                                                                                    | V <sub>CC</sub> =1.65V; I <sub>O</sub> =2mA             | - | - | 0.25  | V  |
|                  |                           |                                                                                                                                    | V <sub>CC</sub> =2.3V; I <sub>O</sub> =2.3mA            | - | - | 0.15  | V  |
|                  |                           |                                                                                                                                    | V <sub>CC</sub> =2.3V; I <sub>O</sub> =3mA              | - | - | 0.2   | V  |
|                  |                           |                                                                                                                                    | V <sub>CC</sub> =3.0V; I <sub>O</sub> =3mA              | - | - | 0.15  | V  |
|                  |                           |                                                                                                                                    | V <sub>CC</sub> =3.0V; I <sub>O</sub> =5.5mA            | - | - | 0.252 | V  |
|                  |                           |                                                                                                                                    | V <sub>CC</sub> =4.5V; I <sub>O</sub> =4mA              | - | - | 0.2   | V  |
|                  |                           |                                                                                                                                    | V <sub>CC</sub> =4.5V; I <sub>O</sub> =8mA              | - | - | 0.35  | V  |
| I <sub>I</sub>   | Input leakage current     | V <sub>I</sub> =V <sub>CC</sub> or GND; V <sub>CC</sub> =0V to 5.5V                                                                |                                                         | - | - | ±1    | uA |
| I <sub>OZ</sub>  | OFF-state output current  | -                                                                                                                                  |                                                         | - | - | ±2.5  | uA |
| I <sub>CC</sub>  | Supply current            | V <sub>I</sub> =V <sub>CC</sub> or GND; I <sub>O</sub> =0A;<br>V <sub>CC</sub> =1.8V, 2.5V, 3.3V, 5.0V                             |                                                         | - | - | 10    | uA |
| ΔI <sub>CC</sub> | Additional supply current | Per input pin; V <sub>CC</sub> =1.8V;<br>V <sub>I</sub> =0.3V or 1.1V; I <sub>O</sub> =0A;<br>Other pins at V <sub>CC</sub> or GND |                                                         | - | - | 10    | uA |
|                  |                           | Per input pin; V <sub>CC</sub> =5.5V;<br>V <sub>I</sub> =0.3V or 3.4V; I <sub>O</sub> =0A;<br>Other pins at V <sub>CC</sub> or GND |                                                         | - | - | 1.5   | mA |

## 7.4.4 AC Characteristics 1

T<sub>amb</sub>=25°C, GND=0V, unless otherwise specified.

| SYMBOL           | PARAMETER                     | CONDITIONS                                                                                               |                                             | MIN. | TYP. | MAX. | UNIT |
|------------------|-------------------------------|----------------------------------------------------------------------------------------------------------|---------------------------------------------|------|------|------|------|
| t <sub>pd</sub>  | Propagation delay             | A to Y;<br>See Figure 8-5 <sup>(1)</sup>                                                                 | V <sub>CC</sub> =1.8V; C <sub>L</sub> =15pF | -    | 13   | 19.2 | ns   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =1.8V; C <sub>L</sub> =30pF | -    | 15.2 | 21.6 | ns   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =2.5V; C <sub>L</sub> =15pF | -    | 9.2  | 13.2 | ns   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =2.5V; C <sub>L</sub> =30pF | -    | 10.6 | 14.8 | ns   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =3.3V; C <sub>L</sub> =15pF | -    | 7.6  | 10.8 | ns   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =3.3V; C <sub>L</sub> =30pF | -    | 8.8  | 12   | ns   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =5.0V; C <sub>L</sub> =15pF | -    | 6.4  | 8.2  | ns   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =5.0V; C <sub>L</sub> =30pF | -    | 7.2  | 9.2  | ns   |
| t <sub>en</sub>  | Enable time                   | $\overline{\text{OE}}$ to Y;<br>See Figure 8-6 <sup>(1)</sup>                                            | V <sub>CC</sub> =1.8V; C <sub>L</sub> =15pF | -    | 15.6 | 21.4 | ns   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =1.8V; C <sub>L</sub> =30pF | -    | 18   | 25.2 | ns   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =2.5V; C <sub>L</sub> =15pF | -    | 11   | 14.2 | ns   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =2.5V; C <sub>L</sub> =30pF | -    | 12.6 | 16.6 | ns   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =3.3V; C <sub>L</sub> =15pF | -    | 9    | 11.2 | ns   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =3.3V; C <sub>L</sub> =30pF | -    | 10.2 | 12.8 | ns   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =5.0V; C <sub>L</sub> =15pF | -    | 6.4  | 8.2  | ns   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =5.0V; C <sub>L</sub> =30pF | -    | 7.4  | 9.4  | ns   |
| t <sub>dis</sub> | Disable time                  | $\overline{\text{OE}}$ to Y;<br>See Figure 8-6 <sup>(1)</sup>                                            | V <sub>CC</sub> =1.8V; C <sub>L</sub> =15pF | -    | 15.2 | 19.4 | ns   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =1.8V; C <sub>L</sub> =30pF | -    | 21   | 25.8 | ns   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =2.5V; C <sub>L</sub> =15pF | -    | 11   | 14   | ns   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =2.5V; C <sub>L</sub> =30pF | -    | 14.8 | 18   | ns   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =3.3V; C <sub>L</sub> =15pF | -    | 9    | 11.6 | ns   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =3.3V; C <sub>L</sub> =30pF | -    | 11.8 | 15   | ns   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =5.0V; C <sub>L</sub> =15pF | -    | 8    | 11   | ns   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =5.0V; C <sub>L</sub> =30pF | -    | 10   | 13   | ns   |
| C <sub>I</sub>   | Input capacitance             | V <sub>I</sub> =V <sub>CC</sub> or GND; V <sub>CC</sub> =3.3V                                            |                                             | -    | 1.5  | 10   | pF   |
| C <sub>O</sub>   | Output capacitance            | V <sub>O</sub> =V <sub>CC</sub> or GND; V <sub>CC</sub> =3.3V                                            |                                             | -    | 2.5  | -    | pF   |
| C <sub>PD</sub>  | Power dissipation capacitance | Per buffer;<br>V <sub>I</sub> =GND to V <sub>CC</sub> ;<br>C <sub>L</sub> =30 pF; f=10MHz <sup>(2)</sup> | V <sub>CC</sub> =1.8V                       | -    | 4.1  | -    | pF   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =2.5V                       | -    | 5.3  | -    | pF   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =3.3V                       | -    | 6.9  | -    | pF   |
|                  |                               |                                                                                                          | V <sub>CC</sub> =5.0V                       | -    | 10.7 | -    | pF   |

(1) t<sub>pd</sub> is the same as t<sub>PLH</sub> and t<sub>PHL</sub>. t<sub>en</sub> is the same as t<sub>PZL</sub> and t<sub>PZH</sub>. t<sub>dis</sub> is the same as t<sub>PLZ</sub> and t<sub>PHZ</sub>.(2) C<sub>PD</sub> is used to determine the dynamic power dissipation (P<sub>D</sub> in uW).P<sub>D</sub>=(C<sub>PD</sub>XV<sub>CC</sub><sup>2</sup>Xf<sub>i</sub>XN)+Σ(C<sub>L</sub>XV<sub>CC</sub><sup>2</sup>Xf<sub>o</sub>) where:f<sub>i</sub>=input frequency in MHz; f<sub>o</sub>=output frequency in MHz;C<sub>L</sub>=output load capacitance in pF; V<sub>CC</sub>=supply voltage in V;N=number of inputs switching; Σ(C<sub>L</sub>XV<sub>CC</sub><sup>2</sup>Xf<sub>o</sub>)=sum of the outputs.

## 7.4.5 AC Characteristics 2

$T_{amb} = -40^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$ ,  $\text{GND} = 0\text{V}$ , unless otherwise specified.

| SYMBOL           | PARAMETER         | CONDITIONS                                                    |                                             | MIN. | TYP. | MAX. | UNIT |
|------------------|-------------------|---------------------------------------------------------------|---------------------------------------------|------|------|------|------|
| t <sub>pd</sub>  | Propagation delay | A to Y;<br>See Figure 8-5 <sup>(1)</sup>                      | V <sub>CC</sub> =1.8V; C <sub>L</sub> =15pF | -    | -    | 21.6 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =1.8V; C <sub>L</sub> =30pF | -    | -    | 24.4 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =2.5V; C <sub>L</sub> =15pF | -    | -    | 15   | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =2.5V; C <sub>L</sub> =30pF | -    | -    | 16.8 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =3.3V; C <sub>L</sub> =15pF | -    | -    | 12   | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =3.3V; C <sub>L</sub> =30pF | -    | -    | 13.6 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =5.0V; C <sub>L</sub> =15pF | -    | -    | 8.8  | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =5.0V; C <sub>L</sub> =30pF | -    | -    | 10.2 | ns   |
| t <sub>en</sub>  | Enable time       | $\overline{\text{OE}}$ to Y;<br>See Figure 8-6 <sup>(1)</sup> | V <sub>CC</sub> =1.8V; C <sub>L</sub> =15pF | -    | -    | 24.2 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =1.8V; C <sub>L</sub> =30pF | -    | -    | 28.6 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =2.5V; C <sub>L</sub> =15pF | -    | -    | 16   | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =2.5V; C <sub>L</sub> =30pF | -    | -    | 18.6 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =3.3V; C <sub>L</sub> =15pF | -    | -    | 12.6 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =3.3V; C <sub>L</sub> =30pF | -    | -    | 14.4 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =5.0V; C <sub>L</sub> =15pF | -    | -    | 9.2  | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =5.0V; C <sub>L</sub> =30pF | -    | -    | 10.6 | ns   |
| t <sub>dis</sub> | Disable time      | $\overline{\text{OE}}$ to Y;<br>See Figure 8-6 <sup>(1)</sup> | V <sub>CC</sub> =1.8V; C <sub>L</sub> =15pF | -    | -    | 21.4 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =1.8V; C <sub>L</sub> =30pF | -    | -    | 28   | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =2.5V; C <sub>L</sub> =15pF | -    | -    | 15.4 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =2.5V; C <sub>L</sub> =30pF | -    | -    | 20   | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =3.3V; C <sub>L</sub> =15pF | -    | -    | 12.8 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =3.3V; C <sub>L</sub> =30pF | -    | -    | 16.2 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =5.0V; C <sub>L</sub> =15pF | -    | -    | 11.8 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =5.0V; C <sub>L</sub> =30pF | -    | -    | 13.8 | ns   |
| C <sub>i</sub>   | Input capacitance | V <sub>I</sub> =V <sub>CC</sub> or GND; V <sub>CC</sub> =3.3V |                                             | -    | -    | 10   | pF   |

(1)  $t_{pd}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ .  $t_{en}$  is the same as  $t_{PZL}$  and  $t_{PZH}$ .  $t_{dis}$  is the same as  $t_{PLZ}$  and  $t_{PHZ}$ .

## 7.4.6 AC Characteristics 3

$T_{amb} = -40^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$ ,  $\text{GND} = 0\text{V}$ , unless otherwise specified.

| SYMBOL           | PARAMETER         | CONDITIONS                                                    |                                             | MIN. | TYP. | MAX. | UNIT |
|------------------|-------------------|---------------------------------------------------------------|---------------------------------------------|------|------|------|------|
| t <sub>pd</sub>  | Propagation delay | A to Y;<br>See Figure 8-5 <sup>(1)</sup>                      | V <sub>CC</sub> =1.8V; C <sub>L</sub> =15pF | -    | -    | 23.2 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =1.8V; C <sub>L</sub> =30pF | -    | -    | 26.2 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =2.5V; C <sub>L</sub> =15pF | -    | -    | 16   | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =2.5V; C <sub>L</sub> =30pF | -    | -    | 18.2 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =3.3V; C <sub>L</sub> =15pF | -    | -    | 12.8 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =3.3V; C <sub>L</sub> =30pF | -    | -    | 14.6 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =5.0V; C <sub>L</sub> =15pF | -    | -    | 9.4  | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =5.0V; C <sub>L</sub> =30pF | -    | -    | 10.8 | ns   |
| t <sub>en</sub>  | Enable time       | $\overline{\text{OE}}$ to Y;<br>See Figure 8-6 <sup>(1)</sup> | V <sub>CC</sub> =1.8V; C <sub>L</sub> =15pF | -    | -    | 25.8 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =1.8V; C <sub>L</sub> =30pF | -    | -    | 30.6 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =2.5V; C <sub>L</sub> =15pF | -    | -    | 17.2 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =2.5V; C <sub>L</sub> =30pF | -    | -    | 20   | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =3.3V; C <sub>L</sub> =15pF | -    | -    | 13.6 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =3.3V; C <sub>L</sub> =30pF | -    | -    | 15.4 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =5.0V; C <sub>L</sub> =15pF | -    | -    | 9.6  | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =5.0V; C <sub>L</sub> =30pF | -    | -    | 11   | ns   |
| t <sub>dis</sub> | Disable time      | $\overline{\text{OE}}$ to Y;<br>See Figure 8-6 <sup>(1)</sup> | V <sub>CC</sub> =1.8V; C <sub>L</sub> =15pF | -    | -    | 22.6 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =1.8V; C <sub>L</sub> =30pF | -    | -    | 29.4 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =2.5V; C <sub>L</sub> =15pF | -    | -    | 16.2 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =2.5V; C <sub>L</sub> =30pF | -    | -    | 20.6 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =3.3V; C <sub>L</sub> =15pF | -    | -    | 13.4 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =3.3V; C <sub>L</sub> =30pF | -    | -    | 17.2 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =5.0V; C <sub>L</sub> =15pF | -    | -    | 12.4 | ns   |
|                  |                   |                                                               | V <sub>CC</sub> =5.0V; C <sub>L</sub> =30pF | -    | -    | 14.6 | ns   |
| C <sub>I</sub>   | Input capacitance | V <sub>I</sub> =V <sub>CC</sub> or GND; V <sub>CC</sub> =3.3V |                                             | -    | -    | 10   | pF   |

(1)  $t_{pd}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ .  $t_{en}$  is the same as  $t_{PZL}$  and  $t_{PZH}$ .  $t_{dis}$  is the same as  $t_{PLZ}$  and  $t_{PHZ}$ .

## 8 Detailed Description

### 8.1 Overview

The CJ74LV1T125 is a single, level translating buffer/line driver with 3-state output. The low threshold inputs support 1.8V input logic at  $V_{CC}=3.3V$  and can be used in 1.8V to 3.3V level up translation. In addition, the 5V tolerant input pins enable down translation (3.3V to 2.5V output at  $V_{CC}=2.5V$ ). The 3-state output is controlled by the output enable input (/OE). A HIGH-level at /OE causes the output to assume a high-impedance OFF-state. The output level is referenced to the supply voltage and supports 1.8V, 2.5V, 3.3V and 5.0V CMOS levels. The wide  $V_{CC}$  range permits the generation of output levels to connect to controllers or processors.

### 8.2 Functional Block Diagram




Figure 8-1 Logic symbol




Figure 8-2 IEC logic symbol




Figure 8-3 Logic diagram


### 8.3 Function Table<sup>(1)</sup>

| INPUT           |   | OUTPUT |
|-----------------|---|--------|
| $\overline{OE}$ | A | Y      |
| L               | L | L      |
| L               | H | H      |
| H               | X | Z      |

(1) H=HIGH voltage level; L=LOW voltage level; X=don't care; Z=high-impedance OFF-state.

## 8.4 Testing Circuit

### 8.4.1 AC Testing Circuit



**Figure 8-4 Test circuit for measuring switching times**

Definitions for test circuit:


$R_T$ =Termination resistance should be equal to the output impedance  $Z_o$  of the pulse generator.

$C_L$ =Load capacitance including jig and probe capacitance.


$R_L$ =Load resistance.

$V_{EXT}$ =External voltage for measuring switching times.

## 8.4.2 AC Testing Waveforms



**Figure 8-5 The input A to output Y propagation delays**  
( $V_{OL}$  and  $V_{OH}$  are typical voltage output levels that occur with the output load.)



**Figure 8-6 3-state enable and disable times**  
( $V_{OL}$  and  $V_{OH}$  are typical voltage output levels that occur with the output load.)

## 8.4.3 Measurement Points

| INPUT    | OUTPUT      |               |               |
|----------|-------------|---------------|---------------|
| $V_M$    | $V_M$       | $V_X$         | $V_Y$         |
| $0.5V_I$ | $0.5V_{CC}$ | $V_{OL}+0.3V$ | $V_{OH}-0.3V$ |

## 8.4.4 Test Data


| SUPPLY VOLTAGE | INPUT    |                           |           | LOAD       |             | $V_{EXT}$          |                    |                    |
|----------------|----------|---------------------------|-----------|------------|-------------|--------------------|--------------------|--------------------|
| $V_{CC}$       | $V_I$    | $\Delta t/\Delta V^{(1)}$ | $f_{max}$ | $C_L$      | $R_L$       | $t_{PLH}, t_{PHL}$ | $t_{PZH}, t_{PHZ}$ | $t_{PZL}, t_{PLZ}$ |
| 1.8V           | $V_{CC}$ | $\leq 1.0ns/V$            | 15MHz     | 15pF, 30pF | 1k $\Omega$ | Open               | GND                | $V_{CC}$           |
| 2.5V           | $V_{CC}$ | $\leq 1.0ns/V$            | 25MHz     | 15pF, 30pF | 1k $\Omega$ | Open               | GND                | $V_{CC}$           |
| 3.3V           | 3V       | $\leq 1.0ns/V$            | 50MHz     | 15pF, 30pF | 1k $\Omega$ | Open               | GND                | $V_{CC}$           |
| 5.0V           | 3V       | $\leq 1.0ns/V$            | 50MHz     | 15pF, 30pF | 1k $\Omega$ | Open               | GND                | $V_{CC}$           |

(1)  $dV/dt \geq 1.0V/ns$

## 9 Mechanical Information

### 9.1 SOT-23-5L Mechanical Information


#### 9.1.1 SOT-23-5L Outline Dimensions



| SYMBOL   | Dimensions In Millimeters |      |      |
|----------|---------------------------|------|------|
|          | Min.                      | Typ. | Max. |
| A        | -                         | -    | 1.26 |
| A1       | 0.00                      | -    | 0.12 |
| A2       | 1.00                      | -    | 1.20 |
| b        | 0.30                      | -    | 0.50 |
| c        | 0.10                      | -    | 0.20 |
| D        | 2.82                      | -    | 3.02 |
| E        | 2.60                      | -    | 3.00 |
| E1       | 1.50                      | -    | 1.70 |
| e        | 0.95 BSC                  |      |      |
| e1       | 1.80                      | -    | 2.00 |
| L        | 0.30                      | -    | 0.60 |
| $\theta$ | 0°                        | -    | 8°   |
| Unit: mm |                           |      |      |

## 9.2 SOT-353 Mechanical Information

### 9.2.1 SOT-353 Outline Dimensions



| SYMBOL   | Dimensions In Millimeters |       |       |
|----------|---------------------------|-------|-------|
|          | Min.                      | Typ.  | Max.  |
| A        | 0.90                      | -     | 1.10  |
| A1       | 0.00                      | -     | 0.10  |
| A2       | 0.90                      | -     | 1.00  |
| b        | 0.15                      | -     | 0.35  |
| c        | 0.11                      | -     | 0.175 |
| D        | 2.00                      | -     | 2.20  |
| E        | 2.15                      | -     | 2.45  |
| E1       | 1.15                      | -     | 1.35  |
| e        | 0.65 BSC                  |       |       |
| e1       | 1.20                      | -     | 1.40  |
| L        | -                         | 0.525 | -     |
| L1       | 0.26                      | -     | 0.46  |
| $\theta$ | 0°                        | -     | 8°    |
| Unit: mm |                           |       |       |

## **10 Notes and Revision History**

### **10.1 Associated Product Family and Others**

To view other products of the same type or IC products of other types, click the official website of JSCJ -- <https://www.jscj-elec.com> for more details.

### **10.2 Notes**

#### **Electrostatic Discharge Caution**



This IC may be damaged by ESD. Relevant personnel shall comply with correct installation and use specifications to avoid ESD damage to the IC. If appropriate measures are not taken to prevent ESD damage, the hazards caused by ESD include but are not limited to degradation of integrated circuit performance or complete damage of integrated circuit. For some precision integrated circuits, a very small parameter change may cause the whole device to be inconsistent with its published specifications.

# DISCLAIMER

## IMPORTANT NOTICE, PLEASE READ CAREFULLY

The information in this data sheet is intended to describe the operation and characteristics of our products. JSCJ has the right to make any modification, enhancement, improvement, correction or other changes to any content in this data sheet, including but not limited to specification parameters, circuit design and application information, without prior notice.

Any person who purchases or uses JSCJ products for design shall: 1. Select products suitable for circuit application and design; 2. Design, verify and test the rationality of circuit design; 3. Procedures to ensure that the design complies with relevant laws and regulations and the requirements of such laws and regulations. JSCJ makes no warranty or representation as to the accuracy or completeness of the information contained in this data sheet and assumes no responsibility for the application or use of any of the products described in this data sheet.

Without the written consent of JSCJ, this product shall not be used in occasions requiring high quality or high reliability, including but not limited to the following occasions: medical equipment, military facilities and aerospace. JSCJ shall not be responsible for casualties or property losses caused by abnormal use or application of this product.

Official Website: [www.jscj-elec.com](http://www.jscj-elec.com)

Copyright © JIANGSU CHANGJING ELECTRONICS TECHNOLOGY CO., LTD