

## 1. Description

The UMW OPA340 series operate on a single supply as low as 2.5 V with an input common-mode voltage range that extends 500 mV below ground and 500 mV above the positive supply. Output voltage swing is to within 1 mV of the supply rails with a 100-k $\Omega$  load. These devices offer excellent dynamic response (BW = 5.5 MHz, SR = 6 V/ $\mu$ s), yet quiescent current is only 750 A. Dual and quad designs feature completely independent circuitry for lowest crosstalk and freedom from interaction. All are specified from  $-40^{\circ}\text{C}$  to  $85^{\circ}\text{C}$  and operate from  $-55^{\circ}\text{C}$  to  $125^{\circ}\text{C}$ .

## 3. Applications

- Driving A/D Converters
- PCMCIA Cards
- Data Acquisition
- Process Control


## 2. Features

- Rail-to-Rail Input
- Rail-to-Rail Output (Within 1mV)
- MicroSize Packages
- Wide Bandwidth: 5.5 MHz
- High Slew Rate: 6 V/ $\mu$ s
- Low THD + Noise: 0.0007% (f=1kHz)
- Low Quiescent Current: 750  $\mu$ A/Channel
- Single, Dual, and Quad Versions

- Audio Processing
- Communications
- Active Filters
- Test Equipment




## 4. OPA340 in Noninverting Configuration Driving ADS7816





## 5.1 Pinning Information (OPA340)




### Pin Functions

Name	PIN		I/O	Description
	SOT23-5	SOP		
-INA	4	2	I	Negative (inverting) input
+INA	3	3	I	Positive (noninverting)input
NC	-	1,5,8	-	No internal connection (can be left floating)
OUT	1	6	O	Output
V-	2	4	-	Negative (lowest) power supply
V+	5	7	-	Positive (highest) power supply



## 5.2 Pinning Information (OPA2340)




### Pin Functions

PIN		I/O	Description
Name	SOP		
-INA	2	I	Negative (inverting)input channel A
+INA	3	I	Positive (noninverting)input channel A
-INB	6	I	Negative (inverting) input channel B
+INB	5	I	Positive (noninverting)input channel B
OUTA	1	O	Output channel A
OUTB	7	O	Output channel B
V-	4	-	Negative (lowest) power supply
V+	8	-	Positive (highest) power supply



### 5.3 Pinning Information (OPA2340)



**SOP-14**

#### Pin Functions

PIN		I/O	Description
Name	SOP		
-INA	2	I	Negative (inverting) input channel A
-INB	6	I	Negative (inverting)input channel B
-INC	9	I	Negative (inverting) input channel C
-IND	13	I	Negative (inverting) input channel D
+INA	3	I	Positive (noninverting) input channel A
+INB	5	I	Positive (noninverting)input channel B
+INC	10	I	Positive (noninverting) input channel C
+IND	12	I	Positive (noninverting) input channel D
NC	-	-	No internal connection (can be left floating)
OUTA	1	O	Output, channel A
OUTB	7	O	Output, channel B
OUTC	8	O	Output, channel C
OUTD	14	O	Output, channel D
V-	11	-	Negative (lowest) power supply
V+	4	-	Positive (highest) power supply



## 6. Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

Parameter		Symbol	Min	Max	Units
Voltage	Supply voltage			5.5	V
	Signal input terminals <sup>(2)</sup>		-0.5	0.5	V
Current	Signal input terminals <sup>(2)</sup>		-10	10	mA
	Output short circuit <sup>(3)</sup>		Continuous		
Temperature	Operating	$T_A$	-55	125	°C
	Junction	$T_J$		150	°C
	Storage	$T_{STG}$	-55	125	°C

Notes:

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) Input terminals are diode-clamped to the power-supply rails. Input signals that can swing more than 0.5 V beyond the supply rails should be current limited to 10 mA or less.

(3) Short-circuit to ground, one amplifier per package

## 7. ESD Ratings

Parameter		Symbol	Value	Units
Electrostatic discharge	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>	$V_{(ESD)}$	±600	V
	Charged-device model (CDM), per JEDEC specification JESD22-C101 <sup>(2)</sup>		±250	V



## 8. Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

Parameter	Min	Max	Units
Supply voltage	2.7	5.5	V
Specified temperature	-40	125	°C

### 9.1 Thermal Information (OPA340)

Thermal Metric <sup>(1)</sup>	Symbol	(SOT-23)	(SOP)	(SOP)	Units
		5 Pins	8 Pins	14 Pins	
Junction-to-ambient thermal resistance	$R_{\theta JA}$	207.9	142	83.8	°C/W
Junction-to-case (top) thermal resistance	$R_{\theta JC(top)}$	71.2	90.2	70.7	°C/W
Junction-to-board thermal resistance	$R_{\theta JB}$	36	82.5	59.5	°C/W
Junction-to-top characterization parameter	$\psi_{JT}$	2	39.4	11.6	°C/W
Junction-to-board characterization parameter	$\psi_{JB}$	35.2	82	37.7	°C/W
Junction-to-case(bottom)thermal resistance	$R_{\theta JC(bot)}$	-	-	-	°C/W

### 9.2 Thermal Information (OPA2340)

Thermal Metric <sup>(1)</sup>	Symbol	(SOP)	Units
		8 Pins	
Junction-to-ambient thermal resistance	$R_{\theta JA}$	138.4	°C/W
Junction-to-case (top) thermal resistance	$R_{\theta JC(top)}$	89.5	°C/W
Junction-to-board thermal resistance	$R_{\theta JB}$	78.6	°C/W
Junction-to-top characterization parameter	$\psi_{JT}$	29.9	°C/W
Junction-to-board characterization parameter	$\psi_{JB}$	78.1	°C/W
Junction-to-case(bottom)thermal resistance	$R_{\theta JC(bot)}$	-	°C/W



## 10. Electrical Characteristics

At  $T_A=+25^\circ\text{C}$ ,  $R_L=10\text{k}\Omega$  connected to  $V_S=1.8\text{V}$  to  $5.5\text{V}$ , and  $V_{CM}=V_{OUT}=\text{midsupply}$  (unless otherwise noted).

Parameter	Symbol	Conditions	Min	Typ <sup>(1)</sup>	Max	Units	
Input offset voltage	$V_{OS}$	$V_S=5\text{V}$		$\pm 150$	$\pm 500$	$\mu\text{V}$	
Input offset voltage versus temperature	$dV_{OS}/dT$	$T_A=-40^\circ\text{C}$ to $+85^\circ\text{C}$ , $V_S=5\text{V}$		$\pm 2.5$		$\mu\text{V}/^\circ\text{C}$	
Input offset voltage vs power supply	Over temperature	$PSRR$ $V_S=2.7\text{V}$ to $5.5\text{V}$ , $V_{CM}=0\text{V}$		30	120	$\mu\text{V}/\text{V}$	
		$V_S=2.7\text{V}$ to $5.5\text{V}$ , $V_{CM}=0\text{V}$ $T_A=-40^\circ\text{C}$ to $+85^\circ\text{C}$ , $V_S=5\text{V}$			120	$\mu\text{V}/^\circ\text{C}$	
Channel separation, DC				0.2		$\mu\text{V}/\text{V}$	
Input bias current	Over temperature	$I_S$		$\pm 0.2$	$\pm 10$	$\text{pA}$	
		$T_A=-40^\circ\text{C}$ to $+85^\circ\text{C}$ , $V_S=5\text{V}$			$\pm 60$	$\text{pA}$	
Input offset current	$I_{OS}$			$\pm 0.2$	$\pm 10$	$\text{pA}$	
Input voltage noise		$f=0.1\text{kHz}$ to $50\text{kHz}$		8		$\mu\text{V}_{RMS}$	
Input voltage noise density	$e_n$	$f=1\text{kHz}$		25		$\text{nV}/\sqrt{\text{Hz}}$	
Current noise density	$i_n$	$f=1\text{kHz}$		3		$\text{fA}/\sqrt{\text{Hz}}$	
Common-mode voltage range	$V_{CM}$		-0.3		$(V^+)+0.3$	V	
Common-mode rejection ratio	$CMRR$	$-0.3\text{V}<V_{CM}<(V^+)-1.8\text{V}$	80	92		dB	
		$V_S=5\text{V}$ , $-0.3\text{V}<V_{CM}<5.3\text{V}$	70	84		dB	
		$V_S=2.7\text{V}$ , $-0.3\text{V}<V_{CM}<3\text{V}$	66	80		dB	
Differential				$10^{13}  3$		$\Omega  \text{pF}$	
Common-mode				$10^{13}  6$		$\Omega  \text{pF}$	
Open-loop voltage gain		$R_L=100\text{k}\Omega$ , $5\text{mV}<V_O<(V^+)-5\text{mV}$	106	124		dB	
		$R_L=10\text{k}\Omega$ , $5\text{mV}<V_O<(V^+)-50\text{mV}$	100	120		dB	
		$R_L=2\text{k}\Omega$ , $200\text{mV}<V_O<(V^+)-200\text{mV}$	94	114		dB	
	Over temperature	$A_{OL}$	$R_L=100\text{k}\Omega$ , $5\text{mV}<V_O<(V^+)-5\text{mV}$ $T_A=-40^\circ\text{C}$ to $+85^\circ\text{C}$ , $V_S=5\text{V}$	106		106	dB
			$R_L=10\text{k}\Omega$ , $5\text{mV}<V_O<(V^+)-50\text{mV}$ $T_A=-40^\circ\text{C}$ to $+85^\circ\text{C}$ , $V_S=5\text{V}$	100		100	dB
			$R_L=2\text{k}\Omega$ , $200\text{mV}<V_O<(V^+)-200\text{mV}$ $T_A=-40^\circ\text{C}$ to $+85^\circ\text{C}$ , $V_S=5\text{V}$	94		94	dB
			$T_A=-40^\circ\text{C}$ to $+85^\circ\text{C}$ , $V_S=5\text{V}$				



Parameter		Symbol	Conditions	Min	Typ <sup>(1)</sup>	Max	Units	
Gain-bandwidth product		GBW	G=1		5.5		MHz	
Slew rate		SR	V <sub>S</sub> =5V, G=1, C <sub>L</sub> =100pF		6		V/μs	
Settling time, 0.1%			V <sub>S</sub> =5V 2-V step, C <sub>L</sub> =100pF		1		μs	
Settling time, 0.01%			V <sub>S</sub> =5V 2-V step, C <sub>L</sub> =100pF		1.6		μs	
Overload recovery time			V <sub>IN</sub> ×G=V <sub>S</sub>		0.2		μs	
Total harmonic distortion + noise		THD+N	V <sub>S</sub> =5V, V <sub>O</sub> =3V <sub>PP</sub> <sup>(2)</sup> G=1, f=1kHz		0.0007%			
Voltage output swing from rail <sup>(2)</sup>			R <sub>L</sub> =100kΩ, A <sub>OL</sub> ≥106dB		1	5	mV	
			R <sub>L</sub> =10kΩ, A <sub>OL</sub> ≥106dB		10		mV	
			R <sub>L</sub> =2kΩ, A <sub>OL</sub> ≥106dB		40		mV	
	Over temperature		R <sub>L</sub> =100kΩ, A <sub>OL</sub> ≥106dB T <sub>A</sub> =-40°C to +85°C, V <sub>S</sub> =5V			5		mV
			R <sub>L</sub> =10kΩ, A <sub>OL</sub> ≥106dB T <sub>A</sub> =-40°C to +85°C, V <sub>S</sub> =5V				50	mV
			R <sub>L</sub> =2kΩ, A <sub>OL</sub> ≥106dB T <sub>A</sub> =-40°C to +85°C, V <sub>S</sub> =5V				200	mV
Short-circuit current		I <sub>SC</sub>			±50		mA	
Capacitive load drive		C <sub>LOAD</sub>		See Typical Characteristics				
Specified voltage range		V <sub>S</sub>		2.7		5	V	
Operating voltage range			Lower end		2.5		V	
			Higher end		5.5		V	
Quiescent current (per amplifier)		I <sub>Q</sub>	I <sub>O</sub> =0, V <sub>S</sub> =5V		750	950	μA	
	Over temperature		I <sub>O</sub> =0, V <sub>S</sub> =5V, T <sub>A</sub> =-40°C to +85°C			100	μA	
Specified range				-40		85	°C	
Operating range				-55		125	°C	
Storage range				-55		125	°C	

(2) Output voltage swings are measured between the output and power-supply rails.



### 11.1 Typical characteristic

<p>Figure 1: Open-Loop Gain/Phase vs Frequency</p>	<p>Figure 2: Power-Supply and Common-Mode Rejection vs Frequency</p>
<p>Figure 3: Input Voltage and Current Noise Spectral Density vs Frequency</p>	<p>Figure 4: Channel Separation vs Frequency</p>
<p>Figure 5: Total Harmonic Distortion + Noise vs Frequency</p>	<p>Figure 6: Closed-Loop Output Impedance vs Frequency</p>



### 11.2 Typical characteristic

<p>Figure 7: Open-Loop Gain and Power-Supply Rejection vs Temperature</p>	<p>Figure 8: Common-Mode Rejection vs Temperature</p>
<p>Figure 9: Quiescent Current vs Temperature</p>	<p>Figure 10: Quiescent Current vs Supply Voltage</p>
<p>Figure 11: Short-Circuit Current vs Temperature</p>	<p>Figure 12: Short-Circuit Current vs Supply Voltage</p>



### 11.3 Typical characteristic

<p>Figure 13: Input Bias Current vs Temperature</p>	<p>Figure 14: Input Bias Current vs Input Common-Mode Voltage</p>
<p>Figure 15: Output Voltage Swing vs Output Current</p>	<p>Figure 16: Maximum Output Voltage vs Frequency</p>
<p>Figure 17: Offset Voltage Production Distribution</p>	<p>Figure 18: Offset Voltage Drift Magnitude Production Distribution</p>




## 11.4 Typical characteristic

<p>Figure 19: Small-Signal Step Response</p>	<p>Figure 20: Large-Signal Step Response</p>
<p>Figure 21: Small-Signal Overshoot vs Load Capacitance</p>	<p>Figure 22: Settling Time vs Closed-Loop Gain</p>



## 12.1 SOT-23-5 Package Outline Dimensions




### DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E1	E	e	e1	L	θ
Min	1.050	0.000	1.050	0.300	0.100	2.820	1.500	2.650	0.950	1.800	0.300	0°
Max	1.250	0.100	1.150	0.500	0.200	3.020	1.700	2.950	BSC	2.000	0.600	8°



## 12.2 SOP-14 Package Outline Dimensions




### DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	A3	b	C	D	E	E1	e	h	L
Min	-	0.05	1.35	0.65	0.203	0.17	8.45	5.80	3.80	1.24	0.25	0.40
Max	1.75	0.25	1.55	0.75	0.305	0.25	8.85	6.20	4.00	1.30	0.50	0.80

Symbol	L1	θ
Min	1.00	0°
Max	1.10	8°



## 12.3 SOP-8 Package Outline Dimensions




### DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E	E1	e	L	θ
<b>Min</b>	1.350	0.000	1.350	0.330	0.170	4.700	3.800	5.800	1.270	0.400	0°
<b>Max</b>	1.750	0.100	1.550	0.510	0.250	5.100	4.000	6.200	BSC	1.270	8°



## 13. Ordering information



Order Code	Marking	Package	Base QTY	Delivery Mode
UMW OPA4340UA	OPA4340UA	SOP-14	2500	Tape and reel
UMW OPA2340UA	OPA2340UA	SOP-8	2500	Tape and reel
UMW OPA340UA	OPA340UA	SOP-8	2500	Tape and reel
UMW OPA340NA	A40	SOT23-5	3000	Tape and reel



## 14.Disclaimer

---

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.