

1. General Description

The 74LVC2G17 is a dual buffer with Schmitt-trigger inputs. Inputs can be driven from either 3.3 V or 5 V devices. This feature allows the use of these devices as translators in mixed 3.3 V and 5 V environments.

This device is fully specified for partial power down applications using I_{OFF} . The I_{OFF} circuitry disables the output, preventing the potentially damaging backflow current through the device when it is powered down.

2. Features and Benefits

- Wide supply voltage range from 1.65 V to 5.5 V
- Overvoltage tolerant inputs to 5.5 V
- High noise immunity
- ± 24 mA output drive ($V_{CC} = 3.0$ V)
- CMOS low power dissipation
- Latch-up performance exceeds 100 mA
- Direct interface with TTL levels
- I_{OFF} circuitry provides partial Power-down mode operation
- Complies with JEDEC standard:
 - JESD8-7 (1.65 V to 1.95 V)
 - JESD8-5 (2.3 V to 2.7 V)
 - JESD8B/JESD36 (2.7 V to 3.6 V)
- ESD protection:
 - HBM ANSI/ESDA/JEDEC JS-001 Class 3B exceeds 8000 V
 - MM JESD22-A115C Class C exceeds 550 V
 - CDM ANSI/ESDA/JEDEC JS-002 Class C3 exceeds 2000 V
- Multiple package options

74LVC2G17

Dual non-inverting Schmitt trigger with 5 V tolerant input


3. Ordering Information

Table 1. Ordering information


Type number	Topside marking	Package		
		Name	Description	Quantity
74LVC2G17GV	VeYW	SOT23-6L	SOT23 package, 6 pins 2.92 mm × 1.6 mm; 1.25 mm (Max) height	3000
74LVC2G17GW	VeYW	SOT363	SOT363 package, 6 pins 2.1 mm × 1.25 mm; 1.0 mm (Max) height	3000
74LVC2G17GS	Ve	DFN1x1-6L	DFN1x1 package, 6 pins 1 mm × 1 mm; 0.42 mm (Max) height	3000
74LVC2G17GM	VeYW	DFN1x1.45-6L	DFN1.45x1 package, 6 pins 1.45 mm × 1 mm; 0.6 mm (Max) height	3000

MARKING INFORMATION

NOTE: YW = Data Code.



4. Function Diagram



5. Pinning Information

5.1. Pin map




Fig 4. Top view pin configuration SOT23-6 and SOT363




Fig 5. Top view pin configuration DFN6L

5.2. Pin description

Table 2. Pin description

Symbol	Pin	Description
1A	1	Data input
GND	2	Ground (0V)
2A	3	Data input
2Y	4	Data output
VCC	5	Supply voltage
1Y	6	Data output

6. Functional Description

Table 3. Function table

H = HIGH voltage level; L = LOW voltage level.

Input	Output
-------	--------

74LVC2G17

Dual non-inverting Schmitt trigger with 5 V tolerant input

nA	nY
L	L
H	H

7. Absolute Maximum Ratings

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

Table 4. Absolute Maximum Ratings

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND.

Symbol	Parameter	Conditions	Min	Max	Unit
V_{CC}	supply voltage		-0.5	6.5	V
I_{IK}	input clamping current	$V_I < 0\text{ V}$	-50		mA
V_I	input voltage	[1]	-0.5	6.5	V
I_{OK}	output clamping current	$V_O > V_{CC}$ or $V_O < 0\text{ V}$		± 50	mA
V_O	output voltage	Active mode [1]	-0.5	$V_{CC} + 0.5$	V
		Power-down mode; $V_{CC} = 0\text{ V}$ [1]	-0.5	6.5	V
I_O	output current	$V_O = 0\text{ V}$ to V_{CC}		± 50	mA
I_{CC}	supply current			100	mA
I_{GND}	ground current		-100		mA
P_{tot}	total power dissipation	$T_{amb} = -40\text{ °C}$ to $+125\text{ °C}$		250	mW
T_{stg}	storage temperature		-65	150	°C

[1] The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

8. Recommended Operating Conditions

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. EnergyMath does not recommend exceeding them or designing to Absolute Maximum Ratings.

Table 5. Recommended Operating Conditions

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
V_{CC}	supply voltage		1.65		5.5	V
V_I	input voltage		0		5.5	V
V_O	output voltage	Active mode	0		V_{CC}	V
		Power-down mode; $V_{CC} = 0$ V	0		5.5	V
T_{amb}	ambient temperature		-40		125	°C

74LVC2G17

Dual non-inverting Schmitt trigger with 5 V tolerant input

9. Static Characteristics

Table 6. Static characteristics

At recommended operating conditions. Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	-40 °C to +85 °C			-40 °C to +125 °C		Unit
			Min	Typ[1]	Max	Min	Max	
V_{OH}	HIGH-level output voltage	$V_I = V_{T+}$ or V_{T-}						
		$I_O = -100\mu A$; $V_{CC} = 1.65 V$ to $5.5 V$	$V_{CC} - 0.1$			$V_{CC} - 0.1$		V
		$I_O = -4 mA$; $V_{CC} = 1.65 V$	1.2			0.95		V
		$I_O = -8 mA$; $V_{CC} = 2.3 V$	1.9			1.7		V
		$I_O = -12 mA$; $V_{CC} = 2.7 V$	2.2			1.9		V
		$I_O = -24 mA$; $V_{CC} = 3.0 V$	2.3			2.0		V
		$I_O = -32 mA$; $V_{CC} = 4.5 V$	3.8			3.4		V
V_{OL}	LOW-level output voltage	$V_I = V_{T+}$ or V_{T-}						
		$I_O = 100\mu A$; $V_{CC} = 1.65 V$ to $5.5 V$			0.10		0.10	V
		$I_O = 4 mA$; $V_{CC} = 1.65 V$			0.45		0.70	V
		$I_O = 8 mA$; $V_{CC} = 2.3 V$			0.30		0.45	V
		$I_O = 12 mA$; $V_{CC} = 2.7 V$			0.40		0.60	V
		$I_O = 24 mA$; $V_{CC} = 3.0 V$			0.55		0.80	V
		$I_O = 32 mA$; $V_{CC} = 4.5 V$			0.55		0.80	V
I_I	Input leakage current	$V_I = 5.5 V$ or GND ; $V_{CC} = 5.5 V$		± 0.1	± 1		± 1	μA
I_{OFF}	power-off leakage current	$V_{CC} = 0V$; V_I or $V_O = 5.5 V$		± 0.1	± 2		± 2	μA
I_{CC}	supply current	$V_I = 5.5V$ or GND ; $I_O = 0A$; $V_{CC} = 5.5V$		0.1	4		4	μA
ΔI_{CC}	additional supply current	per pin ; $V_{CC} = 2.3V$ to $5.5V$; $V_I = V_{CC} - 0.6V$; $I_O = 0A$		5	500		500	μA
C_I	input capacitance	$V_{CC} = 3.3V$; $V_I = GND$ to V_{CC}		5				pF

[1] All typical values are measured at $V_{CC} = 3.3V$ and $T_{amb} = 25^\circ C$.

74LVC2G17

Dual non-inverting Schmitt trigger with 5 V tolerant input

10. Dynamic Characteristics

Table 7. Dynamic characteristics

Voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 7.

Symbol	Parameter	Conditions	-40 °C to +85 °C			-40 °C to +125 °C		Unit
			Min	Typ[1]	Max	Min	Max	
t_{pd}	propagation delay	nA to nY; see Fig. 6 [2]						
		$V_{CC} = 1.65 \text{ V to } 1.95 \text{ V}$	4.0	10.6	19.5	4.0	19.8	ns
		$V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$	2.5	5.9	10.6	2.5	10.9	ns
		$V_{CC} = 3.0 \text{ V to } 3.6 \text{ V}$	2.0	4.3	7	2.0	7.5	ns
		$V_{CC} = 4.5 \text{ V to } 5.5 \text{ V}$	1.5	2.9	4.8	1.5	5.0	ns
C_{PD}	power dissipation capacitance	per buffer ; $V_I = \text{GND to } V_{CC}$; $V_{CC} = 3.3 \text{ V}$ [3]		24				pF

[1] Typical values are measured at $T_{amb} = 25^\circ\text{C}$ and $V_{CC} = 1.8 \text{ V}, 2.5 \text{ V}, 3.3 \text{ V}$ and 5.0 V respectively.

[2] t_{pd} is the same as t_{PLH} and t_{PHL} .

[3] C_{PD} is used to determine the dynamic power dissipation (P_D in μW).

$P_D = C_{PD} \times V_{CC}^2 \times f_i \times N + \sum (C_L \times V_{CC}^2 \times f_o)$ where:

f_i = input frequency in MHz;

f_o = output frequency in MHz;

C_L = output load capacitance in pF;

V_{CC} = supply voltage in V;


N = number of inputs switching;

$\sum (C_L \times V_{CC}^2 \times f_o)$ = sum of outputs.

74LVC2G17

Dual non-inverting Schmitt trigger with 5 V tolerant input

10.1. Waveforms and test circuit



Measurement points are given in Table 8.

V_{OL} and V_{OH} are typical output voltage levels that occur with the output load.


Fig 6. The input nA to output nY propagation delays

Table 8. Measurement points

Supply voltage	Input	Output
V_{CC}	V_M	V_M
1.65 V to 1.95 V	$0.5V_{CC}$	$0.5V_{CC}$
2.3 V to 2.7 V	$0.5V_{CC}$	$0.5V_{CC}$
3.0 V to 3.6 V	1.5 V	1.5 V
4.5 V to 5.5 V	$0.5V_{CC}$	$0.5V_{CC}$

74LVC2G17

Dual non-inverting Schmitt trigger with 5 V tolerant input



Test data is given in Table 9.

Definitions for test circuit:

R_L = Load resistance.

C_L = Load capacitance including jig and probe capacitance.

R_T = Termination resistance should be equal to the output impedance Z_o of the pulse generator.

V_{EXT} = External voltage for measuring switching times.

Fig 7. Test circuit for measuring switching times

Table 9. Test data

Supply voltage	Input		Load		V_{EXT}
V_{CC}	V_I	$t_r = t_f$	C_L	R_L	t_{PLH}, t_{PHL}
1.65 V to 1.95 V	V_{CC}	≤ 2.0 ns	30 pF	1 k Ω	open
2.3 V to 2.7 V	V_{CC}	≤ 2.0 ns	30 pF	500 Ω	open
3.0 V to 3.6 V	3 V	≤ 2.5 ns	50 pF	500 Ω	open
4.5 V to 5.5 V	V_{CC}	≤ 2.5 ns	50 pF	500 Ω	open

11. Transfer Characteristics

Table 10. Transfer characteristics

At recommended operating conditions. Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	-40 °C to +85 °C			-40 °C to +125 °C		Unit
			Min	Typ[1]	Max	Min	Max	
V_{T+}	positive-going threshold voltage	see Fig. 8 and Fig. 9						
		$V_{CC} = 1.8 \text{ V}$	0.82	1.0	1.04	0.79	1.04	V
		$V_{CC} = 2.3 \text{ V}$	1.03	1.2	1.40	1.00	1.40	V
		$V_{CC} = 3.0 \text{ V}$	1.29	1.5	1.71	1.26	1.71	V
		$V_{CC} = 4.5 \text{ V}$	1.84	2.2	2.36	1.81	2.36	V
		$V_{CC} = 5.5 \text{ V}$	2.19	2.6	2.79	2.16	2.79	V
V_{T-}	negative-going threshold voltage	see Fig. 8 and Fig. 9						
		$V_{CC} = 1.8 \text{ V}$	0.46	0.6	0.75	0.46	0.78	V
		$V_{CC} = 2.3 \text{ V}$	0.65	0.7	0.96	0.65	0.99	V
		$V_{CC} = 3.0 \text{ V}$	0.88	1.0	1.24	0.88	1.27	V
		$V_{CC} = 4.5 \text{ V}$	1.32	1.6	1.84	1.32	1.87	V
		$V_{CC} = 5.5 \text{ V}$	1.58	1.9	2.24	1.58	2.27	V
V_H	hysteresis voltage	see Fig. 8 and Fig. 9						
		$V_{CC} = 1.8 \text{ V}$	0.26	0.5	0.62	0.19	0.62	V
		$V_{CC} = 2.3 \text{ V}$	0.28	0.5	0.65	0.22	0.65	V
		$V_{CC} = 3.0 \text{ V}$	0.31	0.6	0.7	0.25	0.7	V
		$V_{CC} = 4.5 \text{ V}$	0.40	0.6	0.77	0.34	0.77	V
		$V_{CC} = 5.5 \text{ V}$	0.47	0.6	0.88	0.41	0.88	V

[1] Typical values are measured at $T_{amb} = 25^\circ\text{C}$.

11.1. Waveforms transfer characteristics





Fig 8. Transfer characteristic



V_{T+} and V_{T-} limits at 70% and 20%.

Fig 9. Definition of V_{T+} , V_{T-} and V_H

74LVC2G17

Dual non-inverting Schmitt trigger with 5 V tolerant input


12. Package Outline

SOT23-6L

74LVC2G17

Dual non-inverting Schmitt trigger with 5 V tolerant input

SOT-23-6L(14RZ) PACKAGE OUTLINE DIMENSIONS




Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E1	1.500	1.700	0.059	0.067
E	2.650	2.950	0.104	0.116
e	0.950(BSC)		0.037(BSC)	
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
L1	0.600REF.		0.024REF.	
θ	0°	8°	0°	8°

SOT363

74LVC2G17

Dual non-inverting Schmitt trigger with 5 V tolerant input


SOT-363 (16R) PACKAGE OUTLINE DIMENSIONS



Symbol	Dimensions in Millimeters		Dimensions in Inches	
	Min.	Max.	Min.	Max.
A	0.900	1.100	0.035	0.043
A1	0.000	0.100	0.000	0.004
A2	0.900	1.000	0.035	0.039
b	0.150	0.350	0.006	0.014
c	0.110	0.175	0.004	0.007
D	2.000	2.200	0.079	0.087
E	1.150	1.350	0.045	0.053
E1	2.150	2.450	0.085	0.096
e	0.650 TYP.		0.026 TYP.	
e1	1.200	1.400	0.047	0.055
L	0.525 REF.		0.021 REF.	
L1	0.260	0.460	0.010	0.018
θ	0°	8°	0°	8°

74LVC2G17


Dual non-inverting Schmitt trigger with 5 V tolerant input



74LVC2G17

Dual non-inverting Schmitt trigger with 5 V tolerant input

DFN1x1.45-6L



74LVC2G17

Dual non-inverting Schmitt trigger with 5 V tolerant input

13. Abbreviations

Table 10. Abbreviations

Acronym	Description
CMOS	Complementary Metal-Oxide Semiconductor
DUT	Device Under Test
ESD	ElectroStatic Discharge
HBM	Human Body Model
MM	Machine Model
TTL	Transistor-Transistor Logic

14. Revision History

Table 11. Revision history

Document ID	Release Date	Data sheet status	Change notice	Supersedes
74LVC2G17 Rev1.0	Apr 24, 2025	Product datasheet		74LVC2G17 Rev1.0
Modifications:	Section 3 updated: Added MARKING INFORMATION.			
74LVC2G17 Rev1.0	Oct 30, 2023	Product datasheet		