

序号 No	目 录 TABLE OF CONTENTS
1	特征 Feature
2	应用范围 Application
3	型号表示法 Ordering Code
4	产品结构 Product Structure
5	产品尺寸 Product Dimensions
6	温度系数/特性 Temperature Coefficient /Characteristics
7	容量范围及电压 Capacitance Range and Voltage
8	可靠性测试方法 Reliability Test Methods
9	包装 Package
10	储存方法 Storage Methods
11	使用前的注意事项 Precautions Before Use
12	推荐焊接温度曲线图 The temperature profile for soldering

■通用型系列片式陶瓷电容器

General Series Multi-layer Ceramic Capacitors

◆特征

Feature

*叠层独石结构，具有高可靠性能

There is high reliability on monolithic structure of laminated layers.

*具有优良的焊接与耐焊性能，适用于回流焊接与波峰焊接

And its character of excellent soldering ability and

soldering resistance ability is suitable for reflow soldering and peak soldering.

*具有较高的容量且容量性能稳定

It includes high and stable capacitance.


*高频类：此类介质材料的电容器为 I 类电容器。其中 C0G、C0H 电容器电性能最稳定，几乎不随温度、电压和时间的变化而变化，适用于低损耗，稳定性要求高的高频电路。

High frequency Type:

This kind of dielectric material is considered as Class I capacitor. C0G and C0H capacitors have the most stable electrical performance, which almost does not change with the change of temperature, Voltage or time, they are suitable for the low-loss and high stability requirement circuits.

*X7R、X7S、X7T、X6S、X6T、X5R、：此类介质材料的电容器为 II 类电容器，具有较高的介电常数，容量比 I 类电容器高，具有较稳定的温度特性，适用于容量范围广，稳定性要求不高的电路中，如隔直、耦合、旁路、鉴频等电路中。

X7R、X5R、X7S、X6S: X7R、X5R、X7S、X6S material is a kind of material has high dielectric constant. The capacitor made of this kind material is considered as Class II capacitor whose capacitance is higher than that of class I. These capacitors are classified as having a semi-stable temperature characteristic and used over a wide temperature range, such in these kinds of circuits, DC-blocking, decoupling, bypassing, frequency discriminating etc.



◆应用范围

Application

*应用于各种滤波、耦合、谐振、旁路、高频电子线路


It is suitable for all kinds of filter, coupled, harmonic vibration, by passing and high frequency circuits.

◆型号表示法
How To Order

MBK	0805	CG	102	K	500	A	T
系列 Series	尺寸规格 Size Code	标称容量 Nominal Capacitance	额定电压 Rated Voltage 单位(unit): V	包装方式 Package Styles	介质种类 Dielectric Code	容量误差 Capacitance Tolerance	端头材料 Terminal Material Styles
MBK 工业级 YBK 消费级 ABK 汽车级	尺寸代码 Size Code EIA 长×宽 (L×W) mm	表示方式 Express Method 实际值 Actual Value	表示方式 Express Method 实际值 Actual Value	表示方式 Express Method 包装方式 Package Styles	介质种类 Dielectric Code 介质材料 Dielectric	代码 Code 误差 Tolerance 备注 Note	端头类别 Termination Styles 表示方式 Express Method
	1005 01005 0.40×0.20 0201 0201 0.60×0.30 0402 0402 1.00×0.50 0603 0603 1.60×0.80 0805 0805 2.00×1.25 1206 1206 3.20×1.60 1210 1210 3.20×2.50 1808 1808 4.50×2.00 1812 1812 4.50×3.20	0R5 0.5 1R0 1.0 102 10×10 ² 注: 头两位数字为有效数字, 第三位数字为0的个数; R为小数点。 Note: the first two digits are significant; third digit denotes number of zeros; R=decimal point.	6R3 6.3 500 50×10 ⁰ 201 20×10 ¹ 注: 头两位数字为有效数字, 第三位数字为0的个数; R为小数点。 Note: the first two digits are significant; third digit denotes number of zeros; R=decimal point.	T 编带 7 寸盘包装 Braided 7 inch disc packing D 编带 13 寸盘包装 Braided 13 inch disc packing	C0G C0G X5R X5R X7R X7R X7S X7S X7T X7T X6S X6S X6T X6T	A ±0.05pF B ±0.10pF C ±0.25pF D ±0.50pF F ±1% G ±2% J ±5% K ±10% M ±20% A ±0.05pF A、B、C、D级误差适用于容量≤10pF的产品。 These Capacitance tolerance A, B, C, D are just applicable the capacitance that equals to or less than 10pF.	三层电镀端头 Nickel Barrier Termination 柔性端头多层片式陶瓷电容器 MLCC with Flexible Solderable Termination N A


◆产品结构
Product Structure

序号 NO	名称 Name
①	陶瓷介质 Ceramic dielectric
②	内电极 Inner electrode
③	外电极 Substrate electrode
④	镍层 Nickel Layer
⑤	锡层 Tin Layer



◆ 产品尺寸

Product Dimensions



型号 Type		尺寸 Dimensions (mm)			
尺寸代码 SizeCode	公制表示 Metric	L	W	T	WB
1005	0402	0.40±0.02	0.20±0.02	0.20±0.02	0.10±0.03
0201	0603	0.60±0.03	0.30±0.03	0.30±0.03	0.15±0.05
		0.60±0.09	0.30±0.09	0.30±0.09	0.15±0.05
		0.60±0.09	0.30±0.09	0.50±0.05	0.15±0.10
0402	1005	1.00±0.05	0.50±0.05	0.50±0.05	0.25±0.05
		1.00±0.15	0.50±0.15	0.50±0.15	0.25±0.05
		1.00±0.20	0.50±0.20	0.50±0.20	0.25±0.05
0603	1608	1.60±0.10	0.80±0.10	0.80±0.10	0.35±0.20
		1.60±0.20	0.80±0.20	0.80±0.20	0.35±0.20
0805	2012	2.00±0.20	1.25±0.20	0.80±0.20	0.50±0.20
				1.25±0.25	
1206	3216	3.20±0.30	1.60±0.30	0.80±0.20	0.60±0.30
				1.25±0.25	
				1.60±0.30	
1210	3225	3.20±0.30	2.50±0.30	1.25±0.25	0.60±0.30
				1.60±0.30	
				2.50±0.30	
1808	4520	4.50±0.40	2.00±0.20	1.60±0.30	0.60±0.30
				2.00±0.30	
1812	4532	4.50±0.40	3.20±0.30	1.60±0.30	0.60±0.30
				2.00±0.30	

备注：可根据客户的特殊要求设计符合客户需求的产品。

Note: We can design according to customer special requirements.

◆ 温度系数/特性 Temperature Coefficient /Characteristics

介质种类 Dielectric	参考温度点 Reference Temperature Point	标称温度系数 Temperature Coefficient	工作温度范围 Operation Temperature Range
C0G	25 ℃	0±30ppm/℃	-55℃~125℃
X7R	25 ℃	±15%	-55℃~125℃
X7S	25 ℃	±22%	-55℃~125℃
X7T	25 ℃	-33%~+22%	-55℃~125℃
X6S	25 ℃	±22%	-55℃~105℃
X6T	25 ℃	-33%~+22%	-55℃~105℃
X5R	25 ℃	±15%	-55℃~85℃

◆ 容量范围及电压

Capacitance Range and Voltage

* 常规电压 (Ur≤50V) 产品

Conventional Voltage (Ur≤50V) products

材料 Dielectric	C0G									
尺寸 Dimension	1005 (0.4mm*0.2mm)				0201 (0.6mm*0.3mm)		0402 (1.0mm*0.5mm)		0603 (1.6mm*0.8mm)	
容量/电压 Capacity/ Voltage	10V	16V	25V	50V	25V	50V	25V	50V	25V	50V
0.1pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
0.5pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
1pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
1.2pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
1.5pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
1.8pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
2.0pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
2.2pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
2.7pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
3.0pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
3.3pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
3.9pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
4.7pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
5.6pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
6.8pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
8.2pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
10pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
12pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
15pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
18pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
22pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
27pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
33pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
39pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
47pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
56pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
68pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
82pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
100pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
120pF					Y	Y	Y	Y	Y	Y
150pF					Y	Y	Y	Y	Y	Y
180pF					Y	Y	Y	Y	Y	Y
220pF					Y	Y	Y	Y	Y	Y
270pF					Y	Y	Y	Y	Y	Y
330pF					Y	Y	Y	Y	Y	Y
390pF					Y	Y	Y	Y	Y	Y
470pF					Y	Y	Y	Y	Y	Y
560pF					Y	Y	Y	Y	Y	Y
680pF					Y	Y	Y	Y	Y	Y
820pF							Y	Y	Y	Y
1nF							Y	Y	Y	Y
1.5nF									Y	Y
1.8nF									Y	Y
2.2nF									Y	Y
2.7nF									Y	Y
3.3nF									Y	Y
4.7nF									Y	Y
5.6nF									Y	Y
6.8nF									Y	Y
10nF									Y	Y

材料 Dielectric	C0G							
尺寸 Dimension	0805 (2.0mm*1.25mm)		1206 (3.2mm*1.6mm)		1210 (3.2mm*2.5mm)		1812 (4.5mm*3.2mm)	
容量/电压 Capacity/ Voltage	25V	50V	25V	50V	25V	50V	25V	50V
0.1pF	Y	Y	Y	Y				
0.2pF	Y	Y	Y	Y				
0.5pF	Y	Y	Y	Y				
1pF	Y	Y	Y	Y				
1.2pF	Y	Y	Y	Y				
1.5pF	Y	Y	Y	Y				
1.8pF	Y	Y	Y	Y				
2.2pF	Y	Y	Y	Y				
2.7pF	Y	Y	Y	Y				
3.3pF	Y	Y	Y	Y				
3.9pF	Y	Y	Y	Y				
4.7pF	Y	Y	Y	Y				
5.6pF	Y	Y	Y	Y				
6.8pF	Y	Y	Y	Y				
8.2pF	Y	Y	Y	Y				
10pF	Y	Y	Y	Y	Y	Y	Y	Y
12pF	Y	Y	Y	Y	Y	Y	Y	Y
15pF	Y	Y	Y	Y	Y	Y	Y	Y
18pF	Y	Y	Y	Y	Y	Y	Y	Y
22pF	Y	Y	Y	Y	Y	Y	Y	Y
27pF	Y	Y	Y	Y	Y	Y	Y	Y
33pF	Y	Y	Y	Y	Y	Y	Y	Y
39pF	Y	Y	Y	Y	Y	Y	Y	Y
47pF	Y	Y	Y	Y	Y	Y	Y	Y
56pF	Y	Y	Y	Y	Y	Y	Y	Y
68pF	Y	Y	Y	Y	Y	Y	Y	Y
100pF	Y	Y	Y	Y	Y	Y	Y	Y
120pF	Y	Y	Y	Y	Y	Y	Y	Y
150pF	Y	Y	Y	Y	Y	Y	Y	Y
180pF	Y	Y	Y	Y	Y	Y	Y	Y
220pF	Y	Y	Y	Y	Y	Y	Y	Y
270pF	Y	Y	Y	Y	Y	Y	Y	Y
330pF	Y	Y	Y	Y	Y	Y	Y	Y
390pF	Y	Y	Y	Y	Y	Y	Y	Y
470pF	Y	Y	Y	Y	Y	Y	Y	Y
560pF	Y	Y	Y	Y	Y	Y	Y	Y
680pF	Y	Y	Y	Y	Y	Y	Y	Y
820pF	Y	Y	Y	Y	Y	Y	Y	Y
1nF	Y	Y	Y	Y	Y	Y	Y	Y
1.5nF	Y	Y	Y	Y	Y	Y	Y	Y
1.8nF	Y	Y	Y	Y	Y	Y	Y	Y
2.2nF	Y	Y	Y	Y	Y	Y	Y	Y
2.7nF	Y	Y	Y	Y	Y	Y	Y	Y
3.3nF	Y	Y	Y	Y	Y	Y	Y	Y
4.7nF	Y	Y	Y	Y	Y	Y	Y	Y
6.8nF	Y	Y	Y	Y	Y	Y	Y	Y
8.2nF	Y	Y	Y	Y	Y	Y	Y	Y
10nF	Y	Y	Y	Y	Y	Y	Y	Y
12nF	Y	Y	Y	Y			Y	Y
22nF	Y	Y	Y	Y			Y	Y
33nF			Y	Y			Y	Y
47nF			Y	Y				
68nF			Y	Y				
82nF			Y	Y				
100nF			Y	Y				

***II 类电容器具体电压对应容量及厚度情况列表**

A list of the specific Voltage-specific capacitors of Class II capacitors

尺寸 Dimension	1005 (0.4mm*0.2mm)																								
材料 Dielectric	X7R 系列					X7S 系列					X7T 系列					X6S/X6T 系列					X5R 系列				
容量/电压 Capacity/ Voltage	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V
120pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
150pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
180pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
220pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
270pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
330pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
390pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
470pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
560pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
680pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
820pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
1nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
1.2nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
1.5nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
1.8nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
2.2nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
2.7nF						Y	Y	Y			Y	Y	Y			Y	Y	Y			Y	Y	Y		
3.3nF						Y	Y	Y			Y	Y	Y			Y	Y	Y			Y	Y	Y		
3.9nF						Y	Y	Y			Y	Y	Y			Y	Y	Y			Y	Y	Y		
4.7nF						Y	Y	Y			Y	Y	Y			Y	Y	Y			Y	Y	Y		
5.6nF						Y					Y					Y					Y	Y	Y		
6.8nF						Y					Y					Y					Y	Y	Y		
8.2nF						Y					Y					Y					Y	Y	Y		
10nF						Y					Y					Y					Y	Y	Y		
15nF						Y					Y					Y					Y	Y	Y		
22nF						Y					Y					Y					Y	Y	Y		
33nF						Y					Y					Y					Y	Y	Y		
47nF						Y					Y					Y					Y	Y	Y		
68nF						Y					Y					Y					Y	Y	Y		
100nF						Y					Y					Y					Y	Y	Y		
220nF																					Y				

尺寸 Dimension	0201 (0.6mm*0.3mm)																								
材料 Dielectric	X7R 系列					X7S 系列					X7T 系列					X6S/X6T 系列					X5R 系列				
容量/电压 Capacity/ Voltage	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V
100pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
120pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
180pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
220pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
330pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
470pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
560pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
680pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
1nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
2.2nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
3.9nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
4.7nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
5.6nF	Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y						
6.8nF	Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y						
10nF	Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y						

尺寸 Dimension	0201 (0.6mm*0.3mm)																								
材料 Dielectric	X7R 系列					X7S 系列					X7T 系列					X6S/X6T 系列					X5R 系列				
容量/电压 Capacity/ Voltage	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V
15nF	Y	Y	Y			Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y	
18nF	Y	Y	Y			Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y	
22nF	Y	Y	Y			Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y	
33nF						Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y	
47nF						Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y	
56nF						Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y	
68nF						Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y	
100nF						Y	Y	Y			Y	Y	Y			Y	Y	Y	Y		Y	Y	Y	Y	
220nF																Y	Y				Y	Y	Y		
330nF																Y					Y	Y	Y		
470nF																Y					Y	Y	Y		
1μF																Y					Y	Y	Y		
2.2μF																					Y	Y			
4.7μF																					Y				

尺寸 Dimension	0402 (1.0mm*0.5mm)																								
材料 Dielectric	X7R 系列					X7S 系列					X7T 系列					X6S/X6T 系列					X5R 系列				
容量/电压 Capacity/ Voltage	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V
330pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
470pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
560pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
680pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
1nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
2.2nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
3.9nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
4.7nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
5.6nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
6.8nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
10nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
15nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
18nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
22nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
33nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
47nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					Y
56nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					Y
68nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					Y
100nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
220nF	Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y	
330nF	Y	Y	Y			Y	Y	Y			Y	Y	Y			Y	Y	Y			Y	Y	Y	Y	
470nF	Y	Y	Y			Y	Y	Y			Y	Y	Y			Y	Y	Y			Y	Y	Y	Y	
680nF	Y	Y				Y	Y				Y	Y				Y	Y	Y			Y	Y	Y	Y	
1μF	Y	Y				Y	Y				Y	Y				Y	Y	Y			Y	Y	Y	Y	
2.2μF						Y					Y					Y	Y	Y			Y	Y	Y	Y	
4.7μF																Y	Y				Y	Y	Y		
6.8μF																Y					Y	Y			
10μF																Y					Y	Y			
22μF																					Y				

尺寸 Dimension	0603 (1.6mm*0.8mm)																								
材料 Dielectric	X7R 系列					X7S 系列					X7T 系列					X6S/X6T 系列					X5R 系列				
容量/电压 Capacity/ Voltage	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V
330pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
470pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
560pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
680pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
820pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
1nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
1.2nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
1.5nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
1.8nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
2.2nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
2.7nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
3.9nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
4.7nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
5.6nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
6.8nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
8.2nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
10nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
12nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
15nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
18nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
22nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
27nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
33nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
39nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
47nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
56nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
68nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
82nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
100nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
220nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
330nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
470nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
680nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
1μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
2.2 μF	Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y	Y
3.3 μF	Y	Y				Y	Y				Y	Y				Y	Y				Y	Y	Y	Y	
4.7 μF	Y	Y				Y	Y				Y	Y				Y	Y				Y	Y	Y	Y	
6.8 μF											Y					Y	Y				Y	Y	Y	Y	
10 μF											Y					Y	Y				Y	Y	Y	Y	
15 μF																Y					Y	Y			
22 μF																Y					Y	Y			
47μF																					Y				

尺寸 Dimension	0805 (2.0mm*1.25mm)																								
材料 Dielectric	X7R 系列					X7S 系列					X7T 系列					X6S/X6T 系列					X5R 系列				
容量/电压 Capacity/ Voltage	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V
330pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
470pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
560pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
680pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
820pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
1nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
1.2nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
1.5nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
1.8nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
2.2nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
2.7nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
3.3nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
3.9nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
4.7nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
5.6nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
6.8nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
8.2nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
10nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
15nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
18nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
22nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
33nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
47nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
56nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
68nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
82nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
100nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
220nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
330nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
470nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
680nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
1μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
2.2μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
3.3μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
4.7μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
6.8μF	Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y	Y
10μF	Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y	Y
15μF																Y	Y	Y			Y	Y	Y	Y	
22μF																Y	Y	Y			Y	Y	Y	Y	
47μF																Y					Y	Y			

尺寸 Dimension	1206 (3.2mm*1.6mm)																								
材料 Dielectric	X7R 系列					X7S 系列					X7T 系列					X6S/X6T 系列					X5R 系列				
容量/电压 Capacity/ Voltage	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V
330pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
470pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
560pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
680pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
820pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
1nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
1.2nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
1.5nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
1.8nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
2.2nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
2.7nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
3.3nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
3.9nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
4.7nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
5.6nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
6.8nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
8.2nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
10nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
12nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
15nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
18nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
22nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
33nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
47nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
56nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
68nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
82nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
100nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
220nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
330nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
470nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
680nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
1μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
2.2μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
3.3μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
4.7μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
6.8μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
10μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
15μF	Y	Y				Y	Y				Y	Y				Y	Y	Y	Y		Y	Y	Y	Y	
22μF	Y	Y				Y	Y				Y	Y				Y	Y	Y	Y		Y	Y	Y	Y	
47μF											Y					Y					Y	Y	Y		
100μF											Y					Y					Y				

尺寸 Dimension	1210 (3.2mm*2.5mm)																								
材料 Dielectric	X7R 系列					X7S 系列					X7T 系列					X6S/X6T 系列					X5R 系列				
容量/电压 Capacity/ Voltage	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V
330pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
470pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
560pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
680pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
820pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
1nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
1.2nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
1.5nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
1.8nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
2.2nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
2.7nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
3.3nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
3.9nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
4.7nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
5.6nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
6.8nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
8.2nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
10nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
12nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
15nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
18nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
22nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
33nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
47nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
56nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
68nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
82nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
100nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
220nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
330nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
470nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
680nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
820nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
1μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
2.2μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
3.3μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y					
4.7μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
6.8μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
10μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
15μF	Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y	Y		Y	Y	Y	Y
22μF	Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y		Y	Y	Y	Y	Y		Y	Y	Y	
47μF	Y	Y				Y	Y				Y	Y				Y	Y					Y	Y	Y	
100μF																						Y	Y		

尺寸 Dimension	1808 (4.5mm*2.0mm)																								
材料 Dielectric	X7R 系列					X7S 系列					X7T 系列					X6S/X6T 系列					X5R 系列				
容量/电压 Capacity/ Voltage	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V
330pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
470pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
560pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
680pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
820pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
1nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
1.2nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
1.5nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
1.8nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
2.2nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
2.7nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
3.9nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
4.7nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
5.6nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
6.8nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
8.2nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
10nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
12nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
15nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
18nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
22nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
33nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
47nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
56nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
68nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
82nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
100nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
120nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
150nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
180nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
220nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
330nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
470nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
680nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
1μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
2.2μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
3.3μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
4.7μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
6.8μF																					Y	Y	Y	Y	

尺寸 Dimension	1812 (4.5mm*3.2mm)																								
材料 Dielectric	X7R 系列					X7S 系列					X7T 系列					X6S/X6T 系列					X5R 系列				
容量/电压 Capacity/ Voltage	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V	6.3V	10V	16V	25V	50V
330pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
470pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
560pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
680pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
820pF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
1nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
1.2nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
1.5nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
1.8nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
2.2nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
3.9nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
4.7n	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
5.6nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
6.8nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
8.2nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
10nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
12n	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
15nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
18nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
22nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
27nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
33nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
47nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
56nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
68nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
82nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
100nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
220nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
330nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
470nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
680nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
820nF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
1μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
2.2μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
3.3μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
4.7μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
6.8μF	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
10μF																					Y	Y	Y	Y	Y

◆可靠性测试方法

Reliability Test Methods



二类介质规格测容量前需去老化处理：测试温度： $25^{\circ}\text{C}\pm 3^{\circ}\text{C}$ ，测试湿度： $<70\%\text{RH}$ 。电容器在 150°C 热处理 1 小时，放置 24h 后进行测量。

The second type of medium specification needs to be aged before measuring the capacity: test temperature: $25^{\circ}\text{C}\pm 3^{\circ}\text{C}$, test humidity: $< 70\%\text{RH}$. The capacitors were heat treated at 150°C for 1 hour and measured after 24 hours of placement.

项目 Item	技术规格 Technical Specification			测试方法 Test Method and Remarks					
容量 Capacitance	I类 Class I	应符合指定的误差级别 Should be within the specified tolerance.	标称容量 Capacitance		测试频率 Measuring Frequency		测试电压 Measuring Voltage		
			≤1000pF		1MHz±10%		1.0±0.2Vrms		
			> 1000 pF		1KHz±10%				
	II类 Class II	应符合指定的误差级别 Should be within the specified tolerance.	测试温度： 25℃±3℃ Test Temperature: 25℃±3℃ C≤10μF：测试频率：1KHz±10% 测试电压：1.0±0.2Vrms Test Frequency: 1KHz±10% Test Voltage: 1.0±0.2Vrms C> 10μF 测试频率：120±24 Hz 测试电压：0.5±0.1Vrms Test Frequency: 120±24 Hz Test Voltage: 0.5±0.1Vrms						
绝缘电阻 (IR) Insulation Resistance	I类 Class I	C≤10 nF, Ri≥50000MΩ C> 10 nF, Ri•CR≥500S	测试电压：额定电压（最高 500V） 测试时间：60±5 秒 测试湿度：≤75% 测试温度： 25℃±3℃ 测试充放电电流：≤50mA Measuring Voltage: Rated Voltage（Max 500V） Duration: 60±5s Test Humidity: ≤75% Test Temperature: 25℃±3℃ Test Current: ≤50mA						
	II类 Class II	C≤25 nF, Ri≥10000MΩ C> 25 nF, Ri•CR> 100S							
	注：S=Ω·F								
损耗角正切 (DF, tanδ) Dissipation Factor	I类 Class I	DF		标称容量 Capacitance		测试频率 Measuring Frequency		测试电压 Measuring Voltage	
		≤1/（400+20C）		C<30pF		1MHz±10% （C> 1000 pF, 1KHz±10%）		1.0±0.2Vrms	
		≤0.1%		C≥30pF					
损耗角正切 (DF, tanδ) Dissipation Factor	II类 Class II	电压 Voltage	DF(×10 ⁻⁴)	1005	0201	0402	0603	0805	1206 及以上 and above
		50V	≤250	——	——	≤10nF	<100nF	——	≤680nF
			≤350	——	≤3.3nF	≤47nF	<470nF	≤1uF	≤2.2uF
			≤500	——	≤10nF	≤0.1μF	——	——	——
			≤750	——	——	——	——	≤2.2uF	≤4.7uF
			≤1000	——	——	——	≤2.2μF	≤10μF	≤10μF
			25V	≤250	——	——	≤10nF	<100nF	——
		≤350		≤1nF	≤3.3nF	≤47nF	<470nF	≤1uF	——
		≤500		——	≤10nF	≤220nF	——	——	——
		≤750		≤10nF	>10nF	——	——	≤2.2μF	≤10μF
		≤1000		——	≤100nF	≤2.2μF	≤10μF	≤22μF	≤22μF
		≤1000		——	——	——	——	——	——

项目 Item	技术规格 Technical Specification							测试方法 Test Method and Remarks		
损耗角正切 (DF, tanδ) Dissipation Factor	II类 Class II	电压 Voltage	DF($\times 10^{-4}$)	1005	0201	0402	0603	0805	1206 及以上 and above	C≤10μF 测试频率: 1KHz±10% 测试电压: 1.0±0.2Vrms Test Frequency: 1KHz±10% Test Voltage: 1.0±0.2Vrms C>10μF X7R、X5R、X7T、X6S 测试频率: 120±24 Hz 测试电压: 0.5±0.1Vrms Test Frequency: 120±24Hz Test Voltage: 0.5 ±0.1Vrms
		16V	≤250	——	——	≤10nF	<100nF	——	≤680nF	
			≤350	≤1nF	≤3.3nF	≤47nF	<470nF	≤1uF	——	
			≤500	——	≤15nF	≤220nF	——	——	——	
			≤750	≤10nF	≤47nF	——	——	≤4.7μF	≤10μF	
			≤1000	≤100nF	≤100nF	≤4.7μF	≤10μF	≤22μF	≤47μF	
		10V	≤250	——	——	≤10nF	<100nF	——	≤680nF	
			≤350	≤1nF	≤3.3nF	≤47nF	<470nF	≤1uF	——	
			≤500	——	≤15nF	≤220nF	——	——	——	
			≤750	≤10nF	≤47nF	——	——	≤2.2μF	≤10μF	
			≤1000	≤100nF	≤1μF	≤10μF	≤22μF	≤47μF	≤100uF	
			≤1500	——	≤2.2μF	——	——	——	——	
		≤6.3 V	≤250	——	——	≤10nF	<100nF	——	≤680nF	
			≤350	≤1nF	≤3.3nF	≤47nF	<470nF	≤1uF	——	
			≤500	——	≤15nF	≤220nF	——	——	——	
			≤750	≤10nF	≤47nF	——	——	≤2.2uF	≤10μF	
			≤1000	≤100nF	≤1μF	≤10μF	≤47μF	≤47μF	≤100uF	
			≤1500	≤200nF	≤4.7μF	≤22μF	/	/	/	
			——	——	——	——	——	——	——	

介质耐电强度 (DW) Dielectric Withstanding Voltage	不应有介质被击穿或损伤 No breakdown or damage.	测量电压: I 类: 300%额定电压 II 类: 250%额定电压 时间: 1~5 秒 充/放电电流: 不应超过 50mA (这部分说明不包括中高压 MLCC) Measuring Voltage: Class I :300% Rated Voltage Class II :250% Rated Voltage Duration: 1~5s Charge/ Discharge Current: 50mA max. (This method excludes high-Voltage MLCC)
可焊性 Solderability	上锡率应大于 95% 外观: 无可见损伤。 At least 95% of the terminal electrode is covered by new solder. Visual Appearance: No visible damage.	将电容在 80~120℃的温度下预热 10~30 秒。 Preheating conditions:80 to 120℃; 10~30s. 无铅焊料: 浸锡温度: 245±5℃ 浸锡时间: 2±0.5s Lead-free soldering Solder Temperature: 245±5℃ Duration: 2±0.5s

项目 Item	技术规格 Technical Specification			测试方法 Test Method and Remarks															
耐焊接热 Resistance to Soldering Heat	项目 Item	I 类 Class I	II 类 Class II	将电容在 100~200℃ 的温度下预热 60~120 秒。 浸锡温度: 265±5℃ 浸锡时间: 10±1s 然后取出溶剂清洗干净, 在 10 倍以上的显微镜底下观察。 试验后放置时间: 24±2 小时。 放置条件: 室温 Preheating conditions: 100 to 200℃; 60~120 seconds. Solder Temperature: 265±5℃ Duration: 10±1s Clean the capacitor with solvent and examine it with a 10X(min.) microscope. Recovery Time: 24±2h. Recovery condition: Room temperature															
	ΔC/C	≤±2.5%或±0.25pF, 取较大值 ≤±2.5% or ±0.25PF, whichever is larger	±15%																
	DF	同初始标准 Same to initial value.																	
	IR	同初始标准 Same to initial value.																	
	外观: 无可见损伤 上锡率: ≥95% Appearance : No visible damage.at least 95% of the terminal electrode is covered by new solder.																		
抗弯曲强度 Resistance to Flexure of Substrate (Bending Strength)	ΔC/C: I 类: ≤±5%或±0. 5pF , 取两者中最大者 II 类: ≤±10% Class I : ≤±5% or ±0. 5pF,whichever is larger. Class II : ≤±10% 外观: 无可见损伤. Appearance: No visible damage.			试验基板: PCB 弯曲深度: 1mm 施压速度: 1mm/sec. 应在弯曲状态下进行测量。 Test Board: PCB Warp: 1mm Speed: 1mm/sec. The measurement should be made with the board in the bending position. 															
	外观无可见损伤 No visible damage.			如图所示: 慢慢施加一个 T 的力到电容侧面瓷体上, 并保持 60+1 秒。 As shown in the picture , Slowly apply a T force to the porcelain body on the side of the capacitor and hold for 60+1 seconds. <table><tr><th>规 格 Specification</th><th>施加力 T Apply force T</th></tr><tr><td>≤0402</td><td>2N</td></tr><tr><td>≥0603</td><td>5N</td></tr></table> 	规 格 Specification	施加力 T Apply force T	≤0402	2N	≥0603	5N									
规 格 Specification	施加力 T Apply force T																		
≤0402	2N																		
≥0603	5N																		
温度循环 Temperature Cycle	项目 Item	I 类 Class I	II 类 Class II	初始测量 Initial Measurement 循环次数: 5 次, 一个循环分以下 4 步: Cycling Times: 5 times, 1 cycle, 4 steps: <table><tr><th>阶段 Step</th><th>温度 (Temperature) (℃)</th><th>时间 (Time)</th></tr><tr><td>1</td><td>下限温度 (Low- category temp.): -55</td><td>30min</td></tr><tr><td>2</td><td>常温 (Normal temp.) : +20℃</td><td>2~3min</td></tr><tr><td>3</td><td>上限温度 (Up- category temp.) (C0G/X7R/X7T/X7S: +125 X5R: +85 X6S/X6T: +105)</td><td>30min</td></tr><tr><td>4</td><td>常温 (Normal temp.) : +20℃</td><td>2~3min</td></tr></table> 试验后放置 (恢复) 时间: 24±2h Recovery time after test: 24±2h	阶段 Step	温度 (Temperature) (℃)	时间 (Time)	1	下限温度 (Low- category temp.): -55	30min	2	常温 (Normal temp.) : +20℃	2~3min	3	上限温度 (Up- category temp.) (C0G/X7R/X7T/X7S: +125 X5R: +85 X6S/X6T: +105)	30min	4	常温 (Normal temp.) : +20℃	2~3min
	阶段 Step	温度 (Temperature) (℃)	时间 (Time)																
	1	下限温度 (Low- category temp.): -55	30min																
	2	常温 (Normal temp.) : +20℃	2~3min																
	3	上限温度 (Up- category temp.) (C0G/X7R/X7T/X7S: +125 X5R: +85 X6S/X6T: +105)	30min																
4	常温 (Normal temp.) : +20℃	2~3min																	
ΔC/C	≤±1%或±1PF, 取较大值 ≤±1% or ±1pF , whichever is larger	-15% ~+15%																	
外观无可见损伤 No visible damage.																			


项目 Item	技术规格 Technical Specification			测试方法 Test Method and Remarks																																					
耐湿负荷 Humidity load	$\Delta C/C$		I 类: $\pm 7.5\%$ 或 $\pm 0.75pF$,取两者之中较大者. II 类: : $\leq \pm 12.5\%$ Class I : $\pm 7.5\%$ or $\pm 0.75pF$, whichever is larger. Class II : $\leq \pm 12.5\%$		温度: $40\pm 2^{\circ}C$ 湿度: $90\sim 95\%RH$ 电压: 额定电压 时间: 500 小时 放置条件: 室温 放置时间: $24\pm 2h$ 小时; II 类: $0201\geq 47nF$ 、 $0402\geq 33nF$ 、 $0603\geq 1\mu F$ 、 $0805\geq 4.7\mu F$ 、 $1206\geq 10\mu F$ 产品试验后需在 $150^{\circ}C$ 温度下保持 1h , 再放置 $24\pm 2h$ 后测试电性能. Humidity: $90\sim 95\%RH$ Voltage: Rated Voltage Duration: 500h Recovery Time: $24h\pm 2h$ Class 2: $0201\geq 47nF$ 、 $0402\geq 33nF$ 、 $0603\geq 1\mu F$ 、 $0805\geq 4.7\mu F$ 、 $1206\geq 10\mu F$ product need to keep in $150^{\circ}C$ 、 1h after the test , and measurement to be made after being kept at room temperature for $24\pm 2h$.																																				
	DF		≤ 2 倍初始标准 Not more than twice of initial value.																																						
	IR	Class I	$Ri\geq 5000M\Omega$ 或 $Ri\cdot C_R\geq 50S$ 取两者之中较小者. $Ri\geq 5000M\Omega$ or $Ri\cdot C_R\geq 50S$ whichever is smaller.																																						
		Class II	$Ri\geq 1000M\Omega$ 或 $Ri\cdot C_R\geq 10S$ 取两者之中较小者. $Ri\geq 1000M\Omega$ or $Ri\cdot C_R\geq 10S$ whichever is smaller.																																						
	外观: 无损伤 Appearance: No visible damage.																																								
寿命试验 Life Test	$\Delta C/C$	I 类 Class I	$\leq \pm 3\%$ 或 $\pm 0.3pF$,取两者之中较大者 $\leq \pm 3\%$ or $\pm 0.3pF$, whichever is larger.																																						
		II 类 Class II	$-20\% \sim +20\%$																																						
	DF		≤ 2 倍初始标准 Not more than twice of initial value.																																						
	IR	I 类 Class I	$Ri\geq 4000M\Omega$ 或 $Ri\cdot C_R\geq 40S$ 取两者之中较小者 $Ri\geq 4000M\Omega$ or $Ri\cdot C_R\geq 40S$ whichever is smaller.																																						
		II 类 Class II	$Ri\geq 2000M\Omega$ 或 $Ri\cdot C_R\geq 50S$ 取两者之中较小者. $Ri\geq 2000M\Omega$ or $Ri\cdot C_R\geq 50S$ whichever is smaller.																																						
	外观: 无损伤 Appearance: No visible damage.			低压产品 ($<100V$) 时间: 1000 小时 电压: 2 倍额定工作电压, 除了表 1 外 温度: $125^{\circ}C$ (C0G、X7R、X7S) $85^{\circ}C$ (X5R) $105^{\circ}C$ (X6S、X6T) 充电电流: 不应超过 50mA. 放置时间: $24\pm 2h$ 小时; II 类: $0201\geq 47nF$ 、 $0402\geq 33nF$ 、 $0603\geq 1\mu F$ 、 $0805\geq 4.7\mu F$ 、 $1206\geq 10\mu F$ 产品试验后需在 $150^{\circ}C$ 温度下保持 1h , 再放置 $24\pm 2h$ 后测试电性能. Low-Voltage ($<100V$) Applied Voltage: $2\cdot U_r$, except the table 1 Duration: 1000h Temperature: $125^{\circ}C$ (C0G、X7R、X7S) $85^{\circ}C$ (X5R) $105^{\circ}C$ (X6S、X6T) Charge/ Discharge Current: 50mA max. Recovery Time: $24h\pm 2h$ Class 2: $0201\geq 47nF$ 、 $0402\geq 33nF$ 、 $0603\geq 1\mu F$ 、 $0805\geq 4.7\mu F$ 、 $1206\geq 10\mu F$ product need to keep in $150^{\circ}C$ 、1h after the test , and measurement to be made after being kept at room temperature for $24\pm 2h$.																																					
				<table><tr><th>容量 Capacitance</th><th>试验电压 Voltage</th></tr><tr><td>$100nF\leq 0201<220nF$</td><td rowspan="6">1.5Ur</td></tr><tr><td>$47nF\leq 0402<2.2uF$</td></tr><tr><td>$220nF\leq 0603<4.7uF$</td></tr><tr><td>$0.47uF\leq 0805<10uF$</td></tr><tr><td>$1uF\leq 1206<22uF$</td></tr><tr><td>$1uF\leq 1210<22uF$</td></tr><tr><td colspan="3"></td><td colspan="2"><table><tr><td>$0201\geq 220nF$</td><td rowspan="6">1.0Ur</td></tr><tr><td>$0402\geq 2.2uF$</td></tr><tr><td>$0603\geq 4.7uF$</td></tr><tr><td>$0805\geq 10uF$</td></tr><tr><td>$1206\geq 22uF$</td></tr><tr><td>$1210\geq 22uF$</td></tr></table></td></tr><tr><td colspan="3"></td><td colspan="2"></td></tr><tr><td colspan="3"></td><td colspan="2"></td></tr><tr><td colspan="3"></td><td colspan="2"></td></tr></table>		容量 Capacitance	试验电压 Voltage	$100nF\leq 0201<220nF$	1.5Ur	$47nF\leq 0402<2.2uF$	$220nF\leq 0603<4.7uF$	$0.47uF\leq 0805<10uF$	$1uF\leq 1206<22uF$	$1uF\leq 1210<22uF$				<table><tr><td>$0201\geq 220nF$</td><td rowspan="6">1.0Ur</td></tr><tr><td>$0402\geq 2.2uF$</td></tr><tr><td>$0603\geq 4.7uF$</td></tr><tr><td>$0805\geq 10uF$</td></tr><tr><td>$1206\geq 22uF$</td></tr><tr><td>$1210\geq 22uF$</td></tr></table>		$0201\geq 220nF$	1.0Ur	$0402\geq 2.2uF$	$0603\geq 4.7uF$	$0805\geq 10uF$	$1206\geq 22uF$	$1210\geq 22uF$															
	容量 Capacitance	试验电压 Voltage																																							
	$100nF\leq 0201<220nF$	1.5Ur																																							
	$47nF\leq 0402<2.2uF$																																								
$220nF\leq 0603<4.7uF$																																									
$0.47uF\leq 0805<10uF$																																									
$1uF\leq 1206<22uF$																																									
$1uF\leq 1210<22uF$																																									
			<table><tr><td>$0201\geq 220nF$</td><td rowspan="6">1.0Ur</td></tr><tr><td>$0402\geq 2.2uF$</td></tr><tr><td>$0603\geq 4.7uF$</td></tr><tr><td>$0805\geq 10uF$</td></tr><tr><td>$1206\geq 22uF$</td></tr><tr><td>$1210\geq 22uF$</td></tr></table>		$0201\geq 220nF$	1.0Ur	$0402\geq 2.2uF$	$0603\geq 4.7uF$	$0805\geq 10uF$	$1206\geq 22uF$	$1210\geq 22uF$																														
$0201\geq 220nF$	1.0Ur																																								
$0402\geq 2.2uF$																																									
$0603\geq 4.7uF$																																									
$0805\geq 10uF$																																									
$1206\geq 22uF$																																									
$1210\geq 22uF$																																									

◆包装

Package


* 塑料压纹带卷盘结构

Embossed Plastic Taping



* 仅适用于 1005 规格，压纹带尺寸如下：

The emboss plastic applies only to 1005 type, the dimensions as follows:




Unit: mm

代号 Code	W	P0	P1	E	F	D0	A0	B0	K0
01005	8±0.1	4±0.1	2±0.05	1.75±0.1	3.5±0.05	1.55±0.05	0.25±0.02	0.45±0.02	0.24±0.02


* 纸带卷盘结构

Paper Taping



* 1005、0201 纸带编带尺寸大小


Dimensions of paper taping for 1005、0201 type



代号 Code	A0	B0	W	F	E	P1	P2	P0	D0	T
1005	0.24 ± 0.02	0.45 ± 0.02	8.0 ± 0.10	3.50 ± 0.05	1.75 ± 0.10	2.0 ± 0.05	2.0 ± 0.05	4.0 ± 0.10	1.50 $-0/+0.10$	0.30 Below
0201	0.37 ± 0.10	0.67 ± 0.10	8.0 ± 0.10	3.50 ± 0.05	1.75 ± 0.10	2.0 ± 0.05	2.0 ± 0.05	4.0 ± 0.10	1.50 $-0/+0.10$	0.80 Below

* 适合 ‘0402、0603、0805、1206’ 常规尺寸产品的纸带尺寸

Dimensions of paper taping for 0402, 0603, 0805, 1206 types.




代 号 Code 纸带规格	A0	B0	W	F	E	P1	P2	P0	D0	T
0402	0.59 ± 0.03	1.12 ± 0.03	8.0 ± 0.10	3.5 ± 0.05	1.75 ± 0.10	2.0 ± 0.05	2 ± 0.05	4.0 ± 0.10	1.55 ± 0.05	0.60 ± 0.03
0603	0.95 ± 0.05	1.90 ± 0.05	8.0 ± 0.10	3.5 ± 0.05	1.75 ± 0.10	4.0 ± 0.05	2 ± 0.05	4.0 ± 0.10	1.55 ± 0.05	0.95 ± 0.03
0805	1.55 ± 0.05	2.30 ± 0.05	8.0 ± 0.10	3.5 ± 0.05	1.75 ± 0.10	4.0 ± 0.05	2 ± 0.05	4.0 ± 0.10	1.55 ± 0.05	0.95 ± 0.03
1206	1.85 ± 0.05	3.45 ± 0.05	8.0 ± 0.10	3.5 ± 0.05	1.75 ± 0.10	4.0 ± 0.05	2 ± 0.05	4.0 ± 0.10	1.55 ± 0.05	0.95 ± 0.03

注意：*表示此处对尺寸的要求非常精确。


Note: The place with “*” means where needs exactly dimensions.

* 塑胶卷盘结构

Embossed taping




* 塑胶带尺寸结构 (适合‘0805~1812’ 型产品)
 Dimensions of embossed tapping for 0805~1812 type



Unit: mm


代号Code 规格 Tape size	A	B	C	D*	E	F	G*	H	J	T
0805	1.40 + 0.10-0.05	2.25 ±0.10	8.00 + 0.10-0.03	3.5±0.05	1.75 ±0.10	4.0±0.1	2±0.05	4.0±0.10	1.55±0.05	1.35 + 0.1-0.03
1206	1.85 ±0.10	3.50 ±0.10	8.00 + 0.10-0.03	3.5±0.05	1.75 ±0.10	4.0±0.1	2±0.05	4.0±0.10	1.55±0.05	1.35 + 0.1-0.03
1206	1.88 ±0.10	3.53 ±0.10	8.00 + 0.10-0.03	3.5±0.05	1.75 ±0.10	4.0±0.1	2±0.05	4.0±0.10	1.55±0.05	1.80 + 0.1-0.03
1210	2.76 ±0.10	3.42 ±0.10	8.00 + 0.10-0.03	3.5±0.05	1.75 ±0.10	4.0±0.1	2±0.05	4.0±0.10	1.55±0.05	1.55 + 0.1-0.03
1808	2.20 + 0.10-0.03	4.95±0.10	12.00 + 0.10-0.03	5.5±0.05	1.75 ±0.10	8.0±0.1	2±0.05	4.0±0.1	1.55±0.05	1.80 + 0.1-0.03
1812	3.66 ±0.10	4.95±0.10	12.00 + 0.10-0.03	5.5±0.05	1.75 ±0.10	8.0±0.1	2±0.05	4.0±0.1	1.55±0.05	1.85±0.1
2220	5.70 ±0.10	6.20 ±0.10	12.00 + 0.10-0.03	5.5±0.05	1.75 ±0.10	8.0±0.1	2±0.05	4.0±0.1	1.55±0.05	2.0 + 0.15-0.03
2225	6.20 + 0.10-0.03	6.70 + 0.10-0.03	12.00 + 0.10-0.03	5.5±0.05	1.75 ±0.10	8.0±0.1	2±0.05	4.0±0.1	1.55±0.05	2.4 + 0.10-0.03

* 传送带的前后结构
 Structure of leader part and end part of the carrier paper



* 卷盘尺寸

Reel dimensions (unit: mm)




卷盘型号 Reel Code	A	B	C	D	E	F	G
7'REEL	$\phi 178 \pm 2.0$	3.0	$\phi 13 \pm 0.5$	$\phi 21 \pm 0.8$	$\phi 50$ 或更大 $\phi 50$ or more	10.0 ± 1.5	12max
13'REEL	$\phi 330 \pm 2.0$	3.0	$\phi 13 \pm 0.5$	$\phi 21 \pm 0.8$	92-100	10.0 ± 1.5	12max


* 关于卷带的说明：面胶剥离强度

Taping specification: top tape peeling strength

纸带 Paper Taping



* 塑料胶盘 Embossed Taping



标准: $0.1N < \text{剥离强度} < 0.7N$

Standard: $0.1N < \text{peeling strength} < 0.7N$

在剥离时，纸带不能有纸碎，也不能粘在底、面胶上。

No paper dirty remains on the scotch when peeling, and sticks to top and bottom tape.

* 包装数量

Packing Quantity

尺寸代码 SizeCode	厚度 (T) Thickness	7 寸纸带卷盘 (PT)	7 寸胶带卷盘 (ET)	13 寸纸带卷盘 (PT)	13 寸胶带卷盘 (ET)
1005	0.20±0.02	20000	—	—	
0201	0.30±0.03	10000	—	70000	
	0.30±0.09	10000	—	70000	
	0.50±0.05	10000	—	70000	
0402	0.50±0.05	10000	—	50000	
	0.50±0.15	10000	—	50000	
	0.50±0.20	10000	—	50000	
0603	0.80±0.10	4000	—	15000	
	0.80±0.20	4000	—	15000	
0805	0.80±0.20	4000	—	15000	—
	1.25±0.25	—	T≤1.35mm 3000 T>1.35mm 2000	—	10000
1206	0.80±0.20	4000	—	15000	—
	1.25±0.25	—	2000	—	10000
	1.60±0.30	—	2000	—	8000
1210	1.25±0.25	—	2000	—	8000
	1.60±0.30	—	2000	—	8000
	2.50±0.30	—	1000	—	8000
1808	1.60±0.30	—	2000	—	8000
	2.00±0.30	—	2000	—	8000
1812	1.60±0.30	—	T≤1.85mm 1000 T>1.85mm 500	—	3000
	2.00±0.30	—		—	3000

注意：包装的形式和数量可根据客户的要求来定。

Note: We can choose packing style and quantity can be according to the customer's requirement.

◆储存注意事项

*MLCC 的储存条件：相对湿度为 20~70%，储存温度为 5~40℃，建议温度低于 30℃。

*MLCC 的性能可能会受到储存条件的影响，交货后请立即使用。高温高湿条件、长期储存可能会导致包装材料变质、产品端头电极氧化。如自交付后已超过六个月，使用前检查包装、外观等。如果交付后超过一年，在使用前要检查可焊性。

* 不要将电容器存放在含有腐蚀性气体（例如硫化氢、二氧化硫、氯气、氨气等）的环境中。

* 不要在阳光直射下或高湿度条件下储存电容器。

◆ Storage Precautions

* Storage Conditions for MLCC: Relative humidity: 20~70%, storage temperature: 5~40℃, recommended temperature is below 30℃.

* The performance of MLCCs may be affected by storage conditions. Please use immediately after delivery. High temperature and high humidity conditions, or long-term storage, may lead to packaging material deterioration and oxidation of the product's end electrodes. If it has been over six months since delivery, check the packaging and appearance before use. If it has been over a year, check the solderability before use.

* Do not store capacitors in environments containing corrosive gases (e.g., hydrogen sulfide, sulfur dioxide, chlorine, ammonia, etc.).

* Do not store capacitors under direct sunlight or in high humidity conditions.

◆使用前注意事项

*安装前的信息

- 1、不要重复使用从设备上拆下的电容器。
- 2、确认额定容量、额定电压等电气特性。
- 3、确认施加电压下的电容特性。
- 4、确认使用下的机械应力。
- 5、确认长期存放的电容器的可焊性。
- 6、在测量电容之前，对长期存放的电容器进行热处理。

◆ Precautions Before Use

Pre-installation Information

- 1、Do not reuse capacitors removed from equipment.
- 2、Confirm electrical characteristics such as rated capacitance and rated Voltage.
- 3、Confirm the capacitor characteristics under applied Voltage.
- 4、Confirm the mechanical stress under use conditions.
- 5、Confirm the solderability of capacitors stored for long periods.
- 6、Perform heat treatment on capacitors that have been stored for a long time before measuring capacitance.

◆应用限制 Application Restrictions

1、我们的产品旨在用于一般消费电子设备(例如家用电器、办公设备、信息和通信设备, AV 设备、OA 设备、包括但不限于手机和 PC 等), 产品的设计基于正常操作和使用条件下的通用应用和标准用途。

2、不推荐用于下列高可靠性应用场景, 包括但不限于: 航天设备、医疗设备、航空设备、原子能设备、灾难预防设备、犯罪预防设备、电加热设备、燃烧设备、公共信息网络设备、数据处理设备、军事设备、发电控制设备、安全设备、车载设备、交通信号设备、运输设备和海底设备。

3、除非您事先获得邦科的书面同意, 否则邦科不对您或第三方因将我们的产品用于第 2 点设备而产生的任何损害承担任何责任。

1、Our products are intended for use in general consumer electronic devices (such as household appliances, office equipment, information and communication devices, AV equipment, OA equipment, including but not limited to mobile phones and PCs), based on general applications and standard uses under normal operating and usage conditions.

2、Our products are not recommended for the following high-reliability application scenarios, including but not limited to: aerospace equipment, medical devices, aviation equipment, atomic energy equipment, disaster prevention equipment, crime prevention equipment, electric heating equipment, combustion equipment, public information network devices, data processing equipment, military equipment, power generation control equipment, safety equipment, vehicle-mounted devices, traffic signal equipment, transportation equipment, and underwater equipment.

3、Unless you have prior written consent from Bangke, Bangke is not liable for any damages caused to you or third parties by using our products in the devices mentioned in point 2.

* 焊接的条件与相关图表

Soldering Condition and Profile

为避免因温度的突然变化而引起的芯片开裂或局部爆炸的现象发生, 请按有关温度曲线图表来进行。(请参考附页中的图表)

To avoid the crack problem by sudden temperature change, follow the temperature profile in the adjacent graph (refer to the graph in the enclosure page).

* 手工焊接

Manual Soldering

手工焊接很容易因为芯片局部受热不均而引起瓷体微裂或局部爆炸的现象, 在焊接时, 如果操作者不小心, 会使烙铁头直接同电容芯片的瓷体部分接触, 这样很容易使电容芯片因热冲击而受损或出现其他意外. 因此, 使用电烙铁手工焊接时应仔细操作, 并对电烙铁的尖端的选择和尖端温度控制应多加小心.


Manual soldering can pose a great risk of creating thermal cracks in capacitors. The hot soldering iron tip comes into direct contact with the end terminations, and operator's careless may cause the tip of the soldering iron to come into direct contact with the ceramic body of the capacitor. Therefore the soldering iron must be handled carefully, and pay much attention to the selection of the soldering iron tip and temperature contact of the tip.

* 推荐焊料用量

Recommended Soldering amounts


回流焊接的最佳焊料用量

The optimal solder fillet amounts for re-flow soldering




波峰焊接的最佳焊料用量

The optimal solder fillet amounts for wave soldering



使用烙铁返修时的最佳焊料量

The optimal solder fillet amounts for reworking by using soldering iron



* 推荐焊接方式

Recommended Soldering Method

规格尺寸 Size	温度特性 Temperature Characteristics	容量范围 Capacitance	焊接方式 Soldering Method
1005	C0G	/	R
	X7R/X5R/X7T/X6S	/	R
0201	C0G	/	R
	X7R/X5R/X7T/X6S	/	R

*推荐焊接方式

Recommended Soldering Method


规格尺寸 Size	温度特性 Temperature Characteristics	容量范围 Capacitance	焊接方式 Soldering Method
0402	C0G	/	R
	X7R/X5R/X7T/X6S	/	R
0603	C0G	/	R/W
	X7R/X5R/X7T/X6S	$C \geq 1\mu\text{f}$	R
		$C < 1\mu\text{f}$	R/W
0805	C0G	/	R/W
	X7R/X5R/X7T/X6S	$C \geq 4.7\mu\text{f}$	R
		$C < 4.7\mu\text{f}$	R/W
1206	C0G	/	R/W
	X7R/X5R/X7T/X6S	$C \geq 10\mu\text{f}$	R
		$C < 10\mu\text{f}$	R/W
≥ 1210	C0G	/	R
	X7R/X5R/X7T/X6S	/	R

焊接方式 Soldering method: R—回流焊 Reflow soldering W—波峰焊 Wave Soldering

*推荐回流焊盘尺寸（单位：mm）

Recommended reflow pad size (Unit: mm)


电容产品尺寸 Capacitor product size			焊盘尺寸 Pad size		
规格代码 SizeCode	L	W	A	B	C
1005	0.40 ± 0.02	0.20 ± 0.02	$0.16 \sim 0.20$	$0.12 \sim 0.18$	$0.20 \sim 0.23$
0201	0.60 ± 0.03	0.30 ± 0.03	$0.20 \sim 0.25$	$0.20 \sim 0.30$	$0.20 \sim 0.35$
	0.60 ± 0.09	0.30 ± 0.09	$0.23 \sim 0.30$	$0.25 \sim 0.35$	$0.30 \sim 0.40$
0402	1.00 ± 0.05	0.50 ± 0.05	$0.30 \sim 0.50$	$0.35 \sim 0.45$	$0.40 \sim 0.60$
	1.00 ± 0.15	0.50 ± 0.15	$0.40 \sim 0.60$	$0.40 \sim 0.50$	$0.50 \sim 0.70$
	1.00 ± 0.20	0.50 ± 0.20			
0603	1.60 ± 0.10	0.80 ± 0.10	$0.60 \sim 0.80$	$0.60 \sim 0.70$	$0.60 \sim 0.80$
	1.60 ± 0.20	0.80 ± 0.20	$0.70 \sim 0.90$	$0.70 \sim 0.80$	$0.80 \sim 1.00$
0805	2.00 ± 0.20	1.25 ± 0.25	$1.00 \sim 1.40$	$0.60 \sim 0.80$	$1.20 \sim 1.40$
1206	3.20 ± 0.30	1.60 ± 0.30	$1.90 \sim 2.10$	$1.00 \sim 1.30$	$1.60 \sim 1.90$
1210	3.20 ± 0.30	2.50 ± 0.30	$2.00 \sim 2.40$	$1.00 \sim 1.30$	$2.50 \sim 2.80$
1808	4.50 ± 0.40	2.00 ± 0.20	$2.50 \sim 3.50$	$1.00 \sim 1.80$	$2.30 \sim 3.50$
1812	4.50 ± 0.40	3.20 ± 0.30	$2.50 \sim 3.50$	$1.00 \sim 1.80$	$2.30 \sim 3.50$



◆ 推荐焊接温度曲线图

The temperature profile for soldering


* 回流焊接（Re-flow soldering）



在预热时，请将焊接温度与芯片表面温度之间的温差维持在 $T \leq 150^\circ\text{C}$ 。

While in preheating, please keep the temperature difference between soldering temperature and surface temperature of chips as: $T \leq 150^\circ\text{C}$.

* 波峰焊接 (Wave soldering)




在预热时, 请将焊接温度与芯片表面温度之间的温差维持在 $T \leq 150^{\circ}\text{C}$ 。

While in preheating, please keep the temperature difference between soldering temperature and surface temperature of chips as: $T \leq 150^{\circ}\text{C}$.

* 手工焊接

Hand soldering



条件 Conditions:

预热 Preheating	烙铁头温度 Temperature of soldering iron head	烙铁功率 Power of soldering iron	烙铁头直径 Diameter of soldering iron head	焊接时间 Soldering time	锡膏量 Solder paste amount	限制条件 Restricted conditions
$\Delta \leq 130^{\circ}\text{C}$	最高 350°C Highest temperature: 350°C	最大 20W 20W at the highest	建议 1mm 1mm recommended	最长 3s 3s at the longest	$\leq 1/2$ 芯片厚度 $\leq 1/2$ chip thickness	请勿使用烙铁头直接接触陶瓷元件 Please avoid the direct contact between soldering iron head and ceramic components

* 备注: 产品规格书仅供设计选型参考用, 不作为交货依据。

Note: The product specification is for design and selection reference only and shall not serve as a basis for delivery.