


L1+B1+G1

SMD ANTENNA

GNSS  1560-1605MHz

Dimensions: 10.0 x 3.0 x 1.6 mm

Clearance Area: 15 x 27 mm



Model: ADGP001
PN: M01-X031031G16





Table of Contents

1 FEATURES & BENEFITS.....	1
2 APPLICATIONS.....	1
3 ORDER INFORMATION.....	1
4 GNSS FREQUENCY BANDS.....	2
5 REFERENCE GUIDE.....	3
6 EVALUATION BOARD WITH THE ANTENNA.....	3
7 MATCHING NETWORK.....	4
8 RECOMMENDED LAYOUT.....	4
9 ELECTRICAL PERFORMANCE.....	5
9.1 VSWR and Return Loss (dB).....	5
9.2 Gain (dBi) and Total Efficiency (%).....	6
9.3 Radiation Patterns	8
10 SOLDERING CONDITIONS.....	11
11 PACKAGING.....	11
11.1 Optimal Storage Conditions for Packaged Reels.....	11
11.2 Packagings and Dimensions (Unit: mm).....	13
12 ANTENNA CERTIFICATION.....	14
13 WELCOME ALL ANTENNA OEM/ODM PROJECTS.....	15

www.aboosty.com

The materials provided herein, which are intended for illustration purposes only, are believed to be reliable and correct. However, no responsibility is further assumed for inaccuracies or incompleteness, and all such information shall be entirely at the user's risk. All information is subject to change without prior notice.

Copyright © 2024 ShenZhen MyAntenna RF Technology Co., Ltd. All Rights Reserved.



1 FEATURES & BENEFITS

- Low Profile
- Light Weight
- Easy to Integrate
- Intended for SMD Mounting
- Reduced Cost and Time-to-Market
- Covering Bands: GPS (L1) / Galileo (E1) / BeiDou (B1)

2 APPLICATIONS

- Satellite Navigation Receivers
- Geodetic Surveying and Mapping
- Channel Surveying and Mapping
- Precision Agriculture
- Marine Surveying
- Asset and Fleet Tracking
- Oil, Gas, and Mining Industries
- M2M Applications
- Hand-held/Portable Devices

Top		Bottom	
Items	Dimensions (mm)		
Length	10.0±0.1		
Width	3.0±0.1		
Thickness	1.6±0.1		


3 ORDER INFORMATION

Product Name	L1+B1+G1 SMD ANTENNA
Part Number	ADGP001
Dimensions	10.0 x 3.0 x 1.6mm
Mounting	SMT
Packaging	Tape & Reel
MOQ	1000 pcs/reel

4 GNSS FREQUENCY BANDS

GNSS Frequency Bands Covered					
GPS	L1	L2	L5		
	●	○	○		
GLONASS	G1	G2	G3		
	○	○	○		
Galileo	E1	E5a	E5b	E6	
	●	○	○	○	
Bei Dou	B1I	B1C	B2a	B2b	B3
	●	●	○	○	○
QZSS (Regional)	L1	L2C	L5	L6	
	●	○	○	○	
IRNSS(Regional)	L5				
	○				
SBAS	L1/E1/B1	L5/B2a/E5a	G1	G2	G3
	●	○	○	○	○

*SBAS systems: WASS(L1/L5), EGNOS(E1/E5a), SDCM(G1/G2/G3), SNAS(B1,B2a), GAGAN(L1/L5), QZSS(L1/L5), KAZZ(L1/L5).




5 REFERENCE GUIDE

Frequency	1560-1605 MHz
VSWR	1.5 : 1
Peak Gain (dBi)	0.33
Peak Efficiency(%)	49.31
Polarization	Linear
Radiation Pattern	Omnidirectional
Input Impedance	50 Ω
Operating Temperature	-40°C to +85°C
Storage Temperature	-40°C to +85°C
Material Substance Compliance	REACH/RoHs Compliant


All data were measured in free space and on a reference ground plane of 85 mm length, 27 mm width, and 1.0 mm thickness. Application data might vary.

6 EVALUATION BOARD WITH THE ANTENNA


The evaluation board provides operation at 1560-1605 MHz.
Evaluation Board dimension: 85.0 x 27.0 x 1.0 mm
Clearance Area: 15 x 27 mm



7 MATCHING NETWORK



8 RECOMMENDED LAYOUT




9 ELECTRICAL PERFORMANCE



© Note

The data displayed in Chapter 8 were measured in free space and on a reference ground plane of 85 mm length, 27 mm width, and 1.0 mm thickness.

9.1 VSWR and Return Loss (dB)




9.2 Gain (dBi) and Total Efficiency (%)






Frequency(MHz)	Gain (dBi)	Efficiency (%)
1560	-0.06	45.89
1565	-0.04	46.27
1570	0.03	46.89
1575	0.07	47.15
1580	0.14	47.33
1585	0.21	47.79
1590	0.2	47.69
1595	0.21	47.72
1600	0.33	49.31
1605	0.26	47.43

9.3 Radiation Patterns




PCB board size: 85 mm x 27 mm x 1.0mm


$\theta = 90^\circ$ Plane XY at 1561 MHz, Gain -0.06 dBi




$\phi = 0^\circ$ Plane XZ at 1561 MHz, Gain -0.06 dBi




$\phi = 90^\circ$ Plane YZ at 1561 MHz, Gain -0.06 dBi







PCB board size: 85 mm x 27 mm x 1.0mm




$\theta = 90^\circ$ Plane XY at 1575 MHz, Gain 0.07 dBi




$\phi = 0^\circ$ Plane XZ at 1575 MHz, Gain 0.07 dBi




$\phi = 90^\circ$ Plane YZ at 1575 MHz, Gain 0.07 dBi







PCB board size: 85 mm x 27 mm x 1.0mm




$\theta = 90^\circ$ Plane XY at 1602 MHz, Gain 0.31 dBi



$\phi = 0^\circ$ Plane XZ at 1602 MHz, Gain 0.31 dBi



$\phi = 90^\circ$ Plane YZ at 1602 MHz, Gain 0.31 dBi




10 SOLDERING CONDITIONS

This antenna is suitable for lead free soldering.

The reflow duration should be adjusted to create good solder joints without raising the antenna temperature beyond the allowed maximum of 260°C.

The figure below shows the temperature profile for soldering.



11 PACKAGING

11.1 Optimal Storage Conditions for Packaged Reels


Temperature	-5°C to 40°C
Humidity	Less than 70% RH
Shelf life	18 months
Storage place	Away from corrosive gas and direct sunlight
Packaging	Reels should be stored in unopened sealed manufacturer's plastic packaging.

© **Note**

Storage of open reels of antennas is not recommended due to possible oxidization of pads on antennas. If short-term storage is necessary, then it is highly recommended that the bag containing the antenna reel is re-sealed and stored in like storage conditions as in the above table.



10.2 Packagings and Dimensions (Unit: mm)





12 ANTENNA CERTIFICATION

RoHS Approval	Compliant [2011/65/EU&2015/863]
REACH Approval	Conform or declared [(EC)1907/2006]
Hazardous material regulation conformance: A certificate of conformance is available upon request. Feel free to consult us for details.	

13 WELCOME ALL ANTENNA OEM/ODM PROJECTS

About ABOOSTY



10+ years in antenna R&D, production, and OEM/ODM



House of Aboosty: 1 M+ units annual output capacity



Factory directly competitive price



Industry-leading quality levels



Professional team-work & support



Quick price and lead time estimation

Why Choose ABOOSTY



Innovative and patented design solutions



Full terminal devices anechoic chamber test



Co-location with its custom



Competitive price



Strict inspection




Prompt reply within 24h

What We Provide

OEM/ODM Services	
Light Customization	Deep Customization
<ul style="list-style-type: none"> • Logo • Packaging • Cables&Connectors 	<ul style="list-style-type: none"> • In-depth tailoring for specific applications • Functional enhancements • Environmental adaptations • Vertical certifications • ...

Custom Process

Light Customization Process



Deep Customization Process

- Start-up Phase
- Samples Phase
- Production and Delivery
- Life-cycle Management

