

GENERAL DESCRIPTION

The LW81XX Series is a group of voltage regulators with high accuracy, high speed, low drop-out, reverse current protection, high ripple rejection and fast discharge function.

The series consists of a voltage reference, an error amplifier, a driver transistor, a current limiter, a thermal protection circuit, a reverse current protection circuit and a phase compensation circuit.

Output voltage is selectable from 0.8V to 5.0V which fixed by laser trimming technologies, Step=100mV.

The LW81XX Series is available in DFN2x2-6L, SOT23-5L and SOT89-5L packages.


FEATURES

- Output Accuracy: $\pm 1.0\%$
- Low Quiescent Current: 28uA
- Low Dropout Voltage: 143mV@500mA/3.3V
- High PSRR: 78dB@1KHz, 10mA
- Output Current: 750mA
- Excellent Line and Load Transient Response
- Operating Voltage Range: from 1.8V to 7.0V
- Output Voltage Range: from 0.8V to 5.0V
- Over-Temperature Protection
- Current Limiting Protection
- Output Short-Circuit Protection
- Reverse Current Protection Function
- Available in DFN2x2-6L, SOT23-5L and SOT89-5L Packages


APPLICATIONS

- Battery-Powered Devices
- Reference Voltage Sources
- USB products and HDMI Equipments
- Other Low Voltage Power Suppliers

TYPICAL APPLICATION CIRCUIT




TYPICAL PERFORMANCE CHARACTERISTICS




PIN DESCRIPTION:

PIN No			SYMBOL	DESCRIPTION
DFN2x2-6L	SOT23-5L	SOT89-5L		
1	1	4	VIN	Power Supply Input
5	2	2	GND	Ground
6	3	1	EN	Chip Enable
2,4	4	3	NC	Not Connected
3	5	5	VOUT	Output
Thermal pad	--	--	Pad	Connect the thermal pad to a large area GND plane


PIN ASSIGNMENT



DFN2x2-6L



SOT23-5L



SOT89-5L

MARK INFORMATION:

DFN2X2-6L

XX: VOLTAGE

YY: DATE CODE

LW81XX
YYYYY

SOT23-5L

XX: VOLTAGE

YY: DATE CODE

LW81XX
YYYYY

SOT89-5L

X: VOLTAGE

YY: DATE CODE

LW81XX
YYYYY

ABSOLUTE MAXIMUM RATINGS ⁽¹⁾:(T_A =25℃, unless otherwise specified.)

SYMBOL	ITEM		RATING	UNIT
V _{IN}	Supply Voltage		-0.3~8.0	V
V _{EN}	EN Pin Voltage		-0.3~8.0	V
V _{OUT}	VOUT pin Voltage		-0.3~ (V _{IN} +0.3)	V
V _(ESD)	ESD Susceptibility, HBM ⁽²⁾		± 4000	V
P _D	Maximum Power Dissipation ⁽³⁾	DFN2x2-6L	1.56	W
		SOT23-5L	0.59	
		SOT89-5L	1.64	
R _{θJA}	Package Thermal Resistance Θ _{JA} ⁽³⁾	DFN2x2-6L	80	℃/W
		SOT23-5L	210	
		SOT89-5L	76	
T _J	Junction Temperature Range		-40~150	℃
T _{STG}	Storage Temperature Range		-40~150	℃
T _{SOLDER}	Lead Temperature (Soldering)		260℃, 10s	

Note:

1. Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability
2. per ANSI/ESDA/JEDEC JS-001
3. Device mounted on FR-4 PCB

RECOMMENDED OPERATING RANGE:

SYMBOL	ITEM	VALUE	UNIT
V _{IN}	VIN Supply Voltage	1.8~7.0	V
V _{EN}	EN Pin Voltage	0~7.0	V
V _{OUT}	VOUT Pin Voltage	0.8~5.0	V
I _{OUT}	Output Current	0~0.75	A
T _J	Junction Temperature Range	-40~125	℃

ELECTRICAL CHARACTERISTICS:


($V_{IN}=V_{OUT}+1V$, $V_{OUT}=3.3V$, $C_{IN}=C_{OUT}=1\mu F$, $T_A=25^{\circ}C$, unless otherwise specified.)

Symbol	Parameter	Conditions	MIN	TYP	MAX	Units
V_{IN}	Input Voltage		1.8		7.0	V
V_{OUT}	Output Accuracy	$I_{OUT}=1mA$	-1.0		+1.0	%
I_{LIM}	Current Limit ⁽¹⁾	$V_{IN}=4.3V$, $V_{OUT}=3.3V$	0.8	1.05		A
I_Q	Quiescent Current	$V_{IN}=V_{EN}=V_{OUT}+1V$, No Load		28	45	μA
I_{SHD}	Shutdown Current	$V_{IN}=7.0V$, $V_{EN}=0V$			0.1	μA
V_{DROP}	Dropout Voltage ⁽²⁾	$I_{OUT}=300mA$		84		mV
		$I_{OUT}=500mA$		143		
		$I_{OUT}=750mA$		221		
S_{LINE}	Line Regulation	$V_{IN}=V_{OUT}+1V$ to $7.0V$, $I_{OUT}=1mA$		0.05	0.1	%/V
S_{LOAD}	Load Regulation	$1mA \leq I_{OUT} \leq 750mA$		0.001	0.01	%/mA
I_{SHORT}	Short Current	$V_{OUT}=0V$		70		mA
V_{ENH}	EN High Voltage	$V_{IN}=1.8V$ to $7.0V$, $I_{OUT}=1mA$	1.5			V
V_{ENL}	EN Low Voltage				0.5	V
T_{STR}	Startup Time	From V_{EN} 'L' $\rightarrow$ 'H' to $95\% \cdot V_{OUT}$, $C_{OUT}=1\mu F$, No Load		50		μs
PSRR	Power Supply Rejection Ratio	$C_{IN}=None$, $V_{OUT}=3.3V$, $I_{OUT}=10mA$	$f=217Hz$	79		dB
			$f=1KHz$	78		
			$f=10KHz$	72		
I_{REV}	Reverse Current ⁽³⁾	$V_{IN}=0V$, $V_{OUT}=7.0V$		0.01	0.5	μA
I_{REVS}	V_{OUT} Pin Sink Current ⁽⁴⁾	$V_{IN}=6.0V$, $V_{OUT}=7.0V$		1.5	2.5	μA
T_{SD}	Thermal Shut Down	Temperature rising		160		$^{\circ}C$
ΔT_{SD}	TSD Hysteresis	Temperature falling		20		$^{\circ}C$
$R_{DISCHRG}$	R_{ON} of Discharge MOSFET	$V_{EN}=0V$		80		Ω

NOTES:

1. Guaranteed by design
2. The dropout voltage is defined as $V_{IN} - V_{OUT}$, when $V_{OUT}=95\% \cdot V_{OUT(NOM)}$
3. Reverse Current (I_{REV}) flows from V_{OUT} to V_{IN}
4. V_{OUT} Pin Sink Current (I_{REVS}) flows from V_{OUT} to GND

SIMPLIFIED BLOCK DIAGRAM:



DETAIL OPERATION DESCRIPTION:

The LW81XX Series is a low noise, high PSRR, low drop-out voltage regulator. It consists of a current limiter circuit, a driver transistor, a precision voltage reference, a thermal protection circuit, a reverse current protection circuit and an error correction circuit, and is compatible with low ESR ceramic capacitors. The current limiter's fold-back circuit operates as a short circuit protection as well as the output current limiter.

Reverse Current Protection

The LW81XX series includes reverse current protection to prevent the damage as a result of current flow from VOUT pin to the VIN pin when the power supply is connected to the VOUT pin. When VIN is smaller than VOUT, the reverse current protection works and suppress the reverse current to 0.5μA (MAX.). When VIN is smaller than VOUT, the VOUT pin sink current flowing from the VOUT pin to the GND pin is 1.5μA (TYP.) as the IC operation current. Please also note when an external power supply is connected to the VOUT pin, please use it within 7.0V.

Current Limiting and Short-Circuit Protection

The current limit circuitry prevents damage to the MOSFET switch and the hub downstream port but can deliver load current up to the current limit

threshold through the switch. When a heavy load or short circuit is applied to an enabled switch, a large transient current may flow until the current limit circuitry responds. Once this current limit threshold is exceeded the device enters constant current mode until the thermal shutdown occurs or the fault is removed.

Thermal Shutdown

When the junction temperature of the built-in driver transistor reaches the temperature limit level (160°C TYP.), the thermal shutdown circuit operates and the driver transistor will be turned OFF. The IC resumes its operation when the thermal shutdown function is released and the IC's operation is automatically restored because the junction temperature drops to the level of 140°C (TYP.) as the thermal shutdown release threshold.

Chip Enable


The LW81XX series can be turned off via the EN pin signal. In shutdown mode, output at the VOUT pin will be pulled down to the GND.







The LW81XX series has a pull-down resistor in order to operate normally even the EN pin is floating.

If the EN pin voltage is set with the specified voltage range, the logic is fixed and the IC will operate normally.

TYPICAL OPERATING CHARACTERISTICS:

(Tested under $T_A = 25^\circ\text{C}$, unless otherwise specified)








Figure 13. Dropout Voltage VS I_{OUT}




Figure 14. V_{OUT} VS V_{IN}




Figure 15. V_{OUT} VS V_{IN}







Figure 16. V_{OUT} VS V_{IN}



Channel 1 = I_{OUT} , channel 2 = V_{OUT} , V_{IN} = 1.8V, V_{OUT} = 0.8V
Figure 17. Load Transient (1 mA to 750 mA)




Channel 1 = I_{OUT} , channel 2 = V_{OUT} , V_{IN} = 1.8V, V_{OUT} = 0.8V
Figure 18. Load Transient (750 mA to 1 mA)




Channel 1 = I_{OUT} , channel 2 = V_{OUT} , $V_{IN}=4.3V$, $V_{OUT}=3.3V$

Figure 19. Load Transient (1 mA to 750 mA)




Channel 1 = I_{OUT} , channel 2 = V_{OUT} , $V_{IN}=4.3V$, $V_{OUT}=3.3V$

Figure 20. Load Transient (750 mA to 1 mA)




Channel 1 = I_{OUT} , channel 2 = V_{OUT} , $V_{IN}=6.0V$, $V_{OUT}=5.0V$

Figure 21. Load Transient (1 mA to 750 mA)




Channel 1 = I_{OUT} , channel 2 = V_{OUT} , $V_{IN}=6.0V$, $V_{OUT}=5.0V$

Figure 22. Load Transient (750 mA to 1 mA)




Channel 1 = En, channel 2 = V_{OUT} , $V_{OUT}=1.8V$, No Load

Figure 23. Power-Up with Enable




Channel 1 = En, channel 2 = V_{OUT} , $V_{OUT}=3.3V$, No Load

Figure 24. Power-Up with Enable



Channel 1 = En, channel 2 = V_{OUT} , $V_{OUT}=5.0V$, No Load

Figure 25. Power-Up with Enable



$V_{OUT}=3.3V$, $V_{IN}=4.3V$, $V_{PP}=0.2V$, $C_{IN}=non$, $C_{OUT}=1\mu F$

Figure 26. PSRR vs Frequency




Figure 27. Output Noise Density vs Frequency

APPLICATION INFORMATION:

● Input Capacitor Selection

Like any low-dropout regulator, the external capacitors used with the LW81XX Series must be carefully selected for regulator stability and performance. Using a capacitor whose value is $\geq 1\mu\text{F}$ on the LW81XX Series input and the amount of capacitance can be increased without limit. An at least $10\mu\text{F}$ input capacitor is needed if input ripple voltage $V_{pp} > 1\text{V}$. The input capacitor must be located a distance less than 0.5 inch from the input pin of the IC and returned to a clean analog ground. Any good quality ceramic or tantalum can be used for this capacitor. The capacitor with larger value and lower ESR (equivalent series resistance) provides better PSRR and line-transient response.

● Layout considerations

To improve ac performance such as PSRR, output noise, and transient response, it is recommended that the PCB be designed with separate ground planes for VIN and VOUT, with each ground plane connected only at the GND pin of the device.

● Output Capacitor Selection

The output capacitor must meet both requirements for minimum amount of capacitance and ESR in all LDOs application. The LW81XX Series is designed specifically to work with low ESR ceramic output capacitor in space-saving and performance consideration. Using a ceramic capacitor whose value is at least $1\mu\text{F}$ on the LW81XX Series output ensures stability. An appropriate output capacitor can reduce noise and improve load transient response and PSRR. The output capacitor should be located not more than 0.5 inch from the VOUT pin of the LW81XX Series and returned to a clean analog ground.

ORDER INFORMATION:

LW81①②③④⑤⑥

Designator	Item	Symbol	Description
①②	Output Voltage	08~50	e.g. 1.2V → ①=1, ②=2
③④⑤⑥	Packages	A22G	DFN2x2-6L(Type-A)
		A23E	SOT23-5L
		A89E	SOT89-5L


Part #	Output Voltage	Package	Shipping
LW8108A22G	0.8V	DFN2x2-6L(Type-A)	3000 Pcs/ Tape & Reel
LW8112A22G	1.2V		
LW8115A22G	1.5V		
LW8118A22G	1.8V		
LW8128A22G	2.8V		
LW8130A22G	3.0V		
LW8133A22G	3.3V		
LW8136A22G	3.6V		
LW8142A22G	4.2V		
LW8150A22G	5.0V		
LW8108A23E	0.8V	SOT23-5L	3000 Pcs / Tape & Reel
LW8112A23E	1.2V		
LW8115A23E	1.5V		
LW8118A23E	1.8V		
LW8128A23E	2.8V		
LW8130A23E	3.0V		
LW8133A23E	3.3V		
LW8136A23E	3.6V		
LW8142A23E	4.2V		
LW8150A23E	5.0V		

Part #	Output Voltage	Package	Shipping
LW8108A89E	0.8V	SOT89-5L	1000 Pcs/ Tape & Reel
LW8112A89E	1.2V		
LW8115A89E	1.5V		
LW8118A89E	1.8V		
LW8128A89E	2.8V		
LW8130A89E	3.0V		
LW8133A89E	3.3V		
LW8136A89E	3.6V		
LW8142A89E	4.2V		
LW8150A89E	5.0V		


If customers have special output voltage requirements, please contact us.

PACKAGE OUTLINE:


DFN2x2-6L Package



TOP VIEW
[顶视图]




BOTTOM VIEW
[背视图]



SIDE VIEW
[侧视图]


Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.700	0.800	0.028	0.031
A1	0.000	0.050	0.000	0.002
A2	0.203REF.		0.008REF.	
D	1.924	2.076	0.076	0.082
E	1.924	2.076	0.076	0.082
D1	1.150	1.250	0.045	0.049
E1	0.650	0.750	0.026	0.030
b	0.200	0.300	0.008	0.012
e1	0.650TYP.		0.026TYP.	
k	0.200MIN.		0.008MIN.	
L	0.300	0.400	0.012	0.016

SOT23-5L Package



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	MIN	MAX	MIN	MAX
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
e	0.950 BSC		0.037 BSC	
e1	1.900 BSC		0.075 BSC	
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°

SOT89-5L Package



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	1.400	1.600	0.055	0.063
b	0.320	0.520	0.013	0.020
b1	0.380	0.580	0.015	0.023
c	0.350	0.440	0.014	0.017
D	4.400	4.600	0.173	0.181
D1	1.550 REF.		0.061 REF.	
D2	1.750 REF.		0.069 REF.	
E	3.940	4.250	0.155	0.167
E1	2.300	2.600	0.091	0.102
E2	1.900 REF.		0.075 REF.	
e	1.500 TYP.		0.060 TYP.	
e1	3.000 TYP.		0.118 TYP.	
L	0.900	1.200	0.035	0.047
θ	45°		45°	

Revision History:

Revision	Date	Descriptions
Rev 0.1	Sep.2023	Initial Version
Rev 1.0	Nov.2023	Formal Version

DISCLAIMER:

- The product is not intended for use in applications that require extraordinary levels of quality and reliability, such as military, aviation/aerospace and life-support systems or other applications whose failure can be reasonably expected to result in serious physical or material damage.
- Lewa-Micro assumes no responsibility for equipment failures that result from using products at parameters that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any Lewa-Micro products described or contained herein.
- Specifications of any and all Lewa-Micro products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- Lewa-Micro strives to supply high-quality and high-reliability products. However, any and all semiconductor products have a certain probability of failure. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures including but not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- To comply with the compliance requirements of relevant export control laws and regulations, if any Lewa-Micro product (including technical data and services) stated herein is subject to relevant export control laws and regulations, it is recommended that the customer apply for and obtain an export license from the competent authority in advance in accordance with the requirements of relevant laws, and do not conduct export activities without obtaining the license. If the customer fails to comply with the aforementioned compliance requirements, all legal liabilities arising therefrom shall be borne solely by the customer.
- To protect Lewa-Micro's intellectual property rights and the security of commercial information, without the prior written permission of Lewa-Micro, no part of this document shall be reproduced or disseminated in any form or by any means (including photocopying, recording, and other electronic or mechanical means, as well as various information storage and retrieval systems). For unauthorized reproduction or dissemination, Lewa-Micro reserves the right to pursue legal liability.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. Lewa-Micro believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc.

Mailing Address: Unit 02&04&05, 10th Floor, Building 5, No.666 Shengxia Road, No.122 Yindong Road,
China (Shanghai) Pilot Free Trade Zone
Shanghai Lewa Micro-electronics Technology Co., Ltd