

INN700TK130D

1. General description

700V, 101mΩ typ., GaN-on-Silicon Enhancement-mode Power Transistor in TO-252 package.

2. Features

- Enhancement mode transistor-Normally off power switch
- Ultra high switching frequency
- No reverse-recovery charge
- Low gate charge, low output charge
- Qualified for industrial applications according to JEDEC Standards
- ESD safeguard
- RoHS, Pb-free, REACH-compliant

3. Applications

- AC-DC converters
- DC-DC converters
- Totem pole PFC
- Fast battery charging
- High density power conversion
- High efficiency power conversion

4. Key performance parameters

Table 1 Key performance parameters at $T_j = 25\text{ }^{\circ}\text{C}$

Parameter	Value	Unit
$V_{DS,max}$	700	V
$R_{DS(on),typ.} @ V_{GS} = 6\text{ V}$	101	mΩ
$R_{DS(on),max} @ V_{GS} = 6\text{ V}$	130	mΩ
$Q_{G,typ} @ V_{DS} = 400\text{ V}$	2.65	nC
$I_{D,pulse}$	32	A
$Q_{OSS} @ V_{DS} = 400\text{ V}$	25.5	nC
$Q_{rr} @ V_{DS} = 400\text{ V}$	0	nC

5. Pin information

Table 2 Pin information

Gate	Source	Drain
1	2	3

Table 3 Ordering information

Type/Ordering Code	Package	Product Code	Carrier	Package base Qty
INN700TK130D	TO-252	70TK130D	Tape & Reel	2500






Table of contents

1. General description1

2. Features1

3. Applications.....1

4. Key performance parameters.....1

5. Pin information1

6. Maximum ratings.....3

7. Thermal characteristics.....4

8. Electric characteristics5

9. Electric characteristics diagrams7

10.Package outlines13

11.Reel information.....14

12.Recommended PCB footprint15

6. Maximum ratings

at $T_j = 25\text{ }^{\circ}\text{C}$ unless otherwise specified.

Continuous application of maximum ratings can deteriorate transistor lifetime. For further information, contact Innoscence sales office.

Table 4 Maximum ratings

Parameter	Symbol	Values	Unit	Note/Test Condition
Drain source voltage	$V_{DS,max}$	700	V	$V_{GS} = 0\text{ V}$, $T_j = -55\text{ }^{\circ}\text{C}$ to $150\text{ }^{\circ}\text{C}$
Drain source voltage transient ¹	$V_{DS,transient}$	800	V	$V_{GS} = 0\text{ V}$
Drain source voltage, pulsed ²	$V_{DS,pulse}$	750	V	$T_j = 25\text{ }^{\circ}\text{C}$; total time < 10 h $T_j = 125\text{ }^{\circ}\text{C}$; total time < 1 h
Continuous current, drain source	I_D	17	A	$T_c = 25\text{ }^{\circ}\text{C}$
Pulsed current, drain source ³	$I_{D,pulse}$	32	A	$T_c = 25\text{ }^{\circ}\text{C}$; $V_G = 6\text{ V}$; $t_{PULSE} = 10\text{ }\mu\text{s}$
Pulsed current, drain source ³	$I_{D,pulse}$	18	A	$T_c = 125\text{ }^{\circ}\text{C}$; $V_G = 6\text{ V}$; $t_{PULSE} = 10\text{ }\mu\text{s}$
Gate source voltage, continuous ⁴	V_{GS}	-1.4 to +7	V	$T_j = -55\text{ }^{\circ}\text{C}$ to $150\text{ }^{\circ}\text{C}$
Gate source voltage, pulsed	$V_{GS,pulse}$	-20 to +10	V	$T_j = -55\text{ }^{\circ}\text{C}$ to $150\text{ }^{\circ}\text{C}$; $f = 100\text{ kHz}$; open drain, $t_{PULSE} = 50\text{ ns}$, total time<50s
Power dissipation	P_{tot}	85	W	$T_c = 25\text{ }^{\circ}\text{C}$
Operating temperature	T_j	-55 to +150	$^{\circ}\text{C}$	
Storage temperature	T_{stg}	-55 to +150	$^{\circ}\text{C}$	

1 $V_{DS,transient}$ is intended for non-repetitive events, $t_{PULSE} < 200\text{ }\mu\text{s}$

2 $V_{DS,pulse}$ is intended for repetitive pulse, $t_{PULSE} < 100\text{ ns}$

3 Limit was extracted from characterization test, not measured during production

4 The minimum V_{GS} is clamped by ESD protection circuit

7. Thermal characteristics

Table 5 Thermal characteristics

Parameter	Symbol	Values	Unit	Note/Test Condition
Thermal resistance, junction-ambient	R_{thJA}^1	55.1	°C/W	
Thermal resistance, junction-case	R_{thJC}	1.44	°C/W	
Maximum reflow soldering temperature	T_{sold}	260	°C	MSL3

1. R_{thJA} is determined with the device mounted on one square inch of copper pad, single layer 2oz copper on FR4 board.

8. Electric characteristics

at $T_j = 25\text{ }^{\circ}\text{C}$, unless specified otherwise

Table 6 Static characteristics

Parameter	Symbol	Values			Unit	Note/Test Condition
		Min.	Typ.	Max.		
Gate threshold voltage	$V_{GS(th)}$	1.2	1.6	2.5	V	$I_D = 14.3\text{ mA}$; $V_{DS} = V_{GS}$; $T_j = 25\text{ }^{\circ}\text{C}$
		-	1.5	-		$I_D = 14.3\text{ mA}$; $V_{DS} = V_{GS}$; $T_j = 125\text{ }^{\circ}\text{C}$
Drain-source leakage current	I_{DSS}	-	0.6	37.5	μA	$V_{DS} = 700\text{ V}$; $V_{GS} = 0\text{ V}$; $T_j = 25\text{ }^{\circ}\text{C}$
		-	4	-		$V_{DS} = 700\text{ V}$; $V_{GS} = 0\text{ V}$; $T_j = 125\text{ }^{\circ}\text{C}$
Gate-source leakage current	I_{GSS}	-	40	-	μA	$V_{GS} = 6\text{ V}$; $V_{DS} = 0\text{ V}$
Drain-source on-state resistance	$R_{DS(on)}$	-	101	130	$\text{m}\Omega$	$V_{GS} = 6\text{ V}$; $I_D = 0.5\text{ A}$; $T_j = 25\text{ }^{\circ}\text{C}$
		-	101	-	$\text{m}\Omega$	$V_{GS} = 6\text{ V}$; $I_D = 5\text{ A}$; $T_j = 25\text{ }^{\circ}\text{C}$
		-	202	-	$\text{m}\Omega$	$V_{GS} = 6\text{ V}$; $I_D = 5\text{ A}$; $T_j = 125\text{ }^{\circ}\text{C}$
Gate resistance	R_G	-	8	-	Ω	$f = 5\text{ MHz}$; open drain

Table 7 Dynamic characteristics

Parameter	Symbol	Values			Unit	Note/Test Condition
		Min.	Typ.	Max.		
Input capacitance	C_{iss}	-	101	-	pF	$V_{GS} = 0\text{ V}$; $V_{DS} = 400\text{ V}$; $f = 100\text{ kHz}$
Output capacitance	C_{oss}	-	36.5	-	pF	$V_{GS} = 0\text{ V}$; $V_{DS} = 400\text{ V}$; $f = 100\text{ kHz}$
Reverse transfer Capacitance	C_{rss}	-	0.4	-	pF	$V_{GS} = 0\text{ V}$; $V_{DS} = 400\text{ V}$; $f = 100\text{ kHz}$
Effective output capacitance, energy related ¹	$C_{o(er)}$	-	49	-	pF	$V_{GS} = 0\text{ V}$; $V_{DS} = 0\text{ to }400\text{ V}$
Effective output capacitance, time related ²	$C_{o(tr)}$	-	65	-	pF	$V_{GS} = 0\text{ V}$; $V_{DS} = 0\text{ to }400\text{ V}$
Output charge	Q_{oss}	-	25.5	-	nC	$V_{GS} = 0\text{ V}$; $V_{DS} = 0\text{ to }400\text{ V}$

1. $C_{o(er)}$ is the fixed capacitance that gives the same stored energy as C_{oss} while V_{DS} is rising from 0 to 400 V

2. $C_{o(tr)}$ is the fixed capacitance that gives the same charging time as C_{oss} while V_{DS} is rising from 0 to 400 V

Table 8 Gate charge characteristics

Parameter	Symbol	Values			Unit	Note/Test Condition
		Min.	Typ.	Max.		
Gate charge	Q_G	-	2.65	-	nC	$V_{GS} = 0 \text{ to } 6 \text{ V}; V_{DS} = 400 \text{ V}; I_D = 5 \text{ A}$
Gate-source charge	Q_{GS}	-	0.22	-	nC	
Gate-drain charge	Q_{GD}	-	1.02	-	nC	
Gate Plateau Voltage	V_{Plat}	-	2.1	-	V	$V_{DS} = 400 \text{ V}; I_D = 5 \text{ A}$

Table 9 Reverse conduction characteristics

Parameter	Symbol	Values			Unit	Note/Test Condition
		Min.	Typ.	Max.		
Source-Drain reverse voltage	V_{SD}	-	2.4	-	V	$V_{GS} = 0 \text{ V}; I_S = 5 \text{ A}$
Pulsed current, reverse	$I_{S,pulse}$	-	-	32	A	$V_{GS} = 6 \text{ V}; t_{PULSE} = 10 \mu\text{s}$
Reverse recovery charge	Q_{rr}	-	0	-	nC	$I_S = 5 \text{ A}; V_{DS} = 400 \text{ V}$
Reverse recovery time	t_{rr}	-	0	-	ns	
Peak reverse recovery current	I_{rrm}	-	0	-	A	

9. Electric characteristics diagrams

at $T_j = 25\text{ }^{\circ}\text{C}$, unless specified otherwise






Figure 5 Typ. channel reverse characteristics




$I_D = f(V_{DS}, V_{GS}); T_j = 25\text{ }^{\circ}\text{C}, T_{\text{Pulse}}=10\mu\text{s}, \text{Duty}=0.001\%$

Figure 6 Typ. channel reverse characteristics




$I_D = f(V_{DS}, V_{GS}); T_j = 125\text{ }^{\circ}\text{C}, T_{\text{Pulse}}=10\mu\text{s}, \text{Duty}=0.001\%$

Figure 7 Typ. channel reverse characteristics




$I_D = f(V_{DS}, V_{GS}); T_j = 25\text{ }^{\circ}\text{C}, T_{\text{Pulse}}=10\mu\text{s}, \text{Duty}=0.001\%$

Figure 8 Typ. channel reverse characteristics




$I_D = f(V_{DS}, V_{GS}); T_j = 125\text{ }^{\circ}\text{C}, T_{\text{Pulse}}=10\mu\text{s}, \text{Duty}=0.001\%$

Figure 9 Typ. transfer characteristics




$I_D = f(V_{GS})$; $V_{DS} = 3\text{ V}$, $T_{\text{Pulse}} = 10\mu\text{s}$, $\text{Duty} = 0.001\%$

Figure 10 Typ. Gate-to-Source leakage




$I_G = f(V_{GS})$; I_G reverse turn on by ESD unit

Figure 11 Drain-source leakage characteristics




$I_{DSS} = f(V_{DS})$; $V_{GS} = 0\text{ V}$

Figure 12 Gate threshold voltage




$V_{TH} = f(T_j); V_{GS} = V_{DS}; I_D = 14.3mA$

Figure 13 Drain-source on-state resistance




$R_{DS(on)} = f(T_j); I_D = 5 A; V_{GS}=6V, Duty=0.001\%$

Figure 14 Power dissipation




$P_{tot} = f(T_c)$

Figure 15 Max.transient thermal impedance




$Z_{thJC} = f(t_p, D)$

Figure 16 Safe operating area




$$I_D = f(V_{DS}); T_C = 25\text{ }^{\circ}\text{C}, \text{Duty}=0$$

Figure 17 Safe operating area




$$I_D = f(V_{DS}); T_C = 125\text{ }^{\circ}\text{C}, \text{Duty}=0$$

Figure 18 Typ. gate charge




$$V_{GS} = f(Q_G); V_{DCLINK} = 400\text{ V}; I_D = 5\text{ A}$$

Figure 19 Typ. capacitances




$$C_{XSS} = f(V_{DS}); \text{Freq.} = 100\text{ kHz}$$

Figure 20 Typ. output charge




$Q_{oss} = f(V_{DS}); \text{Freq.} = 100 \text{ kHz}$

Figure 21 Typ. C_{oss} stored Energy



$E_{oss} = f(V_{DS}); \text{Freq.} = 100 \text{ kHz}$


10. Package outlines



Notes:




- (1) All dimension are in millimeters.
- (2) Drawing is not to scale.
- (3) Dimensions do not include mold protrusion.
- (4) Package outline exclusive of metal burr dimensions.
- (5) Supplier dependent mold locking holes or chamfered corners or edge protrusion.

SYMBOL	MILLIMETER		
	MIN	NOM	MAX
A	2.20	2.30	2.40
A1	0.00	-	0.13
b	0.63	-	0.90
b3	5.10	5.33	5.46
c	0.43	0.53	0.61
D	5.98	6.10	6.22
D1	5.30REF		
E	6.40	6.60	6.73
E1	4.03REF		
e	2.286BSC		
H	9.40	-	10.50
L	1.38	1.50	1.75
L1	2.90REF		
L3	0.88	-	1.28
L4	0.50	-	1.00
theta	0	-	10




ROW	Description	Example
Row1	Company name	INNO
Row2	Product code	XXXXXXXXX
Row3	Date code	YYWW
Row4	ASSY lot No.	XXXXXXXXX

11. Reel information



12. Recommended PCB footprint



SYMBOL	DIMENSION	SYMBOL	DIMENSION
a	6.33	d	1.40
b	6.30	e	2.10
c	2.48	f	4.57
Notes: (1)All dimension are in millimeters. (2)Drawing is not to scale.			

Important Notice

The information provided in this document is intended as a guide only and shall not in any event be regarded as a guarantee of conditions, characteristics or performance. Innoscience does not assume any liability arising out of the application or use of any product described herein, including but not limited to any personal injury, death, or property or environmental damage. No licenses, patent rights, or any other intellectual property rights is granted or conveyed. Innoscience reserves the right to modify without notice. All rights reserved.