



LPDDR5/5X Datasheet

RS1G32LO5D2FDB-23BT

315-ball

Revision 1.2

Dec. 19. 2024

This document and all information provided herein (collectively, "Information") remains the sole and exclusive property of RAYSON. You must keep all Information in strict confidence and trust, and must not, directly or indirectly, in any way, disclose, make accessible, post on the internet, reveal, report, publish, disseminate or transfer any Information to any third party. You must not reproduce or copy Information, without first obtaining express written permission from RAYSON. You must not use, or allow use of, any Information in any manner whatsoever, except to internally evaluate the information. You must restrict access to Information to those of your employees who have a bonafide need-to-know for such purpose and are bound by obligations at least as restrictive as this clause. In order to receive Information, you must agree to the foregoing and to indemnify RAYSON for any failure to strictly comply therewith. If you do not agree, please do not accept any receipt of Information.

Revision History

Version	Date	Changes
V1.0	2023-6-19	Basic spec and architecture
V1.1	2024-7-18	Add discrete package dimension
V1.2	2024-12-19	Change package ballout & addressing

Notes: This data sheet contains minimum and maximum limits specified over the power supply and temperature range set forth herein. Although considered final, these specifications are subject to change at any time without notice, as further product development and data characterization sometimes occur.

Contents

1. Product Overview.....	4
1.1. Feature Overview.....	4
2. Physical Specifications.....	6
2.1. Function Block Diagram.....	6
2.2. Package ballout & Addressing.....	7
2.3. Pad Definition.....	8
2.4. Discrete Package Dimension.....	9
3. Core Specifications.....	11
3.1. Part Number Decoding.....	11
3.2. Ordering Options.....	12
3.3. Die Addressing Table.....	13
3.4. Mode Register Contens.....	14

1. Product Overview


1.1. Feature Overview

- Architecture
 - 17.1 GB/s maximum bandwidth per channel
 - Frequency range: 1067–5 MHz (data rate range per pin: 8533–40 Mbp/s with WCK:CK = 4:1)
 - Selectable CKR (WCK:CK = 2:1 or 4:1)
- LPDDR5 data interface
 - Single x16 channel/die
 - Double-data-rate command/address entry
 - Differential command clocks (CK_t/CK_c) for high-speed operation
 - Differential data clocks (WCK_t/WCK_c)
 - Optional differential read strobe (RDQS_t/ RDQS_c)
 - 16n-bit or 32n-bit prefetch architecture
 - 2KB page size with bank group (BG mode), or 16-bank (16B mode) operation
 - Command-selectable burst lengths (BL = 16 or 32) in bank group or 16-bank modes
 - Background ZQ calibration/command-based ZQ calibration- Optional link protection (link ECC)
 - Optional link protection (link ECC)
 - Partial-array self refresh (PASR) and partial-array auto refresh (PAAR) with segment mask
- Ultra-low-voltage core and I/O power supplies
 - $V_{DD1} = 1.70\text{--}1.95\text{V}$; 1.8V TYP
 - $V_{DD2H} = 1.01\text{--}1.12\text{V}$; 1.05V TYP
 - $V_{DD2L} = V_{DD2H}$ or $0.87\text{--}0.97\text{V}$; 0.9V TYP
 - $V_{DDQ} = 0.5\text{V}$ or 0.45V^l TYP or 0.3V TYP (ODT off only)
- I/O characteristics
 - Interface-LVSTL 0.5/0.3
 - I/O type: Low-swing single-ended, V_{SS} terminated
 - V_{OH} -compensated output drive

-
- Programmable V_{SS} on-die termination (ODT)
 - Non target ODT support
 - DVFSQ support
 - Low power features
 - DVFSC: Dynamic voltage frequency scaling core
 - Single-ended CK, single-ended WCK, and single-ended RDQS
 - $V_{DD1}/V_{DD2H}/V_{DD2L}/V_{DDQ}$ (ODT off only): 1.8V/1.05V/ V_{DD2H} or 0.9V/0.5V or 0.45V^L/0.3V
 - Array configuration
 - 1 Gig x 32 (1G x 16 x 2 Ch x 1R)
 - Device configuration
 - 2 die in package (1G16 x 2 die)
 - FBGA “green” package
 - 315-ball FBGA (12.4mm x 15mm Seated height: 1.1mm MAX)
 - 315-ball FBGA (12.4mm x 15mm Seated height: 0.95mm MAX)
 - Speed grade, cycle time (t_{WCK})
 - 8533 Mb/s
 - Operating temperature range
 - -25°C to + 85°C

2. Physical Specifications

2.1. Function Block Diagram



Dual-Die, Dual-Channel Package, Single-Rank Block Diagram

2.2. Package ballout & Addressing

315-Ball Dual-Channel Single-Rank Discrete VFBGA

	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	
A	NC	NC	VDDQ	DMI0_A	VSS	VDD2L	VDD2H	VDD2H	VDD2H	VDD2L	VSS	DMI1_A	VDDQ	NC	NC	A
B	NC	VDDQ	RDQS0_t_A	VSS	DQ4_A	VDD2L	VDD2H	VSS	VDD2H	VDD2L	DQ12_A	VSS	RDQS1_t_A	VDDQ	NC	B
C	VDD1	DQ1_A	VDDQ	RDQS0_c_A	VSS	DQ5_A	VDD2H	VSS	VDD2H	DQ13_A	VSS	RDQS1_c_A	VDDQ	DQ9_A	VDD1	C
D	DQ0_A	VSS	DQ3_A	VDDQ	WCK0_c_A	VSS	VSS	VDD2H	VSS	VSS	WCK1_c_A	VDDQ	DQ11_A	VSS	DQ8_A	D
E	VSS	DQ2_A	VSS	WCK0_t_A	VDDQ	DQ6_A	VDD2H	VSS	VDD2H	DQ14_A	VDDQ	WCK1_t_A	VSS	DQ10_A	VSS	E
F	VDDQ	VSS	VDDQ	VDDQ	DQ7_A	VDD2H	VDD2H	VSS	VDD2H	VDD2H	DQ15_A	VDDQ	VDDQ	VSS	VDDQ	F
G	VDDQ	VDDQ	VSS	CA0_A	VSS	NC	VSS	CA2_A	VSS	CA4_A	VSS	CA6_A	VSS	VDDQ	VDDQ	G
H	RESET_N	VDD2L	VSS	VSS	CA1_A	VSS	CS0_A	VSS	CK_t_A	VSS	CA3_A	VSS	CA5_A	VDD2L	ZQ_A	H
J	VSS	VDD2L	VSS	RFU	VDD2H	RFU	VSS	VSS	CK_c_A	VSS	VDD2H	VSS	VSS	VDD2L	VSS	J
K	VDD2H	VDD2H	VDD2H	VDD2H	VDD2H	VDD2H	VSS	VSS	VSS	VDD2H	VDD2H	VDD2H	VDD2H	VDD2H	VDD2H	K
L	VSS	VSS	VSS	VSS	VSS	VDD2H	VDD2H	VDD2H	VDD2H	VDD2H	VSS	VSS	VSS	VSS	VSS	L
M	VDD2H	VDD2H	VDD2H	VDD2H	VDD2H	VDD2H	VSS	VSS	VSS	VDD2H	VDD2H	VDD2H	VDD2H	VDD2H	VDD2H	M
N	VSS	VDD2L	VSS	VSS	VDD2H	VSS	CK_c_B	VSS	VSS	VSS	VDD2H	VSS	VSS	VDD2L	VSS	N
P	RFU	VDD2L	CA5_B	VSS	CA3_B	VSS	CK_t_B	VSS	CS0_B	VSS	CA1_B	VSS	VSS	VDD2L	RFU	P
R	VDDQ	VDDQ	VSS	CA6_B	VSS	CA4_B	VSS	CA2_B	VSS	NC	VSS	CA0_B	VSS	VDDQ	VDDQ	R
T	VDDQ	VSS	VDDQ	VDDQ	DQ15_B	VDD2H	VDD2H	VSS	VDD2H	VDD2H	DQ7_B	VDDQ	VDDQ	VSS	VDDQ	T
U	VSS	DQ10_B	VSS	WCK1_t_B	VDDQ	DQ14_B	VDD2H	VSS	VDD2H	DQ6_B	VDDQ	WCK0_t_B	VSS	DQ2_B	VSS	U
V	DQ8_B	VSS	DQ11_B	VDDQ	WCK1_c_B	VSS	VSS	VDD2H	VSS	VSS	WCK0_c_B	VDDQ	DQ3_B	VSS	DQ0_B	V
W	VDD1	DQ9_B	VDDQ	RDQS1_c_B	VSS	DQ13_B	VDD2H	VSS	VDD2H	DQ5_B	VSS	RDQS0_c_B	VDDQ	DQ1_B	VDD1	W
Y	NC	VDDQ	RDQS1_t_B	VSS	DQ12_B	VDD2L	VDD2H	VSS	VDD2H	VDD2L	DQ4_B	VSS	RDQS0_t_B	VDDQ	NC	Y
AA	NC	NC	VDDQ	DMI1_B	VSS	VDD2L	VDD2H	VDD2H	VDD2H	VDD2L	VSS	DMI0_B	VDDQ	NC	NC	AA
	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	


VSS
VDD1
VDD2H
VDD2L
VDDQ
CK
RDQS
WCK
DQ,DMI
CA,CS,ZQ,RESET
NC,RFU

2.3. Pad Definition


Symbol	Type	Description
CK_t_[A:B] CK_c_[A:B]	Input	Clock: CK_t and CK_c are differential clock inputs. All double data rate (DDR) command/address inputs are sampled on both crossing points of CK_t and CK_c. The first crossing point is the rising (falling) edge of CK_t (CK_c) and second crossing point is falling (rising) edge of CK_t (CK_c). Single data rate (SDR) inputs, CS is sampled on the crossing point that is the rising (falling) edge of CK_t (CK_c).
CS0_[A:B]	Input	Chip select: CS is part of the command code, and is sampled on the rising (falling) edge of CK_t (CK_c) unless the device is in power-down or deep sleep mode where it becomes an asynchronous signal. Each rank (0, 1) has its own CS signals. CS1_[A:B] become NC pins in a single-rank package.
CA[6:0]_[A:B]	Input	Command/address inputs: Provide the command and address inputs according to the command truth table.
WCK[1:0]_t_[A:B] WCK[1:0]_c_[A:B]	Input	Data clock: WCK_t and WCK_c are differential clock inputs used for write data capture and read data output.
DQ[15:0]_[A:B]	I/O	Data input/output: Bidirectional databus.
RDQS[1:0]_t_[A:B] RDQS[1:0]_c_[A:B]	I/O Output	Read data strobe: RDQS_t and RDQS_c are differential output clock signals used to strobe data during a READ operation. RDQS_t is also used as a parity pin during write link protection enabled. Each byte of data has RDQS_t and RDQS_c signals.
DMI[1:0]_[A:B]	I/O	Data mask inversion: DMI serves multiple functions such as data mask (DM), data bus inversion (DBI), and parity at READ with ECC operation by setting the mode register. DMI is a bidirectional signal and each byte of data has a DMI signal.
ZQ_A	Reference	ZQ calibration reference: Used to calibrate the output drive strength and the termination resistance. The ZQ pin should be connected to VDDQ through a 240Ω ±1% resistor.
VDDQ, VDD1, VDD2H, VDD2L	Supply	Power supplies: Isolated on the die for improved noise immunity.
VSS	Supply	Ground reference: Power supply ground reference.
RESET_n	Input	RESET: When asserted LOW, the RESET pin resets all channels of the die. Reset is an asynchronous signal.
NC	–	No connect: Not internally connected.
RFU	–	Reserved Future: Not internally connected.

2.4. Discrete Package Dimension

12.4mm X15mm (Package A)




12.4mm X15mm (Package B)



3. Core Specifications

3.1. Part Number Decoding



3.2. Ordering Options

Table 1: Part Number List

Part Number	Total Density	Data Rate	Operating temperature
RS1G32LO5D2FDB-23BT	4GB(32Gb)	8533 Mb/s/pin	-25°C to + 85°C

Table 2: Refresh Requirement Parameters

Parameter	Symbol	16Gb	unit
		BG and 16 B Mode	
REFRESH cycle time (all banks)	t_{RFCab}	280	ns
REFRESH cycle time (per bank)	t_{RFCpb}	140	ns
Per bank refresh to per bank refresh time (different bank)	$t_{PBR2PBR}$	90	ns
Per bank refresh to ACTIVATE command time (different bank)	$t_{PBR2ACT}$	7.5	ns

3.3. Die Addressing Table

Configuration		1G32(32Gb/package)	
Die Configuration	Channel A	× 16 mode × 1 die	
	Channel B	x16 mode × 1 die	
Die Addressing	Bits	17,179,869,184	
	Bank mode	BG mode	16B mode
	Configuration	64Mb × 16 DQ × 4 Banks × 4 BG	64Mb × 16 DQ × 16 Banks
	Number of banks	4	16
	Number of banks groups	4	1
	Array prefetch bits	256	
	Rows per bank	65,536	
	Columns	64	
	Page size (bytes)	2048	
	Native burst length	16	
	Number of I/Os	16	
	Bank address	BA[1:0]	BA[3:0]
	Bank group address	BG[1:0]	-
	Row address	R[15:0]	
	Column address	C[5:0]	
	Burst address	B[3:0]	
	Burst starting address boundar	128-bit	

3.4. Mode Register Contents

MR0		
OP7	Per-pin DFE	OP[0] = 1b: Device supports different NT ODT latency for DQ and RDQS OP[1] = 0b: Device supports x16 mode OP[2] = 1b: Device supports enhanced WCK always-on mode. OP[3] = 1b: Device supports optimized refresh mode OP[4] = 1b: Device supports both DMI behavior mode 1 and 2 and mode selection OP[5] = 1b: The NT ODT behavior follows the unified NT ODT behavior OP[6] = 1b: Device supports Pre Emphasis mode OP[7] = 1b: Device does not support Per Pin DFE
OP6	Pre Emphasis	
OP5	Unified NT ODT behavior mode	
OP4	DMI output behavior mode	
OP3	Optimized refresh mode	
OP2	Enhanced WCK always-on mode	
OP1	Latency Mode	
OP0	NT ODT timing mode	

MR1		
OP7		OP[0] = 0b: Device does not support CS ODT behavior OP[1] = 1b: Device supports ARFM
OP6		
OP5		
OP4		
OP3		
OP2		
OP1	ARFM support	
OP0	CS ODT OP support	

MR3		
OP7		OP[4:3] = 00b: BG; 10b: 16B Mode Supported
OP6		
OP5		
OP4	BK/BG Org	
OP3		
OP2		
OP1		
OP0		

MR5		
OP7	Manufacturer ID	1111 1111b : Micron
OP6		
OP5		
OP4		
OP3		
OP2		
OP1		
OP0		

MR6		
OP7	Revision ID1	0000 1000b
OP6		
OP5		
OP4		
OP3		
OP2		
OP1		
OP0		

MR8		
OP7	I/O width	OP[7:6] = 00b: x16/channel
OP6		
OP5	Density	OP[5:2] = 0110b: 16Gb
OP4		
OP3		
OP2		
OP1	Type	OP[1:0] = 01b: LPDDR5X SDRAM
OP0		

MR13		
OP7		OP[2]=0b: Normal operation (default) 1b: Output the VREF(CA) value on DQ7 and VREF(DQ) value on DQ6
OP6		
OP5		
OP4		
OP3		
OP2	VR0	
OP1		
OP0		

MR19		
OP7		
OP6		
OP5	WCK2DQ Osc FM support	OP[5] = 1b: WCK2DQ Osc FM supported
OP4		
OP3		
OP2		
OP1		
OP0		

MR21		
OP7	WXS	OP[0] = 1b: WRITE DATA COPY function supported OP[1] = 1b: READ DATA COPY function supported OP[2] = 1b: WRITE X function supported OP[3] = 1b: Device ODTD-CS is supported OP[7] = 1b: Data to be written can be selected with 0 and 1
OP6		
OP5		
OP4		
OP3	ODTD-CSFS	
OP2	WXFS	
OP1	RDCFS	
OP0	WDCFS	

MR22		
OP7	RECC	OP[5:4] = 00b: Write link ECC disabled (default) 01b: Write link ECC enabled OP[7:6] = 00b: Read link ECC disabled (default) 01b: Read link ECC enabled
OP6		
OP5	WECC	
OP4		
OP3		
OP2		
OP1		
OP0		

MR24		
OP7	DFES	OP[3] = 1b: Device supports Read DCA OP[7] = 1b: Devices supports DFE
OP6		
OP5		
OP4		
OP3	Read DCA	
OP2		
OP1		
OP0		

MR26		
OP7		OP[6] = 1b: Read/write-based RDQS_t TRAINING function supported
OP6	RDQSTFS	
OP5		
OP4		
OP3		
OP2		
OP1		
OP0		

MR27			
OP7	RAAMULT	OP[0] = 1b: RFM is required OP[5:1] = 01110b: 40 OP[7:6]=01b: 4X	
OP6			
OP5	RAAIMT		
OP4			
OP3			
OP2			
OP1			
OP0			RFM

MR43		
OP7		OP[6] = 1b: Simultaneous SBE on each DQ byte and DMI are independently counted
OP6	SBEC Rule	
OP5		
OP4		
OP3		
OP2		
OP1		
OP0		

MR57		
OP7	ARFM ³	OP[1:0] = 10b: 2 x RAAIMT OP[3:2] = 00b: 1=Does not support single-bank mode OP[5:4] = 00b: One RAA counter per two banks(1 of 8) OP[7:6] = 00b: default (00101b: 40), 01b:Level A, 10b: Level B, 11b: Level C
OP6		
OP5		
OP4		
OP3		
OP2		
OP1		
OP0		
	RFMSB	
	RAADEC	

- Notes:** 1、 *The contents of Product Specific Mode Register definition will reflect information specific to each die in these packages.*
- 2、 *Refer to General LPDDR5 Specifications 1 for mode registers not described here.*
- 3、 *Write link ECC and read link ECC are supported.*

Rayson