

78LXX-XG

3-Terminal 100mA Positive Voltage Regulators

General Description

The 78LXX-XG family is a monolithic fixed voltage regulator integrated circuit. They are suitable for applications that required supply current up to 100mA.

The 78LXX-XG family is available in SOT89-3、TO92、SOT23-3 and SOP8 packages.

Features

- Maximum Output Current of 100mA
- Fixed Output Voltage of 3.3V, 5V, 6V, 8V, 9V, 10V, 12V and 15V
- Thermal Overload Shutdown Protection
- Short Circuit Current Limiting



Applications

- Network Products
- Sound Card and Computer Motherboard
- Linear Regulator Source
- CD-ROM and DVD-ROM
- Controller


Package Information

Part NO.	Order NO.	Package Description	Package Marking	Package Option
78LXXL-XG	78LXXL-XG	SOT89-3	78LXXL SXXXX	1000/Reel
78LXX-XG	78LXX-XG	SOT23-3	78LXX SXXXX	3000/Reel
78LXX-XG	78LXXF-XG	SOP8	CHMC 78LXX SXXXX	100/Tube 4000/Reel
W78LXX-XG	W78LXX-XG	TO92	CHMC 78LXX SXXXX	1000/Bag 2000/Tape


CHMC: Trademark SXXXX: Lot NO. 78LXXL/78LXX: Part NO. (XX: Output Voltage)

XX (Output Voltage): 33(3.3V)/05(5.0V)/06(6.0V)/08(8.0V)/09(9.0V)/10(10V)/12(12V)/15(15V)

Functional Block Diagram



Pin Configuration



78LXXL-XG(SOT89-3)

78LXX-XG(SOP8)

78LXX-XG(SOT23-3) W78LXX-XG(TO92)

Absolute Maximum Ratings

(Operating temperature range applies unless otherwise specified, $T_{amb}=25^{\circ}\text{C}$)

Parameter Name		Symbol	Value	Unit
Input Voltage	$V_O=3.3\text{V}\sim 10\text{V}$	V_{IN}	30	V
	$V_O=12\text{V}\sim 15\text{V}$		35	
Output Current		I_O	100	mA
Power Dissipation	SOT23-3	P_d	125	mW
	SOT89-3		500	
	SOP8		300	
	TO92		625	
Operating Temperature Range		T_{opr}	$-40\sim 125$	$^{\circ}\text{C}$
Storage Temperature Range		T_{stg}	$-55\sim 150$	$^{\circ}\text{C}$
Operating Junction Temperature		T_j	150	$^{\circ}\text{C}$

78L33-XG/78L33L-XG/W78L33-XG Electrical Characteristics

Operating Conditions: $V_{in}=9V$, $I_o=40mA$, $C_i=0.33\mu F$, $C_o=0.1\mu F$ Unless otherwise specified.

(Note 1)

Parameter Name	Symbol	Test conditions	Min	Typ	Max	Unit
Output Voltage	V_o	$T_j=25^{\circ}C$	3.168	3.300	3.432	V
		$6.5V \leq V_i \leq 18V$ $I_o=1mA \sim 40mA$	3.135		3.465	V
		$I_o=1mA \sim 70mA$	3.135		3.465	V (Note 2)
Load Regulation	ΔV_o	$T_j=25^{\circ}C$, $I_o=1mA \sim 100mA$		10	60	mV
		$T_j=25^{\circ}C$, $I_o=1mA \sim 40mA$		5	30	mV
Line Regulation	ΔV_o	$T_j=25^{\circ}C$, $6.5V \leq V_i \leq 18V$		10	150	mV
		$T_j=25^{\circ}C$, $7.5V \leq V_i \leq 18V$		5	100	mV
Quiescent Current	I_q	$T_j=25^{\circ}C$, $I_o=0mA$		2.0	5.5	mA
Quiescent Current Change	ΔI_q	$7.5V \leq V_i \leq 18V$			1.5	mA
		$1mA \leq I_o \leq 40mA$			0.1	mA
Output Noise Voltage	eN	$10Hz \leq f \leq 100kHz$		40		μV
Temperature Coefficient of Output Voltage	$\Delta V_o/\Delta T$	$I_o=5mA$		-0.6		mV/ $^{\circ}C$
Ripple Rejection Ratio	RR	$7.5V \leq V_i \leq 18V$ $f=120Hz$, $T_j=25^{\circ}C$	41	50		dB
Dropout Voltage	V_d	$f=120Hz$		1.7		V

Note 1: The Maximum steady state usable output current is dependent on input voltage, heat sinking, lead length of the package and copper pattern of PCB.

Note 2: Power dissipation is less than 0.75W.

78L05-XG/78L05L-XG/W78L05-XG Electrical Characteristics

Operating Conditions: $V_{in}=10V$, $I_o=40mA$, $C_i=0.33\mu F$, $C_o=0.1\mu F$ Unless otherwise specified.

(Note 1)

Parameter Name	Symbol	Test conditions	Min	Typ	Max	Unit
Output Voltage	V_o	$T_j=25^{\circ}C$	4.80	5.00	5.20	V
		$7V \leq V_i \leq 20V$, $I_o=1mA \sim 40mA$	4.75		5.25	V
		$I_o=1mA \sim 70mA$	4.75		5.25	V (Note 2)
Load Regulation	ΔV_o	$T_j=25^{\circ}C$; $I_o=1mA \sim 100mA$		10	60	mV
		$T_j=25^{\circ}C$; $I_o=1mA \sim 40mA$		5	30	mV
Line Regulation	ΔV_o	$T_j=25^{\circ}C$; $7V \leq V_i \leq 20V$		15	150	mV
		$T_j=25^{\circ}C$; $8V \leq V_i \leq 20V$		10	100	mV
Quiescent Current	I_q	$T_j=25^{\circ}C$; $I_o=0mA$		2.0	5.5	mA
Quiescent Current Change	ΔI_q	$8V \leq V_i \leq 20V$			1.5	mA
		$1mA \leq I_o \leq 40mA$			0.1	mA
Output Noise Voltage	eN	$10Hz \leq f \leq 100kHz$		40		μV
Temperature Coefficient of Output Voltage	$\Delta V_o/\Delta T$	$I_o=5mA$		-0.65		mV/ $^{\circ}C$
Ripple Rejection Ratio	RR	$8V \leq V_i \leq 20V$; $f=120Hz$; $T_j=25^{\circ}C$	41	50		dB
Dropout Voltage	V_d	$T_j=25^{\circ}C$		1.7		V

Note 1: The Maximum steady state usable output current is dependent on input voltage, heat sinking, lead length of the package and copper pattern of PCB.

Note 2: Power dissipation is less than 0.75W.

78L06-XG/78L06L-XG/W78L06-XG Electrical Characteristics

Operating Conditions: $V_{in}=12V$, $I_o=40mA$, $C_i=0.33\mu F$, $C_o=0.1\mu F$ Unless otherwise specified.

(Note 1)

Parameter Name	Symbol	Test conditions	Min	Typ	Max	Unit
Output Voltage	V_o	$T_j=25^{\circ}C$	5.76	6.00	6.24	V
		$8.5V \leq V_i \leq 20V$, $I_o=1mA \sim 40mA$	5.70		6.30	V
		$I_o=1mA \sim 70mA$	5.70		6.30	V (Note 2)
Load Regulation	ΔV_o	$T_j=25^{\circ}C$; $I_o=1mA \sim 100mA$		15	80	mV
		$T_j=25^{\circ}C$; $I_o=1mA \sim 40mA$		5	40	mV
Line Regulation	ΔV_o	$T_j=25^{\circ}C$; $8.5V \leq V_i \leq 20V$		10	175	mV
		$T_j=25^{\circ}C$; $9V \leq V_i \leq 20V$		5	125	mV
Quiescent Current	I_q	$T_j=25^{\circ}C$; $I_o=0mA$		3.9	6.0	mA
Quiescent Current Change	ΔI_q	$9V \leq V_i \leq 20V$			1.5	mA
		$1mA \leq I_o \leq 40mA$			0.1	mA
Output Noise Voltage	eN	$10Hz \leq f \leq 100kHz$		49		μV
Temperature Coefficient of Output Voltage	$\Delta V_o/\Delta T$	$I_o=5mA$		-0.7		mV/ $^{\circ}C$
Ripple Rejection Ratio	RR	$10V \leq V_i \leq 20V$; $f=120Hz$; $T_j=25^{\circ}C$	40	46		dB
Dropout Voltage	V_d	$T_j=25^{\circ}C$		1.7		V

Note 1: The Maximum steady state usable output current is dependent on input voltage, heat sinking, lead length of the package and copper pattern of PCB.

Note 2: Power dissipation is less than 0.75W.

78L08-XG/78L08L-XG/W78L08-XG Electrical Characteristics

Operating Conditions: $V_{in}=14V$, $I_o=40mA$, $C_i=0.33\mu F$, $C_o=0.1\mu F$ Unless otherwise specified.

(Note 1)

Parameter Name	Symbol	Test conditions	Min	Typ	Max	Unit
Output Voltage	V_o	$T_j=25^{\circ}C$	7.68	8.00	8.32	V
		$10.5V \leq V_i \leq 23V$, $I_o=1mA \sim 40mA$	7.60		8.40	V
		$I_o=1mA \sim 70mA$	7.60		8.40	V (Note 2)
Load Regulation	ΔV_o	$T_j=25^{\circ}C$; $I_o=1mA \sim 100mA$		15	80	mV
		$T_j=25^{\circ}C$; $I_o=1mA \sim 40mA$		5	40	mV
Line Regulation	ΔV_o	$T_j=25^{\circ}C$; $10.5V \leq V_i \leq 23V$		15	175	mV
		$T_j=25^{\circ}C$; $11V \leq V_i \leq 23V$		10	125	mV
Quiescent Current	I_q	$T_j=25^{\circ}C$; $I_o=0mA$		2.0	5.5	mA
Quiescent Current Change	ΔI_q	$11V \leq V_i \leq 23V$			1.5	mA
		$1mA \leq I_o \leq 40mA$			0.1	mA
Output Noise Voltage	e_N	$10Hz \leq f \leq 100kHz$		49		μV
Temperature Coefficient of Output Voltage	$\Delta V_o/\Delta T$	$I_o=5mA$		-0.8		mV/ $^{\circ}C$
Ripple Rejection Ratio	RR	$11V \leq V_i \leq 23V$; $f=120Hz$; $T_j=25^{\circ}C$	39	45		dB
Dropout Voltage	V_d	$T_j=25^{\circ}C$		1.7		V

Note 1: The Maximum steady state usable output current is dependent on input voltage, heat sinking, lead length of the package and copper pattern of PCB.

Note 2: Power dissipation is less than 0.75W.

78L09-XG/78L09L-XG/W78L09-XG Electrical Characteristics

Operating Conditions: $V_{in}=15V$, $I_o=40mA$, $C_i=0.33\mu F$, $C_o=0.1\mu F$ Unless otherwise specified.

(Note 1)

Parameter Name	Symbol	Test conditions	Min	Typ	Max	Unit
Output Voltage	V_o	$T_j=25^{\circ}C$	8.64	9.00	9.36	V
		$11.5V \leq V_i \leq 24V$; $I_o=1mA \sim 40mA$	8.55		9.45	V
		$I_o=1mA \sim 70mA$	8.55		9.45	V (Note 2)
Load Regulation	ΔV_o	$T_j=25^{\circ}C$; $I_o=1mA \sim 100mA$		15	90	mV
		$T_j=25^{\circ}C$; $I_o=1mA \sim 40mA$		5	45	mV
Line Regulation	ΔV_o	$T_j=25^{\circ}C$; $11.5V \leq V_i \leq 24V$		15	200	mV
		$T_j=25^{\circ}C$; $13V \leq V_i \leq 24V$		10	150	mV
Quiescent Current	I_q	$T_j=25^{\circ}C$; $I_o=0mA$		2.0	6.0	mA
Quiescent Current Change	ΔI_q	$13V \leq V_i \leq 24V$			1.5	mA
		$1mA \leq I_o \leq 40mA$			0.1	mA
Output Noise Voltage	e_N	$10Hz \leq f \leq 100kHz$		49		μV
Temperature Coefficient of Output Voltage	$\Delta V_o/\Delta T$	$I_o=5mA$		-0.9		mV/ $^{\circ}C$
Ripple Rejection Ratio	RR	$12V \leq V_i \leq 23V$; $f=120Hz$; $T_j=25^{\circ}C$	38	44		dB
Dropout Voltage	V_d	$T_j=25^{\circ}C$		1.7		V

Note 1: The Maximum steady state usable output current is dependent on input voltage, heat sinking, lead length of the package and copper pattern of PCB.

Note 2: Power dissipation is less than 0.75W.

78L10-XG/78L10L-XG/W78L10-XG Electrical Characteristics

Operating Conditions: $V_{in}=16V$, $I_o=40mA$, $C_i=0.33\mu F$, $C_o=0.1\mu F$ Unless otherwise specified.

(Note 1)

Parameter Name	Symbol	Test conditions	Min	Typ	Max	Unit
Output Voltage	V_o	$T_j=25^{\circ}C$	9.6	10.0	10.4	V
		$12.5V \leq V_i \leq 23V$; $I_o=1mA \sim 40mA$	9.5		10.5	V
		$I_o=1mA \sim 70mA$	9.5		10.5	V (Note 2)
Load Regulation	ΔV_o	$T_j=25^{\circ}C$; $I_o=1mA \sim 100mA$		15	95	mV
		$T_j=25^{\circ}C$; $I_o=1mA \sim 40mA$		5	50	mV
Line Regulation	ΔV_o	$T_j=25^{\circ}C$; $12.5V \leq V_i \leq 25V$		15	220	mV
		$T_j=25^{\circ}C$; $14V \leq V_i \leq 25V$		10	200	mV
Quiescent Current	I_q	$T_j=25^{\circ}C$; $I_o=0mA$		4.2	6.5	mA
Quiescent Current Change	ΔI_q	$14V \leq V_i \leq 25V$			1.5	mA
		$1mA \leq I_o \leq 40mA$			0.1	mA
Output Noise Voltage	e_N	$10Hz \leq f \leq 100kHz$		74		μV
Temperature Coefficient of Output Voltage	$\Delta V_o/\Delta T$	$I_o=5mA$		-0.95		mV/ $^{\circ}C$
Ripple Rejection Ratio	RR	$14V \leq V_i \leq 25V$; $f=120Hz$; $T_j=25^{\circ}C$	38	43		dB
Dropout Voltage	V_d	$T_j=25^{\circ}C$		1.7		V

Note 1: The Maximum steady state usable output current is dependent on input voltage, heat sinking, lead length of the package and copper pattern of PCB.

Note 2: Power dissipation is less than 0.75W.

78L12-XG/78L12L-XG/W78L12-XG Electrical Characteristics

Operating Conditions: $V_{in}=19V$, $I_o=40mA$, $C_i=0.33\mu F$, $C_o=0.1\mu F$ Unless otherwise specified.

(Note 1)

Parameter Name	Symbol	Test conditions	Min	Typ	Max	Unit
Output Voltage	V_o	$T_j=25^{\circ}C$	11.52	12.00	12.48	V
		$14.5V \leq V_i \leq 27V$; $I_o=1mA \sim 40mA$	11.40		12.60	V
		$I_o=1mA \sim 70mA$	11.40		12.60	V (Note 2)
Load Regulation	ΔV_o	$T_j=25^{\circ}C$; $I_o=1mA \sim 100mA$		20	150	mV
		$T_j=25^{\circ}C$; $I_o=1mA \sim 40mA$		5	75	mV
Line Regulation	ΔV_o	$T_j=25^{\circ}C$; $14.5V \leq V_i \leq 27V$		20	300	mV
		$T_j=25^{\circ}C$; $16V \leq V_i \leq 27V$		15	250	mV
Quiescent Current	I_q	$T_j=25^{\circ}C$; $I_o=0mA$		2.0	6.0	mA
Quiescent Current Change	ΔI_q	$16V \leq V_i \leq 27V$			1.5	mA
		$1mA \leq I_o \leq 40mA$			0.1	mA
Output Noise Voltage	eN	$10Hz \leq f \leq 100kHz$		80		μV
Temperature Coefficient of Output Voltage	$\Delta V_o/\Delta T$	$I_o=5mA$		-1.0		mV/ $^{\circ}C$
Ripple Rejection Ratio	RR	$15V \leq V_i \leq 25V$; $f=120Hz$; $T_j=25^{\circ}C$	37	42		dB
Dropout Voltage	V_d	$T_j=25^{\circ}C$		1.7		V

Note 1: The Maximum steady state usable output current is dependent on input voltage, heat sinking, lead length of the package and copper pattern of PCB.

Note 2: Power dissipation is less than 0.75W.

78L15-XG/78L15L-XG/W78L15-XG Electrical Characteristics

Operating Conditions: $V_{in}=23V$, $I_o=40mA$, $C_i=0.33\mu F$, $C_o=0.1\mu F$ Unless otherwise specified.


(Note 1)

Characteristics	Symbol	Test conditions		Min	Typ	Max	Unit
Output Voltage	V_o	$T_j=25^{\circ}C$	$\pm 2.0\%$ (A)	14.70	15.00	15.30	V
			- 4.0% (B1)	14.10		14.70	
			+4.0% (B2)	15.30		15.90	
		$17.5V \leq V_i \leq 30V$; $I_o=1mA \sim 40mA$		14.25		15.75	V
		$I_o=1mA \sim 70mA$		14.25		15.75	V (Note 2)
Load Regulation	ΔV_o	$T_j=25^{\circ}C$; $I_o=1mA \sim 100mA$			30	160	mV
		$T_j=25^{\circ}C$; $I_o=1mA \sim 40mA$			10	80	mV
Line Regulation	ΔV_o	$T_j=25^{\circ}C$; $17.5V \leq V_i \leq 30V$			30	300	mV
		$T_j=25^{\circ}C$; $20V \leq V_i \leq 30V$			20	250	mV
Quiescent Current	I_q	$T_j=25^{\circ}C$; $I_o=0mA$			2.2	6.5	mA
Quiescent Current Change	ΔI_q	$20V \leq V_i \leq 30V$				1.5	mA
		$1mA \leq I_o \leq 40mA$				0.1	mA
Output Noise Voltage	eN	$10Hz \leq f \leq 100kHz$			90		μV
Temperature Coefficient of Output Voltage	$\Delta V_o/\Delta T$	$I_o=5mA$			-1.3		mV/ $^{\circ}C$
Ripple Rejection Ratio	RR	$18.5V \leq V_i \leq 28.5V$; $f=120Hz$; $T_j=25^{\circ}C$		34	42		dB
Dropout Voltage	V_d	$T_j=25^{\circ}C$			1.7		V

Note 1: The Maximum steady state usable output current is dependent on input voltage, heat sinking, lead length of the package and copper pattern of PCB.

Note 2: Power dissipation is less than 0.75W.

Typical Application




Note 1: "XX" stands for different output voltage value.

Note 2: Bypass capacitors are recommended for optimum stability and transient response and should be located as close as possible to the regulators.


Outline Dimensions

SOT89-3




Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.450	1.550	0.057	0.061
A1	0.390	0.410	0.015	0.016
B	0.950	1.050	0.037	0.041
B1	2.350	2.550	0.092	0.100
E	0.350	0.450	0.013	0.017
D1	4.400	4.600	0.173	0.181
D	1.550 REF		0.061 REF	
e	1.500 (BSC)		0.059 (BSC)	

SOT23-3




Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.050	1.250	0.041	0.049
A1	0.000	0.130	0.000	0.005
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.080	0.200	0.003	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
e	0.95 (BSC)		0.037(BSC)	
e1	1.90 (BSC)		0.075(BSC)	
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°

SOP8



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.350	1.800	0.053	0.071
A1	0.000	0.250	0.000	0.010
A2	1.250	1.550	0.053	0.061
b	0.300	0.510	0.011	0.020
c	0.170	0.250	0.006	0.010
D	4.700	5.100	0.185	0.201
E	3.800	4.000	0.150	0.157
E1	5.800	6.300	0.228	0.244
e	1.270(BSC)		0.050(BSC)	
L	0.400	1.270	0.016	0.050
θ	0°	8°	0°	8°

TO92



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	3.300	3.700	0.130	0.146
A1	1.100	1.400	0.043	0.055
A2	0.280	0.510	0.011	0.020
D	4.300	4.700	0.169	0.185
E	0.360	0.560	0.014	0.022
E1	4.300	4.700	0.169	0.185
e	1.270 (BSC)		0.050 (BSC)	

Statements

- Silicore Technology reserves the right to make changes without further notice to any products or specifications herein. Before customers place an order, customers need to confirm whether datasheet obtained is the latest version, and to verify the integrity of the relevant information.
- Failure or malfunction of any semiconductor products may occur under particular conditions, customers shall have obligation to comply with safety standards when customers use Silicore Technology products to do their system design and machine manufacturing, and take corresponding safety measures in order to avoid potential risk of failure that may cause personal injury or property damage.
- The product upgrades without end, Silicore Technology will wholeheartedly provide customers integrated Circuits that have better performance and better quality.