

## Features

- Qualified for Automotive Applications
  - AEC-Q100 Grade 1, T<sub>A</sub>: -40°C to +125°C
- Wide Input Voltage Range
  - 3.5 V to 40 V, with 48 V Maximum Rating
- 160-mΩ Maximum Low Turn-On Resistance at Room Temperature
- 4 Independent Input and Output Channels
- 0.3-μA Maximum Low Operating Current in OFF Mode at Room Temperature
- Compatible with 3.3-V and 5-V Logic Control
- Adjustable Current Limit
  - 500 mA to 2.5 A for Each Channel
  - ±15% Accuracy at 500 mA
- Fault Indication (TPS42Q20AQ)
  - Open-Drain Output Status Pin
  - Output Open Load and Short to Battery
  - Output Overload and Short to Ground
  - Over Temperature
- Diagnosis (TPS42Q20BQ)
  - Dedicated Current Sense Pin
  - Accurate Current Sense: ±3% at 500 mA
- Protection
  - Output Short to Battery Protection
  - Overload and Short to Ground Protection
  - Inductive Load Negative Voltage Protection
  - Loss of Ground, Loss of Supply Protection
  - Over-Temperature Protection
- Package Option
  - ETSSOP28

## Applications

- Automotive Off-Board Load Power Supply
- Automotive Body Control, HVAC
- Automotive Infotainment, Navigation, Telematics
- Automotive ADAS, Surround-View Cameras
- Automotive Power Train, Transmission
- Automotive LED Lighting
- Automotive Cluster, Head Unit, HUD
- Industry Control, Factory Automation

## Description

The TPS42Q20Q is a 160-mΩ 4-channel high-side power switch product with AEC-Q100 qualified.


The TPS42Q20Q has a wide voltage operating range of 3.5 V to 40 V, with an absolute maximum rating of 48 V. This flexibility makes it suitable for various automotive applications in different conditions.

The TPS42Q20Q is equipped with high-precision current sensing capabilities. It offers a current sense accuracy of 3% for the loads of 500 mA or greater, and 8% for the loads of 50 mA or greater. This accurate current sensing enables easy identification of load status and measurement of load current.

The TPS42Q20Q integrates full fault detection and device protection to prevent the device damage from open load, overload, over temperature, short-circuit to the battery, short-circuit to ground, reverse battery, loss of ground, loss of power supply, and voltage clamp. With all these protection functions, this device is suitable for different resistive, inductive, and capacitive loads.

The TPS42Q20Q is designed to operate within the ambient temperature range from -40°C to +125°C. Moreover, the TPS42Q20Q provides a thermal-enhanced ETSSOP28 package to enable sustained operation despite significant dissipation across the device.

## Typical Application Circuit



## Table of Contents

|                                                                             |           |
|-----------------------------------------------------------------------------|-----------|
| <b>Features</b> .....                                                       | <b>1</b>  |
| <b>Applications</b> .....                                                   | <b>1</b>  |
| <b>Description</b> .....                                                    | <b>1</b>  |
| <b>Typical Application Circuit</b> .....                                    | <b>1</b>  |
| <b>Product Family Table</b> .....                                           | <b>3</b>  |
| <b>Revision History</b> .....                                               | <b>3</b>  |
| <b>Pin Configuration and Functions</b> .....                                | <b>4</b>  |
| <b>Specifications</b> .....                                                 | <b>6</b>  |
| Absolute Maximum Ratings <sup>(1)</sup> <sup>(2)</sup> <sup>(3)</sup> ..... | 6         |
| ESD, Electrostatic Discharge Protection.....                                | 6         |
| Recommended Operating Conditions.....                                       | 6         |
| Thermal Information.....                                                    | 7         |
| Electrical Characteristics.....                                             | 8         |
| Typical Performance Characteristics.....                                    | 12        |
| <b>Detailed Description</b> .....                                           | <b>14</b> |
| Overview.....                                                               | 14        |
| Functional Block Diagram.....                                               | 14        |
| Feature Description.....                                                    | 14        |
| <b>Application and Implementation</b> .....                                 | <b>19</b> |
| Application Information .....                                               | 19        |
| Typical Application.....                                                    | 19        |
| <b>Layout</b> .....                                                         | <b>21</b> |
| Layout Guideline.....                                                       | 21        |
| Layout Example.....                                                         | 22        |
| <b>Tape and Reel Information</b> .....                                      | <b>24</b> |
| <b>Package Outline Dimensions</b> .....                                     | <b>25</b> |
| ETSSOP-28.....                                                              | 25        |
| <b>Order Information</b> .....                                              | <b>26</b> |
| <b>IMPORTANT NOTICE AND DISCLAIMER</b> .....                                | <b>27</b> |

## Product Family Table


| Order Number      | Operating Voltage Range (V) | Feature          | Package  |
|-------------------|-----------------------------|------------------|----------|
| TPS42Q20AQ-TSCR-S | 4 to 40                     | Fault Indication | ETSSOP28 |
| TPS42Q20BQ-TSCR-S | 4 to 40                     | Current Sense    | ETSSOP28 |

## Revision History


| Date       | Revision | Notes            |
|------------|----------|------------------|
| 2025-12-29 | Rev.A.0  | Initial release. |

## Pin Configuration and Functions

TPS42Q20AQ  
ETSSOP28 Package  
Top View



TPS42Q20BQ  
ETSSOP28 Package  
Top View



### Table 1. Pin Functions: TPS42Q20Q

| Pin No.   | Pin Name       |                           | I/O | Description                                                                                                                                                                      |
|-----------|----------------|---------------------------|-----|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|           | TPS42Q20<br>AQ | TPS42Q20<br>BQ            |     |                                                                                                                                                                                  |
| 10        | –              | CS                        | O   | Current sense output pin (TPS42Q20BQ only). Connect an external resistor to ground to monitor the output current through the internal power MOS. Left this pin open if not used. |
| 14        | DEN            | DEN                       | I   | Fault-diagnosis function or current-sense function enable pin. Pull this pin HIGH to enable the function or pull this pin LOW to disable the function.                           |
| 9         | –              | $\overline{\text{FAULT}}$ | O   | Device fault indication pin (TPS42Q20BQ only). Open-drain output. Left this pin open if not used.                                                                                |
| 1, 12     | GND            | GND                       | –   | Ground reference pin.                                                                                                                                                            |
| 11        | ICL            | ICL                       | O   | Current limit adjust pin. Connect an external resistor to ground to set the current limit value. Connect this pin to ground if not used.                                         |
| 3         | IN1            | IN1                       | I   | Channel 1 control input pin.                                                                                                                                                     |
| 4         | IN2            | IN2                       | I   | Channel 2 control input pin.                                                                                                                                                     |
| 5         | IN3            | IN3                       | I   | Channel 3 control input pin.                                                                                                                                                     |
| 6         | IN4            | IN4                       | I   | Channel 4 control input pin.                                                                                                                                                     |
| 2, 19, 24 | NC             | NC                        | –   | No internal connection. Suggest connecting to GND to improve the thermal performance.                                                                                            |

**Automotive 40-V 160-mΩ 4-Channel High-Side Power Switch**

| Pin No.           | Pin Name                |                | I/O | Description                                                                                                                                                |
|-------------------|-------------------------|----------------|-----|------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                   | TPS42Q20<br>AQ          | TPS42Q20<br>BQ |     |                                                                                                                                                            |
| 27, 28            | OUT1                    | OUT1           | O   | Channel 1 output pin.                                                                                                                                      |
| 25, 26            | OUT2                    | OUT2           | O   | Channel 2 output pin.                                                                                                                                      |
| 17, 18            | OUT3                    | OUT3           | O   | Channel 3 output pin.                                                                                                                                      |
| 15, 16            | OUT4                    | OUT4           | O   | Channel 4 output pin.                                                                                                                                      |
| 7                 | $\overline{\text{ST1}}$ | –              | O   | Channel 1 statues indication pin (TPS42Q20AQ only). Open-drain output. Left this pin open if not used.                                                     |
| 8                 | $\overline{\text{ST2}}$ | –              | O   | Channel 2 statues indication pin (TPS42Q20AQ only). Open-drain output. Left this pin open if not used.                                                     |
| 9                 | $\overline{\text{ST3}}$ | –              | O   | Channel 3 statues indication pin (TPS42Q20AQ only). Open-drain output. Left this pin open if not used.                                                     |
| 10                | $\overline{\text{ST4}}$ | –              | O   | Channel 4 statues indication pin (TPS42Q20AQ only). Open-drain output. Left this pin open if not used.                                                     |
| 7                 | –                       | SEH            | I   | Current sense channel selection high bit (TPS42Q20BQ only) .                                                                                               |
| 8                 | –                       | SEL            | I   | Current sense channel selection low bit (TPS42Q20BQ only) .                                                                                                |
| 13                | THER                    | THER           | I   | Thermal shutdown behavior control pin. Pull this pin low for auto retry or pull this pin high for latch off when thermal shutdown protection is triggered. |
| 20, 21, 22,<br>23 | VS                      | VS             | I   | Power supply input pin.                                                                                                                                    |

(1) Thermal Pad **MUST** be connected to device GND directly.

## Specifications

### Absolute Maximum Ratings <sup>(1)</sup> <sup>(2)</sup> <sup>(3)</sup>

| Parameter                                                           |                                     | Min              | Max | Unit |
|---------------------------------------------------------------------|-------------------------------------|------------------|-----|------|
| Supply Voltage on VS pin, $t < 400\text{ ms}$ <sup>(4)</sup>        |                                     |                  | 48  | V    |
| Reverse Polarity Voltage on VS Pin <sup>(5)</sup>                   |                                     | -36              |     | V    |
| Continuous Drain Current on OUT Pin                                 |                                     | Internal Limited |     | A    |
| Reverse Current on GND Pin                                          |                                     | -50              | 20  | mA   |
| Reverse Current on GND Pins, $t < 120\text{ s}$                     |                                     | -100             | 250 | mA   |
| Voltage on INx, DEN, SEL, SEH and THER Pins                         |                                     | -0.3             | 7   | V    |
| Current on INx, DEN, SEL, SEH and THER Pins                         |                                     | -10              |     | mA   |
| Voltage on $\overline{\text{STx}}$ or $\overline{\text{FAULT}}$ Pin |                                     | -2.7             | 7   | V    |
| Current on $\overline{\text{STx}}$ or $\overline{\text{FAULT}}$ Pin |                                     | -30              | 10  | mA   |
| Input PWM Frequency on INx Pin                                      |                                     |                  | 2   | kHz  |
| Voltage on ICL Pin                                                  |                                     | -0.3             | 7   | V    |
| Current on ICL Pin                                                  |                                     | -2               | 30  | mA   |
| Voltage on CS Pin                                                   |                                     | -2.7             | 7   | V    |
| Current on CS Pin                                                   |                                     | -2               | 30  | mA   |
| T <sub>J</sub>                                                      | Junction Temperature Range          | -40              | 150 | °C   |
| T <sub>A</sub>                                                      | Ambient Temperature Range           | -40              | 125 | °C   |
| T <sub>STG</sub>                                                    | Storage Temperature Range           | -65              | 150 | °C   |
| T <sub>L</sub>                                                      | Lead Temperature (Soldering 10 sec) |                  | 260 | °C   |

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. Exposure to any Absolute Maximum Rating condition for extended periods may affect device reliability and lifetime.

(2) All voltage values are with respect to GND.

(3) All absolute negative voltages on these terminals are not to go below -0.3 V.

(4) Absolute maximum voltage, withstand 48-V load dump voltage for 400 ms.

(5) Reverse polarity condition:  $t < 60\text{ s}$ , reverse current  $< I_{rev1}$ , GND pin 1-kΩ resistor in parallel with diode.

### ESD, Electrostatic Discharge Protection

| Parameter |                          | Condition    | Minimum Level | Unit |
|-----------|--------------------------|--------------|---------------|------|
| HBM       | Human Body Model ESD     | AEC Q100-002 | ±2            | kV   |
| CDM       | Charged Device Model ESD | AEC Q100-011 | ±1            | kV   |

### Recommended Operating Conditions

| Parameter       |                                           | Min | Max | Unit |
|-----------------|-------------------------------------------|-----|-----|------|
| V <sub>VS</sub> | Supply Voltage Range for Normal Operation | 4   | 40  | V    |

**Automotive 40-V 160-mΩ 4-Channel High-Side Power Switch**

| Parameter           |                                                                       | Min | Max | Unit |
|---------------------|-----------------------------------------------------------------------|-----|-----|------|
| V <sub>VS,EXT</sub> | Extended Operating Voltage Range <sup>(1)</sup>                       | 3.5 | 4   | V    |
|                     | Voltage on INx, DEN, SEL, SEH, and THER pins                          | 0   | 5   | V    |
|                     | Voltage on $\overline{\text{STx}}$ and $\overline{\text{FAULT}}$ pins | 0   | 5   | V    |
| I <sub>OUT</sub>    | Nominal DC Load Current                                               | 0   | 2.5 | A    |
| T <sub>A</sub>      | Ambient Temperature Range                                             | −40 | 125 | °C   |
| T <sub>J</sub>      | Junction Temperature Range                                            | −40 | 150 | °C   |

(1) The device can function properly in the extended operating range, whereas the validity of specific parametric values is not ensured.

**Thermal Information**

| Package Type | $\theta_{JA}$ | $\theta_{JB}$ | $\theta_{JC, TOP}$ | Unit |
|--------------|---------------|---------------|--------------------|------|
| ETSSOP28     | 27.7          | 7.5           | 18                 | °C/W |

**Automotive 40-V 160-mΩ 4-Channel High-Side Power Switch**
**Electrical Characteristics**

All test conditions:  $T_A = -40^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$ ; typical values at  $T_A = 25^{\circ}\text{C}$ ,  $V_{VS} = 5\text{ V}$  to  $40\text{ V}$ , over operating free-air temperature range (unless otherwise noted)

| Parameter                                    |                                                       | Conditions                                                                                                                                                               | Min | Typ  | Max | Unit |
|----------------------------------------------|-------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----|------|-----|------|
| Supply Voltage and Current                   |                                                       |                                                                                                                                                                          |     |      |     |      |
| UVLO                                         | Undervoltage Lockout                                  | VS rising to device turns on                                                                                                                                             | 3.4 | 3.7  | 4   | V    |
|                                              |                                                       | VS falling to device turns off                                                                                                                                           |     | 3.2  | 3.4 | V    |
|                                              | Hysteresis                                            |                                                                                                                                                                          |     | 500  |     | mV   |
| I <sub>VS</sub>                              | Operating Current                                     | V <sub>VS</sub> = 13.5V, V <sub>INx</sub> = 5 V, V <sub>DEN</sub> = 0 V, I <sub>OUTx</sub> = 0.5 A, current limit is set to 2 A, all channels on                         |     |      | 8   | mA   |
| I <sub>OFF</sub>                             | Operating Current in OFF Mode                         | V <sub>VS</sub> = 13.5 V, V <sub>INx</sub> = V <sub>DEN</sub> = V <sub>CS</sub> = V <sub>ICL</sub> = V <sub>OUTx</sub> = V <sub>THER</sub> = 0 V, T <sub>A</sub> = 25°C  |     |      | 0.3 | μA   |
|                                              |                                                       | V <sub>VS</sub> = 13.5 V, V <sub>INx</sub> = V <sub>DEN</sub> = V <sub>CS</sub> = V <sub>ICL</sub> = V <sub>OUTx</sub> = V <sub>THER</sub> = 0 V, T <sub>A</sub> = 125°C |     |      | 2   | μA   |
| I <sub>OFF,DIAG</sub>                        | Operating Current with Diagnostic Enabled in OFF Mode | V <sub>VS</sub> = 13.5 V, V <sub>INx</sub> = 0 V, V <sub>DEN</sub> = 5 V, V <sub>VS</sub> – V <sub>OUTx</sub> > V <sub>OL,OFF</sub> , not in open-load mode              |     |      | 5   | mA   |
| t <sub>OFF,DEG</sub> <sup>(1)</sup>          | Off-mode Deglitch Time                                | IN logic from HIGH to LOW, if waiting time > t <sub>OFF,DEG</sub> , enters standby mode.                                                                                 |     | 12.5 |     | ms   |
| I <sub>OFF,OUT</sub>                         | OUT Leakage Current in OFF Mode                       | V <sub>VS</sub> = 13.5 V, V <sub>INx</sub> = V <sub>DEN</sub> = V <sub>OUTx</sub> = 0, T <sub>A</sub> = 25°C                                                             |     |      | 0.3 | μA   |
|                                              |                                                       | V <sub>VS</sub> = 13.5 V, V <sub>INx</sub> = V <sub>DEN</sub> = V <sub>OUTx</sub> = 0, T <sub>A</sub> = 125°C                                                            |     |      | 0.6 | μA   |
| Logic Control (INx, DEN, SEL, SEH, and THER) |                                                       |                                                                                                                                                                          |     |      |     |      |
| V <sub>IH,LOGIC</sub>                        | Logic Input High-level Voltage                        |                                                                                                                                                                          | 2   |      |     | V    |
| V <sub>IL,LOGIC</sub>                        | Logic Input Low-level Voltage                         |                                                                                                                                                                          |     |      | 0.8 | V    |
| V <sub>HYS,LOGIC</sub>                       | Hysteresis Voltage                                    |                                                                                                                                                                          |     | 300  |     | mV   |
| R <sub>PD</sub>                              | Pulldown Resistor                                     | V <sub>INx</sub> = V <sub>SEL</sub> = V <sub>SEH</sub> = V <sub>THER</sub> = 5 V                                                                                         |     | 175  |     | kΩ   |
|                                              |                                                       | V <sub>VS</sub> = V <sub>DEN</sub> = 5 V                                                                                                                                 |     | 275  |     | kΩ   |
| Output Power Stage                           |                                                       |                                                                                                                                                                          |     |      |     |      |
| R <sub>ON</sub>                              | Turn-on Resistance                                    | V <sub>VS</sub> > 5 V, T <sub>A</sub> = 25°C                                                                                                                             |     | 160  |     | mΩ   |
|                                              |                                                       | V <sub>VS</sub> > 5 V, T <sub>A</sub> = 150°C                                                                                                                            |     | 260  |     | mΩ   |
|                                              |                                                       | V <sub>VS</sub> = 3.5 V, T <sub>A</sub> = 25°C                                                                                                                           |     | 160  |     | mΩ   |
| I <sub>LIM</sub>                             | Inherent Current Limit                                |                                                                                                                                                                          | 5   |      | 8   | A    |
|                                              | Current Limit during Over-Temperature Protection      | Inherent current limit under thermal cycling condition                                                                                                                   |     | 3.5  |     | A    |

**Automotive 40-V 160-mΩ 4-Channel High-Side Power Switch**

| Parameter                            |                                                                  | Conditions                                                                                                                                                                               | Min | Typ | Max  | Unit |
|--------------------------------------|------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----|-----|------|------|
|                                      |                                                                  | Inherent the current limit under thermal cycling condition. Percentage of current limit set value                                                                                        |     | 50% |      |      |
| $V_{DS}$                             | Drain-to-Source Internally Clamped Voltage                       |                                                                                                                                                                                          | 49  |     | 70   | V    |
| $V_F$                                | Drain-to-Source Diode Voltage                                    | $V_{INx} = 0$ , $I_{OUTx} = -0.2$ A                                                                                                                                                      |     | 0.7 |      | V    |
| $I_{REV}^{(1)}$                      | Continuous Reverse Current from Source to Drain                  | OUT short-to-battery condition. $t < 60$ s, $V_{INx} = 0$ V. $T_A = 25^\circ\text{C}$ . Single channel is reversed.                                                                      |     | 2.5 |      | A    |
|                                      |                                                                  | Reverse-polarity condition. $t < 60$ s, $V_{INx} = 0$ V, GND pin 1-kΩ resistor in parallel with diode. $T_A = 25^\circ\text{C}$ . All channels are reversed.                             |     | 2   |      | A    |
| $t_{D,ON}^{(1)}$                     | Turn-On Delay Time                                               | $V_{VS} = 13.5$ V, $V_{DEN} = 5$ V, $I_{OUTx} = 0.5$ A, IN rising edge to $V_{OUTx} = 10\%$                                                                                              | 20  |     | 90   | μs   |
| $t_{D,OFF}^{(1)}$                    | Turn-Off Delay Time                                              | $V_{VS} = 13.5$ V, $V_{DEN} = 5$ V, $I_{OUTx} = 0.5$ A, IN falling edge to $V_{OUTx} = 90\%$                                                                                             | 20  |     | 90   | μs   |
| $dV/dt_{ON}^{(1)}$                   | Turn-On Slew Rate                                                | $V_{VS} = 13.5$ V, $V_{DEN} = 5$ V, $I_{OUTx} = 0.5$ A, $V_{OUTx} = 10\%$ to $90\%$                                                                                                      | 0.1 |     | 0.55 | V/μs |
| $dV/dt_{OFF}^{(1)}$                  | Turn-Off Slew Rate                                               | $V_{VS} = 13.5$ V, $V_{DEN} = 5$ V, $I_{OUTx} = 0.5$ A, $V_{OUTx} = 90\%$ to $10\%$                                                                                                      | 0.1 |     | 0.55 | V/μs |
| $\Delta dV/dt^{(1)}$                 | Turn On and Off Delay Time Difference, $t_{d,rise} - t_{d,fall}$ | $V_{VS} = 13.5$ V, $V_{DEN} = 5$ V, $I_{OUTx} = 0.5$ A. $t_{d,rise}$ is the $V_{INx}$ rising edge to $V_{OUTx} = 90\%$ . $t_{d,fall}$ is the $V_{INx}$ falling edge to $V_{OUTx} = 10\%$ | -50 |     | 50   | μs   |
| <b>Fault Detection and Diagnosis</b> |                                                                  |                                                                                                                                                                                          |     |     |      |      |
| $I_{LG,OUT}$                         | OUT Leakage Current with Loss-of-Ground Condition                |                                                                                                                                                                                          |     |     | 12   | μA   |
| $V_{OL,OFF}$                         | Open-Load Detection Threshold in OFF Mode                        | $V_{INx} = 0$ V, when $V_{VS} - V_{OUT} < V_{OL,OFF}$ and duration longer than $t_{OL,OFF}$ , open load fault detected.                                                                  | 1.4 | 2   | 2.6  | V    |
| $t_{d,OL,OFF}$                       | Open-Load Detection Threshold Deglitch                           | $V_{INx} = 0$ V, when $V_{VS} - V_{OUT} < V_{OL,OFF}$ and duration longer than $t_{OL,OFF}$ , open load fault detected.                                                                  | 300 | 600 | 800  | μs   |
| $I_{OL,OFF}$                         | Open-Load Current Sink in OFF Mode                               | $V_{INx} = 0$ V, $V_{DEN} = 5$ V, $V_{VS} = V_{OUT} = 13.5$ V, $T_A = 125^\circ\text{C}$ .                                                                                               | -75 |     |      | μA   |

**Automotive 40-V 160-mΩ 4-Channel High-Side Power Switch**

| Parameter              |                                                                 | Conditions                                                                                                                             | Min                         | Typ  | Max          | Unit               |
|------------------------|-----------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------|-----------------------------|------|--------------|--------------------|
| $t_{OL,OFF}$           | Open-Load Detection Deglitch Time in OFF Mode                   | $V_{INx} = 0\text{ V}$ , When $V_{VS} - V_{OUT} < V_{OL,OFF}$ and duration longer than $t_{OL,OFF}$ , open load fault detected.        |                             | 600  |              | $\mu\text{s}$      |
| $V_{\overline{STx}}$   | Status Output Low Voltage                                       | $I_{\overline{STx}} = 2\text{ mA}$ . (TPS42Q20AQ)                                                                                      |                             |      | 0.4          | V                  |
| $V_{\overline{FAULT}}$ | Fault Output Low Voltage                                        | $I_{\overline{FAULT}} = 2\text{ mA}$ . (TPS42Q20BQ)                                                                                    |                             |      | 0.4          | V                  |
| $t_{CL}$               | Deglitch Time when Current Limit Occurs                         | $V_{INx} = V_{DEN} = 5\text{ V}$ , the deglitch time from current limit toggling to $\overline{FAULT}$ , $\overline{STx}$ , CS report. | 80                          |      | 180          | $\mu\text{s}$      |
| $T_{SD}$               | Thermal Shutdown Threshold                                      |                                                                                                                                        |                             | 175  |              | $^{\circ}\text{C}$ |
| $T_{SD,RST}$           | Thermal Shutdown Status Reset                                   |                                                                                                                                        |                             | 155  |              | $^{\circ}\text{C}$ |
| $T_{SW}$               | Thermal Swing Shutdown Threshold                                |                                                                                                                                        |                             | 60   |              | $^{\circ}\text{C}$ |
| $T_{HYS}$              | Hysteresis for Resetting the Thermal Shutdown and Thermal Swing |                                                                                                                                        |                             | 10   |              | $^{\circ}\text{C}$ |
| <b>Current Sense</b>   |                                                                 |                                                                                                                                        |                             |      |              |                    |
| $K_{CS}$               | Current Sense Ratio                                             |                                                                                                                                        |                             | 300  |              |                    |
| $K_{CL}$               | Current Limit Ratio                                             |                                                                                                                                        |                             | 2500 |              |                    |
| $\Delta CS$            | Current Sense Accuracy,                                         | $V_{VS} = 13.5\text{ V}$ , $I_{OUTx} \geq 5\text{ mA}$                                                                                 | -65%                        |      | 65%          |                    |
|                        |                                                                 | $V_{VS} = 13.5\text{ V}$ , $I_{OUTx} \geq 25\text{ mA}$                                                                                | -15%                        |      | 15%          |                    |
|                        |                                                                 | $V_{VS} = 13.5\text{ V}$ , $I_{OUTx} \geq 50\text{ mA}$                                                                                | -8%                         |      | 8%           |                    |
|                        |                                                                 | $V_{VS} = 13.5\text{ V}$ , $I_{OUTx} \geq 100\text{ mA}$                                                                               | -4%                         |      | 4%           |                    |
|                        |                                                                 | $V_{VS} = 13.5\text{ V}$ , $I_{OUTx} \geq 500\text{ mA}$                                                                               | -3%                         |      | 3%           |                    |
| $\Delta K_{CL}^{(3)}$  | Current Limit Accuracy                                          | $I_{LIMIT} \geq 0.25\text{ A}$                                                                                                         | -20                         |      | 20           | %                  |
|                        |                                                                 | $I_{LIMIT} \geq 0.5\text{ A}$                                                                                                          | -15                         |      | 15           | %                  |
| $V_{CS}$               | Current Sense Voltage Range                                     | $V_{VS} \geq 6.5\text{ V}$                                                                                                             | 0                           |      | 4            | V                  |
|                        |                                                                 | $5\text{ V} \leq V_{VS} < 6.5\text{ V}$                                                                                                | 0                           |      | $V_{VS}-2.5$ | V                  |
| $I_{CS,OFF}$           | Current Sense Leakage Current in OFF Mode                       | $V_{INx} = 5\text{ V}$ , $R_{LOAD} = 10\text{ }\Omega$ , $V_{DEN} = 0\text{ V}$ , $T_A = 125^{\circ}\text{C}$                          |                             |      | 1            | $\mu\text{A}$      |
|                        |                                                                 | $V_{INx} = 0\text{ V}$ , $V_{DEN} = 0\text{ V}$ , $T_A = 125^{\circ}\text{C}$                                                          |                             |      | 0.5          | $\mu\text{A}$      |
| $I_{OUT}$              | Output Current Range                                            | $V_{VS} \geq 6.5\text{ V}$ , $V_{CS} \leq 4\text{ V}$                                                                                  | 0                           |      | 2.5          | A                  |
|                        |                                                                 | $5\text{ V} \leq V_{VS} < 6.5\text{ V}$ , $V_{CS} \leq V_{VS} - 2.5\text{ V}$                                                          | 0                           |      | 2.5          | A                  |
| $V_{CS,H}$             | Current-Sense Fault High Voltage                                | $V_{VS} \geq 7\text{ V}$                                                                                                               | 4.3                         | 4.75 | 5            | V                  |
|                        |                                                                 | $5\text{ V} \leq V_{VS} < 7\text{ V}$                                                                                                  | Min ( $V_{VS} - 0.8$ , 4.5) |      | 5            | V                  |
| $I_{CS,H}$             | Current-Sense Fault Condition Current                           | $V_{CS} = 4.5\text{ V}$ , $V_{VS} = 13.5\text{ V}$                                                                                     | 15                          |      |              | mA                 |


**Automotive 40-V 160-mΩ 4-Channel High-Side Power Switch**

| Parameter          |                                                   | Conditions                                                                                                                                            | Min | Typ | Max | Unit          |
|--------------------|---------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|-----|-----|-----|---------------|
| $V_{CL,TH}$        | Current-Limit Internal Threshold Voltage          |                                                                                                                                                       |     | 0.8 |     | V             |
| $t_{CS,OFF}^{(1)}$ | CS Settling Time from DEN Disabled                | $V_{VS} = 13.5\text{ V}$ , $V_{INx} = 5\text{ V}$ , $I_{OUT} \geq 0.5\text{ A}$ . $V_{DEN}$ from 5 to 0 V. CS to 10% of sense value.                  |     |     | 20  | $\mu\text{s}$ |
|                    | CS Settling Time from IN Falling Edge             | $V_{VS} = 13.5\text{ V}$ , $V_{DEN} = 5\text{ V}$ , $I_{OUT} \geq 0.5\text{ A}$ . $INx$ from 5 to 0 V. CS to 10% of sense value.                      |     |     | 100 | $\mu\text{s}$ |
| $t_{CS,ON}^{(1)}$  | CS Settling Time from DEN Enabled                 | $V_{VS} = 13.5\text{ V}$ , $V_{INx} = 5\text{ V}$ , $I_{OUT} \geq 0.5\text{ A}$ . $V_{DEN}$ from 0 to 5 V. CS to 90% of sense value.                  |     |     | 20  | $\mu\text{s}$ |
|                    | CS Settling Time from IN Rising Edge              | $V_{VS} = 13.5\text{ V}$ , $V_{DEN} = 5\text{ V}$ , $I_{OUT} \geq 0.5\text{ A}$ . $V_{IN}$ from 0 to 5 V. CS to 90% of sense value.                   |     |     | 150 | $\mu\text{s}$ |
| $t_{SEx}$          | Multi-Channel Current Sense Transition Delay Time | $V_{VS} = 13.5\text{ V}$ , $V_{D\_EN} = 5\text{ V}$ , current sense output delay when multi-sense pins SEL and SEH transition from channel to channel |     |     | 50  | $\mu\text{s}$ |


(1) Not subject to production test, specified by design.

## Typical Performance Characteristics


All test conditions:  $V_S = 13.5\text{ V}$ , unless otherwise noted.




**Figure 1.  $IN_x$  Voltage**




**Figure 2. DIAG\_EN Voltage**




**Figure 3.  $SE_x$  Voltage**




**Figure 4. Diode Forward Voltage**




**Figure 5. Clamp Voltage**










**Figure 6. CH1  $R_{on}$**



**Figure 7. CH2  $R_{on}$**



**Figure 8. CH3  $R_{on}$**

**Automotive 40-V 160-mΩ 4-Channel High-Side Power Switch**

**Figure 9. CH4  $R_{ON}$** 

**Figure 10. Current Sense Accuracy, 5 mA**

**Figure 11. Current Sense Accuracy, 25 mA**

**Figure 12. Current Sense Accuracy, 100 mA**

**Figure 13. Current Sense Accuracy, 1 A**

**Figure 14. UVLO**

**Figure 15.  $I_{VS}$**

## Detailed Description

### Overview

The TPS42Q20Q is a 160-mΩ 4-channel high-side power switch product with AEC-Q100 qualified.


The TPS42Q20Q has a wide voltage operating range of 3.5 V to 40 V, with an absolute maximum rating of 48 V. This flexibility makes it suitable for various automotive applications in different conditions.

The TPS42Q20Q is equipped with high-precision current sensing capabilities. It offers a current sense accuracy of 3% for the loads of 500 mA or greater, and 8% for the loads of 50 mA or greater. This accurate current sensing enables easy identification of load status and measurement of load current.

The TPS42Q20Q integrates full fault detection and device protection to prevent the device damage from open load, overload, over temperature, short-circuit to the battery, short-circuit to ground, reverse battery, loss of ground, loss of power supply, and voltage clamp. With all these protection functions, this device is suitable for different resistive, inductive and capacitive loads.

The TPS42Q20Q is designed to operate within the ambient temperature range from  $-40^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$ . Moreover, the TPS42Q20Q provides a thermal-enhanced ETSSOP28 package to enable sustained operation despite significant dissipation across the device.

### Functional Block Diagram



**Figure 16. Functional Block Diagram**

### Feature Description

#### Under-Voltage Lockout (UVLO)

The TPS42Q20Q uses the VS UVLO control to keep the output off until the internal circuitry operates properly. When the VS voltage is lower than the UVLO falling threshold, the TPS42Q20Q stays in the shutdown mode. When the VS voltage is greater than the UVLO rising threshold, the device enters operation mode.

---

**Automotive 40-V 160-mΩ 4-Channel High-Side Power Switch**

---

**Channel Control (IN1, IN2, IN3, and IN4)**

The TPS42Q20Q integrates the IN1, IN2, IN3, and IN4 pins to control each channel. The INx (x = 1, 2, 3, and 4) pins are active high. Connect these pins to the GPIO ports of an external processor or digital logic control circuit to turn on and off the internal power MOSFET of each channel.

**Status Indication ( $\overline{ST1}$ ,  $\overline{ST2}$ ,  $\overline{ST3}$ , and  $\overline{ST4}$ )**

For the TPS42Q20AQ, the  $\overline{STx}$  (x = 1, 2, 3, and 4) pins are integrated to indicate the device output status of each channel.  $\overline{STx}$  are open-drain output pins, and external pull-up resistors are required.

When the fault diagnostic control pin is low (DEN = L), the  $\overline{STx}$  pins are internally high impedance, and they are pulled up high. When DEN = H, the voltage of the  $\overline{STx}$  pins changes according to the output status.

**Current Sense (CS)**

For the TPS42Q20BQ, a CS pin is integrated to sense the output current and diagnostic fault conditions.

When the fault diagnostic control pin is low (DEN = L), the CS pin is internally high impedance. When DEN = H, a current mirror is internally implemented to source a current of  $I_{OUTx}/K_{CS}$ , which is directed outward to the external resistor connected between the CS pin and the ground, and a voltage is formed on the CS pin. It is suggested to keep the CS voltage in the range of 0 to 4 V during normal operation. Use [Equation 1](#) to calculate the external current sense resistor,  $R_{CS}$ .

$$R_{CS} = \frac{V_{CS}}{I_{CS}} = \frac{V_{CS} \times K_{CS}}{I_{OUT}} \quad (1)$$

where,  $K_{CS}$  is the ratio of the output current to the sensed current. It is a constant value regardless of temperature and supply voltage variations.

When fault conditions occur, the CS pin works as a fault indication pin. In the on state, the  $V_{CS}$  voltage is almost 0 while operating in the condition of an open-load or short-to-battery fault. In the OFF state, the  $V_{CS}$  voltage is internally pulled-up to  $V_{CS,H}$  while operating in the condition of a current-limit, thermal-shutdown, thermal-swing, open-load, or short-to-battery fault. Refer to [Diagnostics and Fault Protections](#) for more details.

**Multiplexing of Current Sense (SEH, SEL)**

For the TPS42Q20BQ, SEH and SEL pins are used to select the output channel that needs current detection.

**Adjustable Current Limit (ICL)**

The TPS42Q20Q integrates an accurate current limit function, and it is adjustable with the external resistor  $R_{ICL}$ . When the overload or short-to-ground condition occurs, the current limit function will limit the maximum current through the power FET at the set value and pull up the CS pin voltage to  $V_{CS}$  internally.

There are two current-limit thresholds: the internal current limit and the external adjustable current limit.

While the ICL pin is connected to ground directly, the internal current limitation is used. The internal current limit is set to a fixed value of 3.5 A typically.

While an external resistor is connected at the ICL pin, it transforms a proportional load current into a voltage signal, which is compared with the internal reference voltage,  $V_{CL,TH}$ . When  $V_{ICL}$  exceeds  $V_{CL,TH}$ , a closed feedback loop is immediately activated, and the current is clamped at the set value. When a ground network is used, the  $R_{ICL}$  must be connected to the device GND directly. Use [Equation 3](#) to calculate the  $R_{ICL}$ .

$$\frac{V_{CL,TH}}{R_{ICL}} = \frac{I_{OUT}}{K_{CL}} \quad (2)$$

$$R_{ICL} = \frac{V_{CL,TH} \times K_{CL}}{I_{OUT}} \quad (3)$$

## Automotive 40-V 160-mΩ 4-Channel High-Side Power Switch

After the VS is powered up and IN is high, both the internal current limit and the external current limit are active, and the lower one is utilized as the effective current limit.

To provide enhanced protection against a hard short-to-ground condition, an open-loop fast-response mechanism is set to turn off the channel before the current-limit closed loop is established. The open-loop response time is approximately 1 μs.

### Inductive Load Switching-Off Clamp

When an inductive load of the TPS42Q20Q is turned off, the output voltage is drawn down to a negative level due to the inductance characteristics. The internal power MOSFET could be damaged if the drain-to-source voltage ( $V_{DS}$ ) is not clamped during the current decay period. In this condition, the  $V_{DS,CLAMP}$  voltage is necessary to limit the voltage across the drain and source, and thus prevent the device from damage. During the current-decay period, the TPS42Q20Q turns on the internal power MOSFET to release the energy stored in the inductance. Both the energy from the power supply and the energy from the inductive load are dissipated by the high-side power switch. If there is any resistance in series with the inductance, part of the energy will also be dissipated through this resistance. For PWM-controlled inductive loads, it is recommended to add an external freewheeling diode to protect the device from repetitive power stress.

### Diagnosis Enable Function (DEN)

The TPS42Q20Q uses the DEN pin to control whether the device diagnostic function is active or not. When multiple TPS42Q20Q chips share the same ADC or I/O channel, the multiplexing function can be achieved by the DEN control. Additionally, pulling down the DEN pin can significantly reduce the TPS42Q20Q's total power consumption to below 500 nA.

**Table 2. DEN Logic Table**

| DEN | INx Pin | SEH | SEL | CS Channel | CS, $\overline{\text{FAULT}}$ , $\overline{\text{STx}}$ | Protections and Diagnostics                           |
|-----|---------|-----|-----|------------|---------------------------------------------------------|-------------------------------------------------------|
| H   | –       | 0   | 0   | Channel 1  | See Table 3.                                            | See Table 3.                                          |
|     | –       | 0   | 1   | Channel 2  | See Table 3.                                            | See Table 3.                                          |
|     | –       | 1   | 0   | Channel 3  | See Table 3.                                            | See Table 3.                                          |
|     | –       | 1   | 1   | Channel 4  | See Table 3.                                            | See Table 3.                                          |
| L   | H       | –   | –   | –          | High Impedance                                          | Diagnostics are disabled, and protections are normal. |
|     | L       | –   | –   | –          | High Impedance                                          | Diagnostics are disabled, and no protection.          |

### Diagnostics and Fault Protections

When DEN is high, status indication ( $\overline{\text{STx}}$ ) or current sense (CS) is enabled. When DEN is low, status indication ( $\overline{\text{STx}}$ ) or current sense (CS) is disabled, and the output of  $\overline{\text{STx}}$  or CS is in high-impedance mode.

**Table 3. Fault Table**

| Condition                 | INx | OUTx | THER | Criterion      | $\overline{\text{STx}}$<br>(TPS42Q20<br>AQ) | CS<br>(TPS42Q20<br>BQ) | $\overline{\text{FAULT}}$<br>(TPS42Q20<br>BQ) | Fault<br>Recovery |
|---------------------------|-----|------|------|----------------|---------------------------------------------|------------------------|-----------------------------------------------|-------------------|
| Normal                    | L   | L    | –    | –              | H                                           | 0                      | H                                             | –                 |
|                           | H   | H    | –    | –              | H                                           | Linear                 | H                                             | –                 |
| Overload, Short to Ground | H   | L    | –    | Current limit. | L                                           | $V_{CS,H}$             | L                                             | Auto              |

## Automotive 40-V 160-mΩ 4-Channel High-Side Power Switch

| Condition                                                           | INx | OUTx | THER | Criterion                                             | $\overline{\text{STx}}$<br>(TPS42Q20<br>AQ) | CS<br>(TPS42Q20<br>BQ) | $\overline{\text{FAULT}}$<br>(TPS42Q20<br>BQ) | Fault<br>Recovery |
|---------------------------------------------------------------------|-----|------|------|-------------------------------------------------------|---------------------------------------------|------------------------|-----------------------------------------------|-------------------|
| Open Load <sup>(1)</sup> ,<br>Short to Battery,<br>Reverse Polarity | L   | H    | –    | $V_{\text{VS}} - V_{\text{OUTx}} < V_{\text{OL,OFF}}$ | L                                           | $V_{\text{CS,H}}$      | L                                             | Auto              |
| Over Temperature                                                    | H   | –    | L    | Thermal shutdown.                                     | L                                           | $V_{\text{CS,H}}$      | L                                             | Auto              |
|                                                                     | H   | –    | H    | Thermal shutdown.                                     | L                                           | $V_{\text{CS,H}}$      | L                                             | Latch             |
|                                                                     | H   | –    | –    | Thermal swing.                                        | L                                           | $V_{\text{CS,H}}$      | L                                             | Auto              |

(1) Need an external pull-up resistor during off-state

### Overload and Short to Ground Fault

When the INx pins are high and the output channels are switched on, the over-load or short-to-ground condition will trigger the device current limitation. In this condition, the output current of the fault channel is limited to the set value, and the corresponding  $\overline{\text{STx}}$  pin is pulled low or the CS pin is pulled to  $V_{\text{CS,H}}$ . The current limit and the  $\overline{\text{STx}}$  or the CS pin will be recovered automatically when the fault is removed. The long-time current limit will cause the thermal shutdown to prevent the device from being damaged.

### Open Load Fault

When the INx pins are high and the output channels are switched on, there will be an output current supplied to the load.

- Note that the detection is not reported on the  $\overline{\text{STx}}$  or  $\overline{\text{FAULT}}$  pins.
- The MCU must multiplex the SEL and SEH pins to detect the channel-on open-load fault proactively.

When the INx pins are low and the output channel is switched off, the output voltage will be pulled down to 0 V with a connected load and will remain close to the supply voltage with an open load ( $V_{\text{VS}} - V_{\text{OUTx}} < V_{\text{OL,OFF}}$ ).

- The TPS42Q20AQ will report an open-load fault by pulling the corresponding  $\overline{\text{STx}}$  pin low.
- The TPS42Q20BQ will pull the CS pin voltage up to  $V_{\text{CS,H}}$ . It is recommended to use an external pull-up resistor at the OUTx pin to eliminate the influence of the leakage current,  $I_{\text{OL,OFF}}$ . The pull-up current should not be greater than the load current to prevent false triggering during normal operation. It is recommended to use a switch in series with the pull-up resistor to reduce the standby current and use the pull-up resistor  $R_{\text{PU}}$  less than 15 kΩ.

### Short-to-Battery Fault

The TPS42Q20Q integrates the short-to-battery fault detection, which has the same operating mechanism and behavior as the open-load detection.

In the ON state with the INx high, the reverse current, caused by the short-to-battery fault, flows through the internal MOSFET and leads to small power dissipation on the device.

In the OFF state with the INx low, the short-to-battery fault is reported when  $V_{\text{OUTx}}$  is greater than  $V_{\text{VS}}$ , but the reverse current is determined by the voltage difference between  $V_{\text{OUTx}}$  and  $V_{\text{VS}}$ . When  $V_{\text{OUTx}} - V_{\text{VS}} < V_{\text{F}}$ , there is no reverse current. When  $V_{\text{OUTx}} - V_{\text{VS}} > V_{\text{F}}$ , reverse current occurs. Please note, that the reverse current should be less than  $I_{\text{REV}}$  to prevent the device from damage.

### Reverse-Polarity Fault

The TPS42Q20Q integrates the reverse-polarity fault detection, which has the same operating mechanism and behavior as the open-load detection.

In the ON state with the INx high, the reverse current, caused by the reverse polarity, flows through the internal MOSFET and leads to small power dissipation on the device.

---

**Automotive 40-V 160-mΩ 4-Channel High-Side Power Switch**

---

In the OFF state with the INx low, reverse-polarity is reported and the reverse current flows through the body diode, which will cause high power dissipation. Please note that the reverse current should be less than  $I_{REV}$  to prevent the device from damage.

**Reverse-Current Protection**

Either the short-to-battery fault or the reverse-polarity fault will cause the reverse current to flow through the device. Usually, there are two methods to block the reverse current.

1. Add a block diode between the power supply and the VS pin. With this method, both the device and load are protected from the reverse current fault.
2. Add a ground network between the GND pin and the system ground. It is recommended to use an  $I_F > 100\text{mA}$  diode and a 4.7-kΩ resistor in parallel in the ground network. With this method, only the TPS42Q20Q device is protected from the reverse current fault, and the load is protected by itself.

Please note that when the ground network is used, the  $R_{ICL}$  must be connected to GND pin directly.

**Loss-of-Ground Protection**

The TPS42Q20Q turns off the output when the loss-of-ground fault occurs, no matter whether the IN-pin signal is high or low.

**Loss-of-Power Supply Protection**

The TPS42Q20Q turns off the output when the loss-of-power fault occurs, no matter whether the IN-pin signal is high or low. When a loss-of-power fault occurs, the inductive load will still sink current from all pins connected. It is recommended to use the ground network or a freewheeling diode to prevent damage from negative voltage.

**Over-Temperature Fault and Protection**

The TPS42Q20Q integrates two mechanisms for over-temperature diagnosis and protection: thermal shutdown and thermal swing.

When the junction temperature  $T_J$  rises above the thermal shutdown threshold  $T_{SD}$ , thermal shutdown works and turns off the output immediately. When the device cools down and the junction temperature falls below  $T_{SD} - T_{HYS}$ , the output turns on again. In the thermal shutdown condition, the  $\overline{STx}$  pin of TPS42Q20AQ is pulled down and the CS pin of TPS42Q20BQ is pulled up to  $V_{CS,H}$ , and the current limit is reduced to  $I_{LIM,STD}$  or half of the set value to prevent the device from repeating thermal shutdown. The thermal shutdown fault signal and the reduced current limit will not be reset until the junction temperature decreases below  $T_{SD,RST}$ .

When the MOSFET junction temperature  $T_{MOS}$  rises much more quickly than the logic control module junction temperature  $T_{LOGIC}$  and the temperature difference  $\Delta T = T_{MOS} - T_{LOGIC} > T_{SW}$ , the thermal swing works and turns off the output immediately. When the MOSFET cools down and the temperature difference  $\Delta T = T_{MOS} - T_{LOGIC} < T_{SW}T_{HYS}$ , the output turns on again. In the thermal swing condition, the  $\overline{STx}$  pin of TPS42Q20AQ is pulled down and the CS pin of TPS42Q20BQ is pulled up to  $V_{CS,H}$ . The thermal swing fault signal automatically resets after the device recovers from the thermal swing condition.

## Application and Implementation

### Note


Information in the following application sections is not part of the 3PEAK's component specification and 3PEAK does not warrant its accuracy or completeness. 3PEAK's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

## Application Information

The TPS42Q20Q is a 160-m $\Omega$  4-channel high-side power switch product with AEC-Q100 qualified. The following application schematic shows a typical usage of the TPS42Q20Q series.

## Typical Application

Figure 17 shows the typical protection application schematic of the TPS42Q20Q.



**Figure 17. Typical Application Circuit**

**Power Dissipation**

During normal operation, the junction temperature should meet the requirements in the Recommended Operating Conditions table. Use [Equation 4](#) and [Equation 5](#) to calculate the power dissipation and estimate the junction temperature.

The power dissipation ( $P_D$ ) can be calculated using [Equation 4](#).

$$P_D = (I_{OUT1}^2 + I_{OUT2}^2 + I_{OUT3}^2 + I_{OUT4}^2) \times R_{ON} + V_S \times I_Q \quad (4)$$

Where,

- $I_{OUTx}$  is the output current of each channel,
- $R_{ON}$  is the turn-on resistance,
- $V_S$  is the VS pin power supply voltage,
- $I_Q$  is the quiescent current.

The junction temperature ( $T_J$ ) can be estimated using [Equation 5](#).

$$T_J = T_A + P_D \times \theta_{JA} \quad (5)$$

Where,

- $T_A$  is the ambient temperature,
- $P_D$  is the power dissipation,
- $\theta_{JA}$  is the junction-to-ambient thermal resistance.


## Layout

### Layout Guideline

To get good thermal performance and prevent over-temperature protection, the PCB layout is important. A well-designed PCB layout can effectively optimize heat dissipation, which is crucial for ensuring the long-term reliability of the device.


- It is recommended to maximize the coverage of copper on the PCB to enhance the thermal conductivity of the board. Since the primary heat flow path from the package to the surrounding environment passes through the copper on the PCB, having maximum copper coverage is particularly important when there is no heat sink attached to the opposite side of the board.
- It is recommended to place as many thermal vias as possible underneath the package ground pad to optimize the thermal conductivity of the board.
- It is suggested that all thermal vias be either plated shut or plugged and capped on both sides of the board to prevent solder voids to maintain reliability and performance.
- It is recommended to use wide traces or thick copper weight in the input/output current paths to minimize  $I \times R$  voltage drop.

## Layout Example




**Figure 18. Layout Example**

# Automotive 40-V 160-mΩ 4-Channel High-Side Power Switch



**Figure 19. Layout Example with a Ground Network**

## Tape and Reel Information





| Order Number      | Package  | D1 (mm) | W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P0 (mm) | W0 (mm) | Pin1<br>Quadrant |
|-------------------|----------|---------|---------|---------|---------|---------|---------|---------|------------------|
| TPS42Q20AQ-TSCR-S | ETSSOP28 | 330     | 21.6    | 6.9     | 10.2    | 1.5     | 12      | 16      | Q1               |
| TPS42Q20BQ-TSCR-S | ETSSOP28 | 330     | 21.6    | 6.9     | 10.2    | 1.5     | 12      | 16      | Q1               |

## Package Outline Dimensions

### ETSSOP-28

#### Package Outline Dimensions

#### TSC(ETSSOP-28-D)



| Symbol | Dimensions<br>In Millimeters |       | Dimensions<br>In Inches |       |
|--------|------------------------------|-------|-------------------------|-------|
|        | MIN                          | MAX   | MIN                     | MAX   |
| A      | ---                          | 1.200 | ---                     | 0.047 |
| A1     | 0.050                        | 0.150 | 0.002                   | 0.006 |
| A2     | 0.800                        | 1.050 | 0.031                   | 0.041 |
| b      | 0.190                        | 0.300 | 0.007                   | 0.012 |
| c      | 0.090                        | 0.200 | 0.004                   | 0.008 |
| D      | 9.600                        | 9.800 | 0.378                   | 0.386 |
| D1     | 3.510                        | 3.760 | 0.138                   | 0.148 |
| E      | 6.200                        | 6.600 | 0.244                   | 0.260 |
| E1     | 4.300                        | 4.500 | 0.169                   | 0.177 |
| E2     | 2.500                        | 2.700 | 0.098                   | 0.106 |
| e      | 0.650 BSC                    |       | 0.026 BSC               |       |
| L      | 0.450                        | 0.750 | 0.018                   | 0.030 |
| θ      | 0°                           | 8°    | 0°                      | 8°    |

#### NOTES

1. Do not include mold flash or protrusion.
2. This drawing is subject to change without notice.

## Order Information

| Order Number      | Operating Temperature Range | Package  | Marking Information | MSL  | Transport Media, Quantity | Eco Plan |
|-------------------|-----------------------------|----------|---------------------|------|---------------------------|----------|
| TPS42Q20AQ-TSCR-S | -40 to 125°C                | ETSSOP28 | SQ20A               | MSL3 | 2,500                     | Green    |
| TPS42Q20BQ-TSCR-S | -40 to 125°C                | ETSSOP28 | SQ20B               | MSL3 | 2,500                     | Green    |

**Green:** 3PEAK defines "Green" to mean RoHS compatible and free of halogen substances.

## **IMPORTANT NOTICE AND DISCLAIMER**

**Copyright**© 3PEAK 2012-2025. All rights reserved.

**Trademarks.** Any of the 思瑞浦 or 3PEAK trade names, trademarks, graphic marks, and domain names contained in this document /material are the property of 3PEAK. You may NOT reproduce, modify, publish, transmit or distribute any Trademark without the prior written consent of 3PEAK.

**Performance Information.** Performance tests or performance range contained in this document/material are either results of design simulation or actual tests conducted under designated testing environment. Any variation in testing environment or simulation environment, including but not limited to testing method, testing process or testing temperature, may affect actual performance of the product.

**Disclaimer.** 3PEAK provides technical and reliability data (including data sheets), design resources (including reference designs), application or other design recommendations, networking tools, security information and other resources "As Is". 3PEAK makes no warranty as to the absence of defects, and makes no warranties of any kind, express or implied, including without limitation, implied warranties as to merchantability, fitness for a particular purpose or non-infringement of any third-party's intellectual property rights. Unless otherwise specified in writing, products supplied by 3PEAK are not designed to be used in any life-threatening scenarios, including critical medical applications, automotive safety-critical systems, aviation, aerospace, or any situations where failure could result in bodily harm, loss of life, or significant property damage. 3PEAK disclaims all liability for any such unauthorized use.

This page intentionally left blank