

GENERAL DESCRIPTION

The LW67XX series is a group 70V high accuracy LDO regulator. The 3.0 μ A power consumption makes it ideal for most HV power-saving systems. The maximum operating voltage can be as high as 70V. The LW67XX can deliver 100mA output current.

The other features include current limiting protection, short circuit protection and thermal shutdown protection.

The LW67XX is available in ESOP-8, DFN2x2-6L, SOT89-3L and TO-252 packages.


FEATURES

- Low Power Consumption: 3.0 μ A(Typ.)
- Operating Voltage Range: from 3.5V to 70V
- Output Voltage Range: from 2.5V to 15V
- Maximum Output Current: 100mA
- Output Accuracy: $\pm 1.0\%$ @+25 $^{\circ}$ C
- Low Dropout Voltage: 635mV@100mA/3.3V
- High PSRR: 80dB@1kHz, 10mA
- Low Temperature Coefficient
- Current Limiting Protection
- Output Short-Circuit Protection
- Over-Temperature Protection
- Fast Discharge Function
- Stable with 1 μ F Output Capacitor


APPLICATIONS

- Battery Supplied Systems
- Telecom Systems
- Portable Audio & Video Equipment
- Ultra-Low Power Microcontroller

TYPICAL APPLICATION CIRCUIT




TYPICAL PERFORMANCE CHARACTERISTICS




PIN DESCRIPTION:

PIN No				SYMBOL	DESCRIPTION
ESOP-8	DFN2x2-6L	SOT89-3L (Type-B)	TO-252 /SOT89-3L (Type-C)		
8	6	3	1	VIN	Input pin. For best transient response and to minimize input impedance, use the recommended value or larger ceramic capacitor from IN to ground as listed in the Recommended Operating Conditions table and the Input and Output Capacitor Requirements section. Place the input capacitor as close to the output of the device as possible.
4	3	2、TAB	2、TAB	GND	Ground pin.
5	4	--	--	EN	Enable pin. Drive EN greater than $V_{EN(HI)}$ to turn on the regulator. Drive EN less than $V_{EN(LO)}$ to put the low-dropout regulator (LDO) into shutdown mode.
2,3,6,7	2,5	--	--	NC	No internal connection. Ground this pin for better thermal performance.
1	1	1	3	VOUT	Regulated output voltage pin. Connect a low-equivalent series resistance (ESR) capacitor to this pin. For best transient response, use the nominal recommended value or larger capacitor from OUT to GND. An internal pulldown resistor prevents a charge from remaining on OUT when the regulator is in shutdown mode ($V_{EN} < V_{EN(LOW)}$).
Thermal pad	Thermal pad	--	--	Pad	The thermal pad is electrically connected to the GND node. Connect to the GND plane for improved thermal performance.


PIN ASSIGNMENT




ESOP-8




DFN2x2-6L



SOT89-3L (Type-B)



SOT89-3L (Type-C)



TO-252

MARK INFORMATION:**TO-252/SOT89-3L****XX: VOLTAGE****Y: DATE CODE**

LW67XX
YYYYY

ESOP-8/ DFN2x2-6L**XX: VOLTAGE****YY: DATE CODE**

LW67XX
YYYYY
•

ABSOLUTE MAXIMUM RATINGS ⁽¹⁾:(T_A =25℃, unless otherwise specified.)

SYMBOL	ITEM		RATING	UNIT
V _{IN}	Supply Voltage		-0.3~80	V
V _{EN}	EN Pin Voltage		-0.3~80	V
V _{OUT}	V _{OUT} Pin Voltage		-0.3~16	V
V _(ESD)	ESD Susceptibility, HBM ⁽²⁾		±2000	V
R _{θJA}	Junction-to-ambient Thermal Resistance ⁽³⁾	ESOP-8	45	℃/W
		DFN2x2-6L	60	
		SOT89-3L	90	
		TO-252	35	
T _J	Junction Temperature Range		-40~150	℃
T _{STG}	Storage Temperature Range		-40~150	℃
T _{SOLDER}	Lead Temperature (Soldering)		260℃, 10s	

Note:

1. Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability
2. per ANSI/ESDA/JEDEC JS-001
3. Device mounted on FR-4 PCB, Refer to JESD51-3 for detailed information on the board construction

RECOMMENDED OPERATING RANGE:

SYMBOL	ITEM	VALUE	UNIT
V _{IN}	V _{IN} Supply Voltage	3.5~70	V
V _{EN}	EN Pin Voltage	0~70	V
V _{OUT}	V _{OUT} Pin Voltage	2.5~15	V
I _{OUT}	Output Current	0~100	mA
T _J	Junction Temperature Range	-40~125	℃

ELECTRICAL CHARACTERISTICS:


($V_{IN}=V_{OUT(NOM)}+1V$ or $2V$, whichever is greater, $C_{IN}=C_{OUT}=1\mu F$, unless otherwise specified, typical values are at $T_A = 25^{\circ}C$.)

Symbol	Parameter	Test Conditions		MIN	TYP	MAX	Units
V_{IN}	Input Voltage			3.5		70	V
V_{OUT}	Output Accuracy	$I_{OUT}=1mA$		-1.0		+1.0	%
I_{LIM}	Current Limit ⁽¹⁾			100	150		mA
I_Q	Quiescent Current	$V_{IN}=V_{EN}=V_{OUT}+1V$, No Load	$V_{OUT}\leq 6.0V$		3.0	5.0	μA
			$V_{OUT}> 6.0V$		4.0	6.0	
I_{SHD}	Shutdown Current	$V_{EN}=0V$			0.35	1.0	μA
V_{DROP}	Dropout Voltage ^{(1) (2)}	$I_{OUT}=100mA, V_{OUT}=3.3V$			635		mV
		$I_{OUT}=100mA, V_{OUT}=5.0V$			580		
		$I_{OUT}=100mA, V_{OUT}=15V$			545		
$\Delta V_{OUT}/$ ($\Delta V_{IN}\cdot V_{OUT(NOM)}$)	Line Regulation	$V_{IN}=V_{OUT}+1V$ to $70V, I_{OUT}=1mA$			0.01	0.02	%/V
ΔV_{OUT}	Load Regulation	$1mA\leq I_{OUT}\leq 100mA$			30	60	mV
I_{SHORT}	Short Current ⁽¹⁾	$V_{OUT}=0V$			15		mA
V_{ENH}	EN High Voltage	$V_{IN}=3.5V$ to $70V, I_{OUT}=1mA$		1.5			V
V_{ENL}	EN Low Voltage					0.5	V
PSRR	Power Supply Rejection Ratio	$V_{IN}=4.3V, V_{OUT}=3.3V$, $V_{PP}=0.5V, C_{IN}=None$, $I_{OUT}=10mA$	$f=217Hz$		83		dB
			$f=1KHz$		80		
			$f=10KHz$		71		
			$f=100KHz$		58		
T_{SD}	Thermal Shutdown	Temperature rising			160		$^{\circ}C$
ΔT_{SD}	TSD Hysteresis	Temperature falling			30		$^{\circ}C$
R_{DSCHG}	Output Discharge Resistance	$V_{IN}=12V, V_{EN}=0V$			80		Ω

NOTES:

1. Guaranteed by design
2. The dropout voltage is defined as $V_{IN} - V_{OUT}$, when $V_{OUT}=95\%\cdot V_{OUT(NOM)}$

SIMPLIFIED BLOCK DIAGRAM:



DETAIL OPERATION DESCRIPTION:

The LW67XX Series is a low power consumption low drop-out voltage regulator. It consists of a current limiter circuit, a driver transistor, a precision reference voltage and an error correction circuit, and is compatible with low ESR ceramic capacitors. The current limiter's fold-back circuit operates as a short circuit protection as well as the output current limiter.

Current Limiting and Short-Circuit Protection

The current limit circuitry prevents damage to the MOSFET switch and the hub downstream port but can deliver load current up to the current limit threshold of typically 100mA through the switch. When a heavy load or short circuit is applied to an enabled switch, a large transient current may flow until the current limit circuitry responds. Once this current limit threshold is exceeded the device enters constant current mode until the thermal shutdown occurs or the fault is removed.

TYPICAL OPERATING CHARACTERISTICS:

(Tested under $T_A = 25^\circ\text{C}$, $C_{IN}=C_{OUT}=1\mu\text{F}$, unless otherwise specified)




Figure 1. V_{OUT} vs Temperature




Figure 2. V_{OUT} vs Temperature




Figure 3. V_{OUT} vs Temperature




Figure 4. I_Q vs V_{IN}




Figure 5. I_Q vs V_{IN}




Figure 6. I_Q vs V_{IN}




Figure 7. V_{EN} VS V_{IN}




Figure 8. V_{EN} VS V_{IN}




Figure 9. V_{EN} VS V_{IN}




Figure 10. I_{GND} vs I_{OUT}




Figure 11. I_{GND} vs I_{OUT}




Figure 12. I_{GND} vs I_{OUT}




Figure 13. V_{OUT} vs V_{IN}




Figure 14. Line Regulation




Figure 15. V_{OUT} vs V_{IN}




Figure 16. Line Regulation




Figure 17. V_{OUT} vs V_{IN}




Figure 18. Line Regulation




Figure 19. Dropout Voltage VS I_{OUT}




Figure 20. Dropout Voltage VS I_{OUT}




Figure 21. Dropout Voltage VS I_{OUT}




Figure 22. Load Regulation




Figure 23. Load Regulation






Figure 24. Load Regulation



Time (20 μ s / div)

Channel 1 = V_{IN} , Channel 2 = V_{OUT} , $V_{IN}=4.3V \rightarrow 10V$,
 $T_r=T_f=5\mu s$, $V_{OUT}=3.3V$, $I_{OUT}=10mA$


Figure 25. Line Transient



Time (20 μ s / div)

Channel 1 = V_{IN} , Channel 2 = V_{OUT} , $V_{IN}=6.0V \rightarrow 10V$,
 $T_r=T_f=5\mu s$, $V_{OUT}=5.0V$, $I_{OUT}=10mA$


Figure 26. Line Transient



Time (20 μ s / div)

Channel 1 = V_{IN} , Channel 2 = V_{OUT} , $V_{IN}=16V \rightarrow 24V$,
 $T_r=T_f=5\mu s$, $V_{OUT}=15V$, $I_{OUT}=10mA$


Figure 27. Line Transient



Time (100 μ s / div)

Channel 1 = I_{OUT} , Channel 2 = V_{OUT} , $V_{IN}=4.3V$, $V_{OUT}=3.3V$,
 $C_{IN}=C_{OUT}=1\mu F$


Figure 28. Load Transient (1 mA $\rightarrow$ 100 mA)



Time (100 μ s / div)

Channel 1 = I_{OUT} , Channel 2 = V_{OUT} , $V_{IN}=6.0V$, $V_{OUT}=5.0V$,
 $C_{IN}=C_{OUT}=1\mu F$


Figure 29. Load Transient (1 mA $\rightarrow$ 100 mA)



Time (100 μ s / div)


Channel 1 = I_{OUT} , Channel 2 = V_{OUT} , $V_{IN}=16V$, $V_{OUT}=15V$,
 $C_{IN}=C_{OUT}=1\mu F$

Figure 30. Load Transient (1 mA $\rightarrow$ 100 mA)




Channel 2 = EN, Channel 3 = V_{OUT} , $V_{IN}=4.3V$, $EN=0 \rightarrow 4.3V$, $V_{OUT}=3.3V$, $C_{IN}=C_{OUT}=1\mu F$, No Load

Figure 31. Start-Up with Enable




Channel 2 = EN, Channel 3 = V_{OUT} , $V_{IN}=4.3V$, $EN=4.3 \rightarrow 0V$, $V_{OUT}=3.3V$, $C_{IN}=C_{OUT}=1\mu F$, No Load

Figure 32. Shut-Down with Enable




Channel 2 = EN, Channel 3 = V_{OUT} , $V_{IN}=6.0V$, $EN=0 \rightarrow 6.0V$, $V_{OUT}=5.0V$, $C_{IN}=C_{OUT}=1\mu F$, No Load

Figure 33. Start-Up with Enable




Channel 2 = EN, Channel 3 = V_{OUT} , $V_{IN}=6.0V$, $EN=6.0 \rightarrow 0V$, $V_{OUT}=5.0V$, $C_{IN}=C_{OUT}=1\mu F$, No Load

Figure 34. Shut-Down with Enable









Channel 2 = EN, Channel 3 = V_{OUT} , $V_{IN}=16V$, $EN=0 \rightarrow 10V$, $V_{OUT}=15V$, $C_{IN}=C_{OUT}=1\mu F$, No Load

Figure 35. Start-Up with Enable



Channel 2 = EN, Channel 3 = V_{OUT} , $V_{IN}=16V$, $EN=10 \rightarrow 0V$, $V_{OUT}=15V$, $C_{IN}=C_{OUT}=1\mu F$, No Load

Figure 36. Shut-Down with Enable



APPLICATION INFORMATION:

- **Input Capacitor Selection**

Like any low-dropout regulator, the external capacitors used with the LW67XX Series must be carefully selected for regulator stability and performance. Using a capacitor whose value is $\geq 1\mu\text{F}$ on the LW67XX Series input and the amount of capacitance can be increased without limit. The input capacitor must be located a distance of not more than 0.5 inch from the input pin of the IC and returned to a clean analog ground. Any good quality ceramic or tantalum can be used for this capacitor. The capacitor with larger value and lower ESR (equivalent series resistance) provides better PSRR and line-transient response.

- **Output Capacitor Selection**

The output capacitor must meet both requirements for minimum amount of capacitance and ESR in all LDOs application. The LW67XX Series is designed specifically to work with low ESR ceramic output capacitor in space-saving and performance consideration. Using a ceramic capacitor whose value is at least $1\mu\text{F}$ on the LW67XX Series output ensures stability. Output capacitor of larger capacitance can reduce noise and improve load transient response, stability, and PSRR. The output capacitor should be located not more than 0.5 inch from the VOUT pin of the LW67XX Series and returned to a clean analog ground.

- **Layout considerations**

To improve ac performance such as PSRR, output noise, and transient response, it is recommended that the PCB be designed with separate ground planes for VIN and VOUT, with each ground plane connected only at the GND pin of the device.

ORDER INFORMATION:

LW67①②③④⑤⑥

Designator	Item	Symbol	Description
①②	Output Voltage	25~A5	e.g. 2.8V→①=2,②=8
③④⑤⑥	Packages	ES8H	ESOP-8
		N22G	DFN2x2-6L
		B89C	SOT89-3L(Type-B)
		C89C	SOT89-3L(Type-C)
		A52B	TO-252


Part #	Output Voltage	Package	Shipping
LW6725ES8H	2.5V	ESOP-8	4000 Pcs / Tape & Reel
LW6730ES8H	3.0V		
LW6733ES8H	3.3V		
LW6736ES8H	3.6V		
LW6740ES8H	4.0V		
LW6750ES8H	5.0V		
LW67A2ES8H	12V		
LW67A5ES8H	15V		
LW6725N22G	2.5V	DFN2x2-6L	3000 Pcs/ Tape & Reel
LW6730N22G	3.0V		
LW6733N22G	3.3V		
LW6736N22G	3.6V		
LW6740N22G	4.0V		
LW6750N22G	5.0V		
LW67A2N22G	12V		
LW67A5N22G	15V		

Part #	Output Voltage	Package	Shipping
LW6725B89C	2.5V	SOT89-3L(Type-B)	1000 Pcs / Tape & Reel
LW6730B89C	3.0V		
LW6733B89C	3.3V		
LW6736B89C	3.6V		
LW6740B89C	4.0V		
LW6750B89C	5.0V		
LW67A2B89C	12V		
LW67A5B89C	15V		
LW6725C89C	2.5V	SOT89-3L(Type-C)	1000 Pcs / Tape & Reel
LW6730C89C	3.0V		
LW6733C89C	3.3V		
LW6736C89C	3.6V		
LW6740C89C	4.0V		
LW6750C89C	5.0V		
LW67A2C89C	12V		
LW67A5C89C	15V		
LW6725A52B	2.5V	TO-252	2500 Pcs / Tape & Reel
LW6730A52B	3.0V		
LW6733A52B	3.3V		
LW6736A52B	3.6V		
LW6740A52B	4.0V		
LW6750A52B	5.0V		
LW67A2A52B	12V		
LW67A5A52B	15V		

If customers have special output voltage requirements, please contact us.


PACKAGE OUTLINE:

ESOP-8 Package




Symbol	Dimensions In Millimeters		
	Min	Typ	Max
A	4.70	4.90	5.10
A1	0.37	0.42	0.47
A2	1.22	1.27	1.32
B	3.70	3.90	4.10
B1	5.80	6.00	6.20
B2	3.75	3.85	3.95
B3	3.80	3.90	4.00
C	0.16	0.21	0.26
C1	0.04	0.11	0.18
C2	1.30	1.40	1.50
D	0.95	1.05	1.15
D1	0.40	0.50	0.60
E	4.65	4.85	5.05
E1	4.70	4.90	5.10
θ	REF 8°		
G	3.20	3.35	3.50
F	2.20	2.35	2.50


DFN2x2-6L Package



俯视图




侧视图



背视图


SYMBOL	MILLMETER		
	MIN	NOM	MAX
A	0.70	0.75	0.80
A1	0.00	—	0.05
b	0.25	0.30	0.35
c	0.203 TYP		
D	1.95	2.00	2.05
D1	0.90	1.00	1.10
E	1.95	2.00	2.05
E1	1.55	1.60	1.65
E2	0.20 REF		
e	0.65 BSC		
K	0.25 REF		
L	0.20	0.25	0.30

SOT89-3L Package



COMMON DIMENSION (MM)			
PKG	SOT89-3L		
Symbol	MIN	NOM	MAX
A	1.450	1.500	1.550
A1	0.350	0.400	0.450
b	0.350	0.430	0.500
b1	0.430	0.500	0.570
C	1.650	1.700	1.750
D	4.450	4.550	4.700
D1	1.470	1.500	1.550
E	4.100	4.200	4.300
E1	2.450	2.550	2.650
L1	0.630	0.700	0.770
L2	0.900	0.950	1.000

TO-252 Package



COMMON			
PKG	TO-252		
Symbol	Min	Nom	Max
A	2.200	2.300	2.400
A1	0.000	0.075	0.150
A2	0.460	0.525	0.590
A3	0.960	1.010	1.060
b	0.640	0.720	0.800
C	0.450	0.515	0.580
D	9.800	10.025	10.350
D1	6.000	6.100	6.200
D2	2.850	2.900	3.100
D3	0.490	0.800	1.000
E	6.400	6.550	6.700
E1	4.050	4.130	4.600
E2	2.250	2.286	2.300
L	1.400	1.550	1.700
e	7°	8°	9°
Q	0°	5°	10°

Revision History:

Revision	Date	Descriptions
Rev 0.1	Nov.2022	Initial Version
Rev 0.2	Sep.2023	Adjust product definition
Rev 1.0	Jan.2024	Formal Version
Rev 1.1	Oct.2024	Add Package DFN2x2-6L
Rev 1.2	Aug.2025	Distinguish I_Q under different conditions in Ectable
Rev 1.3	Apr.2026	Update Eletrical Characteristcs & Package Outline
Rev 1.4	Apr.2026	Update Absolute Maximum Ratings & Typical Operating Characteristics

DISCLAIMER:

- The product is not intended for use in applications that require extraordinary levels of quality and reliability, such as military, aviation/aerospace and life-support systems or other applications whose failure can be reasonably expected to result in serious physical or material damage.
- Lewa-Micro assumes no responsibility for equipment failures that result from using products at parameters that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any Lewa-Micro products described or contained herein.
- Specifications of any and all Lewa-Micro products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- Lewa-Micro strives to supply high-quality and high-reliability products. However, any and all semiconductor products have a certain probability of failure. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures including but not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- To comply with the compliance requirements of relevant export control laws and regulations, if any Lewa-Micro product (including technical data and services) stated herein is subject to relevant export control laws and regulations, it is recommended that the customer apply for and obtain an export license from the competent authority in advance in accordance with the requirements of relevant laws, and do not conduct export activities without obtaining the license. If the customer fails to comply with the aforementioned compliance requirements, all legal liabilities arising therefrom shall be borne solely by the customer.
- To protect Lewa-Micro's intellectual property rights and the security of commercial information, without the prior written permission of Lewa-Micro, no part of this document shall be reproduced or disseminated in any form or by any means (including photocopying, recording, and other electronic or mechanical means, as well as various information storage and retrieval systems). For unauthorized reproduction or dissemination, Lewa-Micro reserves the right to pursue legal liability.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. Lewa-Micro believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc.

Mailing Address: Unit 02&04&05, 10th Floor, Building 5, No.666 Shengxia Road, No.122 Yindong Road,
China (Shanghai) Pilot Free Trade Zone
Shanghai Lewa Micro-electronics Technology Co., Ltd