



钜地半导体
Tudi Semiconductor

Product Specification

TUDI-24AA08/24LC08B

8K I²C Serial EEPROM

网址 www.sztdbdt.com 🔍

用芯智造 · 卓越品质


**semiconductor device
manufacturer**

- Design
- research and development
- production
- and sales




Features

- Single Supply with Operation down to 1.7V for 24AA08 Devices, 2.5V for 24LC08B Devices
- Low-Power CMOS Technology:
 - Read current 1 mA, maximum
 - Standby current 1 μ A, maximum (I-temp.)
- 2-Wire Serial Interface, I²C Compatible
- Schmitt Trigger Inputs for Noise Suppression
- Output Slope Control to Eliminate Ground Bounce
- 100 kHz, 400 kHz and 1 MHz Compatibility
- Page Write Time: 5 ms, Maximum
- Self-Timed Erase/Write Cycle
- 16-Byte Page Write Buffer
- Hardware Write-Protect
- ESD Protection >4,000V
- More than 1 Million Erase/Write Cycles
- Data Retention >200 Years
- Factory Programming Available
- RoHS Compliant
- Temperature Ranges:
 - Industrial (I): -40°C to +85°C
 - Extended (E): -40°C to +125°C
- Automotive AEC-Q100 Qualified



SOP8/DIP8/MSOP8




SOT23-5

Description

The 24XX08 is an 8-Kbit Electrically Erasable PROM. The device is organized as four blocks of 256 x 8-bit memory with a two-wire serial interface. Its low-voltage design permits operation down to 1.7V with standby and active currents of only 1 μ A and 1 mA, respectively. The 24XX08 also has a page write capability for up to 16 bytes of data.



Block Diagram



ELECTRICAL CHARACTERISTICS

Absolute Maximum Ratings

V_{CC}	6.5V
All inputs and outputs w.r.t. V_{SS}	-0.3V to $V_{CC} + 1.0V$
Storage temperature	-65°C to +150°C
Ambient temperature with power applied.....	-40°C to +125°C
ESD protection on all pins	≥ 4 kV

NOTICE: Stresses above those listed under “ Absolute Maximum Ratings ” may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational listings of this specification is not implied. Exposure to maximum rating conditions for extended periods may affect device reliability



TABLE 1: DC CHARACTERISTICS

DC CHARACTERISTICS			Industrial(I):TA=-40°C to+85°C,VcC=+1.7V to+5.5V Extended (E):TA=-40°C to+125°C,VcC=+2.5V to+5.5V (24LC08B)				
Param. No.	Symbol	Characteristic	Min.	Typical	Max.	Units	Conditions
D1	V _{IH}	High-Level Input Voltage	0.7 V _{CC}	—	—	V	
D2	V _{IL}	Low-Level Input Voltage	—	—	0.3 V _{CC}	V	
D3	V _{HYS}	Hysteresis of SchmittTrigger Inputs (SDA,SCL pins)	0.05 V _{CC}	—	—	V	Note
D4	V _{OL}	Low-Level OutputVoltage	—	—	0.40	V	I _{OL} =3.0 mA,V _{CC} =2.5V
D5	I _{LI}	Input Leakage Current	—	—	±1	μA	V _{IN} =V _{SS} or V _{CC}
D6	I _{LO}	Output Leakage Current	—	—	± 1	μA	V _{OUT} =V _{SS} or V _{CC}
D7	C _{IN} ,C _{OUT}	Pin Capacitance(all inputs/outputs)	—	—	10	pF	V _{CC} =5.0V(Note)T _A =25°C, F _{CLK} =1 MHz
D8	I _{CCWRITE}	Operating Current	—	—	3	mA	V _{CC} =5.5V,SCL=400 kHz
D9	I _{CCREAD}		—	—	1	mA	V _{CC} =5.5V,SCL=400 kHz
D10	I _{CCS}	Standby Current	—	—	1	μA	SDA=SCL=V _{CC} WP=V _{SS} ,I-Temp.
			—	—	5	μA	SDA=SCL=V _{CC} WP=V _{SS} ,E-Temp.(24LC08B)

Note: This parameter is periodically sampled and not 100% tested.



TABLE 2. AC CHARACTERISTICS

AC CHARACTERISTICS			Industrial(1):TA=-40°C to +85°C,Vcc=+1.7V to +5.5V Extended (E):TA=-40°C to+125°C,Vcc=+2.5V to+5.5V			
Param. No.	Symbol	Characteristic	Min.	Max.	Units	Conditions
1	F _{CLK}	Clock Frequency	—	400	kHz	2.5V≤Vcc≤5.5V
			—	100	kHz	1.7V≤Vcc<2.5V(24AA08)
2	T _{HIGH}	Clock High Time	600	—	ns	2.5V≤Vcc≤5.5V
			4000	—	ns	1.7V≤Vcc<2.5V(24AA08)
3	T _{LOW}	Clock Low Time	1300	—	ns	2.5V≤Vcc≤5.5V
			4700	—	ns	1.7V≤Vcc<2.5V(24AA08)
4	T _R	SDA and SCL Rise Time	—	300	ns	2.5V≤Vcc≤5.5V(Note 1)
			—	1000	ns	1.7V≤Vcc<2.5V(24AA08)(Note 1)
5	T _F	SDA and SCL Fall Time	—	300	ns	Note 1
6	T _{HD:STA}	Start Condition HoldTime	600	—	ns	2.5V≤Vcc≤5.5V
			4000	—	ns	1.7V≤Vcc<2.5V(24AA08)
7	T _{SU:STA}	Start ConditionSetup Time	600	—	ns	2.5V≤Vcc≤5.5V
			4700	—	ns	1.7V≤Vcc<2.5V(24AA08)
8	T _{HD:DAT}	Data Input Hold Time	0	—	ns	Note 2
9	T _{SU:DAT}	Data Input Setup Time	100	—	ns	2.5V≤Vcc≤5.5V
			250	—	ns	1.7V≤Vcc<2.5V(24AA08)
10	T _{SU:STO}	Stop ConditionSetupTime	600	—	ns	2.5V≤Vcc≤5.5V
			4000	—	ns	1.7V≤Vcc<2.5V(24AA08)
11	T _{AA}	Output Valid from Clock	—	900	ns	2.5V≤Vcc≤5.5V(Note 2)
			—	3500	ns	1.7V≤Vcc<2.5V(24AA08)(Note 2)
12	T _{BUF}	Bus Free Time:The timethe bus must befree before a newtransmis-sion can start	1300	—	ns	2.5V≤Vcc≤5.5V
			4700	—	ns	1.7V≤Vcc<2.5V(24AA08)



TABLE 2.AC CHARACTERISTICS(CONTINUED)

AC CHARACTERISTICS			Industrial(1):TA=-40°C to +85°C,Vcc=+1.7V to +5.5V Extended (E):TA=-40°C to+125°C,Vcc=+2.5V to+5.5V			
Param. No.	Symbol	Characteristic	Min.	Max.	Units	Conditions
13	T _{OF}	Output Fall Time from V _{IH} Minimum to V _{IL} Maximum	—	250	ns	2.5V≤Vcc≤5.5V(Notes 1,3 and 4)
			—	250	ns	1.7V≤Vcc<2.5V(24AA08)(Notes 1,3 and 4)
14	T _{SP}	Input Filter Spike Suppression(SDA and SCL pins)	—	50	ns	Note 1
15	T _{WC}	Write Cycle Time (byte or page)	—	5	ms	
16		Endurance	1,000,000	—	cycles	25°C,5.5V,Page Mode(Note 4)

Note 1: Characterized but not 100% tested.

2: As a transmitter, the device must provide an internal minimum delay time to bridge the undefined region (minimum 300 ns) of the falling edge of SCL to avoid unintended generation of Start or Stop conditions.

3: C_B = total capacitance of one bus line in pF.

4: This parameter is not tested but ensured by characterization.




FIGURE 1: BUS TIMING DATA




FIGURE 2: BUS TIMING START/STOP



PIN DESCRIPTIONS

The descriptions of the pins are listed in Table 3.

TABLE 3: PIN FUNCTION TABLE

Name	PDIP	SOIC	TSSOP	SOT-23	Description
A0	1	1	1	—	Not Connected
A1	2	2	2	—	Not Connected
A2	3	3	3	—	Not Connected
Vss	4	4	4	2	Ground
SDA	5	5	5	3	Serial Address/Data I/O
SCL	6	6	6	1	Serial Clock
WP	7	7	7	5	Write-Protect Input
Vcc	8	8	8	4	Power Supply

A0, A1, A2:The A0, A1 and A2 pins are not used by the 24XX08. They may be left floating or tied to either V_{ss} or V_{cc}.

Serial Address/Data Input/Output (SDA) :The SDA input is a bidirectional pin used to transfer addresses and data into and out of the device. Since it is an open-drain terminal, the SDA bus requires a pull-up resistor to V_{CC} (typical 10 k Ω for 100 kHz, 2 k Ω for 400 kHz and 1 MHz). For normal data transfer, SDA is allowed to change only during SCL low. Changes during SCL high are reserved for indicating Start and Stop conditions.

Serial Clock (SCL) :The SCL input is used to synchronize the data transfer to and from the device.

Write-Protect (WP):This pin must be connected to either V_{ss} or V_{cc}.
If tied to V_{ss}, normal memory operation is enabled (read/write the entire memory 000-3FF).
If tied to V_{cc}, write operations are inhibited. The entire memory will be write-protected. Read operations are not affected.
The Chip Scale package does not support the write-protect feature.



FUNCTIONAL DESCRIPTION

The 24XX08 supports a bidirectional, two-wire bus and data transmission protocol. A device that sends data onto the bus is defined as transmitter, while defining a device receiving data as a receiver. The bus has to be controlled by a master device which generates the Serial Clock (SCL), controls the bus access and generates the Start and Stop conditions, while the 24XX08 works as slave. Both master and slave can operate as transmitter or receiver, but the master device determines which mode is activated.

BUS CHARACTERISTICS

The following bus protocol has been defined:

- Data transfer may be initiated only when the bus is not busy.
- During data transfer, the data line must remain stable whenever the clock line is high. Changes in the data line while the clock line is high will be interpreted as a Start or Stop condition. Accordingly, the following bus conditions have been defined (Figure 3).

Bus Not Busy (A): Both data and clock lines remain high.

Start Data Transfer (B): A high-to-low transition of the SDA line while the clock (SCL) is high determines a Start condition. All commands must be preceded by a Start condition.

Stop Data Transfer (C) : A low-to-high transition of the SDA line while the clock (SCL) is high determines a Stop condition. All operations must be ended with a Stop condition.

Data Valid (D) : The state of the data line represents valid data when, after a Start condition, the data line is stable for the duration of the high period of the clock signal.

The data on the line must be changed during the low period of the clock signal. There is one clock pulse per bit of data.

Each data transfer is initiated with a Start condition and terminated with a Stop condition. The number of data bytes transferred between the Start and Stop conditions is determined by the master device and is, theoretically, unlimited (although only the last sixteen will be stored when doing a write operation). When an overwrite does occur, it will replace data based on the first-in first-out (FIFO) principle.



Acknowledge: Each receiving device, when addressed, is obliged to generate an Acknowledge after the reception of each byte. The master device must generate an extra clock pulse which is associated with this Acknowledge bit.

The device that acknowledges has to pull down the SDA line during the Acknowledge clock pulse in such a way that the SDA line is stable-low during the high period of the Acknowledge-related clock pulse. Moreover, setup and hold times must be taken into account. During reads, a master must signal an end of data to the slave by not generating an Acknowledge bit on the last byte that has been clocked out of the slave. In this case, the slave (24XX08) will leave the data line high to enable the master to generate the Stop condition.

Note: The 24XX08 does not generate any Acknowledge bits if an internal programming cycle is in progress.




FIGURE 3: DATA TRANSFER SEQUENCE ON THE SERIAL BUS



DEVICE ADDRESSING

A control byte is the first byte received following the Start condition from the master device. The control byte consists of a four-bit control code. For the 24XX08, this is set as ‘ 1010 ’ binary for read and write operations. The next bit of the control byte is a “ don ’ t care ” for the 24XX08. The last two bits, B1 and B0, are used by the master device to select which of the four 256-word blocks of memory are to be accessed. These bits, in effect, are the Most Significant bits of the word address. The combination of the 4-bit control code and the next three bits are called the slave address.

The last bit of the control byte is the Read/Write (R/W) bit and it defines the operation to be performed. When set to ‘ 1 ’, a read operation is selected. When set to ‘ 0 ’, a write operation is selected. Following the Start condition, the 24XX08 monitors the SDA bus, checking the device type identifier being transmitted. Upon receiving a valid slave address and the R/W bit, the slave device outputs an Acknowledge signal on the SDA line. Depending on the state of the R/W bit, the 24XX08 will select a read or write operation.

The next byte received defines the address of the first data byte within the selected block (Figure 4). The word address byte uses all eight bits.

Operation	ControlCode	Block Select	R/W
Read	1010	Block Address	1
Write	1010	Block Address	0




FIGURE 4: CONTROL BYTE ALLOCATION




FIGURE 5: ADDRESS SEQUENCE BIT ASSIGNMENTS



WRITE OPERATION

Byte Write : Following the Start condition from the master, the device code (4 bits), the block address (1 bit is a “ don't care ”, plus B1 and B0 bits) and the R/W bit, which is a logic-low, is placed onto the bus by the master transmitter. This indicates to the addressed slave receiver that a byte with a word address will follow after it has generated an Acknowledge bit during the ninth clock cycle. Therefore, the next byte transmitted by the master is the word address and will be written into the Address Pointer of the 24XX08. After receiving another Acknowledge signal from the 24XX08, the master device will transmit the data word to be written into the addressed memory location. The 24XX08 acknowledges again and the master generates a Stop condition. This initiates the internal write cycle, and, during this time, the 24XX08 will not generate Acknowledge signals (Figure 6).

Page Write : The write control byte, word address and first data byte are transmitted to the 24XX08 in the same way as in a byte write. However, instead of generating a Stop condition, the master transmits up to 16 data bytes to the 24XX08, which are temporarily stored in the on-chip page buffer and will be written into the memory once the master has transmitted a Stop condition. Upon receipt of each word, the four lower-order Address Pointer bits, which form the byte counter, are internally incremented by one. The higher-order four bits of the word address and bits B1 and B0 remain constant. If the master should transmit more than 16 words prior to generating the Stop condition, the Address Pointer will roll over and the previously received data will be overwritten. As with the byte write operation, once the Stop condition is received, an internal write cycle will begin (Figure 7).

Note: Page write operations are limited to writing bytes within a single physical page regardless of the number of bytes actually being written. Physical page boundaries start at addresses that are integer multiples of the page buffer size (or ‘ page size ’) and end at addresses that are integer multiples of page size – 1. If a page write command attempts to write across a physical page boundary, the result is that the data wraps around to the beginning of the current page (overwriting data previously stored there), instead of being written to the next page, as might be expected. It is therefore necessary for the application software to prevent page write operations that would attempt to cross a page boundary.

Write Protection : The WP pin allows the user to write-protect the entire array (000-3FF) when the pin is tied to V_{CC}. If tied to V_{SS}, the write protection is disabled. The Chip Scale package does not support the write-protect feature.




FIGURE 6: BYTE WRITE




FIGURE 7: PAGE WRITE

ACKNOWLEDGE POLLING

Since the device will not acknowledge during a write cycle, this can be used to determine when the cycle is complete (this feature can be used to maximize bus throughput). Once the Stop condition for a write command has been issued from the master, the device initiates the internally-timed write cycle. ACK polling can then be initiated immediately. This involves the master sending a Start condition followed by the control byte for a write command ($R/W = 0$). If the device is still busy with the write cycle, no ACK will be returned. If the cycle is complete, the device will return the ACK and the master can then proceed with the next read or write operation. See Figure 7-1 for a flow diagram of this operation.




FIGURE 8.ACKNOWLEDGE POLLING FLOW

Sequential Read: Sequential reads are initiated in the same way as a random read or current read, except that once the 24XX08 transmits the first data byte, the master issues an Acknowledge (as opposed to a Stop condition in a random read). This directs the 24XX08 to transmit the next sequentially addressed 8-bit word (Figure 11). To provide sequential reads the 24XX08 contains an internal Address Pointer which is incremented by one at the completion of each operation. This Address Pointer allows the entire memory contents to be serially read during one operation.

Current Address Read : The 24XX08 contains an Address Pointer that maintains the address of the last word accessed, internally incremented by one. Therefore, if the previous access (either a read or write operation) was to address n , the next current address read operation would access data from address $n + 1$. Upon receipt of the slave address with R/W bit set to '1', the 24XX08 issues an Acknowledge and transmits the 8-bit data word. The master will not acknowledge the transfer, but does generate a Stop condition and the 24XX08 discontinues transmission (Figure 9).

Noise Protection : The SCL and SDA inputs have Schmitt Trigger and filter circuits which suppress noise spikes to assure proper device operation even on a noisy bus.



Random Read : Random read operations allow the master to access any memory location in a random manner. To perform this type of read operation, the word address must first be set. This is accomplished by sending the word address to the 24XX08 as part of a write operation. Once the word address is sent, the master generates a Start condition following the Acknowledge. This terminates the write operation, but not before the internal Address Pointer is set. The master then issues the control byte again, but with the R/W bit set to a ' 1 '. The 24XX08 will then issue an Acknowledge and transmits the 8-bit data word. The master will not acknowledge the transfer, but does generate a Stop condition and the 24XX08 discontinues transmission (Figure 10).

READ OPERATION : Read operations are initiated in the same way as write operations, with the exception that the R/W bit of the slave address is set to ' 1 '. There are three basic types of read operations: current address read, random read and sequential read.




FIGURE 9: CURRENT ADDRESS READ




FIGURE 10: RANDOM READ




FIGURE 11: SEQUENTIAL READ



Order information



Order Number	Package	Package Quantity	Marking On The park	Temperature
24AA08-I/P-TUDI	DIP8	Tube,50,A box of 2000	24AA08-I/P	-40°C to +85°C
24AA08T-I/SN-TUDI	SOP8	Tape,Reel,4000	24AA08I/SN	
24AA08T-I/ST-TUDI	TSSOP8	Tape,Reel,4000	24AA08	
24AA08T-I/OT-TUDI	SOT23-5	Tape,Reel,3000	B4xx	
24LC08B-I/P-TUDI	DIP8	Tube,50,A box of 2000	24LC08B-I/P	
24LC08BT-I/SN-TUDI	SOP8	Tape,Reel,4000	24LC08BI/SN	
24LC08BT-I/ST-TUDI	TSSOP8	Tape,Reel,4000	24LC08B	
			4L08	
24LC08BT-I/OT-TUDI	SOT23-5	Tape,Reel,3000	M4xx	
24LC08BT-E/OT-TUDI	SOT23-5	Tape,Reel,3000	N4xx	-40°C to +125°C
24LC08BT-E/SN-TUDI	SOP8	Tape,Reel,4000	24LC08BE/SN	
24LC08BT-E/ST-TUDI	TSSOP8	Tape,Reel,4000	4L08	

Revision history


	Date	Revision	Page
V1.0	2021/3	New	1-17
V1.1	2025/7	Update model and PDF template	1-23






Package SOP8



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.350	1.750	0.053	0.069
A1	0.100	0.250	0.004	0.010
A2	1.350	1.550	0.053	0.061
B	0.330	0.510	0.013	0.020
C	0.190	0.250	0.007	0.010
D	4.780	5.000	0.188	0.197
E	3.800	4.000	0.150	0.157
E1	5.800	6.300	0.228	0.248
e	1.270TYP		0.050TYP	
L	0.400	1.270	0.016	0.050
θ	0°	8°	0°	8°






Package DIP8






Symbol	Min	Non	Max
A1	6.28	6.33	6.38
A2	6.33	6.38	6.43
A3	7.52	7.62	7.72
A4	7.80	8.40	9.00
B1	9.15	9.20	9.25
B2	9.20	9.25	9.30
C		5.57	
D		1.52	
E	0.43	0.45	0.47
F		2.54	
G		0.25	
H	1.54	1.59	1.64
I	3.22	3.27	3.32
R		0.20	
M1	9°	10°	11°
M2	11°	12°	13°

Package TSSOP8



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
D	2.900	3.100	0.114	0.122
E	4.300	4.500	0.169	0.177
b	0.190	0.300	0.007	0.012
C	0.090	0.200	0.004	0.008
E1	6.250	6.550	0.246	0.258
A		1.200		0.047
A2	0.800	1.000	0.031	0.039
A1	0.050	0.150	0.002	0.006
e	0.65(BSC)		0.026(BSC)	
L	0.500	0.700	0.020	0.028
H	0.25(TYP)		0.01(TYP)	
θ	1°		1°	

Package SOT23-5



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	MIN	MAX	MIN	MAX
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.400	0.012	0.016
C	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
e	0.950TYP		0.037TYP	
e1	1.800	2.000	0.071	0.079
L	0.700REF		0.028REF	
L1	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°



Important statement:

- TUDI Semiconductor reserves the right to modify the product manual without prior notice! Before placing an order, customers need to confirm whether the obtained information is the latest version and verify the completeness of the relevant information.
- Any semi-guide product is subject to failure or malfunction under specified conditions. It is the buyer's responsibility to comply with safety standards when using TUDI Semiconductor products for system design and whole machine manufacturing. And take the appropriate safety measures to avoid the potential in the risk of loss of personal injury or loss of property situation!
- TUDI Semiconductor products have not been licensed for life support, military, and aerospace applications, and therefore TUDI Semiconductor is not responsible for any consequences arising from the use of this product in these areas.
- If any or all TUDI Semiconductor products (including technical data, services) described or contained in this document are subject to any applicable local export control laws and regulations, they may not be exported without an export license from the relevant authorities in accordance with such laws.
- The specifications of any and all TUDI Semiconductor products described or contained in this document specify the performance, characteristics, and functionality of said products in their standalone state, but do not guarantee the performance, characteristics, and functionality of said products installed in Customer's products or equipment. In order to verify symptoms and conditions that cannot be evaluated in a standalone device, the Customer should ultimately evaluate and test the device installed in the Customer's product device.
- TUDI Semiconductor documentation is only allowed to be copied without any alteration of the content and with the relevant authorization. TUDI Semiconductor assumes no responsibility or liability for altered documents.
- TUDI Semiconductor is committed to becoming the preferred semiconductor brand for customers, and TUDI Semiconductor will strive to provide customers with better performance and better quality products.