

MOV metal oxide varistors

Leaded varistors, Standard, 20 series

Series/Type: VCRR20D***K****

Ordering code: VCRR20D***K

Date: January 2020

Version: 1

MOV metal oxide varistors

20D***k****

Leaded varistors, Standard, 20 series

VCRR20D***K****

Construction

- Round varistor element, leaded
- Coating: epoxy resin, flame-retardant to UL 94 V-0
- Terminals: tinned wire

Features

- High performance with smaller disk diameter
- Wide operating voltage range 10 ... 680V_{RMS}
- High surge current ratings up to 6500 A
- No derating up to 130°C ambient temperature

Approvals

- UL Certificate:E531647
- TUV Certificate:B1199670002
- CQC Certificate :CQC23001396762

Delivery mode

- Bulk (standard), taped versions on reel or in Ammo pack upon request
- For further details refer to chapter "Taping, packaging and lead configuration" for leaded varistors.

General technical data

Climatic category	to IEC 60068-1	40/130/56	
Operating temperature	to IEC 61051	-40 ... +130	°C
Storage temperature		-40 ... +125	°C
Electric strength	to IEC 61051	≥ 2.5	kV _{RMS}
Insulation resistance	to IEC 61051	≥ 100	MΩ

MOV metal oxide varistors
20D*k******
Leaded varistors, Standard, 20 series
VCRR20D*K******
Electrical specifications and ordering codes

Maximum ratings ($T_A = 130\text{ }^{\circ}\text{C}$)

Ordering code	Type	V_{RMS} [V]	V_{DC} [V]	i_{max} (8/20 μ s) 1 time [A]*	$I_n^{(1)}$ (8/20 μ s) 15 times [A]*	W_{max} (10/1000u s) [J]	P_{max} [W]
VCRR20D180K0101	20D180L	10	14	2000	1000	6.1	0.2
VCRR20D220K0101	20D220K	14	18	2000	1000	7.4	0.2
VCRR20D270K0101	20D270K	17	22	2000	1000	9.1	0.2
VCRR20D330K0101	20D330K	20	26	2000	1000	11.2	0.2
VCRR20D390K0101	20D390K	25	31	2000	1000	13.2	0.2
VCRR20D470K0101	20D470K	30	38	2000	1000	16.8	0.2
VCRR20D560K0101	20D560K	35	45	2000	1000	19.6	0.2
VCRR20D680K0101	20D680K	40	56	2000	1000	23.8	0.2
VCRR20D820K0101	20D820K	50	65	6500	3500	37.8	0.2
VCRR20D101K0101	20D101K	60	85	6500	3500	42	0.2
VCRR20D121K0101	20D121K	75	100	6500	3500	56	0.2
VCRR20D151K0101	20D151K	95	125	6500	3500	70	0.2
VCRR20D181K0101	20D181K	115	150	6500	3500	84	1.0
VCRR20D201K0101	20D201K	130	170	6500	3500	98	1.0
VCRR20D221K0101	20D221K	140	180	6500	3500	105	1.0
VCRR20D241K0101	20D241K	150	200	6500	3500	112	1.0
VCRR20D271K0101	20D271K	175	225	6500	3500	126	1.0
VCRR20D301K0101	20D301K	190	250	6500	3500	133	1.0
VCRR20D331K0101	20D331K	210	270	6500	3500	140	1.0
VCRR20D361K0101	20D361K	230	300	6500	3500	168	1.0
VCRR20D391K0101	20D391K	250	320	6500	3500	182	1.0
VCRR20D431K0101	20D431K	275	350	6500	3500	196	1.0
VCRR20D471K0101	20D471K	300	385	6500	3500	202	1.0
VCRR20D511K0101	20D511K	320	420	6500	3500	207	1.0
VCRR20D561K0101	20D561K	350	460	6500	3500	210	1.0
VCRR20D621K0101	20D621K	385	505	6500	3500	224	1.0
VCRR20D681K0101	20D681K	420	560	6500	3500	224	1.0
VCRR20D751K0101	20D751K	460	615	6500	3500	230	1.0
VCRR20D821K0101	20D821K	510	670	6500	3500	240	1.0
VCRR20D911K0101	20D911K	550	745	6500	3500	250	1.0
VCRR20D951K0101	20D951K	575	765	6500	3500	260	1.0
VCRR20D102K0101	20D102K	625	825	6500	3500	270	1.0
VCRR20D112K0101	20D112K	680	895	6500	3500	280	1.0


¹⁾ **Note:** Nominal discharge current is the specification defined in UL1449 4th edition and tested with 8/20 μ s current waveform

MOV metal oxide varistors
20D*k******
Leaded varistors, Standard, 20 series
VCRR20D*K******
Characteristics (T_A=25 °C):

Ordering code	Type	V _v (1 mA) [V]	ΔV _v (1 mA) [%]	Max clamping voltage		C _{typ} (1 kHz) [pF]
				V _c [V]	I _c [A]	
VCRR20D180K0101	20D180L	18	5	38	20	11100
VCRR20D220K0101	20D220K	22	±10	43	20	9100
VCRR20D270K0101	20D270K	27	±10	53	20	7400
VCRR20D330K0101	20D330K	33	±10	65	20	6100
VCRR20D390K0101	20D390K	390	±10	77	20	5100
VCRR20D470K0101	20D470K	47	±10	93	20	4300
VCRR20D560K0101	20D560K	56	±10	110	20	3600
VCRR20D680K0101	20D680K	68	±10	135	20	2900
VCRR20D820K0101	20D820K	82	±10	135	100	2400
VCRR20D101K0101	20D101K	100	±10	165	100	2000
VCRR20D121K0101	20D121K	120	±10	200	100	1700
VCRR20D151K0101	20D151K	150	±10	250	100	1300
VCRR20D181K0101	20D181K	180	±10	300	100	1100
VCRR20D201K0101	20D201K	200	±10	340	100	900
VCRR20D221K0101	20D221K	220	±10	360	100	830
VCRR20D241K0101	20D241K	240	±10	395	100	740
VCRR20D271K0101	20D271K	270	±10	455	100	670
VCRR20D301K0101	20D301K	300	±10	500	100	610
VCRR20D331K0101	20D331K	330	±10	550	100	560
VCRR20D361K0101	20D361K	360	±10	595	100	510
VCRR20D391K0101	20D391K	390	±10	650	100	460
VCRR20D431K0101	20D431K	430	±10	710	100	430
VCRR20D471K0101	20D471K	470	±10	775	100	390
VCRR20D511K0101	20D511K	510	±10	840	100	360
VCRR20D561K0101	20D561K	560	±10	910	100	320
VCRR20D621K0101	20D621K	620	±10	1025	100	290
VCRR20D681K0101	20D681K	680	±10	1120	100	270
VCRR20D751K0101	20D751K	750	±10	1240	100	260
VCRR20D821K0101	20D821K	820	±10	1355	100	230
VCRR20D911K0101	20D911K	910	±10	1500	100	220
VCRR20D951K0101	20D951K	950	±10	1570	100	200
VCRR20D102K0101	20D102K	1000	±10	1650	100	180
VCRR20D112K0101	20D112K	1100	±10	1815	100	130

2) *Please refer to the suffix code

Dimensional drawings



Weight

Nominal diameter mm	V _{RMS} V	Weight g
20	10...680	2.7...15.7

Different voltage levels result in differences in weight.

Dimensions

Ordering code ²⁾	[e] ±1 mm	W _{max} mm	h _{max} mm	th _{max} mm	a _{typ} mm	l _{min} mm	Ød±0.05 mm
VCRR20D180K0101	10	22	25.5	3.6	1.7	25.0	1.0
VCRR20D220K0101	10	22	25.5	3.6	1.7	25.0	1.0
VCRR20D270K0101	10	22	25.5	3.6	1.7	25.0	1.0
VCRR20D330K0101	10	22	25.5	3.6	1.7	25.0	1.0
VCRR20D390K0101	10	22	25.5	3.6	1.7	25.0	1.0
VCRR20D470K0101	10	22	25.5	3.6	1.7	25.0	1.0
VCRR20D560K0101	10	22	25.5	3.6	1.7	25.0	1.0
VCRR20D680K0101	10	22	25.5	3.6	1.7	25.0	1.0
VCRR20D820K0101	10	22	25.5	3.6	1.7	25.0	1.0
VCRR20D101K0101	10	22	25.5	3.6	1.7	25.0	1.0
VCRR20D121K0101	10	22	25.5	3.6	1.7	25.0	1.0
VCRR20D151K0101	10	22	25.5	3.6	1.7	25.0	1.0
VCRR20D181K0101	10	22	25.5	3.6	1.7	25.0	1.0
VCRR20D201K0101	10	22	25.5	4.2	1.8	25.0	1.0
VCRR20D221K0101	10	22	25.5	4.3	1.9	25.0	1.0
VCRR20D241K0101	10	22	25.5	4.4	2.0	25.0	1.0
VCRR20D271K0101	10	22	25.5	4.6	2.1	25.0	1.0
VCRR20D301K0101	10	22	22	4.7	1.7	25.0	1.0
VCRR20D331K0101	10	22	22	4.8	1.7	25.0	1.0
VCRR20D361K0101	10	22	22	5.0	1.8	25.0	1.0
VCRR20D391K0101	10	22	22	5.1	1.9	25.0	1.0
VCRR20D431K0101	10	22	22	5.4	1.9	25.0	1.0
VCRR20D471K0101	10	22	22	5.6	1.9	25.0	1.0
VCRR20D511K0101	10	22	22	5.8	2.1	25.0	1.0
VCRR20D561K0101	10	22	22	6.1	2.2	25.0	1.0

MOV metal oxide varistors						20D***k****	
Leaded varistors, Standard, 20 series						VCRR20D***K****	
Ordering code ²⁾	[e] ±1 mm	W _{max} mm	h _{max} mm	th _{max} mm	a _{typ} mm	l _{min} mm	Ød±0.05 mm
VCRR20D621K0101	10	22	22	6.2	2.4	25.0	1.0
VCRR20D681K0101	10	22	22	6.3	2.6	25.0	1.0
VCRR20D751K0101	10	22	22	6.7	2.7	25.0	1.0
VCRR20D821K0101	10	22	22	7.1	3.1	25.0	1.0
VCRR20D911K0101	10	22	22	7.5	3.4	25.0	1.0
VCRR20D951K0101	10	22	22	7.9	3.7	25.0	1.0
VCRR20D102K0101	10	22	22	7.9	4.0	25.0	1.0
VCRR20D112K0101	10	22	22	8.0	4.4	25.0	1.0

2) *Please refer to the suffix code.

Reliability data

Test	Test methods/conditions	Requirement
Varistor voltage	The voltage between two terminals with the specified measuring current applied is called V_V (1 mA _{DC} @ 0.2 ... 2 s).	To meet the specified value
Clamping voltage	The maximum voltage between two terminals with the specified standard impulse current (8/20 µs) applied.	To meet the specified value
Endurance at upper category temperature	1000 h at UCT After having continuously applied the maximum allowable AC voltage at UCT ±2 °C for 1000 h, the specimen shall be stored at room temperature and normal humidity for 1 to 2 h. Thereafter, the change of V_V shall be measured.	$ \Delta V/V (1 \text{ mA}) \leq 10\%$
Surge current derating, 8/20 µs	10 surge currents (8/20 µs), unipolar, interval 30 s, amplitude corresponding to derating curve for 10 impulses at 20 µs	$ \Delta V/V (1 \text{ mA}) \leq 10\%$ (measured in direction of surge current) No visible damage
Surge current derating, 2 ms	10 surge currents (2 ms), unipolar, interval 120 s, amplitude corresponding to derating curve for 10 impulses at 2 ms	$ \Delta V/V (1 \text{ mA}) \leq 10\%$ (measured in direction of surge current) No visible damage
Electric strength	IEC 61051-1, test 4.9.2 Metal balls method, 2500 VRMS, 60 s The varistor is placed in a container holding 1.6 ±0.2 mm diameter metal balls such that only the terminations of the varistor are protruding. The specified voltage shall be applied between both terminals of the specimen connected together and the electrode inserted between the metal balls.	No breakdown

MOV metal oxide varistors
20D*k******
Leaded varistors, Standard, 20 series
VCRR20D*K******

Test	Test methods/conditions	Requirement
Climatic sequence	The specimen shall be subjected to: a) dry heat at UCT, 16 h, IEC 60068-2-2, test Ba b) damp heat, 1st cycle: 55 °C, 93% r. H., 24 h, IEC 60068-2-30, test Db c) cold, LCT, 2 h, IEC 60068-2-1, test Aa d) damp heat, additional 5 cycles: 55 °C/25 °C, 93% r. H., 24 h/cycle, IEC 60068-2-30, test Db. Then the specimen shall be stored at room temperature and normal humidity for 1 to 2 h. Thereafter, the change of V_V shall be measured. Thereafter, insulation resistance R_{ins} shall be measured at $V = 500$ V.	$ \Delta V/V (1 \text{ mA}) \leq 10\%$ $R_{ins} \geq 100 \text{ M}\Omega$
Rapid change of temperature	IEC 60068-2-14, test Na, LCT/UCT, dwell time 30 min, 5 cycles	$ \Delta V/V (1 \text{ mA}) \leq 5\%$ No visible damage
Damp heat, steady state	IEC 60068-2-78, test Ca The specimen shall be subjected to 40 ± 2 °C, 90 to 95% r. H. for 56 days without load / with 10% of the maximum continuous DC operating voltage VDC. Then stored at room temperature and normal humidity for 1 to 2 h. Thereafter, the change of V_V shall be measured. Thereafter, insulation resistance R_{ins} shall be measured at $V = 500$ V (insulated varistors only).	$ \Delta V/V (1 \text{ mA}) \leq 10\%$ $R_{ins} \geq 100 \text{ M}\Omega$

MOV metal oxide varistors

20D***k****

Leaded varistors, Standard, 20 series

VCRR20D***K****

Test	Test methods/conditions	Requirement
Solderability	IEC 60068-2-20, test Ta, method 1 with modified conditions for lead-free solder alloys: 245 °C, 3 s: After dipping the terminals to a depth of approximately 3 mm from the body in a soldering bath of 245 °C for 3 s, the terminals shall be visually examined.	The inspection shall be carried out under adequate light with normal eyesight or with the assistance of a magnifier capable of giving a magnification of 4 to 10 times. The dipped surface shall be covered with a smooth and bright solder coating with no more than small amounts of scattered imperfections such as pinholes or un-wetted or de-wetted areas. These imperfections shall not be concentrated in one area.
Resistance to soldering heat	IEC 60068-2-20, test Tb, method 1A, 260 °C, 10 s: Each lead shall be dipped into a solder bath having a temperature of 260 ±5 °C to a point 2.0 to 2.5 mm from the body of the specimen, be held there for 10 ±1 s and then be stored at room temperature and normal humidity for 1 to 2 h. The change of VV shall be measured and the specimen shall be visually examined.	$ \Delta V/V (1 \text{ mA}) \leq 5\%$ No visible damage
Tensile strength	IEC 60068-2-21, test Ua1 After gradually applying the force specified below and keeping the unit fixed for 10 s, the terminal shall be visually examined for any damage. Force for wire diameter: 0.6 mm = 10 N 0.8 mm = 10 N 1.0 mm = 20 N	$ \Delta V/V (1 \text{ mA}) \leq 5\%$ No break of solder joint, no wire break

MOV metal oxide varistors
20D*k******
Leaded varistors, Standard, 20 series
VCRR20D*K******

Test	Test methods/conditions	Requirement
Vibration	IEC 60068-2-6, test Fc, method B4 Frequency range: 10 ... 55 Hz Amplitude: 0.75 mm or 98 m/s ² Duration: 6 h (3 · 2 h) Pulse: sine wave After repeatedly applying a single harmonic vibration according to the table above. The change of V _V shall be measured and the specimen shall be visually examined.	ΔV/V (1 mA) ≤5% No visible damage
Bump	IEC 60068-2-29, test Eb Pulse duration: 6 ms Max. acceleration: 400 m/s ² Number of bumps: 4000 Pulse: half sine	ΔV/V (1 mA) ≤5% No visible damage
Fire hazard	IEC 60695-11-5 (needle flame test) Severity: vertical 10 s	5 s max.

Note:

UCT = Upper category temperature


LCT = Lower category temperature

R_{ins} = Insulation resistance

v/i characteristics

$v = f(i)$ - for explanation of the characteristics refer to "General technical information",


A = Leakage current, B = Protection level } for worst-case varistor tolerances



Derating curves

Maximum surge current $i_{\max} = f(t_r, \text{pulse train})$


For explanation of the derating curves refer to "General technical information".



VCRR20D180---VCRR20D112K

Taping, packaging and lead configuration


1 JORDUN Electronics ordering code system for leaded varistors



2 Taping and packaging of leaded varistors

Tape packaging for lead spacing $\boxed{e}$ = 5 fully conforms to IEC 60286-2, while for lead spacings $\boxed{e}$ = 7.5 and 10 the taping mode is based on this standard.


2.1 Taping in accordance with IEC 60286-2 for lead spacing 5.0 mm



$F \triangleq \boxed{e} = 5.0 \text{ mm}$

VAR0410-X-E

2.2 Taping based on IEC 60286-2 for lead spacing 7.5 and 10 mm



$F \triangleq \boxed{e} = 7.5 \text{ mm}$

$F \triangleq \boxed{e} = 10 \text{ mm}$

VAR0395-J-E

MOV metal oxide varistors
20D*K******
Leaded varistors, Standard, 20series
VCRR20K*K******
2.3 Tape dimensions (in mm)


Symbol	$e = 5.0$	Tolerance	$e = 7.5$	Tolerance	$e = 10.0$	Tolerance	Remarks
w th d	0.6	max. max. ± 0.05	0.8	max. max. ± 0.05	1.0	max. max. ± 0.05	see tables in each series under "Dimensions "
P ₀	12.7	± 0.3	12.7 ¹⁾	± 0.3	12.7	± 0.3	± 1 mm/20 sprocket holes
P ₁	3.85	± 0.7	8.95	± 0.8	7.7	± 0.8	
F	5.0	± 10	7.5	± 0.8	10.0	± 0.8	measured at top of compo- nent body
Δh	0	± 2.0	depends on s		depends on s		
Δp	0	± 1.3	0	± 2.0	0	± 2.0	
W	18.0	± 0.5	18.0	± 0.5	18.0	± 0.5	Peel-off force ≥ 5 N
W ₀	5.5	min.	11.0	min.	11.0	min.	
W ₁	9.0	± 0.5	9.0	$+0.75/-0.5$	9.0	$+0.75/-0.5$	
W ₂	3.0	max.	3.0	max.	3.0	max.	
H	18.0	$+2.0/-0$	18.0	$+2.0/-0$	18.0	$+2.0/-0$	²⁾ ³⁾
H ₀	16.0	± 0.5	16.0	± 0.5	16.0	± 0.5	
	(18.0)		(18.0)				
H ₁	32.2	max.	45.0	max.	45.0	max.	
D ₀	4.0	± 0.2	4.0	± 0.2	4.0	± 0.2	without lead
t	0.9	max.	0.9	max.	0.9	max.	
L	11.0	max.	11.0	max.	11.0	max.	
L ₁	0.5	max.					

1) Taping with P₀ = 15.0 mm upon request

2) Applies only to uncrimped types

3) Applies only to crimped types (H₀ = 18 upon request)

2.4 Ammo pack dimensions



2.5 Quantities Per Packaging

Part No	Voltage	Bulk		Ammo Packing(Taping)	
		Bag	Carton	Box	Carton
7D	181-821	1000	20000	1000	10000
10D	180-182	1000	10000	1000	10000
14D	180-182	500	8000	800	8000
20D	180-182	250	5000	----	----
25D	180-182	200	3000	----	----

3 Lead configuration

Straight leads are standard for disk varistors. Other lead configurations as crimp style or customerspecific lead wire length according to 3.1, 3.2, 3.3 and 3.4 are optional. Crimped leads (non-standard) are differently crimped for technical reasons; the individual crimp styles are denot-ed by consecutive numbers (S, S2 through S5) as shown in the dimensional drawings below.

The crimp styles of the individual types can be seen from the type designation in the ordering tables.

3.1 Standard leads and non-standard crimp styles

The basic dimensions in figure 1 to 5 are valid for types with either round or square (EnergetiQ series) component head

**Standard,
straight leads**




Figure 1

**Non-standard,
crimp style S2**




Figure 2

**Non-standard,
crimp style S3**





Figure 3

**Non-standard,
crimp style S5**



Figure

3.2 Trimmed leads (non-standard)


Varistors with cut leads available upon request.

Lead length tolerances:

Straight leads ± 0.8 mm

Crimped leads ± 0.5 mm

Minimum lead length 3.0 mm



1) Seating plane to IEC 60717

*) For round component head

**) For EnergetiQ series, square component head

VAR0642-U-E

Cautions and warnings

General

1. JORDUN Electronics metal oxide varistors (MOV) are designed for specific applications and should not be used for purposes not identified in our specifications, application notes and data books unless otherwise agreed with JORDUN Electronics during the design-in-phase.
2. Ensure suitability of MOV through reliability testing during the design-in phase. The MOV should be evaluated taking into consideration worst-case conditions.
3. For applications of MOV in line-to ground circuits based on various international and local standards there are restrictions existing or additional safety measures required.

Storage

1. Store MOV only in original packaging. Do not open the package prior to processing.
2. Recommended storage conditions in original packaging:

Storage temperature:	-25 °C ... +45 °C
Relative humidity:	<75% annual average, <95% on maximum 30 days a year.
Dew precipitation:	Is to be avoided.
3. Avoid contamination of an MOV's during storage, handling and processing.
4. Avoid storage of MOVs in harmful environments that can affect the function during long-term operation (examples given under operation precautions).
5. The MOV type series should be soldered after shipment from JORDUN ELECTRONIC within the time specified.

MOV-J,N,T	24 months
-----------	-----------

Handling

1. MOVs must not be dropped.
2. Components must not be touched with bare hands. Gloves are recommended.
3. Avoid contamination of the surface of MOV electrodes during handling, be careful of the sharp edge of MOV electrodes.

Soldering (where applicable)

1. Use rosin-type flux or non-activated flux.
2. Insufficient preheating may cause ceramic cracks.

3. Rapid cooling by dipping in solvent is not recommended.
4. Complete removal of flux is recommended.
5. Temperatures of all preheat stages and the solder bath must be strictly controlled especially for T series (T14 and T20).

Mounting

1. Potting, sealing or adhesive compounds can produce chemical reactions in the MOV ceramic that will degrade the component's electrical characteristics.
2. Overloading MOVs may result in ruptured packages and expulsion of hot materials. For this reason the MOVs should be physically shielded from adjacent components.

Operation

1. Use MOVs only within the specified temperature operating range
2. Use MOVs only within the specified voltage and current ranges.
3. Environmental conditions must not harm the MOVs. Use MOVs only in normal atmospheric conditions. Avoid use in the presence of deoxidizing gases (chlorine gas, hydrogen sulfide gas, ammonia gas, sulfuric acid gas, etc), corrosive agents, humid or salty conditions, Avoid contact with any liquids and solvents.

Symbols and terms

Symbol	Term
C	Capacitance
C_{typ}	Typical capacitance
i	Current
i_c	Current at which $V_{c, max}$ is measured
I_{leak}	Leakage current
i_{max}	Maximum surge current (also termed peak current)
I_{max}	Maximum discharge current
I_n	Nominal discharge current to UL 1449
LCT	Lower category temperature
L_{typ}	Typical inductance
P_{max}	Maximum average power dissipation
R_{ins}	Insulation resistance
R_{min}	Minimum resistance
T_A	Ambient temperature
t_r	Duration of equivalent rectangular wave
UCT	Upper category temperature
v	Voltage
V_{clamp}	Clamping voltage
$V_{c, max}$	Maximum clamping voltage at specified current i_c DC operating voltage
V_{DC}	Maximum jump start voltage
V_{jump}	Maximum voltage
V_{max}	Operating voltage
V_{op}	AC operating voltage, root-mean-square value
V_{RMS}	Root-mean-square value of max. DC operating voltage incl. ripple current
$V_{RMS, op, max}$	Super imposed surge voltage
V_{surge}	Varistor voltage
V_V	Tolerance of varistor voltage
ΔV_V	
W_{LD}	Maximum load dump
W_{max}	Maximum energy absorption
	Lead spacing

All dimensions are given in mm.

The commas used in numerical values denote decimal points.

Release:Version January,2020