

S-5716 Series

LOW CURRENT CONSUMPTION OMNIPOLAR / UNIPOLAR DETECTION TYPE HALL EFFECT SWITCH IC

www.ablic.com

© ABLIC Inc., 2011-2021 Rev.1.7 00

This IC, developed by CMOS technology, is a high-accuracy Hall effect switch IC that operates with low current consumption.

The output voltage changes when this IC detects the intensity level of magnetic flux density. Using this IC with a magnet makes it possible to detect the open / close in various devices.

High-density mounting is possible by using the small SOT-23-3 package or the super small SNT-4A package.

Due to its high-accuracy magnetic characteristics, this IC can make operation's dispersion in the system combined with magnet smaller.

ABLIC Inc. offers a "magnetic simulation service" that provides the ideal combination of magnets and our Hall effect ICs for customer systems. Our magnetic simulation service will reduce prototype production, development period and development costs. In addition, it will contribute to optimization of parts to realize high cost performance.

For more information regarding our magnetic simulation service, contact our sales representatives.

■ Features

Pole detection^{*1}: Detection of omnipolar, S pole or N pole

• Output logic*1: Active "L", active "H"

• Output form*1: Nch open-drain output, CMOS output

• Magnetic sensitivity*1: Bop = 1.8 mT typ.

 $B_{OP} = 3.0 \text{ mT typ.}$ $B_{OP} = 3.4 \text{ mT typ.}$ $B_{OP} = 4.5 \text{ mT typ.}$ $B_{OP} = 7.0 \text{ mT typ.}$

• Operating cycle (current consumption): Product with omnipolar detection

tcycle = 50.50 ms (I_{DD} = 4.0 μ A) typ. Product with S pole or N pole detection I_{CYCLE} = 50.85 ms (I_{DD} = 2.6 μ A) typ.

• Power supply voltage range: $V_{DD} = 2.7 \text{ V to } 5.5 \text{ V}$ • Operation temperature range: Ta = -40°C to $+85^{\circ}\text{C}$

• Lead-free (Sn 100%), halogen-free

*1. The option can be selected.

■ Applications


- Plaything, portable game
- Home appliance
- · Housing equipment
- Industrial equipment

■ Packages

- SOT-23-3
- SNT-4A

■ Block Diagrams


1. Nch open-drain output product



*1. Parasitic diode

Figure 1

2. CMOS output product




*1. Parasitic diode

Figure 2

2 ABLIC Inc.

■ Product Name Structure

1. Product name



^{*1.} Refer to the tape drawing.

2. Packages

Table 1 Package Drawing Codes

Package name Dimension		Tape	Reel	Land
SOT-23-3	MP003-C-P-SD	MP003-C-C-SD	MP003-Z-R-SD	_
SNT-4A	PF004-A-P-SD	PF004-A-C-SD	PF004-A-R-SD	PF004-A-L-SD

3. Product name list

3.1 SOT-23-3

3. 1. 1 Nch open-drain output product

Table 2

Product Name	Operating Cycle (t _{CYCLE})	Output Form	Pole Detection	Output Logic	Magnetic Sensitivity (B _{OP})
S-5716ANDL0-M3T1U	50.50 ms typ.	Nch open-drain output	Omnipolar	Active "L"	1.8 mT typ.
S-5716ANDL1-M3T1U	50.50 ms typ.	Nch open-drain output	Omnipolar	Active "L"	3.0 mT typ.
S-5716ANDL2-M3T1U	50.50 ms typ.	Nch open-drain output	Omnipolar	Active "L"	4.5 mT typ.
S-5716ANDL3-M3T1U	50.50 ms typ.	Nch open-drain output	Omnipolar	Active "L"	7.0 mT typ
S-5716ANSL0-M3T1U	50.85 ms typ.	Nch open-drain output	S pole	Active "L"	1.8 mT typ.
S-5716ANSL1-M3T1U	50.85 ms typ.	Nch open-drain output	S pole	Active "L"	3.0 mT typ.
S-5716ANSL2-M3T1U	50.85 ms typ.	Nch open-drain output	S pole	Active "L"	4.5 mT typ.
S-5716ANSL3-M3T1U	50.85 ms typ.	Nch open-drain output	S pole	Active "L"	7.0 mT typ.
S-5716ANNL1-M3T1U	50.85 ms typ.	Nch open-drain output	N pole	Active "L"	3.0 mT typ.

Remark Please contact our sales representatives for products other than the above.

3. 1. 2 CMOS output product

Table 3

Product Name	Operating Cycle (tcycle)	Output Form	Pole Detection	Output Logic	Magnetic Sensitivity (B _{OP})
S-5716ACDL0-M3T1U	50.50 ms typ.	CMOS output	Omnipolar	Active "L"	1.8 mT typ.
S-5716ACDL1-M3T1U	50.50 ms typ.	CMOS output	Omnipolar	Active "L"	3.0 mT typ.
S-5716ACDL7-M3T1U	50.50 ms typ.	CMOS output	Omnipolar	Active "L"	3.4 mT typ.
S-5716ACDL2-M3T1U	50.50 ms typ.	CMOS output	Omnipolar	Active "L"	4.5 mT typ.
S-5716ACDL3-M3T1U	50.50 ms typ.	CMOS output	Omnipolar	Active "L"	7.0 mT typ
S-5716ACDH0-M3T1U	50.50 ms typ.	CMOS output	Omnipolar	Active "H"	1.8 mT typ.
S-5716ACDH1-M3T1U	50.50 ms typ.	CMOS output	Omnipolar	Active "H"	3.0 mT typ.
S-5716ACDH2-M3T1U	50.50 ms typ.	CMOS output	Omnipolar	Active "H"	4.5 mT typ.
S-5716ACSL0-M3T1U	50.85 ms typ.	CMOS output	S pole	Active "L"	1.8 mT typ.
S-5716ACSL1-M3T1U	50.85 ms typ.	CMOS output	S pole	Active "L"	3.0 mT typ.
S-5716ACSL2-M3T1U	50.85 ms typ.	CMOS output	S pole	Active "L"	4.5 mT typ.
S-5716ACSL3-M3T1U	50.85 ms typ.	CMOS output	S pole	Active "L"	7.0 mT typ.

Remark Please contact our sales representatives for products other than the above.

3. 2 SNT-4A

3. 2. 1 Nch open-drain output product

Table 4

Product Name	Operating Cycle (t _{CYCLE})	Output Form	Pole Detection	Output Logic	Magnetic Sensitivity (B _{OP})
S-5716ANDL0-I4T1U	50.50 ms typ.	Nch open-drain output	Omnipolar	Active "L"	1.8 mT typ.
S-5716ANDL1-I4T1U	50.50 ms typ.	Nch open-drain output	Omnipolar	Active "L"	3.0 mT typ.
S-5716ANDL2-I4T1U	50.50 ms typ.	Nch open-drain output	Omnipolar	Active "L"	4.5 mT typ.
S-5716ANDH0-I4T1U	50.50 ms typ.	Nch open-drain output	Omnipolar	Active "H"	1.8 mT typ.
S-5716ANSL0-I4T1U	50.85 ms typ.	Nch open-drain output	S pole	Active "L"	1.8 mT typ.
S-5716ANSL1-I4T1U	50.85 ms typ.	Nch open-drain output	S pole	Active "L"	3.0 mT typ.
S-5716ANSL2-I4T1U	50.85 ms typ.	Nch open-drain output	S pole	Active "L"	4.5 mT typ.
S-5716ANSL3-I4T1U	50.85 ms typ.	Nch open-drain output	S pole	Active "L"	7.0 mT typ.

Remark Please contact our sales representatives for products other than the above.

3. 2. 2 CMOS output product

Table 5

Product Name	Operating Cycle (tcycle)	Output Form	Pole Detection	Output Logic	Magnetic Sensitivity (B _{OP})
S-5716ACDL0-I4T1U	50.50 ms typ.	CMOS output	Omnipolar	Active "L"	1.8 mT typ.
S-5716ACDL1-I4T1U	50.50 ms typ.	CMOS output	Omnipolar	Active "L"	3.0 mT typ.
S-5716ACDL2-I4T1U	50.50 ms typ.	CMOS output	Omnipolar	Active "L"	4.5 mT typ.
S-5716ACDL3-I4T1U	50.50 ms typ.	CMOS output	Omnipolar	Active "L"	7.0 mT typ.
S-5716ACDH0-I4T1U	50.50 ms typ.	CMOS output	Omnipolar	Active "H"	1.8 mT typ.
S-5716ACDH1-I4T1U	50.50 ms typ.	CMOS output	Omnipolar	Active "H"	3.0 mT typ.
S-5716ACDH2-I4T1U	50.50 ms typ.	CMOS output	Omnipolar	Active "H"	4.5 mT typ.
S-5716ACDH3-I4T1U	50.50 ms typ.	CMOS output	Omnipolar	Active "H"	7.0 mT typ.
S-5716ACSL0-I4T1U	50.85 ms typ.	CMOS output	S pole	Active "L"	1.8 mT typ.
S-5716ACSL1-I4T1U	50.85 ms typ.	CMOS output	S pole	Active "L"	3.0 mT typ.
S-5716ACSL2-I4T1U	50.85 ms typ.	CMOS output	S pole	Active "L"	4.5 mT typ.
S-5716ACSH0-I4T1U	50.85 ms typ.	CMOS output	S pole	Active "H"	1.8 mT typ.
S-5716ACNL0-I4T1U	50.85 ms typ.	CMOS output	N pole	Active "L"	1.8 mT typ.

Remark Please contact our sales representatives for products other than the above.

■ Pin Configurations

1. SOT-23-3

Top view



Figure 3

Table 6

Pin No.	Symbol	Description
1	VSS	GND pin
2	VDD	Power supply pin
3	OUT	Output pin

2. SNT-4A

Top view



Figure 4

Table 7

Pin No.	Symbol	Description
1	VDD	Power supply pin
2	VSS	GND pin
3	NC*1	No connection
4	OUT	Output pin

^{*1.} The NC pin is electrically open.

The NC pin can be connected to the VDD pin or the VSS pin.

■ Absolute Maximum Ratings

Table 8

(Ta = +25°C unless otherwise specified)

	Item	Symbol	Absolute Maximum Rating	Unit
Power supply voltage		V_{DD}	$V_{SS} - 0.3$ to $V_{SS} + 7.0$	V
Output current		Гоит	±2.0	mA
Output voltage	Nch open-drain output product	V _{ОИТ}	$V_{SS} - 0.3 \text{ to } V_{SS} + 7.0$	V
Output voltage	CMOS output product	VOUT	$V_{\text{SS}} - 0.3$ to $V_{\text{DD}} + 0.3$	V
Operation ambient temperature		Topr	-40 to +85	°C
Storage temperatu	ıre	T _{stg}	-40 to +125	°C

Caution The absolute maximum ratings are rated values exceeding which the product could suffer physical damage. These values must therefore not be exceeded under any conditions.

■ Thermal Resistance Value

Table 9

Item	Symbol	Condition		Min.	Тур.	Max.	Unit
			Board A	_	200	_	°C/W
			Board B	1	165	1	°C/W
		SOT-23-3	Board C	1	-	1	°C/W
	$\theta_{\sf JA}$		Board D	1	1	ı	°C/W
lumetica to carbinat the same of a cictor co*1			Board E	1	1	ı	°C/W
Junction-to-ambient thermal resistance*1			Board A	ı	300	ı	°C/W
			Board B	1	242	ı	°C/W
		SNT-4A	Board C	1	1	ı	°C/W
			Board D	1	_	_	°C/W
			Board E	1	_		°C/W

^{*1.} Test environment: compliance with JEDEC STANDARD JESD51-2A

Remark Refer to "■ **Power Dissipation**" and "**Test Board**" for details.

■ Electrical Characteristics

1. Product with omnipolar detection

1. 1 S-5716AxDxx

Table 10

(Ta = +25°C, V_{DD} = 5.0 V, V_{SS} = 0 V unless otherwise specified)

Item	Symbol	Con	Condition			Max.	Unit	Test Circuit
Power supply voltage	V_{DD}		_	2.7	5.0	5.5	V	_
Current consumption	I _{DD}	Average value		_	4.0	8.0	μΑ	1
		Nch open-drain output product	Output transistor Nch, I _{OUT} = 2 mA	_	_	0.4	V	2
Output voltage	Vouт		Output transistor Nch, I _{OUT} = 2 mA	_	_	0.4	>	2
		CMOS output product Output transistor Pch, IouT = -2 mA		V _{DD} – 0.4	_	_	>	3
Leakage current	I _{LEAK}	Nch open-drain output ր Output transistor Nch, V		_	_	1	μΑ	4
Awake mode time	t _{AW}		_	_	0.10	_	ms	_
Sleep mode time	t _{SL}	-		_	50.40	_	ms	_
Operating cycle	tcycle	t _{AW} + t _{SL}		_	50.50	100.00	ms	_

2. Product with S pole or N pole detection

2. 1 S-5716AxSxx, S-5716AxNxx

Table 11

(Ta = +25°C, V_{DD} = 5.0 V, V_{SS} = 0 V unless otherwise specified)

	(14 120 0, VDD 0.0	*, *00		000 0111011				
Item	Symbol	Con	Condition			Max.	Unit	Test Circuit
Power supply voltage	V_{DD}		_	2.7	5.0	5.5	V	-
Current consumption	I _{DD}	Average value		_	2.6	5.0	μΑ	1
		Nch open-drain output product	Output transistor Nch, I _{OUT} = 2 mA	_	_	0.4	٧	2
Output voltage	V _{OUT}	CMOS suitant and dust	Output transistor Nch, I _{OUT} = 2 mA	_	_	0.4	>	2
		CMOS output product	Output transistor Pch, I _{OUT} = -2 mA	V _{DD} – 0.4	_	_	>	3
Leakage current	ILEAK	Nch open-drain output p Output transistor Nch, \		_	_	1	μΑ	4
Awake mode time	t _{AW}		_	_	0.05	_	ms	_
Sleep mode time	tsL	-		_	50.80	_	ms	_
Operating cycle	tcycle	taw + tsL		_	50.85	100.00	ms	_

■ Magnetic Characteristics

1. Product with omnipolar detection

1. 1 Product with $B_{OP} = 1.8 \text{ mT typ.}$

Table 12

(Ta = +25°C, V_{DD} = 5.0 V, V_{SS} = 0 V unless otherwise specified)

Item		Symbol	Condition	Min.	Тур.	Max.	Unit	Test Circuit
S pole		Bops	_	0.9	1.8	2.7	mT	5
Operation point*1	N pole	Bopn	_	-2.7	-1.8	-0.9	mT	5
D - l : 4*2	S pole	B _{RPS}	_	0.3	1.2	2.2	mT	5
Release point*2	N pole	B _{RPN}	_	-2.2	-1.2	-0.3	mT	5
1 1, 104 - 110 - 110 - 111 11	S pole	B _H yss	B _H YSS = B _O PS - B _R PS	_	0.6	1	mT	5
Hysteresis width*3	N pole	Bhysn	BHYSN = BOPN - BRPN	_	0.6	_	mT	5

1. 2 Product with $B_{OP} = 3.0 \text{ mT typ.}$

Table 13

(Ta = +25°C, V_{DD} = 5.0 V, V_{SS} = 0 V unless otherwise specified)

Item		Symbol	Condition	Min.	Тур.	Max.	Unit	Test Circuit
On austion maint*1	S pole	Bops	_	1.4	3.0	4.0	mT	5
Operation point*1	N pole	BOPN	_	-4.0	-3.0	-1.4	mT	5
Dalagas naint*2	S pole	B _{RPS}	_	1.1	2.2	3.7	mT	5
Release point*2	N pole	B _{RPN}	_	-3.7	-2.2	-1.1	mT	5
l lucata na aia unialth*3	S pole	B _{HYSS}	B _{HYSS} = B _{OPS} - B _{RPS}	I	8.0	ı	mT	5
Hysteresis width*3	N pole	BHYSN	BHYSN = BOPN - BRPN	I	0.8	ı	mT	5

1. 3 Product with $B_{OP} = 3.4 \text{ mT typ.}$

Table 14

(Ta = +25°C, V_{DD} = 5.0 V, V_{SS} = 0 V unless otherwise specified)

			\1u 12	O O, V DD	0.0 V, V33	o v arne	000 011101	wice opcomoa
Item		Symbol	Condition	Min.	Тур.	Max.	Unit	Test Circuit
0 ': '*1	S pole	Bops	_	2.0	3.4	5.6	mT	5
Operation point*1	N pole	BOPN	_	-5.6	-3.4	-2.0	mT	5
Dalagas maint*2	S pole	B _{RPS}	_	1.5	2.6	4.2	mT	5
Release point*2	N pole	B _{RPN}	_	-4.2	-2.6	-1.5	mT	5
Uvetereeje width*3	S pole	B _H YSS	B _H YSS = B _O PS - B _R PS	-	8.0	_	mT	5
Hysteresis width*3	N pole	BHYSN	BHYSN = BOPN - BRPN	-	0.8	_	mT	5

1. 4 Product with $B_{OP} = 4.5 \text{ mT typ.}$

Table 15

(Ta = +25°C, V_{DD} = 5.0 V, V_{SS} = 0 V unless otherwise specified)

Item		Symbol	Condition	Min.	Тур.	Max.	Unit	Test Circuit
S	S pole	Bops	_	2.5	4.5	6.0	mT	5
Operation point*1	N pole	Bopn	_	-6.0	-4.5	-2.5	mT	5
Dalagas naint*?	S pole	B _{RPS}	_	2.0	3.5	5.5	mT	5
Release point*2	N pole	B _{RPN}	_	-5.5	-3.5	-2.0	mT	5
Livetenesia viidtle*3	S pole	B _H YSS	B _H YSS = B _O PS - B _R PS	_	1.0	1	mT	5
Hysteresis width*3	N pole	BHYSN	BHYSN = BOPN - BRPN	-	1.0	ı	mT	5

1. 5 Product with $B_{OP} = 7.0 \text{ mT typ.}$

Table 16

(Ta = +25°C, V_{DD} = 5.0 V, V_{SS} = 0 V unless otherwise specified)

Item		Symbol	Condition	Min.	Тур.	Max.	Unit	Test Circuit
Operation point*1	S pole	Bops	_	5.0	7.0	8.5	mT	5
Operation point*1	N pole	Bopn	_	-8.5	-7.0	-5.0	mT	5
Dalagas naint*2	S pole	B _{RPS}	_	3.7	5.2	7.2	mT	5
Release point*2	N pole	B _{RPN}	_	-7.2	-5.2	-3.7	mT	5
l lyesta na aig vyigléla*3	S pole	B _H YSS	B _H YSS = B _O PS - B _R PS	I	1.8	I	mT	5
Hysteresis width*3	N pole	Bhysn	BHYSN = BOPN - BRPN	_	1.8	_	mT	5

2. Product with S pole detection

2. 1 Product with $B_{OP} = 1.8 \text{ mT typ.}$

Table 17

(Ta = +25°C, V_{DD} = 5.0 V, V_{SS} = 0 V unless otherwise specified)

Item		Symbol	Condition	Min.	Тур.	Max.	Unit	Test Circuit
Operation point*1	S pole	B _{OPS}	_	0.9	1.8	2.7	mT	5
Release point*2	S pole	B _{RPS}	_	0.3	1.2	2.2	mT	5
Hysteresis width*3	S pole	B _{HYSS}	B _H YSS = B _{OPS} - B _{RPS}	-	0.6	-	mT	5

2. 2 Product with $B_{OP} = 3.0 \text{ mT typ.}$

Table 18

(Ta = +25°C, V_{DD} = 5.0 V, V_{SS} = 0 V unless otherwise specified)

			\ · · -	,				
Item		Symbol	Condition	Min.	Тур.	Max.	Unit	Test Circuit
Operation point*1	S pole	B _{OPS}	_	1.4	3.0	4.0	mT	5
Release point*2	S pole	B _{RPS}	_	1.1	2.2	3.7	mT	5
Hysteresis width*3	S pole	B _{HYSS}	B _H YSS = B _O PS - B _R PS	ı	8.0	ı	mT	5

2. 3 Product with $B_{OP} = 3.4 \text{ mT typ.}$

Table 19

(Ta = +25°C, V_{DD} = 5.0 V, V_{SS} = 0 V unless otherwise specified)

			(0,	0.0 1, 100	0 1 011110		mee epeemea)
Item		Symbol	Condition	Min.	Тур.	Max.	Unit	Test Circuit
Operation point*1	S pole	B _{OPS}	_	2.0	3.4	5.6	mT	5
Release point*2	S pole	B _{RPS}	_	1.5	2.6	4.2	mT	5
Hysteresis width*3	S pole	B _{HYSS}	B _{HYSS} = B _{OPS} – B _{RPS}	-	8.0	_	mT	5

2. 4 Product with $B_{OP} = 4.5 \text{ mT typ.}$

Table 20

(Ta = +25°C, V_{DD} = 5.0 V, V_{SS} = 0 V unless otherwise specified)

Item		Symbol	Condition	Min.	Тур.	Max.	Unit	Test Circuit
Operation point*1	S pole	Bops	_	2.5	4.5	6.0	mT	5
Release point*2	S pole	B _{RPS}	_	2.0	3.5	5.5	mT	5
Hysteresis width*3	S pole	B _{HYSS}	B _{HYSS} = B _{OPS} - B _{RPS}	_	1.0	1	mT	5

2. 5 Product with $B_{OP} = 7.0 \text{ mT typ.}$

Table 21

(Ta = +25°C, V_{DD} = 5.0 V, V_{SS} = 0 V unless otherwise specified)

			\ · · -	,	,			
Item		Symbol	Condition	Min.	Тур.	Max.	Unit	Test Circuit
Operation point*1	S pole	Bops	-	5.0	7.0	8.5	mT	5
Release point*2	S pole	B _{RPS}	_	3.7	5.2	7.2	mT	5
Hysteresis width*3	S pole	B _H yss	B _{HYSS} = B _{OPS} - B _{RPS}	ı	1.8	ı	mT	5

10 ABLIC Inc.

3. Product with N pole detection

3. 1 Product with $B_{OP} = 1.8 \text{ mT typ.}$

Table 22

(Ta = +25°C, V_{DD} = 5.0 V, V_{SS} = 0 V unless otherwise specified)

Item		Symbol	Condition	Min.	Тур.	Max.	Unit	Test Circuit
Operation point*1	N pole	Bopn	_	-2.7	-1.8	-0.9	mT	5
Release point*2	N pole	B _{RPN}	_	-2.2	-1.2	-0.3	mT	5
Hysteresis width*3	N pole	BHYSN	B _H YSN = B _O PN - B _R PN	1	0.6	1	mT	5

3. 2 Product with $B_{OP} = 3.0 \text{ mT typ.}$

Table 23

(Ta = +25°C, V_{DD} = 5.0 V, V_{SS} = 0 V unless otherwise specified)

Item		Symbol	Condition	Min.	Тур.	Max.	Unit	Test Circuit
Operation point*1	N pole	BOPN	_	-4.0	-3.0	-1.4	mT	5
Release point*2	N pole	B _{RPN}	_	-3.7	-2.2	-1.1	mT	5
Hysteresis width*3	N pole	Bhysn	B _{HYSN} = B _{OPN} - B _{RPN}	_	0.8	_	mT	5

3. 3 Product with $B_{OP} = 3.4 \text{ mT typ.}$

Table 24

(Ta = +25°C, V_{DD} = 5.0 V, V_{SS} = 0 V unless otherwise specified)

Item		Symbol	Condition	Min.	Тур.	Max.	Unit	Test Circuit
Operation point*1	N pole	Bopn	_	-5.6	-3.4	-2.0	mT	5
Release point*2	N pole	B _{RPN}	-	-4.2	-2.6	-1.5	mT	5
Hysteresis width*3	N pole	BHYSN	BHYSN = BOPN - BRPN	_	0.8	_	mT	5

3. 4 Product with $B_{OP} = 4.5 \text{ mT typ.}$

Table 25

(Ta = +25°C, V_{DD} = 5.0 V, V_{SS} = 0 V unless otherwise specified)

			\	0, 100	0.0 1, 100	0 1 00	00 01	
Item		Symbol	Condition	Min.	Тур.	Max.	Unit	Test Circuit
Operation point*1	N pole	Вори	_	-6.0	-4.5	-2.5	mT	5
Release point*2	N pole	B _{RPN}	_	-5.5	-3.5	-2.0	mT	5
Hysteresis width*3	N pole	BHYSN	BHYSN = BOPN - BRPN	_	1.0	_	mT	5

3. 5 Product with $B_{OP} = 7.0 \text{ mT typ.}$

Table 26

(Ta = +25°C, V_{DD} = 5.0 V, V_{SS} = 0 V unless otherwise specified)

			(,	,			
Item		Symbol	Condition	Min.	Тур.	Max.	Unit	Test Circuit
Operation point*1	N pole	Bopn	_	-8.5	-7.0	-5.0	mT	5
Release point*2	N pole	B _{RPN}	_	-7.2	-5.2	-3.7	mT	5
Hysteresis width*3	N pole	BHYSN	BHYSN = IBOPN - BRPNI	_	1.8	_	mT	5

*1. BOPN, BOPS: Operation points

 B_{OPN} and B_{OPS} are the values of magnetic flux density when the output voltage (V_{OUT}) is inverted after the magnetic flux density applied to this IC by the magnet (N pole or S pole) is increased (by moving the magnet closer).

Even when the magnetic flux density exceeds Bopn or Bops, Vout retains the status.

*2. BRPN, BRPS: Release points

 B_{RPN} and B_{RPS} are the values of magnetic flux density when the output voltage (V_{OUT}) is inverted after the magnetic flux density applied to this IC by the magnet (N pole or S pole) is decreased (the magnet is moved further away).


Even when the magnetic flux density falls below BRPN or BRPS, Vout retains the status.

*3. BHYSN, BHYSS: Hysteresis widths

BHYSN and BHYSS are the difference between Bopn and BRPN, and BOPS and BRPS, respectively.

Remark The unit of magnetic density mT can be converted by using the formula 1 mT = 10 Gauss.

■ Test Circuits



*1. Resistor (R) is unnecessary for the CMOS output product.

Figure 5 Test Circuit 1




Figure 6 Test Circuit 2




Figure 7 Test Circuit 3

12 ABLIC Inc.






Figure 8 Test Circuit 4



*1. Resistor (R) is unnecessary for the CMOS output product.

Figure 9 Test Circuit 5

■ Standard Circuit



*1. Resistor (R) is unnecessary for the CMOS output product.

Figure 10

Caution The above connection diagram and constant will not guarantee successful operation. Perform thorough evaluation using the actual application to set the constant.

14 ABLIC Inc.

■ Operation

1. Direction of applied magnetic flux


This IC detects the magnetic flux density which is vertical to the marking surface.

In product with omnipolar detection, the output voltage (V_{OUT}) is inverted when the S pole or N pole is moved closer to the marking surface.

In product with S pole detection, V_{OUT} is inverted when the S pole is moved closer to the marking surface.

In product with N pole detection, V_{OUT} is inverted when the N pole is moved closer to the marking surface.

Figure 11 and Figure 12 show the direction in which magnetic flux is being applied.



2. Position of Hall sensor

Figure 13

2. 1 SOT-23-3

Figure 13 and Figure 14 show the position of Hall sensor.

The center of this Hall sensor is located in the area indicated by a circle, which is in the center of a package as described below.

2. 2 SNT-4A

The following also shows the distance (typ. value) between the marking surface and the chip surface of a package.

Top view Top view The center of Hall sensor; The center of Hall sensor; in this ϕ 0.3 mm in this ϕ 0.3 mm 73 2

Figure 14

0.16 mm tvp.

3. Basic operation

This IC changes the output voltage level (V_{OUT}) according to the level of the magnetic flux density (N pole or S pole) applied by a magnet.

The following explains the operation when the output logic is active "L".

3. 1 Product with omnipolar detection

When the magnetic flux density vertical to the marking surface exceeds the operation point (B_{OPN} or B_{OPS}) after the S pole or N pole of a magnet is moved closer to the marking surface of this IC, V_{OUT} changes from "H" to "L". When the S pole or N pole of a magnet is moved further away from the marking surface of this IC and the magnetic flux density is lower than the release point (B_{RPN} or B_{RPS}), V_{OUT} changes from "L" to "H".

Figure 15 shows the relationship between the magnetic flux density and Vout.




Figure 15

3. 2 Product with S pole detection

When the magnetic flux density vertical to the marking surface exceeds B_{OPS} after the S pole of a magnet is moved closer to the marking surface of this IC, V_{OUT} changes from "H" to "L". When the S pole of a magnet is moved further away from the marking surface of this IC and the magnetic flux density is lower than B_{RPS} , V_{OUT} changes from "L" to "H".

Figure 16 shows the relationship between the magnetic flux density and Vout.




Figure 16

16 ABLIC Inc.

3. 3 Product with N pole detection

When the magnetic flux density vertical to the marking surface exceeds B_{OPN} after the N pole of a magnet is moved closer to the marking surface of this IC, V_{OUT} changes from "H" to "L". When the N pole of a magnet is moved further away from the marking surface of this IC and the magnetic flux density is lower than B_{RPN} , V_{OUT} changes from "L" to "H".

Figure 17 shows the relationship between the magnetic flux density and Vout.




Figure 17


LOW CURRENT CONSUMPTION OMNIPOLAR / UNIPOLAR DETECTION TYPE HALL EFFECT SWITCH IC S-5716 Series Rev.1.7 00

■ Precautions

- If the impedance of the power supply is high, the IC may malfunction due to a supply voltage drop caused by feed-through current. Take care with the pattern wiring to ensure that the impedance of the power supply is low.
- Note that the IC may malfunction if the power supply voltage rapidly changes.
- Do not apply an electrostatic discharge to this IC that exceeds the performance ratings of the built-in electrostatic protection circuit.
- Large stress on this IC may affect the magnetic characteristics. Avoid large stress which is caused by bend and distortion during mounting the IC on a board or handle after mounting.
- ABLIC Inc. claims no responsibility for any disputes arising out of or in connection with any infringement by products including this IC of patents owned by a third party.


■ Power Dissipation

SOT-23-3



Board	Power Dissipation (P _D)
Α	0.50 W
В	0.61 W
С	_
D	_
Е	_


SNT-4A



Board	Power Dissipation (P _D)
Α	0.33 W
В	0.41 W
С	_
D	_
Е	_

SOT-23-3/3S/5/6 Test Board

(1) Board A





Item		Specification		
Size [mm]		114.3 x 76.2 x t1.6		
Material		FR-4		
Number of copper foil layer		2		
	1	Land pattern and wiring for testing: t0.070		
Coppor foil lover [mm]	2	-		
Copper foil layer [mm]	3	-		
	4	74.2 x 74.2 x t0.070		
Thermal via		-		

(2) Board B




Item		Specification		
Size [mm]		114.3 x 76.2 x t1.6		
Material		FR-4		
Number of copper foil layer		4		
	1	Land pattern and wiring for testing: t0.070		
Copper foil layer [mm]	2	74.2 x 74.2 x t0.035		
Copper foil layer [mm]	3	74.2 x 74.2 x t0.035		
	4	74.2 x 74.2 x t0.070		
Thermal via		-		

No. SOT23x-A-Board-SD-2.0

SNT-4A Test Board

(1) Board A






Item		Specification		
Size [mm]		114.3 x 76.2 x t1.6		
Material		FR-4		
Number of copper foil layer		2		
	1	Land pattern and wiring for testing: t0.070		
Copper foil layer [mm]	2	-		
Copper foil layer [ITIII]	3	-		
	4	74.2 x 74.2 x t0.070		
Thermal via		-		


(2) Board B




Item		Specification		
Size [mm]		114.3 x 76.2 x t1.6		
Material		FR-4		
Number of copper foil layer		4		
	1	Land pattern and wiring for testing: t0.070		
Connor foil lover [mm]	2	74.2 x 74.2 x t0.035		
Copper foil layer [mm]	3	74.2 x 74.2 x t0.035		
	4	74.2 x 74.2 x t0.070		
Thermal via		-		

No. SNT4A-A-Board-SD-1.0









No. MP003-C-P-SD-1.1


TITLE	SOT233-C-PKG Dimensions			
No.	MP003-C-P-SD-1.1			
ANGLE	\$			
UNIT	mm			
ABLIC Inc.				
ADLIC IIIC.				






No. MP003-C-C-SD-2.0


SOT233-C-Carrier Tape				
MP003-C-C-SD-2.0				
mm				
ABLIC Inc.				



No. MP003-Z-R-SD-1.0


TITLE	SOT233-C-Reel			
No.	MP00	03-Z-R-SE)-1.0	
ANGLE		QTY.	3,000	
UNIT	mm			
ABLIC Inc.				






No. PF004-A-P-SD-6.0


TITLE	SNT-4A-A-PKG Dimensions		
No.	PF004-A-P-SD-6.0		
ANGLE	\$ = 3		
UNIT	mm		
ABLIC Inc.			






No. PF004-A-C-SD-2.0

TITLE	SNT-4A-A-Carrier Tape		
No.	PF004-A-C-SD-2.0		
ANGLE			
UNIT	mm		
ABLIC Inc.			



TITLE	SNT-4A-A-Reel			
No.	PF004-A-R-SD-1.0			
ANGLE		QTY.	5,000	
UNIT	mm			
ABLIC Inc.				



- %1. ランドパターンの幅に注意してください (0.25 mm min. / 0.30 mm typ.)。 %2. パッケージ中央にランドパターンを広げないでください (1.10 mm ~ 1.20 mm)。
- 注意 1. パッケージのモールド樹脂下にシルク印刷やハンダ印刷などしないでください。
 - 2. パッケージ下の配線上のソルダーレジストなどの厚みをランドパターン表面から0.03 mm 以下にしてください。
 - 3. マスク開口サイズと開口位置はランドパターンと合わせてください。
 - 4. 詳細は "SNTパッケージ活用の手引き"を参照してください。
- ※1. Pay attention to the land pattern width (0.25 mm min. / 0.30 mm typ.).
- ※2. Do not widen the land pattern to the center of the package (1.10 mm to 1.20 mm).
- Caution 1. Do not do silkscreen printing and solder printing under the mold resin of the package.
 - 2. The thickness of the solder resist on the wire pattern under the package should be 0.03 mm or less from the land pattern surface.
 - 3. Match the mask aperture size and aperture position with the land pattern.
 - 4. Refer to "SNT Package User's Guide" for details.
- ※1. 请注意焊盘模式的宽度 (0.25 mm min. / 0.30 mm typ.)。
- ※2. 请勿向封装中间扩展焊盘模式 (1.10 mm ~ 1.20 mm)。
- 注意 1. 请勿在树脂型封装的下面印刷丝网、焊锡。
 - 2. 在封装下、布线上的阻焊膜厚度 (从焊盘模式表面起) 请控制在 0.03 mm 以下。
 - 3. 钢网的开口尺寸和开口位置请与焊盘模式对齐。
 - 4. 详细内容请参阅 "SNT 封装的应用指南"。

No. PF004-A-L-SD-4.1

TITLE	SNT-4A-A -Land Recommendation		
No.	PF004-A-L-SD-4.1		
ANGLE			
UNIT	mm		
ABLIC Inc.			

Disclaimers (Handling Precautions)

- 1. All the information described herein (product data, specifications, figures, tables, programs, algorithms and application circuit examples, etc.) is current as of publishing date of this document and is subject to change without notice.
- 2. The circuit examples and the usages described herein are for reference only, and do not guarantee the success of any specific mass-production design.
 - ABLIC Inc. is not liable for any losses, damages, claims or demands caused by the reasons other than the products described herein (hereinafter "the products") or infringement of third-party intellectual property right and any other right due to the use of the information described herein.
- 3. ABLIC Inc. is not liable for any losses, damages, claims or demands caused by the incorrect information described herein.
- 4. Be careful to use the products within their ranges described herein. Pay special attention for use to the absolute maximum ratings, operation voltage range and electrical characteristics, etc.
 - ABLIC Inc. is not liable for any losses, damages, claims or demands caused by failures and / or accidents, etc. due to the use of the products outside their specified ranges.
- 5. Before using the products, confirm their applications, and the laws and regulations of the region or country where they are used and verify suitability, safety and other factors for the intended use.
- 6. When exporting the products, comply with the Foreign Exchange and Foreign Trade Act and all other export-related laws, and follow the required procedures.
- 7. The products are strictly prohibited from using, providing or exporting for the purposes of the development of weapons of mass destruction or military use. ABLIC Inc. is not liable for any losses, damages, claims or demands caused by any provision or export to the person or entity who intends to develop, manufacture, use or store nuclear, biological or chemical weapons or missiles, or use any other military purposes.
- 8. The products are not designed to be used as part of any device or equipment that may affect the human body, human life, or assets (such as medical equipment, disaster prevention systems, security systems, combustion control systems, infrastructure control systems, vehicle equipment, traffic systems, in-vehicle equipment, aviation equipment, aerospace equipment, and nuclear-related equipment), excluding when specified for in-vehicle use or other uses by ABLIC, Inc. Do not apply the products to the above listed devices and equipments.
 - ABLIC Inc. is not liable for any losses, damages, claims or demands caused by unauthorized or unspecified use of the products.
- 9. In general, semiconductor products may fail or malfunction with some probability. The user of the products should therefore take responsibility to give thorough consideration to safety design including redundancy, fire spread prevention measures, and malfunction prevention to prevent accidents causing injury or death, fires and social damage, etc. that may ensue from the products' failure or malfunction.
 - The entire system in which the products are used must be sufficiently evaluated and judged whether the products are allowed to apply for the system on customer's own responsibility.
- 10. The products are not designed to be radiation-proof. The necessary radiation measures should be taken in the product design by the customer depending on the intended use.
- 11. The products do not affect human health under normal use. However, they contain chemical substances and heavy metals and should therefore not be put in the mouth. The fracture surfaces of wafers and chips may be sharp. Be careful when handling these with the bare hands to prevent injuries, etc.
- 12. When disposing of the products, comply with the laws and ordinances of the country or region where they are used.
- 13. The information described herein contains copyright information and know-how of ABLIC Inc. The information described herein does not convey any license under any intellectual property rights or any other rights belonging to ABLIC Inc. or a third party. Reproduction or copying of the information from this document or any part of this document described herein for the purpose of disclosing it to a third-party is strictly prohibited without the express permission of ABLIC Inc.
- 14. For more details on the information described herein or any other questions, please contact ABLIC Inc.'s sales representative.
- 15. This Disclaimers have been delivered in a text using the Japanese language, which text, despite any translations into the English language and the Chinese language, shall be controlling.

