

### PHOTOCOUPLER LINEUP

RoHS

#### ■ Photocoupler Lineup

#### <Phototransistor output type>

Package type	Output type	Features		Model No. (series)	Page
Mini-flat 4-pin		General purpose,			
Compact, SMT type	Single phototransistor	High collector-emitter voltage, etc.		PC35x series / PC451J00000F	41
			Low input current	PC367NJ0000F	41
		AC input response		PC354NJ0000F	41
1		High sensitivity.	Low input current	PC364NJ0000F	41
	Darlington phototransistor	High collector-emitter voltage		PC355NJ0000F / PC452J00000F	41
			Low input current	PC365NJ0000F	41
Compact, Half pitch (lead space), SMT type	Single phototransistor	General purpose, High resistance to noise, etc.		PC3Hx series	42
			Reinforced insulation	PC3HU7xYIP0B	42
٠.			Low input current	PC3H71xNIP0F	42
•		AC input response		PC3H3J00000F / PC3H4J00000F	42
			Low input current	PC3H41xNIP0F	42
	Darlington phototransistor	High sensitivity		PC3H5J00000F	42
			Low input current	PC3H510NIP0F	42
DIP type (4-pin)	Single phototransistor	Reinforced insulation		PC123XNNSZ0F	43
(4-pin, DIP type)		General purpose,	Low input current	PC1231xNSZ0X	43
		High collector-emitter voltage, etc.		PC817XNNSZ0F / PC851XNNSZ0F	43
			Low input current	PC8171xNSZ0X	43
7,	Darlington phototransistor	High sensitivity, High collector-emitter voltage		PC815XNNSZ0F / PC852XNNSZ0F / PC853XNNSZ0F	43
	<u> </u>		Low input current	PC81510NSZ0X	43
DIP type (6-pin)	Single phototransistor	General purpose, High collector-emitter voltage, etc.	· · ·	PC7xxV0NSZXF	44
	Darlington phototransistor	High sensitivity, High collector-emitter voltage, etc.		PC7x5V0NSZXF	44

#### <OPIC output type>

Package type	Output type	Features	Model No. (series)	Page
Compact, SMT type	Digital output	General purpose, High response speed, 2ch, etc.	PC400J00000F / PC456L0NIP0F ▲ / PC410S0NIP0F / PC410L0NIP0F / PC4D10SNIP0F	45
۰ الم الم	Analog/Digital output	High CMR	PC457S0NIP0F / PC457L0NIP0F	45
DIP type, SMT type	Digital output	General purpose	PC900V0NSZXF	46
	Built-in base amplifier	For inverter control, Built-in short-circuit protection circuit	PC925LxNSZ0F / PC942J00000F ▲ / PC928J00000F / PC929J00000F	46

The model marked with ▲ may not be available in the near future. Contact with SHARP for details before use.

RoHS

Photocouplers

#### Phototransistor Output Type

<(	Compact, SMT	type>			O: Appro	oved							(	Ta = 2	:5°C)
				Approved		Absolute	e maximur	n ratings		Electro	o-optica	al char	acteris	stics	
be		Internal		by safety standards*2			Isolation	Collector-	Current	transfe	er ratio	R	espon	se time	е
Output type	Model No.	connection diagram	Features	UL	Package	Forward current IF (mA)	voltage (AC) Viso (rms) (kV)	emitter voltage VCEO (V)	CTR (%) MIN.	lF (mA)	Vce (V)	tr (µs) TYP.	Ic (mA)	R∟ (Ω)	Vce (V)
	PC357NJ0000F		General purpose	0*		50	3.75	80	50	5	5	4	2	100	2
utput	PC352NJ0000F▲		General purpose, high resistance to noise*1	0		50	3.75	80	90	5	5	4	2	100	2
ansistor o	PC451J00000F		High collector-emitter voltage	0*		50	3.75	350	40	5	5	4	2	100	2
Single phototransistor output	PC367NJ0000F		Low input current, high resistance to noise*1	0		10	3.75	80	100	0.5	5	4	2	100	2
Singl	PC354NJ0000F		AC input response	0*	Mini-flat 4-pin	±50	3.75	80	20	±1	5	4	2	100	2
	PC364NJ0000F		Low input current, AC input response, high resistance to noise*1	0		±10	3.75	80	50	±0.5	5	4	2	100	2
oto- put	PC355NJ0000F		High sensitivity	0*		50	3.75	35	600	1	2	60	2	100	2
Darlington photo- transistor output	PC365NJ0000F		High sensitivity, low input current	0		10	3.75	35	600	0.5	2	60	10	100	2
Dar trar	PC452J00000F		High collector-emitter voltage	0*		50	3.75	350	1 000	1	2	100	20	100	2

\*1 CMR: MIN.10 kV/µs
 \*2 Please refer to Specification Sheets for model numbers approved by safety standards.

\* A VDE approved type is optionally available.

The model marked with ▲ may not be available in the near future. Contact with SHARP for details before use.





### RoHS

#### Phototransistor Output Type <Compact, half pitch (lead space) SMT type>

<(	Compact, half	pitch (lead	space) SMT type>		O: Appr	oved							Т)	a = 28	5°C)
				Approved		Absolute	maximur	n ratings		Electro	-optica	l char	acteris	stics	
Output type	Model No.	Internal connection	Features	by safety standards*3		Forward	voltage	Collector- emitter	Curr	ent trar ratio	nsfer	R	espons	se tim	e
Outpu	Model No.	diagram	reatures	UL	Package	current IF (mA)	(AC) Viso (rms) (kV)	voltage VCEO (V)	CTR (%) MIN.	lF (mA)	Vce (V)	tr (µs) TYP.	Ic (mA)	R∟ (Ω)	Vce (V)
	PC3HU7xYIP0B		Reinforced insulation (internal insulation distance: MIN. 0.4 mm), low-profile package	○*4, 5	Low- profile mini-flat 4-pin	50	3.75	80	50	5	5	4	2	100	2
output	PC3H7J00000F		Standard	⊖*6		50	2.5	80	20	1	5	4	2	100	2
Single phototransistor output	PC3H71xNIP0F		High resistance to noise*1, low input current	0		10	2.5	80	100	0.5	5	4	2	100	2
jle photot	PC3H3J00000F		AC input response, high resistance to noise*1	0	Mini-flat 4-pin	±50	2.5	80	20	±1	5	4	2	100	2
Sing	PC3H4J00000F		AC input response	<b>○*2</b> , 6		±50	2.5	80	20	±1	5	4	2	100	2
	PC3H41xNIP0F		AC input response, high resistance to noise*1, low input current	0		±10	2.5	80	50	±0.5	5	4	2	100	2
Darlington photo- transistor output	PC3H5J00000F		High sensitivity	0	Mini-flat	50	2.5	35	600	1	2	60	2	100	2
Darlingto transisto	PC3H510NIP0F		High sensitivity, low input current	0	4-pin	10	2.5	35	600	0.5	2	60	2	100	2

\*1 CMR: MIN.10 kV/µs
\*2 A VDE approved type is optionally available.
\*3 Please refer to Specification Sheets for model numbers approved by safety standards.
\*4 VDE, CSA approved
\*5 In conformance with BSI, SEMKO, DEMKO, NEMKO, and FIMKO
\*6 UL, cUL approved



### RoHS

#### Phototransistor Output Type

	<dip (4-pin)="" type=""></dip>				Г	— O: A	Approve	d					(Ta = 2	25°C)
e					oprove	d by dards* <sup>8</sup>		Absolu	te maximu	<u> </u>		•		
t typ	Madel No.	Internal	Factures	salet	y stan		Deelvere	Forward	Isolation voltage	Collector- emitter	Current tra		Respon	
Output type	Model No.	connection diagram	Features	UL	VDE *2	Others	Package	current IF (mA)	(AC) Viso (rms) (kV)	voltage Vceo (V)	CTR (%) MIN.	l⊧ (mA)	tr (µs) TYP.	Rι (Ω)
ŧ	PC123XNNSZ0F*1, *5, *6, *7		High isolation voltage, reinforced insulation	0	0	0		50	5.0	70	50	5	4	100
Single phototransistor output	PC1231xNSZ0X*1		High isolation voltage, reinforced insulation, low input current, high resistance to noise <sup>*4</sup>	0	0	0		10	5.0	70	50	0.5	4	100
ototransis	PC817XNNSZ0F*5, *6, *7		High isolation voltage	0	_	O*9		50	5.0	80	50	5	4	100
single pho	PC8171xNSZ0X* <sup>5, *6</sup>		High isolation voltage, low input current, high resistance to noise*4	0	_	-		10	5.0	80	100	0.5	4	100
05	PC851XNNSZ0F*5, *6		High isolation voltage, high collector-emitter voltage	0	_	_	4-pin DIP	50	5.0	350	40	5	4	100
r output	PC815XNNSZ0F* <sup>5, *6</sup>		High isolation voltage, high sensitivity	0	_	_		50	5.0	35	600	1	60	100
Darlington phototransistor output	PC81510NSZ0X		High isolation voltage, high sensitivity, low input current	0	_	-		10	5.0	35	600	0.5	60	100
ngton pho	PC852XNNSZ0F*5, *6		High isolation voltage, high collector-emitter voltage	0	0	_		50	5.0	350	1 000	1	100	100
Darli	PC853XNNSZ0F*5, *6		High isolation voltage, high collector-emitter voltage	0	0	_		50	5.0	350	1 000	1	100	100

\*1 Wide lead spacing type is also available. Creepage distance: 6.4 mm or more, wide lead spacing type: 8 mm or more.
\*2 Optionally available.
\*3 BSI, SEMKO, DEMKO, NEMKO, FIMKO, CSA
\*4 CMR: 10 kV/µs MIN.
\*5 Lead forming type is also available for surface mounting.
\*6 Taped package of lead forming type for surface mounting is also available.
\*7 Wide lead spacing type is also available. Compatible with wide lead spacing type lead-forming models for surface-mount use. Also compatible with taped packages for wide lead spacing type lead-forming models for surface-mount use.
\*8 Please refer to Specification Sheets for model numbers approved by safety standards.
\*9 UIL CSA approved

\*9 UL, CSA approved





### RoHS

#### Phototransistor Output Type

<	DIP type (6-pin)	)>			$\square^{\circ}$	: Approve	ed, ∆: Ur	nder applic	ation			(Ta =	= 25°C)
Output type	Ma dal Na	Internal	<b>F</b>	by s	roved afety ards*2	Dealara	Forward	te maximun Isolation voltage	n ratings Collector- emitter	Electro Current rat		characte Resp tin	onse
Outpu	Model No.	connection diagram	Features	UL	VDE*1	Package	current IF (mA)	(AC) Viso (rms) (kV)	voltage VCEO (V)	CTR (%) MIN.	lf (mA)	tr (μs) TYP.	R∟ (Ω)
or output	PC714V0NSZXF		High isolation voltage	0	0		50	5.0	80	50	5	4	100
Single phototransistor output	PC724V0NSZXF		High isolation voltage, large input current	0	-		150	5.0	35	20	100	4	100
Single ph	PC713V0NSZXF		High isolation voltage, with base terminal	0	0		50	5.0	80	50	5	4	100
Darlington phototransistor output	PC715V0NSZXF		High isolation voltage, high sensitivity	0	0	6-pin DIP	50	5.0	35	600	1	60	100
Darlington photo	PC725V0NSZXF		High isolation voltage, high sensitivity, high collector-emitter voltage, high power	0	0		50	5.0	300	1 000	1	100	100

\*1 Optionally available.
\*2 Please refer to Specification Sheets for model numbers approved by safety standards.



♦ OPIC Output ( "OPIC" (Optical IC) is a trademark of SHARP Corporation. An OPIC consists of a light-detecting element and signal-processing circuit integrated onto a single chip. )

<compact, s<="" th=""><th>SMT type:</th><th>&gt; (1-1)</th><th></th><th>, C</th><th>: Approv</th><th>ed</th><th>0</th><th></th><th></th><th></th><th></th><th></th><th>(Ta =</th><th>= 25°C)</th></compact,>	SMT type:	> (1-1)		, C	: Approv	ed	0						(Ta =	= 25°C)
			Approved by safety				maximum ngs		Electro	o-optica	al chara	acteristic	s*1	
Madalala	Internal	E a standa	stand	ards*2	Package	Forward	Isolation	Lo	w level outpu	ut volta	ge	Thresho	ld input	current
Model No.	connection diagram	Features	UL	VDE*3		current IF (mA)	voltage (AC) Viso (rms) (kV)	Vol (V) MAX.	Ta (°C)	lo∟ (mA)	lF (mA)	IFн∟ (mA) MAX.	Iflн (mA) MAX.	R∟ (Ω)
PC400J00000F		Digital output, normal-off operation	0	-		50	3.75	0.4	0 to +70	16	4	2.0	-	280
PC456L0NIP0F▲		Built-in preamplifier, high speed transmission (2 Mb/s), for flow soldering	0	0	Mini-flat 5-pin	25	3.75	0.6	-40 to +85	2.4	10	5.0	-	20 k
PC410L0NIP0F		High speed (10 Mb/s), High CMR (10 kV/µs), For flow soldering	0	0		20	3.75	0.6	-40 to +85	13	5	5.0	-	350
PC410S0NIP0F		High speed (10 Mb/s), high CMR (10 kV/µs), for flow soldering, Solder heat resistance: 270°C	0	0	SOP 8-pin	20	3.75	0.6	-40 to +85	13	5	5.0	-	350
PC4D10SNIP0F		High speed (10 Mb/s), for flow soldering, Solder heat resistance: 270°C 2ch output	0	_	SOP 8-pin	20	3.75	0.6	-40 to +85	13	5	5.0	-	350

A: Rated voltage circuit

\*1 Each item is measured at Vcc=5V. (PC400)

\_

\*2 Please refer to Specification Sheets for model numbers approved by safety standards.
\*3 Optionally available.
The model marked with ▲ may not be available in the near future. Contact with SHARP for details before use.

<compact,< th=""><th>, SMT type</th><th>&gt; (1-2)</th><th></th><th></th><th>: Approv</th><th>ed</th><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th>(Ta =</th><th>= 25°C)</th></compact,<>	, SMT type	> (1-2)			: Approv	ed								(Ta =	= 25°C)		
			Approved by safety		Approved by safety		100.05		Absolute maximum ratings			Electr	o-optic	al chara	cteristic	cs	
	Internal		stand	ards*1	<b>_</b> .	Forward	Isolation	Cur	rent tra	ansfer i	ratio	Prop	oagatio	n delay	time		
Model No.	connection diagram	Features	UL	VDE*2	Package	current IF (mA)	voltage (AC) Viso (rms) (kV)	CTR (%) MIN.	lF (mA)	Vo (V)	Vcc (V)	t₽HL (µs) TYP.	tpLH (µs) TYP.	RL (Ω)	lF (mA)		
PC457L0NIP0F		High speed (1 Mb/s), high CMR (15 kV/µs), for flow soldering	0	0	Mini-flat 5-pin	25	3.75	19	16	0.4	4.5	0.2	0.4	1 900	16		
PC457S0NIP0F		High speed (1 Mb/s), high CMR (15 kV/µs), for flow soldering, Solder heat resistance: 270°C	0	0	SOP 8-pin	25	3.75	19	16	0.4	4.5	0.2	0.3	1 900	16		

\*1 Please refer to Specification Sheets for model numbers approved by safety standards.

\*2 Optionally available.







**PHOTOCOUPLERS** 



Notice

Notice In the absence of confirmation by device specification sheets, SHARP takes no responsibility for any defects that may occur in equipment using any SHARP devices shown in catalogs, data books, etc. Except where specially indicated, models listed on this page comply with the RoHS Directive\*. For details, please contact SHARP. \*RoHS Directive: Prohibits use of lead, cadmium, hexavalent chromium, mercury and specific brominated flame retardants (PBBs and PBDEs), with certain exceptions. Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device.

PIC" (Optical IC) is a trademark of SHARP Corporation. An OPIC	consists of a	
t-detecting element and signal-processing circuit integrated onto		

	♦OPIC Output (		IC) is a trademark of SH lement and signal-proces												
	<dip digit<="" th="" type,=""><th>tal output&gt;</th><th></th><th></th><th></th><th>): Approve</th><th>ed</th><th></th><th></th><th></th><th></th><th></th><th></th><th>(Ta = 2</th><th>25°C)</th></dip>	tal output>				): Approve	ed							(Ta = 2	25°C)
-				Appro				olute m ratings		Electro-	optical	charac	teristics	*1	
	Model No.	Internal connection	Features	standards			Forward	Isolation voltage	Lo	w level outp	ut volta	ge		shold ir current	nput
		diagram		UL	VDE *4		Ic	(AC) Viso (rms) (kV)	Vo∟ (V) MAX.	Ta (°C)	IoL (mA)	lF (mA)	IFHL (mA) MAX.	IFLH (mA) MAX.	RL (Ω)
-	PC900V0NSZXF*2, *3		Digital output, normal-off operation	0	0	6-pin DIP	50	5.0	0.4	0 to +70	16	4	2.0	-	280

A: Rated voltage circuit \*1 Each item is measured at Vcc=5V.

♦ OPIC Output ("OP light

Lead forming type is also available for surface mounting. \*2

\*3 Taped package of lead forming type for surface mounting is also available.

\*4 Optionally available.

\*5 Please refer to Specification Sheets for model numbers approved by safety standards.

(6-pin DIP) **OPIC Output** ("OPIC" (Optical IC) is a trademark of SHARP Corporation. An OPIC consists of a light-detecting element and signal-processing circuit integrated onto a single chip. )

<dip 0<="" th="" type,=""><th>Gate drive typ</th><th>)e&gt;</th><th></th><th>C</th><th>: Approved</th><th></th><th></th><th></th><th></th><th></th><th></th><th>(Ta =</th><th>= 25°C)</th></dip>	Gate drive typ	)e>		C	: Approved							(Ta =	= 25°C)
				ved by fety			olute m ratings		Electro	-optical	charact	eristics	
	Internal		stand	ards*3	<b>_</b>	Forward	Isolation		Pro	pagatior	n delay i	time	
Model No.	connection diagram	Features	UL	VDE *2	Package	current IF (mA)	voltage (AC) Viso (rms) (kV)	t₽HL (µs) TYP.	tplн (µs) TYP.	Vcc (V)	lF (mA)	RL1 (Ω)	RL2 (Ω)
PC925LxNSZ0F*1		<ul> <li>Built-in drive circuit directly connectable to MOS-FET and IGBT</li> <li>Peak output current: 2.5 A</li> <li>Low dissipation current (Icc = TYP. 2.5 mA)</li> <li>High resistance to noise (CMR: MIN. 15 kV/µs)</li> </ul>	0	0	8-pin DIP	25	5.0	MAX. 0.5	MAX. 0.5	15 to 30	7 to 16	Rg = 10	-
PC942J00000F▲	Interface Amplifier	For controlling inverter- controlled air-conditioner	0	0		25	5.0	2.0	2.0	6	5	5	10
PC928J00000F	Interface	For driving inverter IGBT, built-in short protection circuit	0	0	14-pin SMT (Half pitch	25	4.0	1.0	1.0	24	10	Rg = 47	-
PC929J00000F		For driving inverter IGBT, high speed, built-in short pro- tection circuit	0	0	lead)	20	4.0	0.3	0.3	24	5	Rg = 47	_

PC900V0NSZXF

\*1 Lead forming type is also available for surface mounting. Taped package of lead forming type for surface mounting is also available.
\*2 A VDE approved type is optionally available.
\*3 Please refer to Specification Sheets for model numbers approved by safety standards. The model marked with ▲ may not be available in the near future. Contact with SHARP for details before use.



RoHS

**PHOTOCOUPLERS** 

## OPTO

### PHOTOTRIAC COUPLER LINEUP

RoHS

Package	Applied voltage	ON-state current (rms)	l	Features	Model No.	Page
lini-flat (SMD)	AC 200 V lines (VDRM = 600V)	0.05 A	General purpose		S2S3000F*3 / S2S5A00F*3 / S2S5FA0F*3	48
- <b>A</b>				Built-in zero-cross circuit	S2S4000F*3	49
IP type	AC 200 V lines (Vdrm = 600V)	0.1 A	General purpose		PC3ST11NSZAX* <sup>3</sup>	48
1-pin)				Built-in zero-cross circuit	PC3ST21NSZBX*2	49
			Reinforced isolation	on	PC3SH11YFZAX*3 / PC3SH13YFZAX*3	48
				Built-in zero-cross circuit	PC3SH21YFZBX*2	49
IP type	AC 100 V lines (VDRM = 400V)	0.1 A	General purpose		PC2SD11NTZAF*3 / PC1S3021NTZF*4	48
6-pin package, ith-pin cut)	AC 200 V lines (VDRM = 600V)	0.1 A	General purpose		PC3SD12NTZAF*3 / PC3SD12NTZBF*2 / PC3SD12NTZCF*1 / PC1S3052YTZF*3 / PC3SD11NTZCF*1 / PC3SD13NTZBF*2	48
				Built-in zero-cross circuit	PC3SD21NTZAF*3 / PC3SD21NTZBF*2 / PC3SD21NTZCF*1 / PC3SD21NTZDF*5 / PC3SD23YTZCF*1 / PC1S3063YTZF*1	49
			Reinforced isolation	on	PC3SF11YVZAF*3 / PC3SF11YVZBF*2 / PC3SF13YVZBF*2	48
				Built-in zero-cross circuit	PC3SF21YVZAF*3 / PC3SF21YVZBF*2 / PC3SF23YVZSF*2	49
	AC 200 V lines (VDRM = 800V)	0.1 A	General purpose		PC4SD11NTZBF*2 / PC4SD11NTZCF*1	48
				Built-in zero-cross circuit	PC4SD21NTZCF*1 / PC4SD21NTZDF*5	49
			Reinforced isolation	on	PC4SF11YVZAF*3 / PC4SF11YVZBF*2	48
				Built-in zero-cross circuit	PC4SF21YVZBF*2 / PC4SF21YVZCF*1 / PC4SF21YWPSF*2	49

#### ■ Phototriac Coupler Lineup

Minimum trigger current: \*1 IFT  $\leq$  5 mA, \*2 IFT  $\leq$  7 mA, \*3 IFT  $\leq$  10 mA, \*4 IFT  $\leq$  15 mA, \*5 IFT  $\leq$  3 mA



### **PHOTOTRIAC COUPLERS**



Phototriac	Couplers		Λ.			proved				(Ta = 25°C)
				oproved y standa			Absolut	te maximum	n ratings	Electro-optica characteristics
Model No.	Internal connection diagram	Features	UL, CSA	VDE	Others	Package	ON-state current I⊤ (rms) (A)	Repetitive peak OFF-state voltage VDRM (V)	Isolation voltage (AC) Viso (rms) (kV)	Min. trigger current IFT (mA) MAX. VD = 6 V, RL = 100Ω
S2S3000F		200 V lines, compact	0	○*6	-					10
S2S5A00F		200 V lines, compact	0	○*6	-	Mini-flat 4-pin	0.05		5.0	10
S2S5FA0F		High impulse noise product	0	○*6	-					10
PC3ST11NSZAX		200 V lines, compact	0	○*6	-			600		10
PC3SH11YFZAX		200 V lines, compact, reinforced isolation	0	0	O*2	4-pin DIP	0.1			10
PC3SH13YFZAX	-	200 V lines, compact, reinforced isolation, high noise resistance	0	0	O*2					10
PC2SD11NTZAF		100 V lines	0	-	-			400		10
PC1S3021NTZF		100 V lines	0	_	O*2			400		10
PC3SD12NTZAF		200 V lines	0	○*6	-	-				10
PC1S3052YTZF		200 V lines	0	○*6	O*2			600		10
PC3SD12NTZBF		200 V lines	0	○*6	-					7
PC3SD13NTZBF		High impulse noise product	0	○*6	-					7
PC3SD12NTZCF		200 V lines	0	○*6	-					5
PC4SD11NTZBF		200 V lines, repetitive peak-OFF-state voltage	0	○*6	-	6-pin DIP* <sup>1, 3</sup>	0.1	800	5.0	7
PC3SD11NTZCF		200 V lines	0	○*6	-			600		5
PC4SD11NTZCF	1	200 V lines, repetitive peak-OFF-state voltage	0	○*6	-	1		800		5
PC3SF11YVZAF	1	200 V lines, reinforced isolation	0	0	O*2	1			1	10
PC3SF11YVZBF	1	200 V lines, reinforced isolation	0	0	O*2	1		600		7
PC3SF13YVZBF	1	200 V lines, reinforced isolation, high noise resistance	0	0	O*2					7
PC4SF11YVZAF	1	200 V lines, reinforced isolation, repetitive peak-OFF-state voltage	0	0	O*2				800	10
PC4SF11YVZBF	1	200 V lines, reinforced isolation, repetitive peak-OFF-state voltage	0	0	O*2	1		800		7

For the notes \*1 to \*6, see next page.



### **PHOTOTRIAC COUPLERS**

### RoHS

(Ta = 25°C)

### ■ Phototriac Couplers

(Built-in zero-cross	circuit type)
----------------------	---------------

•		<b>71</b> /								(10 = 20 0)
			Ap safet	proved y standa	by ards*4		Absolut	e maximum	n ratings	Electro-optical characteristics
Model No.	Internal connection dia- gram	Features	UL, CSA	VDE	Others	Package	ON-state current I⊤ (rms) (A)	Repetitive peak OFF-state VDRM (V)	Isolation voltage (AC) Viso (rms) (kV)	Min. trigger current IFT (mA) MAX. VD = 4 V, RL = 100Ω
S2S4000F	Zero-cross circuit	200 V lines, compact	0	○*6	_	Mini-flat 4-pin	0.05	600	3.75	10* <sup>5</sup>
PC3ST21NSZBX		200 V lines, compact	0	○*6	_	4-pin				7
PC3SH21YFZBX		200 V lines, compact, reinforced isolation	0	0	O*2	DIP	0.1	600	5.0	7
PC3SD21NTZAF		200 V lines, low zero-cross voltage: MAX. 20 V	0	○*6	_					10
PC3SD21NTZBF		200 V lines, low zero-cross voltage: MAX. 20 V	0	○*6	_					7
PC3SD21NTZCF		200 V lines, low zero-cross voltage: MAX. 20 V	0	○*6	_					5
PC1S3063YTZF		100 V lines, low zero-cross voltage: MAX. 20 V	0	○*6	O*2	-		600		5
PC3SD23YTZCF		200 V lines, high pulse/noise resistance (TYP. 2 kV)	0	0	_				5.0	5
PC3SD21NTZDF	7	200 V lines, low zero-cross voltage: MAX. 20 V	0	⊖*6	-		3 0.1			3
PC4SD21NTZCF	Zero-cross circuit	200 V lines, repetitive peak-OFF-state voltage	0	⊖*6	_	6-pin DIP* <sup>1, 3</sup>				5
PC4SD21NTZDF		200 V lines, repetitive peak-OFF-state voltage	0	○*6	-			800		3
PC3SF21YVZAF		200 V lines, reinforced isolation	0	0	O*2					10
PC3SF21YVZBF		200 V lines, reinforced isolation	0	0	O*2			600		7
PC3SF23YVZSF		High impulse noise product	0	0	O*2					7
PC4SF21YVZBF		200 V lines, reinforced isolation, repetitive peak-OFF-state voltage	0	0	O*2	_				7
PC4SF21YVZCF		200 V lines, reinforced isolation, repetitive peak-OFF-state voltage	0	0	○*2			800		5
PC4SF21YWPSF		High impulse noise product	0	0	O*2	6-pin DIP* <sup>3</sup>				7

C: Approved

\*1 Lead forming type fc \*2 In conformance with \*3 These are molded p \*4 Please refer to Spec \*5 VD = 6 V, RL = 100Ω \*6 Optionally available

Lead forming type for surface mounting is also available. In conformance with BSI, SEMKO, DEMKO, and FIMKO These are molded pin No. 5. Please refer to Specification Sheets for model numbers approved by safety standards.  $VD = 6 V, RL = 100\Omega$ 





PC2SD series (PC3SD series, PC4SD series) (6-pin DIP)



PC3SF series (PC4SF series) (6-pin DIP)



PC3ST series (4-pin DIP)



# OPTO

## SOLID STATE RELAY LINEUP

RoHS

Package	Applied voltage	ON-state current (rms)	Features	Model No.	Page
DIP 6-pin	AC 100 V lines	0.15 A	General purpose	PR22MA11NTZF	51
	AC 200 V lines	0.06 A	General purpose	PR31MA11NTZF	51
. 41.		0.15 A	General purpose	PR32MA11NTZF	5
		0.3 A	General purpose	PR33MA series	5
IP 8-pin	AC 100 V lines	0.3/0.6/0.9 A	General purpose	PR23MF11NSZF / PR26MF series / PR29MF series	51
		0.6/0.9 A	Built-in zero-cross circuit	PR26MF21NSZF / PR29MF21NSZF	51
	AC 200 V lines	0.3/0.6/0.9/1.2 A	General purpose	PR33MF5 series / PR39MF5 series / PR36MF5 series / PR3BMF5 series	51
		0.6/0.9/1.2 A	Built-in zero-cross circuit	PR36MF2 series / PR39MF2 series / PR3BMF21NSZF	5
SIP 4-pin	AC 100 V lines	2/8 A 3 to 16 A	General purpose	S102T01F*1 / S108T01F*1 / S101S05F / S102S01F / S112S01F / S116S01F	52
43		2/8 A 3 to 16 A	Built-in zero-cross circuit	S102T02F*1 / S108T02F*1 / S101S06F / S102S02F / S116S02F	52
Low profile		8 A	Built-in snubber circuit	S102S11F	52
		3/8 A	Built-in snubber circuit/ zero-cross circuit	S101S16F / S102S12F	52
R	AC 200 V lines		General purpose	S202T01F*1 / S208T01F*1 / S202S01F / S212S01F / S216S01F	52
24		2/8 A 3 to 16 A	Built-in zero-cross circuit	S202T02F*1 / S208T02F*1 / S201S06F / S202S02F / S216S02F	52/53
		8/8 A	Built-in snubber circuit	S202S15F / S202S11F	53
		8 A	Built-in snubber circuit/ zero-cross circuit	S202S12F	53

#### ■ Solid State Relay Lineup

\*1 Low profile



### SOLID STATE RELAYS

☆New product



■ Solid State Relays

<dip type=""></dip>			A	proved	): Appro		Abaula			(Ta = 25°C) Electrical
				y stand		-	Absolu	te maximum	n ratings	characteristics
Model No.	Internal connection diagram	Features		CSA	VDE*2	Package	ON-state current IT (rms) (A)	Repetitive peak OFF-state voltage VDRM (V)	Isolation voltage (AC) Viso (rms) (kV)	Min. trigger current IFT (mA) MAX. VD = 6 V, RL = 100Ω
PR22MA11NTZF		100 V lines, 150 mA model in a small package	0	0	0		0.15	400		10
PR31MA11NTZF		200 V lines, compact	0	0	0	6-pin	0.06		5.0	10
PR32MA11NTZF		200 V lines, 150 mA model in a small package	0	0	0	DIP	0.15	600	5.0	10
☆PR33MA series		200 V lines, 300 mA model in a small package	0	0	0	1	0.3			15
PR23MF11NSZF		100 V lines, compact	0	0	-		0.3	0.3		10
PR26MF11NSZF		100 V lines, compact	0	0	-	1	0.0			10
PR26MF12NSZF		100 V lines, compact, low input current	0	0	-	1	0.6			5
PR29MF11NSZF		100 V lines, compact	0	0	-			-		10
PR29MF12NSZF	-	100 V lines, compact, low input current	0	0	-		0.9			5
PR33MF51NSLF		200 V lines, compact	0	0	0	_				10
PR33MF52NSLF		200 V lines, compact	0	0	0		0.3			10
PR36MF51NSLF		200 V lines, compact	0	0	0		0.0	- 600		10
PR36MF12NSZF		200 V lines, compact, low input current	0	0	0		0.6			5
PR39MF51NSLF		200 V lines, compact	0	0	0	8-pin	0.9			10
PR39MF12NSZF		200 V lines, compact, low input current	0	0	0	DIP	0.9		4.0	5
PR3BMF51NSLF		200 V lines, compact	0	0	0		1.2			10
PR3BMF52NSZF		200 V lines, compact, low input current	0	0	0		1.2			5
PR26MF21NSZF		100 V lines, compact (built-in zero-cross circuit)	0	0	-		0.6	400		10
PR29MF21NSZF		100 V lines, compact (built-in zero-cross circuit)	0	0	-		0.9	400		10
PR36MF21NSZF		200 V lines, compact (built-in zero- cross circuit)	0	0	0		0.6			10
PR36MF22NSZF	Zero- cross	200 V lines, compact (built-in zero- cross circuit), low input current	0	0	0		0.0			5
PR39MF21NSZF		200 V lines, compact (built-in zero- cross circuit)	0	0	0		0.0	600		10
PR39MF22NSZF		200 V lines, compact (built-in zero- cross circuit), low input current	0	0	0		0.9			5
PR3BMF21NSZF		200 V lines, compact (built-in zero- cross circuit)	0	0	0	]	1.2			10

\*1 Please refer to Specification Sheets for model numbers approved by safety standards.
 \*2 Optionally available.



## OPTO

### SOLID STATE RELAYS

Ø	Ø
Ro	HS

<sip type=""></sip>	(1)			O: A	pproved					(Ta =	= 25°C)
				ved by andards <sup>*6</sup>		Absolut	te maximum	ratings		Electrica racteris	
Model No.	Internal connection	Features			Package	ON-state	Repetitive	Isolation	Min. tr	rigger c	current
Model No.	diagram	reatures	UL	CSA	Раскаде	current I⊤ (rms) (A)	peak OFF-state voltage VDRM(V)	voltage (AC) Viso (rms) (kV)	IFT (mA) MAX.	Vd (V)	Rι (Ω)
S102T01F		100 V lines, low profile	0	0		2			8	12	30
S108T01F		100 V lines, low profile	-	-	Low profile	8* <sup>2</sup>			8	12	30
S102T02F		100 V lines, low profile (built-in zero-cross circuit)	0	0	4-pin SIP	2		3.0	8	12	30
S108T02F	Zero- cross circuit	100 V lines, low profile (built-in zero-cross circuit)	-	-		8* <sup>2</sup>			8	12	30
S101S05F		100 V lines	0	0		3* <sup>3</sup>			15	12	30
S102S01F		100 V lines	0	0		8*2			8	12	30
S112S01F		100 V lines	0	0		12* <sup>4</sup>		4.0	8	12	30
S116S01F		100 V lines	0	0		16* <sup>5</sup>	400		8	12	30
S101S06F		100 V lines (built-in zero-cross circuit)	0	0	4 nin	3* <sup>3</sup>		3.0	15	6	30
S102S02F	Zero-	100 V lines (built-in zero-cross circuit)	0	0	4-pin SIP	8* <sup>2</sup>			8	6	30
S116S02F	circuit	100 V lines (built-in zero-cross circuit)	0	0		16* <sup>5</sup>		4.0	8	6	30
S102S11F		100 V lines (built-in snubber circuit)	0	0		8* <sup>1</sup>			8	12	30
S101S16F		100 V lines (built-in snubber circuit, built-in zero-cross circuit)	0	0		3* <sup>3</sup>		3.0	15	6	30
S102S12F	Zero- cross circuit	100 V lines (built-in snubber circuit, built-in zero-cross circuit)	0	0		8*1		4.0	8	6	30
S202T01F		200 V lines, low profile	0	0		2			8	12	30
S208T01F		200 V lines, low profile	-	_	Low profile	8*2	1	2.2	8	12	30
S202T02F		200 V lines, low profile (built-in zero-cross circuit)	0	0	4-pin SIP	2		3.0	8	12	30
S208T02F	Zero- cross circuit	200 V lines, low profile (built-in zero-cross circuit)	-	-		8* <sup>2</sup>	600		8	12	30
S202S01F		200 V lines	0	0		8* <sup>2</sup>			8	12	30
S212S01F		200 V lines	-	-	4-pin SIP	12* <sup>4</sup>		4.0	8	12	30
S216S01F		200 V lines	_	_		16* <sup>5</sup>	1		8	12	30

For the notes \*1 to \*6, see next page.



### SOLID STATE RELAYS

B	Ø
Ro	HS

<sip type=""></sip>	(2)			O: A	pproved					(Ta =	25°C)
				Approved by safety standards*6		Absolute maximum ratings			Electrical characteristics		
Model No.	Internal connection diagram	Features	UL	CSA	Package	ON-state current I⊤ (rms) (A)	Repetitive peak OFF-state voltage VDRM(V)	Isolation voltage (AC) Viso (rms) (kV)	Min. tr IFT (mA) MAX.	igger c VD (V)	RL (Ω)
S201S06F		200 V lines (built-in zero-cross circuit)	0	0		3* <sup>3</sup>		3.0	15	6	30
S202S02F	Zero-	200 V lines (built-in zero-cross circuit)	0	0		8* <sup>2</sup>		4.0	8	6	30
S216S02F		200 V lines (built-in zero-cross circuit)	-	-		16* <sup>5</sup>			8	6	30
S202S15F		200 V lines (built-in snubber circuit)	-	-	4-pin SIP	8* <sup>2</sup>	600	3.0	15	12	30
S202S11F		200 V lines (built-in snubber circuit)	0	0		8*1			8	12	30
S202S12F	Zero- cross circuit	200 V lines (built-in snubber circuit, built-in zero-cross circuit)	0	0		8*1		4.0	8	6	30

\*1 Tc ≦ 88°C

\*2 Tc ≦ 80°C \*3 Tc ≦ 100°C \*4 Tc ≦ 70°C \*5 Tc ≦ 60°C \*6 Please refer to Specification Sheets for model numbers approved by safety standards.





### PHOTOINTERRUPTER LINEUP

RoHS

#### Photointerrupter Lineup

#### <Transmissive type>

Output type	Package type	Outline	Mounting method	Model No. (series)	Page
Single phototransistor	Compact	High resolution	PWB mounting type	GP1S396HCP0F / GP1S09xHCZ0F / GP1S19xHCZ0F	55
High response speed			Surface-mount type/ Soldering reflow	GP1S396HCPSF / GP1S296HCPSF / GP1S092HCPIF / GP1S19xHCxSF	55
	Case type	High resolution	PWB mounting type, etc.	GP1S5x series	56
De d'in et er		Horizontal slit, High resolution	PWB mounting type	GP1S59J0000F	56
	With connector	General purpose	Snap-in	GP1S173LCS2F / GP1S273LCS1F	56
Darlington phototransistor	Case type	General purpose	PWB mounting type, etc.	GP1L5x series	57
High sensitivity		Wide gap	PWB mounting type	GP1L57J0000F	57
Digital output	Compact	High voltage	PWB mounting type	GP1A98HCZ0F	57
(OPIC output)			Surface-mount type	GP1A98HCPSF	57
	Case type	High resolution	With screw hole/ PWB mounting type	GP1A5x series	58
		Wide gap	PWB mounting type	GP1A57HRJ00F	58
	With connector	General purpose	Screw mounting type/Snap-in	GP1A173LCS3F / GP1A173LCS2F / GP1A173LCSVF / GP1A273LCS1F	59

#### <Reflective type>

Output type	Package type	Outline	Mounting method	Model No. (series)	Page
Single phototransistor	Leadless	Long focal distance	Surface-mount type	GP2S700HCP	59
High response speed	Compact, thin (leadless)	General purpose	Surface-mount type	GP2S60	59
OPIC output	With connector	Light modulation type, Sensitivity adjusted	Screw mounting type/ Compact snap-in/ Inverter light countermeasures	GP2A25 series / GP2A28 series / GP2A200LCS0F / GP2A230LRS0F / GP2A231LRSAF / GP2A230LRSAF / GP2A240LCS0F / GP2A250LCS0F	60

#### <Application-specific photointerrupter lineup>

Detection type	Outline (O	output type etc.)	Mounting method	Model No. (series)	Page
Transmissive type	Case type With encoder function Digital 2 output (phase A/B)	Resolution: 45 LPI Linear scale slit pitch: 0.56 mm	PWB mounting type	GP1A057SGKLF	61
	Resolution: 150 LPI Linear scale slit pitch: 0.17 mm		PWB mounting type	GP1A057RBKLF	61
		Resolution: 180 LPI Linear scale slit pitch: 0.14 mm	With screw hole/ PWB mounting type	GP1A058SCK0F	61
		Resolution: 300 LPI Linear scale slit pitch: 0.0847 mm	With screw hole/ PWB mounting type	GP1A054RDKLF	61
	Case type With encoder function Digital 2 output (Multiplying output)	Resolution for reading: 180 LPI Pitch: 0.14 mm Output resolution: 360 LPI	With screw hole/ PWB mounting type	GP1A101C2KSF	61
	For amusement use		Screw mounting	GP1A204HCS0	61
Reflective type	Injection For prism system (Single	e phototransistor)	Screw mounting	GP2S29SVJ00F	61
	For amusement use (Pa	ichinko ball sensor)	-	GP2A222HCKA	62

### PHOTOINTERRUPTERS (TRANSMISSIVE TYPE)

RoHS

(Ta = 25°C)

#### Photointerrupters

<Transmissive type>

Single Phototransistor Output

#### <Compact type>

			Detecting		Electro-optical characteristics							
	Internal		and	Slit width	Currer	nt transfe	er ratio	F	Respon	se time		
Model No.	connection diagram	Features	emitting gap (mm)	(mm)	CTR (%) MIN.	lF (mA)	Vce (V)	tr (µs) TYP.	Ic (mA)	R∟ (kΩ)	Vce (V)	
GP1S092HCPIF		Wide gap, for soldering reflow, surface mount compatible, with positioning boss $(4.5 \times 2.6 \times 2.9$ [height] mm)	2.0	0.3	2.0	5	5	50	0.1	1	5	
GP1S093HCZ0F		Wide gap ( $4.5 \times 2.6 \times 2.9$ [height] mm)	2.0	0.3	2.0	5	5	50	0.1	1	5	
GP1S094HCZ0F		Wide gap, with positioning pin, $(5.5 \times 2.6 \times 4.8 \text{ [height] mm})$	3.0	0.3	0.8	5	5	50	0.1	1	5	
GP1S096HCZ0F		Narrow gap ( $3.5 \times 2.6 \times 2.9$ [height] mm)	1.0	0.3	2.0	5	5	50	0.1	1	5	
GP1S194HCZ0F		Compact, wide gap, size: $3.6 \times 2.0 \times 2.7$ (height) mm	1.7	0.3	3.0	5	5	50	0.1	1	5	
GP1S195HCZSF GP1S195HCPSF		Compact, wide gap, surface mount compatible, size: $3.4 \times 2.0 \times 2.7$ (height) mm	1.5	0.3	3.0	5	5	50	0.1	1	5	
GP1S196HCZ0F		Compact, low profile $(3.1 \times 2.0 \times 2.7 \text{ [height] mm})$	1.1	0.3	2.0	5	5	50	0.1	1	5	
GP1S196HCZSF GP1S196HCPSF		Surface mount, for soldering reflow, compact, low profile $(3.1 \times 2.0 \times 2.7 \text{ [height] mm})$	1.1	0.3	2.0	5	5	50	0.1	1	5	
GP1S296HCPSF		Surface mount, for soldering reflow, compact, low profile (2.5 × 1.8 × 1.9 [height] mm)	1.0	0.2	3.0	5	5	50	0.1	1	5	
GP1S396HCP0F		Straight lead type, compact, low profile $(2.26 \times 1.4 \times 1.6 \text{ [height] mm})$	1.2	0.12	2.0	5	5	30	0.1	1	5	
GP1S396HCPSF		Surface mount, for soldering reflow, compact, low profile $(2.26 \times 1.4 \times 1.6 \text{ [height] mm})$	1.2	0.12	2.0	5	5	30	0.1	1	5	
GP1S097HCZ0F		High resolution, wide gap, with mounting hole $(4.5 \times 2.6 \times 4.5 \text{ [height] mm})$	2.0	0.3	2.0	5	5	50	0.1	1	5	

\* Topr: -25 to +85°C \*\* GP1SxxxHCZxF: Sleeve package, GP1SxxxHCPxF: Taped package



# OPTC

## PHOTOINTERRUPTERS (TRANSMISSIVE TYPE)

RoHS

(Ta = 25°C)

°C)

			Detecting			Elect	ro-optic	al chara	acterist	ics	
	Internal		and	Slit width	Currer	nt transfe	er ratio	Response time			
Model No.	connection diagram	Features	emitting gap (mm)	(mm)	CTR (%) MIN.	lF (mA)	Vce (V)	tr (µs) TYP.	Ic (mA)	R∟ (Ω)	Vce (V)
GP1S50J0000F		High resolution, both-side mounting type	3.0	0.5	2.5	20	5	3	2	100	2
GP1S51VJ000F		High resolution, side mounting type	3.0	0.5	2.5	20	5	3	2	100	2
GP1S52VJ000F		High resolution, PWB mounting type	3.0	0.5	2.5	20	5	3	2	100	2
GP1S53VJ000F		High resolution, PWB mounting type	5.0	0.5	2.5	20	5	3	2	100	2
GP1S54J0000F		High resolution, with positioning pin, PWB mounting type	3.0	0.5	2.5	20	5	3	2	100	2
GP1S56TJ000F		High resolution, with positioning pin, PWB mounting type	2.0	0.15	2.0	20	5	38	0.5	1 000	2
GP1S58VJ000F		High resolution, with positioning pin, PWB mounting type	5.0	0.5	2.5	20	5	3	2	100	2
GP1S59J0000F		High resolution, horizontal slit, with positioning pin, PWB mounting type	4.2	0.5	2.5	20	5	3	2	100	2



#### <With connector>

			Detecting			Elect	ro-optic	al chara	acterist	ics	
	Model No. Internal diagram		and	Slit width	Currer	nt transfe	er ratio	Response time			
Model No.		Features	emitting gap (mm)	(mm)	CTR (%) MIN.	lF (mA)	Vce (V)	tr (μs) TYP.	Ic (mA)	Rι (Ω)	Vce (V)
GP1S173LCS2F		Snap-in mounting integrated connector type Applicable to 3 kinds of thickness of mounting boards	5.0	0.5	2.5	20	5	3	2	100	2
GP1S273LCS1F		Snap-in mounting integrated connector type Applicable to 3 kinds of thickness of mounting boards Compact (Compatible with 1.5 mm pitch connector)	5.0	0.7	2.5	20	5	3	2	100	2

\* Topr: -25 to +85°C, -30 to +95°C (GP1S173LCS2F, GP1S273LCS1F)



## PHOTOINTERRUPTERS (TRANSMISSIVE TYPE)

#### Darlington Phototransistor Output

<case type=""></case>										(Ta = 2	25°C)
			Detecting			Elect	ro-optic	al chara	acterist	ics	
	Internal		and	Slit width	Currer	nt transfe	er ratio	Response time			
Model No.	connection diagram	Features	emitting gap (mm)	(mm)	CTR (%) MIN.	lF (mA)	Vce (V)	tr (µs) TYP.	Ic (mA)	R∟ (Ω)	Vce (V)
GP1L50J0000F		High sensitivity, both-side mounting type	3.0	0.5	50	1	2	80	2	100	2
GP1L51J0000F		High sensitivity, side mounting type	3.0	0.5	50	1	2	80	2	100	2
GP1L52VJ000F	▲≡<	High sensitivity, PWB mounting type	3.0	0.5	50	1	2	80	2	100	2
GP1L53VJ000F		High sensitivity, PWB mounting type	5.0	0.5	30	1	2	80	2	100	2
GP1L57J0000F		High sensitivity, wide gap, PWB mounting type	10.0	1.8	70	1	2	130	2	100	2
* Topr: -25 to +85°	2	•									







GP1L52VJ000F



GP1L53VJ000F



GP1L57J0000F

RoHS

**OPIC Type** ("OPIC" (Optical IC) is a trademark of SHARP Corporation. An OPIC consists of a light-detecting element and signal-processing circuit integrated onto a single chip. )

#### <Compact type>

<compact th="" ty<=""><th>pe&gt;</th><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th></th><th>(Ta</th><th>= 25°C)</th></compact>	pe>											(Ta	= 25°C)
	Internal		Detecting and	Slit width	Thr	eshold i	Ele nput curi		ical cha	racterist Propag	ics ation de	lay time	
Model No.	connection diagram	Features	emitting gap (mm)	(mm)	IFLH (mA) MAX.	IFHL (mA) MAX.	Vcc (V)	R∟ (kΩ)	tpLн (µs) TYP.	t₽HL (µs) TYP.	lF (mA)	R∟ (kΩ)	Vcc (V)
GP1A98HCZ0F	Voltage regulator Amplifier	Compact, PWB mounting	3.2	0.5	8	-	3.3 to 24	3.9 to 20	2.0	10.0	10	3.9 to 20	3.3 to 24
GP1A98HCPSF		Compact, surface mount	3.2	0.5	8	-	3.3 to 24	3.9 to 20	2.0	10.0	10	3.9 to 20	3.3 to 24





## PIU

## PHOTOINTERRUPTERS (TRANSMISSIVE TYPE)

RoHS

<case type=""></case>											(Ta = 2	25°C)
	latera el		Detecting					· ·	aracterist			
Model No.	Internal connection	Features	and emitting	Slit width		old input c	urrent	F	ropagatio	on delay time		
Model No.	diagram	reatures	gap (mm)	(mm)	Iflн (mA) MAX.	IFHL (mA) MAX.	Vcc (V)	tpLн (µs) TYP.	tрн∟ (µs) TYP.	lF (mA)	RL (Ω)	Vcc (V)
GP1A50HRJ00F		Both-side mounting, with screw hole	3.0	0.5	5	_	5	3	5	5	280	5
GP1A51HRJ00F	-Voltage	Side mounting, with screw hole	3.0	0.5	5	-	5	3	5	5	280	5
GP1A52HRJ00F	Amplifier	PWB mounting type	3.0	0.5	5	-	5	3	5	5	280	5
GP1A53HRJ00F	(When light is cut off:	PWB mounting type	5.0	0.5	8	-	5	3	5	8	280	5
GP1A57HRJ00F	low level)	PWB mounting type, with positioning pin	10.0	1.8	7	_	5	3	5	7	280	5
GP1A58HRJ00F		PWB mounting type, with positioning pin	5.0	0.5	8	-	5	3	5	8	280	5
GP1A52LRJ00F	Voltage regulator Amplifier (When light is cut off: high level)	PWB mounting type	3.0	0.5	_	5	5	5	3	5	280	5



GP1A50HRJ00F



GP1A51HRJ00F

GP1A52LRJ00F (GP1A52HRJ00F)



GP1A53HRJ00F GP1A58HRJ00F with positioning pin



GP1A57HRJ00F

### **PHOTOINTERRUPTERS** (TRANSMISSIVE TYPE)/(REFLECTIVE TYPE)

☆New product



	onnector terr									,	a = 25°
	Internal			Detecting and	Slit width Supply voltage			· · ·	characteris	ristics output voltage	
Model No.	connection diagram		Features	emitting gap (mm)	(mm)		CC V) MAX.	Vol (V) MAX.	Light cut-off	lo∟ (mA)	Vcc (V)
☆GP1A173LCS3F			Snap-in mounting integrated connector type*1	5.0	0.5	2.7	5.5	0.35	No	4	3.3
GP1A173LCS2F	Voltage		Snap-in mounting integrated connector type*1	5.0	0.5	4.5	5.5	0.35	No	4	5
GP1A173LCSVF	regulator Amplifier	connector	Snap-in mounting integrated connector type*1, enforced electrostatic discharge (ESD) type	5.0	0.5	4.5	5.5	0.35	No	4	5
GP1A273LCS1F		with 3-pin	Integrated connector, compatible with 1.5 mm pitch connector, snap-in mounting type*1	5.0	0.7	4.5	5.5	0.35	No	4	5
GP1A75EJ000F▲	Voltage regulator Amplifier	5	Either-side mounting type Screw mounting type	5.0	0.5	4.5	5.5	0.35	Yes	16	5

\* Topr: -20 to +75°C, -30 to +95°C (GP1A173LCS3F, GP1A173LCS2F, GP1A173LCSVF, GP1A273LCS1F) \*1 Applicable to 3 kinds of thickness of mounting boards.

The model marked with A may not be available in the near future. Contact with SHARP for details before use.



#### Photointerrupters

- <Reflective type>
- Single Phototransistor Output

#### <Compact>

			Optimum	Electro-optical characteristics								
Model No.	Internal connection	Features	detecting	Curre	Current transfer ratio			Response time				
WOULD INO.	diagram	i eatures	distance (mm)	CTR (%) MIN.	lF (mA)	VCE (V)	tr (µs) TYP.	Ic (mA)	R∟ (kΩ)	Vce (V)		
GP2S700HCP	* 5	Compact ( $4 \times 3 \times 2$ [height] mm), long focal distance, surface mounting leadless type	4	1.5	4	2	20	0.1	1	2		
GP2S60		Thin (3.2 $\times$ 1.7 $\times$ 1.1 [height] mm), surface mounting leadless type	1	1.0	4	2	20	0.1	1	2		

\* Topr: -25 to +85°C



### PHOTOINTERRUPTERS (REFLECTIVE TYPE)

RoHS

♦ OPIC Output	( "OPIC" (Optical IC) is a trademark of SHARP Corporation. An OPIC consists of a light-detecting element and signal-processing circuit integrated onto a single chip. )
---------------	---

#### <With 3-pin connector terminal>

			o .:		E	Electro-opt	ical charac	teristics	
	Internal		Optimum detecting	Supply	voltage	Dissipation	on current	Low level ou	utput voltage
Model No.	connection diagram	Features	distance (mm)		cc √)   MAX.	Icc (mA) MAX.	Vcc (V)	Vol (V) MAX.	Vcc (V)
GP2A200LCS0F		Multi types of paper detectable, light modulation type, with connector, sensitivity adjusted	5 to 15	4.75	5.25	30* <sup>1</sup>	5	0.4	5
GP2A240LCS0F	- (Following	Applicable to inverter fluorescent lamp, light modulation type, with connector, sensitivity adjusted	5 to 15	4.75	5.25	30* <sup>1</sup>	5	0.4	5
GP2A250LCS0F	diagram [A])	Static electricity resistant, applicable to inverter fluorescent lamp, light modulation type, with connector, sensitivity adjusted	2.5 to 12.5	4.75	5.25	30* <sup>1</sup>	5	0.4	5
GP2A25J0000F		Multi types of paper detectable, light modulation type, with connector, sensitivity adjusted	3 to 7	4.75	5.25	30* <sup>1</sup>	5	0.4	5
GP2A230LRS0F									
GP2A230LRSAF	(Following diagram [B])	Compact, hook type (GP2A231LRSAF), multi types of paper detectable, light modulation type, with connector	3 to 7	4.75	5.25	20* <sup>1</sup>	5	0.4	5
GP2A231LRSAF		with connector							
GP2A25NJJ00F	( <b>F</b>    )	Multi types of paper detectable, light modulation type, sensitivity adjusted, improved light-resistance characteristic for inverter lighting, built-in visible light cut filter	3 to 7	4.75	5.25	30* <sup>1</sup>	5	0.4	5
GP2A25DJ000F	(Following diagram [A])	Multi types of paper detectable, light modulation type, with connector, sensitivity adjusted	3 to 7	4.75	5.25	30* <sup>1</sup>	5	0.4	5
GP2A28AJ000F		Multi types of paper detectable, light modulation type, with connector, sensitivity adjusted, hook type	3 to 7	4.75	5.25	30* <sup>1</sup>	5	0.4	5

The model marked with A may not be available in the near future. Contact with SHARP for details before use.





## **OPTO** PHOTOINTERRUPTERS FOR SPECIFIC APPLICATIONS

#### Photointerrupters for Specific Applications

♦Transmissive Type

#### <Case type, with encoder function>

	Absolute m	naximum ratings			Electro-optical characteristics			
Model No.	Vcc (V)	Topr (°C)	Operating voltage Vcc (V) TYP.	Output signal	Resolution	Response f (kHz) MAX.	frequency	Dissipation current (output side) Icc (mA) MAX.
GP1A057RBKLF	6	-10 to +70	3.3		Linear scale slit pitch 0.17 (mm) (150LPI)	60	20	7
GP1A054RDKLF	6	-10 to +70	3.3	Digital 2 output	Linear scale slit pitch 0.0847 (mm) (300LPI)	60	20	5.5
GP1A057SGKLF	6	-10 to +70	3.3	(Phase A/B)	Linear scale slit pitch 0.56 (mm) (45LPI)	25	20	5.5
GP1A058SCK0F	6	-10 to +70	3.3		Linear scale slit pitch 0.14 (mm) (180LPI)	60	20	5.5
GP1A101C2KSF	6.5	-10 to +70	3.3	Digital 2 output (Multiplying output)	Resolution for reading: 180 LPI (Pitch: 0.14 mm) Output resolution: 360 LPI	120	20	20

\* High precision read and low affection of angle error from vibration thanks to the multi-segment PD system. Duty ratio: 50±15%, phase difference: 90±45°







GP1A058SCK0F



RoHS

(Ta = 25°C)

GP1A101C2KSF

#### <For amusement use>

			Detection		Electro-optical characteristics						
Model No.	Internal connection	Features	Detecting and emitting gap	Slit width (mm)	Operating voltage Vcc (V)		Low level output voltage			age	
	diagram		(mm)		MIN.	MAX.	Vol (V) MAX.	Light cut-off	lo∟ (mA)	Vcc (V)	
GP1A204HCS0	Voltage regulator	Connector with lock, screw mounting type, high resistant to noise	4.0	0.5	10.8	24	0.4	Yes	5	10.8 to 24	



#### ♦Reflective Type <Case type, phototransistor output>

(Ta = 25°C)

(Ta = 0 to +40°C)

			Electro-optical characteristics								
Model No.	Internal connection	Features	Pea	k photocur	rrent	Response time					
Model No.	diagram	r catores	ICP (mA)	IF (mA)	VCE (V)	tr (µs) TYP.	Ic (mA)	R∟ (kΩ)	VCE (V)		
GP2S29SVJ00F	*	Long focal distance (with prism system*1), compact, screw mounting type	0.4 to 3.0 <sup>*1</sup>	20	5	38	0.5	1	2		

\* Topr: -25 to +85°C

\*1 Space between prism and sensor is 8 mm.







### **PHOTOINTERRUPTERS FOR SPECIFIC APPLICATIONS / PROXIMITY SENSOR**

RoHS

(Ta = 25°C)

 $(T_2 - 25^{\circ}C)$ 

#### <For amusement use>

		Electro-optical characteristics					
Model No.	Features	Supply voltage Vcc (V)	Dissipation current Icc (mA)	Response frequency f (Hz)			
GP2A222HCKA	Employs reflective type, pinball detector, connector with lock In conjunction with an IC, detects beam interruption*1	4.5 to 16.5	MAX. 12	MAX. 500			

\*1 Used together with interface IC for control (IR3N184)



#### ■ Proximity Sensor

		Absolute max	ximum ratings	Electro-optical characteristics				
Model No.	Features	Vcc (V)	Topr (°C)	Dissipation current Icc (μΑ) TYP.	Detecting distance Lon (mm) MIN.	Non- detecting distance Loff (mm) MAX.	Peak emission wavelength λp (nm)	
GP2AP002S00F	Compact size $(4.0 \times 2.0 \times 1.25 \text{ tmm})$ Drastically reduced LED current consumption by employing a light modulation system Built-in LEDs for simple optical design and I <sup>2</sup> C output	3.8	-25 to +85	240	25	150	940	

### PROXIMITY SENSOR WITH INTEGRATED AMBIENT LIGHT SENSOR

☆New product

RoHS

(Ta = 25°C)

#### Proximity Sensor with Integrated Ambient Light Sensor

Absolute maxi-Electro-optical characteristics mum ratings Proximity sensor portion Ambient light sensor portion Output current Non-Recom-Dissipation Detecting Peak Peak Model No. Features detecting mended Topr (°C) Vcc current sensitivity distance emission distance luminance Icc (µA) TYP. **lo**1 lo2 (V) wavelength Lon wavelength (µA) TYP. Loff range (µA) MAX. (mm) λp (nm) λp (mm) Ev (lx) ÌMIN. (nm) MAX. MIN. LED and ambient light sensor combined in a single package  $(5.6 \times 2.1 \times 1.25 \text{ tmm})$ Drastically reduced LED current consumption by 30 1 employing a light modulation -25 to 3 to GP2AP002A00F▲ 270 940 555 (at Ev = (at Ev = 3.8 25 150 +85 55 000 system 1 000 lx) 0 lx) Built-in LEDs for simple optical design Proximity sensor: I<sup>2</sup>C output Ambient light sensor: logarithmic current output

The model marked with ▲ may not be available in the near future. Contact with SHARP for details before use.

									(Ta = 25°C)	
		Absolut mum	e maxi- atings	Electro-optical characteristics						
					Proximity se	ensor portion	Ambier	it light sensor	portion	
Model No.	Features	Vcc (V)	Topr (°C)	Dissipation current lcc (µA) TYP.	Detecting distance Lon (mm) TYP.	Peak emission wavelength λp (nm)	Recom- mended illuminance range Ev (lx)	Output resolution (bit)	ADC conversion time Tint (ms) TYP.	
☆GP2AP030A00F	LED and ambient light sensor combined in a single package (4.0 × 2.1 × 1.25 t mm) Built-in LEDs for simple optical design Illuminance output: digital 16-bit output (Minimum detectable illuminance: 0.02 lx) I <sup>2</sup> C output compatible (proximity sensor, ambient light sensor)	5.5	-35 to +85	65	100	940	0.02 to 10 000	16	100	



### **PROXIMITY/GESTURE SENSOR WITH** INTEGRATED AMBIENT LIGHT SENSOR

☆New product

RoHS

(Ta = 25°C)

#### ■ Proximity/Gesture Sensor with Integrated Ambient Light Sensor

		Absolute maxi- mum ratings		Electro-optical characteristics							
	Features			Dissipa- tion current Icc (µA) TYP.	Dissipa-		//gesture portion	Ambient light sensor portion			
Model No.		Vcc (V)	Topr (°C)		tion current Icc (Gesture) (μΑ) TYP.	Detecting distance Lon (mm) TYP.	Peak emission wavelength λp (nm)	Recom- mended illuminance range Ev (lx)	Output resolution (bit)	ADC conversion time Tint (ms) TYP.	
☆GP2AP052A00F	LED and ambient light sensor combined in a single package (5.6 × 2.1 × 1.25 t mm) Built-in LEDs for simple optical design Illuminance output: digital 16-bit output (Minimum detectable illuminance: 0.02 lx) I <sup>2</sup> C output compatible Gesture recognition: directional hand movements detected without touching the screen	5.5	-35 to +85	65	200	100	940	0.02 to 10 000	16	100	



### **AMBIENT LIGHT SENSORS**

#### ■ Ambient Light Sensors

OP1

	t Light Sensors		Abaabata				<b>F</b> laster		t!- t!	(la:	= 25°C)
			Absolute	e maximu	m ratings		Electro- Recommended	optical char	Peak	Output	current
Model No.	Туре	Package	Vcc (V)	lo (mA)	Topr (°C)	supply voltage Vcc (V)	illuminance range Ev (Ix)	current Icc (µA) TYP	sensitivity wavelength λp (nm)	Ak         Output cu           ivity         Io1           ingth         (µA)           5         480           5         (at Ev = 1000 kx)           5         480           65         (at Ev = 1000 kx)           5         (at Ev = 1000 kx)           5         (at Ev = 1000 kx)           5         20           65         (at Ev = 1000 kx)           5         20           65         (at Ev = 1000 kx)           5         20           65         (at Ev = 1000 kx)           65         (at Ev = 1000 kx)           65         (at Ev = 1000 kx)	lo2 (μΑ) TYP.
GA1A2S100SS	Built-in amplification circuit Peak sensitivity characteristic close to human visual sensitivity Output characteristic: Linear current output for illuminance Lead frame (straight) type	Transparent epoxy resin	7.0	5	-40 to +85	2.7 to 3.6	10 to 10 000	500	555	(at Ev =	48 (at Ev = 100 lx)
GA1A2S100LY	Built-in amplification circuit Peak sensitivity characteristic close to human visual sensitivity Output characteristic: Linear current output for illuminance Lead frame (L bend) type	$(3 \times 4 \text{ mm})$	7.0	5	-40 to +85	2.7 to 3.6	10 to 10 000	500	555	5 (at Ev = 1 000 lx)	48 (at Ev = 100 lx)
GA1A1S202WP	Built-in amplification circuit Peak sensitivity characteristic close to human visual sensitivity Output characteristic: Logarithmic current output for illuminance	$\begin{array}{l} \text{Compact SMD} \\ (2.0 \times 1.6 \\ \times 0.6 \text{ mm}) \\ \text{Leadless} \end{array}$	7.0	1	-40 to +85	2.3 to 3.2	3 to 55 000	70	555	(at Ev =	30 (at Ev = 1 000 lx)
GA1A1S203WP▲	Built-in amplification circuit Peak sensitivity characteristic close to human visual sensitivity Output characteristic: Logarithmic current output for illuminance Thin type	Compact SMD ( $2.0 \times 1.6 \times 0.42$ mm) Leadless	7.0	1	-40 to +85	2.3 to 3.2	3 to 55 000	70	555	(at Ev =	30 (at Ev = 1 000 lx)
GA1A1S204WP	Built-in amplification circuit Peak sensitivity characteristic close to human visual sensitivity Output characteristic: Logarithmic current output for illuminance Back-mount-available type	Compact SMD ( $3.3 \times 2.0$ $\times 0.6$ mm) Back-mount available, leadless	7.0	1	-40 to +85	2.3 to 3.2	3 to 55 000	70	555	(at Ev =	30 (at Ev = 1 000 lx)
GA1A1S100WP	Built-in amplification circuit Peak sensitivity characteristic close to human visual sensitivity Output characteristic: Linear current output for illuminance	$\begin{array}{l} \text{Compact SMD} \\ (2.0 \times 1.6 \\ \times 0.6 \text{ mm}) \\ \text{Leadless} \end{array}$	7.0	10	-40 to +85	2.7 to 3.6	10 to 5 000	1 460	555	1 420 (at Ev = 1 000 lx)	142 (at Ev = 100 lx)

The model marked with ▲ may not be available in the near future. Contact with SHARP for details before use.

GA1A2S100SS

GA1A2S100LY

GA1A1S202WP (GA1A1S100WP)

GA1A1S203WP▲

GA1A1S204WP



### **OPIC LIGHT DETECTORS**



														RoHS
OPIC Light Detectors ("OPIC" (Optical IC) is a trademark of SHARP Corporation. An OPIC consists of a light-detecting element and signal-processing circuit integrated onto a single chip.) (Ta =													= 25°C)	
			Absolute maximum ratings				Electro-optical characteristics							
Model No.	Type	Type Package V <sub>CC</sub> (V)	Vice	Р	P lo	Topr	EVLH	EVHL		<b>t</b> PLH	<b>t</b> PHL			
inicuor rio.	Туре		(mW) (mA)	(°C)	(lx) MAX.	(lx) MAX.	Vcc (V)	(µs) TYP.	(µs) TYP.	Vcc (V)	E∨ (Ix)	RL (Ω)		
IS485E	Built-in schmidt trigger	Transparent	-0.5 to +17	175	50	-25 to +85	-	35	5	5	3	5	50	280
IS486E	circuit, amplifier and voltage regulator	epoxy resin with condenser (lens)	-0.5 to +17	175	50	-25 to +85	35	-	5	3	5	5	50	280



#### <Low-voltage operation>

Absolute maximum ratings Electro-optical characteristics Operating EVLH EVHL **t**PHL **t**PLH Model No Туре Package Ρ 10 Topr supply voltage (V) (Ix) MAX. (Ix)Vcc (µs) (µs) Vcc Εv Rı (mW) (mA) (°C) MAX (V) TYP. Τ̈́Ύ́Ρ. (V) (Ix)(Ω) Transparent Built-in Schmidt trigger IS489E 80 2 -25 to +85 3 000 epoxy resin with 1.4 to 7.0 \_ 15 3 1.3 8.5 3 125 circuit and amplifier condenser (lens)



#### <Model employing a light modulation system>

Absolute maximum ratings Electro-optical characteristics\*2 External disturbing light **t**PLH **t**PHL Vol Vон Model No. Туре Package Vcc Ρ lo Topr illuminance (V) MAX. (V) (µs) (µs) Vcc R∟ (V) (mW) (mA) (°Ċ) EVDX(IX) TYP. ΜÌŃ. (Ω) ΤΥΡ. ΫΎΡ. (V) Built-in pulse driver circuit at the emitter Visible light side, synchronous IS471FE\*1, \*3 7 000 cut-off epoxy -0.5 to +16 250 50 -25 to +60 0.35 4.97 400 400 5 280 detector circuit. resin amplifier circuit and demodulator circuit

\*1 IS471FE is less susceptible to disturbing effects thanks to the light modulation system

\*2 Vcc = 5 V

\*3 Straight lead type (IS471FSE) is also available.



Notice Notice In the absence of confirmation by device specification sheets, SHARP takes no responsibility for any defects that may occur in equipment using any SHARP devices shown in catalogs, data books, etc. Except where specially indicated, models listed on this page comply with the RoHS Directive\*. For details, please contact SHARP. \*RoHS Directive: Prohibits use of lead, cadmium, hexavalent chromium, mercury and specific brominated flame retardants (PBBs and PBDEs), with certain exceptions. Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device.

6	6
U	U

#### (Ta = 25°C)

(Ta = 25°C)



## **OPIC LIGHT DETECTORS**

RoHS

(Ta = 25°C)

#### <For laser beam printers (laser beam origin detection)>

			Electro-optical characteristics							
Madal Na	Tura	Daskasa	Recommended supply	Vон	Vol	$H \rightarrow L$ delay time variation				
Model No.	Туре	Package	voltage Vcc (V)	(V) MIN.	(V) MAX.	∆tphL (ns) MAX.				
GA220T2L2IZ▲	2-PD, differential type	Transparent epoxy resin 18-pin	4.5 to 5.5	4.9	0.6	±8.5				

The model marked with A may not be available in the near future. Contact with SHARP for details before use.





### **PHOTOTRANSISTOR LINEUP / PHOTOTRANSISTORS**

RoHS

#### ■ Phototransistor Lineup

			Half	Mod	el No.
Package	Output type	Features	sensitivity angle	Standard	Visible light cut-off
Epoxy resin with lens	Single phototransistor	General purpose/Narrow acceptance	±13°	PT480E00000F	PT480FE0000F
		Compact, thin	±35°	PT4800E0000F	PT4800FE000F / PT4850FE000F
	Darlington phototransistor	High sensitivity/Narrow acceptance	±13°	PT481E00000F	PT481FE0000F
		High sensitivity/Narrow acceptance/Long lead	±13°	_	PT483F1E000F▲
		High sensitivity/Intermediate acceptance	±40°	_	PT491FE0000F
Surface mounting leadless type	Single phototransistor	Compact (side view/top view mounting possible)	±15°	PT100MC0MP	PT100MF0MP
	Darlington phototransistor	Compact (side view/top view mounting possible)	±15°	_	PT100MF1MP

#### Phototransistors

Ð			Absolu	ute maxin	num ratings		Ic (I	mA)		ICEO	(A)	Δθ	λρ
Type	Model No.	Package	Vceo (V)	Pc (mW)	Topr (°C)	MIN.	MAX.	VCE (V)	Ee (mW/cm <sup>2</sup> )	MAX.	Vce (V)	(°) TYP.	(nm) TYP.
	PT100MC0MP	Surface mounting	35	75	-30 to +85	1.7	5.1	5	1	1×10 <sup>-7</sup>	20	±15	900
	PT100MF0MP*1	leadless type with lens	35	75	-30 to +85	1.15	3.45	5	1	1×10 <sup>-7</sup>	20	±15	910
	PT480E00000F		35	75	-25 to +85	0.4	TYP. 1.7	5	1	1×10 <sup>-7</sup>	20	±13	800
Single	PT480FE0000F*1		35	75	-25 to +85	0.25	TYP. 0.8	5	1	1×10 <sup>-7</sup>	20	±13	860
0,	PT4800E0000F	Epoxy resin with lens	35	75	-25 to +85	0.12	TYP. 0.4	5	1	1×10 <sup>-7</sup>	20	±35	800
	PT4800FE000F*1		35	75	-25 to +85	0.08	TYP. 0.25	5	1	1×10 <sup>-7</sup>	20	±35	860
	PT4850FE000F*1		35	75	-25 to +85	0.12	0.56	5	1	1×10 <sup>-7</sup>	20	±35	860
	PT481E00000F		35	75	-25 to +85	1.5	25	2	0.1	1×10 <sup>-6</sup>	10	±13	800
R	PT481FE0000F*1		35	75	-25 to +85	0.9	27	2	0.1	1×10 <sup>-6</sup>	10	±13	860
Darlington	PT483F1E000F*1▲	Epoxy resin with lens	35	75	-25 to +85	1.5	4.0	2	0.1	1×10 <sup>-6</sup>	10	±13	860
Dar	PT491FE0000F*1	;	35	75	-25 to +85	0.2	0.8	2	Ev, 2 lx	1×10 <sup>-6</sup>	10	±40	860
	PT100MF1MP*1	Surface mounting leadless type with lens	35	75	-30 to +85	0.2	1.2	5	0.01	1×10 <sup>-6</sup>	10	±15	860

\*1 Visible light cut-off type

The model marked with A may not be available in the near future. Contact with SHARP for details before use.





RoHS

#### ■ PIN Photodiodes

■ PIN Photodiodes (Ta = 2												= 25°C)
Model No.	Features	Package (Material)	Active area (mm <sup>2</sup> )	Topr (°C)	lsc (μΑ) MIN.	Ev (lx)	ld (A) MAX.	Vr (V)	tr, tf (µs) TYP.	Vr (V)	RL (kΩ)	λp (nm) TYP.
PD410PI2E00F		Visible light cut-off epoxy resin with condenser (lens)	3.31	-25 to +85	2.5	100	1 × 10 <sup>-8</sup>	10	0.2	10	1	1 000
PD411PI2E00F	PIN type	Transparent epoxy resin with condenser (lens)	3.31	-25 to +85	5.0	100	1 × 10 <sup>-8</sup>	10	0.2	10	1	960
PD412PI2E00F		Transparent epoxy resin with condenser (lens)	3.31	-25 to +85	3.5	100	1 × 10 <sup>-8</sup>	10	0.25	10	1	800
PD413PI2E00F	PIN type IrDA1.0	Visible light cut-off epoxy resin with condenser (lens)	3.31	-25 to +85	MIN. 4.5 (TYP. 5.4)	100	1 × 10 <sup>-8</sup>	10	0.2	10	1	960
PD100MC0MP	Surface mounting leadless type	Transparent epoxy resin board with lens	-	-30 to +85	0.6	100	1 × 10 <sup>-8</sup>	10	0.01	15	0.18	820
PD100MF0MP	Surface mounting leadless type	Visible light cut-off epoxy resin board with lens	-	-30 to +85	0.4	100	1×10 <sup>-8</sup>	10	0.01	15	0.18	850

PD410PI2E00F (PD411PI2E00F: transparent; PD412PI2E00F: transparent, PD413PI2E00F



PD100MC0MP (PD100MF0MP: black)

**Optoelectronics** 



### INFRARED EMITTING DIODE LINEUP / INFRARED EMITTING DIODES

RoHS

#### ■ Infrared Emitting Diode Lineup

Туре	Package	Featu	Half intensity angle	Model No.	
Single-end lead	Epoxy resin with lens	General purpose/Narrow bean	n angle	±13°	GL480E00000F
(Side view type)	_p., )				
		Compact and thin		±30°	GL4800E0000F
Surface mount type	Epoxy resin with lens/ leadless	Compact/Narrow beam angle		±10°	GL100MN0MP
	(Mountable for Top view/ Side view type)				
			High output type	±10°	GL100MN1MP
		Compact/Wide beam angle		±80°	GL100MD1MP1

Infrared I	Emitting Diodes											(Ta	= 25°C)
		At	solute	maximu	m ratings	Radia	nt flux Φe	e (mW)	VF (V)		Δθ	λρ	
Model No.	Package, features	l⊧ (mA)	Vr (V)	P (mW)	Topr (°C)	MIN.	TYP.	IF (mA)	TYP.	MAX.	IF (mA)	(°) TYP.	(nm) TYP
GL480E00000F	Epoxy resin with lens	50	6	75	-25 to +85	0.7	-	20	1.2	1.4	20	±13	950
GL4800E0000F	Epoxy resin with lens	50	6	75	-25 to +85	0.7	1.6	20	1.2	1.4	20	±30	950
GL100MN0MP	Surface mounting leadless type, epoxy resin board with lens	50	6	75	-30 to +85	1.0	3.0 (MAX.)	20	1.2	1.4	20	±10	940
GL100MN1MP	Surface mounting leadless type, epoxy resin board with lens, high output type	50	6	75	-30 to +85	2.0	6.0 (MAX.)	20	1.2	1.5	20	±10	940
GL100MD1MP1	Surface mounting leadless type, epoxy resin board with lens, wide beam angle	50	6	75	-30 to +85	_	6.0 (MAX.)	20	_	1.5	20	±80	940



### **OPTICAL-ELECTRIC SENSOR LINEUP**

RoHS

#### ■ Distance Measuring Sensor Lineup

Output	Detected distance		Features	Model No.
1-bit digital output according to distance measuring	1.5 cm	Battery drive compatible, c	ompact, 1-bit digital output	
			Capable of operation at high temperature (-30 to +105°C)	GP2Y5D91S00F
	5 cm	Battery drive compatible, c	ompact, 1-bit digital output	GP2Y0D805Z0F
	10 cm	Battery drive compatible, c	ompact, 1-bit digital output	GP2Y0D810Z0F
			Wide operating temperature type (-40 to +85°C)	GP2Y0D810Z1F
	15 cm	Battery drive compatible, c	ompact, 1-bit digital output	GP2Y0D815Z0F
	13 cm	1-bit digital output		GP2Y0D413K0F
	24 cm	1-bit digital output		GP2Y0D21YK0F
	80 cm	1-bit digital output		GP2Y0D02YK0F

Output	Range of distance measuring		Features	Model No.
Analog voltage output according to distance measuring				
(Including I <sup>2</sup> C output)	1.5 to 15 cm		Analog output	GP2Y0AF15 series
	2 to 15 cm		Analog output	GP2Y0A51SK0F
	4 to 30 cm		Analog output	GP2Y0A41SK0F / GP2Y0AF30 series
	4 to 50 cm	CMOS type	Analog output	GP2Y0E02A
			I <sup>2</sup> C output	GP2Y0E02B
			Analog, I <sup>2</sup> C output	GP2Y0E03
	10 to 80 cm		Analog output	GP2Y0A21YK0F
	10 to 150 cm		Compact ( $22 \times 8 \times 7.2$ [T] mm), Analog output	GP2Y0A60SZ0F / GP2Y0A60SZLF
	20 to 150 cm		Analog output	GP2Y0A02YK0F
	100 to 550 cm		Analog output	GP2Y0A710K0F

### ■ High-Precision Displacement Sensor

Output	Range of distance measuring	Features	Model No.
Voltage output according to distance measuring	4.5 to 6.0 mm	Resolution: 50 µm	GP2Y0AH01K0F

#### ■ Dust Sensor Unit Lineup

Output	Features	Model No.
	Pulse analog output, single-shot detection of house dust,	
Analog output	general purpose	GP2Y1010AU0F

### **DISTANCE MEASURING SENSORS**

### RoHS

#### ■ Distance Measuring Sensors (1)

#### ♦Digital Output

			Absolute ma:	ximum ratings	Electro-optical characteristics*1				
Model No.	Detected distance (cm)	Features	Vcc Topr (V) (°C)		VOH VOL (V) (V) MIN. MAX.		Dissipation Operating	n current Standby	
GP2Y5D91S00F	1.5	Light detector, infrared LED and signal processing circuit, short distance measuring type, battery drive compatible (operating power supply: 2.7 to 6.2 V), capable of operation at high temperature	-0.3 to +7	-30 to +105	Vcc –0.6	0.6	(mA)	(µA) _	
GP2Y0D805Z0F	5	Light detector, infrared LED and signal processing circuit, short distance measuring type, battery drive compatible (operating power supply: 2.7 to 6.2 V)	-0.3 to +7	-10 to +60	Vcc -0.6	0.6	MAX. 6.5	MAX. 8	
GP2Y0D810Z0F	10	Light detector, infrared LED and signal processing circuit, short distance measuring type, battery drive compatible (operating power supply: 2.7 to 6.2 V)	-0.3 to +7	-10 to +60	Vcc –0.6	0.6	MAX. 6.5	MAX. 8	
GP2Y0D810Z1F	10	Light detector, infrared LED and signal processing circuit, short distance measuring type, battery drive compatible (operating power supply: 2.7 to 6.2 V), wide operating temperature type	-0.3 to +7	-40 to +85	Vcc –0.6	0.6	TYP. 5	MAX. 8	
GP2Y0D815Z0F	15	Light detector, infrared LED and signal processing circuit, short distance measuring type, battery drive compatible (operating power supply: 2.7 to 6.2 V)	-0.3 to +7	-10 to +60	Vcc –0.6	0.6	MAX. 6.5	MAX. 8	
GP2Y0D413K0F	13	Distance measuring sensor united with PSD*, infrared LED and signal processing circuit, digital voltage output according to the measured distance	-0.3 to +7	-10 to +60	Vcc -0.3	0.6	_	_	
GP2Y0D21YK0F	24	Distance measuring sensor united with PSD*, infrared LED and signal processing circuit, digital voltage output according to the measured distance	-0.3 to +7	-10 to +60	Vcc -0.3	0.6	MAX. 40	-	
GP2Y0D02YK0F	80	Distance measuring sensor united with PSD*, infrared LED and signal processing circuit, long distance measuring type (No external control signal required), digital voltage output according to the measured distance	-0.3 to +7	-10 to +60	Vcc –0.3	0.6	MAX. 50	_	

#### \*1 Vcc = 5 V

\* PSD: Position Sensitive Detector

### **DISTANCE MEASURING SENSORS**

☆New product ★Under development RoHS

(Ta = 25°C)

#### ■ Distance Measuring Sensors (2) Analog Output (Including I<sup>2</sup>C output)

			Absolute max	kimum ratings	Electro-o	optical characte	eristics*1
Model No.	Distance measuring range (cm)	Features	Vcc (V)	Topr (°C)	Voн (V) MIN.	Vol (V) MAX.	Dissipation current Operating
★GP2Y0AF15 series	1.5 to 15	Distance measuring sensor united with PSD*, infrared LED and signal processing circuit, short measuring cycle (16.5 ms), compact, lineup of various connector shapes	-0.3 to +7	-10 to +60	(at L = ∆Vo (TYF	1) = 0.4 V 15 cm), P.) = 2.3 V m → 1.5 cm)	(mA) TYP. 17
GP2Y0A51SK0F	2 to 15	Distance measuring sensor united with PSD*, infrared LED and signal processing circuit, short measuring cycle (16.5 ms)	-0.3 to +7	-10 to +60	(at L = ∆Vo (TYP	() = 0.4 V 15 cm), () = 2.25 V cm $\rightarrow 2$ cm)	TYP. 12
★GP2Y0AF30 series	4 to 30	Distance measuring sensor united with PSD*, infrared LED and signal processing circuit, short measuring cycle (16.5 ms), compact, lineup of various connector shapes	-0.3 to +7	-10 to +60	(at L = ∆Vo (TYF	() = 0.4 V 30 cm), (P) = 2.3 V cm $\rightarrow 4$ cm)	TYP. 17
GP2Y0A41SK0F	4 to 30	Distance measuring sensor united with PSD*, infrared LED and signal processing circuit, short measuring cycle (16.5 ms)	-0.3 to +7	-10 to +60	(at L = ∆Vo (TYP	(1) = 0.4 V 30 cm), (2) = 2.25 V cm $\rightarrow 4$ cm)	MAX. 22
☆GP2Y0E02A	4 to 50	Infrared LED and CMOS image sensor with built-in signal processing circuit, compact size (18.9 $\times$ 8 $\times$ 5.2 mm), high-precision measurement, analog output	-0.3 to +3.6	-10 to +60	Vout (A) 1 = 0.3 to 0.8 V (at L = 50 cm), Vout (A) 3 = 2.1 to 2.3 V (at L = 4 cm)		MAX. 36
☆GP2Y0E02B	4 to 50	Infrared LED and CMOS image sensor with built-in signal processing circuit, compact size (18.9 $\times$ 8 $\times$ 5.2 mm), high-precision measurement, I <sup>2</sup> C output	-0.3 to +3.6	-10 to +60	D1 = 45 to 50 cm (at L = 50 cm), D3 = 3 to 5 cm (at L = 4 cm)		MAX. 36
☆GP2Y0E03	4 to 50	Infrared LED and CMOS image sensor with built-in signal processing circuit, compact size (16.7 $\times$ 11 $\times$ 5.2 mm), high-precision measurement, analog / I <sup>2</sup> C output both compatible	-0.3 to +5.5	-10 to +60	Vout (A) $1 = 0.3$ to 0.8 V, D1 = 45 to 50 cm (at L = 50 cm), Vout (A) $3 = 2.1$ to 2.3 V, D3 = 3 to 5 cm (at L = 4 cm)		MAX. 36
GP2Y0A21YK0F	10 to 80	Distance measuring sensor united with PSD*, infrared LED and signal processing circuit, linear voltage output	-0.3 to +7	-10 to +60	(at L = ∆Vo (TYF	) = 0.4 V 80 cm), P.) = 1.9 V n → 10 cm)	MAX. 40
*2 GP2Y0A60SZ0F/ GP2Y0A60SZLF	10 to 150	Distance measuring sensor united with PSD*, infrared LED and signal processing circuit, compact type (22 x 8 x 7.2 mm), long distance measuring type (No external control signal required)	-0.3 to +5.5	-10 to +60	Vo (TYP.) = 0.65 V *3 (at L = 150 cm), $\Delta$ Vo (TYP.) = 3.0 V (at L = 150 cm → 20 cm)		MAX. 50
GP2Y0A02YK0F	20 to 150	Distance measuring sensor united with PSD*, infrared LED and signal processing circuit, long distance measuring type (No external control signal required)	-0.3 to +7	-10 to +60	(at L = 1 ∆Vo (TYP	(1) = 0.4 V (50  cm), (2) = 2.05 V $(2) \text{ cm} \rightarrow 20 \text{ cm})$	MAX. 50
GP2Y0A710K0F	100 to 550	Distance measuring sensor united with PSD*, infrared LED and signal processing circuit, long distance measuring type (No external control signal required)	-0.3 to +7	-10 to +60	(at L = 1 ∆Vo (TYF	P(t) = 2.5 V P(t) = 0.7 V	TYP. 30

\*1 Vcc = 5 V

<sup>1</sup> VC = 3 V 2 GP2Y0A60SZ0F: Surface mount type GP2Y0A60SZLF: Board insertion type \*3 When Vcc = 3 V: Vo (TYP.) = 0.35 V (at L = 150 cm); ΔVo (TYP.) = 1.6 V (at L = 150 cm → 20 cm)

\* PSD: Position Sensitive Detector



### **DISTANCE MEASURING SENSORS / HIGH-PRECISION DISPLACEMENT SENSOR / DUST SENSOR UNIT**



(Ta = 25°C)

(Ta = 25°C)



#### High-Precision Displacement Sensor

Model No.	Features	Topr (°C)	Operating supply voltage (V)	Dissipation current (mA)	Distance measuring range (mm)	Distance characteristic of output
GP2Y0AH01K0F	Resolution: 50 µm	-10 to +60	4.5 to 5.5	TYP. 20	4.5 to 6.0	TYP. 1.70 V Variation in output over range (4.5 to 6.0 mm)



#### Dust Sensor Unit

Electro-optical characteristics Topr (°C) Operating Dissipation Detection Output voltage Output voltage Model No. Features supply voltage current sensitivity at no dust range (V) Voc (V) (mA) V/(0.1 mg/m<sup>3</sup>) VOH (V) Built-in infrared emitting diode, GP2Y1010AU0F photodiode and signal processing circuit, -10 to +65 4.5 to 5.5 TYP. 11 TYP. 0.5 TYP. 0.9 MIN. 3.4 compact, single-shot detection of house dust



Notice

Nonce In the absence of confirmation by device specification sheets, SHARP takes no responsibility for any defects that may occur in equipment using any SHARP devices shown in catalogs, data books, etc. Except where specially indicated, models listed on this page comply with the RoHS Directive\*. For details, please contact SHARP. "RoHS Directive: Prohibits use of lead, cadmium, hexavalent chromium, mercury and specific brominated flame retardants (PBBs and PBDEs), with certain exceptions. Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device.

74



### FIBER OPTICS LINEUP FOR AUDIO EQUIPMENT

RoHS

#### Fiber Optics Lineup for Audio Equipment

					High anod signal	Mod	el No.
Connector type	Туре	Outline	Featu	ires	High speed signal transmission	Supply voltage 3 to 5 V	Supply voltage 5 V
Square connector	Fiber optic transmitter	Without mounting hole	With shutter	Horizontal mounting type	MAX. 13.2 Mb/s		GP1FMV51TK0F
(EIAJ RC-5720B)			With Shutter	mounting type	MAX. 15.5 Mb/s	GP1FMV31TK0F	Grinwormon
()		With mounting hole	With shutter	Horizontal mounting type	MAX. 13.2 Mb/s		GP1FAV51TK0F*1
					MAX. 15.5 Mb/s	GP1FAV31TK0F	
					MAX. 50 Mb/s		GP1FAV55TK0F
				Vertical mounting type	MAX. 13.2 Mb/s		GP1FSV51TK0F
					MAX. 15.5 Mb/s	GP1FSV31TK0F (mounting height: 15 mm) GP1FSB31TK0F (mounting height: 8.5 mm)	
			With protection cap	Horizontal mounting type	MAX. 13.2 Mb/s		GP1FAV50TK0F*1
					MAX. 15.5 Mb/s	GP1FAV30TK0F	
	Fiber optic receiver	Without mounting hole	With shutter	Horizontal mounting type	MAX. 13.2 Mb/s		GP1FMV51RK0F
					MAX. 15.5 Mb/s	GP1FMV31RK0F	
		With mounting hole	With shutter	Horizontal mounting type	MAX. 13.2 Mb/s		GP1FAV51RK0F
					MAX. 15.5 Mb/s	GP1FAV31RK0F	
			With protection cap	Horizontal mounting type	MAX. 13.2 Mb/s		GP1FAV50RK0F
					MAX. 15.5 Mb/s	GP1FAV30RK0F	

\*1 TTL drive compatible



GP1FMV31 series (GP1FMV51 series)



GP1FAV50TK0F GP1FAV50RK0F, GP1FAV30TK0F, GP1FAV30RK0F



GP1FAV51TK0F GP1FAV31TK0F, GP1FAV55TK0F, GP1FAV51RK0F, GP1FAV31RK0F



GP1FSB31TK0F



GP1FSV31TK0F (GP1FSV51TK0F)

# FIBER OPTIC TRANSMITTERS (Square Connector) / FIBER OPTIC RECEIVERS (Square Connector)

(Ta = 25°C)

RoHS

#### ■ Fiber Optic Transmitters (Square Connector)

•			<b>`</b>	,							(14 - 20 0)	
	Appearance			Absolute max	kimum ratings	Electro-optical characteristics						
Model No.	Mounting		Features	Vcc (V)	Topr	Supply	Propagation delay time		Dissipation current	width	Transmis- sion speed	
	hole	Shutter			(°C)	voltage (V)	tPLH (ns) MAX.	tPHL (ns) MAX.	Icc (mA) MAX.	distortion ∆tw (ns)	T (Mb/s) MAX.	
GP1FMV31TK0F	No	Yes	Compact	-0.5 to +7	-20 to +70	2.7 to 5.25	180	180	12	±15	15.5	
GP1FMV51TK0F	No	Yes	Compact	-0.5 to +7	-20 to +70	4.75 to 5.25	180	180	13	±15	13.2	
GP1FAV30TK0F▲	Yes	No	Low voltage drive, with protection cap	-0.5 to +7	-20 to +70	2.7 to 5.25	180	180	12	±15	15.5	
GP1FAV50TK0F▲	Yes	No	TTL drive compatible, with protection cap	-0.5 to +7	-20 to +70	4.75 to 5.25 Input voltage: MIN. 2.0 V	180	180	13	±15	13.2	
GP1FAV51TK0F	Yes	Yes	TTL drive compatible	-0.5 to +7	-20 to +70	4.75 to 5.25	180	180	13	±15	13.2	
GP1FSV51TK0F	No	Yes	Vertical mounting (mounting height: 15 mm)	-0.5 to +7	-20 to +70	4.75 to 5.25	180	180	13	±15	13.2	
GP1FAV31TK0F	Yes	Yes	Low voltage drive	-0.5 to +7	-20 to +70	2.7 to 5.25	180	180	12	±15	15.5	
GP1FSV31TK0F	No	Yes	Vertical mounting (mounting height: 15 mm)	-0.5 to +7	-20 to +70	2.7 to 5.25	180	180	13	±15	15.5	
GP1FAV55TK0F	Yes	Yes	High response speed	-0.5 to +7	-20 to +70	4.75 to 5.25	180	180	13	±15	50	
GP1FSB31TK0F	No	Yes	Vertical mounting (mounting height: 8.5 mm)	-0.5 to +7	-20 to +70	2.7 to 5.25	180	180	13	±15	15.5	

The model marked with A may not be available in the near future. Contact with SHARP for details before use.

#### ■ Fiber Optic Receivers (Square Connector)

(Ta = 25°C)

-			• •	-								
Model No.	Appearance			Absolute maximum ratings			Electro-optical characteristics					
	Mounting hole Shu		Features	Vcc (V)	Iol (mA)	Topr (°C)	Supply voltage (V)	Propagation delay time		Dissipation current	Pulse width	Transmis- sion speed
		Shutter						tPLH (ns) MAX.	tPHL (ns) MAX.	Icc (mA) MAX.	distortion ∆tw (ns)	T (Mb/s) MAX.
GP1FMV31RK0F	No	Yes	Compact, low voltage drive	-0.5 to +7	10	-20 to +70	2.7 to 3.6	180	180	15	±20	15.5
GP1FMV51RK0F	No	Yes	Compact	-0.5 to +7	10	-20 to +70	4.75 to 5.25	180	180	25	±20	13.2
GP1FAV30RK0F	Yes	No	Low voltage drive, with protection cap	-0.5 to +7	10	-20 to +70	2.7 to 3.6	180	180	15	±20	15.5
GP1FAV50RK0F▲	Yes	No	With protection cap	-0.5 to +7	10	-20 to +70	4.75 to 5.25	180	180	25	±20	13.2
GP1FAV51RK0F	Yes	Yes		-0.5 to +7	10	-20 to +70	4.75 to 5.25	180	180	25	±20	13.2
GP1FAV31RK0F	Yes	Yes	Low voltage drive	-0.5 to +7	10	-20 to +70	2.7 to 3.6	180	180	15	±20	15.5

The model marked with ▲ may not be available in the near future. Contact with SHARP for details before use.

Notice

Notice In the absence of confirmation by device specification sheets, SHARP takes no responsibility for any defects that may occur in equipment using any SHARP devices shown in catalogs, data books, etc. Except where specially indicated, models listed on this page comply with the RoHS Directive\*. For details, please contact SHARP. \*RoHS Directive: Prohibits use of lead, cadmium, hexavalent chromium, mercury and specific brominated flame retardants (PBBs and PBDEs), with certain exceptions. Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device.

### RoHS

### ■ IR Detecting Unit for Remote Control Lineup (Classified by Form)

	Pac	kage			
Туре	Form	Detection position* <sup>5</sup> (from PCB)	Features	Operating voltage	Model No.
etecting unit mote control	Compact, thin typ SMD ( $4.5 \times 5.0 \times$			3 to 5 V General type	GP1USC3xXP series
	Compact type SMD (6.8 $\times$ 2.1 $\times$	2 35 t mm)		3 to 5 V	GP1UF31 series
	Lead L bend with shield case	2.55 ( 1111)		31037	Of TOF ST Series
	(holder)	16.0 mm*1	Compact size	3 to 5 V	GP1UE28XK0VF series
				5 V	GP1UM28XK0VF series
				3 to 5 V General type	GP1UE28xXKC4 series
			Compact size, Strengthened resistance to electromagnetic		
			induction noise (Mesh type)	3 to 5 V	GP1UE28RK0VF series
				5 V	GP1UM28RK0VF series
				3 to 5 V General type	GP1UE28xRKC4 series
		12.0 mm*2	Compact size	3 to 5 V	GP1UE27XK0VF series
				5 V	GP1UM27XK0VF series
				3 to 5 V General type	GP1UE27xXKC4 series
			Compact size, Strengthened resistance to electromagnetic induction noise (Mesh type)	3 to 5 V	GP1UE27RK0VF series
				5 V	GP1UM27RK0VF series
				3 to 5 V General type	GP1UE27xRKC4 series
		6.8 mm* <sup>3</sup>	Compact size	3 to 5 V	GP1UE26XK0VF series
				5 V	GP1UM26XK0VF series
				3 to 5 V General type	GP1UE26xXKC4 series
			Compact size, Strengthened resistance to electromagnetic		
			induction noise (Mesh type)	3 to 5 V	GP1UE26RK0VF series
				5 V	GP1UM26RK0VF series
	Lead straight with shield case		Compact size, Strengthened resistance to electromagnetic	3 to 5 V General type	GP1UE26xRKC4 series
	(holder)	19.0 mm	induction noise (Mesh type)	3 to 5 V	GP1UE29QK0VF series
				5 V	GP1UM29QK0VF series
				3 to 5 V General type	GP1UE29xQKC4 series
		9.6 mm	Compact size	3 to 5 V	GP1UE28YK0VF series
				5 V	GP1UM28YK0VF series
				3 to 5 V General type	GP1UE28xYKC4 series
			Compact size, Strengthened resistance to electromagnetic		
			induction noise (Mesh type)	3 to 5 V	GP1UE28QK0VF series
				5 V	GP1UM28QK0VF series
				3 to 5 V General type	GP1UE28xQKC4 series
	Holderless	Lead straight 6.0 mm		3 to 5 V	GP1UX31QS series
				5 V	GP1UX51QS series
				3 to 5 V General type	GP1UXC4xQS series
		Lead L bend*4 5.3 mm		3 to 5 V	GP1UX31RK series
				5 V	GP1UX51RK series

- \*1 Mesh type (strengthened resistance to electromagnetic induction noise): 16.4 mm
- \*3 Mesh type: 7.2 mm \*4 Mesh type: 5.3 mm
- \*2 Mesh type: 12.4 mm \*5 Lead straight: Distance Lead straight: Distance from lens center to mounting board upper surface No mesh lead L bend: Distance from tip of lens to mounting board upper surface Mesh-type lead L bend: Distance from tip of mesh to mounting board upper surface





### **IR DETECTING UNITS FOR REMOTE CONTROL**

RoHS

#### ■ IR Detecting Units for Remote Control

		Absolute mat	ximum ratings	Operating	ical charac	teristic	S				
Туре	Series No.	Vcc (V)	Topr (°C)	voltage (V)	Icc (mA) <sup>*1</sup> MAX.	Voн (V) MIN.	Vol (V) MAX.	fo (kHz) TYP.	Size (mm)	Terminal layout	
Surface-mount type, Reflow soldering	GP1UF31xXP0F/ *5 GP1UF31xYP0F	0 to 6.0	-30 to +85	2.7 to 5.5	0.4	Vcc-0.5	0.45	*4	$6.8 \times 2.1 \times 2.35$	-	
compatible	GP1USC3xXP	0 to 6.0	-30 to +85	2.7 to 5.5	0.6	Vcc-0.5	0.45	*3	5  imes 4.5  imes 1.3	-	
	GP1UE26xXKC4	0 to 6.0	-10 to +70	2.7 to 5.5	0.6	Vcc-0.5	0.45	*3	$5.6 \times 9.6 \times 6.8$		
ith shield case (holder),	GP1UE27xXKC4	0 to 6.0	-10 to +70	2.7 to 5.5	0.6	Vcc-0.5	0.45	*3	$5.6 \times 9.6 \times 12.0$		
3 to 5 V drive (New type)	GP1UE28xXKC4	0 to 6.0	-10 to +70	2.7 to 5.5	0.6	Vcc-0.5	0.45	*3	$5.6 \times 9.6 \times 16.0$		
	GP1UE28xYKC4	0 to 6.0	-10 to +70	2.7 to 5.5	0.6	Vcc-0.5	0.45	*3	5.6×8.6× 12.5(9.6)* <sup>2</sup>		
	GP1UE26xRKC4	0 to 6.0	-10 to +70	2.7 to 5.5	0.6	Vcc-0.5	0.45	*3	$5.6 \times 9.6 \times 7.2$	-	
ith shield case (holder),	GP1UE27xRKC4	0 to 6.0	-10 to +70	2.7 to 5.5	0.6	Vcc-0.5	0.45	*3	$5.6 \times 9.6 \times 12.4$		
o 5 V drive, engthened resistance to	GP1UE28xRKC4	0 to 6.0	-10 to +70	2.7 to 5.5	0.6	Vcc-0.5	0.45	*3	$5.6 \times 9.6 \times 16.4$		
ctromagnetic induction se (New type)	GP1UE28xQKC4	0 to 6.0	-10 to +70	2.7 to 5.5	0.6	Vcc-0.5	0.45	*3	5.6×9.0× 12.5(9.6)* <sup>2</sup>		
	GP1UE29xQKC4	0 to 6.0	-10 to +70	2.7 to 5.5	0.6	Vcc-0.5	0.45	*3	5.6 × 16.2 × 21.9(19)* <sup>2</sup>		
	GP1UM26XK0VF	0 to 6.0	-10 to +70	4.5 to 5.5	0.6 (0.65)	Vcc-0.5	0.45	*3	$5.6 \times 9.6 \times 6.8$		
th shield case (holder),	GP1UM27XK0VF	0 to 6.0	-10 to +70	4.5 to 5.5	0.6 (0.65)	Vcc-0.5	0.45	*3	$5.6 \times 9.6 \times 12.0$	-	
V drive	GP1UM28XK0VF	0 to 6.0	-10 to +70	4.5 to 5.5	0.6 (0.65)	Vcc-0.5	0.45	*3	$5.6\times9.6\times16.0$		
	GP1UM28YK0VF	0 to 6.0	-10 to +70	4.5 to 5.5	0.6 (0.65)	Vcc-0.5	0.45	*3	5.6×8.6× 12.5(9.6)* <sup>2</sup>		
	GP1UM26RK0VF	0 to 6.0	-10 to +70	4.5 to 5.5	0.6 (0.65)	Vcc-0.5	0.45	*3	$5.6 \times 9.6 \times 7.2$	Center Vcc	
h shield case (holder),	GP1UM27RK0VF	0 to 6.0	-10 to +70	4.5 to 5.5	0.6 (0.65)	Vcc-0.5	0.45	*3	$5.6 \times 9.6 \times 12.4$	VCC	
drive, ngthened resistance to	GP1UM28RK0VF	0 to 6.0	-10 to +70	4.5 to 5.5	0.6 (0.65)	Vcc-0.5	0.45	*3	$5.6\times9.6\times16.4$		
tromagnetic induction e	GP1UM28QK0VF	0 to 6.0	-10 to +70	4.5 to 5.5	0.6 (0.65)	Vcc-0.5	0.45	*3	5.6×9.0× 12.5(9.6)* <sup>2</sup>		
	GP1UM29QK0VF	0 to 6.0	-10 to +70	4.5 to 5.5	0.6 (0.65)	Vcc-0.5	0.45	*3	5.6 × 16.2 × 21.9(19)* <sup>2</sup>		
	GP1UE26XK0VF	0 to 6.0	-10 to +70	2.7 to 5.5	0.4	Vcc-0.5	0.45	*3	$5.6 \times 9.6 \times 6.8$	-	
h shield case (holder),	GP1UE27XK0VF	0 to 6.0	-10 to +70	2.7 to 5.5	0.4	Vcc-0.5	0.45	*3	$5.6 \times 9.6 \times 12.0$		
5 V drive	GP1UE28XK0VF	0 to 6.0	-10 to +70	2.7 to 5.5	0.4	Vcc-0.5	0.45	*3	$5.6 \times 9.6 \times 16.0$		
	GP1UE28YK0VF	0 to 6.0	-10 to +70	2.7 to 5.5	0.4	Vcc-0.5	0.45	*3	5.6×8.6× 12.5(9.6)* <sup>2</sup>		
	GP1UE26RK0VF	0 to 6.0	-10 to +70	2.7 to 5.5	0.4	Vcc-0.5	0.45	*3	$5.6 \times 9.6 \times 7.2$		
h shield case (holder),	GP1UE27RK0VF	0 to 6.0	-10 to +70	2.7 to 5.5	0.4	Vcc-0.5	0.45	*3	$5.6 \times 9.6 \times 12.4$		
5 V drive, engthened resistance to	GP1UE28RK0VF	0 to 6.0	-10 to +70	2.7 to 5.5	0.4	Vcc-0.5	0.45	*3	$5.6 \times 9.6 \times 16.4$		
ctromagnetic induction se	GP1UE28QK0VF	0 to 6.0	-10 to +70	2.7 to 5.5	0.4	Vcc-0.5	0.45	*3	5.6×9.0× 12.5(9.6)* <sup>2</sup>		
	GP1UE29QK0VF	0 to 6.0	-10 to +70	2.7 to 5.5	0.4	Vcc-0.5	0.45	*3	5.6×16.2× 21.9(19)* <sup>2</sup>		
Iderless, 3 to 5 V drive, engthened resistance to	GP1UXC4xQS	0 to 6.0	-10 to +70	2.7 to 5.5	0.6	Vcc-0.5	0.45	*3	$5.5\times5.3\times7.5$		
electromagnetic induction noise (New type)	GP1UXC4xRK	0 to 6.0	-10 to +70	2.7 to 5.5	0.6	Vcc-0.5	0.45	*3	$5.5\times5.3\times7.5$		
olderless, 5 V drive, rengthened resistance to	GP1UX51QS	0 to 6.0	-10 to +70	4.5 to 5.5	0.6	Vcc-0.5	0.45	*3	$5.5 \times 5.3 \times 7.5$	Center	
ectromagnetic induction ise	GP1UX51RK	0 to 6.0	-10 to +70	4.5 to 5.5	0.6	Vcc-0.5	0.45	*3	$5.5\times5.3\times7.5$	GND	
olderless, 3 to 5 V drive,	GP1UX31QS	0 to 6.0	-10 to +70	4.5 to 5.5	0.4	Vcc-0.5	0.45	*3	5.5  imes 5.3  imes 7.5	1	
rengthened resistance to ectromagnetic induction											



A voltage regulator circuit is built-in but hay be affected by the usage environment of the set of the usage environment of the set of the usage environment o

\*5 GP1UF31xXP0F: Top view taped package, GP1UF31xYP0F: Side view taped package